




PELTOR™
Protection & Communication

Keep connected while protected.

3M™ PELTOR™ WS™ ALERT™ XP Headset 
Third Gen XP - Now with App support

Turn your hearing protection into a quiet office you wear to work. Conduct business from inside your headset by connecting to your mobile device using Bluetooth® technology. Talk in a normal volume even in noisy environments by using the noise-canceling boom microphone.

Registering your headset with the 3M™ Connected Equipment App allows you to easily navigate the headset's menus and adjust all of the settings, including the ambient listening volume and programmable FM radio stations.

3M Science. Applied to life.™

Keep working while conversing.

Turn your hearing protection into a quiet office you wear to work. In low noise, the ambient/environmental microphones can increase your ability to communicate with nearby colleagues as well as hear warning signals, approaching vehicles, and critical other machine sounds or processes to help keep you safe.

Voice-guided menus

Navigate ON/OFF, volume, and menus – all while wearing gloves. No need to remove the headset for any adjustments. Get immediate voice confirmation after every setting adjustment, including a “low battery” voice alert.

Push-to-Listen function

The Push-to-listen (PTL) feature allows you to instantly pause your Bluetooth® streaming or turn off the FM radio volume, while increasing your ambient/environmental listening ability, without being tempted to remove your headset.

Ambient/Environmental microphones help promote auditory situational awareness.

Ambient microphones help you hear oncoming vehicles, alerts, and other warning signals while providing hearing protection when you need it.

Bluetooth® connectivity



Simultaneous, seamless connection to Bluetooth® devices allows for flexibility and mobility. While keeping your hearing protection on, you can easily setup and adjust the headset functions using the iOS and Android compatible mobile 3M™ Connected Equipment App on your phone.

Carry on conversations

Since the headset comes with a noise-cancelling boom microphone, you can stop shouting and now speak in a normal volume.



Built in FM-Radio

With vocalized channel selection

Durable, practical electronics

To help reduce corrosion caused by sweat, the electronics are located in the outer part of the cup. The dual-shell design helps protect the electronics from moisture.

Two models: Headband or helmet attachment

Both feature long-lasting, stainless steel wire bands that can help provide consistent wear.

Power saving options

Auto-OFF after 4 hours of non-use. Uses two AA alkaline batteries (or optional LR6NM NiMH rechargeable batteries).



“Since my employees and I usually work at different places on the farm at the same time, we need to discuss issues continuously throughout the working days. I can easily keep in touch with them through the help of my headset. The best thing about the headset is how robust it is and how it can handle all the different environments we work in, both dirty and noisy surroundings, where I can have my hands free to work while I talk to my employees and others. My PELTOR headset almost feels like a colleague I do not want to be without.”

Martin, Farmer



Get the app using the QR codes below



3M™ Connected Equipment



You can download the 3M™ Connected Equipment app that provides ready access to:

- Easily navigate the headset’s menus to set and adjust all of its settings
- Hygiene kit reminder to let you know when it is time to change the cushions and foamliners
- User Instructions (both as text and videos)
- Guides
- FAQs
- Tech support contacts
- Important tech data sheet information



App Store (iOS)




Google Play (Android)

This mobile app is free of charge and is part of the 3M™ Connected Equipment suite, which enables users to manage, operate and view the status of all your 3M Connected personal protective equipment in one place.

The headset app comes in English as well as several other language options and is iOS and Android compatible.

Hearing protection with enhanced situational awareness

In low noise, ambient/environmental microphones can increase your ability to communicate with nearby colleagues, as well as hear warning signals, approaching vehicles and other machine sounds or processes when needed.



“During the manufacturing process, it is important that everything is done in the right order and that nothing goes wrong so we can produce the most amount of beverage for our customers. By using these PELTOR headsets we can easily connect into a mobile group call and talk to each other while still working in this noisy environment where we are apart from one another. If something goes wrong in the manufacturing line, we can quickly remedy the problem and work efficiently without interruptions. Once you start using this headset, you do not understand how you can manage without it.”

Anders, Brewery worker



Headset models

Article number	Description	Legacy 3M ID	SAP ID
MRX21A5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, App, MRX21A5WS6, grey, headband	UU011473848	7100256283
MRX21P3E5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, App, MRX21P3E5WS6, grey, helmet attachment ¹⁾	UU011473830	7100256282

Spareparts & Accessories

Article number	Description	Legacy 3M ID	SAP ID
HY82	3M™ PELTOR™ HY82 Hygiene kit (cushion and foamliner)	UU008567388	7100122439
HY80	3M™ PELTOR™ HY80 Gel Sealing Ring	70071524139	7000127268
LR6NM	3M™ PELTOR™ LR6NM NiMH rechargeable AA batteries, 2 ea	XH001659693	7100064688
MT53N-14/1	3M™ PELTOR™ Electret boom microphone, 240mm with plug incl windshield M995/2	UU011614862	7100264326
M995/2	3M™ PELTOR™ M995 Wind shield for speech microphone, 2 ea	XH001679154	7010044372
HYM1000	3M™ PELTOR™ HYM1000 Microphone protection, 4.5 meters	XH001651328	7100064281
210300-664-GF/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, grey, 1 pair (left+right)	UU011614870	7100264003
210300-664-GY/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, bright yellow, 1 pair (left+right)	UU011614854	7100264002
210300-664-RD/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, red, 1 pair (left+right)	UU011321732	7100246986
210300-664-BA/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, blue, 1 pair (left+right)	UU011321724	7100246985
210300-664-OR/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, orange, 1 pair (left+right)	UU011321153	7100246983
210300-664-RE/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, pink, 1 pair (left+right)	UU011321138	7100247026
210300-664-SV/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, black, 1 pair (left+right)	UU010322590	7100253622
210300-664-GB/1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, neon green, 1 pair (left+right)	UU011140447	7100240624
HY100A	3M™ PELTOR™ HY100A Clean hygiene pads, single-use, self-adhesive, 100 ea/case	XH001651351	7100064410
FR08	3M™ PELTOR™ FR08 Power supply with USB connector	XH001680194	7000108521
FR09	3M™ PELTOR™ FR09 Battery charger with USB connector	XH001680616	7100075611

Approvals

Hereby, 3M Svenska AB declares that the product is in compliance with appropriate Directives or Regulations to fulfill the requirements for the CE and/or UKCA marking. The full text of the Declaration of Conformity is available at the following internet address: www.3M.com/PELTOR/DOC. A copy of the Declaration of Conformity and additional information required in the Directives or Regulations can also be obtained by contacting 3M in the country of purchase.”

1) The safety helmet attachment is certified with several safety helmets. See the User Instruction for the list of compatible helmets.

3M™ PSD products are for occupational use only.

In Europe, 3M PELTOR products may also be appropriate for certain non-work uses.

Please recycle. Printed in Sweden. © 3M 2022. All rights reserved. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by 3M Company is under license. 3M, PELTOR, WS and ALERT are trademarks of 3M Company, used under license in Canada.



3M Personal Safety Division
3M Svenska AB
Box 2341
SE-331 02 Värnamo, Sweden
www.3M.com