


3M™ FASARA™ Glass Finishes Sheet Format

NOTE: Refer to the 3M™ FASARA™ Installation Guide for complete installation instructions


Refer to the 3M™ FASARA™ Technical Datasheet for complete product information.

The images below show the size and gradation layout of 3M™ FASARA™ Seamless Series.

Illumina Silky






SH2SSIM-W/Illumina Silky-W



SH2SSIM-S/Illumina Silky-S

Illumina Seamless



SH2SSIM-Illumina Seamless-W2 SH2SSIM-S2/Illumina Seamless-S2 SH2SSIM-PR/Illumina Seamless-PR

Size Lists

	Product Number	Product Name	Sheet Size		Print Size	
			Width	Length	Width	Length
Illumina Silky	SH2SSIM-W	Illumina Silky-W	60 in./50 in. (152.4 cm/127 cm)	120 in. (305 cm)	57.1 in./47.6 in. (145 cm/121 cm)	116.1 in. (295 cm)
	SH2SSIM-S	Illumina Silky-S	60 in./50 in. (152.4 cm/127 cm)	81.9 in. (208 cm)	57.1 in./47.6 in. (145 cm/121 cm)	76.4 in. (194 cm)
Illumina Seamless	SH2SSIM-W2	Illumina Seamless-W2	60 in. (152.4 cm)	122 in. (310 cm)	57.1 in. (145 cm)	118 in. (300 cm)
	SH2SSIM-S2	Illumina Seamless-S2	60 in. (152.4 cm)	122 in. (310 cm)	57.1 in. (145 cm)	118 in. (300 cm)
	SH2SSIM-PR	Illumina Seamless-PR	60 in. (152.4 cm)	122 in (310 cm)	57.1 in. (145 cm)	118 in. (300 cm)

NOTE: For additional questions, refer to 3M Technical Service at 1-800-328-3908.

Warranty Information

Technical Information

The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment, reviewing all applicable regulations and standards, and reviewing the product label and use instructions. Failure to properly evaluate, select, and use a 3M product in accordance with instructions or to meet all applicable safety regulations may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Commercial Solutions

3M Center, Building 220-12E-04
St. Paul, MN 55144
1-800-328-3908
3M.com/AMD

© 3M 2022. All rights reserved. 3M and FASARA are registered trademarks of 3M. Used under license by 3M subsidiaries and affiliates.
Revision A, February 2022
Please recycle.

