



PELTOR™
Protection & Communication

3M™ PELTOR™ Professional In-Ear
Communication Headset, PIC-100 NA

**Close-connect
wireless technology
for team communication.**

The next generation protective communication solution.

With the 3M™ PELTOR™ PIC-100 NA Headset, 3M™ PELTOR™ Brand is introducing multiple innovative technologies to help workers stay protected and productive.



Hearing protection with on-demand fit test.

Featuring on-demand fit test functionality at the push of a button, users can obtain their current personal protection level, and thereby help to ensure they have appropriate protection for their hazardous noise environment. Compatible with a number of different eartip styles and sizes, users can choose the eartips they prefer and ones that provide adequate protection.

- Replaceable eartips in multiple types and sizes
- On-demand fit test assesses the wearer's current personal protection level: a binaural personal attenuation rating (PAR) at the push of a button
- A field attenuation estimation system (FAES) designed to perform as outlined in ANSI/ASA S12.71-201 Lab testing to certify ANSI S12.71 compliance is currently in progress





Environmental listening.

The 3M™ PELTOR™ Professional In-Ear Communication Headset PIC-100 NA features environmental listening technology. This assists workers to communicate face-to-face, in low or intermittent noise, and to hear environmental sounds at safe levels without being tempted to remove or poorly fit their hearing protection.

- Environmental microphones
- Compresses sound through the environmental microphones down below ≈ 82 dBA
- Adjustable volume levels
- Helps to communicate in lower noise environments while still protected

Bluetooth® technology.



The 3M™ PELTOR™ Professional In-Ear Communication Headset PIC-100 NA comes with **Bluetooth®** wireless communication technology for connection to smart devices and two-way radios. **Bluetooth®** multipoint technology for simultaneous, wireless connection to two devices.

For added long-range communication capability, simply connect to **Bluetooth®** enabled:

- Smart phones
- Tablets
- Two-way radios

3M™ Connected Safety System App

The 3M™ Connected Safety System App allows users to easily navigate the headset's menu and make adjustments. The App also provides ready access to User Instructions, FAQs, instructional videos and tech support contacts. In addition, the app enables over-the-air firmware updates.



Close-connect wireless technology for team communication.

The 3M™ PELTOR™ Professional In-Ear Communication Headset PIC-100 NA headset features 3M's innovative close-connect wireless technology that allows multiple people to speak simultaneously, headset to headset, enabling communication in a variety of noisy environments when workers are in close proximity. Headsets automatically connect with one another as they come into range without any need for pairing. Voice Operated Transmission (VOX) enables users to seamlessly communicate, hands-free, without the touch of a button.

- 6 separate channels enable multiple groups to operate independently without interference
- Configurable listening/talking options: Double press to change settings: VOX (voice activated transmission) and PTT (push-to-talk activated transmission)
- LED channel indication
- No need for pairing; all PIC-100 headsets automatically connect to each other when in range




Close-connect wireless technology for team communication.

Up to

50
listeners

4 Full-duplex,
simultaneous
talkers



~ 20 m (22 yd)
Depending on conditions



In-ear communication microphone.

Featuring an in-ear speech microphone, the 3M™ PELTOR™ Professional In-Ear Communication Headset PIC-100 NA headset is not dependent on a boom microphone near the mouth to detect speech, making it compatible with a wide range of personal protective equipment, including respirators.

- In-ear speech microphones in the earplugs pick up voice, eliminating the need for a traditional boom microphone
- On-demand fit test helps assess the wearer's current personal protection level and promote speech clarity and transmission
- Features a de-noising algorithm to help improve speech intelligibility in noisy environments*
- In-ear speech microphones make it compatible with most 3M respiratory protection including PAPRs, reusable respirators (full face and half face), and disposable respirators**. No boom microphone necessary

* Speech intelligibility, using an in-ear microphone, may vary between different communication devices, and from person to person.

** Based on 3M internal evaluation including PAPRs, reusable respirators (full face and half face) and disposable respirators.





Earmuff compatibility.

The 3M™ PELTOR™ PIC-100 System Control Unit (SCU) can also be connected to the 3M™ PELTOR™ CH-3* Headset via a 3M™ PELTOR™ FLX2 Cable for an over-the-ear configuration (headset and FLX2 cable available separately).

*No environmental listening function or real-time fit test.



+



+



PIC-100 System Control Unit (SCU)

FLX2-214 Cable

CH-3 Headset

Key Performance Specifications

Power:	
Battery type:	Removable Li-ion
Operating time:	Approximately 16 h
Charging time:	Approximately 4 h
Charging jack:	USB Type C 3.1
Headset-to-Headset Full Duplex Radio:	
Range:	Approximately 20 m (22 yd) depending on conditions
Channels:	6
Channel capacity:	Up to 4 talkers and 50 listeners per channel
Modulation:	Time-division multiple access (TDMA) protocol
Frequency band:	915 MHz (North America)
Operation mode:	Full Duplex
Bluetooth® Technology :	
Bluetooth version:	v5.1
Bluetooth headset profile (HSP):	1.2
Bluetooth hands-free profile (HFP):	1.7.1
Bluetooth audio/video remote control profile (AVRCP):	1.6
Bluetooth advanced audio distribution profile (A2DP):	1.3.1
Bluetooth Range:	Up to 10 m (32 ft) (class 2)
Multi-point connection:	Yes
Environmental Characteristics:	
Operating temp:	-20 °C to +50 °C (-4 °F to 122 °F)
Charging temp:	10 °C (50 °F) to +30 °C (86 °F)
Product Life:	Headset (2 years), SCU (4 years), Battery (2 years*)
Ingress Protection:	IP54 compliant
Physical Characteristics:	
Control Unit Size:	L: 101 mm (3.96 in) W: 65 mm (2.55 in) H: 35 mm (1.37 in)
Weight:	Headset (~32 g (1 oz)) SCU w/battery (~134 g (4.65 oz))
Recommended Storage Conditions :	
(<90% humidity)	-20 °C to +40 °C (-4 °F to 104 °F)
Approvals	
US and Canada	Noise Reduction Rating (NRR) tested in accordance with ANSI S3.19-1974
US and Canada	ANSI/ASA S1271-2018

*NOTE: While stored, if possible, keep the batteries separate. Rechargeable Li-Ion batteries (removable and non-removable) have to be recharged every 6 months, not to lose capacity.

Laboratory Attenuation (ANSI S3.19-1974)

3M™ PELTOR™ Triple-C Communication Eartips CCC-GRM-25

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000	NRR*	CSA Class
Mean Attenuation (dB)	33.4	34.2	37.3	38.8	38.1	43.3	40.9	45.9	47.1	27	AL
Standard Deviation (dB)	5.5	6.0	6.4	6.1	3.0	4.1	4.4	4.1	4.4		

PIC-100 with 3M™ UltraFit™ Communication Eartips

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000	NRR*	CSA Class
Mean Attenuation (dB)	34.7	35.4	35.0	32.8	33.0	37.4	30.6	40.9	45.4	21	AL
Standard Deviation (dB)	6.9	5.1	6.0	5.1	5.2	5.7	6.6	7.9	4.6		

PIC-100 with 3M™ Skull Screw Communication Eartips

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000	NRR*	CSA Class
Mean Attenuation (dB)	41.1	40.5	44.9	43.1	40.6	45.7	44.6	48.2	48.5	33	AL
Standard Deviation (dB)	6.3	6.0	5.9	4.0	3.4	3.5	4.0	5.1	4.2		

*See important warnings on last page.

Models

Model #	SAP I.D.	3M I.D.	Description
PIC-100 NA	7100262767	70071766359	3M™ PELTOR™ Professional In-Ear Communication Headset, PIC-100 NA

Accessories and Replacement Parts

Model #	SAP I.D.	3M I.D.	Description
PIC-100HD	7100262876	70071766284	3M™ PELTOR™ Replacement Headset, PIC-100HD
PIC-100BA	7100262644	70071766292	3M™ PELTOR™ Replacement Battery, PIC-100BA
PIC-100CL	7100262875	70071766318	3M™ PELTOR™ Replacement Clip, PIC-100CL
PIC-100CS	7100268555	70071766276	3M™ PELTOR™ Charging Station, PIC-100CS
CCC-GRM-25	7100103087	70071675212	3M™ PELTOR™ CCC-GRM-25 Communication Eartips, 25 pairs
370-TEPL-25	7100066388	70071673746	3M™ UltraFit™ Communication Eartips, Large, 25 pairs
370-TEPM-25	7100066387	70071673738	3M™ UltraFit™ Communication Eartips, Medium, 25 pairs
370-TEPS-25	7100066371	70071673720	3M™ UltraFit™ Communication Eartips, Small, 25 pairs
370-1019-10	7000108492	70071615275	3M™ Skull Screws™ Communication Eartips, 10 pairs

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

WARNING!

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. **Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury.** For correct use, consult supervisor and User Instructions, or call 3M PSD Technical Service in Canada at 1-800-267-4414 and in the USA at 1-800-665-2942.

WARNING!

U.S EPA specifies the NRR as the measure of hearing protector noise reduction. However, 3M makes no warranties as to the suitability of the NRR for this purpose. 3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user. Refer to applicable regulations and guidance on how to adjust attenuation label value(s). It is recommended that the NRR be reduced by 50% to better estimate typical protection.



3M Personal Safety Division
3M Canada
P.O. Box 5757
London, ON N6A 4T1

For more information:
Technical Service: 1-855-484-3093
3M.ca/PELTOR

3M PSD products are occupational use only. Please recycle. Printed in Canada. 3M, PELTOR, UltraFit and Skull Screws are trademarks of 3M. All other trademarks are the trademarks of their respective owners. Used under license in Canada. © 2022, 3M. All rights reserved. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by 3M Company is under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. 2209-24865 E