


**3M**

**SCOTT™**  
Fire & Safety

# Product Catalog



# Product Listing







# Table of Contents

| Self-Contained Breathing Apparatus (SCBA)                  |       |
|------------------------------------------------------------|-------|
| NFPA SCBA                                                  |       |
| 3M™ Scott™ Air-Pak™ X3 Pro SCBA                            | 6     |
| 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt            | 7     |
| SCBA Accessories                                           | 7     |
| 3M™ Scott™ X3-21 Pro SCBA                                  | 8     |
| NIOSH SCBA                                                 |       |
| 3M™ Scott™ Air-Pak™ 75i SCBA                               | 10    |
| 3M™ Scott™ Industrial SCBA                                 | 12-14 |
| 3M™ Scott™ ACSi SCBA                                       | 14-16 |
| Cylinders                                                  |       |
| 3M™ Scott™ SCBA Cylinders                                  | 17-18 |
| Cylinder Accessories                                       | 19    |
| Facepieces                                                 |       |
| 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator   | 20-22 |
| 3M™ Scott™ AV-3000 HT Facepiece                            | 23-25 |
| 3M™ Scott™ AV-3000 SureSeal Facepiece                      | 26-28 |
| 3M™ Scott™ Weld-O-Vista Facepiece                          | 29-31 |
| Voice Communications                                       |       |
| 3M™ Scott™ Vision C5 Facepiece with Radio Direct Interface | 32-33 |
| 3M™ Scott™ EPIC 3 Voice Communications                     | 34-35 |
| SCBA Telemetry and Software Solutions                      |       |
| 3M™ Scott™ Monitor Telemetry Software Solution             | 36    |
| 3M™ Safety & Inspection Manager for Emergency Services     | 37    |
| Search and Rescue                                          |       |
| Thermal Imagers                                            |       |
| 3M™ Scott™ V320 Thermal Imager                             | 38    |
| 3M™ Scott™ Sight In-Mask Thermal Imager                    | 39-40 |
| Firefighter Location                                       |       |
| 3M™ Scott™ Pak-Tracker Firefighter Locator System          | 41    |
| Rapid Intervention                                         |       |
| 3M™ Scott™ RIT-Pak Fast Attack Emergency Air Supply        | 42    |
| 3M™ Scott™ RIT-Pak III Emergency Air Supply                | 43    |

| Respiratory                                                |       |
|------------------------------------------------------------|-------|
| Cartridges, Canisters, Filters and Adapters                |       |
| 3M™ Scott™ AV-632 Bayonet Adapter                          | 44    |
| 3M™ Particulate Filters and Cartridges                     | 45-46 |
| 3M™ Scott™ 40 mm Cartridges, Canister and Filters          | 46    |
| Fit Testing Kits and Accessories                           |       |
| 3M™ Qualitative Fit Test Kit                               | 47    |
| Powered and Supplied Air                                   |       |
| 3M™ Scott™ C420 Plus CBRN Powered Air Purifying Respirator | 48-49 |
| 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator              | 50-52 |
| 3M™ Scott™ Ska-Pak Plus Supplied-Air Respirator            | 53-55 |
| 3M™ Scott™ Ska-Pak Supplied-Air Respirator                 | 56-58 |
| 3M™ Scott™ E-Z Airline Supplied-Air Respirator             | 59-61 |
| 3M™ Scott™ Mobile Air Cart                                 | 62    |
| 3M™ Scott™ TRC-1 Air Cart                                  | 62    |
| Emergency Escape                                           |       |
| 3M™ Scott™ ELSA Emergency Escape Breathing Device (EEBD)-N | 63    |

# Self-Contained Breathing Apparatus (SCBA)



## 3M™ Scott™ Air-Pak™ X3 Pro SCBA

NFPA 1981/1982, 2018 Edition

Built-to Specification Configurator

| SCBA Belt Type (select one number from both columns) |            |                 |                                                   |                           |                                             |         |                |                                |                                                       |        |             |                |
|------------------------------------------------------|------------|-----------------|---------------------------------------------------|---------------------------|---------------------------------------------|---------|----------------|--------------------------------|-------------------------------------------------------|--------|-------------|----------------|
| SCBA Model                                           | Harness    | Pressure (psig) | Belt Type                                         | Accessory Pouch           | Regulator ④                                 | EBSS    | Airline Option | Spare Harness ⑤                | Console Price includes the HUD for all configurations | Case ② | Packaging ③ |                |
| 8 Air-Pak X3 Pro (CGA)                               | 1 Standard | 2 2216          | 0 Standard                                        | 2 None                    | 1 E-Z Flo+, Continuous Hose                 | 0 None  | 0 None         | 1 Yes (UEBSS)                  | 3 Pak-Tracker                                         | 0 None | 3           | 1 SCBA per Box |
| 9 Air-Pak X3 Pro (Snap-Change)                       |            | 4 4500          | N EZ-Scape Pro Firefighter Escape Belt (Fixed)    | G Hip Pouch (No Hardware) | 3 E-Z Flo C5, Continuous Hose               | 3 UEBSS |                | 2 Yes                          | A SEMS II Pro                                         |        | 4           | 2 SCBA per Box |
|                                                      |            | 5 5500          | P EZ-Scape Pro Firefighter Escape Belt (Jettison) |                           | 5 E-Z Flo+, Quick Disconnect Hose, Rectus   |         |                | 3 Yes (EZ-Scape Pro and UEBSS) | H SEMS II Pro Hazmat ①                                |        |             |                |
|                                                      |            |                 |                                                   |                           | 6 E-Z Flo C5, Quick Disconnect Hose, Rectus |         |                | 4 Yes (EZ-Scape Pro)           |                                                       |        |             |                |
|                                                      |            |                 |                                                   |                           |                                             |         |                | 5 No                           |                                                       |        |             |                |

1. Part Number:  
Select a one digit number per box from the chart above that corresponds to your choice.

|    |   |   |   |   |   |   |   |   |   |   |   |   |
|----|---|---|---|---|---|---|---|---|---|---|---|---|
| X8 | X | X | X | X | X | X | X | X | X | X | X | X |
|----|---|---|---|---|---|---|---|---|---|---|---|---|

- ① SEMS II Pro Hazmat (motion sensor disabled) does not comply with the requirements of NFPA 1982, 2018 Edition.
- ② Case option must be ordered separately.
- ③ Air-Pak X3 Pro SCBA may only be packaged 1 SCBA per box when configured with a spare harness kit.
- ④ When selecting the E-Z Flo C5 regulator, you must also choose the Vision C5 facepiece for compatibility.
- ⑤ Spare harness does not include optional accessory pouch.

Example  
Air-Pak X3 Pro SCBA  
Snap-Change, 5500 psig,  
Standard Waist Belt, E-Z  
Flo+ Regulator with Quick  
Disconnect Hose, UEBSS,  
SEMS II Pro, Shipped (1) per  
Box (black)

|    |   |   |   |   |   |   |   |   |   |   |   |   |
|----|---|---|---|---|---|---|---|---|---|---|---|---|
| X8 | 9 | 1 | 5 | 0 | 2 | 6 | 3 | 0 | 5 | A | 0 | 3 |
|----|---|---|---|---|---|---|---|---|---|---|---|---|

This configurator is a guide to 3M™ Scott™ Air-Pak™ SCBA part numbers certified to the NFPA 1981, 2018 Edition Standard.

# 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt



The 3M™ Scott™ EZ-Scape Pro Integrated Self-Rescue Belt (full bailout system) is no longer available. Please contact 3M Scott Technical Support for replacement options.

## 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt and Pouch Options (compatible with 3M™ Scott™ Air-Pak™ X3 Pro SCBA)

| Part Number | Description                                                                                       |
|-------------|---------------------------------------------------------------------------------------------------|
| 201096-38   | EZ-Scape Pro Firefighter Escape Belt, Air-Pak X3 Pro, Waist Belt Only – Jettison                  |
| 201096-36   | EZ-Scape Pro Firefighter Escape Belt, Air-Pak X3 Pro, Waist Belt and Hip Pouch (empty) – Jettison |
| 201096-08   | EZ-Scape Pro Firefighter Escape Belt, Air-Pak X3 Pro, Waist Belt Only – Fixed                     |
| 201096-06   | EZ-Scape Pro Firefighter Escape Belt, Air-Pak X3 Pro, Waist Belt and Hip Pouch (empty) – Fixed    |

The 3M™ Scott™ EZ-Scape Pro Accessory Pouch attaches to the 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt and is compatible with the 3M™ Scott™ Air-Pak™ X3 Pro SCBA. The accessory pouch may be used to store a NFPA 1983 certified bailout system, provided the system fits inside the pouch and can connect to the integrated D-ring on the 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt. The accessory pouch is supplied empty and does not include bailout hardware (anchor, descender, escape rope).

## Accessories for 3M™ Scott™ EZ-Scape Pro Firefighter Escape Belt

| Part Number    | Description                  |
|----------------|------------------------------|
| 78-8151-3609-4 | EZ-Scape Pro Accessory Pouch |
| 31003385       | Multi-Use Ladder Strap       |

# SCBA Accessories

| Part Number | Description                                                           |
|-------------|-----------------------------------------------------------------------|
| 805511-01   | Chest Strap (Air-Pak Wireframe, Air-Pak 75, Air-Pak X3 SCBA)          |
| 201612-01   | Chest Strap, Universal (Air-Pak X3 Pro SCBA)                          |
| 200112-01   | Extended Duration Adapter Assy, Hansen                                |
| 200112-02   | Extended Duration Adapter Assy, Foster                                |
| 200112-03   | Extended Duration Adapter Assy, Hansen HK                             |
| 200112-04   | Extended Duration Adapter Assy, Schrader                              |
| 201729-01   | Extended Duration Adapter Assy, Hansen, UEBSS                         |
| 201729-02   | Extended Duration Adapter Assy, Foster, UEBSS                         |
| 201729-03   | Extended Duration Adapter Assy, Hansen HK, UEBSS                      |
| 201729-04   | Extended Duration Adapter Assy, Schrader, UEBSS                       |
| 200388-01*  | Tool Adapter, Snap Change                                             |
| 803620-03** | Pass Thru Assembly, Hansen                                            |
| 803620-04** | Pass Thru Assembly, Schrader                                          |
| 803620-05   | Pass Thru Assembly, CEJN                                              |
| 805088-01   | Waist Belt Extension (Air-Pak Wireframe, Air-Pak 75, Air-Pak X3 SCBA) |
| 201614-01   | Waist Belt Extension (Air-Pak X3 Pro SCBA)                            |
| 200673-01*  | Pak-Link Programmer/Data-logger                                       |

\* Accommodates 2.2, 4.5, and 5.5 Snap-Change Cylinders.

\*\* For use with Dual EBSS in an encapsulated protective suit.

\* For use in downloading PASS data from any 3M™ Scott™ Air-Pak™ SCBA certified to the NFPA 1981/1982, 2007 Edition standards (and newer) including pneumatic data introduced as part of the 2018 Edition standard; may also be used for programming the 3M™ Scott™ Pak-Tracker Firefighter Locator System ID of a 3M™ Scott™ Air-Pak™ SCBA.

Note: For 3M™ Scott™ Air-Pak™ X3 Pro SCBA, customers may also use the mobile application.

# Self-Contained Breathing Apparatus (SCBA)



## 3M™ Scott™ X3-21 Pro SCBA

NFPA 1986, 2017 Edition

Built-to Specification Configurator

| SCBA Model  | Cylinder Connection | Pressure (psig) | Cylinder Shroud | Regulator Type                                               | EBSS   | Spare Harness           | Case                            | Packaging ①      |
|-------------|---------------------|-----------------|-----------------|--------------------------------------------------------------|--------|-------------------------|---------------------------------|------------------|
| 6 X3-21 Pro | 1 CGA Threaded      | 4 4500          | 0 No            | 1 E-Z Flo+, Quick Disconnect Hose (Hansen), Heads-Up Display | 0 None | 0 None                  | 0 None                          | 1 1 SCBA per Box |
|             | 2 Snap-Change       | 5 5500          | 1 Yes           | 2 E-Z Flo+, Quick Disconnect Hose (Hansen)                   | 1 Dual | 2 Yes (with EBSS Pouch) | 1 Hard Plastic<br>2 Soft Canvas | 2 2 SCBA per Box |

1. Part Number:  
Select a one digit number per box from the chart above that corresponds to your choice.

|       |   |   |   |   |   |   |   |   |   |
|-------|---|---|---|---|---|---|---|---|---|
| X321- | X | X | X | X | X | X | X | X | X |
|-------|---|---|---|---|---|---|---|---|---|

① X3-21 Pro may only be packaged 1 SCBA per box when configured with a spare harness kit or when selecting a case option.

Example

X3-21 Pro SCBA  
Snap-Change, 5500 psig, Cylinder Shroud, E-Z Flo+ Regulator with Quick Disconnect Hose, Dual EBSS Accessory Hose, Shipped (2) per Box

|       |   |   |   |   |   |   |   |   |   |
|-------|---|---|---|---|---|---|---|---|---|
| X321- | 6 | 2 | 5 | 1 | 2 | 1 | 0 | 0 | 2 |
|-------|---|---|---|---|---|---|---|---|---|

This configurator is a guide for selecting 3M™ Scott™ X3-21 Pro SCBA part numbers certified to the NFPA 1986, 2017 Edition Standard.

# Accessories for 3M™ Scott™ X3-21 Pro SCBA

| Part Number | Description             |
|-------------|-------------------------|
| 201809-02   | Cylinder Shroud         |
| 201810-01   | Facepiece Bag, Tactical |



# Self-Contained Breathing Apparatus (SCBA)

## 3M™ Scott™ Air-Pak™ 75i SCBA

Built-to Specification Configurator



| SCBA Model          | Harness                     | Pressure (psig)     | Cylinder ① | Regulator ③                                     | EBSS   | Airline Options ②  | Facepiece ④                    | Console         | Case        | Packaging     |
|---------------------|-----------------------------|---------------------|------------|-------------------------------------------------|--------|--------------------|--------------------------------|-----------------|-------------|---------------|
| 4 Air-Pak™ 75i SCBA | 5 Kevlar®/ Parachute Buckle | 2 2216              | 00 None    | 1 E-Z Flo with Vibralert                        | 0 None | 0 None             | 0 None                         | 1 Gauge         | 0 None      | 1 One Per Box |
|                     |                             | 4 4500              |            | 2 E-Z Flo with Vibralert Quick Disconnect       | 2 Dual | 1 Hansen           | 3 AV-3000 SureSeal Kevlar® (M) | 4 Gauge and HUD | 1 Hard Case |               |
|                     |                             | 5 2216 with RIC/UAC |            | 5 E-Z Flo with Vibralert / HUD                  |        | 2 Schrader         | 6                              |                 | 2 Soft Case |               |
|                     |                             | 7 4500 with RIC/UAC |            | 6 E-Z Flo with Vibralert Quick Disconnect / HUD |        | 4 Hansen HK Plug   | 9                              |                 |             |               |
|                     |                             | 8 5500              |            |                                                 |        | 5 Hansen HK Socket |                                |                 |             |               |
|                     |                             | 9 5500 with RIC/UAC |            |                                                 |        |                    |                                |                 |             |               |

1. Part Number:  
Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| APi | 4 | 5 | X | 00 | X | X | X | X | 1 | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

- ① Order cylinders separately.
- ② Airline options not available when dual EBSS is installed on 3M™ Scott™ Air-Pak™ 75i SCBA.
- ③ When selecting an E-Z Flo with HUD, you must select Gauge and HUD for the Console.
- ④ If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved facepiece as a separate line item (see pages 23-28 for selections).

Example

Air-Pak™ 75i SCBA  
Kevlar®/parachute buckle;  
for 4500 psig cylinder,  
no cylinder, with E-Z Flo  
regulator with Vibralert,  
no EBSS, no airline, no  
facepiece, standard gauge,  
no case, shipped one  
per box.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| APi | 4 | 5 | 4 | 00 | 1 | 0 | 0 | 0 | 1 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order (4500 psig) cylinder, facepiece and case separately.

This configurator is a guide to 3M™ Scott™ Air-Pak™ 75i SCBA part numbers.

# 3M™ Scott™ Industrial SCBA (ISCBA)

Built-to Specification Configurator



| SCBA Model | Harness |   | Pressure (psig)      |   | Cylinder |    | Regulator                  |   | Manifold ①          |   | Airline Options |   | Facepiece ②      |   | Console                                 |   | Case  |   | Packaging |   |             |
|------------|---------|---|----------------------|---|----------|----|----------------------------|---|---------------------|---|-----------------|---|------------------|---|-----------------------------------------|---|-------|---|-----------|---|-------------|
| 1          | ISCBA   | 1 | Nylon/Polymer Buckle | 2 | 2216     | 00 | None                       | 3 | E-Z Flo standard    | 1 | Single          | 0 | None             | 0 | None                                    | 1 | Gauge | 0 | None      | 1 | One Per Box |
|            |         | 4 | Kevlar®/Metal Buckle | 4 | 4500     | 01 | 2216 psi Aluminum, 30 min. | 4 | E-Z Flo Modulair QD | 2 | Dual            | 1 | Hansen           | 3 | AV-3000 SureSeal Facepiece, Kevlar® (M) |   |       | 1 | Hard Case |   |             |
|            |         |   |                      |   |          | 02 | 2216 psi Carbon, 30 min.   |   |                     |   |                 | 2 | Schrader         | 6 | AV-3000 SureSeal Facepiece Poly (M)     |   |       | 2 | Soft Case |   |             |
|            |         |   |                      |   |          | 04 | 4500 psi Carbon, 30 min.   |   |                     |   |                 | 3 | Cejn             | 9 | AV-3000 SureSeal Facepiece Rubber (M)   |   |       |   |           |   |             |
|            |         |   |                      |   |          | 05 | 4500 psi Carbon, 45 min.   |   |                     |   |                 | 4 | Hansen HK Plug   |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | 06 | 4500 psi Carbon, 60 min.   |   |                     |   |                 | 5 | Hansen HK Socket |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          |    | Drained                    |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | AA | 2216 psi Aluminum, 30 min. |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | BB | 2216 psi Carbon, 30 min.   |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | DD | 4500 psi Carbon, 30 min.   |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | EE | 4500 psi Carbon, 45 min.   |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |
|            |         |   |                      |   |          | FF | 4500 psi Carbon, 60 min.   |   |                     |   |                 |   |                  |   |                                         |   |       |   |           |   |             |

1. Part Number:  
Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| IND | 1 | X | X | XX | X | X | X | X | 1 | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

- ① Airline options require a dual manifold.
- ② If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved facepiece as a separate line item (see pages 23-28 for selection).

Example

ISCBA  
Kevlar®/metal buckle;  
for 4500 psig cylinder,  
no cylinder, with E-Z Flo  
regulator, single manifold,  
no airline, no facepiece,  
standard gauge, no case,  
shipped one per box.


|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| IND | 1 | 4 | 4 | 00 | 3 | 1 | 0 | 0 | 1 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order (4500 psig) cylinder, facepiece and case separately.

This configurator is a guide to 3M™ Scott™ ISCBA part numbers.

# Self-Contained Breathing Apparatus (SCBA) □

3M™ Scott™ ISCBA



## Industrial SCBA Parts and Accessories

| Item Number | Description                                        | Pieces Per Pkg  | Part Number |
|-------------|----------------------------------------------------|-----------------|-------------|
| 1           | <b>Facepieces</b>                                  |                 |             |
| 1a          | AV-3000 HT Facepiece                               | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece                         | See Pages 26-28 |             |
| 2           | <b>Regulator</b>                                   |                 |             |
| 2a          | E-Z Flo                                            | 1               | 804441-04   |
| 2b          | E-Z Flo Modulair Quick Disconnect                  | 1               | 804441-05   |
| 3           | <b>Quick Disconnect Low Pressure Hose Assembly</b> | 1               | 804678-01   |
| 4           | <b>Backframe and Harnesses</b>                     |                 |             |
| 4a          | Kevlar® with Metal Buckles                         | 1               | 804621-02   |
| 4b          | Nylon with Plastic Buckles                         | 1               | 804621-03   |
| 5           | <b>Pressure Reducers</b>                           |                 |             |
| 5a          | 2216 psig, Single Port                             | 1               | 804619-01   |
| 5b          | 2216 psig, Dual Port                               | 1               | 804619-02   |
| 5e          | 4500 psig, Single Port                             | 1               | 804642-01   |
| 5f          | 4500 psig, Dual Port                               | 1               | 804642-02   |
| 6           | <b>Cylinder and Valve Assemblies</b>               |                 |             |
| 6a          | Aluminum, 30-Minute, 2216 psig                     | 1               | 804101-01   |
| 6b          | Carbon, 30-Minute, 2216 psig                       | 1               | 804840-01   |
| 6c          | Carbon, 30-Minute, 4500 psig                       | 1               | 804721-01   |
| 6d          | Carbon, 45-Minute, 4500 psig                       | 1               | 804722-01   |
| 6e          | Carbon, 60-Minute, 4500 psig                       | 1               | 804723-01   |
| 7           | <b>Airline Hose and Fittings (not shown)</b>       |                 |             |
| 7a          | Airline Accessory Hose, Hansen Fitting             | 1               | 27537-01    |
| 7b          | Airline Accessory Hose, Schrader Fitting           | 1               | 27537-02    |
| 7c          | Airline Accessory Hose, Hansen HK Fitting          | 1               | 27537-03    |
| 8           | <b>Supply Hoses</b>                                | See Page 61     |             |
| 9           | <b>Communications</b>                              | See Pages 34-35 |             |
| Not shown   | Hard Carrying Case, SCBA                           | 1               | 804497-02   |
| Not shown   | Soft Carrying Case, SCBA                           | 1               | 10009324    |

# Self-Contained Breathing Apparatus (SCBA)

## 3M™ Scott™ ACSi SCBA

Built-to Specification Configurator



| SCBA Model  | Harness         | Pressure (psig) | Cylinder ① |                            | Regulator             | Manifold   | Extended Duration Airline | Facepiece ②                              |         | Console     | Case          | Packaging |
|-------------|-----------------|-----------------|------------|----------------------------|-----------------------|------------|---------------------------|------------------------------------------|---------|-------------|---------------|-----------|
| 3 ACSi SCBA | A ACSi Standard | 2 2216          | 00         | None                       | 3 E-Z Flo Standard    | 0 Standard | 0 None                    | 0 None                                   | 1 Gauge | 0 None      | 1 One Per Box |           |
|             |                 | 4 4500          | 01         | 2216 psi Aluminum, 30 min. | 4 E-Z Flo Modulair QD |            | 1 Hansen                  | 3 AV-3000 SureSeal Facepiece Kevlar® (M) |         | 1 Hard Case |               |           |
|             |                 |                 | 02         | 2216 psi Carbon, 30 min.   |                       |            | 2 Schrader                | 6 AV-3000 SureSeal Facepiece Poly (M)    |         | 2 Soft Case |               |           |
|             |                 |                 | 04         | 4500 psi Carbon, 30 min.   |                       |            | 3 Cejn HK Plug            | 9 AV-3000 SureSeal Facepiece Rubber (M)  |         |             |               |           |
|             |                 |                 | 05         | 4500 psi Carbon, 45 min.   |                       |            | 4 Hansen HK Plug          |                                          |         |             |               |           |
|             |                 |                 | 06         | 4500 psi Carbon, 60 min.   |                       |            | 5 Hansen HK Socket        |                                          |         |             |               |           |
|             |                 |                 | Drained    |                            |                       |            |                           |                                          |         |             |               |           |
|             |                 |                 | AA         | 2216 psi Aluminum, 30 min. |                       |            |                           |                                          |         |             |               |           |
|             |                 |                 | BB         | 2216 psi Carbon, 30 min.   |                       |            |                           |                                          |         |             |               |           |
|             |                 |                 | DD         | 4500 psi Carbon, 30 min.   |                       |            |                           |                                          |         |             |               |           |
|             |                 |                 | EE         | 4500 psi Carbon, 45 min.   |                       |            |                           |                                          |         |             |               |           |
|             |                 |                 | FF         | 4500 psi Carbon, 60 min.   |                       |            |                           |                                          |         |             |               |           |

1. Part Number:  
Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| ACS | 3 | A | X | XX | X | 0 | X | X | 1 | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

- ① When selecting a cylinder with the 3M™ Scott™ ACSi SCBA, the cylinder will ship with a unique 90-degree valve assembly.  
② If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved facepiece as a separate line item (see pages 23-28 for selection).

Example


ACSi SCBA  
Standard harness, for 2216 psig cylinder, no cylinder, with E-Z Flo regulator, standard manifold, no airline, no facepiece, standard gauge, no case, shipped one per box.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| ACS | 3 | A | 2 | 00 | 3 | 0 | 0 | 0 | 1 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order (2216 psig) cylinder, facepiece and case separately.

This configurator is a guide to 3M™ Scott™ ACSi SCBA part numbers.

3M™ Scott™ ACSi SCBA



# Self-Contained Breathing Apparatus (SCBA) ■

## 3M™ Scott™ ACSi SCBA Parts and Accessories

| Item Number | Description                                                            | Pieces Per Pkg  | Part Number |
|-------------|------------------------------------------------------------------------|-----------------|-------------|
| 1           | <b>Facepieces</b>                                                      |                 |             |
| 1a          | AV-3000 HT Facepiece                                                   | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece                                             | See Pages 26-28 |             |
| 2           | <b>Regulator</b>                                                       |                 |             |
| 2a          | E-Z Flo Regulator                                                      | 1               | 804441-06   |
| 2b          | E-Z Flo Modulair Quick Disconnect                                      | 1               | 804441-05   |
| 3           | <b>Quick Disconnect Low Pressure Hose Assembly</b>                     | 1               | 200867-01   |
| 4           | <b>Backframe and Harnesses</b>                                         |                 |             |
| 4a          | ACS (Advanced Carrying System) Standard Backframe/<br>Harness Assembly | 1               | 200877-01   |
| 5           | <b>Pressure Reducers</b>                                               |                 |             |
| 5a          | 2.2 Pressure Reducer Assembly                                          | 1               | 2019231     |
| 5b          | 4.5 Pressure Reducer Assembly                                          | 1               | 2019232     |
| 6           | <b>ACS Cylinder and Valve Assemblies<br/>(with ACS valve)</b>          |                 |             |
| 6a          | Aluminum, 30-Minute, 2216 psig                                         | 1               | 200874-01   |
| 6b          | Carbon, 30-Minute, 2216 psig                                           | 1               | 200873-01   |
| 6c          | Carbon, 30-Minute, 4500 psig                                           | 1               | 200870-01   |
| 6d          | Carbon, 45-Minute, 4500 psig                                           | 1               | 200871-01   |
| 6e          | Carbon, 60-Minute, 4500 psig                                           | 1               | 200872-01   |
| 7           | <b>Extended Duration Airline Assembly (not shown)</b>                  |                 |             |
| 7a          | Airline Accessory Hose, Hansen Fitting                                 | 1               | 200879-01   |
| 7b          | Airline Accessory Hose, Schrader Fitting                               | 1               | 200879-02   |
| 7c          | Airline Accessory Hose, Hansen HK Fitting                              | 1               | 200879-03   |
| 7d          | Airline Accessory Hose, CEJN Fitting                                   | 1               | 200879-05   |
| 8           | <b>Supply Hoses</b>                                                    | See Page 61     |             |

# 3M™ Scott™ SCBA Cylinders

30, 45, 60 and 75 Minute Assemblies

## 2216 psig 30 Minute Cylinder and Valve Assemblies

| Part Number | Aluminum | Carbon | 30-Year | Cylinder Valve |
|-------------|----------|--------|---------|----------------|
| 804101-01   | ●        |        |         | ●              |
| 804840-01   |          | ●      |         | ●              |
| 200131-01*  |          | ●      |         | ●              |
| 10010063**  |          | ●      |         |                |

## 4500 psig, 30 Minute Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 804721-01   | ●      |     |         | ●              |
| 200128-01*  | ●      |     |         | ●              |
| 10009671**  | ●      |     |         |                |
| 804721-11   | ●      | ●   |         | ●              |
| 200128-11*  | ●      | ●   |         | ●              |
| 804721-35   | ●      |     | ●       | ●              |
| 200128-35*  | ●      |     | ●       | ●              |

## 4500 psig, 45 Minute Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 804722-01   | ●      |     |         | ●              |
| 200129-01*  | ●      |     |         | ●              |
| 10009673**  | ●      |     |         |                |
| 804722-11   | ●      | ●   |         | ●              |
| 200129-11*  | ●      | ●   |         | ●              |
| 804722-35   | ●      |     | ●       | ●              |
| 200129-35*  | ●      |     | ●       | ●              |

## 4500 psig, 60 Minute Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 804723-01   | ●      |     |         | ●              |
| 200130-01*  | ●      |     |         | ●              |
| 10009672**  | ●      |     |         |                |
| 804723-11   | ●      | ●   |         | ●              |
| 200130-11*  | ●      | ●   |         | ●              |
| 804723-35   | ●      |     | ●       | ●              |
| 200130-35*  | ●      |     | ●       | ●              |

# Self-Contained Breathing Apparatus (SCBA) ■

## 5500 psig, 30 Minute, Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 200930-01   | ●      |     |         | ●              |
| 200967-01*  | ●      |     |         | ●              |
| 31002299**  | ●      |     |         |                |

## 5500 psig, 45 Minute, Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 200969-01   | ●      |     |         | ●              |
| 200970-01*  | ●      |     |         | ●              |
| 31002300**  | ●      |     |         |                |

## 5500 psig, 60 Minute, Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 200972-01   | ●      |     |         | ●              |
| 200973-01*  | ●      |     |         | ●              |
| 31002301**  | ●      |     |         |                |

## 5500 psig, 75 Minute, Cylinder and Valve Assemblies

| Part Number | Carbon | ST7 | 30-Year | Cylinder Valve |
|-------------|--------|-----|---------|----------------|
| 200975-01   | ●      |     |         | ●              |
| 200976-01*  | ●      |     |         | ●              |
| 31002302**  | ●      |     |         |                |

## ACSi Cylinder and Valve Assemblies

See Page 16

\* Snap-Change Valve Assembly.

\*\* Standard Carbon Cylinder (without valve).

## Accessories for 3M™ Scott™ SCBA Cylinders

| Part Number | Description                                                    |
|-------------|----------------------------------------------------------------|
| 200952-02   | Cylinder Sleeve Kit, 30-min, 4500 psi                          |
| 200952-03   | Cylinder Sleeve Kit, 45-min, 4500 psi                          |
| 200952-04   | Cylinder Sleeve Kit, 60-min, 4500 psi                          |
| 200952-05   | Cylinder Sleeve Kit, 15-min, 4500 psi                          |
| 200952-06   | Cylinder Sleeve Kit, 30-min, 5500 psi                          |
| 200952-07   | Cylinder Sleeve Kit, 45-min, 5500 psi                          |
| 200952-08   | Cylinder Sleeve Kit, 60-min, 5500 psi                          |
| 200952-09   | Cylinder Sleeve Kit, 75-min, 5500 psi                          |
| 200952-10   | Cylinder Sleeve Kit, 30-min, 2216 psi                          |
| 200688-S430 | Cylinder Protective Cap, Valve End, 30-min, 4500 psi           |
| 200688-D430 | Cylinder Protective Cap, Dome End, 30-min, 4500 psi            |
| 200688-S445 | Cylinder Protective Cap, Valve End, 45-min, 4500 psi           |
| 200688-D445 | Cylinder Protective Cap, Dome End, 45-min, 4500 psi            |
| 200689-01*  | Epoxy Pack (Epoxy for 8 caps, Mixing Nozzle, O&M Instructions) |
| 31001465*   | Applicator Gun/Mixer                                           |

\* Required for installation of cylinder protective caps.

## 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator



Designed using a platform approach, the 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator incorporates the latest technology to enhance situational intelligence, while providing a customizable solution. Incorporating a wider field of view to see more and a new regulator design to breathe easier, the 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator delivers the features that matter to help meet the changing needs of today's firefighter.

### 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator with Kevlar® Head Harness

| Part Number      | Description                                           |
|------------------|-------------------------------------------------------|
| FP1SK0000000000  | Small Face Seal                                       |
| FP1MK0000000000  | Medium Face Seal                                      |
| FP1LK0000000000  | Large Face Seal                                       |
| FP1SK0100000000  | Small Face Seal, Neck Strap Accessory                 |
| FP1MK0100000000  | Medium Face Seal, Neck Strap Accessory                |
| FP1LK0100000000  | Large Face Seal, Neck Strap Accessory                 |
| FP1SKK0000000000 | Small Face Seal, Spare Headnet                        |
| FP1MKK0000000000 | Medium Face Seal, Spare Headnet                       |
| FP1LKK0000000000 | Large Face Seal, Spare Headnet                        |
| FP1SKK1000000000 | Small Face Seal, Neck Strap Accessory, Spare Headnet  |
| FP1MKK1000000000 | Medium Face Seal, Neck Strap Accessory, Spare Headnet |
| FP1LKK1000000000 | Large Face Seal, Neck Strap Accessory, Spare Headnet  |


### Accessories for 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator

| Part Number  | Description                      |
|--------------|----------------------------------|
| 201520-01    | Fit Test Adapter                 |
| 201682-01    | Neck Strap Accessory             |
| 200372-52FC5 | Spectacle Kit, 52 mm, Frame only |
| 200372-60FC5 | Spectacle Kit, 60 mm, Frame only |
| 805534-01    | Fleece Bag                       |
| 31004024     | Laundry Bag                      |

### 3M™ Scott™ E-Z Flo C5 Regulator

| Part Number | Description                                |
|-------------|--------------------------------------------|
| 201650-01   | Quick Disconnect Hose, Hansen-type Fitting |
| 201650-02   | Continuous Hose, X3/X3 Pro CGA, 3-Wire     |
| 201650-03   | Continuous Hose, X3/X3 Pro SC, 3-Wire      |
| 201650-04   | Continuous Hose, AP/WF                     |
| 201650-05   | Quick Disconnect Hose, Rectus-type Fitting |
| 201650-06   | Continuous Hose, X3/X3 Pro CGA, 6-Wire     |
| 201650-07   | Continuous Hose, X3/X3 Pro SC, 6-Wire      |

# 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator



## 3M™ Scott™ Vision C5 Facepiece with E-Z Flo C5 Regulator Parts and Accessories

| Item Number | Description                                                               | Pieces Per Pkg | Part Number |
|-------------|---------------------------------------------------------------------------|----------------|-------------|
| 1           | <b><i>Nosecup Assembly</i></b>                                            |                |             |
| 1a          | Nosecup Assembly, Small                                                   | 1              | 201484-01   |
| 1b          | Nosecup Assembly, Medium                                                  | 1              | 201486-01   |
| 1c          | Nosecup Assembly, Large                                                   | 1              | 201488-01   |
| 2           | <b><i>Inhalation Valve</i></b>                                            | 2              | 31002788    |
| 3           | <b><i>Temple Tab, Left</i></b>                                            | 1              | 201491-01   |
| 4           | <b><i>Temple Tab, Right</i></b>                                           | 1              | 201500-01   |
| 5           | <b><i>Sizing Stud</i></b>                                                 |                |             |
| 5a          | Large, Red                                                                | 2              | 31003601    |
| 5b          | Medium, Black                                                             | 2              | 31003602    |
| 5c          | Small, Green                                                              | 2              | 31003603    |
| 6           | <b><i>Headnet Buckle</i></b>                                              | 2              | 201502-02   |
| 7           | <b><i>Headnet Buckle with D-ring</i></b>                                  | 2              | 201502-01   |
| 8           | <b><i>Headnet Assembly (Includes Headnet, Temple and Neck Straps)</i></b> |                |             |
| 8a          | Headnet Assembly, Small                                                   | 1              | 201496-03   |
| 8b          | Headnet Assembly, Medium                                                  | 1              | 201496-02   |
| 8c          | Headnet Assembly, Large                                                   | 1              | 201496-01   |
| 9           | <b><i>Temple Strap</i></b>                                                | 1              | 804178-05   |
| 10          | <b><i>Neck Strap</i></b>                                                  | 1              | 804178-03   |
| 11          | <b><i>Accessory Neck Strap</i></b>                                        | 1              | 201682-01   |
| Not shown   | Fleece Facepiece Bag                                                      | 1              | 805534-01   |

# 3M™ Scott™ AV-3000 HT Facepiece



The 3M™ Scott™ AV-3000 HT Facepiece is fully interchangeable with the full line of 3M Scott SCBA, air-supplied respirators, and air purifying respirators, as well as 3M Scott communications products providing "Top-Down Convertibility" options. It is designed to minimize equipment inventories, simplify the complexities of user training when issued as a single personal issue facepiece and reduce redundant facepiece fit tests.

## 3M™ Scott™ AV-3000 HT Facepiece with Kevlar® Head Harness, 5-Strap

| Part Number | Description                                                                                                             |
|-------------|-------------------------------------------------------------------------------------------------------------------------|
| 201215-01   | Small Faceseal                         |
| 201215-02   | Medium Faceseal                       |
| 201215-03   | Large Faceseal                       |
| 201215-04   | Small Faceseal, Right Comm Bracket   |
| 201215-05   | Medium Faceseal, Right Comm Bracket  |
| 201215-06   | Large Faceseal, Right Comm Bracket   |
| 201215-07   | Small Faceseal, Left Comm Bracket    |
| 201215-08   | Medium Faceseal, Left Comm Bracket   |
| 201215-09   | Large Faceseal, Left Comm Bracket    |

## 3M™ Scott™ AV-3000 HT Facepiece with Kevlar® Head Harness, 4-Strap

| Part Number | Description                                                                                                             |
|-------------|-------------------------------------------------------------------------------------------------------------------------|
| 201215-21   | Small Faceseal                       |
| 201215-22   | Medium Faceseal                      |
| 201215-23   | Large Faceseal                       |
| 201215-27   | Small Faceseal, Right Comm Bracket   |
| 201215-28   | Medium Faceseal, Right Comm Bracket  |
| 201215-29   | Large Faceseal, Right Comm Bracket   |
| 201215-34   | Small Faceseal, Left Comm Bracket    |
| 201215-35   | Medium Faceseal, Left Comm Bracket   |
| 201215-36   | Large Faceseal, Left Comm Bracket    |



3M™ Scott™ AV-3000 HT Facepiece with Kevlar® Head Harness is NIOSH CBRN APR approved with 3M™ Scott™ 40 mm First Responder Adapter and 3M™ Scott™ CBRN Cap-1 Canister.


## 3M™ Scott™ AV-3000 HT Facepiece Parts and Accessories

| Item Number | Description                                                                  | Pieces Per Pkg | Part Number |
|-------------|------------------------------------------------------------------------------|----------------|-------------|
| 1           | <b>Complete Head Harness Assemblies</b>                                      |                |             |
| 1a          | Kevlar® Head Harness, 5-Strap*                                               | 1              | 200803-01   |
| 1b          | Kevlar® Head Harness, 4-Strap, Small                                         | 1              | 201467-01   |
| 1c          | Kevlar® Head Harness, 4-Strap, Medium/Large                                  | 1              | 201467-02   |
| 2           | <b>Temple Straps</b>                                                         |                |             |
| 2a          | Kevlar® Temple Strap**                                                       | 1              | 804178-03   |
| 3           | <b>Neck Straps</b>                                                           |                |             |
| 3a          | Kevlar® Neck Strap                                                           | 1              | 804176-03   |
| 4           | <b>Facepiece Lens (Fenestra, Drilled) (AV-3000 HT Facepiece only)</b>        | 1              | 201134-01   |
| 5           | <b>Upper Bezel (AV-3000 HT Facepiece only)</b>                               | 1              | 31002809    |
| 6           | <b>Lower Bezel (AV-3000 HT Facepiece only)</b>                               | 1              | 31002810    |
| 7           | <b>Bezel Screw</b>                                                           | 2              | 33361-020   |
| 8           | <b>Facepiece Seals (AV-3000 SureSeal Facepiece and AV-3000 HT Facepiece)</b> |                |             |
| 8a          | AV-3000 SureSeal Facepiece, FaceSeal, Small                                  | 1              | 200802-01   |
| 8b          | AV-3000 SureSeal Facepiece, FaceSeal, Medium                                 | 1              | 200802-02   |
| 8c          | AV-3000 SureSeal Facepiece, FaceSeal, Large                                  | 1              | 200802-03   |
| 8d          | AV-3000 SureSeal Facepiece, FaceSeal, 4-Strap, Small                         | 1              | 200802-04   |
| 8e          | AV-3000 SureSeal Facepiece, FaceSeal, 4-Strap, Medium                        | 1              | 200802-05   |
| 8f          | AV-3000 SureSeal Facepiece, FaceSeal, 4-Strap, Large                         | 1              | 200802-06   |
| 9           | <b>Left Voicemitter Duct Kit (AV-3000 HT Facepiece only)</b>                 | 1              | 201311-02   |
| 10          | <b>Right Voicemitter Duct Kit (AV-3000 HT Facepiece only)</b>                | 1              | 201311-01   |
| 11          | <b>Nosecups (AV-3000 HT Facepiece ONLY)</b>                                  |                |             |
| 11a         | Nosecup with Red Valves, Small                                               | 1              | 201126-02   |
| 11b         | Nosecup with Red Valves, Medium                                              | 1              | 201127-02   |
| 11c         | Nosecup with Red Valves, Large                                               | 1              | 201128-02   |
| 12          | <b>Inhalation Valve, Red (AV-3000 HT Facepiece only)</b>                     | 2              | 31002788    |
| 13          | <b>Comm Bracket Kit, Right (AV-3000 HT Facepiece only)</b>                   | 1              | 201210-01   |
| 14          | <b>Comm Bracket Kit, Left (AV-3000 HT Facepiece only)</b>                    | 1              | 201210-02   |
| Not shown   | <b>Fleece Facepiece Bag</b>                                                  | 1              | 805534-01   |
| Not shown   | <b>Neck Strap Accessory</b>                                                  | 1              | 804088-02   |

\* Includes the temple strap sewn into the headnet.

\*\* Replacement of the temple strap on 3M™ Scott™ AV-3000 HT Facepiece, 5-Strap products produced after August 2015 will require replacement of headnet assembly (P/N 200803-01).

# 3M™ Scott™ AV-3000 HT Facepiece



3M™ Scott™ AV-3000  
SureSeal Facepiece



It is designed to minimize equipment inventories, simplify the complexities of user training when issued as a single personal issue facepiece and reduce redundant facepiece fit tests.

3M™ Scott™ AV-3000 SureSeal Facepiece with Kevlar® Head Harness

| Part Number | Description                                                                                                       | Pieces Per Pkg |
|-------------|-------------------------------------------------------------------------------------------------------------------|----------------|
| 805773-81   | Small Faceseal                   | 1              |
| 805773-82   | Medium Faceseal                  | 1              |
| 805773-83   | Large Faceseal                 | 1              |
| 805773-84   | Small Faceseal, Comm Bracket   | 1              |
| 805773-85   | Medium Faceseal, Comm Bracket  | 1              |
| 805773-86   | Large Faceseal, Comm Bracket   | 1              |



3M™ Scott™ AV-3000 SureSeal Facepiece with Kevlar® Head Harness is NIOSH CBRN APR approved with 3M™ Scott™ 40 mm First Responder Adapter and 3M™ Scott™ CBRN Cap-1 Canister, and with the 3M™ Scott™ C420 CBRN Powered Air Purifying Respirator (PAPR) as configured on page 59.

3M™ Scott™ AV-3000 SureSeal Facepiece with Polyester Head Harness

| Part Number | Description     | Pieces Per Pkg |
|-------------|-----------------|----------------|
| 805774-81   | Small Faceseal  | 1              |
| 805774-82   | Medium Faceseal | 1              |
| 805774-83   | Large Faceseal  | 1              |

3M™ Scott™ AV-3000 SureSeal Facepiece with Rubber Head Harness

| Part Number | Description                                                                                         | Pieces Per Pkg |
|-------------|-----------------------------------------------------------------------------------------------------|----------------|
| 805775-81   | Small Faceseal   | 1              |
| 805775-82   | Medium Faceseal  | 1              |
| 805775-83   | Large Faceseal   | 1              |



3M™ Scott™ AV-3000 SureSeal Facepiece with Rubber Head Harness is NIOSH CBRN APR approved with 3M™ Scott™ 40 mm First Responder Adapter (200423-01) and 3M™ Scott™ CBRN Cap-1 Canister (045135).

### 3M™ Scott™ AV-3000 SureSeal Facepiece Parts and Accessories

| Item Number | Description                                                            | Pieces Per Pkg | Part Number |
|-------------|------------------------------------------------------------------------|----------------|-------------|
| 1           | <b>Complete Head Harness Assemblies</b>                                |                |             |
| 1a          | Kevlar® Head Harness (AV-3000 SureSeal Facepiece)*                     | 1              | 200803-01   |
| 1d          | Polyester Head Harness (AV-3000 SureSeal Facepiece)*                   | 1              | 200965-01   |
| 1g          | Rubber Head Harness (AV-3000 SureSeal Facepiece)                       | 1              | 10008522    |
| 2           | <b>Temple Straps (AV-3000 SureSeal Facepiece)</b>                      |                |             |
| 2a          | Kevlar® Temple Strap**                                                 | 1              | 804178-03   |
| 2b          | Polyester Temple Strap**                                               | 1              | 804061-01   |
| 3           | <b>Neck Straps (AV-3000 SureSeal Facepiece)</b>                        |                |             |
| 3a          | Kevlar® Neck Strap                                                     | 1              | 804176-03   |
| 3b          | Polyester Neck Strap                                                   | 1              | 803920-02   |
| 5           | <b>Facepiece Lens (Fenestra, Drilled) (AV-3000 SureSeal Facepiece)</b> | 1              | 805345-01   |
| 6           | <b>Upper Bezel</b>                                                     | 1              | 10011024    |
| 7           | <b>Lower Bezel</b>                                                     | 1              | 10011025    |
| 8           | <b>Bezel Screw</b>                                                     | 1              | 33335-022   |
| 9           | <b>Facepiece Seals</b>                                                 |                |             |
| 9a          | AV-3000 SureSeal Facepiece, FaceSeal, Small                            | 1              | 200802-01   |
| 9b          | AV-3000 SureSeal Facepiece, FaceSeal, Medium                           | 1              | 200802-02   |
| 9c          | AV-3000 SureSeal Facepiece, FaceSeal, Large                            | 1              | 200802-03   |
| 10          | <b>Voicemitter</b>                                                     | 1              | 803759-01   |
| 11          | <b>Left Voicemitter Dust Assembly</b>                                  | 1              | 805339-01   |
| 12          | <b>Right Voicemitter Duct Assembly</b>                                 | 1              | 805339-02   |
| 13          | <b>Nosecups (AV-3000 SureSeal Facepiece)</b>                           |                |             |
| 13a         | Nosecup Grey Small                                                     | 1              | 31001043    |
| 13b         | Nosecup Grey Medium                                                    | 1              | 31001044    |
| 13c         | Nosecup Grey Large                                                     | 1              | 31001045    |
| Not shown   | Fleece Facepiece Bag                                                   | 1              | 805534-01   |
| Not shown   | EPIC Communications Clamp, Right Side Only                             | 1              | 200715-01   |
| Not shown   | Neck Strap Accessory                                                   | 1              | 804088-02   |


\* Includes the temple strap sewn into the headnet.

\*\* Replacement of the temple strap on 3M™ Scott™ AV-3000 SureSeal Facepiece assemblies produced after August 2015 will require replacement of headnet assembly (Kevlar® P/N 200803-01 or Polyester PN 200965-01).

### Lens Kit Accessories for 3M™ Scott™ AV-3000 Series Facepieces

| Part Number | Description                   |
|-------------|-------------------------------|
| 805753-01   | Standard Eyeglass Kit         |
| 200372-52F  | 52 mm Wire Frame Eyeglass Kit |
| 200372-60F  | 60 mm Wire Frame Eyeglass Kit |

3M™ Scott™ AV-3000 SureSeal Facepiece



# 3M™ Scott™ Weld-O-Vista Facepiece



Fully interchangeable with the full line of 3M Scott SCBA, air-supplied respirators, and air-purifying respirators, the 3M™ Scott™ Weld-O-Vista facepiece also works with the 3M Scott communications products providing “Top-Down Convertibility” options. It is designed to minimize equipment inventories, simplify the complexities of user training when issued as a single personal issue facepiece and reduce redundant facepiece fit tests.

## 3M™ Scott™ Weld-O-Vista Facepiece with Kevlar® Head Harness

| Part Number | Description           | Pieces Per Pkg |
|-------------|-----------------------|----------------|
| 805438-01   | Small Faceseal        | 1              |
| 805438-02   | Large Faceseal        | 1              |
| 805438-03   | X-Large Faceseal      | 1              |
| 805438-08   | Comfort Seal Faceseal | 1              |


## Lens Kit Accessories for 3M™ Scott™ Weld-O-Vista Facepiece

| Part Number | Description                   |
|-------------|-------------------------------|
| 804442-01   | Standard Eyeglass Kit         |
| 200371-52F  | 52 mm Wire Frame Eyeglass Kit |
| 200371-60F  | 60 mm Wire Frame Eyeglass Kit |

## 3M™ Scott™ Weld-O-Vista Facepiece Parts and Accessories

| Item Number | Description                                                                   | Pieces Per Pkg | Part Number |
|-------------|-------------------------------------------------------------------------------|----------------|-------------|
| 1           | <b>Head Harnesses</b>                                                         |                |             |
| 1a          | Kevlar® Head Harness Assembly                                                 | 1              | 804177-01   |
| 2           | <b>Temple Straps</b>                                                          |                |             |
| 2a          | Kevlar® Temple Strap                                                          | 1              | 804178-01   |
| 3           | <b>Neck Straps</b>                                                            |                |             |
| 3a          | Kevlar® Neck Strap                                                            | 1              | 804176-01   |
| 4           | <b>Lower Buckle Strap</b>                                                     | 1              | 803732-01   |
| 5           | <b>Lens Frame</b>                                                             | 1              | 10008068    |
| 6           | <b>Facepiece Seals</b>                                                        |                |             |
| 6a          | Faceseal, Small (Green)                                                       | 1              | 10005913    |
| 6b          | Faceseal, Large (Black)                                                       | 1              | 10005135    |
| 6c          | Faceseal, X-Large (Red)                                                       | 1              | 10006212    |
| 6d          | Faceseal, Comfort Seal (Black)                                                | 1              | 10009779    |
| 7           | <b>Nosecup Retaining Ring</b>                                                 | 1              | 10008398    |
| 8           | <b>Nosecup Assembly (Nosecup with Inhalation Valves)</b>                      | 1              | 804014-01   |
| 10          | <b>Lens Assemblies</b>                                                        |                |             |
| 10a         | Weld-O-Vista Facepiece Assembly (Lens with Voicemitter, Lens Holder, Nosecup) | 1              | 805574-01   |
| 10b         | Weld-O-Vista Facepiece Lens Assembly Kit (Lens and Lens Holder)               | 1              | 805537-01   |
| 11          | <b>Voicemitter Duct</b>                                                       | 1              | 10008400    |
| 12          | <b>Voicemitter</b>                                                            | 1              | 804010-01   |
| 13          | <b>Lens Holder Assembly</b>                                                   | 1              | 805182-02   |
| 14          | <b>Lens Separator and Lens Retainer Kit</b>                                   | 1              | 805536-01   |
| Not shown   | Fleece Facepiece Bag                                                          | 1              | 805534-01   |

# 3M™ Scott™ Weld-O-Vista Facepiece



## 3M™ Scott™ Vision C5 Facepiece with Radio Direct Interface



### 3M™ Scott™ Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone (Motorola Compatible)

| Part Number     | Description                                                                                                                                                     |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| FP1SK0002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, Motorola®, English                                       |
| FP1MK0002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, Motorola®, English                                      |
| FP1LK0002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, Motorola®, English                                       |
| FP1SK0102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory                 |
| FP1MK0102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory                |
| FP1LK0102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory                 |
| FP1SKK002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, Motorola®, English, Spare Headnet                        |
| FP1MKK002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, Motorola®, English, Spare Headnet                       |
| FP1LKK002M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, Motorola®, English, Spare Headnet                        |
| FP1SKK102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory, Spare Headnet  |
| FP1MKK102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory, Spare Headnet |
| FP1LKK102M10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, Motorola®, English, Neck Strap Accessory, Spare Headnet  |

\*See Configurator for more options.

### 3M™ Scott™ Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone (L3Harris Compatible)

| Part Number     | Description                                                                                                                                                     |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| FP1SK0002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, L3Harris®, English                                       |
| FP1MK0002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, L3Harris®, English                                      |
| FP1LK0002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, L3Harris®, English                                       |
| FP1SK0102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory                 |
| FP1MK0102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory                |
| FP1LK0102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory                 |
| FP1SKK002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, L3Harris®, English, Spare Headnet                        |
| FP1MKK002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, L3Harris®, English, Spare Headnet                       |
| FP1LKK002H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, L3Harris®, English, Spare Headnet                        |
| FP1SKK102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Small, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory, Spare Headnet  |
| FP1MKK102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Medium, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory, Spare Headnet |
| FP1LKK102H10010 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone, Large, Kevlar® Headnet, L3Harris®, English, Neck Strap Accessory, Spare Headnet  |

### 3M™ Scott™ Vision C5 Charger

| Part Number | Description                                                                 |
|-------------|-----------------------------------------------------------------------------|
| CF5V20S0    | Vision C5 Charger (qty 1), Low-Power Supply (AC)                            |
| CF5V2SS0    | Vision C5 Charger (qty 1), Single Mounting Bracket, Low-Power Supply (AC)   |
| CF5V2SHO    | Vision C5 Charger (qty 1), Single Mounting Bracket, Hard-Wired Power Supply |
| CF5V2DDB    | Vision C5 Charger (qty 2), Double Mounting Bracket, High-Power Supply (AC)  |
| CF5V2DH0    | Vision C5 Charger (qty 2), Double Mounting Bracket, Hard-Wired Power Supply |
| CF5V2TDB    | Vision C5 Charger (qty 3), Triple Mounting Bracket, High-Power Supply (AC)  |
| CF5V2TH0    | Vision C5 Charger (qty 3), Triple Mounting Bracket, Hard-Wired Power Supply |

\*See Configurator for more options.

### Accessories for 3M™ Scott™ Vision C5 Facepiece

| Part Number | Description                              |
|-------------|------------------------------------------|
| 201506-01   | Lithium-ion Battery, Vision C5 Facepiece |

### 3M™ Scott™ Vision C5 Facepiece with Radio Direct Interface Install Kit

| Part Number    | Description                                                                               |
|----------------|-------------------------------------------------------------------------------------------|
| 70-0020-0994-5 | Vision C5 Facepiece with Radio Direct Interface Install Kit                               |
| 70-0020-0995-2 | Vision C5 Facepiece with Radio Direct Interface and Bone Conduction Headphone Install Kit |

## 3M™ Scott™ EPIC 3 Voice Communications



### 3M™ Scott™ EPIC 3 RDI Voice Communications

| Part Number | Description                                                                                      |
|-------------|--------------------------------------------------------------------------------------------------|
| 201276-11   | EPIC 3 Radio Direct Interface Voice Amplifier, Motorola APX radios, *Open Bracket Configuration  |
| 201276-12   | EPIC 3 Radio Direct Interface Voice Amplifier, Motorola APX radios, Closed Bracket Configuration |
| 201276-21   | EPIC 3 Radio Direct Interface Voice Amplifier, L3Harris XL radios, *Open Bracket Configuration   |
| 201276-22   | EPIC 3 Radio Direct Interface Voice Amplifier, L3Harris XL radios, Closed Bracket Configuration  |

### 3M™ Scott™ EPIC 3 RI Voice Communication System

| Part Number | Description                                                          |
|-------------|----------------------------------------------------------------------|
| 201276-01   | EPIC 3 Radio Interface Voice Amplifier, *Open Bracket Configuration  |
| 201276-02   | EPIC 3 Radio Interface Voice Amplifier, Closed Bracket Configuration |

### 3M™ Scott™ EPIC 3 Voice Amplifier

| Part Number | Description                                          |
|-------------|------------------------------------------------------|
| 201275-01   | EPIC 3 Voice Amplifier, *Open Bracket Configuration  |
| 201275-02   | EPIC 3 Voice Amplifier, Closed Bracket Configuration |

### 3M™ Scott™ EPIC 3 Bluetooth Lapel Speaker Microphone

| Part Number | Description                                                                                                          |
|-------------|----------------------------------------------------------------------------------------------------------------------|
| 201277-02   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with Motorola HT1000, XTS series radios                           |
| 201277-04   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with Motorola HT750/1250/1550 series radios                       |
| 201277-06   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with Motorola Mototrbo XPR Series, APX series radios              |
| 201277-07   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with Kenwood TK280/290/380/390 series radios                      |
| 201277-11   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with Motorola Radius GP300 series radios                          |
| 201277-22   | EPIC 3 Bluetooth Lapel Speaker Microphone, for use with L3Harris P5400/7300, Unity Series and XG 25/75 series radios |

\*Open bracket configuration required when used with 3M™ Scott™ Air-Pak™ SCBA compliant to NFPA 1981, 2013 Edition and NFPA 1981, 2018 Edition standards.

**3M™ Scott™ EPIC 3 Lapel Speaker Microphone**

| Part Number | Description                                                                                          |
|-------------|------------------------------------------------------------------------------------------------------|
| 201224-02   | EPIC 3 Lapel Speaker Microphone, for use with Motorola HT1000, XTS series radios                     |
| 201224-04   | EPIC 3 Speaker Microphone, for use with Motorola HT750/1250/1550 series radios                       |
| 201224-06   | EPIC 3 Lapel Speaker Microphone, for use with Motorola Mototrbo XPR Series, APX series radios        |
| 201224-07   | EPIC 3 Lapel Speaker Microphone, for use with Kenwood TK280/290/380/390 series radios                |
| 201224-22   | EPIC 3 Speaker Microphone, for use with L3Harris P5400/7300, Unity Series and XG 25/75 series radios |

**3M™ Scott™ Radio Interface PTT Paddle Accessory**

| Part Number | Description                                                                                     |
|-------------|-------------------------------------------------------------------------------------------------|
| 201675-02   | Radio Interface PTT Paddle, for use with Motorola HT1000, XTS series radios                     |
| 201675-04   | Radio Interface PTT Paddle, for use with Motorola HT750/1250/1550 series radios                 |
| 201675-06   | Radio Interface PTT Paddle, for use with Motorola APX/XPR/DP/DGP/MTP series radios              |
| 201675-07   | Radio Interface PTT Paddle, for use with JVCKenwood multi-pin connector TK and NX series radios |
| 201675-11   | Radio Interface PTT Paddle, for use with Motorola Radius GP300 series radios                    |
| 201675-21   | Radio Interface PTT Paddle, for use with L3Harris XL-200, Unity XG-100 radios                   |
| 201675-22   | Radio Interface PTT Paddle, for use with L3Harris P5400/7300, XG 25/75 radios                   |
| 201675-28   | Radio Interface PTT Paddle, for use with JVCKenwood two-pin connector TK and NX series radios   |

**Accessories for 3M™ Scott™ EPIC 3 Voice Communication System**

| Part Number | Description                                                                |
|-------------|----------------------------------------------------------------------------|
| 201226-01   | 3M™ Scott™ EPIC 3 Voice Communication System PTT Ring                      |
| 201227-01   | 3M™ Scott™ EPIC 3 Voice Communication System PTT Paddle                    |
| 201228-01   | 3M™ Scott™ EPIC 3 Voice Communication System Throat Mic                    |
| 201229-01   | 3M™ Scott™ EPIC 3 Voice Communication System Command Communication Headset |

**Facepiece Brackets for 3M™ Scott™ EPIC 3 Voice Communication System**

| Part Number | Description                                                                                                                  |
|-------------|------------------------------------------------------------------------------------------------------------------------------|
| 201210-01   | 3M™ Scott™ AV-3000 HT Facepiece Open Bracket, Right (for use with 3M™ Scott™ EPIC 3 Voice Communication System only)         |
| 201210-02   | 3M™ Scott™ AV-3000 HT Facepiece Open Bracket, Left (for use with 3M™ Scott™ EPIC 3 Voice Communication System only)          |
| *200715-01  | 3M™ Scott™ AV-3000 Series Facepiece Closed Bracket, Right (for use with all 3M™ Scott™ EPIC 3 Voice Communications products) |

\*Compatible with 3M™ Scott™ AV-3000 HT Facepiece and 3M™ Scott™ AV-3000 SureSeal Facepiece.

## 3M™ Scott™ Monitor/Monitor Pro Telemetry Software Solution



The 3M™ Scott™ Monitor Telemetry Software Solution puts critical, real-time responder information at incident command's fingertips. Designed for use on modern, touch-enabled PCs, Monitor is an intuitive and powerful air management/telemetry solution meant to complement existing accountability practices. Monitor works with all SEMS-equipped 3M™ Scott™ Air-Pak™ SCBA, though some features are only available when used with the 3M™ Scott™ Air-Pak™ X3 Pro SCBA.

### Core Components

| Part Number | Description                           |
|-------------|---------------------------------------|
| 8005197     | Monitor Software Base Command Install |
| *8006951    | Monitor Software Pro Edition Add-on   |
| 201088-03   | SEMS II USB Gateway                   |
| 201051-01   | SEMS II Repeater                      |

\*Required for compatibility with SEMS II Pro. Must be purchased in addition to Monitor Software Base Command Install, part number 8005197.

### Accessories / Hardware

| Part Number | Description                |
|-------------|----------------------------|
| 200773-01   | RFID Reader/Writer         |
| 200774-01   | RFID cards, 10 pack        |
| 201279-01   | Tally Tag, Red, 10 pack    |
| 201279-02   | Tally Tag, White, 10 pack  |
| 201279-03   | Tally Tag, Black, 10 pack  |
| 201279-04   | Tally Tag, Yellow, 10 pack |
| 201279-05   | Tally Tag, Orange, 10 pack |
| 201280-01   | Button Tag, 10 pack        |

## 3M™ Safety & Inspection Manager for Emergency Services



3M™ Safety & Inspection Manager Software for Emergency Services (SIM-ES) empowers command staff to take a proactive approach to managing records and documentation of training, qualification, service, maintenance and inspections, as well as cleaning and decontamination of PPE and other equipment. 3M™ Safety & Inspection Manager for Emergency Services also enables fire departments to track exposure reduction programs and activities. Alerts and notifications of impending and overdue activities keep your agency on track and support adherence of regulatory requirements.

Part of 3M™ Connected Safety, SIM is a platform that connects people, information and systems to help you improve productivity, increase situational awareness, and run an efficient health and safety program.

### 3M™ Safety & Inspection Manager for Emergency Services Packages

| Part Number | Description                                                                                        |
|-------------|----------------------------------------------------------------------------------------------------|
| 6100003148  | 3M™ Safety & Inspection Manager for Emergency Services Bronze Package (1-25 Personnel) – One Year  |
| 6100003149  | 3M™ Safety & Inspection Manager for Emergency Services Silver Package (26-50 Personnel) – One Year |
| 6100003150  | 3M™ Safety & Inspection Manager for Emergency Services Gold Package (51-75 Personnel) – One Year   |
| 6100003151  | 3M™ Safety & Inspection Manager for Emergency Services Custom (>75 Personnel) – One Year           |

### 3M™ Safety & Inspection Manager for Emergency Services Training and Services

| Part Number | Description                                                                            |
|-------------|----------------------------------------------------------------------------------------|
| 6010002882  | On-site training for 3M™ Safety & Inspection Manager for Emergency Services – Full Day |
| 6100001903  | Remote training for 3M™ Safety & Inspection Manager for Emergency Services – Per Hour  |

**Note:** 3M™ Safety & Inspection Manager for Emergency Services is an exciting collaboration between 3M Connect Safety and 3M Scott Fire & Safety that leverages the proven Safety and Inspection Manager solution and optimizes the offering for the fire service. Due to the unique nature of this offering, 3M™ Safety & Inspection Manager for Emergency Services is a direct sale only product through 3M Scott Fire & Safety.

To register for a product demonstration or claim a 90-day free trial, customers may contact 3M Scott Customer Service at 1-800-247-7257 or visit [3M.com/SIM-ES](http://3M.com/SIM-ES)

## 3M™ Scott™ V320 Thermal Imager



### 3M™ Scott™ V320 Thermal Imager

| Part Number | Temp | Description                                                                                                                                                    |
|-------------|------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 8007134     | F    | V320 Thermal Imager (Fahrenheit) – Kit includes two batteries, retractable lanyard, desktop charger and truck holder kit in a carton. Three years of warranty. |
| 8007135     | C    | V320 Thermal Imager (Celsius) – Kit includes two batteries, retractable lanyard, desktop charger and truck holder kit in a carton. Three years of warranty.    |

### Accessories for 3M™ Scott™ V320 Thermal Imager

| Part Number    | Description                   |
|----------------|-------------------------------|
| 8007136        | V-Series Retractable Lanyard  |
| 8007137        | V-Series Battery Charger      |
| 8007138        | V-Series Charger Power Supply |
| 8007139        | V-Series Standard Battery     |
| 78-8151-2502-2 | Truck Mount Holder            |

## 3M™ Scott™ Sight In-Mask Thermal Imager

For use with 3M™ Scott™ AV-3000 HT Facepiece.



### 3M™ Scott™ Sight In-Mask Thermal Imager

| Part Number | Description                                                     |
|-------------|-----------------------------------------------------------------|
| 201581-01   | Sight In-Mask Thermal Imager Full Kit – Small 5 Strap           |
| 201581-02   | Sight In-Mask Thermal Imager Full Kit w/comms* – Small 5 Strap  |
| 201581-11   | Sight In-Mask Thermal Imager Full Kit – Small 4 Strap           |
| 201581-12   | Sight In-Mask Thermal Imager Full Kit w/comms* – Small 4 Strap  |
| 201582-01   | Sight In-Mask Thermal Imager Full Kit – Medium 5 Strap          |
| 201582-02   | Sight In-Mask Thermal Imager Full Kit w/comms* – Medium 5 Strap |
| 201582-11   | Sight In-Mask Thermal Imager Full Kit – Medium 4 Strap          |
| 201582-12   | Sight In-Mask Thermal Imager Full Kit w/comms* – Medium 4 Strap |
| 201583-01   | Sight In-Mask Thermal Imager Full Kit – Large 5 Strap           |
| 201583-02   | Sight In-Mask Thermal Imager Full Kit w/comms* – Large 5 Strap  |
| 201583-11   | Sight In-Mask Thermal Imager Full Kit – Large 4 Strap           |
| 201583-12   | Sight In-Mask Thermal Imager Full Kit w/comms* – Large 4 Strap  |
| 201584-01   | Sight In-Mask Thermal Imager Install Kit – Small                |
| 201584-02   | Sight In-Mask Thermal Imager Install Kit w/comms* – Small       |
| 201585-01   | Sight In-Mask Thermal Imager Install Kit – Medium               |
| 201585-02   | Sight In-Mask Thermal Imager Install Kit w/comms* – Medium      |
| 201586-01   | Sight In-Mask Thermal Imager Install Kit – Large                |
| 201586-02   | Sight In-Mask Thermal Imager Install Kit w/comms* – Large       |

\* Includes left-sided communications mounting bracket.

## 3M™ Scott™ Sight In-Mask Thermal Imager with Pro Package

For use with 3M™ Scott™ AV-3000 HT Facepiece.



### 3M™ Scott™ Sight In-Mask Thermal Imager with Pro Package

| Part Number | Description                                                                      |
|-------------|----------------------------------------------------------------------------------|
| 201581-01P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Small 5 Strap           |
| 201581-02P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Small 5 Strap  |
| 201581-11P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Small 4 Strap           |
| 201581-12P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Small 4 Strap  |
| 201582-01P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Medium 5 Strap          |
| 201582-02P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Medium 5 Strap |
| 201582-11P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Medium 4 Strap          |
| 201582-12P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Medium 4 Strap |
| 201583-01P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Large 5 Strap           |
| 201583-02P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Large 5 Strap  |
| 201583-11P  | Sight In-Mask Thermal Imager with Pro Package Full Kit – Large 4 Strap           |
| 201583-12P  | Sight In-Mask Thermal Imager with Pro Package Full Kit w/comms* – Large 4 Strap  |
| 201584-01P  | Sight In-Mask Thermal Imager with Pro Package Install Kit – Small                |
| 201584-02P  | Sight In-Mask Thermal Imager with Pro Package Install Kit w/comms* – Small       |
| 201585-01P  | Sight In-Mask Thermal Imager with Pro Package Install Kit – Medium               |
| 201585-02P  | Sight In-Mask Thermal Imager with Pro Package Install Kit w/comms* – Medium      |
| 201586-01P  | Sight In-Mask Thermal Imager with Pro Package Install Kit – Large                |
| 201586-02P  | Sight In-Mask Thermal Imager with Pro Package Install Kit w/comms* – Large       |

\* Includes left-sided communications mounting bracket.

### 3M™ Scott™ Universal Bluetooth® Programmer

| Part Number | Description                     |
|-------------|---------------------------------|
| **201243-02 | Universal Bluetooth® Programmer |

\*\*For use in downloading thermal video recorded with the 3M™ Scott™ Sight In-Mask Thermal Imager with Pro Package.



# 3M™ Scott™ Pak-Tracker Firefighter Locator System



## 3M™ Scott™ Pak-Tracker Firefighter Locator System

| Part Number | Description                        |
|-------------|------------------------------------|
| 200266-04   | Pak-Tracker Hand-Held Receiver Kit |

## Accessories for 3M™ Scott™ Pak-Tracker Firefighter Locator System

| Part Number | Description                                                     |
|-------------|-----------------------------------------------------------------|
| 200433-01   | Pak-Tracker Hand-Held Receiver Truck Charging System, 12V DC    |
| 200433-02   | Pak-Tracker Hand-Held Receiver Truck Charging System, 110V AC   |
| 200434-01   | Pak-Tracker Hand-Held Receiver Desktop Charging System, 110V AC |
| 200673-01*  | Pak-Link Programmer/Data-logger                                 |

\* For use in programming the Pak-Tracker ID of 3M™ Scott™ Air-Pak™ SCBA; may also be used for downloading PASS data from any 3M™ Scott™ Air-Pak™ SCBA certified to the NFPA 1981/1982, 2007 Edition standards (and newer), including pneumatic data introduced as part of the 2018 Edition standard.

**Note:** For 3M™ Scott™ Air-Pak™ X3 Pro SCBA, customers may also use the mobile application.

## 3M™ Scott™ RIT-Pak Fast Attack Emergency Air Supply System



### 3M™ Scott™ RIT-Pak Fast Attack Emergency Air Supply System (without Cylinder)

| Part Number | Bag Size | Pressure (psig) | Carrying Bag | 6' EBSS Hose | 5' RIC Hose | Facepiece Model       | Regulator Model |
|-------------|----------|-----------------|--------------|--------------|-------------|-----------------------|-----------------|
| 201564-01   | Medium   | 4500            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 201564-02   | Medium   | 5500            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 201564-03   | Small    | 4500            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *201564-11  | Medium   | 4500            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *201564-12  | Medium   | 5500            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *201564-13  | Small    | 4500            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 201564-21   | Medium   | 4500            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 201564-22   | Medium   | 5500            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 201564-23   | Small    | 4500            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| *201564-31  | Medium   | 4500            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| *201564-32  | Medium   | 5500            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| *201564-33  | Small    | 4500            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |

\*Compatible with Rectus-type fittings used on SCBA certified to the NFPA 1981, 2018 Edition standard.

### Cylinders for 3M™ Scott™ RIT-Pak Fast Attack Emergency Air Supply System

| Part Number | Description                           |
|-------------|---------------------------------------|
| 201561-01   | 4.5, 15-min, Cylinder and Valve (90°) |
| 200870-01   | 4.5, 30-min, Cylinder and Valve (90°) |
| 201567-01   | 5.5, 30-min, Cylinder and Valve (90°) |
| 201568-01   | 5.5, 45-min, Cylinder and Valve (90°) |

### Accessories for 3M™ Scott™ RIT-Pak Fast Attack Emergency Air Supply System

| Part Number | Description                                                    |
|-------------|----------------------------------------------------------------|
| 201558-01   | RIT-Pak Fast Attack, Bag, Medium                               |
| 201558-02   | RIT-Pak Fast Attack, Bag, Small                                |
| 201600-01   | RIT-Pak Fast Attack, Shoulder Strap Assembly                   |
| 201595-01   | RIT-Pak Fast Attack, AV-Series Facepiece                       |
| 201605-02   | RIT-Pak Fast Attack, E-Z Flo Regulator, Hansen                 |
| 201605-03   | RIT-Pak Fast Attack, E-Z Flo Regulator, Rectus                 |
| 31003648    | RIT-Pak Fast Attack, Carabiner                                 |
| 201825-01   | Vision C5 Facepiece with E-Z Flo C5 Regulator, RIT-Pak Variant |
| 201673-03   | RIT-Pak Fast Attack, E-Z Flo C5 Regulator, Hansen              |
| 201673-04   | RIT-Pak Fast Attack, E-Z Flo C5 Regulator, Rectus              |

## 3M™ Scott™ RIT-Pak III Emergency Air Supply System



### 3M™ Scott™ RIT-Pak III Emergency Air Supply System (without Cylinder)

| Part Number | Bag Size | Pressure (psig) | Carrying Bag | 6' EBSS Hose | 5' RIC Hose | Facepiece Model       | Regulator Model |
|-------------|----------|-----------------|--------------|--------------|-------------|-----------------------|-----------------|
| 200954-01   | Large    | 2216            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 200954-02   | Large    | 4500            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 200954-05   | Large    | 5500            | ●            | Hansen       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *200954-11  | Large    | 2216            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *200954-12  | Large    | 4500            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| *200954-15  | Large    | 5500            | ●            | Rectus       | ●           | AV-3000 (RIT-style)   | E-Z Flo         |
| 200954-21   | Large    | 2216            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 200954-22   | Large    | 4500            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 200954-25   | Large    | 5500            | ●            | Hansen       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 200954-31   | Large    | 2216            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 200954-32   | Large    | 4500            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |
| 200954-35   | Large    | 5500            | ●            | Rectus       | ●           | Vision C5 (RIT-style) | E-Z Flo C5      |

\*Compatible with Rectus-type fittings used on SCBA certified to the NFPA 1981, 2018 Edition standard.

### Accessories for 3M™ Scott™ RIT-Pak III Emergency Air Supply System

| Part Number | Description                                                    |
|-------------|----------------------------------------------------------------|
| 200955-01   | RIT-Pak III Bag, Less Shoulder Strap                           |
| 200989-01   | RIT-Pak III, Shoulder Strap Assembly                           |
| 200959-01   | RIT-Pak III, AV-3000 Facepiece                                 |
| 200962-01   | RIT-Pak III, E-Z Flo Regulator, Hansen                         |
| 200962-02   | RIT-Pak III, E-Z Flo Regulator, Rectus                         |
| 200991-01   | RIT-Pak III, Carrying Strap                                    |
| 201825-01   | Vision C5 Facepiece with E-Z Flo C5 Regulator, RIT-Pak Variant |
| 201673-01   | RIT-Pak III, E-Z Flo C5 Regulator, Hansen                      |
| 201673-02   | RIT-Pak III, E-Z Flo C5 Regulator, Rectus                      |

## 3M™ Scott™ AV-632 Bayonet Adapter

For use with Cartridges and Canisters.



### 3M™ Scott™ AV-632 Bayonet Adapter

| Part Number    | Description                                       | Pieces Per Pkg |
|----------------|---------------------------------------------------|----------------|
| XP-1008-4113-7 | AV-632 Bayonet Adapter*                           | 5              |
| 78-8151-2385-2 | Exhalation valve cover for AV-632 bayonet adapter | 1              |

\*Note: The 3M™ Scott™ 742 series twin cartridge 1/4 turn adapter (805622-01) is no longer available. The 3M™ Scott™ AV-632 Bayonet Adapter is the replacement product for use with the 3M™ Scott™ AV-3000 SureSeal Facepiece or 3M™ Scott™ AV-3000 HT Facepiece and 3M filters and cartridges on page 59.

### 3M™ Scott™ 40mm Adapters

| Part Number | Description                   | Pieces Per Pkg |
|-------------|-------------------------------|----------------|
| 805059-01   | 40 mm Canister Adapter        | 1              |
| 200423-01+  | 40 mm First Responder Adapter | 1              |
| 200423-02** | 40 mm First Responder Adapter | 1              |

+Approved for use with the 3M™ Scott™ AV-3000 SureSeal Facepiece (NIOSH 42 CFR + NIOSH CBRN) and 3M™ Scott™ AV-3000 HT Facepiece (NIOSH 42 CFR).

\*\*Approved for use with the 3M™ Scott™ AV-3000 HT Facepiece (NIOSH 42 CFR + NIOSH CBRN).

### Quantitative Fit Testing Adapters for use with TSI PortaCount

| Facepiece to be Fit Tested                       | Quantitative Fit Test Probe Adapter Required | Filter Required | Facepiece Adapter Required |
|--------------------------------------------------|----------------------------------------------|-----------------|----------------------------|
| 40 mm Cartridge Series                           | 805628-01                                    | 052683          | 805059-01                  |
| AV-3000 Series, Weld-O-Vista Facepiece           | ●                                            | ●               | ●                          |
| Vision C5                                        |                                              | ●               | 201520-01                  |
| 3M Bayonet Cartridges, 6000 Series               | 601*                                         | 2091*           | XP-1008-4113-7             |
| AV-3000 SureSeal Facepiece, AV-3000 HT Facepiece | ●                                            | ●               | ●                          |

\*Must be ordered through 3M bCom.

# 3M Particulate Filters and Cartridges

## 3M Bayonet Cartridges and Filters



### 3M™ Organic Vapor/Acid Gas Cartridge/Filter (6000 series)\*

| Part Number | Description                    | Pieces Per Pkg |
|-------------|--------------------------------|----------------|
| 6001        | Organic Vapor                  | 60             |
| 6002        | Acid Gas                       | 60             |
| 6003        | Organic Vapor/Acid Gas         | 60             |
| 6004        | Ammonia/Methylamine            | 60             |
| 6005        | Formaldehyde/Organic Vapor     | 60             |
| 6006        | Multi-Gas/Vapor                | 60             |
| 6007        | Mercury/Organic Vapor/Acid Gas | 60             |

### 3M™ Combination Cartridges/ P100 Particulate Filters (6000 series)\*

| Part Number | Description                                                                                                                           | Pieces Per Pkg |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------|----------------|
| 60921       | Organic Vapor/P100                                                                                                                    | 60             |
| 60922       | Acid Gas/P100                                                                                                                         | 60             |
| 60923       | Organic Vapor/Acid Gas/P100                                                                                                           | 60             |
| 60924       | Ammonia/Methylamine/P100                                                                                                              | 60             |
| 60925       | Formaldehyde/Organic Vapor/P100                                                                                                       | 60             |
| 60926       | Multi-Gas/Vapor/P100                                                                                                                  | 60             |
| 60927       | Mercury/Organic Vapor/AG/P100                                                                                                         | 60             |
| 60928       | Organic Vapor/Acid Gas/P100 3M recommended for use against methylbromide or radioiodine up to 5 ppm with daily cartridge replacement. | 60             |

### 3M™ Particulate Filters\*

| Part Number | Description                                                                             | Pieces Per Pkg |
|-------------|-----------------------------------------------------------------------------------------|----------------|
| 2091        | P100                                                                                    | 100            |
| 5N11        | N95 Prefilter                                                                           | 100            |
| 5P71        | P95 Prefilter                                                                           | 100            |
| 2071        | P95                                                                                     | 100            |
| 2076HF      | P95 HF with Nuisance Level AG relief. (Nuisance levels are less than OSHA PEL.)         | 100            |
| 2078        | P95 with Nuisance Level OV and AG relief. (Nuisance levels are less than OSHA PEL.)     | 100            |
| 2096        | P100 with Nuisance Level AG relief. (Nuisance levels are less than OSHA PEL.)           | 100            |
| 2097        | P100 with Nuisance Level OV relief. (Nuisance levels are less than OSHA PEL.)           | 100            |
| 2291        | P100                                                                                    | 100            |
| 2296        | P100 filter with Nuisance Level AG relief. (Nuisance levels are less than OSHA PEL.)    | 100            |
| 2297        | P100 filter with Nuisance Level OV relief. (Nuisance levels are less than OSHA PEL.)    | 100            |
| 7093        | P100                                                                                    | 100            |
| 7093C       | P100 HF with Nuisance Level OV and AG relief. (Nuisance levels are less than OSHA PEL.) | 100            |

\*Must be ordered through 3M bCom.

## Retainers\*

| Part Number | Description                                                                                                | Pieces Per Pkg |
|-------------|------------------------------------------------------------------------------------------------------------|----------------|
| 603         | Filter Retainer/Filter Adapter                                                                             | 16             |
| 501         | Filter Retainer                                                                                            | 100            |
| 502         | Filter Adapter (The 502 filter adapter is not NIOSH approved on any of the 3M Scott facepiece respirators) | 100            |

## Accessories\*

| Part Number | Description                   | Pieces Per Pkg |
|-------------|-------------------------------|----------------|
| 601         | Quantitative Fit Test Adapter | 1              |

\*Must be ordered through 3M bCom.

## 3M™ Scott™ 40 mm Cartridges and Canisters



### 3M™ Scott™ 40 mm Cartridges and Canisters

| Part Number | Description                                                                                              | Pieces Per Pkg |
|-------------|----------------------------------------------------------------------------------------------------------|----------------|
| 805557-01   | MPC Plus Cartridge                                                                                       | 1              |
| 052683      | 40 mm P100 (HEPA) Cartridge                                                                              | 1              |
| 045123      | Enforcement Cartridge                                                                                    | 1              |
| 045135      | CBRN Cap-1 Canister*  | 1              |
| 8004109     | TAC 1 Cartridge (For FRR facepiece only)                                                                 | 1              |
| 045170      | MPC40PF Cartridge                                                                                        | 1              |

\*Approved for use with the AV-3000 SureSeal Facepiece and 40 mm First Responder Adapter (200423-01) or AV-3000 HT Facepiece and 40 mm First Responder Adapter (200423-02)

# Bitrex

3M™ Qualitative Fit Test Kit



## 3M™ Qualitative Fit Test Kit

| Part Number | Description                         | Pieces Per Pkg |
|-------------|-------------------------------------|----------------|
| 2017070     | Bitrex 3M™ Qualitative Fit Test Kit | 1              |

## 3M™ Qualitative Fit Test Kit – Spare Parts

| Part Number | Description                                          | Pieces Per Pkg |
|-------------|------------------------------------------------------|----------------|
| 2017093     | Fit Test Solution Applicator Kit (6 ampoules/box)    | 6              |
| 2017092     | Sensitivity Solution Applicator Kit (6 ampoules/box) | 6              |
| 2017094     | Nebulizer                                            | 1              |
| 2017095     | Test Hood                                            | 1              |
| FT-10       | Fit Test Kit, Quantitative, Sweet                    | 1              |
| FT-30       | Fit Test Kit, Quantitative, Bitter                   | 1              |

## Fit Test Parts and Accessories For Use With 3M™ Scott™ 40 mm Cartridges and Canisters

| Part Number | Description                 | Pieces Per Pkg |
|-------------|-----------------------------|----------------|
| 805059-01   | 40 mm Canister Adapter      | 1              |
| 052683      | 40 mm P100 (HEPA) Cartridge | 1              |

## 3M™ Scott™ C420 Plus CBRN Powered Air Purifying Respirator (PAPR)



### 3M™ Scott™ C420 Plus CBRN Powered Air Purifying Respirator (PAPR)

|          | Blower    | LiSO2 Battery | Decon Belt | 30" CBRN AV-PAPR Hose (Use with AV-Facepieces.*) | 36" CBRN AV-PAPR Hose (Use with AV-Facepieces.*) |
|----------|-----------|---------------|------------|--------------------------------------------------|--------------------------------------------------|
| Part No: | 200699-01 | 805358-01     | 805359-01  | 200829-30                                        | 200829-36                                        |

#### PAPR Blowers:

|                                                                                                                |   |   |   |   |   |
|----------------------------------------------------------------------------------------------------------------|---|---|---|---|---|
| 200699-01                                                                                                      | ● |   |   |   |   |
| 200698-00                                                                                                      | ● |   | ● |   |   |
| <i>For use with 3M™ Scott™ AV-3000 SureSeal Facepiece or 3M™ Scott™ AV-3000 HT Facepiece (sold separately)</i> |   |   |   |   |   |
| 200830-30                                                                                                      | ● |   | ● | ● |   |
| 200830-36                                                                                                      | ● |   | ● |   | ● |
| 200833-30                                                                                                      | ● | ● | ● | ● |   |
| 200833-36                                                                                                      | ● | ● | ● |   | ● |

\*AV-PAPR hose connects directly to AV-series facepieces.

\*\*The 3M™ Scott™ C420 Plus CBRN Powered Air Purifying Respirator (PAPR) is also approved for NIOSH non-CBRN applications; Additional configurations are available.

#### CBRN Canister:

| Part Number | Description                                                                                             |
|-------------|---------------------------------------------------------------------------------------------------------|
| 045135      | CBRN Cap-1 Canister  |

#### Other NIOSH approved canisters:

| Part Number | Description                |
|-------------|----------------------------|
| 045170      | MPC40PF                    |
| 045123      | Enforcement Cartridge      |
| 052683      | 40mm P100 (HEPA) Cartridge |

**3M™ Scott™ C420 Plus CBRN Powered Air Purifying Respirator (PAPR) Parts and Accessories**

| Part Number             | Description                                                                            | Pieces Per Pkg |
|-------------------------|----------------------------------------------------------------------------------------|----------------|
| <b>Facepiece</b>        |                                                                                        |                |
| See Pg 47-49            | AV-3000 HT Facepiece with Kevlar® Head Harness                                         | 1              |
| See Pg 50-52            | AV-3000 SureSeal Facepiece with Kevlar® Head Harness                                   | 1              |
| <b>Breathing Tubes</b>  |                                                                                        |                |
| 200829-30               | 30" AV-PAPR Breathing Tube for approved AV-Facepieces                                  | 1              |
| 200829-36               | 36" AV-PAPR Breathing Tube for approved AV-Facepieces                                  | 1              |
| <b>PAPR Blower Unit</b> |                                                                                        |                |
| 200698-00               | C420 Plus CBRN PAPR Blower Kit (Blower, decon belt, airflow indicator)                 | 1              |
| 200699-01               | C420 Plus CBRN PAPR Blower only                                                        | 1              |
| 805359-01               | Decontamination Belt                                                                   | 1              |
| 805374-01               | Airflow Indicator                                                                      | 1              |
| <b>Batteries</b>        |                                                                                        |                |
| 805358-01               | LiSO2 Battery                                                                          | 1              |
| 31002361                | (Black) End cap for LiSO2 Battery                                                      |                |
| 200701-01               | NiMH Rechargeable Battery Conversion Kit, (Single Bank Charger, NiMH Battery, End Cap) | 1              |
| 31001504                | NiMH Rechargeable Battery Pack                                                         | 1              |
| 31001506                | (Green) End Cap for NiMH Rechargeable Battery                                          | 1              |
| 200703-01               | Single Unit Battery Recharger                                                          | 1              |
| <b>Carry Case</b>       |                                                                                        |                |
| 31000578                | Duffle bag carry case                                                                  | 1              |
| See Pages 46            | <b>Cartridges and Canisters</b>                                                        |                |

## 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator



| SAR Model        | Entry/Egress   | Pressure (psig) | Cylinder               | Harness   | Regulator              | Airline            | Facepiece ①                               | Case ② | Packaging     |
|------------------|----------------|-----------------|------------------------|-----------|------------------------|--------------------|-------------------------------------------|--------|---------------|
| 4 Ska-Pak AT SAR | 2 Entry/Egress | 2 2216          | 00 None                | 3 Nylon   | 3 E-Z Flo Vibralert    | 1 Hansen           | 0 None                                    | 0 None | 1 One Per Box |
|                  |                | 3 3000          | 01 2216/Aluminum/3 min | 4 Kevlar® | 4 E-Z Flo Vibralert QD | 2 Schrader         | 3 AV-3000 SureSeal Facepiece, Kevlar® (M) |        |               |
|                  |                | 4 4500          | 02 3000/Carbon/5 min   |           |                        | 3 Cejn             | 6 AV-3000 SureSeal Facepiece Poly (M)     |        |               |
|                  |                |                 | 03 3000/Carbon/10 min  |           |                        | 4 Hansen HK Plug   | 9 AV-3000 SureSeal Facepiece Rubber (M)   |        |               |
|                  |                |                 | 06 4500/Carbon/15 min  |           |                        | 5 Hansen HK Socket |                                           |        |               |
|                  |                |                 | Drained                |           |                        |                    |                                           |        |               |
|                  |                |                 | AA 2216/Aluminum/3 min |           |                        |                    |                                           |        |               |
|                  |                |                 | BB 3000/Carbon/5 min   |           |                        |                    |                                           |        |               |
|                  |                |                 | CC 3000/Carbon/10 min  |           |                        |                    |                                           |        |               |
|                  |                |                 | FF 4500/Carbon/15 min  |           |                        |                    |                                           |        |               |

### 1. Part Number:

Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 4 | 2 | X | XX | 0 | X | X | X | X | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

- ① If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved facepiece as a separate line item (see pages 23-28 for selection).  
 ② Cases are not compatible with select 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator configurations. Please choose "none" for case option and order case separately as required noting that fit on all configurations cannot be guaranteed.

### Example

#### Ska-Pak AT SAR


For entry/egress, for 3000 psi cylinder, with 3000 psig 10 min carbon cylinder, Kevlar® harness, with E-Z Flo Vibralert, Hansen airline, no case, shipped one per box.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 4 | 2 | 3 | 03 | 0 | 4 | 3 | 1 | 0 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order facepiece and case separately.

This configurator is a guide to 3M™ Scott™ AT Supplied-Air Respirator Ska-Pak AT SAR part numbers.

# 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator



## 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator Parts and Accessories

| Item Number | Description                              | Pieces Per Pkg  | Part Number |
|-------------|------------------------------------------|-----------------|-------------|
| <b>1</b>    | <b>Facepiece</b>                         |                 |             |
| 1a          | AV-3000 HT Facepiece                     | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece               | See Pages 26-28 |             |
| <b>2</b>    | <b>Regulator</b>                         |                 |             |
| 2a          | E-Z Flo with Vibralert                   | 1               | 804370-09   |
| 2b          | E-Z Flo with Vibralert Quick Disconnect  | 1               | 804370-02   |
| <b>3</b>    | <b>Quick Disconnect Hose Assembly</b>    | 1               | 804694-05   |
| <b>4</b>    | <b>Harnesses</b>                         |                 |             |
| 4a          | Nylon                                    | 1               | 804982-01   |
| 4b          | Kevlar®                                  | 1               | 804981-01   |
| <b>5</b>    | <b>Pressure Reducers</b>                 |                 |             |
| 5a          | 2216/3000, Entry/Egress                  | 1               | 200031-03   |
| 5b          | 4500 psig, Entry/Egress                  | 1               | 200031-04   |
| <b>6</b>    | <b>Cylinder and Valve Assemblies</b>     |                 |             |
| 6a          | 2216 psi, Aluminum, 3-minute             | 1               | 805031-01   |
| 6b          | 3000 psi, Carbon, 5-minute               | 1               | 805947-02   |
| 6c          | 3000 psi, Carbon, 10-minute              | 1               | 805948-02   |
| 6f          | 4500 psi, Carbon, 15-minute              | 1               | 200779-01   |
| <b>7</b>    | <b>Airlines Hose and Fittings</b>        |                 |             |
| 7a          | Airline Hose with Hansen/Foster Fitting  | 1               | 804305-01   |
| 7b          | Airline Hose with Schrader Fitting       | 1               | 804305-02   |
| 7c          | Airline Hose with Hansen HK Fitting Plug | 1               | 804305-03   |
| <b>8</b>    | <b>Airlines Supply Hoses</b>             | See Page 61     |             |
| <b>9</b>    | <b>Waist Extension Belts</b>             |                 |             |
| 9a          | Kevlar® Extension Belt, 1.5 Inches Wide  | 1               | 805088-01   |
| 9b          | Nylon Extension Belt, 2 Inches Wide      | 1               | 805088-02   |
| <b>10</b>   | <b>Accessories (Not shown)</b>           |                 |             |
| 10a*        | Ska-Pak Series Hard Case                 | 1               | 803278-01   |

\* Cases are not compatible with select 3M™ Scott™ Ska-Pak AT Supplied-Air Respirator configurations.

# 3M™ Scott™ Ska-Pak Plus Supplied Air Respirator



| SAR Model          | Entry/Egress ① | Pressure (psig) ② | Cylinder               | Harness   | Regulator             | Airline            | Facepiece ③                               | Case        | Packaging     |
|--------------------|----------------|-------------------|------------------------|-----------|-----------------------|--------------------|-------------------------------------------|-------------|---------------|
| 3 Ska-Pak Plus SAR | 2 Entry/Egress | 2 2216            | 00 None                | 3 Nylon   | 1 E-Z Flo             | 0 None             | 0 None                                    | 0 None      | 1 One Per Box |
|                    | 3 Egress Only  | 3 3000            | 01 2216/Aluminum/5 min | 4 Kevlar® | 2 E-Z Flo Modulair QD | 1 Hansen           | 3 AV-3000 SureSeal Facepiece, Kevlar® (M) | 1 Hard Case |               |
|                    |                | 4 4500            | 02 3000/Carbon/5 min   |           |                       | 2 Schrader         | 6 AV-3000 SureSeal Facepiece Poly (M)     |             |               |
|                    |                | 7 3000 E-Z Fill   | 03 3000/Carbon/10 min  |           |                       | 3 Cejn             | 9 AV-3000 SureSeal Facepiece Rubber (M)   |             |               |
|                    |                | 8 4500 E-Z Fill   | 06 4500/Carbon/15 min  |           |                       | 4 Hansen HK Plug   |                                           |             |               |
|                    |                |                   | Drained                |           |                       | 5 Hansen HK Socket |                                           |             |               |
|                    |                |                   | AA 2216/Aluminum/5 min |           |                       |                    |                                           |             |               |
|                    |                |                   | BB 3000/Carbon/5 min   |           |                       |                    |                                           |             |               |
|                    |                |                   | CC 3000/Carbon/10 min  |           |                       |                    |                                           |             |               |
|                    |                |                   | FF 4500/Carbon/15 min  |           |                       |                    |                                           |             |               |

**1. Part Number:**  
Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 3 | X | X | XX | 0 | X | X | X | X | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

- ① Must select entry/egress to select an Airline option.  
 ② Pressure with E-Z Fill designation utilizes an alternate filling connection fitting on the cylinder valve to enable convenient charging of the cylinder.  
 ③ If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved Facepiece as a separate line item (see pages 23-28 for selection).

Example

**Ska-Pak Plus**  
For entry/egress, for 2216 psi cylinder, with 2216 psig 5 min Aluminum cylinder, Kevlar® harness, with E-Z Flo Regulator, Hansen airline, no facepiece, no case, shipped one per box.


|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 3 | 2 | 2 | 01 | 0 | 4 | 1 | 1 | 0 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order facepiece and case separately.

This configurator is a guide to 3M™ Scott™ Ska-Pak Plus Supplied-Air Respirator part numbers.

# Powered and Supplied Air

## 3M™ Scott™ Ska-Pak Plus Supplied-Air Respirator



**3M™ Scott™ Ska-Pak Plus Supplied-Air Respirator Parts and Accessories**

| Item Number | Description                                        | Pieces Per Pkg  | Part Number |
|-------------|----------------------------------------------------|-----------------|-------------|
| <b>1</b>    | <b><i>Facepiece</i></b>                            |                 |             |
| 1a          | AV-3000 HT Facepiece                               | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece                         | See Pages 26-28 |             |
| <b>2</b>    | <b><i>Regulator</i></b>                            |                 |             |
| 2a          | E-Z Flo                                            | 1               | 804221-01   |
| 2b          | E-Z Flo with Modulair Quick Disconnect             | 1               | 804441-05   |
| <b>3</b>    | <b><i>Quick Disconnect Hose Assembly</i></b>       | 1               | 804694-01   |
| <b>4</b>    | <b><i>Harnesses</i></b>                            |                 |             |
| 4a          | Kevlar®                                            | 1               | 804981-01   |
| 4b          | Nylon                                              | 1               | 804982-01   |
| <b>5</b>    | <b><i>Pressure Reducers</i></b>                    |                 |             |
| 5a          | 2.2/3.0 Reducer Assembly                           | 1               | 804304-11   |
| 5f          | 4.5 Reducer Assembly                               | 1               | 804304-01   |
| 5g          | 4.5 Reducer Assembly (Escape Only)                 | 1               | 804310-01   |
| <b>6</b>    | <b><i>Cylinder and Valve Assemblies</i></b>        |                 |             |
| 6a          | 2216 psi, Aluminum, 5-minute                       | 1               | 805031-01   |
| 6b          | 3000 psi, Carbon, 5-minute                         | 1               | 805947-02   |
| 6c          | 3000 psi, Carbon, 10-minute                        | 1               | 805948-02   |
| 6f          | 4500 psi, Carbon, 15-minute                        | 1               | 200779-01   |
| <b>7</b>    | <b><i>E-Z Fill Cylinder and Valve Assembly</i></b> |                 |             |
| 7a          | 3000 psi, Carbon, 10-minute                        |                 | 201386-01   |
| 7b          | 4500 psi, Carbon, 15-minute                        |                 | 201389-01   |
| <b>8</b>    | <b><i>Airlines Hose and Fittings</i></b>           |                 |             |
| 8a          | Airline Hose with Hansen/Foster Fitting            | 1               | 804305-01   |
| 8b          | Airline Hose with Schrader Fitting                 | 1               | 804305-02   |
| 8c          | Airline Hose with Hansen HK Fitting Plug           | 1               | 804305-03   |
| <b>9</b>    | <b><i>Airlines Supply Hose</i></b>                 | See Page 61     |             |
| <b>10</b>   | <b><i>Waist Extension Belts</i></b>                |                 |             |
| 10a         | Nylon Extension Belt, 2 Inches Wide                | 1               | 805088-02   |
| 10b         | Kevlar® Extension Belt, 1.5 Inches Wide            | 1               | 805088-01   |
| <b>11</b>   | <b><i>Accessories</i></b>                          |                 |             |
| 11a*        | Ska-Pak Series Hard Case                           | 1               | 803278-01   |

# Powered and Supplied Air

## 3M™ Scott™ Ska-Pak Supplied-Air Respirator



| SAR Model     | Entry/Egress ① | Pressure ④ (psig) | Cylinder ②             | Harness         | Regulator | Airline            | Facepiece ③                               | Case        | Packaging     |
|---------------|----------------|-------------------|------------------------|-----------------|-----------|--------------------|-------------------------------------------|-------------|---------------|
| 2 Ska-Pak SAR | 2 Entry/Egress | 2 2216            | 00 None                | 2 Polypropylene | 1 E-Z Flo | 0 None             | 0 None                                    | 0 None      | 1 One Per Box |
|               | 3 Egress Only  | 4 4500            | 01 2216/Aluminum/5 min | 4 Kevlar®       |           | 1 Hansen           | 3 AV-3000 SureSeal Facepiece, Kevlar® (M) | 1 Hard Case |               |
|               |                | 8 4500 E-Z Fill   | 06 4500/Carbon/15 min  |                 |           | 2 Schrader         | 6 AV-3000 SureSeal Facepiece Poly (M)     |             |               |
|               |                |                   | Drained                |                 |           | 3 Cejn             | 9 AV-3000 SureSeal Facepiece Rubber (M)   |             |               |
|               |                |                   | AA 2216/Aluminum/5 min |                 |           | 4 Hansen HK Plug   |                                           |             |               |
|               |                |                   | FF 4500/Carbon/15 min  |                 |           | 5 Hansen HK Socket |                                           |             |               |

### 1. Part Number:

Select a one or two digit number per box from the chart above that corresponds to your choice.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 2 | X | X | XX | 0 | X | 1 | X | X | X | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

① Must select entry/egress to select an Airline option.

② Cylinder clamps not included when selecting option 00.

③ If you prefer an alternate facepiece style, head harness, or size, choose "none" and order an approved facepiece as a separate line item (see pages 23-28 for selection).

④ Pressure with E-Z Fill designation utilizes an alternate filling connection fitting on the cylinder valve to enable convenient charging of the cylinder.

### Example

#### Ska-Pak SAR


For entry/egress, for 2216 psi cylinder, with 2216 psig 5 min Aluminum cylinder, Polypropylene Harness, with E-Z Flo Regulator, Hansen airline, no facepiece, no case, shipped one per box.

|     |   |   |   |    |   |   |   |   |   |   |   |
|-----|---|---|---|----|---|---|---|---|---|---|---|
| SAR | 2 | 2 | 2 | 01 | 0 | 2 | 1 | 1 | 0 | 0 | 1 |
|-----|---|---|---|----|---|---|---|---|---|---|---|

In this example, order facepiece and case separately.

This configurator is a guide to 3M™ Scott™ Ska-Pak Supplied-Air Respirator part numbers.

# 3M™ Scott™ Ska-Pak Supplied-Air Respirator



# Powered and Supplied Air

## 3M™ Scott™ Ska-Pak Supplied-Air Respirator Parts and Accessories

| Item Number | Description                                 | Pieces Per Pkg  | Part Number |
|-------------|---------------------------------------------|-----------------|-------------|
| 1           | <b>Facepiece</b>                            |                 |             |
| 1a          | AV-3000 HT Facepiece                        | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece                  | See Pages 26-28 |             |
| 2           | <b>E-Z Flo Regulator</b>                    | 1               | 804221-01   |
| 3           | <b>Harnesses</b>                            |                 |             |
| 3a          | Polypropylene                               | 1               | 802200-01   |
| 3b          | Kevlar®                                     | 1               | 804307-01   |
| 4           | <b>Pressure Reducers</b>                    |                 |             |
| 4a          | 2.2/3.0 Reducer Assembly                    | 1               | 804304-11   |
| 4c          | 4.5 Reducer Assembly                        | 1               | 804304-01   |
| 4d          | 4.5 Reducer Assembly (Escape only)          | 1               | 804310-01   |
| 5           | <b>Cylinder and Valve Assemblies</b>        |                 |             |
| 5a          | Aluminum, 5-minute, 2216 psig               | 1               | 801935-03   |
| 5d          | Carbon, 15-minute, 4500 psig                | 1               | 200779-03   |
| 6           | <b>E-Z Fill Cylinder and Valve Assembly</b> |                 |             |
| 6a          | 4500 psi, Carbon, 15-minute                 |                 | 201389-02   |
| 7           | <b>Airline Hose and Fittings</b>            |                 |             |
| 7a          | Airline Hose with Hansen/Foster Fitting     | 1               | 804305-01   |
| 7b          | Airline Hose with Schrader Fitting          | 1               | 804305-02   |
| 7c          | Airline Hose with Hansen HK Fitting Plug    | 1               | 804305-03   |
| 8           | <b>Airline Supply Hoses</b>                 | See Page 61     |             |
| 9           | <b>Accessories</b>                          |                 |             |
| 9a          | Ska-Pak Series Hard Case                    | 1               | 803278-01   |



# 3M™ Scott™ E-Z Airline Supplied Air Respirator



## 3M™ Scott™ E-Z Airline Supplied Air Respirator

| Part Numbers | Harness | Facepiece                                 | Regulator                | Hose Fitting |
|--------------|---------|-------------------------------------------|--------------------------|--------------|
| 804386-66    | Nylon   | Facepiece not included, order separately. | E-Z Flo with Modulair QD | Hansen       |
| 804386-62    | Nylon   | Facepiece not included, order separately. | E-Z Flo with Modulair QD | Schrader     |


## 3M™ Scott™ E-Z Airline Supplied Air Respirator (without Modulair)

| Part Numbers | Harness | Facepiece                                 | Regulator | Hose Fitting |
|--------------|---------|-------------------------------------------|-----------|--------------|
| 804386-67    | Nylon   | Facepiece not included, order separately. | E-Z Flo   | Hansen       |

# Powered and Supplied Air

## 3M™ Scott™ E-Z Airline Supplied Air Respirator Parts and Accessories

| Item Number | Description                   | Pieces Per Pkg  | Part Number |
|-------------|-------------------------------|-----------------|-------------|
| 1           | <b>Full Facepieces</b>        |                 |             |
| 1a          | AV-3000 HT Facepiece          | See Pages 23-25 |             |
| 1b          | AV-3000 SureSeal Facepiece    | See Pages 26-28 |             |
| 2           | <b>Harness</b>                | 1               | 804493-01   |
| 3           | <b>E-Z Flo Regulator</b>      |                 |             |
| 3a          | Without Modulair, Hansen      | 1               | 804441-01   |
| 3b          | Without Modulair, Schrader    | 1               | 804441-02   |
| 3c          | Without Modulair, Hansen HK   | 1               | 804441-03   |
| 3d          | With Modulair                 | 1               | 804679-01   |
| 4           | <b>Modulair Hose Assembly</b> |                 |             |
| 4a          | Hose Assembly, Hansen         | 1               | 804694-04   |
| 4b          | Hose Assembly, Schrader       | 1               | 804694-03   |
| 4c          | Hose Assembly, Hansen HK      | 1               | 804694-02   |
| 5           | <b>Airline Supply Hoses</b>   | See Page 61     |             |





## Supply Hose Assemblies

| Part Number | Description       | Pieces Per Pkg |
|-------------|-------------------|----------------|
| 26369-006   | Hansen HK, 6 Ft   | 1              |
| 26369-010   | Hansen HK, 10 Ft  | 1              |
| 26369-025   | Hansen HK, 25 Ft  | 1              |
| 26369-050   | Hansen HK, 50 Ft  | 1              |
| 26369-100   | Hansen HK, 100 Ft | 1              |
| 26370-006   | Foster, 6 Ft      | 1              |
| 26370-010   | Foster, 10 Ft     | 1              |
| 26370-025   | Foster, 25 Ft     | 1              |
| 26370-050   | Foster, 50 Ft     | 1              |
| 26370-100   | Foster, 100 Ft    | 1              |
| 26370-150   | Foster, 150 Ft    | 1              |
| 30010-006   | Hansen, 6 Ft      | 1              |
| 30010-010   | Hansen, 10 Ft     | 1              |
| 30010-025   | Hansen, 25 Ft     | 1              |
| 30010-050   | Hansen, 50 Ft     | 1              |
| 30010-100   | Hansen, 100 Ft    | 1              |
| 30010-150   | Hansen, 150 Ft    | 1              |
| 30010-300   | Hansen, 300 Ft    | 1              |
| 30020-006   | Schrader, 6 Ft    | 1              |
| 30020-010   | Schrader, 10 Ft   | 1              |
| 30020-025   | Schrader, 25 Ft   | 1              |
| 30020-050   | Schrader, 50 Ft   | 1              |
| 30020-100   | Schrader, 100 Ft  | 1              |
| 30020-150   | Schrader, 150 Ft  | 1              |
| 805659-006  | Cejn, 6 Ft        | 1              |
| 805659-025  | Cejn, 25 Ft       | 1              |
| 805659-050  | Cejn, 50 Ft       | 1              |
| 805659-100  | Cejn, 100 Ft      | 1              |

## Pass-Thru Assemblies

| Part Number | Description                                     | Pieces Per Pkg |
|-------------|-------------------------------------------------|----------------|
| 803620-01*  | Pass-Thru Assembly, Hansen Fitting, Airline     | 1              |
| 803620-02*  | Pass-Thru Assembly, Schrader Fitting, Airline   | 1              |
| 803620-05   | Pass-Thru Assembly, Cejn Fitting, Airline       | 1              |
| 803620-03** | Pass-Thru Assembly, Hansen Fitting, Dual EBSS   | 1              |
| 803620-04** | Pass-Thru Assembly, Schrader Fitting, Dual EBSS | 1              |

\* For use with airline.

\*\* For use with Dual EBSS.

\*\*\* Pass-thru devices are manufactured for use in protective chemical suits, e.g. Level A and Level B. NIOSH approvals for pass-thru devices in chemical suits are carried by the chemical suit manufacturer. The pass-thru devices must be installed by the suit manufacturer to maintain proper NIOSH approvals.

**Note:** UEBSS Rectus fitting is compatible with the Cejn fitting.

## 3M™ Scott™ Mobile Air Cart



### 3M™ Scott™ Mobile Air Cart (without Cylinders)

| Part Number | Description                                                 | Pieces Per Pkg |
|-------------|-------------------------------------------------------------|----------------|
| 805825-01   | Mobile Air Cart, 2 Outlet, Hansen Style, Aux. Inlet         | 1              |
| 805825-04   | Mobile Air Cart, 2 Outlet, Schrader, Aux. Inlet             | 1              |
| 805826-01   | Mobile Air Cart, 4 Outlet, Hansen Style, Aux. Inlet         | 1              |
| 805826-04   | Mobile Air Cart, 4 Outlet, Schrader Aux. Inlet              | 1              |
| 805827-01   | Mobile Air Cart, 4 Outlet, 2 Tool, Hansen Style, Aux. Inlet | 1              |
| 805827-04   | Mobile Air Cart, 4 Outlet, 2 Tool, Schrader, Aux. Inlet     | 1              |

## 3M™ Scott™ TRC-1 Air Cart



### 3M™ Scott™ TRC-1 Air Cart (without Cylinders)

| Part Number | Description                                        | Pieces Per Pkg |
|-------------|----------------------------------------------------|----------------|
| 200070-01   | TRC-1 Air Cart, 8 Outlet, Aux. Inlet, Hansen Style | 1              |
| 200070-03   | TRC-1 Air Cart, 8 Outlets, Aux. Inlet, Hansen HK   | 1              |
| 200070-04   | TRC-1 Air Cart, 8 Outlets, Aux. Inlet, Schrader    | 1              |
| 200070-05   | TRC-1 Air Cart, 8 Outlets, Aux. Inlet, Cejn        | 1              |

See page 17-18 for applicable cylinders.

## 3M™ Scott™ ELSA Emergency Escape Breathing Device (EEBD)-N



### 3M™ Scott™ ELSA EEBD-N

| Part Number | Description                             |
|-------------|-----------------------------------------|
| 8007212     | ELSA EEBD 5 Min-N                       |
| 8007213     | ELSA EEBD 10 Min-N                      |
| 8007214     | ELSA EEBD 15 Min-N                      |
| 8007212-D   | ELSA EEBD 5 Min-N, Drained              |
| 8007213-D   | ELSA EEBD 10 Min-N, Drained             |
| 8007214-D   | ELSA EEBD 15 Min-N, Drained             |
| 8007196     | ELSA Carry Bag Assy, 5 Min-N            |
| 8007197     | ELSA Carry Bag Assy, 10 Min-N           |
| 8007198     | ELSA Carry Bag Assy, 15 Min-N           |
| 8007210     | ELSA Replacement Carry Strap-N          |
| 8007204     | ELSA Replacement Hood w/Diffuser-N      |
| 2010173     | Anti-Fog Wipe                           |
| 2007294     | Cylinder Fill Port Dust Covers (10/pkg) |



**Personal Safety Division**  
**3M Scott Fire & Safety**  
P.O. Box 569  
Monroe, NC 28111  
1-800-247-7257

3M PSD Products are for  
occupational use only.

Rev C 09/22

[3M.com/ScottFire](https://3M.com/ScottFire) (US)  
[3M.ca/ScottFire](https://3M.ca/ScottFire) (Canada)  
[3M.com/ScottIndustrial](https://3M.com/ScottIndustrial) (US)  
[3M.ca/ScottIndustrial](https://3M.ca/ScottIndustrial) (Canada)

The Bluetooth® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company | PortaCount is a registered trademark of TSI, Inc. | Bitrex is a registered trademark of Macfarlan Smith Ltd. MOTOROLA is a trademark of Motorola Trademark Holdings, LLC.

3M, Scott and Air-Pak are trademarks of 3M. Used under license in Canada.  
© 2022, 3M. All rights reserved. All other trademarks are property of their  
respective owners. 2206-24343