


# 3M™ Dry-Sanding Net and Multi-Hole Abrasive Discs for Dust Extraction

**NEW**



**Cubitron™ II Net**

**Cut Rate**  
●●●●●


**Disc Life**  
●●●●●

**Dust Extraction**  
●●●●●

**Grades**  
80, 120, 150, 180,  
220, 240, 320

**Material**  
Net

**Attachment Type**  
Hookit™



**Cubitron™ II**

**Cut Rate**  
●●●●●

**Disc Life**  
●●●●●


**Dust Extraction**  
●●●●●

**Grades**  
40, 80, 120, 150, 180,  
220, 240, 320, 400

**Material**  
Paper

**Attachment Type**  
Hookit™

**NEW**



**Blue Net**

**Cut Rate**  
●●●


**Disc Life**  
●●●

**Dust Extraction**  
●●●●●

**Grades**  
80, 120, 150,  
180, 220, 240, 320

**Material**  
Net

**Attachment Type**  
Hookit™



**Blue**

**Cut Rate**  
●●●●●


**Disc Life**  
●●●●●

**Dust Extraction**  
●●●●●

**Grades**  
40, 80, 120, 150,  
180, 220, 240, 320,  
400, 500, 600, 800

**Material**  
Paper

**Attachment Type**  
Hookit™ and Stikit™



**Gold**

**Cut Rate**  
●●


**Disc Life**  
●●

**Dust Extraction**  
●●

**Grades**  
80, 100, 120, 150, 180,  
220, 240, 320, 360,  
400, 500, 600, 800

**Material**  
Paper

**Attachment Type**  
Hookit™ and Stikit™



**Finishing Film**

**Cut Rate**  
●●●●●

**Disc Life**  
●●●●●

**Dust Extraction**  
●●●

**Grades**  
500, 600, 800,  
1000, 1200, 1500, 2000

**Material**  
Film

**Attachment Type**  
Hookit™