
3M[™] MetPak[™] 2-FB Inverse Header

2 mm 5-Row, Right Angle, Elevated, Solder Tail

MP2 Series



- Elevated connector for offset coplanar/end-to-end stacking
- Ideal for low profile IU boxes
- Ideal for "pizza box" applications
- Ideal for hot swapping applications
- 16 mm to 18.5 mm high profile stacking
- Mates with MP2-SXXXG sockets
- Prevents removing top cover in rack applications
- Footprint compatible with standard Futurebus+®
- See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of www.3Mconnectors.com for compliance information (RIAE1 & C1 apply)

Date Modified: September 17, 2013

TS-1124-C Sheet 1 of 4

Physical

Insulation:

Material: High Temp LCP Flammability: UL 94V-0 Color: Beige

Contact:

Material: Copper Alloy

Plating:

Underplating: 50 µ" [1.27 µm] Nickel Wiping Area: See Ordering Information Solder Tails: See Ordering Information

Electrical

Current Rating: Signal: 1.5 A – All contacts simultaneously

Insulation Resistance: 10³ MΩ Withstanding Voltage: 1000 V_{AC}

Environmental


Temperature Rating: -55°C to +125°C

Process Temperature Rating: 260°C (Profile per J-STD-020C)

Moisture Sensitivity Level: 1 (per J-STD-020C)

MetPak is a trademark of 3M Company. Futurebus+ is a registered trademark of the Institute of Electrical and Electronic Engineers, Inc. (IEEE) 2 mm 5-Row, Right Angle, Elevated, Solder Tail

MP2 Series



2 mm 5-Row, Right Angle, Elevated, Solder Tail

MP2 Series

Table 1 - Connector & Row Lengths					
Pin Count	Pin Count Dim. "A" mm [inch]		Rows		
120	47.95 [1.888]	46.00 [1.811]	5		
240	95.95 [3.778]	94.00 [3.701]	5		


Table 2 - Mate Length						
Loading Pattern Code	Description	Mate Length Row A	Mate Length Row B	Mate Length Row C	Mate Length Row D	Mate Length Row E (5-Row Prod. Only)
1	All Positions Filled	5.00 [0.197]	5.00 [0.197]	5.00 [0.197]	5.00 [0.197]	5.00 [0.197]

Table 3 - Tail Length						
Loading Pattern Code	Description	Tail Length Row A	Tail Length Row B	Tail Length Row C	Tail Length Row D	Tail Length Row E
1	All Positions Filled	3.13 [0.123]	3.13 [0.123]	3.13 [0.123]	2.38 [0.094]	2.38 [0.094]

Table 4 - Plating				
Plating Suffix Plating Composition				
KR (RIA E1 & C1 apply)	0.76 μm [30 μ"] Min. Au Contact Area 2.54 μm [100 μ"] Min. Matt Whisker Mitigating Sn Tail Area 1.27 μm [50 μ"] Min. Ni all over			
LR (RIA E1& C1 apply)	0.08 μm [3 μ"] Min. Au Contact Area 0.67 μm [27 μ"] Min. PdNi Contact Area 2.54 μm [100 μ"] Min. Matt Whisker Mitigating Sn Tail Area 1.27 μm [50 μ"] Min. Ni all over			

TS-1124-C Sheet 3 of 4 2 mm 5-Row, Right Angle, Elevated, Solder Tail

MP2 Series



RECOMMENDED PCB HOLE MOUNTING PATTERN

Table 5 - HOLE PLATING FINISHES							
HOLE	Finished Dia. MM [in]	Cu Thickness [mm [in]	Immersion Matte Sn Thickness microns [µ"]	Electrolytic Au Thickness microns [µ"]	OSP ENTEK Thickness microns [µ"]	Drilled Hole Dia. mm [in]	
"D"	0.700-0.800 [.02760315]	0.025-0.045 [0.001-0.002]	0.5 - 2.5 [20 - 100]	0.1 - 0.5 [4 - 20]	0.2 - 0.5 [8 - 20]	0.830-0.860 [.0330- .0340] or 0.85 mm [#66] TWIST DRILL	

TS-1124-C Sheet 4 of 4 3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of

SVI

3M Electronics Solutions Division 6801 River Place Blvd. Austin, TX 78726-9000 U.S.A. 1-800-225-5373 www.3Mconnectors.com

the legal theory asserted.

unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.