

# Masking and Duct Tapes Product Catalog





# Table of Contents

<b>General Purpose Masking Tape</b>	<b>3</b>
Utility.....	4
General Purpose Paint Masking.....	5
Outdoor.....	6
<b>High Temp Masking Tape</b>	<b>9</b>
225°F.....	10
250°F.....	11
300°F.....	12
325°F.....	13
350°F.....	13
<b>Fine Line Masking Tape</b>	<b>15-17</b>
<b>Duct Tape</b>	<b>19</b>
Utility.....	20
Heavy Duty.....	21
Clean Removal.....	22
<b>Masking Film</b>	<b>27-29</b>
<b>Flatback Tape</b>	<b>30-31</b>
Utility.....	30
Specialty.....	31
<b>Product Attributes/Features</b> .....	<b>34-46</b>
<b>Detailed Product List</b> .....	<b>34-46</b>



3M 2017  
3M

LIFE.COM

LOTTE

# General Purpose Masking Tape




## ▶ Tapes ready to tackle any task.

When you need a reliable product to help you get the job done, there's a masking tape to suit your needs. Masking tape was designed to provide instant adhesion to a variety of surfaces without lifting or curling. Available in a variety of strengths, heat and UV resistance, widths and applications, you can rely on 3M General Purpose Masking tapes to step up and stick around until the job is done.

**Helping you find the right tape for every task.**



# Utility Masking



## 3M™ Value Masking Tape 101+



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 150°F (66°C)

**Tensile Strength:** 22 lb/in (38.5 N/cm)

**Adhesion to Steel:** 34 oz/in (3.7 N/cm)


**Elongation:** 9%

**Thickness:** 0.13 mm (5.1 mil)

**Applications:** Intended for light-duty indoor use, ideal for marking, temporary holding, wrapping, sealing and masking.

Sticks instantly to paper, metal, wood, plastic, glass and many other clean surfaces.

## 3M™ General Use Masking Tape 201+



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 200°F (93°C)

**Tensile Strength:** 19 lb/in (33.3 N/cm)

**Adhesion to Steel:** 25 oz/in (2.7 N/cm)


**Elongation:** 8%

**Thickness:** 0.11 mm (4.4 mil)

**Applications:** Intended for light- to medium-duty indoor use, ideal for wrapping electrical cords, air hoses and PVC pipes as well as masking and labeling.

Can be used on a variety of surfaces such as wood, plastic, glass, metal and painted surfaces.

Removes cleanly for up to 24 hours indoors.





# General Purpose Paint Masking



## 3M™ General Purpose Masking Tape 203



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 200°F (93°C)

**Tensile Strength:** 22 lb/in (38.6 N/cm)

**Adhesion to Steel:** 29 oz/in (3.2 N/cm)

**Elongation:** 9%

**Thickness:** 0.12 mm (4.9 mil)

**Applications:** Bundling cords, hanging poly drapes, attaching production notes and masking for routine maintenance painting.



## 3M™ Masking Tape 2307



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 200°F (93°C)

**Tensile Strength:** 23 lb/in (40.3 N/cm)

**Adhesion to Steel:** 28 oz/in (3.1 N/cm)

**Elongation:** 8%

**Thickness:** 0.13 mm (5.2 mil)

**Applications:** Ideal for woodworking and general paint masking as well as other applications like tabbing, splicing, bundling and holding.

Provides excellent holding power and good paint hold-out that resists bleed through.





# Outdoor Masking

## Scotch® Solvent Resistant Masking Tape 226

**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 225°F (107°C)

**Tensile Strength:** 34 lb/in (59.5 N/cm)

**Adhesion to Steel:** 38 oz/in (4.2 N/cm)

**Elongation:** 11%

**Thickness:** 0.27 mm (10.6 mil)

**Applications:** Recommended for sealing and protection of metal, plastic and painted surfaces as well as masking operations involving solvent and water-based solutions.

Provides excellent chemical resistance and removes cleanly from most opaque surfaces for up to three months of outdoor exposure.



## Scotch® Weather Resistant Masking Tape 225

**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 200°F (93°C)

**Tensile Strength:** 21 lb/in (36.8 N/cm)


**Adhesion to Steel:** 33 oz/in (3.6 N/cm)

**Elongation:** 9%

**Thickness:** 0.15 mm (5.8 mil)

**Applications:** Designed for outdoor applications including, paint masking, surface protection and temporary holding.

Offers UV, solvent and moisture resistance and can be removed cleanly for up to one month outdoors.



## Scotch® Ultimate Paint Edge Masking Tape 2460

**Adhesive Type:** Acrylic

**Maximum Operating Temperature:** 300°F (149°C)

**Tensile Strength:** 18 lb/in (31.5 N/cm)

**Adhesion to Steel:** 8 oz/in (0.9 N/cm)

**Elongation:** 6%

**Thickness:** 0.08 mm (3.3 mil)

**Applications:** Excellent for creating sharp, smooth paint lines.

Recommended for masking straight lines with solvent or latex based paints as well as surface protection, identification and holding during construction.

UV resistant for outdoor use up to 21 days.










# High Temp Masking Tape



► **Tapes you can count on when it really matters.**

Designed to perform when you need it most.

Built to perform during high temperature paint curing cycles to help produce crisp, clean paint lines every time.

Available in a variety of backing and adhesive combinations, there's a high temperature tape for any task.

**Find the right tape that can handle the heat.**



225°F



**3M™ Performance  
Masking Tape 301+**



**Adhesive Type:** Rubber

**Maximum Operating Temperature:**  
225°F (107°C)

**Tensile Strength:**  
20 lb/in (35 N/cm)

**Adhesion to Steel:** 33 oz/in (3.6 N/cm)

**Elongation:** 11%

**Thickness:** 0.14 mm (5.4 mil)

**Applications:** Sticks confidently to most surfaces while removing cleanly and ideal for paint masking applications.





# 250°F



## 3M™ General Purpose Masking Tape 234



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 250°F (121°C)

**Tensile Strength:** 30 lb/in (52.5 N/cm)

**Adhesion to Steel:** 32 oz/in (3.5 N/cm)

**Elongation:** 10%

**Thickness:** 0.15 mm (5.9 mil)

**Applications:** Offers instant adhesion and withstands paint bake operations up to 250°F (121°C) for 30 minutes.

Manufactured without solvents.

## 3M™ High Performance Green Masking Tape 401+



**Adhesive Type:**

Natural/Synthetic Rubber Blend

**Maximum Operating Temperature:** 250°F (121°C)

**Tensile Strength:** 24 lb/in (42 N/cm)

**Adhesion to Steel:** 35 oz/in (3.8 N/cm)

**Elongation:** 14%

**Thickness:** 0.16 mm (6.4 mil)

**Applications:** Ideal for high-temperature paint baking and resists paint bleed through for sharp paint lines.

Stays in place around corners and sticks to irregular surfaces.



## 3M™ Masking Tape 2308



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 250°F (121°C)

**Tensile Strength:** 22 lb/in (40.2 N/cm)

**Adhesion to Steel:** 32 oz/in (3.5 N/cm)

**Elongation:** 10%

**Thickness:** 0.12 mm (4.9 mil)

**Applications:** Designed to deliver clean paint lines, while removing easily and cleanly without any leftover residue.



## 3M™ High Performance Masking Tape 232



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 250°F (121°C)

**Tensile Strength:** 30 lb/in (52.5 N/cm)

**Adhesion to Steel:** 37 oz/in (4.1 N/cm)

**Elongation:** 10%


**Thickness:** 0.16 mm (6.3 mil)

**Applications:** Designed to provide clean paint lines while protecting surrounding surfaces from over-spray.





# 300°F



## 3M™ Specialty High Temperature Masking Tape 501+



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 300°F (149°C)

**Tensile Strength:** 31 lb/in (54.3 N/cm)

**Adhesion to Steel:** 37 oz/in (4 N/cm)

**Elongation:** 11%

**Thickness:** 0.185 mm (7.3 mil)

**Applications:** Sticks securely through multiple or extended process cycles and up to 300°F (149°C) for 30 minutes.

Great Versatility

## 3M™ Performance Masking Tape 2364



**Adhesive Type:**

Natural/Synthetic Rubber Blend

**Maximum Operating Temperature:** 300°F (149°C)

**Tensile Strength:** 24 lb/in (42 N/cm)

**Adhesion to Steel:** 31 oz/in (3.4 N/cm)

**Elongation:** 10%

**Thickness:** 0.165 mm (6.5 mil)

**Applications:** Easy to tear, removes cleanly and can withstand up to 300°F (149°C) masking operations while still having good adhesion.

Good for Oil and Gas

Thinnest Option

## 3M™ Paint Masking Tape 231/231A



**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 300°F (149°C)

**Tensile Strength:** 28 lb/in (49 N/cm)

**Adhesion to Steel:** 38 oz/in (4.1 N/cm)

**Elongation:** 10%

**Thickness:** 0.19 mm (7.6 mil)

**Applications:** Removes cleanly from many surfaces, even after multi-bake or high temperature bake.

Designed to meet aerospace demands levels of strength and reliability.

Good for Aerospace





# 325°F



## 3M™ Performance Masking Tape 2380

**Adhesive Type:**

Natural/Synthetic Rubber Blend

**Maximum Operating Temperature:**

325°F (163°C)

**Tensile Strength:**

28 lb/in (49 N/cm)

**Adhesion to Steel:** 39 oz/in (4.3 N/cm)**Elongation:** 10%**Thickness:** 0.182 mm (7.2 mil)

**Applications:** An essential for producing precise paint lines and can withstand bake temperatures of up to 325°F (163°C) for 30 minutes while removing cleanly.

Highly versatile with strong adhesion and reliable holding power.

Smooth Crepe Backing

High Holding Power

## 3M™ High Performance Masking Tape 2693

**Adhesive Type:** Rubber**Maximum Operating Temperature:**

325°F (163°C)

**Tensile Strength:**

29 lb/in (50.8 N/cm)

**Adhesion to Steel:** 40 oz/in (4.4 N/cm)**Elongation:** 10%**Thickness:** 0.2 mm (7.9 mil)

**Applications:** Offers great paint masking performance with high solid paint and urethane clear coats while removing cleanly. Offers the highest holding power among 3M masking tapes.

Great for AOEM



# 350°F



## Scotch® High Performance Masking Tape 213

**Adhesive Type:** Rubber**Maximum Operating Temperature:**

350°F (177°C)

**Tensile Strength:**

27 lb/in (47.3 N/cm)

**Adhesion to Steel:** 34 oz/in (3.7 N/cm)**Elongation:** 10%**Thickness:** 0.152 mm (6 mil)

**Applications:** Bonds and removes cleanly from even the most challenging surfaces and is designed to deliver reliability when exposed to high temperatures.

Better Adhesion

## Scotch® High Temperature Masking Tape 214

**Adhesive Type:** Rubber**Maximum Operating Temperature:**

350°F (177°C)

**Tensile Strength:**

27 lb/in (47.3 N/cm)

**Adhesion to Steel:** 29 oz/in (3.2 N/cm)**Elongation:** 10%**Thickness:** 0.14 mm (5.5 mil)


**Applications:** Designed specifically for use on metals without leaving behind stains. Offers one-piece removal while resisting lifting and curling.

Good for Copper and Precious Metals





# Fine Line Masking Tape



► **Tapes that make the sharpest paint lines.**

In order to create sharp paint lines, you need a tape that has the flexibility to create both smooth curved lines or long straight lines. The Scotch® lineup of fine line tapes offers a solution for all applications while still removing easily and cleanly at a variety of temperature ranges.

**Choose a tape that keeps lines sharp.**



# Fine Line Masking Tape

## Scotch® Fine Line Tape 218

**Adhesive Type:** Rubber

**Maximum Operating Temperature:** 250°F (121°C)

**Tensile Strength:** 13 lb/in (22.8 N/cm)

**Adhesion to Steel:** 37 oz/in (4 N/cm)

**Elongation:** 720%

**Thickness:** 0.13 mm (5 mil)

**Applications:** A high adhesion tape that has a stiffer backing than vinyl tapes with a low-profile.

Ideal for long, crisp paint lines while conforming easily around corners.



Good for Straight Lines

Solvent Resistant

## Scotch® Fine Line Masking Tape 265

**Adhesive Type:** Silicone-Rubber

**Maximum Operating Temperature:** 200°F (93°C)

**Tensile Strength:** 21 lb/in (36.8 N/cm)


**Adhesion to Steel:** 21 oz/in (2.3 N/cm)

**Elongation:** 881%

**Thickness:** 0.13 mm (5.1 mil)

**Applications:** Ideal for gel coat color paint-separation for in-mold fine line masking.

For difficult to stick to surfaces, such as semi-perm mold release surfaces.



Great for Gel Coat

## Scotch® Fine Line Masking Tape 2800

**Adhesive Type:** Acrylic

**Maximum Operating Temperature:** 300°F (149°C)

**Tensile Strength:** 25 lb/in (43 N/cm)


**Adhesion to Steel:** 16 oz/in (1.75 N/cm)

**Elongation:** 1000%

**Thickness:** 0.105 mm (4.1 mil)

**Applications:** Designed specifically for thermoplastic olefin surfaces as an alternative for adhesive tapes in paint systems prone to residue, tape tracking and ghosting by rubber adhesive tapes.

Features a translucent backing to assist with placement.



7 day outdoor clean removal

Good for TPO Masking



### Scotch® High Temperature Fine Line Tape 4735/L

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 14 lb/in (24.5 N/cm)  
**Adhesion to Steel:** 9.5 oz/in (1 N/cm)  
**Elongation:** 130%  
**Thickness:** 0.137 mm (5.4 mil)  
**Applications:** Ideal for achieving excellent color line separation in high-temperature paint processes as high as 300°F for up to 30 minutes for fascia panels, two-tone and other multiple color applications where critical paint break lines are required.



### Scotch® High Temperature Fine Line Tape 4737T/TL

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 16 lb/in (28 N/cm)  
**Adhesion to Steel:** 15 oz/in (1.6 N/cm)  
**Elongation:** 75%  
**Thickness:** 0.13 mm (5.1 mil)  
**Applications:** The adhesive and backing work together to minimize paint seepage, while the translucent backing allows visual confirmation of adhesive wet out on the lower layer.  
 Designed for die-cutting and stencils, this natural rubber adhesive tape delivers sharp color separation during painting and lays flat despite changes in humidity.



### Scotch® High Temperature Fine Line Tape 4737S/4737SL

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 16 lb/in (28 N/cm)  
**Adhesion to Steel:** 15 oz/in (1.6 N/cm)  
**Elongation:** 75%  
**Thickness:** 0.13 mm (5.1 mil)  
**Applications:** Ideal for working with complex shapes and curved surfaces, it's specially developed backing allows it to resist lifting and withstand bake cycles with temperatures of 300°F for 30 minutes. Features a die-cuttable poly-coated kraft liner that makes it capable of laying flat despite changes in humidity. Ideal for paint masking and high temperature paint processes.





# Duct Tape



► **Tapes that are built to stick.**

Duct tapes were initially designed to work in the HVAC industry, so you know they're built for heavy duty settings.

Today, they are used for a variety of industrial, maintenance, repair and construction applications.

These tapes adhere to most surfaces and are available in a variety of colors and strengths to help you accomplish your goals.

**Find a tape that's as versatile as your tasks.**



# Utility



## 3M™ All Purpose Duct Tape DT8



**Adhesive Type:** Synthetic/Natural Rubber Blend  
**Maximum Operating Temperature:** 150°F (66°C)  
**Tensile Strength:** 24 lb/in (42 N/cm)  
**Adhesion to Steel:** 74 oz/in (8.1 N/cm)  
**Elongation:** 19%  
**Thickness:** 0.2 mm (8 mil)  
**Applications:** Poly abatement, quick repairs, splicing, labeling, temporary holding and fast attachments.

## 3M™ Value Duct Tape 1900



**Adhesive Type:** Synthetic Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 19 lb/in (33 N/cm)  
**Adhesion to Steel:** 62 oz/in (6.8 N/cm)  
**Elongation:** 15%  
**Thickness:** 0.147 mm (5.8 mil)  
**Applications:** Thin duct tape with a moisture-resistant backing, great for light-duty and simple tasks. Easily tears by hand and sticks well to many surfaces.

## 3M™ Multi-Purpose Duct Tape 3900



**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 28 lb/in (49 N/cm)  
**Adhesion to Steel:** 53 oz/in (5.8 N/cm)  
**Elongation:** 19%  
**Thickness:** 0.19 mm (7.6 mil)  
**Applications:** Visual marking, labeling and temporary repairs.  
 Good for moist and humid environments.

Available in Multiple Colors

## 3M™ Vinyl Duct Tape 3903




**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 14.5 lb/in (25.3 N/cm)  
**Adhesion to Steel:** 15.4 oz/in (1.7 N/cm)  
**Elongation:** 134%  
**Thickness:** 0.19 mm (7.3 mil)  
**Applications:** Color-coding, identifying trip hazards and securing wires.  
 The embossed vinyl backing seals out dust, dirt and moisture and removes cleanly after 30 minutes in temperatures as high as 200°F (93°C).

Available in Multiple Colors

Embossed Vinyl Backing



# Heavy Duty



## 3M™ Heavy Duty Duct Tape DT11



3M  
Choice

**Adhesive Type:**

Synthetic/Natural Rubber Blend

**Maximum Operating Temperature:**

150°F (66°C)

**Tensile Strength:**

29 lb/in (50.8 N/cm)

**Adhesion to Steel:** 88 oz/in (9.6 N/cm)

**Elongation:** 19%

**Thickness:** 0.27 mm (11 mil)

**Applications:** Securing temporary flooring, pipe sealing, hanging heavy poly drapes and reinforcing.

Balanced  
Construction

## 3M™ Super Duty Duct Tape DT17



**Adhesive Type:**

Synthetic/Natural Rubber Blend

**Maximum Operating Temperature:**

150°F (66°C)

**Tensile Strength:**

38 lb/in (66.5 N/cm)

**Adhesion to Steel:** 85 oz/in (9.3 N/cm)

**Elongation:** 18%

**Thickness:** 0.43 mm (17 mil)

**Applications:** Excellent for repairing, seaming, extra-strength bundling and protecting metal parts and surfaces from sandblast over-spray.

High  
Abrasion  
Resistance

## 3M™ Heavy Duty Duct Tape 3939



**Adhesive Type:** Rubber

**Maximum Operating Temperature:**

200°F (93°C)

**Tensile Strength:**

27 lb/in (47.3 N/cm)

**Adhesion to Steel:** 58 oz/in (6.3 N/cm)

**Elongation:** 17%

**Thickness:** 0.22 mm (8.6 mil)

**Applications:** Ideal for use in maintenance, repair and construction applications.

Removes cleanly for up to one month from many opaque, non-glass surfaces when applied indoors.

## 3M™ Extra Heavy Duty Duct Tape 6969



**Adhesive Type:** Rubber

**Maximum Operating Temperature:**

200°F (93°C)

**Tensile Strength:**

34 lb/in (59.5 N/cm)

**Adhesion to Steel:** 51 oz/in (5.6 N/cm)


**Elongation:** 16%

**Thickness:** 0.25 mm (10 mil)

**Applications:** Heavy duty solution for maintenance, repair and construction.



# Clean Removal



## 3M™ Performance Plus Duct Tape 8979



**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 36.5 lb/in (64 N/cm)  
**Adhesion to Steel:** 57 oz/in (6.2 N/cm)  
**Elongation:** 17%  
**Thickness:** 0.29 mm (11.5 mil)  
**Applications:** An outdoor, UV-tolerant tape that removes cleanly for up to six months. Sticks immediately and stays on for up to one year with a strong water-resistant backing.

6 month outdoor clean removal

UV resistant

Last Up to 1 Year

## 3M™ Performance Plus Duct Tape 8979N\*



**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 36 lb/in (63 N/cm)  
**Adhesion to Steel:** 48 oz/in (5.3 N/cm)  
**Elongation:** 19%  
**Thickness:** 0.3 mm (11.7 mil)  
**Applications:** Specialized tape ideal for demanding applications like sealing, holding and protection. Resists wear, abrasion, moisture and UV exposure for up to 12 months.

\*MIL-STD-2041E Compliant

## 3M™ Outdoor Masking and Stucco Tape 5959



**Adhesive Type:** Natural/Synthetic Rubber Blend  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 36 lb/in (63 N/cm)  
**Adhesion to Steel:** 57 oz/in (6.2 N/cm)  
**Elongation:** 16%  
**Thickness:** 0.28 mm (11 mil)  
**Applications:** Designed for outdoor use and removes cleanly for up to three months. Sticks instantly and stays on without deterioration for up to one year.

3 month outdoor clean removal

UV resistant

Last Up to 1 Year

## 3M™ Outdoor Masking Poly Tape 5903



**Adhesive Type:** Synthetic Rubber  
**Maximum Operating Temperature:** 173°F (78°C)  
**Tensile Strength:** 21 lb/in (36.8 N/cm)  
**Adhesion to Steel:** 79 oz/in (8.7 N/cm)  
**Elongation:** 72%  
**Thickness:** 0.19 mm (7.5 mil)  
**Applications:** Ideal for permanent and temporary applications. Resists curling and sticks immediately while conforming to irregular surfaces without lifting off.

1 month outdoor clean removal

UV resistant







# Masking Film



► **Achieve a quality paint finish in less time.**

Available with a range of features and options to help you stay efficient when quality painting really matters.

The films are easy to apply over large areas, which speeds up the masking and clean-up portions of the painting process to increase efficiency.

Not only do they resist bleed through and seal against solvents, enamels, paint and lacquers, they're also designed to work with your 3M masking tapes for a dynamic duo painting solution.

**Find a film that will keep you covered,  
even when the heat is on.**




# Masking Film



## 3M™ High Temperature Paint Masking Film 7300




**Backing:** Polypropylene Film  
**Maximum Operating Temperature:** 310°F (155°C)  
**Tensile Strength Machine Direction:** 118 oz/in (13 N/cm)  
**Tensile Strength Cross Direction:** N/A  
**Elongation Machine Direction:** 680%  
**Elongation Cross Direction:** 680%  
**Thickness:** 0.086 mm (3.4 mil)  
**Applications:** Designed to protect in paint applications, especially in temperatures as high as 310°F (155°C) for an hour.  
 Ideal for situations where paint and solvents might bleed through.



## 3M™ High Temperature Protective Bags and Sheets 7260M




**Backing:** Soft Polypropylene Film  
**Maximum Operating Temperature:** 315°F (157°C)  
**Tensile Strength Machine Direction:** 120 oz/in (13 N/cm)  
**Tensile Strength Cross Direction:** 80 oz/in (8.8 N/cm)  
**Elongation Machine Direction:** 700%  
**Elongation Cross Direction:** 700%  
**Thickness:** 0.0457 mm (1.8 mil)  
**Applications:** Applies quickly and handles large surfaces easily. Available in bags, perforated sheets or non-perforated sheeting.



## 3M™ High Temperature Paint Masking Film 7302




**Backing:** Laminated Polymer  
**Maximum Operating Temperature:** 320°F (160°C)  
**Tensile Strength Machine Direction:** 90 oz/in (10 N/cm)  
**Tensile Strength Cross Direction:** 60 oz/in (6.5 N/cm)  
**Elongation Machine Direction:** 400%  
**Elongation Cross Direction:** 500%  
**Thickness:** 0.03 mm (1.2 mil)  
**Applications:** Ideal for use during high temperature paint curing cycles and can withstand temperatures of up to 320°F (160°C).  
 Available in continuous sheeting and bags.



## 3M™ Ultra High Temperature Paint Masking Film 7305



**Backing:** Laminated Polymer  
**Maximum Operating Temperature:** 356°F (180°C)  
**Tensile Strength Machine Direction:** 95.9 oz/in (10.5 N/cm)  
**Tensile Strength Cross Direction:** 68.5 oz/in (7.5 N/cm)  
**Elongation Machine Direction:** 200%  
**Elongation Cross Direction:** 300%  
**Thickness:** 0.03 mm (1.2 mil)  
**Applications:** Easily conforms to surfaces and is designed to protect through cure cycles of up to 356°F (180°C).







# Flatback



- ▶ **Quick and efficient to meet the demands of high-volume industries.**

3M designed a series of flatback tapes that feature a combination of smooth paper backing and controlled unwind to provide optimal performance for large-scale jobs.

If you're in need of temperature and moisture resistance, as well as easy handling, there's a flatback tape that will quickly become your go-to solution.

**Choose the right flatback that helps get the job done on time.**




# Utility



## 3M™ Flatback Tape 2517

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 35 lb/in (54.3 N/cm)  
**Adhesion to Steel:** 78 oz/in (8.5 N/cm)  
**Elongation:** 2%  
**Thickness:** 0.16 mm (6.5 mil)  
**Applications:** General purpose flatback for most web processing and splicing applications.  
 Can withstand a bake cycle up to 300°F (149°C) for up to 30 minutes.



## 3M™ High Performance Flatback Tape 2519

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 47 lb/in (82.3 N/cm)  
**Adhesion to Steel:** 47 oz/in (5.1 N/cm)  
**Elongation:** 8%  
**Thickness:** 0.18 mm (7.1 mil)  
**Applications:** Ideal for seaming of temporary floor protection, roll starting, roll closing, general purpose splicing, bundling and packaging.  
 The kraft paper backing combines strength and moisture resistance and can withstand temperatures of up to 200°F (93°C).



## 3M™ Flatback Tape 2515


**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 150°F (65°C)  
**Tensile Strength:** 40 lb/in (70 N/cm)  
**Adhesion to Steel:** 54 oz/in (5.9 N/cm)  
**Elongation:** 9.5%  
**Thickness:** 0.16 mm (6.4 mil)  
**Applications:** Good for low heat, web-processing and general purpose packaging.







# Specialty



## Scotch® Flatback Masking Tape 250

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 125°F (52°C)  
**Tensile Strength:** 61 lb/in (107 N/cm)  
**Adhesion to Steel:** 84 oz/in (9.2 N/cm)  
**Elongation:** 4%  
**Thickness:** 0.15 mm (5.9 mil)  
**Applications:** Recommended for paint adhesion testing.  
 Removes cleanly from paint, plating and powder coatings.




## Scotch® Printable Flatback Paper Tape 256

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 200°F (93°C)  
**Tensile Strength:** 32 lb/in (56 N/cm)  
**Adhesion to Steel:** 35 oz/in (3.8 N/cm)  
**Elongation:** 3.5%  
**Thickness:** 0.12 mm (4.8 mil)  
**Applications:** Printable with standard flexographic inks and easily marked with ball point pens, pencils and rubber stamps.  
 Specifically designed for operations requiring multiple colors of identification or marking.  
 Works best on papers, films, fabric and yarn.




## 3M™ Textile Flatback Tape 2526

**Adhesive Type:** Natural Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 50 lb/in (85.8 N/cm)  
**Adhesion to Steel:** 69 oz/in (7.5 N/cm)  
**Elongation:** 4%  
**Thickness:** 0.242 mm (9.8 mil)  
**Applications:** Ideal for rolling and bundling heavy textiles as well as other hard to stick materials.  
 Resistant to moisture and can withstand temperatures of 300°F (149°C) for up to 30 minutes.



## 3M™ Performance Flatback Tape 2525

**Adhesive Type:** Rubber  
**Maximum Operating Temperature:** 300°F (149°C)  
**Tensile Strength:** 49 lb/in (85.8 N/cm)  
**Adhesion to Steel:** 69 oz/in (7.5 N/cm)  
**Elongation:** 2%  
**Thickness:** 0.241 mm (9.5 mil)  
**Applications:** Ideal for high temperature splicing operations as well as temporary surface protection.  
 Bright orange color allows for improved visibility.  
 Can withstand bake cycles up to 300°F (149°C) for up to one hour.



# Product Attributes/Features

## General Purpose Masking Tape

### Utility

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
101+	Rubber	5.1 mil (0.13 mm)	150°F (66°C)	22 lb/in (38.6 N/cm)	34 oz/in (3.7 N/cm)	9%	N/A
201+	Rubber	4.4 mil (0.11 mm)	200°F (93°C)	19 lb/in (33.3 N/cm)	25 oz/in (2.7 N/cm)	8%	N/A
2214	Rubber	4.9 mil (0.12 mm)	200°F (93°C)	17 lb/in (29.8 N/cm)	25 oz/in (2.7 N/cm)	8%	N/A

### General Purpose Painting

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
203	Rubber	4.7 mil (0.12 mm)	200°F (93°C)	22 lb/in (38.5 N/cm)	29 oz/in (3.2 N/cm)	8%	3 day clean removal
2307	Rubber	5.2 mil (0.13 mm)	200°F (93°C)	23 lb/in (40.3 N/cm)	28 oz/in (3.1 N/cm)	8%	N/A
2510	Rubber	5.6 mil (0.14 mm)	200°F (93°C)	20 lb/in (35 N/cm)	35 oz/in (3.7 N/cm)	9%	N/A

### Outdoor

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
2460	Acrylic	3.3 mil (0.08 mm)	300°F (149°C)	18 lb/in (31.5 N/cm)	8 oz/in (0.9 N/cm)	6%	21 days outdoor clean removal
226	Rubber	10.6 mil (0.27 mm)	225°F (107°C)	34 lb/in (59.5 N/cm)	38 oz/in (4.2 N/cm)	11%	N/A
225	Rubber	5.8 mil (0.15 mm)	200°F (93°C)	21 lb/in (36.8 N/cm)	33 oz/in (3.6 N/cm)	9%	1 Month weather resistance

## High Temp Masking Tape

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
301+	Rubber	5.4 mil (0.14 mm)	225°F (107°C)	20 lb/in (35 N/cm)	33 oz/in (3.6 N/cm)	11%	N/A
401+	Natural/Synthetic Rubber Blend	6.4 mil (0.16 mm)	250°F (121°C)	24 lb/in (42 N/cm)	35 oz/in (3.8 N/cm)	14%	N/A
501+	Rubber	7.3 mil (0.185 mm)	300°F (149°C)	31 lb/in (54.3 N/cm)	37 oz/in (4 N/cm)	11%	N/A
2380	Natural/Synthetic Rubber Blend	7.2 mil (0.182 mm)	325°F (163°C)	28 lb/in (49 N/cm)	39 oz/in (4.3 N/cm)	10%	N/A
213	Rubber	6 mil (0.152 mm)	350°F (177°C)	27 lb/in (47.3 N/cm)	34 oz/in (3.7 N/cm)	10%	N/A
226	Rubber	10.6 mil (0.27 mm)	225°F (107°C)	34 lb/in (59.5 N/cm)	38 oz/in (4.2 N/cm)	11%	N/A
234	Rubber	5.9 mil (0.15 mm)	250°F (121°C)	30 lb/in (52.5 N/cm)	32 oz/in (3.5 N/cm)	10%	N/A
232	Rubber	6.3 mil (0.16 mm)	250°F (121°C)	30 lb/in (52.5 N/cm)	37 oz/in (4.1 N/cm)	10%	N/A
202	Rubber	6.3 mil (0.16 mm)	250°F (121°C)	30 lb/in (52.5 N/cm)	37 oz/in (4.1 N/cm)	10%	N/A
2308	Rubber	4.9 mil (0.12 mm)	250°F (121°C)	22 lb/in (40.2 N/cm)	32 oz/in (3.5 N/cm)	10%	N/A
231/231A	Rubber	7.6 mil (0.19 mm)	300°F (149°C)	28 lb/in (49 N/cm)	38 oz/in (4.1 N/cm)	10%	N/A
2364	Natural/Synthetic Rubber Blend	6.5 mil (0.165 mm)	300°F (149°C)	24 lb/in (42 N/cm)	31 oz/in (3.4 N/cm)	10%	N/A
2460	Acrylic	3.3 mil (0.08 mm)	300°F (149°C)	18 lb/in (31.5 N/cm)	8 oz/in (0.9 N/cm)	6%	N/A
EXPP	Acrylic	3.5 mil (0.09 mm)	300°F (149°C)	19 lb/in (34 N/cm)	11 oz/in (1.2 N/cm)	10%	N/A
2693	Synthetic Rubber	7.9 mil (0.2 mm)	325°F (163°C)	29 lb/in (50.8 N/cm)	40 oz/in (4.4 N/cm)	10%	N/A
2393	Rubber	7.6 mil (0.185 mm)	325°F (163°C)	28 lb/in (49 N/cm)	32 oz/in (3.6 N/cm)	11%	N/A
214	Rubber	5.5 mil (0.14 mm)	350°F (177°C)	27 lb/in (47.3 N/cm)	29 oz/in (3.2 N/cm)	10%	N/A

## Fine Line Masking Tape

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
218	Rubber	5 mil (0.13 mm)	250°F (121°C)	13 lb/in (22.8 N/cm)	37 oz/in (4 N/cm)	720%	N/A
4737TL	Rubber	5.1 mil (0.13 mm)	300°F (149°C)	256 lb/in (28 N/cm)	26 oz/in (2.8 N/cm)	75%	N/A
215	Rubber	4.8 mil (0.12 mm)	250°F (121°C)	15 lb/in (26.3 N/cm)	43 oz/in (4.7 N/cm)	1150%	N/A
4737T	Rubber	5.1 mil (0.13 mm)	300°F (149°C)	16 lb/in (28 N/cm)	15 oz/in (1.6 N/cm)	75%	N/A
265	Silicone-Rubber	5.1 mil (0.13 mm)	200°F (93°C)	21 lb/in (36.8 N/cm)	21 oz/in (2.3 N/cm)	881%	N/A
2800	Acrylic	4.1 mil (0.105 mm)	300°F (149°C)	25 lb/in (43 N/cm)	16 oz/in (1.75 N/cm)	1000%	N/A
4735L	Rubber	5.4 mil (0.137 mm)	300°F (149°C)	14 lb/in (24.5 N/cm)	16 oz/in (1.7 N/cm)	130%	N/A
4737SL	Rubber	5.1 mil (0.13 mm)	300°F (149°C)	14 lb/in (24.5 N/100mm)	15 oz/in (1.6 N/cm)	75%	N/A
4735	Rubber	5.4 mil (0.137 mm)	300°F (149°C)	14 lb/in (24.5 N/cm)	9.5 oz/in (1 N/cm)	130%	N/A

## Duct Tape

### Utility

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
DT8	Synthetic/ Natural Rubber Blend	8 mil (0.2 mm)	150°F (65.5°C)	24 lb/in (42 N/cm)	74 oz/in (8.1 N/cm)	19%	N/A
1900	Synthetic Rubber	5.8 mil (0.147 mm)	200°F (93°C)	19 lb/in (33 N/cm)	62 oz/in (6.8 N/cm)	15%	N/A
3900	Rubber	7.6 mil (0.19 mm)	200°F (93°C)	28 lb/in (49 N/cm)	53 oz/in (5.8 N/cm)	19%	N/A
3903	Rubber	7.3 mil (0.19 mm)	200°F (93°C)	14.5 lb/in (25.3 N/cm)	15.4 oz/in (1.7 N/cm)	134%	N/A

### Heavy Duty

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
DT11	Synthetic/ Natural Rubber Blend	11 mil (0.27 mm)	150°F (65.5°C)	29 lb/in (50.8 N/cm)	88 oz/in (9.6 N/cm)	19%	N/A
DT17	Synthetic/ Natural Rubber Blend	17 mil (0.43 mm)	150°F (65.5°C)	38 lb/in (66.5 N/cm)	85 oz/in (9.3 N/cm)	18%	N/A
3939	Rubber	8.6 mil (0.22 mm)	200°F (93°C)	27 lb/in (47.3 N/cm)	58 oz/in (6.3 N/cm)	17%	N/A
6969	Rubber	10 mil (0.25 mm)	200°F (93°C)	34 lb/in (59.5 N/cm)	51 oz/in (5.6 N/cm)	16%	N/A

### Clean Removal

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
8979	Rubber	11.5 mil (0.29 mm)	200°F (93°C)	36.5 lb/in (64 N/cm)	57 oz/in (6.2 N/cm)	17%	6 month Clean Removal
8979N	Rubber	11.7 mil (0.3 mm)	200°F (93°C)	36 lb/in (63 N/cm)	48 oz/in (5.3 N/cm)	19%	6 month Clean Removal
5959	Natural/ Synthetic Rubber Blend	11 mil (0.28 mm)	200°F (93°C)	36 lb/in (63 N/cm)	57 oz/in (6.2 N/cm)	16%	3 month weather resistance
5903	Synthetic Rubber	7.5 mil (0.19 mm)	173°F (78°C)	21 lb/in (36.8 N/cm)	79 oz/in (8.7 N/cm)	72%	1 month weather resistance

### Gaffers Tape

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
GT1	Synthetic Rubber	11 mil (0.27 mm)	200°F (93°C)	896 oz/in (98.1 N/100 mm)	72 oz/in (7.9 N/cm)	6%	N/A

# Product Attributes/Features

## Masking Film

### Utility

Product	Backing	Thickness	Max Operating Temperature	Tensile Strength Machine Direction	Tensile Strength Cross Direction	Elongation Machine Direction	Elongation Cross Direction	Clean Removability
7300	Polypropylene Film	3.4 mil (0.086 mm)	310°F (155°C)	118 oz/in (13 N/cm)	N/A	9%	9%	N/A
7260M	Soft Polypropylene Film	1.8 mil (0.0457 mm)	315°F (157°C)	120 oz/in (13 N/cm)	80 oz/in (8.8 N/cm)	8%	8%	N/A
7302	Laminated polymer	1.2 mil (0.03 mm)	320°F (160°C)	90 oz/in (10 N/cm)	60 oz/in (6.5 N/cm)	8%	8%	N/A
7305	Laminated polymer	1.2 mil (0.03 mm)	356°F (180°C)	95.9 oz/in (10.5 N/cm)	68.5 oz/in (7.5 N/cm)	8%	8%	N/A

## Flatback

### Utility

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
2517	Rubber	6.5 mil (0.16 mm)	300°F (149°C)	35 lb/in (54.3 N/cm)	78 oz/in (8.5 N/cm)	2%	N/A
2519	Rubber	7.1 mil (0.18 mm)	200°F (93°C)	47 lb/in (82.3 N/cm)	47 oz/in (5.1 N/cm)	8%	N/A

### Specialty

Product	Adhesive Type	Thickness	Max Operating Temperature	Tensile Strength	Adhesion to Steel	Elongation	Clean Removability
250	Rubber	5.9 mil (0.15 mm)	125°F (52°C)	61 lb/in (107 N/cm)	84 oz/in (9.2 N/cm)	4%	N/A
256	Rubber	4.8 mil (0.12 mm)	200°F (93°C)	32 lb/in (56 N/cm)	35 oz/in (3.8 N/cm)	3.5%	N/A
2526	Natural Rubber	9.8 mil (0.242 mm)	300°F (149°C)	50 lb/in (85.8 N/cm)	69 oz/in (7.5 N/cm)	4%	N/A
2525	Rubber	9.5 mil (0.241 mm)	300°F (149°C)	49 lb/in (85.8 N/cm)	69 oz/in (7.5 N/cm)	2%	N/A

# Detailed Product list

## General Purpose Masking Tape

UPC	3M ID	Product	Stocked or MTO
<b>Utility</b>			
00689330205400	7100242374	3M™ Value Masking Tape 101+, Tan, 12 mm x 55 m, 5.1 mil, 72 Roll/per case	Stocked
00689330205431	7100242375	3M™ Value Masking Tape 101+, Tan, 18 mm x 55 m, 5.1 mil, 48 Roll/per case	Stocked
00689330205448	7100242376	3M™ Value Masking Tape 101+, Tan, 24 mm x 55 m, 5.1 mil, 36 Roll/per case	Stocked
00689330205455	7100242377	3M™ Value Masking Tape 101+, Tan, 36 mm x 55 m, 5.1 mil, 24 Roll/per case	Stocked
00689330205462	7100242378	3M™ Value Masking Tape 101+, Tan, 48 mm x 55 m, 5.1 mil, 24 Roll/per case	Stocked
00689330205479	7100242379	3M™ Value Masking Tape 101+, Tan, 72 mm x 55 m, 5.1 mil, 12 Roll/per case	Stocked
00689330205486	7100242380	3M™ Value Masking Tape 101+, Tan, 96 mm x 55 m, 5.1 mil, 8 Roll/per case	Stocked
00051115647383	7000124879	3M™ General Use Masking Tape 201+, Tan, 12 mm x 55 m, 4.4 mil, 72 per case	Stocked
00051115647390	7000124880	3M™ General Use Masking Tape 201+, Tan, 18 mm x 55 m, 4.4 mil, 48 per case	Stocked
00051115647406	7000144751	3M™ General Use Masking Tape 201+, Tan, 24 mm x 55 m, 4.4 mil, 36 per case	Stocked
00051115647413	7000124882	3M™ General Use Masking Tape 201+, Tan, 36 mm x 55 m, 4.4 mil, 24 per case	Stocked
00051115647420	7000144752	3M™ General Use Masking Tape 201+, Tan, 48 mm x 55 m, 4.4 mil, 24 per case	Stocked
00051115647437	7000124884	3M™ General Use Masking Tape 201+, Tan, 72 mm x 55 m, 4.4 mil, 12 per case	Stocked
00051115647444	7000124885	3M™ General Use Masking Tape 201+, Tan, 96 mm x 55 m, 4.4 mil, 8 per case	Stocked
00689330156276	7100114943	3M™ General Use Masking Tape 201+, Tan, 115 mm x 55 m, 4.4 mil, 8 per case	Stocked
00051115814358	7100031484	3M™ General Use Masking Tape 201+, Tan, 144 mm x 55 m, 4.4 mil, 8 per case	Stocked
00051115647451	7000124886	3M™ General Use Masking Tape 201+, Tan, 1490 mm x 55 m, 4.4 mil, 1 per case	Stocked
00051115647468	7000148416	3M™ General Use Masking Tape 201+, Tan, 24 mm x 55 m, 4.4 mil, 36 per case, Individually Wrapped Conveniently Packaged	Stocked
00051115647475	7000148417	3M™ General Use Masking Tape 201+, Tan, 36 mm x 55 m, 4.4 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051115647482	7000148418	3M™ General Use Masking Tape 201+, Tan, 48 mm x 55 m, 4.4 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked

## General Purpose Painting

00048011580371	7000124208	3M™ General Purpose Masking Tape 203, Beige, 36 mm x 55 m, 4.7 mil, 24 per case	Stocked
00048011580388	7000124209	3M™ General Purpose Masking Tape 203, Beige, 48 mm x 55 m, 4.7 mil, 24 per case	Stocked
00048011584546	7000124233	3M™ General Purpose Masking Tape 203, Beige, 48 mm x 55 m, 4.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00048011580395	7000124210	3M™ General Purpose Masking Tape 203, Beige, 72 mm x 55 m, 4.7 mil, 12 per case	Stocked
00051115314384	7000124328	3M™ General Purpose Masking Tape 203, Beige, 1490 mm x 55 m, 4.7 mil, 1 per case	Stocked
00048011584522	7000124232	3M™ General Purpose Masking Tape 203, Beige, 24 mm x 55 m, 4.7 mil, 36 per case, Individually Wrapped Conveniently Packaged	Stocked
00048011584546	7000124233	3M™ General Purpose Masking Tape 203, Beige, 48 mm x 55 m, 4.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
50051125062072	7000137773	3M™ Industrial Painter's Tape, Green, 5 mil, 1490 mm x 55 m, 1 per case	Made to Order
00021200711169	7000123529	3M™ Masking Tape 2307, Tan, 12 mm x 55 m, 5.2 mil, 72 per case	Stocked
00021200711176	7000123530	3M™ Masking Tape 2307, Tan, 18 mm x 55 m, 5.2 mil, 48 per case	Stocked
00021200711183	7000123531	3M™ Masking Tape 2307, Tan, 24 mm x 55 m, 5.2 mil, 36 per case	Stocked
00021200711190	7000123532	3M™ Masking Tape 2307, Tan, 36 mm x 55 m, 5.2 mil, 24 per case	Stocked
00021200711206	7000123533	3M™ Masking Tape 2307, Tan, 48 mm x 55 m, 5.2 mil, 24 per case	Stocked
00021200711213	7000123534	3M™ Masking Tape 2307, Tan, 72 mm x 55 m, 5.2 mil, 12 per case	Stocked
00021200738005	7000123726	3M™ Masking Tape 2307, Tan, 96 mm x 55 m, 5.2 mil, 8 per case	Stocked

## General Purpose Masking Tape (Cont.)

UPC	3M ID	Product	Stocked or MTO
<b>Outdoor Masking</b>			
00021200028281	7000048947	Scotch® Weather Resistant Masking Tape 225, Silver, 18 mm x 55 m, 5.8 mil, 48 per case	Make to Order
00021200028298	7000048948	Scotch® Weather Resistant Masking Tape 225, Silver, 24 mm x 55 m, 5.8 mil, 36 per case	Make to Order
00021200045974	7000048949	Scotch® Weather Resistant Masking Tape 225, Silver, 48 mm x 55 m, 5.8 mil, 24 per case	Stocked
00051115176463	7010373496	Scotch® Solvent Resistant Masking Tape 226, Black, 1/2 in x 60 yd, 10.6 mil, 72 per case	Make to Order
00021200611735	7000048632	Scotch® Solvent Resistant Masking Tape 226, Black, 3/4 in x 60 yd, 10.6 mil, 48 per case	Make to Order
00021200611742	7010334220	Scotch® Solvent Resistant Masking Tape 226, Black, 1 in x 60 yd, 10.6 mil, 36 per case	Stocked
00021200611766	7000048633	Scotch® Solvent Resistant Masking Tape 226, Black, 2 in x 60 yd, 10.6 mil, 24 per case	Stocked
00021200611773	7010373601	Scotch® Solvent Resistant Masking Tape 226, Black, 3 in x 60 yd, 10.6 mil, 12 per case	Make to Order
00021200611780	7000123577	Scotch® Solvent Resistant Masking Tape 226, Black, 4 in x 60 yd, 10.6 mil, 8 per case	Make to Order
00051115176302	7010334133	Scotch® Solvent Resistant Masking Tape 226, 12 in x 60 yd, 10.0 mil, 1 per case	Make to Order
00051138946159	7010374274	Scotch® Solvent Resistant Masking Tape 226, Black, 48 in x 60 yd, 10.6 mil, 1 per case	Make to Order
00051119196728	7100141029	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 1/2 in x 60 yd, 3.3 mil, 72 per case	Stocked
0005111919286	7100141030	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 1 in x 60 yd, 3.3 mil, 36 per case	Stocked
0005111919293	7100141031	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 1-1/2 in x 60 yd, 3.3 mil, 24 per case	Stocked
0005111919309	7100106569	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 2 in x 60 yd, 3.3 mil, 24 per case	Stocked
0005111927519	7100141047	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 3 in x 60 yd, 3.3 mil, 12 per case	Stocked
	7100132950	Scotch® 60-Day Ultimate Paint Edge Masking Tape 2460, Gold, Roll, Config	Make to Order
0005111919279	7000124759	Scotch® Ultimate Paint Edge Masking Tape 2460, Gold, 3/4 in x 60 yd, 3.3 mil, 48 per case	Stocked
00051138516512	7010373509	Scotch® Solvent Resistant Masking Tape 226, Black, 24 in x 60 yd, 10.0 mil, 1 per case	Make to Order
00051115175510	7010373489	Scotch® Solvent Resistant Masking Tape 226, Black, 16 in x 60 yd, 10.6 mil, 1 per case	Make to Order
00051115175459	7100042803	Scotch® Solvent Resistant Masking Tape 226, Black, 1-1/2 in x 60 yd, 10.6 mil, 24 per case	Make to Order
00021200611780	7000123577	Scotch® Solvent Resistant Masking Tape 226, Black, 4 in x 60 yd, 10.6 mil, 8 per case	Make to Order

## High Temp Masking Tape

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

### 225°F Maximum Operating Temperature

00051115647499	7000124887	3M™ Performance Yellow Masking Tape 301+, 12 mm x 55 m, 6.3 mil, 72 per case	Stocked
00051115647505	7000124888	3M™ Performance Yellow Masking Tape 301+, 18 mm x 55 m, 6.3 mil, 48 per case	Stocked
00051115647512	7000124889	3M™ Performance Yellow Masking Tape 301+, 24 mm x 55 m, 6.3 mil, 36 per case	Stocked
00051115647529	7000124890	3M™ Performance Yellow Masking Tape 301+, 36 mm x 55 m, 6.3 mil, 24 per case	Stocked
00051115647536	7000124891	3M™ Performance Yellow Masking Tape 301+, 48 mm x 55 m, 6.3 mil, 24 per case	Stocked
00051115647543	7000124892	3M™ Performance Yellow Masking Tape 301+, 72 mm x 55 m, 6.3 mil, 12 per case	Stocked
00051115647550	7000124893	3M™ Performance Yellow Masking Tape 301+, 96 mm x 55 m, 6.3 mil, 8 per case	Stocked
00051115691089	7000124905	3M™ Performance Yellow Masking Tape 301+, 1490 mm x 55 m, 6.3 mil, 1 per case	Stocked
00051115647567	7000148419	3M™ Performance Yellow Masking Tape 301+, 24 mm x 55 m, 36 case, Individually Wrapped Conveniently Packaged	Stocked
00051115647574	7000148420	3M™ Performance Yellow Masking Tape 301+, 36 mm x 55 m, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051115647581	7000148421	3M™ Performance Yellow Masking Tape 301+, 48 mm x 55 m, 24 per case, Individually Wrapped Conveniently Packaged	Stocked

## 250°F Maximum Operating Temperature

00051115691096	7000124906	3M™ High Performance Green Masking Tape 401+, 6 mm x 55 m, 96 rolls per case Bulk	Stocked
00051115647598	7000124894	3M™ High Performance Green Masking Tape 401+, 12 mm x 55 m 6.7 mil, 48 per case Bulk	Stocked
00051115647604	7000124895	3M™ High Performance Green Masking Tape 401+, 18 mm x 55 m, 48 rolls per case	Stocked
00051115647611	7000124896	3M™ High Performance Green Masking Tape 401+, 24 mm x 55 m 6.7 mil, 24 per case Bulk	Stocked
00051115647628	7000124897	3M™ High Performance Green Masking Tape 401+, 36 mm x 55 m 6.7 mil, 16 per case Bulk	Stocked
00051115647635	7000124898	3M™ High Performance Green Masking Tape 401+, 48 mm x 55 m 6.7 mil, 12 per case Bulk	Stocked
00051115647642	7000124899	3M™ High Performance Green Masking Tape 401+, 72 mm x 55 m, 6.7 mil, 8 per case	Stocked
00051115647659	7000124900	3M™ High Performance Green Masking Tape 401+, 96 mm x 55 m, 6.7 mil, 8 per case	Stocked
00051115647666	7000124901	3M™ High Performance Green Masking Tape 401+, 1490 mm x 55 m, 6.7 mil, untrimmed, 1 per case	Stocked
	7100151700	3M™ High Performance Green Masking Tape 401+, Roll, Config	Make to Order
00051115647673	7000148422	3M™ High Performance Green Masking Tape 401+, 24 mm x 55 m, 24 individually wrapped rolls per case, Conveniently Packaged	Stocked
00051115647680	7000148423	3M™ High Performance Green Masking Tape 401+, 36 mm x 55 m, 16 individually wrapped rolls per case, Conveniently Packaged	Stocked
00051115647697	7000148424	3M™ High Performance Green Masking Tape 401+, 48 mm x 55 m, 12 individually wrapped rolls per case, Conveniently Packaged	Stocked
00021200029806	7000048955	3M™ General Purpose Masking Tape 234, Tan, 12 mm x 55 m, 5.9 mil, 72 per case	Stocked
00021200029813	7000143654	3M™ General Purpose Masking Tape 234, Tan, 18 mm x 55 m, 5.9 mil, 48 per case	Stocked
00021200029820	7000048943	3M™ General Purpose Masking Tape 234, Tan, 24 mm x 55 m, 5.9 mil, 36 per case	Stocked
00021200029837	7000124039	3M™ General Purpose Masking Tape 234, Tan, 36 mm x 55 m, 5.9 mil, 24 per case	Stocked
00021200042447	7000048944	3M™ General Purpose Masking Tape 234, Tan, 48 mm x 55 m, 5.9 mil, 24 per case	Stocked
00021200042454	7000124041	3M™ General Purpose Masking Tape 234, Tan, 60 mm x 55 m, 5.9 mil, 12 per case	Stocked
00021200029851	7000048945	3M™ General Purpose Masking Tape 234, Tan, 72 mm x 55 m, 5.9 mil, 12 per case	Stocked
00021200029875	7000124037	3M™ General Purpose Masking Tape 234, Tan, 96 mm x 55 m, 5.9 mil, 8 per case	Stocked
00021200029882	7000124040	3M™ General Purpose Masking Tape 234, Tan, 144 mm x 55 m, 5.9 mil, 8 per case	Stocked
00051115172328	7000124098	3M™ General Purpose Masking Tape 234, Tan, 57 in x 60 yd, 5.9 mil, 1 per case	Make to Order
00021200028502	7000124028	3M™ High Performance Masking Tape 232, Tan, 6 mm x 55 m, 6.3 mil, 144 per case	Stocked
00021200028519	7010373300	3M™ High Performance Masking Tape 232, Tan, 9 mm x 55 m, 6.3 mil, 96 per case	Stocked
00021200028526	7000048952	3M™ High Performance Masking Tape 232, Tan, 12 mm x 55 m, 6.3 mil, 72 per case	Stocked
00021200028533	7000048942	3M™ High Performance Masking Tape 232, Tan, 18 mm x 55 m, 6.3 mil, 48 per case	Stocked
00021200028540	7000001265	3M™ High Performance Masking Tape 232, Tan, 24 mm x 55 m 6.3 mil, 36 per case	Stocked
00021200028557	7000124031	3M™ High Performance Masking Tape 232, Tan, 36 mm x 55 m, 6.3 mil, 24 per case	Stocked
00021200042409	7000001266	3M™ High Performance Masking Tape 232, Tan, 48 mm x 55 m, 6.3 mil, 24 per case	Stocked
00021200028588	7000001267	3M™ High Performance Masking Tape 232, Tan, 72 mm x 55 m, 6.3 mil, 12 per case	Stocked
00021200028519	7010373300	3M™ High Performance Masking Tape 232, Tan, 9 mm x 55 m, 6.3 mil, 96 per case	Stocked
00021200028595	7000124033	3M™ High Performance Masking Tape 232, Tan, 96 mm x 55 m, 6.3 mil, 8 per case	Stocked
00021200028601	7000124034	3M™ High Performance Masking Tape 232, Tan, 144 mm x 55 m, 6.3 mil, 8 per case	Stocked
00021200433870	7000123878	3M™ Masking Tape 2308, Tan, 12 mm x 55 m 5.3 mil, 72 per case	Make to Order
00051131065451	7000148380	3M™ Masking Tape 2308, Tan, 18 mm x 55 m, 5.3 mil, 48 per case	Stocked
00051131065468	7000123879	3M™ Masking Tape 2308, Tan, 24 mm x 55 m, 5.3 mil, 36 per case	Stocked

## High Temp Masking Tape (Cont.)

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

### 250°F Maximum Operating Temperature (Cont.)

00051131065475	7000123880	3M™ Masking Tape 2308, Tan, 36 mm x 55 m, 5.3 mil, 24 per case	Stocked
00051131065482	7000148381	3M™ Masking Tape 2308, Tan, 48 mm x 55 m, 5.3 mil, 24 per case	Stocked
00051131065499	7000123881	3M™ Masking Tape 2308, Tan, 72 mm x 55 m, 5.3 mil, 12 per case	Stocked
00051115055713	7000124180	3M™ Masking Tape 2308, Tan, 96 mm x 55 m, 5.3 mil, 8 per case	Make to Order

### 300°F Maximum Operating Temperature

00021200037740	7000124024	3M™ Paint Masking Tape 231/231A, Tan, 6 mm x 55 m, 7.6 mil, 144 per case	Stocked
00021200037757	7100084069	3M™ Paint Masking Tape 231/231A, Tan, 12 mm x 55 m, 7.6 mil, plastic core, 72 per case	Stocked
00021200037764	7000088513	3M™ Paint Masking Tape 231/231A Tan, 18 mm x 55 m, 7.6 mil, 48 per case	Stocked
00021200037771	7000088514	3M™ Paint Masking Tape 231/231A, Tan, 24 mm x 55 m, 7.6 mil, 36 per case	Stocked
00021200041112	7000088515	3M™ Paint Masking Tape 231/231A, Tan, 36 mm x 55 m, 7.6 mil, 24 per case	Stocked
00021200042379	7000088516	3M™ Paint Masking Tape 231/231A, Tan, 48 mm x 55 m, 7.6 mil, 24 per case	Stocked
00021200049361	7000088517	3M™ Paint Masking Tape 231/231A, Tan, 72 mm x 55 m, 7.6 mil, 12 per case	Stocked
00051138957056	7010295786	3M™ Paint Masking Tape 231/231A, Tan, 3-1/4 in x 60 yd, 7.6 mil, 16 Roll/Case	Stocked
00051115058073	7010334145	3M™ Paint Masking Tape 231/231A, Tan, 57 in x 60 yd, 7.6 mil, 1 per case	Make to Order
	7100132908	3M™ Paint Masking Tape 231/231A, Tan, Roll, Config.	Make to Order
04054596116306	7100086765	3M™ Specialty High Temperature Purple Masking Tape 501+, 18 mm x 55 m, 6.0 mil, 48 per case	Stocked
04054596116351	7100086194	3M™ Specialty High Temperature Purple Masking Tape 501+, 24 mm x 55 m, 6.0 mil, 36 per case	Stocked
04054596116375	7100086190	3M™ Specialty High Temperature Purple Masking Tape 501+, 36 mm x 55 m, 6.0 mil, 24 per case	Stocked
04054596116399	7100086764	3M™ Specialty High Temperature Purple Masking Tape 501+, 48 mm x 55 m, 6.0 mil, 24 per case	Stocked
04054596116450	7100086191	3M™ Specialty High Temperature Purple Masking Tape 501+, 72 mm x 55 m, 6.0 mil, 12 per case	Stocked
00076308866754	7010313352	3M™ Specialty High Temperature Purple Masking Tape 501+, 144 mm x 55 m, 6.0 mil, 8 per case	
04054596116306	7100086765	3M™ Specialty High Temperature Purple Masking Tape 501+, 1490 mm x 55 m, 6.0 mil, 7 per case	Stocked
	7100133102	3M™ Specialty High Temperature Purple Masking Tape 501+, Roll, Config.	Make to Order
00021200445774	7000142982	3M™ Performance Masking Tape 2364, Tan, 12 mm x 55 m, 6.5 mil, plastic core, 72 per case	Stocked
00021200433511	7000088383	3M™ Performance Masking Tape 2364, Tan, 18 mm x 55 m, 6.5 mil, 48 per case	Stocked
00021200433528	7100094011	3M™ Performance Masking Tape 2364, Tan, 24 mm x 55 m, 6.5 mil, 36 per case	Stocked
00021200433535	7000088384	3M™ Performance Masking Tape 2364, Tan, 36 mm x 55 m, 6.5 mil, 24 per case	Stocked
00021200433542	7000088385	3M™ Performance Masking Tape 2364, Tan, 48 mm x 55 m, 6.5 mil, 24 per case	Stocked
00021200433559	7000088407	3M™ Performance Masking Tape 2364, Tan, 72 mm x 55 m, 6.5 mil, 12/Case	Stocked
00021200445422	7000088411	3M™ Performance Masking Tape 2364, Tan, 100 mm x 55 m, 6.5 mil, 8 per case	Stocked
00051115057021	7010312638	3M™ Performance Masking Tape 2364, Tan, 57 in x 60 yd, 6.5 mil, untrimmed, 1 per case	Make to Order
	7100151699	3M™ Performance Masking Tape 2364, Tan, Roll, Config	Make to Order

### 325°F Maximum Operating Temperature

00021200445859	7000123904	3M™ Performance Masking Tape 2380, Tan, 12 mm x 55 m, 7.2 mil, plastic core, 72 per case	Stocked
----------------	------------	--	---------



00021200445842	7000088413	3M™ Performance Masking Tape 2380, Tan, 18 mm x 55 m, 7.2 mil, 48 per case	Stocked
00021200445835	7000088414	3M™ Performance Masking Tape 2380, Tan, 24 mm x 55 m, 7.2 mil, 36 per case	Stocked
00021200445828	7000088415	3M™ Performance Masking Tape 2380, Tan, 36 mm x 55 m 7.2 mil, 24 per case	Stocked
00021200445811	7000088416	3M™ Performance Masking Tape 2380, Tan, 48 mm x 55 m 7.2 mil, 24 per case	Stocked
00021200445804	7000088417	3M™ Performance Masking Tape 2380, Tan, 72 mm x 55 m, 7.2 mil, 12 per case	Stocked
00051138956974	7010373532	3M™ Performance Masking Tape 2380, Tan, 57 in x 60 yd, 7.2 mil, untrimmed, 1 per case	Make to Order
	7100151697	Scotch® Performance Masking Tape 2380, Tan, Roll, Config.	Make to Order
00021200429743	7000088391	3M™ High Performance Masking Tape 2693, Tan, 18 mm x 55 m, 7.9 mil, 48 per case	Stocked
00021200376290	7000088348	3M™ High Performance Masking Tape 2693, Tan, 24 mm x 55 m, 7.9 mil, 36 per case	Stocked
00021200411212	7000088380	3M™ High Performance Masking Tape 2693, Tan, 36 mm x 55 m, 7.9 mil, 24 per case	Stocked
00021200376306	7000088347	3M™ High Performance Masking Tape 2693, Tan, 48 mm x 55 m, 7.9 mil, 24 per case	Stocked
00021200429798	7000088390	3M™ High Performance Masking Tape 2693, Tan, 72 mm x 55 m, 7.9 mil, 12 per case	Stocked
00021200445569	7100093911	3M™ High Performance Masking Tape 2693, Tan, 100 mm x 55 m, 7.9 mil, 8 per case	Stocked
00051115059681	7100031837	3M™ High Performance Masking Tape 2693, Tan, 57 in x 60 yd, 7.9 mil, untrimmed, 1 per case	Make to Order
	7100151698	Scotch® High Performance Masking Tape 2693, Tan, Roll, Config.	Make to Order
00051115175275	7010334128	Scotch® High Performance Masking Tape 213, 1/4 in x 60 yd, 144/Case	Make to Order
00051138948931	7010374397	3M™ Premium High Temperature Masking Tape 2393, Tan, 100 mm x 55 m, 7.6 mil, plastic core, 12 per case	Make to Order
00051115059988	7100160346	3M™ Premium High Temperature Masking Tape 2393, Tan, 18 mm x 55 m 7.6 mil, 48 per case	Make to Order
00021200713026	7000088308	3M™ Premium High Temperature Masking Tape 2393, Tan, 24 mm x 55 m, 7.6 mil, 36 per case	Stocked
00051138963415	7010292649	3M™ Premium High Temperature Masking Tape 2393, Tan, 3/8 in x 60 yd, 7.6 mil, 96 per case	Make to Order
00021200713033	7000123560	3M™ Premium High Temperature Masking Tape 2393, Tan, 36 mm x 55 m, 7.6 mil, 24 per case	Make to Order
00021200713040	7000088309	3M™ Premium High Temperature Masking Tape 2393, Tan, 48 mm x 55 m, 7.6 mil, 24 per case	Stocked
00051115172120	7100036554	3M™ Premium High Temperature Masking Tape 2393, Tan, 72 mm x 55 m, 7.6 mil, 12 per case	Make to Order

### 350°F Maximum Operating Temperature

00021200028182	7100019551	Scotch® High Performance Masking Tape 213, Tan, 1/2 in x 60 yd, 6.5 mil, 72 per case	Make to Order
00021200028199	7000047436	Scotch® High Performance Masking Tape 213, Tan, 3/4 in x 60 yd, 6.5 mil, 48 per case	Make to Order
00021200028205	7000047437	Scotch® High Performance Masking Tape 213, Tan, 1 in x 60 yd, 6.5 mil, 36 per case	Stocked
00021200028212	7100025511	Scotch® High Performance Masking Tape 213, Tan, 1-1/2 in x 60 yd, 6.5 mil, 24 per case	Stocked
00021200044045	7000048415	Scotch® High Performance Masking Tape 213, Tan, 2 in x 60 yd, 6.5 mil, 24 per case	Stocked
00021200028229	7100025514	Scotch® High Performance Masking Tape 213, Tan, 3 in x 60 yd, 6.5 mil, 12 per case	Make to Order
00051115176180	7010373494	Scotch® High Performance Masking Tape 213, Tan, 6 in x 60 yd, 6.5 mil, 8 per case	Make to Order
00021200404283	7010372843	Scotch® High Performance Masking Tape 213, Tan, 12 in x 60 yd, 6.5 mil, 4 per case	Make to Order
00051131178229	7010370745	Scotch® High Performance Masking Tape 213, Tan, 24 in x 180 yd, 6.5 mil, 1 per case	Make to Order
00051115175206	7100000279	Scotch® High Performance Masking Tape 213, Tan, 48 in x 60 yd, 6.5 mil, 1 per case	Make to Order
00051115058042	7010373514	Scotch® High Performance Masking Tape 213, Tan, 48 in x 720 yd, 6.5 mil, 1 per case	Make to Order
00021200038495	7100056193	Scotch® High Performance Masking Tape 214, Tan, 1/2 in x 60 yd, 5.8 mil, 72 per case	Make to Order

## High Temp Masking Tape (Cont.)

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

### 350°F Maximum Operating Temperature (Cont.)

00051115174223	7000049030	Scotch® High Performance Masking Tape 214, Tan, 5/8 in x 60 yd, 60 per case	Make to Order
00051115176005	7000049031	Scotch® High Performance Masking Tape 214, Tan, 5/8 in x 180 yd, 14 per case	Make to Order
00021200038501	7000048382	Scotch® High Performance Masking Tape 214, Tan, 3/4 in x 60 yd, 5.8 mil, 48 per case	Make to Order
00021200038518	7000028847	Scotch® High Performance Masking Tape 214, Tan, 1 in x 60 yd, 5.8 mil, 36 per case	Stocked
00051115169748	7010300212	Scotch® High Performance Masking Tape 214, Tan, 1-1/4 in x 60 yd, 5.8 mil, 24 per case	Make to Order
00051115169731	7000048858	Scotch® High Performance Masking Tape 214, Tan, 1-1/2 in x 60 yd, 5.8 mil, 24 per case	Make to Order
00021200042324	7000048397	Scotch® High Performance Masking Tape 214, Tan, 2 in x 60 yd, 5.8 mil, 24 per case	Make to Order
00051115173301	7010374224	Scotch® High Performance Masking Tape 214, 3 in x 60 yd, 12 per case	Make to Order
00051115056086	7000049035	Scotch® High Performance Masking Tape 214, 6 in x 60 yd, 8 per case	Make to Order
00051115172823	7000048996	Scotch® High Performance Masking Tape 214, Tan, 12 in x 60 yd, 1 per case	Make to Order
00051115175138	7100002520	Scotch® High Performance Masking Tape 214, 48 in x 60 yd, 1 per case	Make to Order

## Fine Line

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

000212000610370	7010373385	Scotch® Fine Line Tape 218, Green, 1/8 in x 60 yd, 5.0 mil, 288 per case	Make to Order
00021200160288	7000028866	Scotch® Fine Line Tape 218, Green, 1/4 in x 60 yd, 5.0 mil, 144 per case	Stocked
00021200183683	7000123346	Scotch® Fine Line Tape 218, Green, 3/8 in x 60 yd, 5.0 mil, 96 per case	Make to Order
00021200046995	7000048423	Scotch® Fine Line Tape 218, Green, 3/4 in x 60 yd, 5.0 mil, 48 per case	Stocked
00021200047008	7000001161	Scotch® Fine Line Tape 218, Green, 1 in x 60 yd, 5.0 mil, 36 per case	Stocked
00051115171741	7010334619	Scotch® Fine Line Tape 218, Green, 1-1/4 in x 60 yd, 5.0 mil, 28 per case	Make to Order
00051138947101	7000028860	Scotch® Fine Line Tape 218, Green, 2 in x 60 yd, 5.0 mil, 24 per case	Stocked
00021200047015	7100028502	Scotch® Fine Line Tape 218, Green, 2-1/4 in x 60 yd, 5.0 mil, 12 per case	Make to Order
00021200444524	7100107031	Scotch® Fine Line Tape 218, Green, 3 in x 60 yd, 5.0 mil, 12 per case	Make to Order
00021200055003	7000048446	Scotch® Fine Line Tape 218, Green, 4 in x 60 yd, 5.0 mil, 8 per case	Stocked
00051115169878	7010334446	Scotch® Fine Line Tape 218, Green, 6 in x 60 yd, 5.0 mil, 8 per case	Make to Order
00051138950330	7010374413	Scotch® Fine Line Tape 218, Green, 7 in x 60 yd, 5.0 mil, 8 per case	Make to Order
00051115119712	7000048994	Scotch® Fine Line Tape 218, Green, 12 in x 60 yd, 5.0 mil, 4 per case	Make to Order
00051115169786	7010373107	Scotch® Fine Line Tape 218, Green, 24 in x 60 yd, 5.0 mil, no liner, 1 per case	Make to Order
00051115119651	7000001286	Scotch® Fine Line Tape 218, Green, 48 in x 60 yd, 5.0 mil, 1 per case	Make to Order
00021200063060	7000050052	Scotch® Fine Line Tape 218, Green, 1/16 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063084	7000050054	Scotch® Fine Line Tape 218, Green, 3/32 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063008	7000048455	Scotch® Fine Line Tape 218, Green, 1/8 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063077	7000050050	Scotch® Fine Line Tape 218, Green, 3/16 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063015	7000048456	Scotch® Fine Line Tape 218, Green, 1/4 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063022	7000048457	Scotch® Fine Line Tape 218, Green, 3/8 in x 60 yd, 5.0 mil, 96 per case (12 rolls/pack 8 packs/case)	Stocked
00021200063039	7000048458	Scotch® Fine Line Tape 218, Green, 1/2 in x 60 yd, 5.0 mil, 72 per case (12 rolls/pack 4 packs/case)	Stocked
00021200046988	7000048422	Scotch® Fine Line Tape 218, Green, 1/2 in x 60 yd, 5.0 mil, 72 per case (18 rolls/pack 4 packs/case)	Stocked

00021200063053	7000048459	Scotch® Fine Line Tape 218, Green, 3/4 in x 60 yd, 5.0 mil, 48 per case (12 rolls/pack 4 packs/case)	Stocked
00021200612640	7000048522	Scotch® Fine Line Tape 218, Green, 1-1/2 in x 60 yd, 5.0 mil, 24 per case (6 rolls/pack 4 packs/case)	Stocked
00021200046988	7000048422	Scotch® Fine Line Tape 218, Green, 1/2 in x 60 yd, 5.0 mil, 72 per case (18 rolls/pack 4 packs/case)	Stocked
00021200046995	7000048423	Scotch® Fine Line Tape 218, Green, 3/4 in x 60 yd, 5.0 mil, 48 per case	Stocked
00021200047008	7000001161	Scotch® Fine Line Tape 218, Green, 1 in x 60 yd, 5.0 mil, 36 per case	Stocked
00051138947101	7000028860	Scotch® Fine Line Tape 218, Green, 2 in x 60 yd, 5.0 mil, 24 per case	Stocked
00021200055003	7000048446	Scotch® Fine Line Tape 218, Green, 4 in x 60 yd, 5.0 mil, 8 per case	Stocked
00021200063008	7000048455	Scotch® Fine Line Tape 218, Green, 1/8 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063015	7000048456	Scotch® Fine Line Tape 218, Green, 1/4 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063022	7000048457	Scotch® Fine Line Tape 218, Green, 3/8 in x 60 yd, 5.0 mil, 96 per case (12 rolls/pack 8 packs/case)	Stocked
00021200063039	7000048458	Scotch® Fine Line Tape 218, Green, 1/2 in x 60 yd, 5.0 mil, 72 per case (12 rolls/pack 4 packs/case)	Stocked
00021200063053	7000048459	Scotch® Fine Line Tape 218, Green, 3/4 in x 60 yd, 5.0 mil, 48 per case (12 rolls/pack 4 packs/case)	Stocked
00021200160288	7000028866	Scotch® Fine Line Tape 218, Green, 1/4 in x 60 yd, 5.0 mil, 144 per case	Stocked
00021200612640	7000048522	Scotch® Fine Line Tape 218, Green, 1-1/2 in x 60 yd, 5.0 mil, 24 per case (6 rolls/pack 4 packs/case)	Stocked
00021200063077	7000050050	Scotch® Fine Line Tape 218, Green, 3/16 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063060	7000050052	Scotch® Fine Line Tape 218, Green, 1/16 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200063084	7000050054	Scotch® Fine Line Tape 218, Green, 3/32 in x 60 yd, 5.0 mil, 144 per case (12 rolls/pack 12 packs/case)	Stocked
00021200722882	7000048652	Scotch® High Temperature Fine Line Tape 4735, Orange, 3/4 in x 36 yd, 5.4 mil, 48 per case	Make to Order
00076308863968	7100103296	Scotch® High Temperature Fine Line Tape 4735, Orange, 3/4 in x 108 yd, 12 per case	Make to Order
00021200404511	7000048833	Scotch® High Temperature Fine Line Tape 4735, Orange, 1 in x 36 yd, 36 per case	Make to Order
00051111982488	7000049651	Scotch® High Temperature Fine Line Tape 4735, Orange, 2 in x 36 yd, 5.1 mil, 24 per case	Make to Order
	7100000191	Scotch® High Temperature Fine Line Tape 4735, Orange, Roll, Config.	Make to Order
	7100012331	Scotch® High Temperature Fine Line Tape 4735L, Orange, Roll, Liner, Config.	Make to Order
00021200722462	7000048634	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 1/4 in x 36 yd, 5.4 mil, 144 per case	Make to Order
00021200720482	7000048630	Scotch® High Temperature Fine Line Tape 4737T, Transparent Blue, 3/8 in x 36 yd, 5.4 mil, 96 per case	Make to Order
00021200713538	7000048629	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 1/2 in x 36 yd, 5.4 mil, 72 per case	Stocked
00021200713545	7000048628	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 3/4 in x 36 yd, 5.4 mil, 48 per case	Make to Order
00021200713552	7000048627	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 1 in x 36 yd, 5.4 mil, 36 per case	Stocked
00021200738876	7000048758	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 1-1/2 in x 36 yd, 5.4 mil, 24 per case	Make to Order
00021200228285	7000048610	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 2 in x 36 yd, 5.4 mil, 24 per case	Make to Order
00051115629686	7000049655	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 9-7/8 in x 180 yd, 5.4 mil, 1 per case	Make to Order
00638060533765	7100226234	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 23 in x 36 yd, 5.4 mil, 4 Rolls/per case	Make to Order

## Fine Line (Cont.)

UPC	3M ID	Product	Stocked or MTO
00076308864033	7010337024	Scotch® High Temperature Fine Line Tape 4737T, Translucent Blue, 5.4 mil, 48 in x 36 yd, 4 per case	Make to Order
00076308979966	7100071174	Scotch® High Temperature Fine Line Tape 4737TL, Translucent Blue, 10 in x 36 yd, 4 per case	Make to Order
00051128993910	7100077898	Scotch® High Temperature Fine Line Tape 4737TL, Translucent Blue, 48 in x 36 yd, 5.4 mil, liner, 1 per case	Make to Order
00076308870058	7010379488	Scotch® High Temperature Fine Line Tape 4737TL, Translucent Blue, 48 in x 100 yd, 5.4 mil, liner, 1 per case	Make to Order
00638060402405	7100202953	Scotch® High Temperature Fine Line Tape 4737TL, Translucent Blue, 48 in x 180 yd, 1 per pallet	Make to Order
00021200721731	7000123578	Scotch® High Temperature Fine Line Tape 4737S, Blue, 1 in x 36 yd, 5.4 mil, 36 per case	Make to Order
00021200722134	7010373602	Scotch® High Temperature Fine Line Tape 4737S, Blue, 1/4 in x 36 yd, 5.4 mil, 144 per case	Make to Order
00021200722158	7000123582	Scotch® High Temperature Fine Line Tape 4737S, Blue, 1/2 in x 36 yd, 5.4 mil, 72 per case	Stocked
00021200722165	7000123583	Scotch® High Temperature Fine Line Tape 4737S, Blue, 3/4 in x 36 yd, 5.4 mil, 48 per case	Stocked
00021200738869	7010333880	Scotch® High Temperature Fine Line Tape 4737S, Blue, 2 in x 36 yd, 5.4 mil, 24 per case	Make to Order
00048011539614	7000001303	Scotch® High Temperature Fine Line Tape 4737S, Blue, 49 in x 36 yd, 5.4 mil, 4 per case	Make to Order
	7100012315	Scotch® High Temperature Fine Line Tape 4737S, Blue, Roll, No Liner, Config.	Make to Order
	7100013637	Scotch® High Temperature Fine Line Tape 4737SL, Blue, Liner, Roll, Config.	Make to Order
00051115317989	7010312804	Scotch® Fine Line Masking Tape 265, Green, 1/4 in x 60 yd, 5.1 mil, 36 per case	Make to Order
00051115317996	7010373932	Scotch® Fine Line Masking Tape 265, Green, 1/2 in x 60 yd, 5.1 mil, 72 per case	Make to Order
00051115318009	7010335032	Scotch® Fine Line Masking Tape 265, Green, 3/4 in x 60 yd, 5.1 mil, 48 per case	Make to Order
00051115318016	7010373933	Scotch® Fine Line Masking Tape 265, Green, 1 in x 60 yd, 5.1 mil, 36 per case	Make to Order
	7100194155	Scotch® Masking Tape 2800, Blue, 1200 mm x 50 m, 1 per case	Stocked
	7100194289	Scotch® Masking Tape 2800, Blue, 12 mm x 50 m, 100 per case	Stocked
	7100194156	Scotch® Masking Tape 2800, Blue, 19 mm x 50 m, 64 per case	Stocked
	7100194288	Scotch® Masking Tape 2800, Blue, 25 mm x 50 m, 48 per case	Stocked
	7100194287	Scotch® Masking Tape 2800, Blue, 50 mm x 50 m, 24 per case	Stocked

## Duct Tape

UPC	3M ID	Product	Stocked or MTO
<b>Utility</b>			
00689330172252	7100158345	3M™ All Purpose Duct Tape DT8, Silver, 48 mm x 54.8 m, 8 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00689330178094	7100174104	3M™ All Purpose Duct Tape DT8, Black, 48 mm x 54.8 m, 8 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051111978412	7010375734	3M™ Value Duct Tape 1900, Silver, 1.88 in x 60 yd, 5.8 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051115234224	7000124256	3M™ Value Duct Tape 1900, Silver, 2.83 in x 50 yd, 5.8 mil, 12 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200498336	7000148383	3M™ Multi-Purpose Duct Tape 3900, Black, 48 mm x 54.8 m, 7.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked

00021200498329	7000124009	3M™ Multi-Purpose Duct Tape 3900, Blue, 48 mm x 54.8 m, 7.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200498312	7000049744	3M™ Multi-Purpose Duct Tape 3900, Olive, 48 mm x 54.8 m, 8.1 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00689330201006	7100234711	3M™ Multi-Purpose Duct Tape 3900, Orange, 8.1 mil, 48 mm x 54.8 m, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200498305	7000144749	3M™ Multi-Purpose Duct Tape 3900, Red, 48 mm x 54.8 m, 8.1 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051131069763	7100029108	3M™ Multi-Purpose Duct Tape 3900 Silver, 48 mm x 54.8 m, 8.1 mil, 24 per case, Conveniently Packaged	Stocked
00021200498299	7000124008	3M™ Multi-Purpose Duct Tape 3900, White, 48 mm x 54.8 m, 7.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200498282	7000124007	3M™ Multi-Purpose Duct Tape 3900, Yellow, 48 mm x 54.8 m, 8.1 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051131069954	7100145924	3M™ Vinyl Duct Tape 3903, Black, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200455148	7100149680	3M™ Vinyl Duct Tape 3903, Black, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051131069787	7100155016	3M™ Vinyl Duct Tape 3903, Blue, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200454868	7010408810	3M™ Vinyl Duct Tape 3903, Blue, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051131069848	7100145925	3M™ Vinyl Duct Tape 3903, Gray, 2 in x 50 yd 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200449895	7100152407	3M™ Vinyl Duct Tape 3903, Gray, 3 in x 50 yd, 6.5 mil, 18 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200453236	7100171192	3M™ Vinyl Duct Tape 3903, Gray, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051131069862	7100145926	3M™ Vinyl Duct Tape 3903, Green, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200455155	7010415509	3M™ Vinyl Duct Tape 3903, Green, 49 in x 50 yd 6.5 mil, 2 per case	Stocked
00051131069923	7100148743	3M™ Vinyl Duct Tape 3903, Red, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200455131	7010410520	3M™ Vinyl Duct Tape 3903, Red, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051131069817	7100148262	3M™ Vinyl Duct Tape 3903, White, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200455179	7010415510	3M™ Vinyl Duct Tape 3903, White, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051111920572	7010378167	3M™ Vinyl Duct Tape 3903, Yellow, 3 in x 50 yd, 6.5 mil, 18 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200455162	7000124787	3M™ Vinyl Duct Tape 3903, Yellow, 49 in x 50 yd, 6.5 mil, 2 per case	Stocked
00051131069824	7100146009	3M™ Vinyl Duct Tape 3903, Yellow, 2 in x 50 yd, 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051111925751	7100153654	3M™ Vinyl Duct Tape 3903, White, 3 in x 50 yd, 6.5 mil, 18 Roll/Case, Individually Wrapped Conventionalty Packaged	Make to Order
00051115234217	7000049202	3M™ Value Duct Tape 1900, Silver, 1.88 in x 50 yd, 5.8 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051131069848	7100145925	3M™ Vinyl Duct Tape 3903, Gray, 2 in x 50 yd 6.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked

### Heavy Duty

00689330172283	7100158377	3M™ Heavy Duty Duct Tape DT11, Black, 48 mm x 54.8 m, 11 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00689330172276	7100158346	3M™ Heavy Duty Duct Tape DT11, Silver, 48 mm x 54.8 m, 11 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00689330172290	7100158390	3M™ Super Duty Duct Tape DT17, Black, 48 mm x 32 m, 17 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200855610	7000048814	3M™ Heavy Duty Duct Tape 3939, Silver, 24 mm x 54.8 m, 9.0 mil, 36 per case	Stocked

## Duct Tape (Cont.)

UPC	3M ID	Product	Stocked or MTO
<b>Heavy Duty (Cont.)</b>			
00051131069756	7000028933	3M™ Heavy Duty Duct Tape 3939, Silver, 48 mm x 54.8 m, 9.0 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200855634	7100022015	3M™ Heavy Duty Duct Tape 3939, Silver, 96 mm x 54.8 m, 9.0 mil, 12 per case	Stocked
00021200855627	7000048815	3M™ Heavy Duty Duct Tape 3939, Silver, 72 mm x 54.8 m, 9.0 mil, 12 per case	Stocked
00021200227738	7000001232	3M™ Extra Heavy Duty Duct Tape 6969, Black, 48 mm x 54.8 m, 10.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200227806	7000123814	3M™ Extra Heavy Duty Duct Tape 6969, Olive, 48 mm x 54.8 m, 10.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051131069695	7000001230	3M™ Extra Heavy Duty Duct Tape 6969, Silver, 48 mm x 54.8 m, 10.7 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00021200856358	7000001231	3M™ Extra Heavy Duty Duct Tape 6969, Silver, 72 mm x 54.8 m, 10.7 mil, 12 per case	Stocked
<b>Clean Removal</b>			
00051131178199	7100140217	3M™ Performance Plus Duct Tape 8979, Olive, 48 mm x 55 m, 12.1 mil, 24 per case	Stocked
00048011539188	7000124266	3M™ Performance Plus Duct Tape 8979, Black, 48 mm x 54.8 m, 12.1 mil, 24 per case, Conveniently Packaged	Stocked
00051115259128	7100139310	3M™ Performance Plus Duct Tape 8979, Black, 72 mm x 54.8 m, 12.1 mil, 12 per case	Stocked
0005111916438	7100139301	3M™ Performance Plus Duct Tape 8979, Black, 12 in x 60 yd, 12.1 mil, 1 per case	Make to Order
0005111922125	7100005781	3M™ Performance Plus Duct Tape 8979, Black, 29 in x 60 yd, 12.1 mil, 1 per case	Make to Order
00051131178199	7100140217	3M™ Performance Plus Duct Tape 8979, Olive, 48 mm x 55 m, 12.1 mil, 24 per case	Stocked
00076308145293	7100160397	3M™ Performance Plus Duct Tape 8979, Olive, 27-1/2 in x 60 yd, 1 per case	Make to Order
0005111923290	7000049575	3M™ Performance Plus Duct Tape 8979, Olive, 29 in x 60 yd, 12.1 mil, 1 per case	Make to Order
00048011539225	7000124257	3M™ Performance Plus Duct Tape 8979, Slate Blue, 24 mm x 54.8 m 12.1 mil, 48 per case	Stocked
00048011538518	7000001329	3M™ Performance Plus Duct Tape 8979 Slate Blue, 48 mm x 22.8 m 12.1 mil, 12 per case, Conveniently Packaged	Stocked
00021200564680	7000001330	3M™ Performance Plus Duct Tape 8979, Slate Blue, 48 mm x 54.8 m, 12.1 mil, 24 per case, Conveniently Packaged	Stocked
00021200564697	7000124263	3M™ Performance Plus Duct Tape 8979, Slate Blue, 72 mm x 54.8 m, 12.1 mil, 12 per case	Stocked
00021200564703	7000049207	3M™ Performance Plus Duct Tape 8979, Slate Blue, 96 mm x 54.8 m, 12.1 mil, 12 per case	Stocked
00051138949280	7100139308	3M™ Performance Plus Duct Tape 8979, Slate Blue, 7 in x 60 yd, 12.1 mil, 6 per case	Make to Order
00048011539201	7000124267	3M™ Performance Plus Duct Tape 8979, Slate Blue, 12 in x 60 yd, 12.1 mil, 2 per case	Stocked
00048011581835	7000124264	3M™ Performance Plus Duct Tape 8979, Slate Blue, 144 mm x 54.8 m, 12.1 mil, 6 per case	Stocked
00048011581309	7000124223	3M™ Performance Plus Duct Tape 8979N (Nuclear), Red, 24 mm x 54.8 m, 12.1 mil, 48 per case	Stocked
00048011539140	7000049014	3M™ Performance Plus Duct Tape 8979N (Nuclear), Red, 48 mm x 54.8 m, 12.1 mil, 24 per case	Stocked
00048011539157	7010334653	3M™ Performance Plus Duct Tape 8979N (Nuclear), Red, 72 mm x 54.8 m, 12.1 mil, 12 per case	Stocked
00051115259258	7010374791	3M™ Performance Plus Duct Tape 8979N (Nuclear), Red, 96 mm x 54.8 m, 12.1 mil, 12 per case	Make to Order
00051115259258	7000124268	3M™ Performance Plus Duct Tape 8979N (Nuclear), Slate Blue, 48 mm x 54.8 m, 12.1 mil, 24 per case	Stocked

00021200743283	7000124269	3M™ Performance Plus Duct Tape 8979N (Nuclear), Slate Blue, 72 mm x 54.8 m, 12.1 mil, 12 per case	Stocked
00048011583259	7100139300	3M™ Performance Plus Duct Tape 8979N (Nuclear), Slate Blue, 96 mm x 54.8 m, 12.1 mil, 12 per case	Make to Order
00048011581859	7100139306	3M™ Performance Plus Duct Tape 8979N (Nuclear), Slate Blue, 144 mm x 54.8 m, 12.1 mil, 6 per case	Make to Order
00051115318429	7000049309	3M™ Outdoor Masking Poly Tape 5903, Red, 48 mm x 54.8 m, 7.5 mil, 24 per case, Individually Wrapped Conveniently Packaged	Stocked
00051111075913	7010334725	3M™ Outdoor Masking Poly Tape 5903, Red, 5 in x 60 yd, 7.5 mil, 8 per case	Stocked
00051115689017	7010295459	3M™ Outdoor Masking Poly Tape 5903, Red, 50 in x 60 yd, 4 per case	Make to Order
00051115254918	7000124742	3M™ Outdoor Masking and Stucco Tape 5959, Red, 48 mm x 41.1 m, 12.0 mil, 12 per case, Conveniently Packaged	Stocked
0005111923283	7000001486	3M™ Performance Plus Duct Tape 8979, Slate Blue, 29 in x 60 yd, 12.1 mil, 1 per case	Make to Order
00051115689017	7010295459	3M™ Outdoor Masking Poly Tape 5903, Red, 50 in x 60 yd, 4 per case	Make to Order

## Masking Film

UPC	3M ID	Product	Stocked or MTO
00021200228322	7000123523	3M™ High Temperature Paint Masking Film 7300 Translucent, 3 in x 1500 ft 3.4 mil, 6 per case Boxed	Not Stocked
00021200721052	7010312298	3M™ High Temperature Paint Masking Film 7300, Translucent, 4 in x 1500 ft, 3.4 mil, 6 per case	Stocked
00021200554872	7010379181	3M™ High Temperature Paint Masking Film 7300, Translucent, 5 in x 1500 ft, 3.4 mil, 6 per case	Stocked
00021200228339	7100082513	3M™ High Temperature Paint Masking Film 7300 Translucent, 6 in x 1500 ft, 3.4 mil, 6 per case Boxed	Make to Order
00021200228346	7010334191	3M™ High Temperature Paint Masking Film 7300, Translucent, 9 in x 1500 ft, 3.4 mil, 4 per case	Make to Order
00021200228353	7000123524	3M™ High Temperature Paint Masking Film 7300, Translucent, 12 in x 1500 ft, 3.4 mil, 3 per case	Stocked
00021200228377	7000123525	3M™ High Temperature Paint Masking Film 7300, Translucent, 18 in x 1500 ft, 3.4 mil, 2 per case	Stocked
00048011580708	7000124214	3M™ High Temperature Paint Masking Film 7300, Translucent, 24 in x 1500 ft, 3.4 mil, 1 per case	Make to Order
00021200453212	7100205686	3M™ High Temperature Paint Masking Film 7300, Translucent, 28 in x 1500 ft, 3.4 mil, 1 per case	Make to Order
00021200228391	7000048609	3M™ High Temperature Paint Masking Film, 7300, Translucent, 36 in x 1500 ft, 3.4 mil, 1 per case	Stocked
00048011580715	7000124215	3M™ High Temperature Paint Masking Film 7300 Translucent, 48 in x 1500 ft, 2.0 mil, 1 roll per case, 16 rolls per pallet	Make to Order
00051138964948	7010334823	3M™ High Temperature Paint Masking Film 7300, Translucent, 62 in x 1500 ft, 2 mil, 1 per case	Make to Order
00051115637315	7100205687	3M™ High Temperature Protective Bags and Sheets 7260M, Translucent, 10 in x 14 in, 1.8 mil, 1 case (1000 bags/case)	Make to Order
00076308987817	7100205688	3M™ High Temperature Protective Bags and Sheets 7260M, Transparent, 12 in x 14 in, 1.8 mil, 1 case (1000 bags/case)	Make to Order
00021200742934	7000124128	3M™ High Temperature Protective Bags and Sheets 7260M, Translucent, 89 in x 100 yd, 1.8 mil, Center-slit Sheeting, 25 per pallet	Make to Order
00051115322273	7010335055	3M™ High Temperature Protective Bags and Sheets 7260M, Translucent, 262 in x 89 in, 1.8 mil, 20 per pallet (25 bags/roll)	Make to Order
00021200969621	7010374250	3M™ High Temperature Protective Bags and Sheets 7260M, Translucent, 262 in x 89 in, perf and seal, 20 per pallet (25 bags/roll)	Make to Order
00638060534908	7100244627	3M™ High Temperature Paint Masking Film 7302, Translucent, 0.356 m x 460 m, 1.2 mil, 48 Rolls/Pallet	Make to Order

## Masking Film (Cont.)

UPC	3M ID	Product	Stocked or MTO
00638060534922	7100244677	3M™ High Temperature Paint Masking Bag 7302, Translucent, 0.51 m x 1.12 m, 1.2 mil, 300 Bags/Roll, 40 Rolls/Pallet	Make to Order
00638060534489	7100234122	3M™ Ultra High Temperature Paint Masking Film 7305, Translucent, 1.2 mil, 230 in x 144 in, (20 Pieces/Roll) 40 Roll/Pallet	Make to Order
00638060534472	7100234115	3M™ Ultra High Temperature Paint Masking Film 7305, Translucent, 1.2 mil, 236 in x 157 in, (20 Pieces/Roll) 40 Rolls/Pallet	Make to Order
00638060534458	7100234117	3M™ Ultra High Temperature Paint Masking Film 7305, Translucent, 1.2 mil, 268 in x 170 in, (20 Pieces/Roll) 40 Roll/Pallet	Make to Order
00638060534915	7100242727	3M™ High Temperature Paint Masking Bag 7302, Translucent, 6.07 m x 4.19 m, 1.2 mil, 20 Bags/Roll, 40 Rolls/Pallet	Make to Order
00638060535813	7100246047	3M™ High Temperature Paint Masking Bag 7302, Translucent, 4.5 m x 6.65 m, 1.2 mil, 15 Bags/Roll, 40 Rolls/Pallet	Make to Order

## Flatback Tape

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

### Utility

00021200485701	7000088499	3M™ Flatback Tape 2517, Medium Brown, 18 mm x 55 m, 6.5 mil, 48 per case	Stocked
00021200485695	7000088500	3M™ Flatback Tape 2517, Medium Brown, 6.5 mil, 24 mm x 55 m, 36 per case	Stocked
00021200485688	7000088501	3M™ Flatback Tape 2517, Medium Brown, 36 mm x 55 m, 6.5 mil, 24 per case	Stocked
00021200485671	7000088502	3M™ Flatback Tape 2517, Medium Brown, 48 mm x 55 m, 6.5 mil, 24 per case	Stocked
00021200485763	7000088503	3M™ Flatback Tape 2517, Medium Brown, 6.5 mil, 72 mm x 55 m, 12 per case	Stocked
00021200485664	7000088504	3M™ Flatback Tape 2517, Medium Brown, 100 mm x 55 m, 6.5 mil, 8 per case	Stocked
00021200485725	7000048946	3M™ Flatback Tape 2517, Medium Brown, 144 mm x 55 m, 6.5 mil, 8 per case	Make to Order
00051115173981	7010295674	3M™ Flatback Tape 2517, Medium Brown, 8 in x 60 yd, 6.5 mil, 4 per case	Make to Order
00051115058455	7010334146	3M™ Flatback Tape 2517, Medium Brown, 12 in x 60 yd, 6.5 mil, 4 per case	Make to Order
00051138946630	7010312645	3M™ Flatback Tape 2517, Medium Brown, 12 mm x 55 m, 6.5 mil, 72 per case	Make to Order
	7100151694	3M™ Flatback Tape 2517, Medium Brown, Roll, Config.	Make to Order
	7100243538	3M™ High Performance Flatback Tape 2519, Tan, 24 mm x 55 m, 36 per case	Stocked
	7100243697	3M™ High Performance Flatback Tape 2519, Tan, 36 mm x 55 m, 24 per case	Stocked
	7100243535	3M™ High Performance Flatback Tape 2519, Tan, 48 mm x 55 m, 24 per case	Stocked
	7100243536	3M™ High Performance Flatback Tape 2519, Tan, 72 mm x 55 m, (3 Roll/Pack) 12 Roll/Case	Stocked
00638060536193	7100246870	3M™ High Performance Flatback Tape 2519, Tan, 72 mm x 110 m, 12 per case	Stocked
	7100243539	3M™ High Performance Flatback Tape 2519, Tan, 100 mm x 55 m, 8 per case	Stocked
00054007999379	7010322595	3M™ High Performance Flatback Tape 2519, Tan, 120 mm x 55 m, 8 per case	Stocked
	7100245354	3M™ High Performance Flatback Tape 2519, Tan, Roll, Config.	Make to Order
00051128988732	7100048098	3M™ General Use Flatback Tape 2515, Tan, 18 mm x 55 m, 48 per case	Stocked
00051128988749	7100048110	3M™ General Use Flatback Tape 2515, Tan, 24 mm x 55 m, 36 per case	Stocked
00051128988756	7100048097	3M™ General Use Flatback Tape 2515, Tan, 36 mm x 55 m, 24 per case	Stocked
00051128988763	7100048231	3M™ General Use Flatback Tape 2515, Tan, 48 mm x 55 m, 24 per case	Stocked
00051128988770	7100048220	3M™ General Use Flatback Tape 2515, Tan, 72 mm x 55 m, 12/per case	Stocked
00051128988787	7100048099	3M™ General Use Flatback Tape 2515, Tan, 96 mm x 55 m, 8 per case	Stocked
00021200028762	7000001488	Scotch® Flatback Masking Tape 250 Tan, 1 in x 60 yd, 6.0 mil, 36 per case (6 rolls/pack 6 packs/case)	Stocked



## Specialty

00021200054235	7010373263	Scotch® Printable Flatback Paper Tape 256, Light Green, 3/4 in x 60 yd, 6.7 mil, 48 per case	Make to Order
00021200049682	7000048435	Scotch® Printable Flatback Paper Tape 256, Light Green, 1 in x 60 yd, 6.7 mil, 36 per case	Make to Order
00051115176883	7010312635	Scotch® Printable Flatback Paper Tape 256, Light Green, 2 in x 60 yd, 6.7 mil, 24 per case	Make to Order
00021200041211	7010295143	Scotch® Printable Flatback Paper Tape 256, Red, 3/8 in x 60 yd 6.7 mil, 96 per case	Make to Order
00051115171680	7010374227	Scotch® Printable Flatback Paper Tape 256, Red, 1/2 in x 60 yd, 6.7 mil, 72 per case	Make to Order
00021200038556	7000048383	Scotch® Printable Flatback Paper Tape 256, Red, 3/4 in x 60 yd, 6.7 mil, 48 per case	Make to Order
00021200028915	7000047438	Scotch® Printable Flatback Paper Tape 256, Red, 1 in x 60 yd, 6.7 mil, 36 per case	Make to Order
00021200408267	7010372841	Scotch® Printable Flatback Paper Tape 256, Red, 2 in x 60 yd, 6.7 mil, 24 per case	Make to Order
00051138949747	7100050576	Scotch® Printable Flatback Paper Tape 256, Red, 48 in x 60 yd, 6.7 mil, 1 per case	Make to Order
00021200038129	7010373208	Scotch® Printable Flatback Paper Tape 256, White, 1/4 in x 60 yd, 6.7 mil, 144 per case	Make to Order
00021200028922	7010369023	Scotch® Printable Flatback Paper Tape 256, White, 3/8 in x 60 yd, 6.7 mil, 96 per case	Make to Order
00021200028939	7000001101	Scotch® Printable Flatback Paper Tape 256, White, 1/2 in x 60 yd, 6.7 mil, 72 per case	Stocked
00021200028946	7000047439	Scotch® Printable Flatback Paper Tape 256, White, 3/4 in x 60 yd, 6.7 mil, 48 per case	Stocked
00051138951221	7010302196	Scotch® Printable Flatback Paper Tape 256, White, 3/4 in x 180 yd, 6.7 mil, 9 per case	Make to Order
00021200028953	7000047440	Scotch® Printable Flatback Paper Tape 256, White, 1 in x 60 yd, 6.7 mil, 36 per case	Stocked
00021200028960	7010369025	Scotch® Printable Flatback Paper Tape 256, White, 1-1/2 in x 60 yd, 6.7 mil, 24 per case	Make to Order
00021200408403	7010334403	Scotch® Printable Flatback Paper Tape 256, White, 1-1/2 in x 180 yd, 6.7 mil, 6 per case	Make to Order
00021200042584	7000123288	Scotch® Printable Flatback Paper Tape 256, White, 2 in x 60 yd, 6.7 mil, 24 per case	Stocked
00051138946401	7010374275	Scotch® Printable Flatback Paper Tape 256, White, 2 in x 60 yd, 6.7 mil, plastic core, 24 per case	Make to Order
00051115058998	7010295677	Scotch® Printable Flatback Paper Tape 256, White, 2.62 in x 60 yd, 6.7 mil, 12 per case	Make to Order
00051115175947	7010334131	Scotch® Printable Flatback Paper Tape 256, White, 3-1/4 in x 180 yd, 6.7 mil, 3 per case	Make to Order
00051138946869	7010295678	Scotch® Printable Flatback Paper Tape 256, White, 57 in x 60 yd, 6.7 mil, 1 per case	Make to Order
00021200070525	7010292867	Scotch® Printable Flatback Paper Tape 256, White, 1/2 in x 60 yd, 6.7 mil, 72 per case (12 rolls/pack 6 packs/case)	Make to Order
00021200068751	7000050010	Scotch® Printable Flatback Paper Tape 256, White, 3/4 in x 60 yd, 6.7 mil, 48 per case (12 rolls/pack 4 packs/case)	Stocked
00021200070549	7010378934	Scotch® Printable Flatback Paper Tape 256, White, 1 in x 60 yd, 6.7 mil, 36 per case (12 rolls/pack 3 packs/case)	Stocked
00021200375149	7100029128	3M™ Textile Flatback Tape 2526, White, 18 mm x 55 m, 9.8 mil, 48 per case	Make to Order
00021200375156	7000088519	3M™ Textile Flatback Tape 2526, White, 24 mm x 55 m, 9.8 mil, 36 per case	Stocked
00021200375163	7010333881	3M™ Textile Flatback Tape 2526, White, 36 mm x 55 m, 9.8 mil, 24 per case	Make to Order
00021200375170	7010373789	3M™ Textile Flatback Tape 2526, White, 48 mm x 55 m, 9.8 mil, 24 per case	Make to Order
00021200375187	7100135532	3M™ Textile Flatback Tape 2526, White, 72 mm x 55 m, 9.8 mil, 12 per case	Make to Order
00021200375293	7000123733	3M™ Textile Flatback Tape 2526, White, 96 mm x 55 m, 9.8 mil, 8 per case	Make to Order
00051115174483	7010334126	3M™ Textile Flatback Tape 2526, White, 12 in x 60 yd, 9.8 mil, 4 per case	Make to Order
00051115176593	7010373497	3M™ Textile Flatback Tape 2526, White, 18 in x 60 yd, 9.8 mil, 1 per case	Make to Order
00051115175725	7100034662	3M™ Performance Flatback Tape 2525, Orange, 1/2 in x 60 yd, 9.5 mil, 72 per case	Make to Order

## Flatback Tape (Cont.)

UPC	3M ID	Product	Stocked or MTO
-----	-------	---------	----------------

### Specialty (Cont.)

00021200555664	7000088506	3M™ Performance Flatback Tape 2525, Orange, 18 mm x 55 m, 9.5 mil, 48 per case	Stocked
	7100243626	3M™ High Performance Flatback Tape 2519, Tan, 18 mm x 55 m, 48 per case	Stocked
00021200555640	7000088507	3M™ Performance Flatback Tape 2525, Orange, 36 mm x 55 m, 9.5 mil, 24 per case	Stocked
00021200555633	7000088508	3M™ Performance Flatback Tape 2525, Orange, 48 mm x 55 m, 9.5 mil, 24 per case	Stocked
00021200555626	7000088509	3M™ Performance Flatback Tape 2525, Orange, 72 mm x 55 m, 9.5 mil, 12 per case	Stocked
00021200555657	7000088510	3M™ Performance Flatback Tape 2525, Orange, 100 mm x 55 m, 9.5 mil, 8 per case	Stocked
00051115175572	7010334129	3M™ Performance Flatback Tape 2525, Orange, 58 in x 60 yd, 9.5 mil, 1 per case	Make to Order
	7100151695	3M™ Performance Flatback Tape 2525, Orange, 9.5 mil, Roll, Config.	Make to Order
00021200389344	7010372864	Scotch® Printable Flatback Paper Tape 256, Red, 1-1/2 in x 60 yd, 6.7 mil, 24 per case	Make to Order
00021200389207	7010300205	Scotch® Printable Flatback Paper Tape 256, Green, 1 in x 360 yd, 9 per case	Make to Order
00021200555671	7100016326	3M™ Performance Flatback Tape 2525, Orange, 24 mm x 55 m, 9.5 mil, 36 per case	Stocked

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M and Tartan are trademarks of 3M Company. Scotch is a registered trademark of 3M Company.



Closure and Masking Systems Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000

Phone 800-362-3550  
Fax 877-369-2923  
Web 3M.com/Masking

Please recycle. Printed in USA.  
© 3M 2022. All rights reserved.  
70-0717-0969-8 Mar 2022