



3M Ireland Limited

Product catalogue 2023

Personal Safety

Valid from 01.10.2023

The information in this catalogue is current at the date of publication. Products availability may be amended by 3M from time to time. 3M is not liable in case of any errors or omissions.



■ Table of Contents

Respiratory Protection

Disposable Respirators	10
Half Mask Respirators	13
Full Face Respirators	17
Cartridges & Filters	19
Respirator Fit Testing	22
Reusable Respirator Parts & Accessories	27
Powered Air Respirator Systems	35
Supplied Air Respirator Systems	42
Hoods & Headgear	43
Powered & Supplied Air Parts & Accessories	47

Detection & Monitoring Equipment

Monitor Badges	56
----------------	----

Hearing Protection

Earplugs	67
Earplug Dispensers	72
Earmuffs	73
Hygiene Kits	78
Validation	79

Protective Communications

In-ear Headsets	86
Over-ear Headsets	88
Protective Communications Parts & Accessories	94

Head & Face Protection

Hard Hats	112
-----------	-----

■ Table of Contents

Faceshields	119
Head Protection Accessories	121

Eye Protection

Safety Glasses	129
Safety Goggles	139
Protective Eyewear Accessories	142

Welding Safety

Welding Helmets	149
Welding Helmet & Respirator Sets	153
Welding Filters	156
Welding Parts & Accessories	159

Apparel & Workwear

Coveralls	168
Lab Coats	173
Protective Apparel Accessories	174

50⁺ Years of Health and Safety Leadership



Get safety facts & tips from 3M experts



To provide and maintain the correct safety levels can be a challenge, hindering your health and safety process. Our safety experts are ready to share the latest facts and practical tips in a new series of free, complimentary webinars.

Sign up to watch on-demand or access live webinars!





Fall Protection



3M Fall Protection solutions.

At 3M Fall Protection our mission is to bring every worker at height home safely.

Every day on your job, you climb to new heights with two things in mind: getting your work done well and returning home safely to those you love.

Our job? Helping you get there. With our two brands, DBI-SALA® and Protecta®, we offer solutions for all your work at height needs.

Learn about the products and training options:

3m.co.uk/fallprotection

Or contact your local sales team



3M is a trademark of 3M Company. DBI-SALA is a trademark of D B Industries, LLC. Protecta is a trademark of Capital Safety Group EMEA



Respiratory Protection

3M™ Respiratory Protection Solutions

Disposable Respirators



Disposable respirators are an excellent choice for workplaces where cleaning and maintenance is not practical.

Constructed from advanced materials, including 3M™ Advanced Electret Filter Media, 3M™ Disposable Respirators are designed for comfort and protection, allowing your team to give their best.

Reusable Respirators



Reusable respirators can help to reduce cost and waste* in workplaces where regular cleaning and maintenance is possible.

Designed to be easy-to-use and utilising comfortable, durable materials, 3M™ Reusable Respirators will help to give your team confidence in their protection.




Powered and Supplied Air Respirators



Powered and supplied air respirators can integrate head, eye, face, hearing and respiratory protection, while keeping your team comfortable for long periods.

Designed to be adaptable for different conditions, 3M™ Powered and Supplied Air Respirators will help to protect your team in demanding environments.

*Compared to daily usage and disposal of disposable respirators, when the reusable respirator is properly maintained.

	Disposable Respirators 	Reusable Respirators 	Powered and Supplied Air Respirators 
Can provide protection from particulate hazards (e.g. dust, mists, metal fumes)	✓	✓	✓
Can provide protection from gas and vapour hazards (e.g. solvents)	✗	✓	✓
Requires cleaning and maintenance	✗	✓ ¹	✓
Options for wearers who have facial hair	✗	✗	✓
Options for companies who prefer not to face-fit test ²	✗	✗	✓ ²




1. Maintenance-free options are available. For example the 3M™ Maintenance Free Reusable Respirator 4000+ Series.

2. Face-fit testing is a legal requirement in some countries, and is always 3M recommended best-practice, for tight-fitting respirators.



Filtering Facepiece Respirators

Selecting a Filtering Facepiece Respirator

	FFP1 	FFP2 	FFP3 
Nominal Protection Factor	NPF 4	NPF 12	NPF 50
Typical Applications	Low levels of fine dust particles and oil or water based mist typically found during hand sanding, drilling and cutting	Moderate levels of fine dust particles and oil or water based mist typically found during plastering, cement, sanding and wood dust	Higher levels of fine dust particles and oil or water based mist typically found when handling hazardous powders found in the pharmaceutical industry or work with biological agents and fibres

Nominal Protection Factor (NPF): The theoretical protection level of a respirator based on laboratory measured performance data.

Types of Filtering Facepiece Respirator



3M™ Flat-Fold Respirators

- Ultra soft, flexible and comfortable fit resulting from the multiple panel design
- Comfort Series - Flat Fold only: Individually packed, foldable design prevents contamination before use and allows easy storage



3M™ Cup-Shaped Respirators

- Convex shape, nose clip and twin strap design
- Easy to fit
- Durable, collapse resistant shell



3M™ Cool Flow™ Valve

Effective removal of heat build-up provides a cooler and more comfortable wear

- Provides longer continuous wear time
- Reduces risk of fogging of spectacles and eyewear



3M™ Buckle Strap Respirators

- Robust and durable design provides multishift capability and secure feel
- Adjustable braided headbands
- Soft inner face-seal improves comfort

Respiratory Protection

Disposable Respirators

Focus

3M™ Aura Particulate Respirators 9300+Gen3

3M™ Aura™ Particulate Respirator 9300+Gen3 Series is the third generation of the best-selling 3M™ Aura™ flat fold respirator.

- Original 3-panel, flat-fold design fits a wide range of face shapes and sizes
- 3M™ Cool Flow™ Comfort Valve allows a greater percentage of warm, exhaled air to escape, helping to increase your comfort. *compared to 3M™ Aura™ 9300+ equivalent model
- 3M™ Advanced Electret (filter) Media helps you breathe easier



Product ID	Part Number	Product Name	MOQ	OU
7100134313	9322+GEN3	3M™ Aura™ Particulate Respirator, FFP2, Valved, 9322+Gen3	120	Each
7100138120	9322+GEN3SP	3M™ Aura™ Particulate Respirator, FFP2, Valved, 9322+Gen3-SP	40	Each
7100134314	9332+GEN3	3M™ Aura™ Particulate Respirator, FFP3, Valved, 9332+Gen3	120	Each
7100138357	9332+GEN3SP	3M™ Aura™ Particulate Respirator, FFP3, Valved, 9332+Gen3-SP	40	Each

3M™ Aura™ Particulate Respirators 9300+ Series

3M™ Aura™ Particulate Respirators 9300+ Series has an ergonomic, flat-fold, 3-panel design featuring a low breathing resistance filter media. Available in FFP1, FFP2 and FFP3 protection levels, and with valved and unvalved models, our respirators feature an innovative chin tab for easy adjustments and an embossed, sculpted upper panel to help reduce eyewear fogging.

- Original 3-panel design allows for greater facial movement
- Low resistance filter technology helps you breathe easily
- Available with 3M™ Cool Flow™ Valve which helps reduce heat build-up



Product ID	Part Number	Product Name	MOQ	OU
7100258912	9310+	3M™ Aura™ Particulate Respirator, FFP1, Unvalved, 9310+	240	Each
7100258911	9312+	3M™ Aura™ Particulate Respirator, FFP1, Valved, 9312+	120	Each
7100258909	9322+	3M™ Aura™ Particulate Respirator, FFP2, Valved, 9322+	120	Each
7000088730	9322+BULK	3M™ Aura™ Particulate Respirator, FFP2, Valved, Bulk, 9322+	330	Each
7100258913	9332+	3M™ Aura™ Particulate Respirator, FFP3, Valved, 9332+	120	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Respiratory Protection

3M™ Aura™ Particulate Respirators 9400+ Series

3M™ Aura™ Particulate Respirators 9400+ Series provides FFP2 and FFP3 breathing protection. Our 3-panel, flat-fold design is completely free from staples and comes in highly visible bright blue. It has an embedded, metal-detectable nose clip, an embossed top panel to help reduce eyewear fogging and a sculpted upper panel for eyewear compatibility. They're supplied in hygienic individual packaging.



- Highly visible bright blue for fast, easy identification
- No staples or small detachable parts, helping to minimise the risk of contaminates
- „3-panel design accommodates greater facial movement as you talk „

Product ID	Part Number	Product Name	MOQ	OU
7000088835	9422+	3M™ Aura™ Particulate Respirator, FFP2, Valved, 9422+	120	Each
7000088836	9432+	3M™ Aura™ Particulate Respirator, FFP3, Valved, 9432+	120	Each

3M™ Particulate Respirators 8000 Series

The 3M™ Particulate Respirator 8000 Series is our range of cup-shaped respirators, with a lightweight, twin-strap design. They provide FFP1, FFP2 and FFP3 respiratory protection, with a convex shape, nose foam and adjustable nose clip that helps you get a comfortable fit across a broad range of face sizes.



- Robust, cup-shaped respirators
- FFP1 (NPF 4), FFP2 (NPF 12) and FFP3 (NPF 50) protection against dusts and mists
- Lightweight, twin-strap design, nose foam and nose clip help provide a comfortable, custom fit

Product ID	Part Number	Product Name	MOQ	OU
7000034734	8710	3M™ Particulate Respirator, FFP1, Unvalved, 8710E	240	Each
7000006980	8812	3M™ Particulate Respirator, FFP1, Valved, 8812	240	Each
7100003010	8810	3M™ Particulate Respirator, FFP2, Unvalved, 8810	240	Each
7100101091	8822	3M™ Particulate Respirator, FFP2, Valved, 8822	240	Each
7100081543	8825+	3M™ Particulate Respirator, FFP2, Valved, 8825+	50	Each
7100057145	8833	3M™ Particulate Respirator, FFP3, Valved, 8833	80	Each
7100081542	8835+	3M™ Particulate Respirator, FFP3, Valved, 8835+	50	Each
7100091323	8833SP	3M™ Particulate Respirator, Valved, FFP3, Small Pack, 8833SP	20	Each

Respiratory Protection

3M™ Speciality Particulate Respirators 9900 Series

3M™ Speciality Particulate Respirators provide lightweight and comfortable FFP1, FFP2 and FFP3 breathing protection against organic vapours, acid gases, ozone, hydrogen fluoride, and nuisance odours. Our respirators have an activated carbon layer that provides relief against nuisance-level odours. The convex shape, soft inner face seal, nose clip and twin strapping helps adjust to a broad range of faces, and the braided, colour-coded headbands help you quickly identify their protection level.



- Provides FFP1 (NPF 4), FFP2 (NPF 12), and FFP3 (NPF 50) protection against dusts and mists
- Activated carbon layer helps guard against nuisance odours and, in some models, low levels of organic vapours, acid gases and ozone (NPF 10)
- Convex shape, nose clip and twin strapping helps provide a comfortable fit across a broad range of face shapes

Product ID	Part Number	Product Name	MOQ	OU
7000034740	9913	3M™ Speciality Particulate Respirator, FFP1, Unvalved, 9913	100	Each
7000034739	9914	3M™ Speciality Particulate Respirator, FFP1, Valved, 9914	100	Each
7000088787	9922	3M™ Speciality Particulate Respirator, FFP2, Valved, 9922	100	Each
7000034738	9926	3M™ Speciality Particulate Respirator, FFP2, Valved, 9926	100	Each

Respiratory Protection

Half Mask Respirators

Focus

3M™ Maintenance Free Reusable Respirators 4000+ Series

3M™ Maintenance Free Reusable Respirators 4000+ Series are a range of simple and ready-to-use respirators with integrated cartridge and filters. A newly enhanced valve assembly helps to reduce exhalation breathing resistance, and the close-fitting, non-silicone, textured face seal is soft and non-allergenic. Includes a resealable bag for hygienic storage and transportation.

- A newly enhanced valve assembly helps to reduce exhalation breathing resistance for improved breathing comfort
- Lightweight, well-balanced design
- Integrated filters mean it's ready to use and maintenance free



Product ID	Part Number	Product Name	MOQ	OU
7100113098	4251+	3M™ Maintenance Free Reusable Respirator Half Mask, FFA1P2 R D Filters, 4251+	10	Each

Focus

3M™ Cool Flow™ Fan

3M™ Cool Flow™ Fan is an optional attachment for your 3M™ Maintenance Free Reusable Respirators. Our fan features a single button control function offering improved wearer comfort during long work shifts. It's rechargeable and is supplied with a plug.

- Reduces heat and moisture build up
- For use with 3M™ Maintenance Free Reusable Respirators 4000+ or 0694X+
- Optional attachment that attaches simply and securely



Product ID	Part Number	Product Name	MOQ	OU
7100135812	1040N	3M™ Cool Flow™ Fan, Standard, 1040	5	Each

Respiratory Protection

Focus

3M™ Secure Click™ Reusable Half Mask Respirator HF-800 Series

Designed with smart and intuitive features 3M™ Secure Click™ Reusable Half Mask Respirator HF-800 Series is simple, comfortable and reliable. Available in three sizes: small, medium, and large, our respirators all come with an optional speaking diaphragm.



- Greater breathability and comfort provided by the world's first quad flow cartridge system
- Push button seal check helps bolster confidence that the respirator is properly sealed to the face
- Speaking diaphragm is designed to help provide easier communication while you work

Product ID	Part Number	Product Name	MOQ	OU
7100172004	HF-803	3M™ Secure Click™ Reusable Half Mask Respirator, Large, HF-803	10	Each
7100172003	HF-802	3M™ Secure Click™ Reusable Half Mask Respirator, Medium, HF-802	10	Each
7100171979	HF-801	3M™ Secure Click™ Reusable Half Mask Respirator, Small, HF-801	10	Each
7100172005	HF-803SD	3M™ Secure Click™ Reusable Half Mask Respirator, Speaking Diaphragm, Large, HF-803SD	10	Each
7100171980	HF-802SD	3M™ Secure Click™ Reusable Half Mask Respirator, Speaking Diaphragm, Medium, HF-802SD	10	Each
7100172006	HF-801SD	3M™ Secure Click™ Reusable Half Mask Respirator, Speaking Diaphragm, Small, HF-801SD	10	Each

Focus

3M™ Reusable Half Mask Respirator 7500 Series

3M™ Reusable Half Face Masks 7500 Series have a bayonet-style twin-filter design that fits a broad range of 3M lightweight filters. Our 7500 Series reusable masks have a 3M™ Cool Flow™ Valve, a soft sealing surface for comfort, and a unique head harness with an optional drop-down strap.



- Soft sealing surface and low breathing resistance makes them comfortable to wear for long durations
- Cool Flow™ Valve helps reduce heat build-up by allowing warm, exhaled air to escape
- Twin-filter design for even distribution of weight and minimal obstruction to field of vision

Product ID	Part Number	Product Name	MOQ	OU
7000104178	7503	3M™ Reusable Half Face Mask, Large, 7503	10	Each
7000104177	7502	3M™ Reusable Half Face Mask, Medium, 7502	10	Each
7000104176	7501	3M™ Reusable Half Face Mask, Small, 7501	10	Each
7000061555	RTU7523L	3M™ Reusable Half Mask Respirator Kit, A2P3 R Filter, Large Mask, 7523L	4	Kit
7000061553	RTU7523M	3M™ Reusable Half Mask Respirator Kit, A2P3 R Filter, Medium Mask, 7523M	4	Kit

Respiratory Protection

3M™ Reusable Half Mask Respirator 6500QL Series

3M™ Reusable Half Face Mask 6500QL is a premium choice to help protect your workforce from certain airborne contaminants when used with approved 3M filters.

- Reusable respirator designed for tough and dirty work environments
- When used with the correct 3M bayonet filter it can protect against, gases, vapours and/or particulate hazards
- Quick Latch Drop Down mechanism makes it easy to put on or take off



Product ID	Part Number	Product Name	MOQ	OU
7100018995	6503QL	3M™ Reusable Half Face Mask Respirator, Quick Latch, Large, 6503QL	10	Each
7100018994	6502QL	3M™ Reusable Half Face Mask Respirator, Quick Latch, Medium, 6502QL	10	Each
7100020699	6501QL	3M™ Reusable Half Face Mask Respirator, Quick Latch, Small, 6501QL	10	Each

3M™ Reusable Half Mask Respirator 6000 Series

3M™ Reusable Half Face Masks 6000 Series are made from a lightweight, comfortable elastomeric material with a bayonet-style twin-filter design, cradle head harness and easy-fasten neck strap. Our reusable half masks are low profile and are available in three sizes.

- Economical, low maintenance and easy to handle
- Reusable half masks designed for simplicity
- Cradle head harness and easy-fasten neck strap



Product ID	Part Number	Product Name	MOQ	OU
7000146849	6300	3M™ Reusable Half Mask Respirator, Large, 6300	8	Each
7000146847	6200	3M™ Reusable Half Mask Respirator, Medium, 6200	8	Each
7000146845	6100	3M™ Reusable Half Mask Respirator, Small, 6100	8	Each

Respiratory Protection

3M™ Reusable Half Mask HF-300 Series

3M™ Reusable Half Mask, HF-300 Series, has been designed with user comfort and convenience in mind. Compatible with DIN threaded, 3M™ Filters DT-Series, the HF-300 offers protection against a wide range of respiratory hazards. Convenient for workplaces where different types of respiratory protection are used, the HF-300 shares the DT-Series filter range with the 3M™ Powered Air Respirator PF-600 Series and the 3M™ Reusable Full Face Masks, FF-300 and FF-600 Series, minimising the number of filter types that must be kept in stock. Please note, the 3M™ Reusable Half Mask, HF-300 Series, was previously named the Scott™ AVIVA 40 Reusable Half Mask.



- Compatible with the 3M™ Filters DT-Series
- Available in three sizes
- Available as a ready to use kit, complete with respirator and filters

Product ID	Part Number	Product Name	MOQ	OU
7100265024	HF-301	3M™ Reusable Half Face Mask Respirator HF-301, Small, 10 Each/Case	10	Each
7100265524	HF-302	3M™ Reusable Half Face Mask Respirator HF-302, Medium, 10 Each/Case	10	Each
7100265229	HF-303	3M™ Reusable Half Face Mask Respirator HF-303, Large, 10 Each/Case	10	Each
7100265072	HF-3014	3M™ Reusable Half Face Mask and A2P3 Combination Filter Kit HF-3014, Small, 10 Each/Case	10	Each
7100265073	HF-3024	3M™ Reusable Half Face Mask and A2P3 Combination Filter Kit HF-3024, Medium, 10 Each / Case	10	Each
7100265044	HF-3034	3M™ Reusable Half Face Mask and A2P3 Combination Filter Kit HF-3034, Large, 10 Each/ Case	10	Each
7100265070	HF-3011	3M™ Reusable Half Face Mask and P3 Particulate Filter Kit HF-3011, Small, 10 Each/Case	10	Each
7100265235	HF-3021	3M™ Reusable Half Face Mask and P3 Particulate Filter Kit HF-3021, Medium, 10 Each/Case	10	Each
7100265071	HF-3031	3M™ Reusable Half Face Mask and P3 Particulate Filter Kit HF-3031, Large, 10 Each/Case	10	Each

3M™ Reusable Half Mask HF-350 Series

3M™ Reusable Half Mask, HF-350 Series, has been designed with user comfort and convenience in mind. Featuring a 50mm filter thread, and compatible with the 3M™ Filters PV-251, the HF-350 is a convenient choice for users of the 3M™ Powered Air Respirator System Asbestos Kit, PV-300 Series, as the number of filter types that must be kept in stock can be minimised. Please note, the 3M™ Reusable Half Mask, HF-350 Series, was previously named the Scott™ AVIVA 50 Reusable Half Mask.



- Compatible with the 3M™ Filters PV-251
- Available in three sizes
- Available as a ready to use kit, complete with respirator and filters

Product ID	Part Number	Product Name	MOQ	OU
7100265223	HF-351	3M™ Reusable Half Face Mask Respirator HF-351, Small, 50 mm, 10 Each/Case	10	Each
7100265228	HF-352	3M™ Reusable Half Face Mask Respirator HF-352, Medium, 50 mm, 10 Each/Case	10	Each
7100265222	HF-353	3M™ Reusable Half Face Mask Respirator HF-353, Large, 50 mm, 10 Each/Case	10	Each

Respiratory Protection

Full Face Respirators

Focus

3M™ Secure Click™ Reusable Full Face Respirators

The 3M™ Secure Click™ Reusable Full Face Mask FF-800 Series helps protect against particulates and/or a wide variety of gases and vapours when used with approved 3M™ Secure Click™ filters. This facepiece comes with exciting features that make it 3M's next generation in comfort, breathability and simplicity.

- The quick, easy, one-touch positive pressure push button seal check helps provide improved confidence in respirator fit
- Two dual-flow gas & vapour filters on each respirator combine to create the world's first quad flow gas & vapour filter system with four airflow paths providing easy breathing and comfort
- Large lens for excellent field of vision, and treated with Scotchgard™ Protector for improved paint and stain resistance



Product ID	Part Number	Product Name	MOQ	OU
7100262626	FF-803	3M™ Secure Click™ Reusable Full Face Respirator, Large, FF-803	4	Each
7100262628	FF-802	3M™ Secure Click™ Reusable Full Face Respirator, Medium, FF-802	4	Each
7100262627	FF-801	3M™ Secure Click™ Reusable Full Face Respirator, Small, FF-801	4	Each

3M™ Reusable Full Face Mask Respirator FF-600 Series

3M™ Reusable Full Face Mask, FF-600 Series features a panoramic visor that is designed to prevent visual distortion and allows for a virtually unrestricted field of vision.

Compatible with the 3M™ Filters, DT Series, and with options suitable for use as part of a powered air system, the FF-600 is suitable for a wide range of wearers and applications. Please note, the 3M™ Reusable Full Face Mask, FF-600 Series, was previously named the Scott™ Vision 2 / FM4 Reusable Full Face Mask.

- Designed with features to enhance user comfort, including a soft, flexible liquid silicone rubber faceseal, adjustable 5 point head harness and a panoramic visor
- Compatible with the 3M™ Filters DT-Series, or can be used as a facepiece for the 3M™ Powered Air Respirator PF-600E+ Series (FF-600 only)
- Available in three sizes, each with a choice of front-fitting (FF-600F) or side-fitting (FF-600) filter ports



Product ID	Part Number	Product Name	MOQ	OU
7100236941	FM4M	3M™ Full Facepiece Reusable Respirator, Medium, FF-602	4	Each
7100236885	FM4ML	3M™ Full Facepiece Reusable Respirator, Medium/Large, FF-603	4	Each
7100236942	FM4S	3M™ Full Facepiece Reusable Respirator, Small, FF-601	4	Each

Respiratory Protection

3M™ Reusable Full Face Mask Respirator FF-300 Series

3M™ Reusable Full Face Mask Respirator FF-300 Series is our multi-function full-face mask designed to provide durable and comfortable protection against a wide range of respiratory hazards. Use in conjunction with approved 3M powered air systems or as a negative pressure respirator with the 3M™ DT Series filter range, providing protection against a wide range of industrial hazards.

- Use as a negative-pressure single-filter mask or as a face piece for a powered air respirator
- Sweat port helps to improve user comfort during long periods of use
- Visor provides a good field of view and comes in choice of polycarbonate or high-heat material



Product ID	Part Number	Product Name	MOQ	OU
7100236989	FM3L	3M™ Full Facepiece Reusable Respirator, Medium/Large, FF-302	4	Each
7100237033	FM3S	3M™ Full Facepiece Reusable Respirator, Small, FF-301	4	Each

3M™ Reusable Full Face Mask FF-600 Series

3M™ Reusable Full Face Mask, FF-600 Series features a panoramic visor that allows for a virtually unrestricted field of vision. Compatible with the 3M™ Filters, DT Series, the FF-600 Series is suitable for a wide range of wearers and applications.

- Panoramic visor to allow for a virtually unrestricted field of vision
- Visor is designed to minimise visual distortion
- Soft, highly flexible and conforming Liquid Silicone Rubber face seal to enhance user comfort



Product ID	Part Number	Product Name	MOQ	OU
7100265075	FF-601F	3M™ Front-Fitting Reusable Full Face Mask FF-601F, Small, 4 Each/Case	4	Each
7100265074	FF-602F	3M™ Front-Fitting Reusable Full Face Mask FF-602F, Medium, 4 Each/Case	4	Each
7100265236	FF-603F	3M™ Front-Fitting Reusable Full Face Mask FF-603F, Large, 4 Each/Case	4	Each

3M™ Reusable Full Face Mask 6000 Series

3M™ Reusable Full Face Masks 6000 Series have a large polycarbonate lens and soft, elastomeric facepiece. The 3M™ Bayonet Connection System enables you to connect to a broad range of 3M twin lightweight filters. The 6000 Series is lightweight and features a 3M™ Cool Flow™ Valve and four-strap suspension.

- Soft, elastomeric facepiece for wearer comfort
- Four-strap suspension means the mask is easy to put on and take off
- Large polycarbonate lens offers good visibility and that complies to relevant performance requirements of EN166:B



Product ID	Part Number	Product Name	MOQ	OU
7100015052	6900	3M™ Reusable Full Face Mask, Large, 6900	4	Each
7100015051	6800	3M™ Reusable Full Face Mask, Medium, 6800	4	Each
7100015974	6700	3M™ Reusable Full Face Mask, Small, 6700	4	Each

Respiratory Protection

Cartridges & Filters

3M™ Secure Click™ Particulate Filters

3M™ Secure Click™ Series Particulate Filters are CE approved for environments containing certain particles for use with 3M™ Secure Click™ Respirators



- New dual flow cartridges and filters allow for easier breathing
- Protects against particulates with optional nuisance level organic vapour/acid gas relief
- Quick, simple connection. Simply align the connections and push until you hear a click

Product ID	Part Number	Product Name	MOQ	OU
7100206892	D9038	3M™ Secure Click™ Particulate Filter with Hydrogen Fluoride and Nuisance Level Organic Vapour and Acid Gas Relief, Hard Case, P3 R, D9038	40	Pack
7100197270	D3138	3M™ Secure Click™ Particulate Filter with Nuisance Level Organic Vapour and Acid Gas Relief, and Ozone up to 10 x OEL, P3 R, D3138	40	Pack
7100206891	D9035	3M™ Secure Click™ Particulate Filter, Hard Case, P3 R, D9035	40	Pack
7100197283	D7915	3M™ Secure Click™ Particulate Filter, P1 R, D7915	320	Each
7100197481	D3125	3M™ Secure Click™ Particulate Filter, P2 R, D3125	40	Pack
7100197286	D7925	3M™ Secure Click™ Particulate Filter, P2 R, D7925	320	Each
7100197284	D3135	3M™ Secure Click™ Particulate Filter, P3 R, D3135	40	Pack
7100197285	D7935	3M™ Secure Click™ Particulate Filter, P3 R, D7935	320	Each

3M™ Secure Click™ Gas, Vapour and Particulate Filters D8000 Series

3M™ Secure Click™ Gas, Vapour and Particulate Filters D8000 Series can offer protection against a range of respiratory hazards depending upon the model selected. Use with 3M™ Secure Click™ Reusable Respirators. New dual flow cartridges and filters allow for easier breathing.



- New dual flow cartridges and filters allow for easier breathing
- Protects against a range of respiratory hazards depending upon the model selected
- Quick, simple cartridge connection. Simply align the connections and push until you hear a click

Product ID	Part Number	Product Name	MOQ	OU
7100153224	D8051	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1 ,with Dual Flow, D8051	32	Pack
7100153226	D8059	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1, with Dual Flow, D8059	32	Pack
7100153236	D8094	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1P3 R, with Dual Flow, D8094	32	Pack
7100153231	D8055	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A2, with Dual Flow, D8055	32	Pack
7100153235	D8095	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A2P3 R, with Dual Flow, D8095	32	Pack

Respiratory Protection

3M™ Particulate Filters

3M™ Particulate Filters provide protection against a wide range of dusts, mist and other particles. 3M particulate filters offer low breathing resistance and good balance with a slim, swept back profile, designed to optimise your field of vision when wearing the respirator. Selected filters in the range can be used in conjunction with a 3M™ 501 filter retainer and a 3M™ Gas & Vapour Filter to provide combined gas, vapour and particulate protection.



- Protects against a range of dusts, mists and particulates
- Options for P1, P2 or P3 protection
- Features the 3M Bayonet style connection

Product ID	Part Number	Product Name	MOQ	OU
7000037674	5925	3M™ Particulate Filter P2 R, 5925	80	Each
7100052193	6925	3M™ Particulate Filter P2 R, 06925	80	Each
7000037675	5935	3M™ Particulate Filter P3 R, 5935	80	Each
7000032083	6035	3M™ Particulate Filter P3 R, 6035	80	Each
7000059883	6038	3M™ Particulate Filter P3 R, 6038	80	Each
7000037673	5911	3M™ Particulate Filter, P1 R, 5911	120	Each
7100015050	2125	3M™ Particulate Filter, P2 R, 2125	80	Each
7000052348	2128	3M™ Particulate Filter, P2 R, 2128	80	Each
7100240628	2135	3M™ Particulate Filter, P3 R, 2135	80	Each
7000029735	2138	3M™ Particulate Filter, P3 R, 2138	80	Each

3M™ Gas, Vapour and Particulate Filters

3M™ Gas, Vapour and Particulate Filters have a bayonet-style connection that fits a wide range of compatible half and full-face 3M™ Reusable Masks. The swept back profile is designed to optimise your field of vision. Our range of lightweight filters offer well-balanced breathing protection for hazardous environments.



- Protects against a range of vapours, gases and particulates
- Combines protection with comfort and balance
- Low profile design to optimise your field of vision

Product ID	Part Number	Product Name	MOQ	OU
7000034746	6075	3M™ Gas and Vapour Filter, A1 + Formaldehyde, 6075	64	Each
7000034751	6051	3M™ Gas and Vapour Filter, A1, 6051	64	Each
7000034749	6055	3M™ Gas and Vapour Filter, A2, 6055	64	Each
7100006000	6057	3M™ Gas and Vapour Filter, ABE1, 6057	64	Each
7000034747	6059	3M™ Gas and Vapour Filter, ABEK1, 6059	64	Each
7000034750	6054	3M™ Gas and Vapour Filter, K1, 6054	64	Each
7100104317	6092	3M™ Gas, Vapour and Particulate Filter, A1B1E1K1P3 R + Formaldehyde, 6092	32	Each
7100104310	6091	3M™ Gas, Vapour and Particulate Filter, A1P3 R, 6091	32	Each
7100104327	6099	3M™ Gas, Vapour and Particulate Filter, A2B2E2K2HgP3 + Formaldehyde, 6099	32	Each
7100104312	6095	3M™ Gas, Vapour and Particulate Filter, A2P3 R, 6095	32	Each
7000021315	6098	3M™ Gas, Vapour and Particulate Filter, AXP3 NR, 6098	32	Each
7000089106	6911	3M™ Organic Gas and Vapour Filter, A1, 06911	64	Each
7000089105	6915	3M™ Organic Vapour Filter, A2, 06915	16	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Respiratory Protection

3M™ Filters DT-Series

For effective protection against a range of particulates, gases and vapours or combination hazards, use 3M™ Filters DT-Series.



Suitable for use with certain 3M™ half and full-face tight-fitting respirators in negative-pressure mode as well as 3M™ Powered Air Respirator System PF-600E+ Series.

- Includes specifications to provide protection against particulate hazards, gas & vapour hazards or a combination of both
- Features a DIN40 mm threaded connection
- Please note DT-Series filters were previously known as Pro2000 Filters

Product ID	Part Number	Product Name	MOQ	OU
7100264840	DT-4041E	3M™ Combination Filter CF32 A2P3 R D, DT-4041E, 10 Each/Case	10	Each
7100264838	DT-4048E	3M™ Combination Filter CF32 AXB2P3 R D, DT-4048E, 10 Each/Case	10	Each
7100264837	DT-4047E	3M™ Combination Filter CF32 AXP3 R D, DT-4047E, 10 Each/Case	10	Each
7100264841	DT-4049E	3M™ Combination Filter CF32 Reactor HgP3 R D, DT-4049E, 10 Each/Case	10	Each
7100266031	DT-4149E	3M™ Combination Filter CFR32 Reactor HgP3 R D (Li2) DT-4149E, 10/Case	10	Each
7100266028	DT-4145E	3M™ Combination Filter CFR 32 A2B2E2K2-P3 R D DT-4145E, 10 Each/Case	10	Each
7100260645	DT4046EN	3M™ Combination Filter, CF32 A2B2E2K2HgP3 R D, DT-4046E	10	Each
7100260628	DT4045EN	3M™ Combination Filter, CF32 A2B2E2K2P3 R D, DT-4045E	10	Each
7100264834	DT-4001E	3M™ Gas & Vapour Filter GF22 A2, DT-4001E, 10 Each/Case	10	Each
7100265237	DT-4005E	3M™ Gas & Vapour Filter GF22 A2B2, DT-4005E, 10 Each/Case	10	Each
7100264839	DT-4006E	3M™ Gas & Vapour Filter GF32 A2B2E2K2, DT-4006E, 10 Each/Case	10	Each
7100264836	DT-4007E	3M™ Gas & Vapour Filter GF32 AX, DT-4007E, 10 Each/Case	10	Each
7100264835	DT-1135E	3M™ Particulate Filter PF10 P3 R D, DT-1135E, Yellow, 10 Each/Case	10	Each
7100265523	DT-1235E	3M™ Particulate Filter PFR 10 P3 DT-1235E, 10 Each/Case	10	Each
7100265239	DT-1235E BULK	3M™ Particulate Filter PFR 10 P3 DT-1235E, Bulk, 20 Each/Case	20	Each

3M™ Filters PV Series for use with PV-300 Series

3M™ Particulate Filter PV-1251E provides protection against particles such as solid and liquid particles, toxic and radioactive particles, microorganisms (e.g. bacteria and viruses) and enzymes. It is designed for use with 3M™ Powered Air Respirator System PV-300E and 3M™ HF-350 Series half face respirator in negative pressure mode



- Provides protection against particulates such as solid and liquid particles, toxic and radioactive particles, microorganisms (e.g. bacteria and viruses)
- Suitable for use with 3M™ Powered Air Respirator System PV-300E (formerly known as 3M™ Scott™ Phantom Vision)
- Suitable for use with 3M™ HF-350 Series half face respirator in negative pressure mode (formerly known as 3M™ Scott™ AVIVA 50)

Product ID	Part Number	Product Name	MOQ	OU
7100264725	PV-1251E	3M™ Particulate Filter PV-1251E, 10 Each/Case	10	Each
7100265015	PV-1251E BULK	3M™ Particulate Filter PV-1251E, Bulk, 20 Each/Case	20	Each

Respiratory Protection

Respirator Fit Testing

3M™ Training and Fit Testing Kit

Test kits and accessories designed to help your organisation meet regulatory fit testing requirements for tight fitting respirators. The kits can be used to validate face to respirator seal on any disposable respirator or half mask respirator. Not suitable for fit testing full facepiece respirators - this must be through Quantitative face fit testing.

- Fit test kits and accessories can be used to check respirator fit
- FT-10 uses a test solution of sodium saccharin that produces a sweet tasting aerosol
- FT-30 uses a test solution of denatonium benzoate to produce a bitter tasting aerosol



Product ID	Part Number	Product Name	MOQ	OU
7000002042	FT30	3M™ Fit Test Kit, Qualitative, Bitter, FT-30	1	Each
7000001898	FT10	3M™ Fit Test Kit, Qualitative, Sweet, FT-10	1	Each

3M™ Nebulizer FT-13

Replacement nebulizer used with the 3M™ Qualitative Fit Test Apparatus FT 10, FT 30 and the 3M™ Training and Fit Testing Case FT 20.

- A replacement part for 3M™ Qualitative Fit Test Apparatus Kits FT-10 Sweet and FT-30 Bitter
- Fast, easy method for performing qualitative fit testing
- Used with the 3M™ Qualitative Fit Test Apparatus FT-10, FT-30 and the 3M™ Training and Fit Testing Case FT-20



Product ID	Part Number	Product Name	MOQ	OU
7000001897	FT13	3M™ Nebulizer, FT-13	3	Each

3M™ Sensitivity Solution

3M™ Sensitivity Solutions are used to test the sensitivity of the respirator wearer to a sweet or bitter solution. For use with 3M™ Qualitative Fit Test Apparatus Kits FT-10 (Sweet) and FT-30 (Bitter)

- Sweet or bitter taste sensitivity solutions for fit testing
- 3M™ Sensitivity Solution, Sweet, FT-11 uses a test solution of sodium saccharin that produces a sweet tasting aerosol
- 3M™ Sensitivity Solution, Bitter, 55ml, FT-31 uses a test solution of denatonium benzoate to produce a very bitter taste



Product ID	Part Number	Product Name	MOQ	OU
7100004635	FT31	3M™ Sensitivity Solution, Bitter, 55ml, FT-31	6	Each
7000029587	FT11	3M™ Sensitivity Solution, Sweet, 55ml, FT-11	6	Each

Respiratory Protection

3M™ Fit Test Solution

Replacement fit test solutions for use with 3M™ Qualitative Fit Test Apparatus Kits FT-10 (Sweet) and FT-30 (Bitter). The choice between the bitter and sweet test kit is a personal one, however a small percentage of the population are unable to detect saccharin in which case the bitter test must be used.



- Sweet or bitter taste fit test solutions for fit testing
- 3M™ Fit Test Solution, Sweet, FT-12 uses a test solution of sodium saccharin that produces a sweet tasting aerosol
- 3M™ Fit Test Solution, Bitter, FT-32 uses a test solution of denatonium benzoate to produce a bitter aerosol

Product ID	Part Number	Product Name	MOQ	OU
7100004634	FT32	3M™ Fit Test Solution, Bitter, 55ml, FT-32	6	Each
7100004636	FT12	3M™ Fit Test Solution, Sweet, 55ml, FT-12	6	Each

3M™ Secure Click™ Quantitative Fit Test Adapter Kits

3M™ Secure Click™ Quantitative Fit Test Adaptor Kits are for conducting quantitative fit testing on 3M™ Secure Click™ Reusable Respirators. Filters are not included.



- Use to conduct quantitative fit testing on 3M™ Secure Click™ Reusable Respirators with speaking diaphragm
- Includes head harness assembly
- Not for use with 3M™ Secure Click™ Respirators without Speaking Diaphragm - for these respirators manually probe the respirator

Product ID	Part Number	Product Name	MOQ	OU
7100181558	HF-800-03	3M™ Secure Click™ Quantitative Fit Test Adapter Kit, for 3M™ Secure Click™ Half Mask HF-800 Series, HF-800-03	1	Each
7100265593	FF-800-06	3M™ Secure Click™ Quantitative Fit Test Adapter, FF-800-06	1	Each

3M™ Fit Test Adapters

For an alternative method to sharing a probed fit testing respirator, use 3M™ Quantitative Fit Test Adapters. Our fit test adaptor kits allow you to fit test with a personal 3M™ Respirator, rather than using a shared probed fit test respirator.



- Adapter allows fit testing with an individual's personal 3M™ Respirator
- Alternative to sharing a probed fit testing respirator
- Quick and easy to fit

Product ID	Part Number	Product Name	MOQ	OU
7000001945	601	3M™ Fit Test Adapter, Quantitative, 601	1	Each

Filter selection guide.

Application	Hazard	Typical Protection Considered
Painting, Spraying, Varnishing, Coating (Non Isocyanates** based)	Solvent-Based Paint**	A2P3 R
	Anti-Fouling Paint Spraying / Grinding	A2P3 R
	Water Soluble Paint	A1P2 R
	Solvents, Resins, Synthetic Resins**	A2P3 R
	Latex-Paint, Residual Solvents	A2P3 R
	Wood Preservatives	A1P2 R
Maintenance	Disinfection, Cleaning*	ABEK1P2 R
Decoration	Spray-On Glue, Foam, Varnish, Adhesive	A1P2 R
Waste Removal	Bacteria, Spores, Odours	A1P2 R
Agriculture	Pesticides, Insecticides	ABEK1P2 R
Wood Treatment	Bonding, Spray-On Glue	A2P3 R
Construction, Grinding, Cutting, Drilling	Tarring	A2P3 R
	Sealing	A1P2 R
	Spray Foam Insulation	A1P2 R
Coating	Organic Solvent/with boiling point less than 65 C	AXP3 R
	Ammonia Based Paint Remover	ABEK
	Polyurethane Coating**	ABEK1P3 R
	Solvent Based Varnish	A2
	Water Based Varnish	A1
Bonding	Solvent containing Adhesives	A1
Handling	Sulphur Dioxide	ABE
	Hydrochloric Acid	ABE
	Liquid Manure	ABEK
	Ammonia	K
	Formaldehyde	A1 + Form
	Hazardous goods storage/transport	ABEK1P3 R

Warning:
This guide is only an outline. It should not be used as the only means for selecting a respirator. Details regarding performance and limitations are set out on the respirator package and user instructions. Before using any of these respirators, the wearer must read and understand the user instructions for each product. Specific country legislation must be observed.

* excluding Formaldehyde

** for occurrence of Isocyanates, please contact the 3M Customer Helpline +44 (0) 870 60 800 60 or your local 3M office

What types of filters are there?

Filter Type	Colour	Main area of application
P	White	Solid and liquid particles
A	Brown	Organic gases and vapours with boiling point >65°C.
AX	Brown	Highly volatile organic solvents with boiling point <65°C.
B	Grey	Inorganic gases
E	Yellow	Acid Gases
K	Green	Ammonia and organic ammonia derivatives
Hg	Red	Mercury (vapour) and mercury compounds

Filter Classification	APF with 3M Half Mask	APF with 3M Full Face Mask
P1	4	4
P2	10	10
P3	20	40
Class 1 Gas and Vapour filters	10 or 1000ppm (whichever is lower)	20 or 1000ppm (whichever is lower)
Class 2 Gas and Vapour filters	10 or 5000ppm (whichever is lower)	20 or 5000ppm (whichever is lower)


AX-Filter for low boiling point (organic composition with a low boiling point under 65 °C). AX-Filter should only be fitted to 3M™ Full Face masks. AX filters may only be used for a single shift.
A1 and A2 Filter for organic vapour with a boiling point above 65 °C.

APF = Assigned Protection Factor (For further information on APFs see HSE document HSG53)

Select the right respirator and filter.

3M™ Bayonet Filter Series

3M™ Reusable Respirators and Filters at a glance




* Only for full face masks

3M™ Secure Click™ Series Filters



3M™ DT-Series Filters



Respiratory Protection

Reusable Respirator Parts & Accessories

3M™ Reusable Respirator Overspray Guards

Product ID	Part Number	Product Name	MOQ	OU
7100113104	400+	3M™ Reusable Respirator Overspray Guard for 3M™ Maintenance-Free Reusable Half Mask 4000+ Series, 400+	500	Each

3M™ Reusable Respirator Face Shield & Lens Covers

Product ID	Part Number	Product Name	MOQ	OU
7100188168	6885	3M™ Reusable Respirator Full Facepiece Faceshield Cover, for 3M™ Reusable Full Face Mask 6000 Series, 6800	100	Each

3M™ Secure Click™ Reusable Respirator Filter Retainers

Product ID	Part Number	Product Name	MOQ	OU
7100184498	D701	3M™ Secure Click™ Reusable Respirator Filter Retainer, D701	1	Each

3M™ Reusable Respirator Filter Retainers

Product ID	Part Number	Product Name	MOQ	OU
7100066103	3M501	3M™ Reusable Respirator Filter Retainer, 501	20	Each

3M™ Reusable Respirator Filter Adapters

Product ID	Part Number	Product Name	MOQ	OU
7100066104	603	3M™ Reusable Respirator Filter Adapter, 603	16	Each

3M™ Reusable Respirator Cleaning Wipes

Product ID	Part Number	Product Name	MOQ	OU
7100050720	105	3M™ Reusable Respirator Face Seal Cleaning Wipes, 105	200	Pack

Respiratory Protection

3M™ Reusable Respirator Spectacle Kits

Product ID	Part Number	Product Name	MOQ	OU
7100254233	SK102	3M™ Reusable Respirator Spectacle Kit, Universal, 102	1	Case
7100236681	FM421	3M™ Spectacle Kit 52 mm FF-600-21 for 3M™ Full Facepiece Respirator, FF-600	3	Each
7100236821	FM420	3M™ Spectacle Kit FF-600-20 for 3M™ Full Facepiece Respirator, FF-600	4	Each
7100236816	FM320	3M™ Spectacle Kit FF-300-20 for 3M™ Full Facepiece Respirator, FF-300	5	Each

3M™ Reusable Respirator Carry & Storage Bags

Product ID	Part Number	Product Name	MOQ	OU
7000087291	107	3M™ Reusable Respirator Full Face Storage Bag, 107	10	Each
7000108590	106	3M™ Reusable Respirator Half Mask Carry Case, 106	10	Each

3M™ Reusable Respirator Head Harness Assemblies




Product ID	Part Number	Product Name	MOQ	OU
7100278098	6897	3M™ Reusable Respirator Head Harness Assembly Kit, for 3M™ Reusable Full Face Mask 6000 Series, 6897	5	Each


3M™ Versaflō™ Powered Air Respirator System, TR-300+ Series with Loose Fitting Headtops





Headtops								
	M-206	M-207	M-306	S-133S S-133L	S-333SG S-333LG	S-433S/S-433L S-533S/S-533L	S-655	S-657
								
	M-307	M-406	M-407				S-757	S-855E



Breathing Tubes			
	BT-20S/BT-20L Lightweight Breathing Tube (Short/Long)	BT-30 Length Adjusting Breathing Tube	BT-40 Heavy Duty Breathing Tube

Powered Air Turbo		
	TR-302E+ Powered Air Turbo	TR-315E+ Starter Kit*

Filters			
	TR-3712E Particulate Filter	TR-3802E Particulate, Nuisance Odour Organic Vapour Filter**	TR-3822E Particulate, Nuisance Odour Acid Gas Filter***




Batteries	
	TR-332 High Capacity Battery


Backpacks / Belts				
	BPK-HD Backpack	TR-325 Standard Belt	TR-326 High Durability Belt	TR-327 Easy Clean Belt

Battery Chargers		
	TR-341E/TR-341UK Single Station Battery Charger Kit	TR-344E/TR-344UK 4-Station Battery Charger Kit

Covers	
	TR-381 Powered Air Cover

*Starter Kit Includes	TR-315E+
TR-302E+ Powered Air Turbo Unit	x
TR-3712E Particulate Filter	x
TR-341E/TR-341UK Battery Charger Kit	x
TR-325 Standard Belt	x
TR-332 High Capacity Battery	x
TR-3600 Prefilter	x
TR-362 Spark Arrester	x
TR-971 Air Flow Indicator	x
BT-30 Length Adjusting Breathing Tube	x














Ready Kit		
		
TR-300 ECK Easy Clean Kit	TR-300 HIK Heavy Industry Kit	TR-300 HKL Healthcare Kit

Accessories for use with certain M-Series Helmets	
M-973 Radiant Heat Cover for M-307	
M-975 Radiant Heat Cover for M-407	
M-961 Over-Visor Frame	
BT-927 Breathing Tube Radiant Heat Cover	
M-967 Gold Coated Tinted Over-Visor with UV/IR Protection	
Hearing and Communication Solutions	
MT7V/1 & MT53V/1****	

**Nuisance level describes contaminants below the Occupational Exposure Limit (OEL)
 ***Includes Hydrogen Fluoride protection up to 10 x OEL
 ****Hearing protection must be ordered separately

3M™ VersaFlo™ Powered Air Respirator System, TR-600 Series with Loose Fitting Headtops

Headtops

 M-206	 M-207	 M-306	 S-133S S-133L	 S-333SG S-333LG	 S-433S/S-433L S-533S/S-533L	 S-655	 S-657
 M-307	 M-406	 M-407				 S-757	 S-855E

Breathing Tubes

 BT-20S/BT-20L Lightweight Breathing Tube (Short/Long)	 BT-30 Length Adjusting Breathing Tube	 BT-40 Heavy Duty Breathing Tube
---	---	---

Powered Air Turbo

 TR-602E Powered Air Turbo Unit	 TR-619E Starter Kit**
---	--



Filters/Covers

 TR-6110E A1P Filter	 TR-6130E A1B1E1P Filter	 TR-6310E A2P Filter	 TR-6580E A2B2E2K1HgP Filter	 TR-6710E Particulate Filter	 TR-6820E Particulate plus Nuisance Odour Organic Vapour and Acid Gas***
 TR-6100FC Filter Cover	 TR-6300FC Filter Cover	 TR-6500FC Filter Cover	 TR-6700FC Filter Cover	 TR-6800FC Filter Cover	

Batteries

 TR-630 Standard Battery	 TR-632 High Capacity Battery
---	--



Chargers

 TR-641E/TR-641UK Single Station Battery Charger Kit	 TR-644E/TR-644UK 4-Station Battery Charger Kit
---	--

Backpacks / Belts

 BPK-HD Backpack	 TR-626 High Durability Belt	 TR-627 Easy Clean Belt
---	---	--

Accessories




 TR-655 Backpack Adapter	 TR-653 Cleaning & Storage Kit
---	---



Covers

 TR-681 Powered Air Cover
--

**Starter Kit Includes	TR-619E
TR-602E Powered Air Turbo Unit	x
TR-632 High Capacity Battery	x
BT-30 Length Adjusting Breathing Tube	x
TR-627 Easy Clean Belt	x
TR-971 Airflow Indicator	x
TR-6310E A2P Filter	x
TR-6300FC Filter Cover	x
TR-641E/TR-641UK Single Station Battery Charger Kit	x
TR-6600 Prefilter	x
TR-662 Spark Arrestor	x







































Ready Kit

 TR-600 HKL Healthcare Kit	 TR-600 HIK Heavy Industry Kit	 TR-600 ECK Easy Clean Kit
---	---	---




Accessories for use with certain M-Series Helmets	
M-973 Radiant Heat Cover for M-307	
M-975 Radiant Heat Cover for M-407	
M-961 Over-Visor Frame	
BT-927 Breathing Tube Radiant Heat Cover	
M-967 Gold Coated Tinted Over-Visor with UV/IR Protection	
Hearing and Communication Solutions	
MT7V/1 & MT53V/1****	

*BT-30 not approved for use with M-406/M-407 and TR-600 Powered Air Respirator System.
 ***Nuisance level describes contaminants below the Occupational Exposure Limit (OEL).
 Includes Hydrogen Fluoride protection up to 10 x OEL.
 ****Hearing protection must be ordered separately.

3M™ Versaflo™ Intrinsically Safe Powered Air Respirator System, TR-800 Series with Loose Fitting Headtops


Headtops	 M-206	 M-207	 M-306	 S-133S S-133L	 S-333SG S-333LG	 S-433S/S-433L S-533S/S-533L	 S-655	 S-657
	 M-307	 M-406	 M-407				 S-757	 S-855E
Breathing Tubes	 BT-20S/BT-20L Lightweight Breathing Tube (Short/Long)	 BT-30 Length Adjusting Breathing Tube	 BT-40 Heavy Duty Breathing Tube					
Powered Air Turbo	 TR-802E Intrinsically Safe Powered Air Turbo Unit		 TR-819E Intrinsically Safe Powered Air Starter Kit*					
Filters/Covers	 TR-6110E A1P Filter	 TR-6130E A1B1E1P Filter	 TR-6310E A2P Filter	 TR-6580E A2B2E2K1HgP Filter	 TR-6710E Particulate Filter	 TR-6820E Particulate plus Nuisance Odour Organic Vapour and Acid Gas**		
	 TR-6100FC Filter Cover	 TR-6300FC Filter Cover	 TR-6500FC Filter Cover	 TR-6700FC Filter Cover	 TR-6800FC Filter Cover			
Batteries	 TR-830 Battery, Intrinsically Safe with TR-838 Battery Removal Tool							
			Chargers		 TR-641E/TR-641UK Single Station Battery Charger Kit			 TR-644E/TR-644UK 4-Station Battery Charger Kit
Backpacks / Belts	 BPK-HD Backpack	 TR-626 High Durability Belt	 TR-627 Easy Clean Belt					
Accessories	 TR-655 Backpack Adapter		 TR-653 Cleaning & Storage Kit					
			Covers					
		 TR-681 Powered Air Cover						

*Starter Kit Includes	TR-819E
TR-802E Intrinsically Safe Powered Air Turbo Unit	x
TR-830 Battery, Intrinsically Safe	x
TR-838 Battery Attachment Tool	x
BT-30 Length Adjusting Breathing Tube	x
TR-627 Easy Clean Belt	x
TR-971 Airflow Indicator	x
TR-6310E A2P Filter	x
TR-6300FC Filter Cover	x
TR-641E/TR-641UK Single Station Battery Charger Kit	x
TR-6600 Prefilters	x

Ready Kit		
 TR-800 PSK Paint Spray Kit	 TR-800 HIK Heavy Industry Kit	 TR-800 ECK Easy Clean Kit


**Nuisance level describes contaminants below the Occupational Exposure Limit (OEL). Includes Hydrogen Fluoride protection up to 10 x OEL.

3M™ VersaFlo™ Powered Air Respirator Systems with Tight Fitting Facepieces



*Nuisance level describes contaminants below the Occupational Exposure Limit (OEL). Includes Hydrogen Fluoride protection up to 10 x OEL.

3M™ Powered Air Respirator System, PF-600E+ Series with Loose Fitting Headtops and Tight Fitting Facepieces



*Starter Kit Includes	PF-619E+
PF-602E+ Turbo with Integrated Battery, PF-930	x
PF-641E Battery Charger	x
SS-626 Comfort Belt	x
PF-972 Airflow Indicator	x
BT-30 Length Adjusting Breathing Tube	x
2 x DT-1135E P Filters	x
2 x SS-6601 Pre-Filters and Holders	x

Ready Kit

PF-600E+-LIK
Light Industry Kit

Accessories for use with certain M-Series Helmets	
M-973 Radiant Heat Cover for M-307	
M-975 Radiant Heat Cover for M-407	
M-961 Over-Visor Frame	
BT-927 Breathing Tube Radiant Heat Cover	
M-967 Gold Coated Tinted Over-Visor with UV/IR Protection	
Hearing and Communication Solutions	
MT7V/1 & MT53V/1***	

** A1 gas classification on relevant filters. Hg filters only approved with TH3 and TM3 systems. DT-4031E, DT-4032E, DT-4035E, DT-4045E, DT-4036E and DT-4046E are not approved for use with the 3M™ Powered Air Turbo PF-602E+ connected to the 3M™ Full Facepiece Resuable Respirator FF-600 Series.
***Hearing protection must be ordered separately.

3M™ Powered Air Respirator System, PF-600E-ASB Series with Tight Fitting Facepieces

Facepiece




**FF-301 (S)
FF-302 (M/L)**
Full Facepiece




**FF-601 (S)
FF-602 (M)
FF-603 (M/L)**
Full Facepiece

Breathing Tubes



SC-BT-56-ASB
Breathing Tube (80cm)



SC-BT-56-ASB-L
Breathing Tube (100cm)

Powered Air Turbo



PF-602E-ASB
Powered Air Turbo Unit



PF-619E-ASB
Starter Kit*

*Starter Kit Includes	PF-619E-ASB
PF-602E-ASB Turbo with Integrated Battery (PF-930)	x
PF-972 Airflow Indicator	x
SC-327 Belt	x
PF-641E Battery Charger	x
SC-BT-56-ASB Breathing Tube	x
2 x DT-1135E P Filters	x
2 x SS-6601 Prefilters & Holders	x
PF-653 Shower Plugs	x

Filters**



DT-1135E
(P R SL Protection)
Particulate Filter



DT-1235E
(P R SL Protection)
Particulate Filter Reduced Opening



DT-4031E
(A1 P R SL Protection) Combinator
Filter




DT-4032E
(B2 P R SL Protection) Combinator
Filter



DT-4035E
(A1B2 P R SL Protection)
Combinator Filter



DT-4036E
(A1B2E1 P R SL Protection)
Combinator Filter



DT-4045E
(A1B2E2K2 P R SL Protection)
Combinator Filter



DT-4046E
(A1B2E2K2Hg P R SL Protection)
Combinator Filter

Belts



SC-327
Wipe Clean Belt

Battery Charger



PF-641E
Battery Charger

Ready Kits



PF-600E-ASB-FF-302



**PF-600E-ASB-FF-601
PF-600E-ASB-FF-602
PF-600E-ASB-FF-603**

**A1 gas classification on relevant filters. Hg filters only approved with TM3 systems. DT-4031E, DT-4032E, DT-4035E, DT-4045E, DT-4036E and DT-4046E are not approved for use with the 3M™ Powered Air Turbo PF-602E-ASB connected to 3M™ Full Facepiece Reusable Respirator FF-600 Series.

Respiratory Protection

Powered Air Respirator Systems

3M™ Versaflo™ Powered Air Respirator Systems TR-300+ Series

3M™ Versaflo™ Powered Air Turbo Unit TR-302E+ is slim, lightweight and well-balanced, with two selectable flow rate options of 185 l/min and 205 l/min. Our unit has an intelligent lithium ion battery and charge indicator and features visual and audible alarms to signal low air flow and low battery levels.

- Combines with 3M™ Versaflo™ components to build a complete system
- Respiratory protection against dusts, mists, fumes and other particulate hazards, and nuisance-level organic vapour and acid gas
- Versatile and easy-to use



Product ID	Part Number	Product Name	MOQ	OU
7100098846	TR-302E+	3M™ Versaflo™ Powered Air Respirator System, TR-302E+	1	Each

Focus

3M™ Versaflo™ Powered Air Respirator Starter Kits TR-300+ Series

3M™ Versaflo™ Powered Air System TR-300+ combines performance, protection and functionality with modern, stylish, lightweight design and unrivalled comfort. It is the key to easy-to-use, versatile respiratory protection for particulate environments.

3M™ Versaflo™ Powered Air Starter Kit TR-315+ contains TR-302E+ Turbo Unit, Particle Filter, Pre-Filter, Spark Arrestors, Standard Belt, High Capacity Battery, Battery Charger Kit and length adjusting Breathing Tube. Simply add your 3M™ Versaflo™ Headtop for complete respiratory protection.

- Simple starter kit with all the component parts to get you up and running. Simply add the headtop required
- Easy to use, versatile respiratory protection against dusts, mists, fumes and other particulate hazards
- Kit includes Turbo Unit TR-302E+, particulate filter, pre-filter, high-capacity battery, battery charger, length-adjusting breathing tube, air flow indicator, standard belt and spark arrestor



Product ID	Part Number	Product Name	MOQ	OU
7100098908	TR-315E+	3M™ Versaflo™ Powered Air Respirator Starter Kit, TR-315E+	1	Each

Respiratory Protection

Focus

3M™ Versaflo™ Powered Air Respirator System Ready to Use Kits TR-300+ Series

For a simple, convenient way to purchase 3M™ Versaflo™ Powered Air Respirator, TR-300+ Series, choose 3M™ Versaflo™ Powered Air Respirator System, TR-300+ Series Ready to Use Kits.



Whether you're working in heavy industry applications, healthcare settings or require an easy clean solution, 3M™ Versaflo™ TR-300+ Series Ready to Use Kits are built for environments containing particulates. Each one of these kits come equipped with everything your team needs to get started, including a 3M Versaflo™ Headtop, Helmet or Hood.

- The TR-300E+-EC: For use in operations where it is important to be able to easily clean the powered respirator system
- The TR-300E+-HIK: For use in rugged industrial environments requiring integrated head protection
- TR-300E+-HKL: for use in healthcare settings

Product ID	Part Number	Product Name	MOQ	OU
7100233764	TR300EECK	3M™ Versaflo™ Powered Air Respirator System Easy Clean Ready Kit, TR-300E+ ECK	1	Each
7100233765	TR300EHKL	3M™ Versaflo™ Powered Air Respirator System Healthcare Ready Kit, TR-300E+ HKL	1	Each
7100233767	TR300EHIK	3M™ Versaflo™ Powered Air Respirator System Heavy Industry Ready Kit, TR-300E+ HIK	1	Each

3M™ Versaflo™ Powered Air Respirator Filters TR-300+ Series

3M™ Versaflo™ Powered Air Respirator Filters, TR-300+ Series provide protection against dusts, mists and other particulate hazards when use with 3M™ Versaflo Powered Air Respirator, TR-300 Series and a 3M™ approved headtop.



- TR-3712E - Particulate (P) filter for protection against dusts, mists, fumes and other particulate hazards
- TR-3802E - Particulate (P) filter for protection against dusts, mists, fumes and other particulate hazards + nuisance level Organic Vapours (concentrations below the occupational exposure limit)
- TR-3822E - Particulate (P) filter for protection against dusts, mists, fumes and other particulate hazards + nuisance level Acid Gases (concentrations below the occupational exposure limit). Protection against Hydrogen Fluoride up to 10 x Threshold Limit Value

Product ID	Part Number	Product Name	MOQ	OU
7100018861	TR-3822E	3M™ Versaflo™ Powered Air Respirator Particulate & Nuisance Level, Acid Gas Filter, TR-3822E	5	Each
7100018809	TR-3802E	3M™ Versaflo™ Powered Air Respirator Particulate & Nuisance Organic Vapour Filter, TR-3802E	5	Each
7100266123	TR-3712EN	3M™ Versaflo™ Powered Air Respirator Particulate Filter, TR-3712E	5	Each

Respiratory Protection

3M™ Versaflo™ Powered Air Respirator Systems TR-600 Series

3M™ Versaflo™ Powered Air Turbo Unit TR-602E has three selectable flow rates and visual, vibratory and audible alarms that show you low battery and low air flow. The unit also has battery charge, airflow and particulate filter loading status indicators. Our powered air turbo can be temporarily submerged in water when using the appropriate kit to aid cleaning. The unit also has a choice of batteries; standard and high capacity and a choice of belt types; easy clean or high durability.



- Combines with 3M™ Versaflo™ components to build a complete system
- Three selectable flow rates (185 l/min, 205 l/min or 225 l/min) for maximum comfort with a steady airflow
- Visual, vibratory and audible warning alarms show you low battery and low air flow

Product ID	Part Number	Product Name	MOQ	OU
7100259576	TR-602E	3M™ Versaflo™ Powered Air Respirator System, TR-602E	1	Each

Focus

3M™ Versaflo™ Powered Air Respirator Starter Kits TR-600 Series

3M™ Versaflo™ Powered Air Turbo Starter Kit, TR-619E is our ready-to-use kit for respiratory protection against particles, gases and vapours. It comes with everything you need to get started including powered air turbo TR-602E, A2P filter, filter cover, pre-filters, spark arrestors, easy clean belt, high capacity battery, single station battery charger kit, BT-30 length adjusting breathing tube and an airflow indicator. Simply add your 3M™ Versaflo™ Headtop for complete respiratory protection.



- Simple starter kit with all the component parts to get you up and running. Simply add the headtop required
- Easy to use, versatile respiratory protection against dusts, mists, fumes and organic vapours
- Kit includes Turbo Unit TR-602E, A2P filter, filter cover, pre-filters, spark arrestors, easy clean belt, high capacity battery, single station battery charger kit, BT-30 length adjusting breathing tube and airflow indicator

Product ID	Part Number	Product Name	MOQ	OU
7100053532	TR-619E	3M™ Versaflo™ Powered Air Respirator Starter Kit, TR-619E	1	Each

Respiratory Protection

Focus

3M™ Versaflo™ Powered Air Respirator System Ready to Use Kits TR-600 Series

For a simple, convenient way to purchase 3M™ Versaflo™ Powered Air Respirators, TR-600 Series choose 3M™ Versaflo™ TR-600 Series Ready to Use Kits.



Whether you're working in heavy industry applications, healthcare settings or require an easy clean solution, 3M™ Versaflo™ TR-600 Series Ready to Use Kits are built for environments containing particulate, gas and vapour hazards. Each one of these kits come equipped with everything your team needs to get started, including a 3M Versaflo™ Headtop, Helmet or Hood.

- TR-600E-ECK: For use in operations where it is important to be able to easily clean the powered air respirator system
- TR-600E-HKL : For use in healthcare operations
- TR-600E-HIK: For use in heavy duty industrial applications

Product ID	Part Number	Product Name	MOQ	OU
7100258808	TR600EECK	3M™ Versaflo™ Powered Air Respirator System Easy Clean Ready Kit, TR-600E ECK	1	Each
7100258810	TR-600E HKL	3M™ Versaflo™ Powered Air Respirator System Healthcare Ready Kit, TR-600E HKL	1	Each
7100258809	TR-600E HIK	3M™ Versaflo™ Powered Air Respirator System Heavy Industry Ready Kit, TR-600E HIK	1	Each

Focus

3M™ Versaflo™ Intrinsically Safe Powered Air Respirator Starter Kits TR-800 Series

3M™ Versaflo™ Intrinsically Safe Powered Air Turbo Starter Kit TR-819E is our handy kit that's approved to Zone 0 requirements and so may be suitable for areas where potentially explosive atmospheres are expected and permanent within normal operations. It's ready-to-use and has everything you need to get started. The TR-819E kit is approved for use with a wide range of Versaflo™ Soft Headtops S Series and Rigid Headtops M Series, and is ATEX certified and CE approved.



- Convenient ready-to-use kit
- Approved for use with a wide range of Versaflo™ Soft Headtops S Series and Rigid Headtops M Series
- Includes a rechargeable standard capacity lithium Ion battery

Product ID	Part Number	Product Name	MOQ	OU
7100169180	TR-819E	3M™ Versaflo™ Intrinsically Safe Powered Air Turbo Starter Kit, TR-819E	1	Each

Respiratory Protection

Focus

3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System Ready to Use Kits TR-800 Series



For a simple, convenient way to purchase 3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator, choose 3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System, TR-800 Series Ready to Use Kits. Whether you're mixing and granulating compounds in a pharmaceutical facility, working with combustible gases in the oil and gas industry or working in painting and coating applications, 3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System, TR-800 Series Ready to Use Kits are built for environments where intrinsically safe (IS) equipment is essential. Each one of these kits come equipped with everything your team needs to get started.

- Compatible with particulate filters or gas and vapor combination cartridges for protection in a variety of environments
- Battery includes a bumper to absorb impact; mechanical attachment of the battery helps prevent removal during use
- Work at your own speed - Multiple airflow rates put you in control of your comfort

Product ID	Part Number	Product Name	MOQ	OU
7100233763	TR800EECK	3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System Easy Clean Kit, TR-800E ECK	1	Each
7100233766	TR800EHIK	3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System Heavy Industry Kit, TR-800E HIK	1	Each
7100233732	TR800EPSK	3M™ Versaflo™ Intrinsicly Safe Powered Air Respirator System Paint Spray Kit, TR-800E PSK	1	Each

3M™ Versaflo™ Powered Air Respirator Filters TR-600 & TR-800 Series



3M™ Versaflo™ Powered Air Respirator Filters, TR-600 & TR-800 Series is our range of filters for use with 3M™ Versaflo™ Powered Air Respirators TR-600 & TR-800 Series and a 3M™ approved headtop, hood or facepiece. Filters are available in a range of options covering particulate only hazards, or for hazards containing a combination of gas, vapour and particulates.

- Designed for use with 3M™ Versaflo™ Powered Air Turbo TR-600 and TR-800 series
- TR-6710E - Particulate (P) filter for protection against dusts, mists, fumes and other particulate hazards.
- TR-6820E - Particulate (P) filter for protection against dusts, mists, fumes and other particulate hazards + nuisance level Acid Gases (concentrations below the occupational exposure limit). Protection against Hydrogen Fluoride up to 10 x Threshold Limit Value
- TR-6110E - A1P - For protection against organic vapours, dusts, mists, fumes and particulates.
- TR-6130E - ABE1P - For protection against organic vapours, inorganic vapours, acid gases, dusts, mists, fumes and particulates.
- TR-6310E - A2P - For protection against organic vapours, dusts, mists, fumes and particulates

Product ID	Part Number	Product Name	MOQ	OU
7100020996	TR-6110E	3M™ Versaflo™ Powered Air Respirator A1P Filter, TR-6110E	5	Each
7100020998	TR-6310E	3M™ Versaflo™ Powered Air Respirator A2P Filter, TR-6310E	5	Each
7100020997	TR-6130E	3M™ Versaflo™ Powered Air Respirator ABE1P Filter, TR-6130E	1	Each
7100020999	TR-6580E	3M™ Versaflo™ Powered Air Respirator ABE2K1HgP Filter, TR-6580E	5	Each
7100020995	TR-6820E	3M™ Versaflo™ Powered Air Respirator Particulate & Nuisance Odour Filter, TR-6820E	5	Each
7100020971	TR-6710E	3M™ Versaflo™ Powered Air Respirator Particulate Filter, TR-6710E	5	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Respiratory Protection

3M™ Powered Air Respirator System PF-600E+ Series

3M™ Powered Air Respirator System PF-600E+ Series is a durable powered air respirator system designed for heavy duty environments at an affordable price.



- Durable and economical powered air respirator system
- Compatible with the 3M™ DT Series filters and specific 3M™ Versaflo™ headtops
- Automatic monitoring feature checks that the unit is operating as designed, warns the user of low battery and compensates for changes in filter resistance (i.e. as the filter loads with particulate)

Product ID	Part Number	Product Name	MOQ	OU
7100299964	PF-619E+	3M™ Powered Air Respirator System Starter Kit, PF-619E+	1	Each
7100293325	PF-602E+	3M™ Powered Air Respirator, PF-602E+	1	Each

3M™ Powered Air Respirator System Ready to Use Kits PF-600E+ Series

3M™ Powered Air Respirator System PF-600E+ Ready to Use Kits are a convenient and economical way to purchase powered air systems. Ready to Use Kits include a turbo unit, headtop, and accessories including battery, charger and belt.



- Designed for a variety of heavy duty environments at an affordable price
- Ready to Use Kit include a 3M™ PF-602E+ turbo unit, headtop, particulate filters, charger and belt
- Compatible with the 3M™ DT Series filters and specific 3M™ Versaflo™ headtops

Product ID	Part Number	Product Name	MOQ	OU
7100290789	PF-600E+LIK	3M™ Powered Air Respirator System Light Industry Ready Kit, PF-600E+ LIK	1	Each

3M™ Powered Air Respirator System PF-600-ASB Series

3M™ Powered Air Respirator System PF-600-ASB Series is a durable powered air respirator system, designed for heavy duty environments including Asbestos applications.



- Powered Air Respirator designed for Asbestos Removal applications
- Compatible with 3M™ Resuable Respirators FF-300 and FF-600
- PF-602E-ASB turbo is also approved with loose fitting 3M™Versaflo™ M-200 and M-300 range of helmets

Product ID	Part Number	Product Name	MOQ	OU
7100295035	PF-600E-ASB-FF-302	3M™ Powered Air Respirator System Asbestos Kit, PF-600E-ASB-FF-302	1	Each
7100293327	PF-600E-ASB-FF-601	3M™ Powered Air Respirator System Asbestos Kit, PF-600E-ASB-FF-601	1	Each
7100293329	PF-600E-ASB-FF-602	3M™ Powered Air Respirator System Asbestos Kit, PF-600E-ASB-FF-602	1	Each
7100293328	PF-600E-ASB-FF-603	3M™ Powered Air Respirator System Asbestos Kit, PF-600E-ASB-FF-603	1	Each
7100293330	PF-619E-ASB	3M™ Powered Air Respirator System Starter Kit, PF-619E-ASB	1	Each
7100293324	PF-602E-ASB	3M™ Powered Air Respirator, PF-602E-ASB	1	Each

Respiratory Protection

3M™ Powered Air Respirator System PV-300 Series

3M™ Powered Air Respirator System PV-300 Series is a durable powered air respirator system kit featuring a face-mounted motor for use in heavy duty environments including Asbestos applications. This kit includes PV-300E respirator system comprising full facepiece, motor unit, filter, battery and belt



- Powered Air Respirator designed for Asbestos Removal applications
- Features a mask mounted motor and waist mounted battery
- IP 54 rating with filter fitted to the filter port, suitable for cleaning by showering / water spray

Product ID	Part Number	Product Name	MOQ	OU
7100265026	PV-300E-L	3M™ Powered Air Respirator System Asbestos Kit PV-300E-L, 1 Each/Case	1	Each
7100265033	PV-300E-M	3M™ Powered Air Respirator System Asbestos Kit PV-300E-M, 1 Each/Case	1	Each
7100265016	PV-300E-S	3M™ Powered Air Respirator System Asbestos Kit PV-300E-S, 1 Each/Case	1	Each

Respiratory Protection

Supplied Air Respirator Systems

3M™ Supplied Air Filters V-500 Series

Replacement filters for the 3M™ Versaflo™ Supplied Air Regulator V-500 with ,O' Rings.



- Replacement odour filter and O rings
- Designed for use with 3M™ Versaflo™ Supplied Air System V-500E
- Filter helps remove residual odours in the supplied air line

Product ID	Part Number	Product Name	MOQ	OU
7000042672	0230551P	3M™ V-500E Odour Filter Pack, 023-05-51P	1	Pack

3M™ Supplied Air Respirator Systems S200+ Series

3M™ Versaflo™ S-200+ Supplied Air System is our supplied air system which provides respiratory protection against particles, gases and vapours, and combination hazards when used with an approved 3M face mask.



- For use with 3M™ Full Facepiece Respirator 6000 Series and 3M™ Half Face Mask 7500 Series
- Provides protection against particles like fine dusts, aerosols, paint spray or metal fume; gases and vapours; and combined hazards
- System provides constant flow of air across the face for maximum user comfort

Product ID	Part Number	Product Name	MOQ	OU
7000144498	S200+	3M™ Supplied Air Respirator System, S-200+	1	Each

3M™ Scott™ RAS Asbestos Airline Breathing Apparatus

3M™ Scott™ RAS (Respiratory Airline Supply) Asbestos airline breathing apparatus set is a positive pressure set that provides the highest levels of breathing protection. The RAS Asbestos apparatus is ideal for areas with high levels of contamination.



- Developed to meet the needs of the asbestos removal and stripping industry
- Ideal for areas with high levels of contamination
- Highest level of breathing protection with an assigned protection factor of 2000

Product ID	Part Number	Product Name	MOQ	OU
7100265060	RAS-930-L	3M™ Full Facepiece RAS-930-L for RAS-ASB, 4 Each/Case	4	Each
7100265048	RAS-930-S	3M™ Full Facepiece RAS-930-S for RAS-ASB, 4 Each/Case	4	Each
7100265049	RAS-931-S	3M™ Full Facepiece RAS-931-S for RAS-ASB, 4 Each/Case	4	Each
7100265036	RAS-931-L	3M™ Full Facepiece Respirator RAS-931-L for RAS-ASB, 4 Each/Case	4	Each
7100265028	RAS-931-M	3M™ Full Facepiece Respirator RAS-931-M for RAS-ASB, 4 Each/Case	4	Each
7100265238	RAS-ASB	3M™ Supplied Air Respirator Bandolier Assembly RAS-ASB, 1 Each/Case	1	Each
7100265034	RAS-ASB-M	3M™ Supplied Air Respirator System Asbestos Kit RAS-ASB-M, 1 Each/Case	1	Each
7100265035	RAS-ASB-S	3M™ Supplied Air Respirator System Asbestos Kit RAS-ASB-S, 1 Each/Case	1	Each

Respiratory Protection

Hoods & Headgear

3M™ Versaflo™ Faceshields M-200 Series

3M™ Versaflo™ Faceshields, M-200 Series feature lightweight, compact and well-balanced faceshield that can offer integrated protection from a range of respiratory, head, eye, face and hearing hazards (when used with optional hearing protection). It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.

- Highly versatile, integrated protection from a range of respiratory, face, eye, hearing and head hazards
- Lightweight, compact and well-balanced faceshield with a choice of face seals including comfort face seal or flame resistant polyester face seal
- Fully-adjustable suspension that includes textile harness for correct fit and weight distribution



Product ID	Part Number	Product Name	MOQ	OU
7100258667	M-206	3M™ Versaflo™ Faceshield with Comfort Face Seal, M-206	1	Each
7100256071	M-207	3M™ Versaflo™ Faceshield with Flame Resistant Poly Face Seal, M-207	1	Each

Focus

3M™ Versaflo™ Helmets M-300 Series

3M™ Versaflo™ Helmets, M-300 Series feature lightweight, compact and well-balanced helmets that can offer integrated protection from a range of respiratory, head, eye, face and hearing hazards, making it suitable for use on construction sites. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.

- Highly versatile, integrated protection from a range of respiratory, head (EN397), eye and face (EN166 medium energy impact), and hearing hazards
- Lightweight, compact and well-balanced helmet providing head protection approved according to EN397
- Fully-adjustable suspension that includes textile harness for optimal fit and weight distribution



Product ID	Part Number	Product Name	MOQ	OU
7100257937	M-306	3M™ Versaflo™ Helmet with Comfort Face Seal, M-306	1	Each
7100257936	M-307	3M™ Versaflo™ Helmet with Flame Resistant Face Seal, M-307	1	Each

3M™ Versaflo™ Helmets with Shroud M-400 Series

3M™ Versaflo™ Helmets with Shroud, M-400 Series offer integrated protection from a range of respiratory, head, eye and face with additional neck and shoulder coverage. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.

- Shroud options include Nylon for construction applications and heavy industry or Flame Resistant Polyaramid for applications with hot particles
- Versatile protection against a range of respiratory, head (EN397), eye and face hazards (EN166 medium impact)
- Lightweight, compact and well-balanced design



Product ID	Part Number	Product Name	MOQ	OU
7100258668	M-407	3M™ Versaflo™ Helmet with Flame Resistant Shroud, M-407	1	Each
7000104037	M-406	3M™ Versaflo™ Helmet with Highly Durable Shroud, M-406	1	Each

Respiratory Protection

3M™ Versaflo™ Integrated Suspension Head Covers S-100 Series

3M™ Versaflo™ Integrated Suspension Head Cover, S-100 Series is our head cover with integrated head suspension for full head and face coverage, as well as eye and face protection. Our head cover is the entry-level, cost-effective head cover for powered and supplied air respiratory protection. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.



- Entry-level, general-purpose head cover for powered and supplied air respiratory protection
- Integrated head suspension provides head and face coverage
- Provides face and eye protection from liquid splash and low energy flying particles and dust (Grade F)

Product ID	Part Number	Product Name	MOQ	OU
7000000142	S-133L	3M™ Versaflo™ Integrated Suspension Head Cover, Large, S-133L	1	Each
7000044300	S-133S	3M™ Versaflo™ Integrated Suspension Head Cover, Small, S-133S	1	Each

3M™ Versaflo™ Integrated Suspension High Durability Head Covers S-300 Series

3M™ Versaflo™ High Durability Headcover, S-300 Series is our high durability head cover with an integrated head suspension for full head and face coverage, as well as eye and face protection. Our head cover is manufactured using soft, quiet, low-linting fabric for high levels of comfort. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.



- Integrated head suspension provides head and face coverage
- Protects face and eyes from liquid splash and low energy flying particles and dust (Grade F)
- Manufactured using durable, soft, low-linting fabric for user comfort

Product ID	Part Number	Product Name	MOQ	OU
7000000144	S-333LG	3M™ Versaflo™ Integrated Suspension High Durability Head Cover, Large, S-333LG	1	Each
7000044301	S-333SG	3M™ Versaflo™ Integrated Suspension High Durability Head Cover, Small, S-333SG	1	Each

3M™ Versaflo™ Integrated Suspension Hoods S-400 Series

3M™ Versaflo™ Integrated Suspension Hood, S-400 Series is our head cover with integrated head suspension which provides head, face, neck and shoulder coverage as well as providing eye and face protection from liquid splash and low energy flying particles and dust. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.



- Integrated head suspension provides head, face, neck and shoulder coverage
- Protects face and eyes from liquid splash and low energy flying particles and dust (Grade F)
- Suitable for applications which require frequent replacement of the entire headtop assembly or those where there is less soiling of the outer fabric

Product ID	Part Number	Product Name	MOQ	OU
7000000145	S-433L	3M™ Versaflo™ Integrated Suspension Hood, Large, S-433L	1	Each
7000044302	S-433S	3M™ Versaflo™ Integrated Suspension Hood, Small, S-433S	1	Each

Respiratory Protection

3M™ Versaflo™ Integrated Suspension Hoods S-500 Series

The 3M™ S-Series High Durability Hood S-500 Series with integrated head suspension and face seal is similar to the S-400 Series but with a more durable, soft, quiet, low-linting fabric that more readily drapes comfortably over the wearer.

- Integrated head suspension provides head, face, neck and shoulder coverage
- Protects face and eyes from liquid splash and low energy flying particles and dust (Grade F)
- Manufactured using durable, soft, low-linting fabric for user comfort



Product ID	Part Number	Product Name	MOQ	OU
7000000147	S-533L	3M™ Versaflo™ S-Series High Durability Hood, Large, S-533L	1	Each
7100011287	S-533S	3M™ Versaflo™ S-Series High Durability Hood, Small, S-533S	1	Each

3M™ Versaflo™ Premium Hoods with Reusable Suspension S-600 Series

3M™ Versaflo™ Premium Hoods with Reusable Suspension, S-600 Series offer combined head, hair, neck and shoulder coverage. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.

- Provides head, hair, neck and shoulder coverage
- Protects eyes and face from liquid splash and low energy flying particles and dust (Grade F)
- Hood fabric: 2-layer polypropylene spunbond/laminated film



Product ID	Part Number	Product Name	MOQ	OU
7000000149	S-60510	3M™ Versaflo™ Premium Replacement Hood S-655 with Inner Shroud, S-605	10	Pack
7000000151	S-60710	3M™ Versaflo™ Premium Replacement Hood S-657 with Inner Shroud, S-607	10	Pack
7100079871	S-657	3M™ Versaflo™ Premium Replacement Hood with Double Shroud, S-657	1	Each
7100079870	S-655	3M™ Versaflo™ Premium Replacement Hood with Inner Collar, S-655	1	Each

3M™ Versaflo™ Painter's Hoods S-700 Series

3M™ Versaflo™ Painters Hoods S-700 Series offer combined head, hair, neck and shoulder coverage with a fabric designed to help capture paint overspray. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.

- Designed to help capture paint overspray and minimises the potential for paint to flake onto the work piece
- Inner shroud minimises the risk of paint coming into contact with skin or clothes
- Reusable premium inner head suspension can be a cost-effective solution for high disposal rate environments



Product ID	Part Number	Product Name	MOQ	OU
7000027992	S-707	3M™ Versaflo™ Painter's Hood S-757 with Inner Shroud, S-707	10	Each
7100079872	S-757	3M™ Versaflo™ Painter's Hood, S-757	1	Each

Respiratory Protection

3M™ Versaflo™ Premium Hoods with Reusable Suspension and Sealed Seams S-800 Series

3M™ Versaflo™ Premium Hood with Reusable Suspension, Sealed Seams, S-800 Series is our hood specifically developed for liquid chemical splash environments. It can be used with 3M™ Powered Air Respirators and Supplied Air Respirator Systems in a wide variety of applications.



- Replaceable overhead developed for liquid chemical splash environments
- Protects eyes and face from liquid splash and low energy flying particles and dust (Grade F)
- Manufactured from chemically resistant fabric with sealed seams

Product ID	Part Number	Product Name	MOQ	OU
7100079874	S-855E	3M™ Versaflo™ Premium Hood with Sealed Seam, Single Size, S-855E	1	Each
7100079873	S-805E-5	3M™ Versaflo™ Premium Replacement Hood with Sealed Seams and Inner Collar, S-805-5	5	Each

3M™ Powered Air Respirator System Hoods

3M™ Hood with Inner Helmet, FH-51 is a durable loose-fitting headtop approved with 3M™ Powered Air Respirator System PF-602E combining respiratory, head, face and eye protection. The hood is intended for use in liquid chemical splash environments and incorporates a helmet which makes it particularly suited for demanding industry environments



- Loose fitting hood with integrated helmet
- Suitable for demanding industry environments
- Hood designed for use in liquid chemical splash environments

Product ID	Part Number	Product Name	MOQ	OU
7100265226	FH-51	3M™ Hood with Inner Helmet, FH-51, 1 Each/Case	1	Each

Respiratory Protection

Powered & Supplied Air Parts & Accessories

3M™ Powered Air Respirator Batteries

Product ID	Part Number	Product Name	MOQ	OU
7100265192	PV-330	3M™ Battery PV-330 for PV-300E Powered Air Respirator, 1 Each/Case	1	Each
7100150925	TR-830	3M™ Versaflo™ Battery TR-830/94243(AAD), Intrinsically Safe for TR-800 PAPR	1	Each
7100005643	TR-332	3M™ Versaflo™ Battery, High Capacity, TR-332	1	Each
7000144502	TR-632	3M™ Versaflo™ Battery, High Capacity, TR-632	1	Each
7000144501	TR-630	3M™ Versaflo™ Battery, Standard, TR-630	1	Each

3M™ Powered Air Respirator Battery Chargers

Product ID	Part Number	Product Name	MOQ	OU
7100264730	PV-341	3M™ Battery Charger PV-341 for PV-300E Powered Air Respirator, 1 Each/Case	1	Each
7100236843	PF641E	3M™ Battery Charger for PF-630 Battery, PF-641E	1	Each
7000103975	TR-344	3M™ Versaflo™ 4-station Battery Charger Kit, UK, TR-344	1	Case
7100020282	TR-644UK	3M™ Versaflo™ Battery Charger, 4- Station, UK, TR-644UK	1	Each
7000103971	TR-340	3M™ Versaflo™ Battery Charging Cradle, TR-340	1	Each
7000144503	TR-640	3M™ Versaflo™ Battery Charging Cradle, TR-640	1	Each
7100007089	TR-341UK	3M™ Versaflo™ Single Station Battery Charger, UK, TR-341UK	1	Each

3M™ Powered Air Respirator Belts & Belt Assemblies

Product ID	Part Number	Product Name	MOQ	OU
7000044238	3010062P	3M™ Belt Assembly, 301-00-62P	5	Each
7000042675	5301253P	3M™ Coupling Plug CEJN 95, 1/4" BSP, Male Thread, 530-12-53P	1	Pack
7100265218	SC-327	3M™ Easy Clean Belt SC-327 for PF-602E-ASB and PV-300E Powered Air Respirators, 1 Each/Case	5	Each
7000044405	835005	3M™ Powered Air Respirator Belt Front Part for Adflo™, 835005	1	Each
7100055314	835000	3M™ Powered Air Respirator Belt for Adflo™, Leather, 835000	1	Each
7100222675	TR-626	3M™ Powered Air Respirator High Durability Belt, Leather, TR-626	1	Each
7100236811	SS625	3M™ Standard Belt for 3M™ Powered Air Respirators PF-602E+ and PF-602E-ASB, SS-625	1	Each
7000103973	TR-327	3M™ Versaflo™ Easy-Clean Belt, TR-327	1	Each
7100222674	TR-627	3M™ Versaflo™ Easy-Clean Belt, TR-627	1	Each
7100006958	TR-325	3M™ Versaflo™ Standard Belt, TR-325	1	Pack
7100236838	SS626	3M™ Comfort Belt for 3M™ Powered Air Respirator PF-602E+, SS-626	4	Each

Respiratory Protection

3M™ Powered Air Respirator Brace & Shoulder Straps

Product ID	Part Number	Product Name	MOQ	OU
7000044317	TR-329	3M™ Versaflo™ Braces, TR-329	1	Pair

3M™ Powered Air Respirator Back Pack Harnesses

Product ID	Part Number	Product Name	MOQ	OU
7100300071	TR-927	3M™ Versaflo™ Easy Clean Backpack, TR-927	1	Each

3M™ Powered Air Respirator Belt Extenders

Product ID	Part Number	Product Name	MOQ	OU
7100135289	TR627X	3M™ Powered Air Respirator Belt Extender for TR-627 Easy Clean Belt, TR-627X	1	Each

3M™ Powered Air Respirator Back Pack Adapters

Product ID	Part Number	Product Name	MOQ	OU
7100035843	TR-655	3M™ Versaflo™ Backpack Adaptor, TR-655	1	Each

3M™ Powered Air Respirator Filter Covers

Product ID	Part Number	Product Name	MOQ	OU
7100080252	838031	3M™ Powered Air Respirator Filter Cover for Adflo™, Black, 838031	1	Carton
7100237883	SS6000FC	3M™ Powered Air Respirator Filter Cover, SS-6607	10	Each
7100099577	TR-371+	3M™ Versaflo™ Filter Cover, TR-371+	1	Bag
7100021248	TR-6100	3M™ Versaflo™ Filter Cover, TR-6100FC	1	Each
7100021336	TR-6300	3M™ Versaflo™ Filter Cover, TR-6300FC	1	Each
7100021252	TR-6500	3M™ Versaflo™ Filter Cover, TR-6500FC	1	Each
7100021251	TR-6700	3M™ Versaflo™ Filter Cover, TR-6700FC	1	Each
7100021247	TR-6800	3M™ Versaflo™ Filter Cover, TR-6800FC	1	Each

3M™ Powered Air Respirator Spark Arrestors

Product ID	Part Number	Product Name	MOQ	OU
7000103970	TR-362E	3M™ Versaflo™ Spark Arrestor, TR-362	1	Each
7100035845	TR-662	3M™ Versaflo™ Spark Arrestor, TR-662	2	Each

Respiratory Protection

3M™ Powered Air Respirator Prefilters

Product ID	Part Number	Product Name	MOQ	OU
7100236853	SS6601	3M™ Powered Air Respirator Prefilter and Prefilter Holder for PF-600E/DF-600E Powered Air Turbo, SS-6601	5	Each
7100236854	SS6600	3M™ Powered Air Respirator Prefilter for PF-600E/DF-600E Powered Air Turbo, SS-6600	100	Each
7100237884	SS6602	3M™ Powered Air Respirator Prefilter for PF-600E/DF-600E Powered Air Turbo, SS-6602	10	Each
7000059880	TR-3600	3M™ Versaflo™ Pre-filter, TR-3600	10	Pack
7100021255	TR-6600	3M™ Versaflo™ Pre-filter, TR-6600	50	Each

3M™ Powered & Supplied Air Breathing Tubes

Product ID	Part Number	Product Name	MOQ	OU
7000144499	S-222	3M™ Breathing Tube, S-222	1	Each
7100265213	SC-BT-56-ASB	3M™ Heavy Duty Breathing Tube SC-BT-56-ASB for PF-602E-ASB, 1 Each/Case	1	Each
7100265025	SC-BT-56-ASB-L	3M™ Heavy Duty Breathing Tube SC-BT-56-ASB-L for PF-602E-ASB, 1 Each/Case	1	Each
7100069524	BT-40	3M™ Versaflo™ Breathing Tube, Heavy Duty, BT-40	1	Each
7000000159	BT-20L	3M™ Versaflo™ Breathing Tube, Lightweight, BT-20L	1	Each
7000000158	BT-20S	3M™ Versaflo™ Breathing Tube, Lightweight, BT-20S	1	Each
7100006955	BT-30	3M™ Versaflo™ Breathing Tube, Self-adjusting, BT-30	1	Each
7100189372	BT-63	3M™ Versaflo™ Tight Fitting Breathing Tube BT-63, Standard	1	Each
7100189597	BT-64	3M™ Versaflo™ Tight Fitting Breathing Tube BT-64, Heavy Duty	1	Each
7100218783	BT54	3M™ Versaflo™ Tight Fitting Breathing Tube, BT-54	1	Each

3M™ Powered & Supplied Air Breathing Tube Covers

Product ID	Part Number	Product Name	MOQ	OU
7000042907	BT-926	3M™ Versaflo™ Breathing Tube Cover, Flame Resistant, BT-926	1	Each
7100099908	BT-927	3M™ Versaflo™ Breathing Tube Radiant Heat Cover, BT-927	1	Each
7000103964	BT-922	3M™ Versaflo™ Disposable Breathing Tube Cover, BT-922	1	Pack

3M™ Powered Air Respirator Radiant Heat Covers

Product ID	Part Number	Product Name	MOQ	OU
7100099853	M-973	3M™ Versaflo™ Radiant Heat Cover, M-973	1	Each
7100099854	M-975	3M™ Versaflo™ Radiant Heat Cover, M-975	1	Each

Respiratory Protection

3M™ Powered Air Respirator Protective Covers

Product ID	Part Number	Product Name	MOQ	OU
7100260719	TR-381	3M™ Versaflo™ PAPR Cover TR-381, for TR-300+ PAPR, 10 EA/Case,	10	Each
7100260718	TR-681	3M™ Versaflo™ PAPR Cover TR-681, for TR-600/800 PAPR, 10 EA/Case	10	Each
7100236812	PF651	3M™ Protective Cover for 3M™ Powered Air Respirator PF-602E+, PF-651	5	Each

3M™ Powered Air Respirator Head Neck & Shoulder Covers

Product ID	Part Number	Product Name	MOQ	OU
7100063882	M-972	3M™ Versaflo™ Flame Resistant Headtop Cover, M-972	1	Each
7100063944	M-976	3M™ Versaflo™ Head, Neck and Shoulder Cover, M-976	1	Each

3M™ Powered Air Respirator Airflow Indicators

Product ID	Part Number	Product Name	MOQ	OU
7100293333	PF-972	3M™ Airflow Indicator for PF-602E+ Powered Air Respirator, PF-972	1	Each
7000103967	TR-970	3M™ Versaflo™ Air Flow Indicator, TR-970	1	Case
7100035846	TR-971	3M™ Versaflo™ Air Flow Indicator, TR-971	1	Each

3M™ Powered & Supplied Air Peel Off Visor Covers & Films

Product ID	Part Number	Product Name	MOQ	OU
7100001829	M-928	3M™ Versaflo™ Peel-Off Visor Cover, M-928	40	Each
7000000156	S-922	3M™ Versaflo™ S Series Peel-Off Visor Cover, Premium Hoods, S-922	4	Bag
7000042683	S-920L	3M™ Versaflo™ S Series Peel-Off Visor Covers, Large, S-920L	40	Each

3M™ Powered & Supplied Air Replacement Visors and Lenses

Product ID	Part Number	Product Name	MOQ	OU
7100063883	M-927	3M™ Versaflo™ Coated Visor, Polycarbonate, M-927	5	Each
7000042917	M-925	3M™ Versaflo™ Visor, Polycarbonate, Uncoated, M-925	5	Each

Respiratory Protection

3M™ Powered & Supplied Air Sweatbands & Comfort Pads

Product ID	Part Number	Product Name	MOQ	OU
7000103918	M-957	3M™ Comfort Pads, M-957	1	Pack
7000042684	S-953	3M™ Versaflo™ Comfort Pad for Premium Hoods, S-953	1	Each
7000042685	M919	3M™ Versaflo™ Size Reducing Comfort Pad, S-954	20	Each
7100064142	M-956	3M™ Versaflo™ Size Reducing Ratchet Comfort Pad, M-956	10	Each

3M™ Versaflo™ Battery Attachment Tools

Product ID	Part Number	Product Name	MOQ	OU
7100150921	TR-838	3M™ Versaflo™ Battery Attachment Tool for TR-800 PAPR and TR-830 Battery, TR-838/94244	1	Each

3M™ Powered Air Respirator Cleaning & Storage Kits

Product ID	Part Number	Product Name	MOQ	OU
7100035841	TR-653	3M™ Versaflo™ Cleaning & Storage Kit, TR-653	1	Each

3M™ Powered Air Respirator Over-Visors

Product ID	Part Number	Product Name	MOQ	OU
7100099909	M-967	3M™ Versaflo™ Over-visor, Gold, IR Shade 5, M-967	1	Each

3M™ Versaflo™ Supplied Air Systems V-Series

Product ID	Part Number	Product Name	MOQ	OU
7000103980	V-100E	3M™ Versaflo™ Supplied Air System, Air Cooling Regulator, V-100E	1	Each
7000103979	V-200E	3M™ Versaflo™ Supplied Air System, Air Heating Regulator, V-200E	1	Each
7100005806	V-500E	3M™ Versaflo™ Supplied Air System, Air Regulator, V-500E	1	Each

3M™ Supplied Air Hoses & Hose Assemblies

Product ID	Part Number	Product Name	MOQ	OU
7000042678	3080040P	3M™ Air Supply Tube, 7.5m, Coiled, 308-00-40P	1	Each
7000042676	3080030P	3M™ Air Supply Tube, Standard Duty, 10m, 308-00-30P	1	Each
7000042677	3080031P	3M™ Air Supply Tube, Standard Duty, 20m, 308-00-31P	1	Each
7000044242	3080072P	3M™ Air Supply Tube, Standard Duty, Anti-Static, Heat Resistant, 10m, 308-00-72P	1	Each

Respiratory Protection

3M™ Powered & Supplied Air Plugs & Plug Assemblies

Product ID	Part Number	Product Name	MOQ	OU
7000044241	5301252P	3M™ Coupling Plug Rectus 25, 1/4" BSP, Male Thread, 530-12-52P	3	Each
7000042674	5301282P	3M™ Coupling Set 3/8" BSP Rectus 25, Female Thread, 530-12-82P	1	Pack
7000042673	5301281P	3M™ Coupling Set 3/8" CEJN 95, Female Thread, 530-12-81P	1	Pack
7100237055	PF653	3M™ Shower Plugs for 3M™ Powered Air Respirators PF-600E+ and PF-600E-ASB, PF-653	5	Each

3M™ Spray Gun Auxiliary Air Supply Hose Kit

Product ID	Part Number	Product Name	MOQ	OU
7000088331	C231	3M™ Auxiliary Air Supply Hose, C-231	1	Kit

3M™ Easy Clean Bandolier for RAS-ASB

Product ID	Part Number	Product Name	MOQ	OU
7100265050	RAS- 327	3M™ Easy Clean Bandolier RAS-327 for RAS-ASB, 1 Each/Case	1	Each

3M™ Supplied Air Respirator System Asbestos Kit

Product ID	Part Number	Product Name	MOQ	OU
7100266045	RAS-ASB-L	3M™ Supplied Air Respirator System Asbestos Kit RAS-ASB-L, 1 Each/Case	1	Each

3M™ Powered Air Respirator Headtop Collars

Product ID	Part Number	Product Name	MOQ	OU
7100137832	M-444	3M™ Versaflo™ Inner Collar, M-444	1	Each

3M™ Powered Air Respirator Headtop Suspensions

Product ID	Part Number	Product Name	MOQ	OU
7100063886	M150	3M™ Versaflo™ Head Suspension, M-150	1	Each
7100063895	M-350	3M™ Versaflo™ Head Suspension, M-350	1	Each

Respiratory Protection

3M™ Powered Air Respirator Shrouds

Product ID	Part Number	Product Name	MOQ	OU
7100137850	M-447	3M™ Versaflo™ Outer Shroud, Flame Resistant, M-447	1	Each
7100137905	M-448	3M™ Versaflo™ Outer Shroud, Heavy Duty, M-448	1	Each

3M™ Powered & Supplied Air Faceseals

Product ID	Part Number	Product Name	MOQ	OU
7100137904	M-936	3M™ Versaflo™ Face seal, Comfort, M-936	5	Each
7100137903	M-937	3M™ Versaflo™ Face seal, Flame Resistant, M-937	5	Each
7100064141	M-935	3M™ Versaflo™ Face seal, Standard, M-935	5	Each

3M™ Powered Air Respirator Muffler Kits

Product ID	Part Number	Product Name	MOQ	OU
7000104061	0230635P	3M™ V-200E Muffler Kit, 023-06-35P	1	Kit

3M™ Versaflo™ Supplied Air System, Air Regulator

Product ID	Part Number	Product Name	MOQ	OU
7100024108	S-212	3M™ Versaflo™ Supplied Air System, Air Regulator, S-212	1	Each



Detection & Monitoring Equipment

Detection & Monitoring Equipment

Monitor Badges

3M™ Organic Vapor Monitor 3500+

3M™ Organic Vapour Monitor 3500+ is a cost-effective and convenient way to perform personal air sampling for many organic vapours.

It is easy to use - clip it to your shirt lapel, collar, or pocket without interfering with your work activities. No batteries, hoses or pumps or needed to use the monitor to sample your air.

- State of the Art Monitor Design
- Simple, cost-effective and convenient
- High sample capacity for sampling a broad range of organic vapours



Product ID	Part Number	Product Name	MOQ	OU
7100249088	3500+	3M™ Organic Vapour Monitor, 3500+	10	Each

3M™ Organic Vapour Monitor 3501+

3M™ Organic Vapour High Sampling Rate Monitor 3501+ is a cost-effective and convenient way to perform personal air sampling for low levels of organic vapours and short term exposure limit (STEL) sampling.

It is easy to use - clip it to your shirt lapel, collar, or pocket without interfering with your work activities. No batteries, hoses or pumps or needed to use the monitor to sample your air.

- State of the Art Monitor Design
- Simple, cost-effective and convenient
- Highest diffusive sampling rate available for monitoring low contaminant levels and STEL sampling



Product ID	Part Number	Product Name	MOQ	OU
7100249097	3501+	3M™ Organic Vapour Monitor, High Sampling Rate, 3501+	5	Each

3M™ Ethylene Oxide Monitor 3551+

3M™ Ethylene Oxide Monitor Badge, 3551 is a lightweight device that collects ethylene oxide gas in the surrounding environment. Our badge is made from a plastic housing that contains a permeable, absorbent membrane which can be lab tested to help you assess the airborne concentration of ethylene oxide.

- Collect and separately analyse ethylene oxide in the workplace environment
- Accuracy of +/-25%, at a 95% confidence level for many workplace contaminants
- Lightweight



Product ID	Part Number	Product Name	MOQ	OU
7100249356	3551+	3M™ Ethylene Oxide Monitor, 3551+	5	Each

■ Detection & Monitoring Equipment

3M™ Formaldehyde Monitor 3721+

3M™ Formaldehyde Monitor 3721+ is a cost-effective and convenient way to perform personal air sampling for formaldehyde and certain other aldehydes.

It is easy to use - clip it to your shirt lapel, collar, or pocket without interfering with your work activities. No batteries, hoses or pumps or needed to use the monitor to sample your air.

- State of the Art Monitor Design
- Simple, cost-effective and convenient
- A valid method for air sampling and analysis of formaldehyde and certain other aldehydes



Product ID	Part Number	Product Name	MOQ	OU
7100251921	3721+	3M™ Formaldehyde Monitor, 3721+	5	Each



Hearing Protection

40 million workers are exposed to loud noise and 13 million suffer from hearing disorders despite industry regulations*. You can advance your hearing conservation programme with a customised and comprehensive approach to the hearing protection challenge. Implementing a solution that really makes a difference begins with understanding the hazards, the regulation and the factors that impact protection.

The real world concerns of hearing protection

Variable Noise Levels: Every environment is different and workers can face a wide range of sound levels throughout the day and in different areas at the same facility.


The Human Factor: Each person has a different shape, size and anatomy of the ear canal, so there is no one-size fits all hearing protection solution. The key to achieving optimal protection is having the best fit possible.

Employee Communication: Where there is an essential need for workers to communicate or hear warning sounds it is vital that their hearing is protected from hazardous noise levels.

What types of sounds require hearing protection?

At home and work, it's important to understand which sounds may cause hearing loss and require hearing protection:

Decibel scale dB(A)



* Source: European Agency for Safety and Health at Work

Ear fit validation

How do you decide what hearing protection you will offer to your workers?

If you are simply using the SNR found on the hearing protection packaging as a guide you may not be providing accurate protection levels for every worker. Ears come in many shapes and sizes and to make sure all workers are getting the protection they need, you need to know their Personal Attenuation Rating (PAR).

Noise-induced hearing loss is 100% preventable.

Why 3M?

As the leader in hearing protection, 3M offers a complete solution, with dual-ear and earmuff testing capabilities plus a user-friendly interface. The 3M™ E-A-Rfit™ Dual-Ear Validation System is the fast and easy way to find your employees' PAR, because we know how important it is to make your hearing conservation program fit seamlessly into your operation.

Learn more: 3M.co.uk/Earfit



What's your PAR?

Every employee is different.
Every job is different.
Every ear is different.

Finding each employee's PAR will help you have assurance that workers' hearing is protected and they are compliant with the law. That's why we made the new 3M™ E-A-Rfit Dual-Ear Validation System fast, accurate and easy.

Fit testing is key

Get results you can trust. The 3M™ E-A-Rfit™ Dual-Ear Validation System measures the effectiveness of the earplug or earmuff inside the employee's ear providing accurate, quantitative results. Because you can simultaneously test both ears, you have more to focus on education including the importance of fit and protection.

1 Fit

Have the employee insert their hearing protection.

2 Test

Connect to microphones and begin speaker test sound.

3 Assess

Use PAR to customise hearing protector selection.



Hear for life.

The importance of hearing
protections performance
and selection.

Personal Protective Equipment used to control exposure to harmful noise needs to be CE approved against the PPE Regulation 2016/425 (EU).

This is typically done by testing the hearing protector
against relevant parts of the Harmonised European
Standard EN 352.


Did you know that the EN 352 family of standards have recently undergone a periodic revision?

3Ms technical experts can help explain how
attenuation testing is performed, the differences
in reporting test results and product performance.
These are some of the key factors to help make an
informed choice on the selection of the right hearing
protection for the job.

















**Download the bulletin
to learn more**

Choose the right passive hearing solution.




Comparison Chart

This comparison chart helps you understand the key differences between 3M's core line passive hearing protectors. Please note that the chart focuses only on a selection of featured hero products. We have a lot more products available, so if you are looking for an alternative product please contact your local 3M representative.

	 3M™ E-A-Rsoft™ Yellow Neons™	 3M™ E-A-R™ Classic™	 3M™ E-A-R™ Classic™ Corded	 3M™ 1100 Earplugs	 3M™ One Touch™ Pro Earplug Dispenser	 3M™ E-A-R™ Express™ Earplugs	 3M™ E-A-R™ Push-Ins™ Earplugs	 3M™ E-A-R™ UltraFit™ Earplugs	 3M™ E-A-Rcaps™	 3M™ PELTOR™ Optime™ I Earmuffs	 3M™ PELTOR™ Optime™ II Earmuffs	 3M™ PELTOR™ Optime™ III Earmuffs	 3M™ PELTOR™ Earmuff X4	 3M™ PELTOR™ Earmuff X5
Hearing protection types:														
Disposable earplugs	•	•	•	•	•									
Push-to-fit earplugs						•	•							
Re-usable earplugs								•						
Banded earplugs									•					
Ear muffs										•	•	•	•	•
SNR v dB (EN 352:2020)	34	31	31	35		28	31/35	29	24	27	31	34	32	37
Noise level:														
< 85 dB														
83–93 dB														
87–98 dB		•	•			•			•	•				
94–105 dB							•	•			•			
95–110 dB	•			•			•					•	•	•
Customer need:														
Corded	•		•	•		•	•	•						
Un-corded	•	•		•		•	•	•						
Application/environment:														
Temperature (+cold/hot*)	••	••	••	••		••	••	••	••	•	•	•	•	•
Humidity		•	•							•	•	•	•	•
Lack of hygiene facility						•	•	•		•	•	•	•	•

Hearing protection use and care

Roll down earplugs




How to use


Slowly roll and compress foam earplugs into a very thin cylinder. While compressed, insert the earplug well into the ear canal. Fitting is easier if you reach around the head to pull the ear outward and upward during insertion.

Care and cleaning

Keep the earplugs clean and free from material that can irritate the ear canal. Wipe dirt and debris from earplugs with a clean cloth between uses. Discard the earplugs if they noticeably change their firmness or do not re-expand to their original size and shape.



Reusable pre moulded earplugs




How to use



Reach around the back of your head and pull outward on the ear while inserting the plug until you feel it sealing. This may seem tight at first, especially if you have never worn earplugs.

Care and cleaning

Pre-moulded earplugs could last several months depending on the type and on your work environment, hygiene and body chemistry. They should be replaced if they shrink, harden, tear, crack or become permanently deformed. Wash them in warm soapy water and rinse well. When dry, store them in a carrying case.



Banded earplugs




How to use

Hold the large ends of the pods and swivel them to direct the tips into the ear canal openings. Firmly push and wiggle the pods into the ear canal until a snug seal is obtained. Pulling on the outer ear while pushing the pods will be helpful to most wearers.

Care and cleaning

Most semi-aural hearing protectors can be cleaned in the same way as pre-moulded earplugs. Since the band holds the tips in place to provide an acoustic seal, do not tamper with it otherwise the protection afforded by the device may be reduced.



Earmuffs




How to use

Earmuffs must fully enclose the ears to seal against the head. Adjust the headband so cushions exert even pressure around the ears to get the best noise reduction. Pull hair back and out from beneath the cushions. Do not wear caps, store pencils behind the ear or anything that may break the seal.

Care and cleaning

Cushions can be cleaned with warm soapy water and rinsed thoroughly. Do not use alcohol or solvents. Cushions normally need replacing at least twice a year or more – whenever they become stiff, cracked, or do not seal. Do not modify earmuffs in any way, and especially do not stretch or abuse the headband as this will reduce protection.



Fitting guide



3M™ E-A-R™ One Touch™ Pro Earplug Dispenser

Conveniently provide hearing protection where employees need it. The 3M™ One Touch™ Pro Earplug Dispenser dispenses one earplug at a time with a simple twist. No more expense and waste of individually wrapped plugs. Made from ABS plastic with a powder-coated steel-back plate, it's designed for challenging environments - indoors and outdoors.

- ▶ Accurately dispenses one earplug at a time
- ▶ Dispenses earplug directly into hand
- ▶ Powder coated steel back plate and durable ABS and POM plastic for tough environments
- ▶ Free-standing or wall-mounted, could be located inside or outside
- ▶ Mounting holes designed to fit a variety of competitive dispensers
- ▶ The innovative design protects against sun, rain and wind, when dispensing earplugs outside



3M™ E-A-R™
Classic™ Earplugs



3M™ E-A-Rsoft™
Yellow Neons™ Earplugs



3M™ 1100 Earplugs

Product number	Product description	Case qty
391-0000	3M™ E-A-R™ One Touch™ Earplugs Dispenser	1 EA
PD-01-001	3M™ E-A-R™ Classic™ Earplugs Refill Bottle	500 PR
PD-01-002	3M™ E-A-Rsoft™ Yellow Neons™ Earplugs Refill Bottle	500 PR
1100-R	3M™ 1100 Earplugs Refill Bottle	500 PR

Hearing Protection

Earplugs

Focus

3M™ E-A-R™ Express™ Earplugs

The 3M™ E-A-R™ Express™ Earplugs are a push to fit design for insertion into the ear canal to help reduce exposure to hazardous levels of noise. Offering both a one hand and two hand insertion performance claim of 28 dB SNR tested in accordance with EN 352-2:2020.



- Offering both a one hand and two hand insertion performance claim of 28 dB SNR in accordance with EN 352-2:2020
- Pod design shaped to help provide an effective seal
- Patented 3M™ E-A-R™ foam tips compress easily for smooth insertion and slow expansion for secure fit

Product ID	Part Number	Product Name	MOQ	OU
7000103732	EX01001	3M™ E-A-R™ Express™ Earplugs, Corded, 100 Pairs/Box, EX-01-001	400	Pair

Focus

3M™ E-A-R™ Push-Ins™ Earplugs

3M™ E-A-R™ Push-Ins™ Earplugs have a 3M E-A-Rform™ Foam tip that's shaped and sized to fit comfortably in most ears.



Our recognisable yellow earplugs have a flexible blue stem for easy insertion using one or two hands. Push in insertion makes fitting and removal easy and hygienic.

- Single Number Rating (SNR) 35 dB (two-hand insertion) and 31 dB (one-hand insertion)
- Unique E-A-Rform™ tip shaped and sized to fit comfortably in most ears
- Flexible stem makes them easy and hygienic to use as you don't need to touch the foam tip

Product ID	Part Number	Product Name	MOQ	OU
7000052713	EX01020	3M™ E-A-R™ Push-Ins™ Earplugs, Corded, 400 Pairs/Box, EX-01-020	400	Pair
7000052714	EX01021	3M™ E-A-R™ Push-Ins™ Earplugs, Uncorded, 400 Pairs/Box, EX-01-021	400	Pair

3M™ E-A-Rsoft™ 21 Earplugs

The 3M™ E-A-Rsoft™ 21 Earplugs are disposable and designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise and loud sound.



- Slow expanding, soft polyurethane foam for all day comfort
- Round shape helps secure fit
- Requires no roll down

Product ID	Part Number	Product Name	MOQ	OU
7000052712	ES01009	3M™ E-A-Rsoft™ 21 Earplugs, Uncorded, 1000 Pairs/Box, ES-01-009	1000	Pair

Hearing Protection

Focus

3M™ E-A-R™ Classic™ Earplugs

The 3M™ E-A-R™ Classic™ Earplugs are disposable and designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise and loud sound up to 31 dB SNR. These products are available in a corded and uncorded version.



- Reduces noise levels up to 31 dB (both corded and uncorded), tested to EN 352-2:2020
- Soft energy absorbing foam provides a low equilibrium pressure making it one of 3M's most comfortable earplugs
- Moisture resistant making them less likely to swell through moisture absorption

Product ID	Part Number	Product Name	MOQ	OU
7000052844	CC01000	3M™ E-A-R™ Classic™ Earplugs, Corded, 200 Pairs/Box, CC-01-001	200	Pair
7000038203	PD01001	3M™ E-A-R™ Classic™ Earplugs, Refill Bottle, 500 Pairs /Bottle, PD-01-001	500	Pair
7000103748	PD01009	3M™ E-A-R™ Classic™ Earplugs, Top Up Bag, 500 Pairs/Bag, PD-01-009	2000	Pair
7000103777	FP01008	3M™ E-A-R™ Classic™ Earplugs, Uncorded, 2 Pairs/Box, FP-01-008P	24	Pair
7000038198	PP01002	3M™ E-A-R™ Classic™ Earplugs, Uncorded, Pillowpack, 250 Pairs/Box, PP-01-002	1000	Pair

3M™ E-A-Rsoft™ Yellow Neons™ Earplugs

The 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs are designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise up to 34 dB, tested to EN 352-2:2020. Available in a corded and uncorded version.



- Reduces noise levels up to 34 dB, tested to EN 352-2:2020
- Brightly-coloured, neon-yellow earplugs are easy to identify in compliance checks
- Soft foam helps provide low pressure inside the ear canal

Product ID	Part Number	Product Name	MOQ	OU
7000052845	ES01005	3M™ E-A-Rsoft™ Yellow Neons™ Earplugs, Corded, 200 Pairs/Box, ES-01-005	200	Pair
7000038202	PD01002	3M™ E-A-Rsoft™ Yellow Neons™ Earplugs, Refill Bottle, 500 Pairs/Bottle, PD-01-002	500	Pair
7000103747	PD01010	3M™ E-A-Rsoft™ Yellow Neons™ Earplugs, Top Up Bag, 500 Pairs/Bag, PD-01-010	2000	Pair
710011802	ES01001	3M™ E-A-Rsoft™ Yellow Neons™ Earplugs, Uncorded, 250 Pairs/Box, ES-01-001	1000	Pair

3M™ E-A-Rsoft™ FX Earplugs

3M™ E-A-Rsoft™ FX™ Earplugs are comfortable bell shape and feature expandable super soft PU foam. They offer the highest level of noise reduction in the 3M earplug line, up to 37 dB, tested to EN 352-2:2002.



- Reduces noise levels up to 37 dB, tested to EN 352-2:2020
- Tapered design provides a good fit on a wide range of ear canal sizes
- Features super soft slow recovery PU foam providing a reliable seal

Product ID	Part Number	Product Name	MOQ	OU
7000052711	ES01021	3M™ E-A-Rsoft™ FX Earplugs, Corded, 2000 Pairs/Box, ES-01-021	200	Pair
7000052710	ES01020	3M™ E-A-Rsoft™ FX Earplugs, Uncorded, 2000 Pairs/Box, ES-01-020	2000	Pair

Hearing Protection

3M™ E-A-Rsoft™ Metal Detectable Earplugs

The 3M™ E-A-Rsoft™ Metal Detectable ear plugs are ideal for high noise exposure levels, particularly effective against low frequency noise.

- Implanted stainless steel ball in the earplug with metal infused cord detectable by metal sensing systems in the food and beverage industry
- Slow recovery, environmental friendly polyurethane foam
- Tapered shape conforms quickly to most ear canals



Product ID	Part Number	Product Name	MOQ	OU
7000052715	ES01011A	3M™ E-A-Rsoft™ Metal Detectable Earplugs, 2000 Pairs/Box, ES-01-011A	200	Pair

Focus

3M™ Earplugs 1100 Series

The 3M™ 1100 Earplugs are disposable foam earplugs designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise up to 35 dB, tested to EN 352-2:2020.

- Reduces noise levels up to 35 dB, tested to EN 352-2:2020
- Tapered design provides a good fit on a wide range of ear canal sizes
- Soft hypoallergenic foam softens with body temperature once inserted for comfortable extended wear



Product ID	Part Number	Product Name	MOQ	OU
7100100637	1100	3M™ Earplugs 1100, 37 dB, Uncorded, 200 Pairs/Box	1000	Pair
7100100638	1110	3M™ Earplugs 1100, Corded, 500 Pairs / Box	500	Pair
7100100263	1100R	3M™ Earplugs 1100, Top Up Bag, Uncorded, 2000 Pairs/Box, 1100R	2000	Pair
7000103721	1100B	3M™ Earplugs, Refill Bottle, Uncorded, 500 Pairs/Box, 1100D	500	Pair

Focus

3M™ E-A-R™ Reusable Earplugs

The 3M™ E-A-R™ UltraFit™ & 3M™ E-A-R™ Tracers™ Earplugs are reusable and designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise.

- Reduces noise levels up to 29 dB SNR in accordance with EN 352-2:2020
- Patented tri-flange design in pre-moulded material makes them a fit for most ear canals
- Firm, long stem for easy insertion and removal



Product ID	Part Number	Product Name	MOQ	OU
7000038200	TR01000T	3M™ E-A-R™ Tracers™ Earplugs, Corded, 50 Pairs/Box, TR-01-000	200	Pair
7000103735	TR01100	3M™ E-A-R™ Tracers™ Earplugs, Corded, 50 Pairs/Box, TR-01-100	200	Pair
7000038199	UF01000	3M™ E-A-R™ Ultrafit™ Earplugs, Corded, 50 Pairs/Box, UF-01-000	500	Pair
7000103727	UF01000S	3M™ E-A-R™ Ultrafit™ Earplugs, Corded, 50 Pairs/Box, UF-01-000	200	Pair
7000103745	UF01020	3M™ E-A-R™ Ultrafit™ Earplugs, Corded, Storage Case, 50 Pairs/Box, UF-01-100	200	Pair

Hearing Protection

3M™ E-A-R™ Ultrafit X™ Earplugs

3M™ E-A-R™ Ultrafit™ X Earplugs are our corded hearing protectors with an innovative pistol grip stem designed to make them easy to take in and out. They fit most ears comfortably and reduce noise levels by 33 dB as certified under EN 352:2:2020.



- Reduces noise levels up to 33 dB, tested to EN 352-2:2020
- Features an innovative pistol grip stem for optimised insertion and removal for improved seal and protection
- Triple flange pliable polymer tip for a comfortable fit in most size ear canals

Product ID	Part Number	Product Name	MOQ	OU
7000103757	UF01014	3M™ E-A-R™ Ultrafit™ X Earplugs, Corded, 220 Pairs/Box, UF-01-014	50	Pair

Focus

3M™ Earplugs 1200 Series

The 3M™ Earplugs 1200 Series are reusable and designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise up to 26 dB.



- Reduces noise levels up to 26dB tested to EN 352:2020
- Triple flange design for optimum fit for most ear canal sizes
- Made from soft and durable material for optimum comfort

Product ID	Part Number	Product Name	MOQ	OU
7100288286	3M1261	3M™ Reusable Earplug 1261, No Cord, Pillow Pack	300	Pair
7100288287	3M1271	3M™ Reusable Earplug 1271, Corded, Pillow Pack	300	Pair

3M™ Tri-Flange™ Earplugs

3M™ Tri-Flange™ Earplugs are our innovative, comfortable hearing protectors with soft, flexible flanges that adapt to the shape of your ears. Available with a cloth or vinyl cord, convenient for intermittent use.



- Reduces noise levels up to 29 dB SNR in accordance with EN 352-2:2020
- Features soft, flexible triple flanges that adapt to the shape of your ear providing an effective acoustic seal
- No need to handle the plug tip as simply and hygienically push the plug to fit

Product ID	Part Number	Product Name	MOQ	OU
7000052850	PN01005	3M™ Tri-Flange™ Earplugs, Vinyl Cord, 100 Pairs/Box, PN-01-005	100	Pair

Hearing Protection

3M™ No-Touch™ Earplugs

3M™ No-Touch™ Foam Earplugs create a hygienic noise-reducing seal with no need to touch or roll down, simply push to fit. Protect your hearing up to 34 dB with our EN 352-2:2020 certified earplugs.

- CE Certified against EN 352-2:2020
- Reduces noise levels by 34 dB
- Flexible paddle stem makes them easy and hygienic to use as you don't need to touch the foam tip



Product ID	Part Number	Product Name	MOQ	OU
7000052849	PN01004	3M™ No-Touch™ Earplugs, Corded, 100 Per Pack, PN-01-004	100	Pair

3M™ 1310 Banded Earplugs

3M™ E-A-R™ 1310 Banded Earplugs are designed with a patented headband with flexing capability that adjusts to the movements of your jaw and head, for a comfortable and secure fit with constant low pressure in the ear. Our blue robust acetal plastic band is made to fit behind the head or under the chin, making it ideal for wearers exposed to intermittent noise.

- Reduces noise levels up to 26 dB
- Flexible band design helps maintain a constant pressure, at a comfortable level, irrespective of head size
- Innovative flexible band for optimum fit and superior comfort



Product ID	Part Number	Product Name	MOQ	OU
7100089592	1310	3M™ Banded Earplugs, 10/Box, 1310	50	Each

3M™ E-A-R™ Caboflex™ Banded Earplugs

3M™ E-A-R™ Caboflex Earplugs are ideal when moving in and out of high noise areas, fitting comfortably around the neck when not in use. Each conical shaped insert swivels to align with the ear canal, providing a move-resistant seal against noise.

- Reduces noise levels up to 21 dB when used with headband
- Banded earplugs with conical shaped earplugs that swivel to align with the ear canal to provide a move-resistant seal against noise
- Earplugs are washable and reusable for improved hygiene and economy



Product ID	Part Number	Product Name	MOQ	OU
7000089406	CF01000	3M™ E-A-R™ Caboflex™ Banded Earplugs, 40/Box, CF-01-000	40	Each

Hearing Protection

Focus

3M™ E-A-Rcaps™ Banded Earplugs

The 3M™ E-A-Rcaps™ Banded hearing protector is fitted with semi-aural eartips designed to seal the entrance part of the ear canal to help reduce exposure to hazardous levels of noise up to 23 dB.

- Reduces noise levels up to 23 dB
- One of the lightest banded hearing protectors on the market
- Flexible and durable band that can be washed and reused multiple times



Product ID	Part Number	Product Name	MOQ	OU
7000103729	EC01000S	3M™ E-A-Rcaps™ Banded Ear Plugs, 10/Box, EC-01-000	50	Each
7000089405	EC01000	3M™ E-A-Rcaps™ Banded Earplugs, 400 /Box, EC-01-000	40	Each

3M™ E-A-R™ Replacement Pods

Replacement pods for improved hygiene and economy, fits the 3M™ E-A-Rcaps™, 3M™ E-A-R™ Caboflex™ and 1310 banded earplugs.

- Replacement foam ear pods for the 3M™ E-A-Rcaps™, 3M™ E-A-R™ Caboflex™ and 1310 banded earplugs
- Easy to remove and replace the pods on your banded earplugs
- Replacement pods are an easy way to improve hygiene and comfort on your washable banded hearing protector



Product ID	Part Number	Product Name	MOQ	OU
7000103730	ES01300	3M™ E-A-Rcaps™ Replacement Pods, 23 dB, 2000 Pairs/Box, ES-01-300	500	Pair
7000089404	ES01301	3M™ E-A-Rcaps™ Replacement Pods, 50 Pairs/Box, ES-01-301	50	Pair
7100100262	1311	3M™ E-A-R™ Replacement Pods, 26 dB, 20 Pairs/Box, 1311	100	Pair

Earplug Dispensers

Focus

3M™ E-A-R™ One Touch™ Pro Earplug Dispenser

3M™ E-A-R™ One Touch™ Pro Earplugs dispenser offers convenient access to workers on the move. A simple twist accurately and consistently dispenses one earplug at a time. The reusable free-standing or wall hanging dispenser can be re-stocked with One Touch™ refills of our most popular 3M™ E-A-R™ Earplugs.

- Accurately dispenses one earplug at a time
- Dispenses earplug directly into hand
- Durable ABS plastic for tough environments



Product ID	Part Number	Product Name	MOQ	OU
7100064963	3910000	3M™ One Touch™ Pro Earplug Dispenser, 391-0000	1	Each

Hearing Protection

Earmuffs

Focus

3M™ PELTOR™ X1 Earmuffs

3M™ PELTOR™ X1 Earmuffs are our lightweight hearing protectors with comfortable, soft ear cushions. Available as headband, helmet attachment and neckband models. The headband model features an electrically insulated, twin headband that decreases heat build-up on top of the head. Depending on wearer preference or application need, the helmet attached versions are available as either dielectric electrically insulated or with robust metal arms.



- Reducing noise levels from 26-27 dB, model dependant, tested to EN 352:2020
- Wide flat headband is electrically insulated making the earmuffs electrically resistant or ,dielectric'
- Colour-coding makes it easy to identify the level of protection being worn

Product ID	Part Number	Product Name	MOQ	OU
7100123139	X1B- EU	3M™ PELTOR™ Earmuffs, Green, Neckband, X1B	10	Each
7000103987	X1A	3M™ PELTOR™ Earmuffs, Green, Headband, X1A	10	Each
7100095526	X1P5	3M™ PELTOR™ Earmuffs, Green, Helmet Mounted, X1P5E	10	Each
7000103988	X1P3	3M™ PELTOR™ Earmuffs,Green, Helmet Mounted, X1P3	10	Each

3M™ PELTOR™ X2 Earmuffs

3M™ PELTOR™ X2 Earmuffs are our innovative hearing protectors with a modern slim cup design. Available as headband, helmet attachment and neckband models. The headband model features an electrically insulated, twin headband that decreases heat build-up on top of the head. Depending on wearer preference or application need, the helmet attached versions are available as either dielectric electrically insulated or with robust metal arms.



- Reducing noise levels from 30-31 dB, model dependant, tested to EN 352:2020
- Wide flat headband is electrically insulated making the earmuffs electrically resistant or ,dielectric'
- Colour-coding makes it easy to identify the level of protection being worn

Product ID	Part Number	Product Name	MOQ	OU
7000103989	X2A	3M™ PELTOR™ Earmuffs, Yellow, Headband, X2A	10	Each
7000103990	X2P3	3M™ PELTOR™ Earmuffs, Yellow, Helmet Mounted, X2P3	10	Each
7100095525	X2P5	3M™ PELTOR™ Earmuffs, Yellow, Helmet Mounted, X2P5E	10	Each
7100123157	X2B- EU	3M™ PELTOR™ Earmuffs, Yellow, Neckband, X2B	10	Each

Hearing Protection

3M™ PELTOR™ X3 Earmuffs

3M™ PELTOR™ X3 Earmuffs include a specially designed spacer to offer protection against moderate to high noise levels without the weight or bulk.

Available as headband, helmet attachment and neckband models.

The headband model features an electrically insulated, twin headband that decreases heat build-up on top of the head. Depending on wearer preference or application need, the helmet attached versions are available as either dielectric electrically insulated or with robust metal arms.



- Reducing noise levels from 32-33 dB, model dependant, tested to EN 352:2020
- Available as electrically insulated and resistant or ,dielectric' in A band and P5 helmet attached models
- Colour-coding makes it easy to identify the level of protection being worn

Product ID	Part Number	Product Name	MOQ	OU
7000103991	X3A	3M™ PELTOR™ Earmuffs, Red, Headband, X3A	10	Each
7000103992	X3P3	3M™ PELTOR™ Earmuffs, Red, Helmet Mounted, X3P3	10	Each
7100095553	X3P5	3M™ PELTOR™ Earmuffs, Red, Helmet Mounted, X3P5	10	Each
7100123160	X3B- EU	3M™ PELTOR™ Earmuffs, Red, Neckband, X3B	10	Each

Focus

3M™ PELTOR™ X4 Earmuffs

3M™ PELTOR™ X4 Earmuffs are our lightweight and slim hearing protectors with innovative foam earcup inserts and spacers to help boost attenuation and protect against low frequencies.

Available as headband, helmet attachment and neckband models.

The headband model features an electrically insulated, twin headband that decreases heat build-up on top of the head. Depending on wearer preference or application need, the helmet attached versions are available as either dielectric electrically insulated or with robust metal arms.



- Reducing noise levels from 32-33 dB, model dependant, tested to EN 352:2020
- Available as electrically insulated and resistant or ,dielectric' in A band and P5 helmet attached models
- Colour-coding makes it easy to identify the level of protection being worn

Product ID	Part Number	Product Name	MOQ	OU
7000103993	X4A	3M™ PELTOR™ Earmuffs, Hi-Viz, Headband, X4A	10	Each
7000103994	X4P3	3M™ PELTOR™ Earmuffs, Hi-Viz, Helmet Mounted, X4P3	10	Each
7100095551	X4P5	3M™ PELTOR™ Earmuffs, Hi-Viz, Helmet Mounted, X4P5	10	Each
7100123162	X4B- EU	3M™ PELTOR™ Earmuffs, Hi-Viz, Neckband, X4B	10	Each

Hearing Protection

3M™ PELTOR™ X5 Earmuffs

3M™ PELTOR™ X5 Earmuffs are our innovative hearing protectors that offer exceptional performance – without the need for double protection. Offering the same premium features you expect from 3M Peltor X Series they also reduce noise up to 37 dB.

- Reducing noise levels from 36-37 dB, model dependant, tested to EN 352:2020
- Available as electrically insulated and resistant or ,dielectric' in A band and P5 helmet attached models
- Colour-coding makes it easy to identify the level of protection being worn



Product ID	Part Number	Product Name	MOQ	OU
7000103995	X5A	3M™ PELTOR™ Earmuffs, Black, Headband, X5A	10	Each
7000103996	X5P3	3M™ PELTOR™ Earmuffs, Black, Helmet Mounted, X5P3	10	Each
7100095550	X5P5	3M™ PELTOR™ Earmuffs, Black, Helmet Mounted, X5P5E	10	Each
7100123159	X5B- EU	3M™ PELTOR™ Earmuffs, Black, Neckband, X5B	10	Each

3M™ PELTOR™ Optime™ I Earmuffs

3M™ PELTOR™ Optime™ I Earmuffs are our innovative, lightweight hearing protectors that reduce noise levels up to 27 dB tested in accordance with EN 352:2020. They feature a low-profile design that makes them easy to combine with other safety equipment and have soft, wide comfortable cushions that reduce pressure around the ears.

- Reducing noise levels from 26-27 dB, model dependant, tested to EN 352:2020
- Low-profile design combines easily with other safety equipment
- Compatible with the 3M™ E-A-Rfit™ Dual-Ear Validation System



Product ID	Part Number	Product Name	MOQ	OU
7000103737	H510AGB	3M™ PELTOR™ Optime™ I Earmuffs, Hi-Viz, Headband, H510A-470-GB	10	Each
7000038205	H510FGU	3M™ PELTOR™ Optime™ I Earmuffs, Yellow, Foldable, H510F-404-GU	10	Each
7000039616	H510AGU	3M™ PELTOR™ Optime™ I Earmuffs, Yellow, Headband, H510A-401-GU	20	Each
7000039617	H510PEGU	3M™ PELTOR™ Optime™ I Earmuffs, Yellow, Helmet Mounted, H510P3E-405-GU	20	Each
7000039618	H510BGU	3M™ PELTOR™ Optime™ I Earmuffs, Yellow, Neckband, H510B-403-GU	10	Each

Hearing Protection

3M™ PELTOR™ Optime™ II Earmuffs

3M™ PELTOR™ Optime™ II Earmuffs are our innovative hearing protectors for use in loud, demanding environments including airports and construction sites, reducing noise levels up to 31 dB. These earmuffs feature soft foam cushions, ventilation channels in the sealing rings and spacious cups, providing agreeable comfort even in long-term use and improving incidence of wear and compliance.



- Reducing noise levels from 30-31 dB, model dependant, tested to EN 352:2020
- Compatible with the 3M™ E-A-Rfit™ Dual-Ear Validation System
- Large space inside the cups helps minimise heat and moisture build-up

Product ID	Part Number	Product Name	MOQ	OU
7000038208	H520FGQ	3M™ PELTOR™ Optime™ II Earmuffs, Green, Foldable, H520F-409-GQ	10	Each
7000039619	H520AGQ	3M™ PELTOR™ Optime™ II Earmuffs, Green, Headband, H520A-407-GQ	20	Each
7000039621	H520PEGQ	3M™ PELTOR™ Optime™ II Earmuffs, Green, Helmet Mounted, H520P3E-410-GQ	20	Each
7000107763	H520EGQ1	3M™ PELTOR™ Optime™ II Earmuffs, Green, Helmet Mounted, H520P3E-410-GQ-01	20	Each
7000039620	H520BGQ	3M™ PELTOR™ Optime™ II Earmuffs, Green, Neckband, H520B-408-GQ	10	Each
7000038210	H520PEGB	3M™ PELTOR™ Optime™ II Earmuffs, Hi-Viz, Helmet Mounted, H520P3E-467-GB	10	Each

3M™ PELTOR™ Optime™ III Earmuffs

3M™ PELTOR™ Optime™ III Earmuffs are our high performance hearing protectors for use in extremely loud environments, reducing noise levels by up to 34 dB. They have a double casing that minimises resonance and comfortable soft, wide cushions to decrease pressure around the ears. Available in headband, neckband, helmet attached and Hi-Viz green models.



- Reducing noise levels from 33-34 dB, model dependant, tested to EN 352:2020
- Double casing technology minimises resonance effect
- Large space inside the cups helps minimise heat and moisture build-up

Product ID	Part Number	Product Name	MOQ	OU
7000038211	H540AGB	3M™ PELTOR™ Optime™ III Ear Muffs, Hi-Viz, Headband, H540A-461-GB	10	Each
7000039622	H540ASV	3M™ PELTOR™ Optime™ III Earmuffs, Black/Red, Headband, H540A-411-SV	20	Each
7000039624	H540PESV	3M™ PELTOR™ Optime™ III Earmuffs, Black/Red, Helmet Mounted, H540P3E-413-SV	20	Each
7000039623	H540BSV	3M™ PELTOR™ Optime™ III Earmuffs, Black/Red, Neckband, H540B-412-SV	10	Each
7000038212	H540PEGB	3M™ PELTOR™ Optime™ III Earmuffs, Hi-Viz, Helmet Mounted, H540P3E-475-GB	10	Each

3M™ PELTOR™ Bull's Eye™ I Earmuffs

3M™ PELTOR™ Bull's Eye™ I Earmuffs are our hearing protectors designed for hunting and shooting environments. They're shaped to avoid any interference with the rifle butt, helping you obtain the optimum shot. Available in black and green models.



- Reduces noise levels up to 28 dB, tested to EN 352:2020
- Designed for use during hunting and shooting
- Padded metal headband construction helps maintain a consistent force throughout the day for reliable protection

Product ID	Part Number	Product Name	MOQ	OU
7000107973	H515MIL	3M™ PELTOR™ Bull's Eye™ I Earmuffs, Green, Foldable, H515FB-508-GN	1	Each

Hearing Protection

3M™ PELTOR™ Earmuffs H31 Series

3M™ PELTOR™ Earmuffs H31 Series provide slimline hearing protection, ideal for use in forestry, sawmills and industry applications.

- Single Number Rating (SNR) 30 dB (headband) or 28 dB (helmet attached model)
- Slimline hearing protection, ideal for use in forestry, sawmills and industry applications
- Earmuff cup has a recess at the top making it a more comfortable fit with Safety Helmets



Product ID	Part Number	Product Name	MOQ	OU
7000038214	H31P3AF	3M™ PELTOR™ Earmuffs, Orange, Helmet Mounted, H31P3AF	6	Each

Focus

3M™ PELTOR™ Welding Earmuff H505B

3M™ PELTOR™ H505B Welding Earmuffs are a neckband fit with a low profile and are designed to be used with welding helmets such as our 3M™ Speedglas™ Welding Helmet Series 9100. The 24 dB protection provides the moderate attenuation needed in most welding applications.

- CE certified and tested to EN 352 it reduces noise up to 24 dB
- Modern, stylish slim cup design
- Semi-soft cup that minimises scratch sound transmission



Product ID	Part Number	Product Name	MOQ	OU
7000103787	H505BSV	3M™ PELTOR™ Welding Earmuffs, Black, Neckband, H505B	10	Each

Hearing Protection

Hygiene Kits

3M™ PELTOR™ Hygiene Kits for X Series Earmuffs

3M™ PELTOR™ Hygiene Kits for 3M X Series Earmuffs help you maintain the correct levels of protection, comfort and hygiene.



- Maintain hygiene, comfort and protection of 3M™ PELTOR™ Earmuffs with 3M™ PELTOR™ Hygiene Kits. 3M recommends replacing earmuff cushions and foam inserts every 6 months or sooner if they are damaged.
- Maintain hygiene, comfort and protection of 3M™ PELTOR™ Earmuffs
- Extend the life of your earmuff

Product ID	Part Number	Product Name	MOQ	OU
7000104045	HYX1	3M™ PELTOR™ Hygiene Kit for X1-A / X1-P3E Earmuffs, HYX1	10	Each
7000104046	HYX2	3M™ PELTOR™ Hygiene Kit for X2-A / X2-P3E Earmuffs, HYX2	10	Each
7000104047	HYX3	3M™ PELTOR™ Hygiene Kit for X3-A / X3-P3E Earmuffs, HYX3	10	Each
7000104048	HYX4	3M™ PELTOR™ Hygiene Kit for X4-A / X4-P3E Earmuffs, HYX4	10	Each
7000104049	HYX5	3M™ PELTOR™ Hygiene Kit for X5-A / X5-P3E Earmuffs, HYX5	10	Each

3M™ PELTOR™ Hygiene Kits for Communication Solutions

3M™ PELTOR™ Hygiene Kits for 3M™ PELTOR™ Communication Headsets help you maintain the correct levels of protection, comfort and hygiene.



- Maintain hygiene, comfort and protection of 3M™ PELTOR™ Communication Headsets
- Extend the life of your headset
- Avoid wearing uncomfortable earmuffs

Product ID	Part Number	Product Name	MOQ	OU
7100063118	HY79	3M™ PELTOR™ Hygiene Kit for FM Radio, ProTac, & LiteCom Headsets, HY79	20	Kit
7100122439	HY82	3M™ PELTOR™ Hygiene Kit for WS ALERT and DAB+FM headsets, HY82	1	Each
7100101874	HY220	3M™ PELTOR™ Hygiene Kit for Worktunes Headset, HY220	1	Each

3M™ PELTOR™ Optime Earmuff Hygiene Replacement Kit

3M™ PELTOR™ Hygiene Kit for Earmuffs are our quick and easy solution to maintain your 3M™ PELTOR™ Earmuffs with replacement cushions and liners.



- Kit contains replacement sealing rings and muffler pads which can be replaced in a few easy steps
- Extends the life of earmuffs
- Ensures good function and hygiene

Product ID	Part Number	Product Name	MOQ	OU
7000108016	HY54	3M™ PELTOR™ Hygiene Kit for Optime™ III Earmuffs, HY54	20	Each

Hearing Protection

3M™ PELTOR™ Clean Hygiene Pads HY100A Series

Disposable covers for the ear cushions that are intended to provide a clean contact surface when the headset is used by multiple people.

- Single use hygiene pads for cleaning earmuffs
- Extends the life of earmuffs
- Roll format, delivered in handy dispenser box



Product ID	Part Number	Product Name	MOQ	OU
7100064410	HY100A	3M™ PELTOR™ Hygiene Pads, 100 Pairs / Pack, HY100A	100	Pair

Validation

3M™ E-A-Rfit™ Dual-Ear Validation System

Fit testing is key for effective wear and hearing conservation. The 3M™ E-A-Rfit™ Dual-Ear Validation System accurately quantifies each wearers personal attenuation from inside both ears when wearing earplugs or earmuffs. Our system takes only seconds to measure across 7 standard frequencies and gives a simple pass or fail rating for each employee's personal attenuation rating (PAR) to facilitate training on the importance of fit.

- Gives fast, clear, accurate fit testing of your hearing protection as quantified scientific data
- Personal attenuation rating (PAR) is first step in fit testing and hearing conservation programme
- Measures sound levels inside and outside of the earplug in only 5 seconds



Product ID	Part Number	Product Name	MOQ	OU
7100062125	393-1100	3M™ E-A-Rfit™ Dual-Ear Validation System, 393-1100	1	Kit

3M™ E-A-R™ Express™ Probed Test Plugs

3M™ E-A-R™ Express™ Earplugs equipped with a probe tube for fit testing using the 3M™ E-A-Rfit™ Validation System. Cannot be used for hearing protection.

- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- 50 pairs per case
- 3M™ PSD products are for occupational use only



Product ID	Part Number	Product Name	MOQ	OU
7000052879	EXPRESSP	3M™ E-A-R™ Express™ Probed Test Plugs, 50 Pairs/Box, 393-2008-50	50	Pair

Hearing Protection

3M™ E-A-R™ Push-Ins™ Probed Test Plugs

3M™ E-A-R™ Push-Ins™ Probed Test Plugs are for use with the 3M™ E-A-Rfit™ Dual-Ear Validation System. Our earplugs are specially equipped with a probe tube for fit testing.



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- For use with 3M™ E-A-Rfit™ Validation System to measure HPE effectiveness
- Should not be used as hearing protection

Product ID	Part Number	Product Name	MOQ	OU
7100113020	EARCAPSP	3M™ E-A-RCaps™ Model 200 Probed Test Plugs, 50 Pairs/Box, 393-2002-50	50	Pair

3M™ E-A-R™ Classic™ Probed Test Plugs

3M™ E-A-R™ Classic™ Probed Test Plug are a modified version of the disposable foam 3M Classic Earplugs you know and use, specially designed to be used with the 3M™ E-A-Rfit™ Dual-Ear Validation System.



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- For use with 3M™ E-A-Rfit™ Validation System to measure HPE effectiveness
- Should not be used as hearing protection

Product ID	Part Number	Product Name	MOQ	OU
7000052882	CLASSICP	3M™ E-A-R™ Classic™ Probed Test Plugs, 50 Pairs/Box, 393-2003-50	1	Pair

3M™ E-A-Rsoft™ Yellow Neons™ Probed Test Plugs

3M™ E-A-Rsoft™ Yellow Neons™ Earplugs equipped with a probe tube for fit testing using the 3M™ E-A-Rfit™ Validation System. Cannot be used for hearing protection.



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- 50 pairs per case
- 3M™ PSD products are for occupational use only

Product ID	Part Number	Product Name	MOQ	OU
7100069736	EARSOFTP	3M™ E-A-Rsoft™ Yellow Neons™ Probed Test Plugs, 50 Pairs/Box, 393-2000-50	50	Pair

3M™ 1100 Series Probed Test Plugs

3M™ 1100 Earplugs equipped with a probe tube for fit testing using the 3M™ E-A-Rfit™ Validation System. Cannot be used for hearing protection.



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- 50 pairs per case
- 3M™ PSD products are for occupational use only

Product ID	Part Number	Product Name	MOQ	OU
7000002409	1100P	3M™ 1100 Series Probed Test Plugs, 50 Pairs/Box, 393-2010-50	5	Pack

Hearing Protection

3M™ 1200 Series Probed Test Plugs

3M™ 1200 Series Probed Test Plugs are a modified version of the 3M earplugs you know and use, specially designed to be used with the 3M™ E-A-Rfit™ Dual-Ear Validation System



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- For use with 3M™ E-A-Rfit™ Validation System to measure HPE effectiveness
- Should not be used as hearing protection

Product ID	Part Number	Product Name	MOQ	OU
7100034169	1200P	3M™ 1260/1270/1271 Probed Test Plugs, 50 Pairs/Box, 393-2016-50	50	Pair

3M™ E-A-R™ Ultrafit™ Probed Test Plugs

3M™ E-A-R™ UltraFit™ Probed Test Plugs are for use with the 3M™ E-A-Rfit™ Dual-Ear Validation System. Our earplugs are specially equipped with a probe tube for fit testing.



- Specially modified with a probe tube for fit testing 3M earplugs
- For use with 3M™ E-A-Rfit™ Validation System to measure HPE effectiveness
- Should not be used as hearing protection

Product ID	Part Number	Product Name	MOQ	OU
7000002387	ULTRAFIP	3M™ E-A-R™ UltraFit™ Probed Test Plugs, 50 Pairs/Box, 393-2001-50	5	Pack

3M™ E-A-Rsoft™ FX™ Probed Test Plugs

3M™ E-A-Rsoft™ FX™ Earplugs equipped with a probe tube for fit testing using the 3M™ E-A-Rfit™ Validation System. Cannot be used for hearing protection.



- These test earplugs are modified with a probe tube for use during earplug fit testing with the 3M™ E-A-Rfit™ Validation System
- 50 pairs per case
- 3M™ PSD products are for occupational use only

Product ID	Part Number	Product Name	MOQ	OU
7000052883	EARSOFXP	3M™ E-A-Rsoft™ FX™ Probed Test Plugs, 50 Pairs/Box, 393-2004-50	50	Pair

3M™ PELTOR™ Optime™ Earmuffs Probed Test Cushions

These 3M™ PELTOR™ Optime™ Earmuffs Probed Test Cushions are specially designed with a probe tube to enable individual worker fit testing for 3M PELTOR Optime Series Earmuffs.



- Specially modified with a probe tube for fit testing 3M™ PELTOR™ Optime™ Earmuffs
- For use with 3M™ E-A-Rfit™ Validation System to measure HPE effectiveness
- Should not be used as hearing protection

Product ID	Part Number	Product Name	MOQ	OU
7100062126	X1/X2P	3M™ PELTOR™ Earmuffs Probed Test Cushions X1/X2, 393-3001-2	1	Kit
7100062127	IM3579707	3M™ PELTOR™ Earmuffs Probed Test Cushions X3, 393-3003-2	1	Kit
7100062128	X4/X5P	3M™ PELTOR™ Earmuffs Probed Test Cushions X4/X5, 393-3005-2	1	Kit





Protective Communications

3M™ PELTOR™ Communication Solutions

The Sound Solution

First-class communication and hearing protection! There was a time when wearing hearing protectors meant being isolated and out of contact. Those days are over. Today, 3M™ PELTOR™ offers first-class communication solutions that not only make your working day safer and more efficient, but also much nicer!

3M™ PELTOR™ products are developed for all environments where high safety must be combined with communication. Industrial environments, construction sites, agriculture and forestry are a few examples. We have developed several models to ensure there's a 3M™ PELTOR™ Headset for every situation. Headband models for all-round use, and models with helmet attachments for people who wear safety helmets at work. To ensure easy use of our products and good functions for all environments we use advance technology such as Level Dependent technology and Bluetooth®.

This pricelist mainly focuses on general industry communication solutions, but 3M also offers specialised products for e.g. military or hunting and shooting. Please contact your local 3M representative if you want to learn more about these industries and products.



Oil and gas



Mining



Hunting and sport shooting



Airport ground handling




Military and law enforcement



Energy and utilities



Transportation




Industry



Construction

Communicate at distance and boost your productivity

The importance of wearing hearing protection 100% of time exposed









Safety

To be effective, a hearing protector should be used 100% of the time in noisy environments. Even taking it off for a short time dramatically reduces its effectiveness and greatly increases the risk of hearing damage. The 3M™ PELTOR™ Communication Solutions encourage longer use because the wearer feels less isolated and can communicate with others more easily.

Function symbols

To help you to understand the functionality of our key communication solutions we have developed a small comparison chart with the following symbols.

 <p>Hearing protection with level-dependent function for ambient listening</p>	 <p>Hearing protection that features Bluetooth® technology, for wireless connection to mobile phone, or communication radio</p>	 <p>Hearing protection with built-in two-way radio</p>	 <p>Hearing protection with built-in FM radio receiver</p>	 <p>Hearing protection with external audio input</p>	 <p>Hearing protection for communication with external two-way radio</p>
--	---	--	---	--	--

Find the headset with the right mix of features and value for you or your customer!

			
<p>3M™ PELTOR™ LiteCom</p>	<p>3M™ PELTOR™ LiteCom Plus</p>	<p>3M™ PELTOR™ WS™ LiteCom Plus</p>	<p>3M™ PELTOR™ WS ProTac XPI</p>
			
			
			
			
			

Request demonstration samples!

Protective Communications

In-ear Headsets

Focus

3M™ PELTOR™ Level Dependent Earplugs

3M™ PELTOR™ Level Dependent Earplugs are wireless electronic earplugs, designed to protect against loud noises and help improve situational awareness and communication. They come in a kit which includes a protective charging case and an assortment of ear tips, a retention cord, windscreens and a USB cable for charging. They are available in two versions, one for industrial use and one for shooting and forestry use.



- Wireless earplugs for protection against loud noises
- Designed to help improve situational awareness and communication
- Comes with a compact storage box for USB charging, offering 16 hours operating time

Product ID	Part Number	Product Name	MOQ	OU
7100194360	EEP-100	3M™ PELTOR™ Electronic Earplug, Green, EEP-100 EU	1	Each

3M™ PELTOR™ UltraFit™ Communication Replacement Eartips

3M™ UltraFit™ Communication Eartips are replacement parts that are specially designed for PELTOR™ TEP-100, LEP-100, TEP-200, LEP-200, EEP-100. Our eartips increase the effective service life of your equipment and come in small, medium or large.



- Replace damaged or worn eartips
- Maintains the right level of protection, comfort and hygiene
- Specially designed for use with 3M™ PELTOR™ in-ear communication products

Product ID	Part Number	Product Name	MOQ	OU
7100066388	708742	3M™ UltraFit™ Communication Eartips, Large, 370-TEPL-25	25	Pair
7100066387	708716	3M™ UltraFit™ Communication Eartips, Medium, 370-TEPM-25	25	Pair
7100066371	708687	3M™ UltraFit™ Communication Eartips, Small, 370-TEPS-25	25	Pair

3M™ PELTOR™ Triple-C Communication Eartips

3M™ PELTOR™ Triple-C Communication Eartips are replacement parts that are specially designed for PELTOR™ TEP-100, LEP-100, TEP-200, LEP-200, EEP-100. Our eartips come in packs of 25.



- No roll-down needed
- Double-tapered shape for easy insertion
- Designed for comfort

Product ID	Part Number	Product Name	MOQ	OU
7100103087	CCC-GRM-25	3M™ PELTOR™ Triple-C Communication Eartips, CCC-GRM-25	25	Pair

MOQ = Minimum Order Quantity, OU = Order Unit

Protective Communications

3M™ PELTOR™ Torque™ Replacement Eartips

3M™ Torque™ Communication Eartips replace worn or damaged parts, helping you maintain the correct levels of protection, comfort and hygiene. Our grey, large-size eartips come in packs of 50.



- Replace damaged or worn eartips
- Maintain the right level of protection, comfort and hygiene
- Increase the effective service life of your equipment

Product ID	Part Number	Product Name	MOQ	OU
7000108492	PELTIP5	3M™ Torque™ Communication Eartips, PELTIP5-01	50	Pair

3M™ PELTOR™ Earplug Retention Cord

3M™ PELTOR™ Earplug Retention Cord is a replacement cord that can be used to connect your 3M™ PELTOR™ Electronic Earplugs.



- Replacement cord for 3M™ PELTOR™ Electronic Earplugs
- Maintain the correct levels of protection, comfort and hygiene
- Replace damaged or worn cords

Product ID	Part Number	Product Name	MOQ	OU
7100074090	TEP-CORD	3M™ PELTOR™ Tactical Earplug Replacement Cord, TEP-CORD	1	Each

Protective Communications

Over-ear Headsets

Focus

3M™ PELTOR™ WS™ ALERT™ X Headsets

3M™ PELTOR™ WS™ ALERT™ X Headset is a Bluetooth® headset with noise-cancelling boom microphone that connects to your mobile phone for hands free calls and streaming in noisy environments. The headset has a level-dependent function for ambient listening and it synchs to a mobile app so users can easily set-up and adjust the headset

- Attenuating hearing protector comes in two models: headband or a safety helmet attachment
- Bluetooth® technology for connection to an external Bluetooth® device allows for hands-free talking and streaming
- Noise-cancelling boom microphone for clear speech transmission in noisy environments



Product ID	Part Number	Product Name	MOQ	OU
7100256658	MRX21P3E4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset, Bright Yellow Cups, Hard Hat Attached, Compatible with Mobile App, MRX21P3E4WS6	1	Each
7100257811	MRX21A4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset, Bright Yellow Cups, Headband, Compatible with Mobile App, MRX21A4WS6	1	Each

Focus

3M™ PELTOR™ WS™ ALERT™ XP Headsets

With the 3M™ PELTOR™ WS™ ALERT™ XP Headset turn your hearing protector headset into a communications centre. Connect one device via Bluetooth® technology and converse in normal volume even in noisy environments with the noise-cancelling microphone.

- Hearing protector in two models: stand-alone headband or safety helmet attachment
- Bluetooth® technology for connection to one external device for hands-free talk and streaming
- Noise cancelling boom microphone for clear speech transmission in noisy environments



Product ID	Part Number	Product Name	MOQ	OU
7100256282	MRX21P3E5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, Bluetooth®, FM Radio, Grey, Helmet Attached, MRX21P3E5WS6	1	Each
7100256283	MRX21A5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, Bluetooth®, FM Radio, Grey, Headband, MRX21A5WS6	1	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Protective Communications

Focus

3M™ PELTOR™ WS™ ALERT™ XPI Headsets

With the WS™ ALERT™ XPI Headset turn your hearing protector headset into a communications centre. Connect one or two devices via Bluetooth Multipoint technology and converse in normal volume even in noisy environments with the noise-cancelling microphone.

- Hearing protector in two models: stand-alone headband or safety helmet attachment
- Level-dependent function for ambient listening to help improve your situational awareness (limited to 82 dB)
- Bluetooth® MultiPoint Technology for connection to one or two external devices for hands-free talk and streaming



Product ID	Part Number	Product Name	MOQ	OU
7100205304	MRX21P3E3WS6	3M™ PELTOR™ WS™ ALERT™ XPI Headset, 30 dB, Bluetooth, Mobile App, Hard Hat Attached, MRX21P3E3WS6	1	Each
7100205302	MRX21A3WS6	3M™ PELTOR™ WS™ ALERT™ XPI Headset, 30 dB, Bluetooth, Mobile App, Headband, MRX21A3WS6	1	Each
7100205297	MRX21P3E3WS6-ACK	3M™ PELTOR™ WS™ ALERT™ XPI Headset, 30 dB, Bluetooth, Mobile App, Includes Accessories, Hard Hat Attached, MRX21P3E3WS6-ACK	1	Each
7100205299	MRX21A3WS6-ACK	3M™ PELTOR™ WS™ ALERT™ XPI Headset, 30 dB, Bluetooth, Mobile App, Includes Accessories, Headband, MRX21A3WS6-ACK	1	Each

Focus

3M™ PELTOR™ WS™ ProTac™ XPI Headsets

3M™ PELTOR™ WS™ ProTac™ XPI is a range of level-dependent Bluetooth® headsets for effective hearing protection without compromising communication. These innovative headsets are equipped with level-dependent microphones for ambient sound awareness and communication in noisy environments. Bluetooth connectivity allows seamless connection to enabled devices and the headsets feature IP68 classified noise-cancelling microphones. They come in a high visibility yellow colour, with a headband, neckband or helmet attachment, and are also available with FLX2 accessory connectors.

- Helps provide hearing protection and wireless communication
- Level-dependent for ambient listening
- Bluetooth® connectivity for seamless connection



Product ID	Part Number	Product Name	MOQ	OU
7100195960	MT15H7P3EWS6	3M™ PELTOR™ WS™ ProTac XPI Level Dependent Bluetooth® Headset, Yellow, Hard Hat Attached, MT15H7P3EWS6	1	Each
7100195906	MT15H7AWS6-111	3M™ PELTOR™ WS™ ProTac XPI Level Dependent Bluetooth® Headset, Yellow, Headband, FLX2, MT15H7AWS6-111	1	Each
7100196045	MT15H7AWS6	3M™ PELTOR™ WS™ ProTac XPI Level Dependent Bluetooth® Headset, Yellow, Headband, MT15H7AWS6	1	Each
7100195976	MT15H7BWS6-111	3M™ PELTOR™ WS™ ProTac XPI Level Dependent Bluetooth® Headset, Yellow, Neckband, FLX2, MT15H7BWS6-111	1	Each
7100195961	MT15H7P3EWS6-111	3M™ PELTOR™ WS™ ProTac™ XPI Level Dependent Bluetooth® Headset, Yellow, Hard Hat Attached, FLX2, MT15H7P3EWS6-111	1	Each

Protective Communications

3M™ PELTOR™ ProTac III Headsets

3M™ PELTOR™ ProTac™ III Headset with level-dependent function for ambient listening helps you focus on your work and communicate with colleagues in noisy environments, without removing the hearing protection. Stereo feedback will allow you to hear and better determine direction of alarms, warning cries, backing vehicles and so on. Headset unit has a rugged design with dual shells. The electronics are protected from moisture and sweat, from both the inside and the outside. Smart technology, practical design and user friendly functions will help you weather rough days in the field.



- Hearing protector helps protect against harmful noise, whilst allowing ambient sounds to be heard
- Built-in level-dependent function allows the wearer to hear ambient sounds, such as conversations, machine sounds and warning signals
- 3.5 mm stereo jack to connect to your mobile phone or two-way radio to hear the call right in your ear

Product ID	Part Number	Product Name	MOQ	OU
7100088455	719057	3M™ PELTOR™ ProTac™ III Headset, 25 dB, Slim Cups, Black, Hard Hat Attached, MT13H220P3E	1	Each
7100088456	719058	3M™ PELTOR™ ProTac™ III Headset, 26 dB, Slim Cups, Black, Headband, MT13H220A	1	Each
7100088423	719059	3M™ PELTOR™ ProTac™ III Headset, 31 dB, Black, Hard Hat Attached, MT13H221P3E	1	Each
7100088424	719060	3M™ PELTOR™ ProTac™ III Headset, 32 dB, Black, Headband, MT13H221A	1	Each

3M™ PELTOR™ LiteCom Plus Headsets

3M™ PELTOR™ LiteCom Plus Headsets are our robust hearing protectors with a built-in analogue two-way communication radio, noise cancelling dynamic microphone, Lithium-Ion battery and level dependent functionality for ambient listening. Available in headband and helmet mounted models.



- Hearing protector with built-in analogue two-way communication radio
- Available in 16 channel PMR 446 MHz version with 121 sub-channels
- Level-dependent technology helps improve situational awareness and communication

Product ID	Part Number	Product Name	MOQ	OU
7100229277	MT73H7P3E4410EU	3M™ PELTOR™ LiteCom Plus Headset, 32 dB, PMR446 MHz, Hard Hat Attached, MT73H7P3E4410EU	1	Each
7100229259	MT73H7A4410EU	3M™ PELTOR™ LiteCom Plus Headset, 32 dB, PMR446 MHz, Headband, MT73H7A4410EU	1	Each

Focus

3M™ PELTOR™ LiteCom Headsets

3M™ PELTOR™ LiteCom Headsets are our robust hearing protectors with a built-in analogue two-way communication radio and noise cancelling dynamic microphone. Available in headband, neckband and helmet mounted models.



- Hearing protector with built-in communication radio for „hands free“ short-range communications with other LiteCom headsets and comms radio devices on the same frequency
- 8 channels and 38 sub channels allow users to communicate individually using the same channel
- An auxiliary input also lets you connect a mobile phone or external com radio, regardless of the frequency

Product ID	Part Number	Product Name	MOQ	OU
7000108540	88028	3M™ PELTOR™ LiteCom Headset, 32 dB, PMR 446 MHz, Headband, MT53H7A4400-EU	1	Each
7000108542	MT53H7B4400-EU	3M™ PELTOR™ LiteCom Headset, 32 dB, PMR 446 MHz, Neckband, MT53H7B4400-EU	1	Each
7000108541	LITECOMP	3M™ PELTOR™ LiteCom Headset, 33 dB, PMR 446 MHz, Hard Hat Attached, MT53H7P3E4400-EU	1	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Protective Communications

Focus

3M™ PELTOR™ WS™ LiteCom Plus Headsets

3M™ PELTOR™ WS™ LiteCom Plus Headset features integrated pre-programmed two-way radio, Bluetooth® Multipoint connectivity, noise-cancelling microphones, and a level-dependent function for ambient listening. The headset is available with a headband, neckband or as helmet attachments.



- Hearing protector with built-in two-way radio
- Level-dependent technology helps improve situational awareness and communication
- Bluetooth® multipoint connectivity allows seamless connection of mobile devices

Product ID	Part Number	Product Name	MOQ	OU
7100204418	MT73H7P3E4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset PMR446 MHz, Analog, Hard Hat Attached, MT73H7P3E4410WS6EU	1	Each
7100204388	MT73H7A4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset PMR446 MHz, Analog, Headband, MT73H7A4410WS6EU	1	Each
7100201938	MT73H7B4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset PMR446 MHz, Analog, Neckband, MT73H7B4410WS6EU	1	Each

3M™ PELTOR™ WS™ LiteCom Pro III Headsets

3M™ PELTOR™ WS™ LiteCom Pro III Headsets are our high performance hearing protectors with a built-in analogue and digital programmable two-way communication radio, level-dependent functionality for ambient listening, Bluetooth® multipoint connectivity, Lithium-Ion rechargeable battery and an external connection jack. Available in headband, neckband and helmet-mounted models.



- Hearing protector with built-in programmable analogue and digital two-way radio
- Push-to-listen quick activation of level dependent function
- Push-to-listen quick activation of level dependent function

Product ID	Part Number	Product Name	MOQ	OU
7100098898	MT73H7B4D10EU-50	3M™ PELTOR™ WS™ LiteCom PRO III EX Headset, 32 dB, 403-470 MHz, Analogue/Digital, Neckband, MT73H7B4D10EU-50	1	Each
7100098897	MT73H7F4D10EU-50	3M™ PELTOR™ WS™ LiteCom PRO III EX Headset, 33 dB, 403-470 MHz, Analogue/Digital, Headband, MT73H7F4D10EU-50	1	Each
7100153479	MT73H7P3E4D10EU	3M™ PELTOR™ WS™ LiteCom PRO III GB Headset, 32 dB, PMR446 MHz, Analogue/Digital, Hard Hat Attached, MT73H7P3E4D10EU GB	1	Each
7100153481	MT73H7B4D10EU	3M™ PELTOR™ WS™ LiteCom PRO III GB Headset, 32 dB, PMR446 MHz, Analogue/Digital, Neckband, MT73H7B4D10EU GB	1	Each
7100153423	MT73H7A4D10EU	3M™ PELTOR™ WS™ LiteCom PRO III GB Headset, 33 dB, PMR446 MHz, Analogue/Digital, Headband, MT73H7A4D10EU GB	1	Each

Protective Communications

3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headsets

3M™ PELTOR™ WorkTunes™ Pro FM Radio Headset allows you to receive FM and AM-radio and store up to 5 stations. Our headset is available as a standalone headband or as a hard hat attached model, has a 3.5 mm stereo audio input and an auto power-off function that saves battery life.



- Protect your hearing from harmful noise while enjoying FM or AM-Radio
- Built-in antenna prevents snagging on equipment
- Store up to 5 of your favourite stations

Product ID	Part Number	Product Name	MOQ	OU
7100089440	719147	3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headset, 31 dB, Black, Hard Hat Attached, HRXS221P3E	1	Each
7100089368	719149	3M™ PELTOR™ WorkTunes™ Pro AM/FM Radio Headset, 32 dB, Black, Headband, HRXS221A	1	Each

3M™ PELTOR™ CH-3 Headsets

3M™ PELTOR™ CH-3 Headsets utilise the FLX2 cable system for a simple and reliable connection. They feature a speaker system and boom microphone that's optimised for speech frequency in high noise environments and a modern cup design which provides high comfort and attenuation. Comes with a headband, neckband or helmet attachment. Available in bright yellow for the standard model or bright blue to indicate Explosive atmosphere (Ex) approval.



- Communication headsets that help provide hearing protection
- Optimised speakers for use in noisy environments
- FLX2 accessory connector for easy adaptation to required solution

Product ID	Part Number	Product Name	MOQ	OU
7100203635	MT74H52P3E-110	3M™ PELTOR™ CH-3 Headset, Hard Hat Attached, MT74H52P3E-110	1	Each
7100203637	MT74H52A-110	3M™ PELTOR™ CH-3 Headset, Headband, MT74H52A-110	1	Each
7100203636	MT74H52B-110	3M™ PELTOR™ CH-3 Headset, Neckband, MT74H52B-110	1	Each

3M™ PELTOR™ CH-3 Listen Only Headsets

3M™ PELTOR™ CH-3 Listen Only Headsets utilise the FLX2 cable system for a simple and reliable connection. They feature a speaker system that's optimised for speech frequency in high noise environments and a modern cup design which provides high comfort and attenuation. Comes with a headband, neckband or helmet attachment. Available in bright yellow for the standard model or bright blue to indicate Explosive atmosphere (Ex) approval.



- Hear-only communication headsets that help provide hearing protection
- Optimised speakers for use in noisy environments
- FLX2 accessory connector for easy adaptation to required solution

Product ID	Part Number	Product Name	MOQ	OU
7100203297	HT52P3E-112-50	3M™ PELTOR™ CH-3 Listen Only Headset, Ex approved, Hard Hat Attached, HT52P3E-112-50	1	Each
7100203639	HT52A-112-50	3M™ PELTOR™ CH-3 Listen Only Headset, Ex approved, Headband, HT52A-112-50	10	Each
7100203302	HT52P3E-112	3M™ PELTOR™ CH-3 Listen Only Headset, Hard Hat Attached, HT52P3E-112	1	Each
7100203299	HT52A-112	3M™ PELTOR™ CH-3 Listen Only Headset, Headband, HT52A-112	1	Each
7100203298	HT52B-112	3M™ PELTOR™ CH-3 Listen Only Headset, Neckband, HT52B-112	1	Each

Protective Communications

3M™ PELTOR™ CH-3 Headsets with PTT Adaptor

3M™ PELTOR™ CH-3 Headsets with PTT Adaptor utilise the FLX2 cable system for a simple and reliable connection. They feature a speaker system and boom microphone that's optimised for speech frequency in high noise environments and a modern cup design which provides high comfort and attenuation. Comes with a headband, neckband or helmet attachment. Available in bright yellow for the standard model or bright blue to indicate Explosive atmosphere (Ex) approval.



- Push to talk (PTT) communication headsets that help provide hearing protection
- Optimised speakers for use in noisy environments
- FLX2 accessory connector for easy adaptation to required solution

Product ID	Part Number	Product Name	MOQ	OU
7100203150	MT74H52P3E-111	3M™ PELTOR™ CH-3 Headset with PTT Adapter, Hard Hat Attached, MT74H52P3E-111	1	Each
7100203638	MT74H52A-111	3M™ PELTOR™ CH-3 Headset with PTT Adapter, Headband, MT74H52A-111	1	Each
7100205729	MT74H52B-111	3M™ PELTOR™ CH-3 Headset with PTT Adapter, Neckband, MT74H52B-111	1	Each

3M™ PELTOR™ CH-5 High Attenuation Headsets

3M™ PELTOR™ CH-5 Headset provides protection against hazardous levels of noise including impulse sounds. The robust headset is designed to be used in extreme and rough environments with high noise.



- High attenuation headset helps provide good impulse sound protection
- Water tight boom microphone approved to IP68
- One of the highest attenuation headsets on the market

Product ID	Part Number	Product Name	MOQ	OU
7100099881	MT73H450P3E-77 GB	3M™ PELTOR™ CH-5 High Attenuation Headset, 36 db, Hi-Viz, Flex Connector, Hard Hat Attached, MT73H450P3E-77 GB	1	Each
7100106867	MT73H450P3E GB	3M™ PELTOR™ CH-5 High Attenuation Headset, 36 db, Hi-Viz, Hard Hat Attached, MT73H450P3E GB	1	Each
7100099845	MT73H450A-38	3M™ PELTOR™ CH-5 High Attenuation Headset, 37 dB, Grey, Headband, MT73H450A-38	1	Each
7100099883	MT73H450A-86	3M™ PELTOR™ CH-5 High Attenuation Headset, 37 dB, Grey, Headband, MT73H450A-86	1	Each
7100099844	MT73H450A-77 GB	3M™ PELTOR™ CH-5 High Attenuation Headset, 37 dB, Hi-Viz, Flex Connector, Headband, MT73H450A-77 GB	1	Each
7100106703	MT73H450A GB	3M™ PELTOR™ CH-5 High Attenuation Headset, 37 dB, Hi-Viz, Headband, MT73H450A GB	1	Each

3M™ PELTOR™ ALERT™ FM Radio Headsets

The 3M™ PELTOR™ ALERT™ FM Radio Headset has been developed to improve safety and motivation for users in noisy environments. It enables you to listen to FM-radio or an external device at the same time as you can hear your surroundings and communicate with your colleagues without taking the hearing protector off.



- Protect your hearing and listen to the radio - at the same time
- Excellent FM-radio reception
- Level dependent function lets the user hear surrounding noise and converse with colleagues

Product ID	Part Number	Product Name	MOQ	OU
7000108538	ALERTPWS	3M™ PELTOR™ ALERT™ FM-Radio Headset, 30 dB, Hard Hat Attached, M2RX7P3E2-01	1	Each
7000108376	M2RX7A2	3M™ PELTOR™ ALERT™ FM-Radio Headset, 30 dB, Headband, M2RX7A2-01	1	Each

Protective Communications

Protective Communications Parts & Accessories

3M™ PELTOR™ WS™ ALERT™ Headset Covers

Product ID	Part Number	Product Name	MOQ	OU
7100253622	210300664SV1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Black, 1 pair (left+right), 210300-664-SV/1, 25pair/Case	1	Each
7100246985	210300664BA1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Blue, 1 pair (left+right), 210300-664-BA/1, 25pair/Case	1	Each
7100264002	210300664GY1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Bright Yellow, 1 Pair (Left+Right), 210300-664-GY/1, 25pair/Case	1	Each
7100264003	210300664GF1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Grey, 1 pair (left+right), 210300-664-GF/1, 25 Pair/Case	1	Each
7100240624	210300650GB1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Neon Green, 1 pair (left+right), 210300-664-GB/1, 25pair/Case	1	Each
7100246983	210300664OR1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Orange, 1 pair (left+right), 210300-664-OR/1, 25pair/Case	1	Each
7100247026	210300664RE1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Pink, 1 Pair (left+right), 210300-664-RE/1, 25pair/Case	1	Each
7100246986	210300664RD1	3M™ PELTOR™ Covers for WS™ ALERT™ Headsets, Red, 1 Pair (Left+Right), 210300-664-RD/1, 25pair/Case	1	Each

3M™ PELTOR™ Hygiene Kit for Communication Headset

Product ID	Part Number	Product Name	MOQ	OU
7100113964	HY83	3M™ PELTOR™ Hygiene Kit for WS™ LiteCom Pro III Headset, HY83	1	Each

3M™ PELTOR™ Sealing Rings

Product ID	Part Number	Product Name	MOQ	OU
7000127268	HY80N	3M™ PELTOR™ Replacement Gel Cushions, Camelback, HY80	1	Each

3M™ PELTOR™ Microphones

Product ID	Part Number	Product Name	MOQ	OU
7100099097	MT7V/1	3M™ PELTOR™ Boom Microphone, MT7V/1	1	Each
7100240432	MT7N021	3M™ PELTOR™ Dynamic Boom Microphone MT7N-02/1, 270 mm Cable with J22 Plug including Wind Protection M40/1, 50 Each/Case	1	Each
7100240278	MT7N1	3M™ PELTOR™ Dynamic Boom Microphone, 240mm cable with J22 plug including wind protection M40/1, MT7N/1, 1 Each/Case	1	Each

Protective Communications

3M™ PELTOR™ Electret Microphones

Product ID	Part Number	Product Name	MOQ	OU
7100264326	MT53N141	3M™ PELTOR™ Electret Boom Microphone MT53N-14/1, with Plug, 240mm, incl. Windshield, M995/2	1	Each
7100240431	MT53N111	3M™ PELTOR™ Electret boom microphone, 240mm cable with J22 plug including wind protection M995/2, MT53N-11/1, 1 Each/Case	1	Each
7100245437	MT53N12A1	3M™ PELTOR™ Electret boom microphone, 270mm cable with J22 plug including wind protection M995/2, MT53N-12A/1, 1 Each/Case	1	Each

3M™ PELTOR™ Throat Microphones

Product ID	Part Number	Product Name	MOQ	OU
7000040037	MT90-02	3M™ PELTOR™ Amplify Throat Microphone, Dynamic, MT90-02	1	Each

3M™ PELTOR™ Microphone Protector Hygiene Tape

Product ID	Part Number	Product Name	MOQ	OU
7100064281	HYM1000	3M™ PELTOR™ Microphone Protector Tape, 5m Roll, Black, HYM1000	1	Each

3M™ PELTOR™ Wind Protection Screens

Product ID	Part Number	Product Name	MOQ	OU
7010044372	M995/2	3M™ PELTOR™ Foam Windssock for Electret Boom Microphone, M995	1	Each
7000039648	M40/1	3M™ PELTOR™ Microphone Wind Cover for MT7 Microphone, M40/1	1	Each
7000039650	M60/2	3M™ PELTOR™ Microphone Wind Cover, M60/2	1	Each

3M™ PELTOR™ Charging Cables

Product ID	Part Number	Product Name	MOQ	OU
7100067410	AL2AH	3M™ PELTOR™ Battery Charging Cable for Lite-Com Pro II, AL2AH	1	Each
7100075611	FR09	3M™ PELTOR™ USB Charger Cable, FR09 for Lite-Com BRS Headset Battery ACK053	1	Each

3M™ PELTOR™ Rechargeable Battery

Product ID	Part Number	Product Name	MOQ	OU
7100112102	ACK082	3M™ PELTOR™ Rechargeable Li-Ion Battery, ACK082	1	Each
7100075380	ACK081	3M™ PELTOR™ Rechargeable Li-ion Battery Pack, 3.7V, 1800mAh, ACK081	1	Each
7100075338	ACK053	3M™ PELTOR™ Rechargeable NimH Battery Pack, 2.4V, 2500mAh, ACK053	1	Each

Protective Communications

3M™ PELTOR™ FLX2 Cables

Product ID	Part Number	Product Name	MOQ	OU
7100224039	FLX2-207	3M™ PELTOR™ Cable FLX2, 3-pole 1/4" Mono, FLX2-207, 120/Case	1	Each
7100191444	FLX2-204	3M™ PELTOR™ FLX2 Cable 1/4" Stereo, FLX2-204, 200/Case	1	Each
7100185762	FLX2-203	3M™ PELTOR™ FLX2 Cable 2,5mm Mono Ex Approved, FLX2-203, 120/Case	1	Each
7100185800	FLX2-205	3M™ PELTOR™ FLX2 Cable 3,5mm Mono Ex Approved, FLX2-205, 120/Case	1	Each
7100191443	FLX2-202	3M™ PELTOR™ FLX2 Cable 3,5mm Stereo, FLX2-202, 200/Case	1	Each
7100220865	FLX2-69	3M™ PELTOR™ FLX2 Cable FLX2-69 for Motorola DP2400/3441, 120/Case	1	Each
7100219827	FLX2-210	3M™ PELTOR™ FLX2 Cable FLX2-210, Straight Open End, 10m, 120/Case	1	Each
7100224037	FLX2-211	3M™ PELTOR™ FLX2 Cable FLX2-211, Curly Open End, 120/Case	1	Each
7100197719	FLX2-111	3M™ PELTOR™ FLX2 Cable Hytera PD7 Series, FLX2-111, 120/Case	1	Each
7100197556	FLX2-35	3M™ PELTOR™ FLX2 Cable Icom 2-Pin Angled, FLX2-35, 120/Case	1	Each
7100197565	FLX2-44	3M™ PELTOR™ FLX2 Cable Icom F31/41, FLX2-44, 120/Case	1	Each
7100197568	FLX2-64	3M™ PELTOR™ FLX2 Cable Icom F34/44, FLX2-64, 120/Case	1	Each
7100185799	FLX2-200	3M™ PELTOR™ FLX2 Cable J11, Ex Approved, FLX2-200, 120/Case	1	Each
7100193170	FLX2-36	3M™ PELTOR™ FLX2 Cable Kenwood 2-Pin, FLX2-36	1	Each
7100185797	FLX2-107-50	3M™ PELTOR™ FLX2 Cable Kenwood Multipin Ex approved, FLX2-107-50, 120/Case	1	Each
7100193229	FLX2-28	3M™ PELTOR™ FLX2 Cable Mobile/DECT Phone, FLX2-28, 120/Case	1	Each
7100185795	FLX2-63-50	3M™ PELTOR™ FLX2 Cable Motorola DP4000 Ex approved, FLX2-63-50, 120/Case	1	Each
7100193228	FLX2-21	3M™ PELTOR™ FLX2 Cable Motorola GP300 DP1200, FLX2-21	1	Each
7100193227	FLX2-32	3M™ PELTOR™ FLX2 Cable Motorola GP340, FLX2-32	1	Each
7100197572	FLX2-65	3M™ PELTOR™ FLX2 Cable Motorola GP344, FLX2-65, 120/Case	1	Each
7100197566	FLX2-18	3M™ PELTOR™ FLX2 Cable Motorola GP900, FLX2-18, 120/Case	1	Each
7100197718	FLX2-101	3M™ PELTOR™ FLX2 Cable Sepura STP8/9000, FLX2-101, 200/Case	1	Each
7100207323	FLX2-201	3M™ PELTOR™ FLX2 Cable, Ground Mec, FLX2-201, 200/Case	1	Each

Headsets with built-in two-way radio

3M™ PELTOR™ LiteCom PMR 446

7000108540	MT53H7A4400EU	3M™ PELTOR™ LiteCom headset headband
7000108542	MT53H7B4400EU	3M™ PELTOR™ LiteCom headset neckband
7000108541	MT53H7P3E4400EU	3M™ PELTOR™ LiteCom headset helmet attachment



Accessories

3M ID	Order number	Description
7100075338	ACK053	3M™ PELTOR™ Battery pack NiMH 2,4V 1900mAh
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100075611	FR09	3M™ PELTOR™ Battery charger with USB
7100063118	HY79	3M™ PELTOR™ Hygiene kit for other headset
7100221901	1180SV/1	3M™ PELTOR™ Battery cover black incl connection bridge
7100147895	MT53N121	3M™ PELTOR™ Microphone electret WS Alert XP, WS ALERT XPI, LiteCom etc
7010044372	M9952	3M™ PELTOR™ Wind shield to electret microphone 2 pcs/bag
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m



3M™ PELTOR™ LiteCom Plus PMR 446

Hearing protection with built-in communication radio, level dependent function and external jack. 16 channels and 121 subchannels on the frequency PMR 446 MHz.

7100229259	MT73H7A4410EU	3M™ PELTOR™ LiteCom Plus Headset headband
7100229277	MT73H7P3E4410EU	3M™ PELTOR™ LiteCom Plus Headset helmet attachment




Accessories

3M ID	Order number	Description
7100075380	ACK081	3M™ PELTOR™ Battery pack Lithium 3,7V 1800mAh
7100088372	AL2AISP	3M™ PELTOR™ Battery charger with USB
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100113964	HY83	3M™ PELTOR™ Hygiene kit for WS ProTac XPI, WS LiteCom Plus etc
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100112094	MT731	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset
7000039666	FL560250	3M™ PELTOR™ External PTT ATEX
7000040037	MT9002	3M™ PELTOR™ Throat microphone dynamic

Cables to 3M™ PELTOR™ LiteCom Plus

3M ID	Order number	Description
7100016085	FL6BR	3M™ PELTOR™ Cable LiteCom-series to J11-plug spiral





3M™ PELTOR™ WS™ LiteCom Plus PMR 446 3M™ PELTOR™ WS™ LiteCom Plus LPD 433

7100204388	MT73H7A4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset headband
7100201938	MT73H7B4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset neckband
7100204418	MT73H7P3E4410WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset helmet attachment
7100204419	MT73H7A4310WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset headband
7100204420	MT73H7B4310WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset neckband
7100204422	MT73H7P3E4310WS6EU	3M™ PELTOR™ WS™ LiteCom Plus Headset helmet attachment

Accessories

3M ID	Order number	Description
7100088372	AL2AISP	3M™ PELTOR™ Battery charger with USB
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100113964	HY83	3M™ PELTOR™ Hygiene kit for WS ProTac XPI, WS LiteCom Plus etc.
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100112094	MT731	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset
7000039666	FL560250	3M™ PELTOR™ External PTT ATEX
7000040037	MT9002	3M™ PELTOR™ Throat microphone dynamic

Example
WS LiteCom Plus can be wireless connected to a mobile phone at the same time as you use the built-in communication radio.

LiteCom Plus
WS LiteCom Plus
Phone

3M™ PELTOR™ WS™ LiteCom III GB PMR 446

7100153423	MT73H7A4D10EUGB	3M™ PELTOR™ WS LiteCom III GB headset headband
7100153481	MT73H7B4D10EUGB	3M™ PELTOR™ WS LiteCom III GB headset neckband
7100153479	MT73H7P3E4D10EUGB	3M™ PELTOR™ WS LiteCom III GB headset helmet attachment



Accessories

3M ID	Order number	Description
7100075380	ACK081	3M™ PELTOR™ Battery pack Lithium 3,7V 1800mAh
7100088372	AL2AISP	3M™ PELTOR™ Battery charger with USB
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100113964	HY83	3M™ PELTOR™ Hygiene kit for WS ProTac XPI, WS LiteCom III GB etc
7100112094	MT731	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7000040037	MT9002	3M™ PELTOR™ Throat microphone dynamic
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset
7000039666	FL560250	3M™ PELTOR™ External PTT ATEX

Cables to 3M™ PELTOR™ WS™ LiteCom PMR 446

3M ID	Order number	Description
7100016085	FL6BR	3M™ PELTOR™ Cable LiteCom-series to J11-plug spiral



Headset with Bluetooth® to cellphone or two-way radio

3M™ PELTOR™ Cover for WS™ ALERT™ Headset

3M ID	Order number	Description
7100253622	210300-664-SV/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, black, Left+Right
7100264003	210300-664-GF/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, grey, Left+Right
7100246983	210300-664-OR/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, orange, Left+Right
7100246986	210300-664-RD/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, red, Left+Right
7100264002	210300-664-GY/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, bright yellow, Left+Right
7100240624	210300-664-GB/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, neon green, Left+Right
7100247026	210300-664-RE/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, pink, Left+Right
7100246985	210300-664-BA/1	3M™ PELTOR™ Cover for WS™ ALERT™ Headset, blue, Left+Right



3M™ PELTOR™ WS™ ALERT™ XPI Headset

Headset with Bluetooth® MultiPoint, level dependent function and FM-radio

7100205302	MRX21A3WS6	3M™ PELTOR™ WS™ ALERT™ XPI Headset, App, Bluetooth® MultiPoint headband
7100205304	MRX21P3E3WS6	3M™ PELTOR™ WS™ ALERT™ XPI Headset, App, Bluetooth® MultiPoint helmet attachment
7100205299	MRX21A3WS6-ACK	3M™ PELTOR™ WS™ ALERT™ XPI Headset, App, ACK, Bluetooth® MultiPoint incl battery and charger headband
7100205297	MRX21P3E3WS6-ACK	3M™ PELTOR™ WS™ ALERT™ XPI Headset, App, ACK, Bluetooth® MultiPoint incl battery and charger helmet attachment



Accessories

3M ID	Order number	Description
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100075611	FR09	3M™ PELTOR™ Battery charger with USB
7100064688	LR6NM	3M™ PELTOR™ Rechargeable battery AA NiMH 1,5V 2100 mAh
7100122439	HY82	3M™ PELTOR™ Hygiene kit for WS Alert XP, WS ALERT XPI, DAB+ FM-radio
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100148519	MT12SP	3M™ PELTOR™ Ambient noise microphone incl wind protection
7100264326	MT53N-14/1	3M™ PELTOR™ Electret boom microphone, MT53N-14/1 incl windshield M995/2
7010044372	M9952	3M™ PELTOR™ Wind shield to electret microphone 2 pcs/bag
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7100064410	HY100A	3M™ PELTOR™ HY100A Clean Hygiene Pad
7100147892	AG9-20/1	3M™ PELTOR™ Headband spare part
7100088344	L201AX03SP	3M™ PELTOR™ Cable to helmet attachment complete
7100147934	P3EG-F/2	3M™ PELTOR™ Helmet attachment with friction sleeve
7000108550	A44F1	3M™ PELTOR™ Guide with microphone holder and friction sleeve

Note that the batteries LR6NM have the selling unit "each" and that you need 2 pcs to each headset.



FR08



FR09



LR6NM

Example

Wireless connection via Bluetooth MultiPoint to two cellphones for calls and streaming.



Android

WS ALERT XPI App

IOS

3M™ PELTOR™ WS™ ALERT™ XP Headset

Headset with Bluetooth®, level dependent function and FM-radio

7100256283	MRX21A5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, App, Headband
7100256282	MRX21P3E5WS6	3M™ PELTOR™ WS™ ALERT™ XP Headset, App, Helmet attachment



Accessories

3M ID	Order number	Description
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100075611	FR09	3M™ PELTOR™ Battery charger with USB
7100064688	LR6NM	3M™ PELTOR™ Rechargeable battery AA NiMH 1,5V 2100 mAh
7100122439	HY82	3M™ PELTOR™ Hygiene kit for WS™ ALERT™ XP, WS™ ALERT™ XPI, DAB+
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100148519	MT12SP	3M™ PELTOR™ Ambient noise microphone incl wind protection
7100264326	MT53N-14/1	3M™ PELTOR™ Electret boom microphone, MT53N-14/1 incl windshield M995/2
7010044372	M9952	3M™ PELTOR™ Wind shield to electret microphone 2 pcs/bag
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7100147892	AG9-20/1	3M™ PELTOR™ Headband spare part
7100088344	L201AX03SP	3M™ PELTOR™ Cable to helmet attachment complete
7100147934	P3EG-F/2	3M™ PELTOR™ Helmet attachment with friction sleeve
7000108550	A44F1	3M™ PELTOR™ Guide with microphone holder and friction sleeve

Example
Wireless connection via Bluetooth for phone calls and streaming.

WS ALERT XP
Phone

3M™ PELTOR™ WS™ ALERT™ X Headset

Headset with Bluetooth® and level dependent function

7100257811	MRX21A4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset, App, bright yellow, headband
7100256658	MRX21P3E4WS6	3M™ PELTOR™ WS™ ALERT™ X Headset, App, bright yellow, helmet attachment



Accessories

3M ID	Order number	Description
7100122439	HY82	3M™ PELTOR™ Hygiene kit for WS™ ALERT™ X
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100148519	MT12SP	3M™ PELTOR™ Ambient noise microphone incl wind protection
7100264326	MT53N-14/1	3M™ PELTOR™ Electret boom microphone, MT53N-14/1 incl windshield M995/2
7010044372	M9952	3M™ PELTOR™ Wind shield to electret microphone 2 pcs/bag
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m
7100064410	HY100A	3M™ PELTOR™ HY100A Clean Hygiene Pad
7100147892	AG9-20/1	3M™ PELTOR™ Headband spare part
7100088344	L201AX03SP	3M™ PELTOR™ Cable to helmet attachment complete
7100147934	P3EG-F/2	3M™ PELTOR™ Helmet attachment with friction sleeve
7000108550	A44F1	3M™ PELTOR™ Guide with microphone holder and friction sleeve

Example
Wireless connection via Bluetooth for phone calls and streaming.

WS ALERT X
Phone


3M™ PELTOR™ WS™ ProTac™ XPI 3M™ PELTOR™ WS™ ProTac™ XPI FLX2



7100196045	MT15H7AWS6	3M™ PELTOR™ WS ProTac XPI Headset headband
7100195960	MT15H7P3EWS6	3M™ PELTOR™ WS ProTac XPI Headset helmet attachment
7100195906	MT15H7AWS6-111	3M™ PELTOR™ WS ProTac XPI Headset FLX2 headband
7100195961	MT15H7P3EWS6-111	3M™ PELTOR™ WS ProTac XPI Headset FLX2 helmet attachment
7100195976	MT15H7BWS6-111	3M™ PELTOR™ WS ProTac XPI Headset FLX2 neckband

Accessories

3M ID	Order number	Description
7100075338	ACK053	3M™ PELTOR™ Battery pack NiMH 2,4V 1900mAh
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100075611	FR09	3M™ PELTOR™ Battery charger with USB
7100221901	1180SV/1	3M™ PELTOR™ Battery cover black incl connection bridge
7100113964	HY83	3M™ PELTOR™ Hygiene kit for WS ProTac XPI, WS LiteCom Plus etc
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset
7100221899	MT73021	3M™ PELTOR™ Microphone dynamic IP68 with long cable
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m



WS adapter to Flex-cabel to communication radio

3M ID	Order number	Description
7100011357	FL6077WS5	3M™ PELTOR™ WS adapter Flex



Headset with FLX2 cable to cellphone or two-way radio

3M™ PELTOR™ WS™ ProTac™ XPI FLX2

7100195906	MT15H7AWS6-111	3M™ PELTOR™ WS™ ProTac™ XPI Headset FLX2 headband
7100195961	MT15H7P3EWS6-111	3M™ PELTOR™ WS™ ProTac™ XPI Headset FLX2 helmet attachment
7100195976	MT15H7BWS6-111	3M™ PELTOR™ WS™ ProTac™ XPI Headset FLX2 neckband



Accessories

3M ID	Order number	Description
7100075338	ACK053	3M™ PELTOR™ Battery pack NiMH 2,4V 1900mAh
7000108521	FR08	3M™ PELTOR™ 230 V DC to USB adapter 5V
7100075611	FR09	3M™ PELTOR™ Battery charger with USB
7100221901	1180SV/1	3M™ PELTOR™ Battery cover black incl connection bridge
7100113964	HY83	3M™ PELTOR™ Hygiene kit for WS ProTac XPI, WS LiteCom Plus etc
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset
7100221899	MT73021	3M™ PELTOR™ Microphone dynamic IP68 with long cable
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m

3M™ PELTOR™ CH-3 FLX2 Headset with PTT

7100203638	MT74H52A-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT headband
7100205729	MT74H52B-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT neckband
7100203150	MT74H52P3E-111	3M™ PELTOR™ CH-3 FLX2 Headset with PTT helmet attachment



Accessories

3M ID	Order number	Description
7100212095	HY84	3M™ PELTOR™ Hygiene kit for CH-3 Headset
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100221884	MT741	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m

FLX2 cables to WS ProTac XPI and CH-3 FLX2 Headset with PTT

3M ID	Order number	Description
7100197719	FLX2-111	3M™ PELTOR™ FLX2 cable to Hytera PD7*
7100197556	FLX2-35	3M™ PELTOR™ FLX2 cable to Icom angled 2-pin
7100197565	FLX2-44	3M™ PELTOR™ FLX2 cable to Icom F31/F41
7100197568	FLX2-64	3M™ PELTOR™ FLX2 cable to Icom F34/F44
7100193170	FLX2-36	3M™ PELTOR™ FLX2 cable to Kenwood 2-pin
7100185797	FLX2-107	3M™ PELTOR™ FLX2 cable to Kenwood NX5000
7100193228	FLX2-21	3M™ PELTOR™ FLX2 cable to Motorola GP300/DP1400
7100193227	FLX2-32	3M™ PELTOR™ FLX2 cable to Motorola GP340
7100197572	FLX2-65	3M™ PELTOR™ FLX2 cable to Motorola GP344
7100197566	FLX2-18	3M™ PELTOR™ FLX2 cable to Motorola GP900
7100220865	FLX2-69	3M™ PELTOR™ FLX2 cable to Motorola DP2400/DP3441
7100185795	FLX2-63	3M™ PELTOR™ FLX2 cable to Mototrbo DP4***
7100193229	FLX2-28	3M™ PELTOR™ FLX2 cable to Mobile/Dect phone
7100197718	FLX2-101	3M™ PELTOR™ FLX2 cable to Sepura STP 8*/9*
7100219827	FLX2-210	3M™ PELTOR™ FLX2 cable 10m straight
7100224037	FLX2-211	3M™ PELTOR™ FLX2 cable curled open end



3M™ PELTOR™ CH-3 FLX2 Headset without PTT

7100203637	MT74H52A-110	3M™ PELTOR™ CH-3 FLX2 Headset headband
7100203636	MT74H52B-110	3M™ PELTOR™ CH-3 FLX2 Headset neckband
7100203635	MT74H52P3E-110	3M™ PELTOR™ CH-3 FLX2 Headset helmet attachment



Accessories

3M ID	Order number	Description
7100212095	HY84	3M™ PELTOR™ Hygiene kit for CH-3 Headset
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions
7100221884	MT741	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m

FLX2 cables to CH-3 FLX2 Headset without PTT

3M ID	Order number	Description
7100185799	FLX2-200	3M™ PELTOR™ FLX2 cable to J11 Standard
7100207323	FLX2-201	3M™ PELTOR™ FLX2 cable to Ground Mech



FLX2-200



FLX2-200



FLX2-201

3M™ PELTOR™ CH-3 FLX2 Listen Only

7100203299	HT52A-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset headband
7100203298	HT52B-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset neckband
7100203302	HT52P3E-112	3M™ PELTOR™ CH-3 FLX2 Listen Only Headset helmet attachment



Accessories

3M ID	Order number	Description
7100212095	HY84	3M™ PELTOR™ Hygiene kit for CH-3 Headset
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions

FLX2 cables to CH-3 FLX2 Listen Only

3M ID	Order number	Description
7100191443	FLX2-202	3M™ PELTOR™ FLX2 cable to 3,5mm Stereo
7100185762	FLX2-203	3M™ PELTOR™ FLX2 cable to 2,5mm Mono
7100191444	FLX2-204	3M™ PELTOR™ FLX2 cable to 1/4" Stereo
7100185800	FLX2-205	3M™ PELTOR™ FLX2 cable to 3,5mm Mono
7100224039	FLX2-207	3M™ PELTOR™ FLX2 cable to 1/4" mono
7100207324	FLX2-208	3M™ PELTOR™ FLX2 cable to 3,5mm Threaded



FLX2-202



FLX2-203



FLX2-204



FLX2-205



FLX2-208

Headset to Flex cable (-77) for two-way radio or cellphone

3M™ PELTOR™ CH-5 High Attenuation Headset Flex

7100099844	MT73H450A77GB	3M™ PELTOR™ CH-5 High Att Headset Flex headband Hi-Viz
7100099881	MT73H450P3E77GB	3M™ PELTOR™ CH-5 High Att Headset Flex helmet attachment Hi-Viz



Accessories

3M ID	Order number	Description
7100107408	HY45	3M™ PELTOR™ Hygiene kit for CH-5 High Att Headset
7100112094	MT731	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m


Flex cables to communication radio to headset -77

3M ID	Order number	Description
7100064359	FL6U21	3M™ PELTOR™ Flex cable to headset -77 to Motorola GP300, CP040
7100064602	FL6U32	3M™ PELTOR™ Flex cable to headset -77 to Motorola GP340/380
7000107901	FL6U35	3M™ PELTOR™ Flex cable to headset -77 to Icom F3G, F4G angled
7000107902	FL6U36	3M™ PELTOR™ Flex cable to headset -77 to Kenwood 2,5-3,5 mm
7000108781	FL6U61	3M™ PELTOR™ Flex cable to headset -77 to Motorola Visar
7000108535	FL6U63	3M™ PELTOR™ Flex cable to headset -77 to Motorola Mototrbo DP3000, DP4000
7000108466	FL6U64	3M™ PELTOR™ Flex cable to headset -77 to Icom F1000/F2000, F3002/F4002
7000108467	FL6U65	3M™ PELTOR™ Flex cable to headset -77 to Motorola GP344
7000108135	FL6U71	3M™ PELTOR™ Flex cable to headset -77 to Vertex VX-160/400
7100064984	FL6U101	3M™ PELTOR™ Flex cable to headset -77 to Sepura STP8000-series



Flex cables to phone/DECT to headset -77

3M ID	Order number	Description
7100064305	FL6U28	3M™ PELTOR™ Flex cable to headset -77 to Ericsson phone DECT 2,5mm stereo





3M™ PELTOR™ CH-5 High Attenuation Headset with J11 plug

7100106703	MT73H450AGB	3M™ PELTOR™ CH-5 High Att Headset with J11-plug headband
7100106867	MT73H450P3EGB	3M™ PELTOR™ CH-5 High Att Headset with J11-plug helmet attachment

Accessories

3M ID	Order number	Description
7100107408	HY45	3M™ PELTOR™ Hygiene kit for CH-5 High Att Headset
7100112094	MT731	3M™ PELTOR™ Microphone dynamic IP68
7100112112	M1712	3M™ PELTOR™ Windshield to MT73
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m

PTT-adaptors to communication radio to PELTOR headset with J11 plug

3M ID	Order number	Description
7100049552	FL4030	3M™ PELTOR™ PTT-adapter to Motorola GP320/340
7100049623	FL4063	3M™ PELTOR™ PTT-adapter to Motorola Mototrbo DP3000, DP4000
7000107774	FL5001	3M™ PELTOR™ PTT-adapter PELTOR standard
7000039629	FL5035	3M™ PELTOR™ PTT-adapter to Kenwood 260/270 360/370
7100009674	FL5042	3M™ PELTOR™ PTT-adapter to Nokia TETRA THR880
7000107881	FL5044	3M™ PELTOR™ PTT-adapter to Icom F31/F41, F51/F61
7000108481	FL5046	3M™ PELTOR™ PTT-adapter to Icom A6/A22 (replacing FL50-T9089A)
7100011659	FL5062	3M™ PELTOR™ PTT-adapter to Motorola TETRA MTH800 / MTP850
7000039662	FL5064	3M™ PELTOR™ PTT-adapter to Icom F34, F44
7000107887	FL5066	3M™ PELTOR™ PTT-adapter to Icom IC-M1 (replacing FL50-T9088)
7000108319	FL50101	3M™ PELTOR™ PTT-adapter to Sepura Tetra STP8000
7000039651	TKD55021	3M™ PELTOR™ Shroud for PTT-adapter



Extension cables with J11 plugs

3M ID	Order number	Description
7000107866	FL3A	3M™ PELTOR™ Extension cable J11-hane to J11-hona spiral 0,4-2,0m
7000107867	FL3B	3M™ PELTOR™ Extension cable J11-hane to J11-hona spiral 0,7-4,0m
7000107868	FL3C	3M™ PELTOR™ Extension cable J11-hane to J11-hona 10m



LEMO cables to communication radio to headset -47

3M ID	Order number	Description
7000107857	FL6P32	3M™ PELTOR™ LEMO cable to headset -47 to Motorola GP340
7000108133	FL6P65	3M™ PELTOR™ LEMO cable to headset -47 to Motorola GP344



Hearing protection with level dependent function

3M™ PELTOR™ Alert™

7000108376	M2RX7A201	3M™ PELTOR™ Alert Hearing protection headband
7000108538	M2RX7P3E201	3M™ PELTOR™ Alert Hearing protection helmet attachment



Accessories

3M ID	Order number	Description
7000108359	FL6CE1	3M™ PELTOR™ Cable with 3,5mm stereo to 3,5mm stereo 1,1m
7000108833	HY81	3M™ PELTOR™ Hygiene kit for FM-radio, Radio XP, Alert
7100147755	1173SVSP	3M™ PELTOR™ Battery cover black to FM-radio, Radio XP, Alert etc
7000039650	M602	3M™ PELTOR™ Wind shield for ambient noise microphone other headset

3M™ PELTOR™ ProTac™ III

7100088456	MT13H220A	3M™ PELTOR™ ProTac™ III Slim Hearing protection headband black
7100088455	MT13H220P3E	3M™ PELTOR™ ProTac™ III Slim Hearing protection helmet attachm. black
7100088424	MT13H221A	3M™ PELTOR™ ProTac™ III Hearing protection headband black
7100088423	MT13H221P3E	3M™ PELTOR™ ProTac™ III Hearing protection helmet attachment black



Accessories

3M ID	Order number	Description
7000108359	FL6CE1	3M™ PELTOR™ Cable with 3,5mm stereo to 3,5mm stereo 1,1m
7100241871	220323-631-SV/1	3M™ PELTOR™ Covers for ProTac III Headsets, black, left+right
7100101874	HY220	3M™ PELTOR™ Hygiene kit for ProTac III, ProTac Hunter & Shooter

Hearing protection with radio

3M™ PELTOR™ WorkTunes™ Pro FM-Radio

7100088416	HRXS220A	3M™ PELTOR™ WorkTunes™ Pro FM-radio Hearing protection headband black
7100088417	HRXS220P3E	3M™ PELTOR™ WorkTunes™ Pro FM-radio Hearing protection helmet attachment black



Accessories

3M ID	Order number	Description
7000108359	FL6CE1	3M™ PELTOR™ Cable with 3,5mm stereo to 3,5mm stereo 1,1m
7100241900	220322-633-SV/1	3M™ PELTOR™ Covers for WorkTunes™ FM Radio Headsets, black, left+right
7100101874	HY220	3M™ PELTOR™ Hygiene kit for WorkTunes Pro, ProTac III etc



3M™ PELTOR™ DAB+/FM-radio

7100113507	HRXD7A01	3M™ PELTOR™ DAB+ FM Radio Hearing protection headband
7100114034	HRXD7P3E01	3M™ PELTOR™ DAB+ FM Radio Hearing protection helmet attachment black



Accessories DAB+/FM-radio, FM-radio and Radio XP

3M ID	Order number	Description
7000108359	FL6CE1	3M™ PELTOR™ Cable with 3,5mm stereo to 3,5mm stereo 1,1m
7100147755	1173SVSP	3M™ PELTOR™ Battery cover black to FM-radio, Radio XP, Alert etc
7000108833	HY81	3M™ PELTOR™ Hygiene kit for FM-radio, Radio XP, Alert
7100122439	HY82	3M™ PELTOR™ Hygiene kit for WS Alert XP, WS ALERT XPI, DAB+ FM-radio



FL6CE/1

Headsets to connect to two-way radio, ATEX approved

Via PTT-adapter with J11 jack



High attenuation headsets, standard Twin Cup with J11 plug, ATEX approved

7000108282	MT72H540F50	3M™ PELTOR™ High attenuation headset Twin Cup with J11-plug ATEX foldable headband
7000108283	MT72H540P3E50	3M™ PELTOR™ High attenuation headset Twin Cup with J11-plug ATEX helmet attachment

Accessories

3M ID	Order number	Description
7000108013	HY13	3M™ PELTOR™ Hygiene kit for Twin Cup headsets
7100247722	MT72N081	3M™ PELTOR™ Microphone dynamic with 340mm long cable
7100064281	HYM1000	3M™ PELTOR™ Mike protector 5m

Small PTT-adaptors to communication radio to PELTOR headset with J11 plug, ATEX

3M ID	Order number	Description
7000147319	FL403050	3M™ PELTOR™ PTT-adapter ATEX to Motorola GP320/340
7000147323	FL4010350	3M™ PELTOR™ PTT-adapter ATEX to Funkwerk FT4
7000147322	FL4010750	3M™ PELTOR™ PTT-adapter ATEX to Kenwood TK2160/Nextel



Listen only headset, ATEX approved



CH-3 FLX2 Listen only headset, detachable lead Ex approved

7100203639	HT52A-112-50	3M™ PELTOR™ CH-3 FLX2 Listen Only, detachable down lead, headband, Ex approved, blue
7100203297	HT52P3E-112-50	3M™ PELTOR™ CH-3 FLX2 Listen Only, detachable down lead, helmet attachment, Ex approved,

FLX2 cables for CH-3 Ex approved

3M ID	Order number	Description
7100185762	FLX2-203-50	3M™ PELTOR™ FLX2 CABLE, FLX2-203 / 2,5mm Mono Ex, 1 per bag
7100185800	FLX2-205-50	3M™ PELTOR™ FLX2 CABLE, FLX2-205 / 3,5mm Mono Ex, 1 per bag



Accessories

3M ID	Order number	Description
7100212095	HY84	3M™ PELTOR™ Hygiene kit for CH-3 Headset
7000127268	HY80	3M™ PELTOR™ HY80 Replacement Gel Cushions



Head & Face Protection

3M Science.
Applied to Life.™

**3M™ SecureFit™ Safety Helmet
X5000 and X5500 Series**

**Comfort
without
compromise.**

When you work at height or on the ground, it's just another day on the job – and we've got a safety helmet to meet the demands of it.

And when it comes to safety, 3M believes the bar can never be high enough. That's why we're proud to introduce the 3M™ SecureFit™ Safety Helmet.

Learn more at
3m.co.uk/SecureFitX5000



#3MScienceOfSafety

Choose your 3M™ SecureFit™ Safety Helmet



Features	X5500NVE	X5500V	X5000V	X5000VE
EN Standard selector			•	•
EN 397:2021+A1:2012	•	•	•	•
EN 12492:2012			•	•
EN 50365:2002 (1000Vac)	•			•
-30°C	•	•	•	•
Molten Metal (MM)	•			
Lateral Deformation (LD)	•	•	•	•
440V	•			
Ratchect suspension	•	•	•	•
4-point suspension	•	•		
6-point suspension			•	•
Foam insert			•	•
Ventilation		•	•	•
Chin strap plastic buckle				•
Chin strap magnetic buckle			•	
Lamp strap clips	•	•	•	•
Uvicator™	•	•	•	•
Reflective material			•	

Head & Face Protection

Hard Hats

Focus

3M™ SecureFit™ Safety Helmet X5000 Series

3M™ SecureFit™ Safety Helmet, X5000 Series, provides secure, comfortable and adjustable head protection for workers in a variety of situations. Our helmets feature six different settings to adjust positions and 4-point chin strap selector systems to switch between EN397 (industrial safety helmets) or EN12492 (helmets for mountaineers) certification standards. X5000 Series safety helmets are vented, brimless and have 3M™ UVi-cator™ Sensors that indicate levels of exposure to damaging ultraviolet (UV) light. They have easily-adjustable, 6-point ratchet suspension systems which feature the exclusive 3M™ Pressure Diffusion Technology. They're available in a variety of colours with reflective options available.



- Secure, comfortable head protection for working at heights and other hazardous industrial jobs
- Suspension system incorporates exclusive patented 3M™ Pressure Diffusion Technology
- 4-point chin strap selector system unique to 3M makes it possible to switch between EN 12492 (Mountaineering helmets) and EN 397 (Industrial safety helmets) standards

Product ID	Part Number	Product Name	MOQ	OU
7100175536	X5012VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Black, X5012VE-CE	4	Each
7100175512	X5003VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Blue, X5003VE-CE	4	Each
7100175533	X5004VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Green, X5004VE-CE	4	Each
7100175537	X5014VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Hi-Viz Green, X5014VE-CE	4	Each
7100175535	X5007VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Orange, X5007VE-CE	4	Each
7100175534	X5005VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Red, X5005VE-CE	4	Each
7100175101	X5001VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, White, X5001VE-CE	4	Each
7100175511	X5002VE-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, 1000V, CE, Yellow, X5002VE-CE	4	Each
7100175099	X5012V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Black, X5012V-CE	4	Each
7100175095	X5003V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Blue, X5003V-CE	4	Each
7100175096	X5004V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Green, X5004V-CE	4	Each
7100175100	X5014V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Hi-Viz Green, X5014V-CE	4	Each
7100175098	X5007V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Orange, X5007V-CE	4	Each
7100175097	X5005V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Red, X5005V-CE	4	Each
7100175093	X5001V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, White, X5001V-CE	4	Each
7100175094	X5002V-CE	3M™ SecureFit™ X5000 Safety Helmet, Vented, Reflective, CE, Yellow, X5002V-CE	4	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Head & Face Protection

Focus

3M™ SecureFit™ Safety Helmet X5500 Series

3M™ SecureFit™ Safety Helmet X5500 Series provides secure, comfortable and adjustable head protection for workers in a variety of situations. Our helmets feature adjustable positioning and easy-turning, 4-point ratchet suspension systems that features the exclusive 3M™ Pressure Diffusion Technology. X5500 Series safety helmets have 3M™ UVicator™ Sensors that indicates damaging levels of ultraviolet (UV) light. They meet the EN397 standard for general industrial use and are available in a variety of colours with or without vents.



- Secure, comfortable head protection against small falling objects and for general industrial use
- Suspension system incorporates exclusive patented 3M™ Pressure Diffusion Technology
- 4-point ratchet suspension allows wearer to customise height and fit with multiple levels of vertical adjustment

Product ID	Part Number	Product Name	MOQ	OU
7100175605	X5512NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Black, X5512NVE-CE	4	Each
7100175601	X5503NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Blue, X5503NVE-CE,	4	Each
7100175602	X5504NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Green, X5504NVE-CE	4	Each
7100175606	X5514NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Hi-Viz Green, X5514NVE-CE	4	Each
7100175545	X5514NVE-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Hi-Viz Green, X5514NVE-CE	80	Each
7100175604	X5507NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Orange, X5507NVE-CE,	4	Each
7100175603	X5505NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Red, X5505NVE-CE	4	Each
7100175538	X5501NVE-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, White, X5501NVE-CE	80	Each
7100175599	X5501NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, White, X5501NVE-CE,	4	Each
7100175539	X5502NVE-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Yellow, X5502NVE-CE	80	Each
7100175600	X5502NVE-CE	3M™ SecureFit™ X5500 Safety Helmet, Non-vented, CE, Yellow, X5502NVE-CE	4	Each
7100175597	X5512V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Black, X5512V-CE	4	Each
7100175593	X5503V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Blue, X5503V-CE	4	Each
7100175594	X5504V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Green, X5504V-CE	4	Each
7100175553	X5514V-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Hi-Viz Green, X5514V-CE	80	Each
7100175598	X5514V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Hi-Viz Green, X5514V-CE	4	Each
7100175596	X5507V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Orange, X5507V-CE	4	Each
7100175595	X5505V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Red, X5505V-CE	4	Each
7100175546	X5501V-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, White, X5501V-CE	80	Each
7100175591	X5501V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, White, X5501V-CE	4	Each
7100175547	X5502V-CE-10	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Yellow, X5502V-CE	80	Each
7100175592	X5502V-CE	3M™ SecureFit™ X5500 Safety Helmet, Vented, CE, Yellow, X5502V-CE	4	Each

Head & Face Protection

Focus

3M™ Hard Hat G3000 Series

3M™ Series G3000 hard hat has been designed in close collaboration with industrial and forestry workers. It is intended for use in harsh environments with tough demands for effective protection, excellent ventilation and a maximum field of vision. The slim design means that falling objects slide off easily and do not dislodge the helmet from its position. Softly rounded design, without any sharp or protruding components, the extremely comfortable lining and the simple adjustment of fit makes the G3000 unique.



- Hard hat designed for use in harsh environments, with excellent ventilation and a good field of vision
- 3M™ Uvicator™ sensor disc tells you when your hard hat has been over exposed to UV-radiation and it's time to replace it
- Softly rounded design helps avoid parts snagging on cables or branches

Product ID	Part Number	Product Name	MOQ	OU
7000039717	102644	3M™ Hard Hat, Uvicator, Pinlock, Non vented, Dielectric 440V, Plastic Sweatband, Red, G3001CUV-RD	20	Each
7000039718	G31CVI	3M™ Hard Hat, Uvicator, Pinlock, Non vented, Dielectric 440V, Plastic Sweatband, White, G3001CUV-VI	20	Each
7000108296	G30DGP	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Leather Sweatband, Green, G3000DUV-GP	20	Each
7000108298	G30DVI	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Leather Sweatband, White, G3000DUV-VI	20	Each
7000108288	G30DGU	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Leather Sweatband, Yellow, G3000DUV-GU	20	Each
7000039713	G30CBB	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Blue, G3000CUV-BB	20	Each
7000108289	G30CGP	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Green, G3000CUV-GP	1	Each
7000039714	G30CGB	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Hi-Viz, G3000CUV-GB	20	Each
7000039715	G30COR	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Orange, G3000CUV-OR	20	Each
7000039716	G30CRD	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Red, G3000CUV-RD	20	Each
7000009698	G30CVI	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, White, G3000CUV-VI	20	Each
7100002023	G30CGU	3M™ Hard Hat, Uvicator, Pinlock, Ventilated, Plastic Sweatband, Yellow, G3000CUV-GU	20	Each
7000039722	G31NVI	3M™ Hard Hat, Uvicator, Ratchet, Non vented, Dielectric 440V, Plastic Sweatband, White, G3001NUV-VI	20	Each
7000039719	G30NBB	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Blue, G3000NUV-BB	20	Each
7000108315	G30NGP	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Green, G3000NUV-GP	20	Each
7000108316	G30NGB	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Hi-Viz, G3000NUV-GB	20	Each
7000039720	G30NOR	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Orange, G3000NUV-OR	20	Each
7000039721	G30NRD	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Red, G3000NUV-RD	20	Each
7100001960	G30NVI	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, White, G3000NUV-VI	20	Each
7000009701	G30NGU	3M™ Hard Hat, Uvicator, Ratchet, Ventilated, Plastic Sweatband, Yellow, G3000NUV-GU	20	Each

Head & Face Protection

Focus

3M™ Elevated Temperature Hard Hat Series G3501 Series

Temperature extremes, metal sparks and splashes – that’s the job. And it’s a tough environment to work in. 3M™ High Heat Helmet Series G3501 is designed to offer high levels of protection for the toughest of applications. The helmet is also the platform for a range of hearing, eye and face protection products that are designed to withstand the metal working environments without compromising compatibility, comfort or easy of use. Available in six colours, with pinlock or ratchet suspension.



- Lightweight high heat hard hat compatible with 3M eye, face and hearing protection
- Leather sweatband for improved comfort
- Head harness can be rotated 180° for better visibility when working in confined spaces

Product ID	Part Number	Product Name	MOQ	OU
7100077171	G3501MBB	3M™ High Heat Hard Hat, Ratchet, Non vented, 1000V, Leather Sweatband, Blue, G3501M-BB	20	Each
7100077212	G3501MOR	3M™ High Heat Hard Hat, Ratchet, Non vented, Dielectric 1000V, Leather Sweatband, Orange, G3501M-OR	20	Each
7100077179	G3501MRD	3M™ High Heat Hard Hat, Ratchet, Non vented, Dielectric 1000V, Leather Sweatband, Red, G3501M-RD	20	Each
7100077208	G3501MVI	3M™ High Heat Hard Hat, Ratchet, Non vented, Dielectric 1000V, Leather Sweatband, White, G3501M-VI	20	Each
7100077280	G3501MGU	3M™ High Heat Hard Hat, Ratchet, Non vented, Dielectric 1000V, Leather Sweatband, Yellow, G3501M-GU	20	Each

3M™ Hard Hat H700 Series

3M™ Hard Hats Series H700 is our series of lightweight hard hats with plastic sweatbands and ventilated headbands for improved comfort. They feature a short peak and a head harness that can be rotated 180° for improved visibility. They’re available with pinlock or ratchet suspension.



- Comfortable, tough and lightweight protective hard hats
- Short peak gives improved upwards visibility
- Head harness can be rotated 180° for better visibility when working in confined spaces

Product ID	Part Number	Product Name	MOQ	OU
7000104210	H700N-BB	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, Blue, H700N-BB	20	Each
7000104211	H700N-GP	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, Green, H700N-GP	20	Each
7000104213	H700N-OR	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, Orange, H700N-OR	20	Each
7000104212	H700N-RD	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, Red, H700N-RD	20	Each
7000104208	H700N-VI	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, White, H700N-VI	20	Each
7000104209	H700N-GU	3M™ Hard Hat, Ratchet, Ventilated, Plastic Sweatband, Yellow, H700N-GU	20	Each

Head & Face Protection

3M™ Forestry Hard Hat Combination H700 Series

The 3M™ Hard Hat Forestry Kit is designed for forestry and agriculture, but is adaptable to any industry. This combination kit includes head, face and hearing protection solutions.



- Suspension sits lower on the head for a balanced fit that helps reduce pressure and increase security
- Metal mesh faceshield provides ventilation and face protection
- 3M™ PELTOR™ Ear muff features earcup pivot points for comfort and efficiency

Product ID	Part Number	Product Name	MOQ	OU
7100096305	H700NOR51V4G	3M™ Forestry Hard Hat Combination, H700 Orange Hard Hat, Optime I Earmuffs, Steel Mesh Faceshield V4G, H700NOR51V4G	1	Each

3M™ Headgear Combinations G500 Series

The 3M™ Headgear G500 is a versatile and comfortable solution for use as a standalone face protection system or for combined face and hearing protection.



- Ventilation for increased comfort
- Design incorporates a cable holder for PELTOR™ Communication products
- A wide range of visors and face shields available for many industrial applications

Product ID	Part Number	Product Name	MOQ	OU
7000103790	G500V5CH510OR	3M™ Headgear Combination, Forestry, Orange, G500V5CH510-OR	12	Each
7000038216	G500-GU	3M™ Headgear Combination, Industry, Yellow, G500-GU	10	Each
7100029146	G500V5FH	3M™ Headgear Combination, Industry, Yellow, G500V5F11H51-GU	12	Each

Head & Face Protection

Focus

3M™ First Base™ 3 Bump Caps

3M™ First Base™ 3 Bump Caps provide industrial head protection to EN812:A1. They come in a range of styles, with a variety of peak lengths, fabrics and colours. These bump caps incorporate an ABS shell, ergonomically designed for comfort.



- Protects wearer from light contact with stationary objects
- Provides industrial bump protection to EN812:A1
- Patented shell design provides enhanced coverage for a wide range of head sizes

Product ID	Part Number	Product Name	MOQ	OU
7100217750	2021101	3M™ First Base™ 3 Bump Cap 2021101, Extra, Navy Blue, Reduced Peak, 55mm	20	Each
7100217836	2021200	3M™ First Base™ 3 Bump Cap 2021200, Winter, Navy Blue, Reduced Peak, 55mm	20	Each
7100217837	2021209	3M™ First Base™ 3 Bump Cap 2021209, Winter, High Visibility, Yellow Reduced Peak, 55mm	20	Each
7100217838	2021218	3M™ First Base™ 3 Bump Cap 2021218, Winter, High Visibility, Orange Reduced Peak, 55mm	20	Each
7100217844	2021866	3M™ First Base™ 3 Bump Cap 2021866, Classic, High Visibility, Yellow Reduced Peak, 55mm	20	Each
7100232846	2021867	3M™ First Base™ 3 Bump Cap 2021867, Classic, High Visibility, Yellow Standard Peak, 70mm	20	Each
7100217847	2021875	3M™ First Base™ 3 Bump Cap 2021875, Classic, High Visibility, Orange Standard Peak, 70mm	20	Each
7100217850	2030031	3M™ First Base™ 3 Bump Cap 2030031, Classic, Navy Blue, Reduced Peak, 55mm	20	Each
7100217852	2030037	3M™ First Base™ 3 Bump Cap 2030037, Classic, Navy Blue, Micro Peak, 25mm	20	Each
7100217854	2030043	3M™ First Base™ 3 Bump Cap 2030043, Classic, Navy Blue, Standard Peak, 70mm	20	Each
7100217856	2030595	3M™ First Base™ 3 Bump Cap 2030595, Classic, Dark Green, Micro Peak, 25mm	20	Each
7100217857	2030596	3M™ First Base™ 3 Bump Cap 2030596, Classic, Dark Green, Reduced Peak, 55mm	20	Each
7100217858	2030597	3M™ First Base™ 3 Bump Cap 2030597, Classic, Red Standard Peak, 70mm	20	Each
7100217859	2030599	3M™ First Base™ 3 Bump Cap 2030599, Classic, Royal Blue, Standard Peak, 70mm	20	Each
7100217860	2030601	3M™ First Base™ 3 Bump Cap 2030601, Classic, Royal Blue, Reduced Peak, 55mm	20	Each
7100217861	2030604	3M™ First Base™ 3 Bump Cap 2030604, Classic, White Reduced Peak, 55mm	20	Each
7100217862	2030605	3M™ First Base™ 3 Bump Cap 2030605, Classic, Grey, Standard Peak, 70mm	20	Each
7100217863	2030606	3M™ First Base™ 3 Bump Cap 2030606, Classic, Grey, Micro Peak, 25mm	20	Each
7100217864	2030607	3M™ First Base™ 3 Bump Cap 2030607, Classic, Grey, Reduced Peak, 55mm	20	Each
7100217865	2030608	3M™ First Base™ 3 Bump Cap 2030608, Classic, Black Standard Peak, 70mm	20	Each
7100217866	2030609	3M™ First Base™ 3 Bump Cap 2030609, Classic, Black Micro Peak, 25mm	20	Each
7100217867	2030610	3M™ First Base™ 3 Bump Cap 2030610, Classic, Black Reduced Peak, 55mm	20	Each
7100217868	2030616	3M™ First Base™ 3 Bump Cap 2030616, Classic, Red Reduced Peak, 55mm	20	Each
7100217873	2031214	3M™ First Base™ 3 Bump Cap 2031214, Elite, Navy/Grey, Standard Peak	20	Each
7100217874	2031215	3M™ First Base™ 3 Bump Cap 2031215, Elite, Navy/Grey, Micro Peak, 25mm	20	Each
7100217875	2031216	3M™ First Base™ 3 Bump Cap 2031216, Elite, Navy/Grey, Reduced Peak, 55mm	20	Each
7100217876	2031217	3M™ First Base™ 3 Bump Cap 2031217, Elite, Black/Grey, Standard Peak, 70mm	20	Each
7100217877	2031219	3M™ First Base™ 3 Bump Cap 2031219, Elite, Black/Grey, Reduced Peak, 55mm	20	Each

Head & Face Protection

Focus

3M™ First Base™ + Bump Cap

3M™ First Base™ + Bump Caps are designed to provide limited head protection from bumps and minor lacerations to the head from stationary objects. They offer industrial bump protection to EN812 with their patented flexible shell design manufactured from durable ABS plastic.



- Provide industrial bump protection to EN812
- Low profile design
- Flexible shell made with ABS plastic, can be removed for cleaning

Product ID	Part Number	Product Name	MOQ	OU
7100206561	2014278	3M™ First Base™ + Bump Cap 2014278, Navy Blue, Standard Peak, 70mm	20	Each
7100206582	2014280	3M™ First Base™ + Bump Cap 2014280, Navy Blue, Reduced Peak, 55mm	20	Each
7100206586	2014282	3M™ First Base™ + Bump Cap 2014282, Black, Standard Peak, 70mm	20	Each
7100206562	2014284	3M™ First Base™ + Bump Cap 2014284, Black, Reduced Peak, 55mm	20	Each
7100206593	2014288	3M™ First Base™ + Bump Cap 2014288, Royal Blue, Standard Peak, 70mm	20	Each
7100208068	2014286	3M™ First Base™ + Bump Cap 2014288, Royal Blue, Reduced Peak, 55mm	20	Each
7100206560	2014298	3M™ First Base™ + Bump Cap 2014298, Grey, Standard Peak, 70mm	20	Each
7100206559	2014300	3M™ First Base™ + Bump Cap 2014300, Grey, Reduced Peak, 55mm	20	Each
7100206581	2018529	3M™ First Base™ + Bump Cap 2018529, Navy Blue, Micro Peak, 25mm	20	Each
7100207096	2018550	3M™ First Base™ + Bump Cap 2018550, Grey, Micro Peak, 25mm	20	Each

Head & Face Protection

Faceshields

3M™ SecureFit™ Short Visors for X5 Series Safety Helmets

3M™ X5 SV-Series Faceshields is a range of short polycarbonate faceshields, certified to EN 166:2001, and designed to protect against impact of high speed particles and other industrial or forestry hazards. These short faceshields are designed to fit 3M™ SecureFit™ X5000 & X5500 Helmets



- Molded out of polycarbonate for impact protection in a variety of applications
- Features an anti-fog, anti-scratch coating
- Available in clear, grey, and amber

Product ID	Part Number	Product Name	MOQ	OU
7100176968	X5-SV03-CE	3M™ SecureFit™ Short Visor for X5 Series Safety Helmet, X5000 and X5500, Amber Anti-Fog Anti-Scratch Polycarbonate, X5-SV03-CE	10	Each
7100176840	X5-SV01-CE	3M™ SecureFit™ Short Visor for X5 Series Safety Helmet, X5000 and X5500, Clear Anti-Fog Anti-Scratch Polycarbonate, X5-SV01-CE	10	Each
7100176972	X5-SV02-CE	3M™ SecureFit™ Short Visor for X5 Series Safety Helmet, X5000 and X5500, Grey Anti-Fog Anti-Scratch Polycarbonate, X5-SV02-CE	10	Each

3M™ Faceshields 5 Series

3M™ 5-Series Faceshields is a range of polycarbonate, acetate and mesh faceshields, certified to EN 166:2001 and EN 1731:2006, and designed to protect against impact of high speed particles and other industrial or forestry hazards. These faceshields are designed to fit 3M™ SecureFit™ X5000 & X5500 and G3000 Safety Helmets and G500 headgear



- 3M™ 5-series clear polycarbonate and acetate Faceshields certified to EN 166:2001, provide protection against high speed particles, liquid splashes and molten metal splashes
- 3M™ 5-series mesh Faceshields certified to EN 1731:2006, provide protection against flying wood chips and twigs
- 3M™ 5-series clear Faceshields provide protection against UV, IR (heat) and/or intense visible light

Product ID	Part Number	Product Name	MOQ	OU
7100212096	5A-CP	3M™ Faceshield 5 Series, Clear Acetate with Chin Protection, 5A-CP	10	Each
7000103792	5C-1	3M™ Faceshield 5 Series, Mesh, Stainless Steel, Black, 5C	10	Each
7100029680	5F-11	3M™ Faceshield 5 Series, Polycarbonate, Clear, 5F-11	10	Each
7000103788	5E-11	3M™ Faceshield 5 Series, Polycarbonate, Green, Shade 5, 5E-11	10	Each

Head & Face Protection

3M™ Faceshields WP Series

3M™ WP-Series Faceshields is a range of polycarbonate and acetate faceshields, certified to EN 166:2001 and designed to protect against impact of high speed particles and other industrial hazards. These faceshields are designed to fit 3M™ SecureFit™ X5000 & X5500 Safety Helmets and H8 headgear



- 3M™ WP-series polycarbonate and acetate Faceshields certified to EN 166:2001, provide protection against high speed particles, liquid splashes and molten metal splashes
- 3M™ WP-series Faceshields provide protection against UV
- 3M™ WP-series clear Faceshields are optical class 1, curved and flat face polycarbonate or acetate aceshields with protection against high speed particles of medium energy (120 m/s), grade B, or of low energy (45 m/s), grade F

Product ID	Part Number	Product Name	MOQ	OU
7000089416	WP98	3M™ Faceshield WP Series, Acetate, Clear, WP98	10	Each
7100016704	WP96	3M™ Faceshield WP Series, Polycarbonate, Clear, WP96	10	Each

Head & Face Protection

Head Protection Accessories

3M™ Safety Helmet Chinstraps

Product ID	Part Number	Product Name	MOQ	OU
7000108175	GH4	3M™ Safety Helmet Chinstrap for Hard Hat Series G3000, 3-Point, GH4	10	Each
7100148985	GH1	3M™ Safety Helmet Chinstrap for Hard Hat Series G3000, G22, 2-point, GH1	1	Each
7100175589	X5-P4PTCS2	3M™ Safety Helmet Premium 4 Point Chinstrap with magnetic buckle and selector for SecureFit™ Safety Helmet X5000, X5-P4PTCS2	10	Each
7100175587	X5-S4PTCS2	3M™ Safety Helmet Standard 4 Point Chinstrap with buckle and selector for SecureFit™ Safety Helmet X 5000, X5-S4PTCS2	10	Each

3M™ SecureFit™ Safety Helmet Replacement Suspension Straps

Product ID	Part Number	Product Name	MOQ	OU
7100180681	X5-6PTSTRAP	3M™ SecureFit™ Safety Helmet Replacement 6 Point Suspension Strap for Safety Helmet, X5-6PTSTRAP	10	Each

3M™ SecureFit™ Safety Helmet Replacement Suspension Systems

Product ID	Part Number	Product Name	MOQ	OU
7100180682	X5-4PTSUS	3M™ SecureFit™ Safety Helmet Replacement 4 Point Suspension System for Safety Helmet X5500, X5-4PTSUS	10	Each
7100180703	X5-6PTSUS	3M™ SecureFit™ Safety Helmet Replacement 6 Point Suspension System for Safety Helmet X5000, X5-6PTSUS	10	Each

3M™ SecureFit™ X5 Safety Helmet Standard Reflective Sticker Kits X5-REFKIT

Product ID	Part Number	Product Name	MOQ	OU
7100175590	X5-REFKIT	3M™ SecureFit™ X5 Safety Helmet Standard Reflective Sticker Kit, X5-REFKIT	10	Each

3M™ X5 Lampholder

Product ID	Part Number	Product Name	MOQ	OU
7100232855	X5LAMPHLDR	3M™ X5 Lampholder for Industrial Safety Helmets, 10 ea/Case	10	Each

Head & Face Protection

3M™ Splash and Heat Covers

Product ID	Part Number	Product Name	MOQ	OU
7100082483	NC1-GR	3M™ Splash and Heat Elevated Temperature Neck Cover, Cotton/Para Aramide, NC1-GR	1	Each
7100256707	X5-UVSHVYLW	3M™ Splash and Heat UV HV Neck Cover, Yellow, X5-UVSHVYLW	20	Each

3M™ Replacement Sweatbands

Product ID	Part Number	Product Name	MOQ	OU
7000108030	HYG4	3M™ Replacement Sweatband for Hard Hats, Leather, HYG4	10	Each
7000108029	HYG30	3M™ Replacement Sweatband for Hard Hats, Plastic, HYG3	10	Each
7100247316	TCS2	3M™ Replacement Sweatband for Hard Hats, Terry Cloth, Black, TCS2	20	Each
7100241118	X5-SWBD02	3M™ Replacement Sweatband for SecureFit™ Safety Helmet, Black, X5-SWBD02	200	Each
7100180680	X5-SWBD01	3M™ Replacement Sweatband for SecureFit™ Safety Helmet, Black/Grey, X5-BWPD01	10	Each

3M™ Headgear H8 Series

Product ID	Part Number	Product Name	MOQ	OU
7000144936	82501	3M™ Headgear H8 Series, Ratchet Headband, 82501-00000CP	10	Each

3M™ Hard Hat Integrated Safety Glasses

Product ID	Part Number	Product Name	MOQ	OU
7100092588	V9A	3M™ Hard Hat Integrated Safety Glasses, Amber, V9A	20	Each
7100092589	V9C	3M™ Hard Hat Integrated Safety Glasses, Clear, V9C	20	Each
7100092586	V9G	3M™ Hard Hat Integrated Safety Glasses, Grey, V9G	20	Each

3M™ Helmet Side Covers & Guards

Product ID	Part Number	Product Name	MOQ	OU
7100224833	SC1-AL	3M™ Helmet Side Cover, Aluminized, SC1-AL	1	Each
7100229734	FC2AL	3M™ Helmet Side Covers & Guards, Front Cover, FC2-AL	10	Each

■ Head & Face Protection

3M™ Hard Hat & Helmet Visor Adapters

Product ID	Part Number	Product Name	MOQ	OU
7100246136	P3EV2	3M™ P3E Adapter without Muffs, 1 pair	20	Pair





Eye Protection

3M Science.
Applied to Life.™

3M™ SecureFit™ Safety Glasses



**Safety backed
by science.**


Performance. Style. Comfort.

Protecting your vision on the job is important. But it doesn't have to mean sacrificing style or comfort.

Get eyewear that performs — and looks good doing it. Featuring a comfortable fit and a sleek profile designed to work with other personal protective equipment, 3M™ SecureFit™ Safety Glasses helps keep you safe and comfortable on the job.

Learn more at:

3m.co.uk/SecureFit



Contact your 3M sales rep to request trial wear samples of 3M™ SecureFit™ Safety Glasses and feel the difference the instant you put them on. See for yourself.







3M™ SecureFit™ Safety Glasses

Choose your style and fit



Features	100 Series	200 Series	400 Series	400X Series	500 Series	600 Series	3700 Series
3M™ Pressure Diffusion Temple Technology	•	•	•	•	•	•	•
3M™ Scotchgard™ Anti-Fog/ Anti-Scratch Coating		•	•	•	•	•	•
Soft Temple Tips			•	•			
Rugged Anti-Scratch or Anti-Scratch+ (K) Coating				•	•	•	•
Soft Nose Bridge			•	•		•	•
Brow Guard				•			•
Removable Foam Gasket		•	•		•	•	
Dual Lens Design						•	
Readers			•				
Indoor/Outdoor (Mirror) Lens	•		•	•	•	•	
IR lens					•	•	•
Orange Lens			•				
Comfort Filter Light Brown Lens					•		
Sunglare Mirror Lens			•	•	•		
Sunglare Brown Lens			•		•		
Vermillion Lens				•			
Polarised Lens						•	
Protection against UV up to 400nm					•		

Goggle features overview

		GOGGLES						
		4700 Series	4800 Series	GoggleGear™ 500	2890 Series	GoggleGear™ 6000	Fahrenheit™	Solus™ 1000 TPE Kits
								
Protection properties	Impact protection	B	B	BT	BT: 2890, 2890S, 2891, 2891S FT: 2890A, 2890SA BT: 2890S B: 2895S	BT	BT: 71360-00011, 00012, 00014 F: 71360-00013, 00015, 00017	BT
	3 Splash/droplet		●	●	●	●	●	S1201SGAF-TSKT S1101NSGAF-TSKT
	4 Large dust particles			●	●	●	●	S1201SGAF-TSKT S1101NSGAF-TSKT
	5 Gas and fine dust				2890SA, 2895S, 2891S			
	9 Molten metals and hot solids				2891, 2891S		71360-00013, 00015, 00017	
	K Resistance to surface damage by fine particles			●	2890, 2890S, 2895S, 2891, 2891S	●		●
	N Resistance to fogging			●	●	●		●
Design	Over the Glasses (OTG)				●	●	●	
	Elasticated textured strap	●	●	●	●	●	●	●
	Neoprene strap			GG501N SGAF		GG6001N SGAF	71360-00015	S1101NSGAF-TSKT
	Direct ventilation	●						
	Indirect ventilation			●	2890, 2890A, 2891	●	71360-00011; 00012; 00013; 00014	●
	Sealed				2890S, 2890SA, 2895S, 2891S		71360-00015, 00017	
	Approx. weight	66g	66g	50g	86g-99g	82g	128g	44g
Accessory	Prescription insert			●				●
	Replaceable lens				2890A, 2890SA			
Lens colour	Clear UV Filter 2-1.2 Reference end 01	●	●	●	2890, 2890A, 2890S, 2890SA, 2891, 2891S	●	●	●
	Dark Grey Filter 3.1 Reference end 02			●		●		●
	Amber UV Filter 2-1.2 Reference end 03							●
	Indoor/outdoor							●
	Shade 5			●	2895S			
Coatings	Scotchgard™ Anti-Fog (K&N)			●	2891, 2891S	●		●
	Traditional anti-fog (with anti-scratch properties)		4800AF		2890, 2890A, 2890S, 2890SA, 2895S		71360-00011, 00013, 00014, 00015, 00017	
	Traditional anti-scratch						71360-00012	

Eye Protection

Safety Glasses

Focus

3M™ SecureFit™ Safety Glasses 100 Series

3M™ SecureFit™ 100 Series features a sleek, sporty lens shape coupled with a patented temple design that self-adjusts to different head sizes to provide a stylish yet comfortable fit for an extended period of time.



- Economical robust 3M™ SecureFit™ Safety Glasses range
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head
- Slim wrap around design to look better on smaller faces

Product ID	Part Number	Product Name	MOQ	OU
7100244064	SF101AF-BLU	3M™ SecureFit™ 100 Safety Glasses, Blue frame, Anti-Scratch / Anti-Fog, Clear lens, SF101AF-BLU-EU, 20/Case	20	Each
7100244060	SF101AF-BLK	3M™ SecureFit™ 100 Safety Glasses, Black frame, Anti-Scratch / Anti-Fog, Clear lens, SF101AF-BLK-EU, 5-pk 20Pks/Case	100	Each
7100244046	SF101AS-BLK	3M™ SecureFit™ 100 Safety Glasses, Black frame, Anti-Scratch, Clear lens, SF101AS-BLK-EU, 5-pk 20Pks/Case	100	Each
7100243969	SF103AF-BLU	3M™ SecureFit™ 100 Safety Glasses, Blue frame, Anti-Scratch / Anti-Fog, Amber lens, SF103AF-BLU-EU, 20/Case	20	Each
7100244048	SF102AF-BLU	3M™ SecureFit™ 100 Safety Glasses, Blue frame, Anti-Scratch / Anti-Fog, Grey lens, SF102AF-BLU-EU, 20/Case	20	Each
7100244061	SF107AF-BLU	3M™ SecureFit™ 100 Safety Glasses, Blue frame, Anti-Scratch / Anti-Fog, Indoor / Outdoor Light Grey lens, SF107AF-BLU-EU, 20/Case	20	Each
7100244047	SF101AS-BLU	3M™ SecureFit™ 100 Safety Glasses, Blue frame, Anti-Scratch, Clear lens, SF101AS-BLU-EU, 20/Case	20	Each

Focus

3M™ SecureFit™ Safety Glasses 200 Series

3M™ SecureFit™ 200 Series are lightweight safety glasses with 3M™ Pressure Diffusion Temple Technology. Our glasses feature a wraparound design that's secure and comfortable. They are available in various lens tints.



- Economical lightweight (18 gram) 3M™ SecureFit™ Safety Glasses range
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100112010	SF202AF	3M™ SecureFit™ 200 Safety Glasses, Anti-Scratch / Anti-Fog, Grey Lens, SF202AS/AF-EU, 20/Case	20	Each
7100112180	SF201AS	3M™ SecureFit™ 200 Safety Glasses, Anti-Scratch, Clear Lens, SF201AS-EU, 20/Case	20	Each
7100185279	SF201SGAF-BLU	3M™ SecureFit™ 200 Safety Glasses, Blue Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, SF201SGAF-BLU-EU	20	Each

Eye Protection

Focus

3M™ SecureFit™ Safety Glasses 400 Series

3M™ SecureFit™ Safety Glasses 400 Series features a lightweight design with a rimless polycarbonate lens, 3M™ Pressure Diffusion Temple Technology, wide flexible temple arms, and soft, adjustable nose pads.



- Comfortable 3M™ SecureFit™ Safety Glasses range with soft adjustable nose and soft temple ends to improve comfort and fit
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head.
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100148082	SF405SGAF-BLA	3M™ SecureFit™ 400 Safety Glasses, Black/Brown Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Brown Lens, SF405SGAF-BLA-EU	20	Each
7100148075	SF406SGAF-BLA	3M™ SecureFit™ 400 Safety Glasses, Black/Brown Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Orange Lens, SF406SGAF-BLA-EU	20	Each
7100078986	SF403AF	3M™ SecureFit™ 400 Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, Amber Lens, SF403AS/AF-EU, 20/Case	20	Each
7100078989	SF401AF	3M™ SecureFit™ 400 Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, Clear Lens, SF401AS/AF-EU, 20/Case	20	Each
7100078987	SF402AF	3M™ SecureFit™ 400 Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, Grey Lens, SF402AS/AF-EU, 20/Case	20	Each
7100078880	SF408AS	3M™ SecureFit™ 400 Safety Glasses, Black/Green frame, Anti-Scratch, Blue Mirror Lens, SF408AS-EU, 20/Case	20	Each
7100078988	SF410AS	3M™ SecureFit™ 400 Safety Glasses, Black/Green frame, Anti-Scratch, Indoor/Outdoor Mirror Lens, SF410AS-EU, 20/Case	20	Each
7100148074	SF401SGAF-BLU	3M™ SecureFit™ 400 Safety Glasses, Blue/Grey Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, SF401SGAF-BLU-EU	20	Each
7100148052	SF402SGAF-BLU	3M™ SecureFit™ 400 Safety Glasses, Blue/Grey Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens, SF402SGAF-BLU-EU	20	Each
7100148072	SF407SGAF-BLU	3M™ SecureFit™ 400 Safety Glasses, Blue/Grey Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Indoor/Outdoor Grey Lens, SF407SGAF-BLU-EU	20	Each
7100148073	SF401SGAF-BLU-F	3M™ SecureFit™ 400 Safety Glasses, Blue/Grey Frame, Foam, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, SF401SGAF-BLU-F-EU	20	Each
7100148026	SF401SGAF-RED	3M™ SecureFit™ 400 Safety Glasses, Red/Grey Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, SF401SGAF-RED-EU	20	Each
7100148081	SF403SGAF-YEL	3M™ SecureFit™ 400 Safety Glasses, Yellow/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens, SF403SGAF-YEL-EU	20	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Eye Protection

3M™ SecureFit Safety Glasses 400X Series

3M™ SecureFit™ Safety Glasses 400X Series features a lightweight design with a rimless polycarbonate lens, 3M™ Pressure Diffusion Temple Technology, wide flexible temple arms, a soft nose bridge and a brow guard for additional protection from flying particles.



- Comfortable 3M™ SecureFit™ Safety Glasses range with soft temple ends, brow guard and integrated nose bridge for additional top coverage and comfortable fit
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head.
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100185269	SF401XSGAF-BLU	3M™ SecureFit™ 400 Series Safety Glasses SF401XSGAF-BLU, Blue/Gray, Clear Scotchgard™ Anti-Fog/Anti-Scratch Lens	20	Each
7100185268	SF401XSGAF-GRN	3M™ SecureFit™ 400 Series Safety Glasses SF401XSGAF-GRN, Hi-Vis GRN/Clear, Clear Scotchgard™ Anti-Fog/Anti-Scratch Lens	20	Each
7100185278	SF402XSGAF-BLU	3M™ SecureFit™ 400 Series Safety Glasses SF402XSGAF-BLU, Blue/Gray, Gray Scotchgard™ Anti-Fog/Anti-Scratch Lens	20	Each
7100185291	SF403XSGAF-YEL	3M™ SecureFit™ 400 Series Safety Glasses SF403XSGAF-YEL, Yellow/Black, Amber Scotchgard™ Anti-Fog/Anti-Scratch Lens	20	Each
7100185289	SF407XSGAF-BLU	3M™ SecureFit™ 400 Series Safety Glasses SF407XSGAF-BLU, BLU/GRY, I/O GRY Scotchgard™ Anti-Fog/Anti-Scratch Lens	20	Each
7100185292	SF416XAS-BLK	3M™ SecureFit™ 400X Safety Glasses, Black/Black frame, Anti-Scratch, Orange Mirror Lens, SF416XAS-BLK-EU, 20/Case	20	Each
7100185109	SF422XSGAF-BLK	3M™ SecureFit™ 400X Safety Glasses, Black/Black frame, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Vermillion Lens, SF422XSGAF-BLK-EU	20	Each

3M™ SecureFit™ 400 Series Readers Safety Glasses

3M™ SecureFit™ Safety Readers 400 Series features a lightweight design with a rimless polycarbonate lens, 3M™ Pressure Diffusion Temple Technology, wide flexible temple arms, soft, adjustable nose pads and an additional reader part.



- Safety glasses with an additional reading dioptr part at the bottom of the lens for magnifying small details
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head
- Wraparound design gives the user a wide field of vision

Product ID	Part Number	Product Name	MOQ	OU
7100114612	SF415AF	3M™ SecureFit™ 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, clear +1.5 Lens, SF415AS/AF-EU, 20/Case	20	Each
7100114948	SF420AF	3M™ SecureFit™ 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, clear +2.0 Lens, SF420AS/AF-EU, 20/Case	20	Each
7100114613	SF425AF	3M™ SecureFit™ 400 Reader Safety Glasses, Black/Green frame, Anti-Scratch / Anti-Fog, clear +2.5 Lens, SF425AS/AF-EU, 20/Case	20	Each

Eye Protection

Focus

3M™ SecureFit™ Safety Glasses 500 Series

3M™ SecureFit™ Safety Glasses 500 Series features a stylized lens shape with temples that automatically self-adjust to help provide a secure and comfortable fit.



- Sleek and compatible 3M™ SecureFit™ Safety Glasses range with adjustable ratchet temples to adjust the lens for facial features and eyeglass position, designed to help improve the positioning when worn with respirators
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100244045	SF501AF-BLK	3M™ SecureFit™ 500 Safety Glasses, Black frame, Anti-Scratch / Anti-Fog, Clear lens, SF501AF-BLK-EU, 20/Case	20	Each
7100243963	SF509AF-BLK	3M™ SecureFit™ 500 Safety Glasses, Black frame, Anti-Scratch / Anti-Fog, Silver Mirror lens, SF509AF-BLK- 20/Case	20	Each
7100243979	SF501ASP-BLK	3M™ SecureFit™ 500 Safety Glasses, Black frame, Anti-Scratch+ (K), Clear lens, SF501ASP-BLK-EU, 20/Case	20	Each
7100243978	SF550ASP-GRN	3M™ SecureFit™ 500 Safety Glasses, Green/Black frame, Anti-Scratch + (K), IR 5.0 Grey lens, SF550ASP-GRN-EU, 20/Case	20	Each
7100243977	SF517ASP-GRN	3M™ SecureFit™ 500 Safety Glasses, Green/Black frame, Anti-Scratch+ (K), IR 1.7 Grey lens, SF517ASP-GRN-EU, 20/Case	20	Each
7100243989	SF530ASP-GRN	3M™ SecureFit™ 500 Safety Glasses, Green/Black frame, Anti-Scratch+ (K), IR 3.0 Grey lens, SF530ASP-GRN-EU, 20/Case	20	Each
7100244201	SF502SGAF-BLK	3M™ SecureFit™ 500 Series, Black, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Grey AF-AS Lens, SF502SGAF-BLK	20	Each
7100244022	SF505SGAF-DGR	3M™ SecureFit™ 500 Series, Dark Green, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N),Brown Lens, SF505SGAF-DGR	20	Each
7100243934	SF501SGAF-RED	3M™ SecureFit™ 500 Series, Red, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear AF-AS Lens, SF501SGAF-RED	20	Each
7100243142	SF501SGAF-BLK	3M™ SecureFit™ 500 Series,Black, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear AF-AS Lens, SF501SGAF-BLK	20	Each
7100243964	SF501SGAF-BLK-FM	3M™ SecureFit™ 500, Black, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, Foam, SF501SGAF-BLK-FM	20	Each
7100243995	SF507SGAF-BLK	3M™ SecureFit™ 500, Black, Scotchgard™ Anti-Fog/Anti-Scratch Coating(K&N),IO Grey AF-AS Lens, SF507SGAF-BLK	20	Each
7100244062	SF528SGAF-DGR	3M™ SecureFit™ 500, Dark Green, Scotchgard Anti-Fog/Anti-Scratch Coating (K&N), Lt Brown AF-AS Lens, SF528SGAF-DGR	20	Each
7100243971	SF501SGAF-GRN	3M™ SecureFit™ 500, Green, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear AF-AS Lens, SF501SGAF-GRN	20	Each
7100243980	SF503SGAF-BLK	3M™ SecureFit™ 500, Series, Black, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Amber AF-AS Lens, SF503SGAF-BLK	20	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Eye Protection

Focus

3M™ SecureFit™ Safety Glasses 600 Series

3M™ SecureFit™ Safety Glasses 600 Series are semi-rimless glasses with 3M™ Pressure Diffusion Temple Technology and fixed-length temple arms over the ears.



- Robust semi-rimless 3M™ SecureFit™ Safety Glasses range with dual-lenses providing optimal optical performance
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100112713	SF611AS	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Grey Polarised Lens, SF611AS-EU, 20/Case	20	Each
7100112718	SF610AS	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Indoor/Outdoor Mirror Lens, SF610AS-EU, 20/Case	20	Each
7100112721	SF617AS	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 1,7 Lens, SF617AS-EU, 20/Case	20	Each
7100112724	SF630AS	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 3.0 Lens, SF630AS-EU, 20/Case	20	Each
7100112715	SF650AS	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Anti-Scratch, Welding Shade 5.0 Lens, SF650AS-EU, 20/Case	20	Each
7100112716	SF602SGAF	3M™ SecureFit™ 600 Safety Glasses, Grey frame, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Grey Lens, SF602SGAF-EU, 20/Case	20	Each
7100134761	SF601SGAF/FI	3M™ SecureFit™ Safety Glasses, Grey Frame, Foam, Scotchgard™ Anti-Fog, Clear Lens, SF601SGAF/FI-EU	1	Each
7100112712	SF603SGAF	3M™ SecureFit™ Safety Glasses, Grey frame, Scotchgard™ Anti-Fog, Amber Lens, SF603SGAF-EU	20	Each
7100112717	SF601SGAF	3M™ SecureFit™ Safety Glasses, Grey frame, Scotchgard™ Anti-Fog, Clear Lens, SF601SGAF-EU	20	Each

Eye Protection

Focus

3M™ Solus™ Safety Glasses 1000 Series

3M™ Solus™ Safety Glasses 1000 Series feature a strong polycarbonate lens in a slim, stylish frame. Our safety glasses have 3M™ Scotchgard™ Anti-Fog / Anti-Scratch Coating, and can be configured in different ways because of the headband and gasket options. They are available in various lens tints.



- Sporty, low profile 3M™ Solus™ Safety Glasses range which can be easily swapped with headband and/or gaskets to suit the application
- Soft nose and soft temple ends to improve comfort, fit and style
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties

Product ID	Part Number	Product Name	MOQ	OU
7100078883	S1202S	3M™ Solus™ 1000 Safety Glasses Green/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens, S1202SGAF-EU	20	Each
7100243970	S1101NSGAF-TSKT	3M™ Solus™ 1000 Safety Glasses, Blue / Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear lens, TPE Gasket and Neoprene Strap, S1101NSGAF-TSKT-EU	20	Each
7100080184	S1101SKT	3M™ Solus™ 1000 Safety Glasses, Blue/Black Frame, Scotchgard™ Anti-Fog /Anti-Scratch Coating (K&N), Clear Lens, Foam Gasket and Strap, S1101SGAFKT-EU	20	Each
7100080187	S1103S	3M™ Solus™ 1000 Safety Glasses, Blue/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Amber Lens, S1103SGAF-EU	1	Each
7100080258	S1101S	3M™ Solus™ 1000 Safety Glasses, Blue/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, S1101SGAF-EU	20	Each
7100244049	S1107SGAF	3M™ Solus™ 1000 Safety Glasses, Blue/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Indoor/Outdoor Light Grey lens, S1107SGAF-EU	20	Each
7100080185	S1102S	3M™ Solus™ 1000 Safety Glasses, Blue/Black frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens, S1102SGAF-EU	20	Each
7100244066	S1201SGAF-TSKT	3M™ Solus™ 1000 Safety Glasses, Green / Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear lens, TPE Gasket and Strap, S1201SGAF-TSKT-EU	20	Each
7100080186	S1203S	3M™ Solus™ 1000 Safety Glasses, Green/Black Frame, Scotchgard™ Anti-Fog Anti-Scratch Coating (K&N), Amber Lens, S1203SGAF-EU	20	Each
7100078881	S1201SKT	3M™ Solus™ 1000 Safety Glasses, Green/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, Foam Gasket and Strap, S1201SGAFKT-EU	20	Each
7100078882	S1201S	3M™ Solus™ 1000 Safety Glasses, Green/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, S1201SGAF-EU	20	Each
7100244063	S1207SGAF	3M™ Solus™ 1000 Safety Glasses, Green/Black Frame, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Indoor /Outdoor Light Grey lens, S1207SGAF-EU	20	Each

Eye Protection

3M™ Solus™ Safety Glasses 2000 Series

3M™ Solus™ Safety Glasses 2000 Series are our stylish safety glasses which feature temple arms with an adjustable ratchet for a customised fit. The polycarbonate lens is available with anti-scratch and anti-fog coatings for increased durability and improved vision. Available in a range of temple arm colours and lens options.



- Stylish, low profile half frame 3M™ Solus™ Safety Glasses Range with adjustable ratchet temples to adjust the lens for facial features and eyeglass position
- Semi-soft nose and soft temple ends to improve comfort and fit
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)

Product ID	Part Number	Product Name	MOQ	OU
7100218150	S2017ASPBLK	3M™ Solus™ 2000 Safety Glasses, Black/Green frame, Anti-Scratch + (K), IR 1.7 Grey Lens, S2017ASP-BLK, 20/Case	20	Each
7100218153	S2030ASPBLK	3M™ Solus™ 2000 Safety Glasses, Black/Green frame, Anti-Scratch + (K), IR 3.0 Grey Lens, S2030ASP-BLK, 20/Case	20	Each
7100220423	S2050ASPBLK	3M™ Solus™ 2000 Safety Glasses, Black/Green frame, Anti-Scratch + (K), IR 5.0 Grey Lens, S2050ASP-BLK, 20/Case	20	Each
7100208382	S2001AF-BLU	3M™ Solus™ 2000 Series, S2001AF-BLU, Blue/Grey Temples, Clear Anti-Fog/Anti-Scratch lens, 20/Case	20	Each
7100208825	S2001ASP-BLU	3M™ Solus™ 2000 Series, S2001ASP-BLU, Blue/Grey Temples, Clear Anti-Scratch+ lens, 20/Case	20	Each
7100208751	S2001SGAF-BGR	3M™ Solus™ 2000 Series, S2001SGAF-BGR, Grey/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS lens, 20/Case	20	Each
7100208817	S2001SGAF-RED	3M™ Solus™ 2000 Series, S2001SGAF-RED, Grey/Red Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS lens, 20/Case	20	Each
7100208793	S2002SGAF-BGR	3M™ Solus™ 2000 Series, S2002SGAF-BGR, Grey/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Grey AF-AS lens, 20/Case	20	Each
7100209600	S2002SGAF-RED	3M™ Solus™ 2000 Series, S2002SGAF-RED, Grey/Red Temples, Scotchgard™ Anti-Fog Coating, Grey AF-AS lens, 20/Case	20	Each
7100208818	S2003SGAF-BGR	3M™ Solus™ 2000 Series, S2003SGAF-BGR, Grey/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Amber AF-AS lens, 20/Case	20	Each
7100208819	S2005SGAF-BGR	3M™ Solus™ 2000 Series, S2005SGAF-BGR, Grey/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Brown AF-AS lens, 20/Case	20	Each
7100208815	S2007SGAF-BGR	3M™ Solus™ 2000 Series, S2007SGAF-BGR, Grey/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, I/O Grey AF-AS lens, 20/Case	20	Each
7100208826	S2024AS-RED	3M™ Solus™ 2000 Series, S2024AS-RED, Grey/Red Temples, Red Mirror Anti-Scratch lens, 20/Case	20	Each
7100208820	S2001SGAF-BGR-F	3M™ Solus™ 2000 Series, Grey/Blue-Green Temple, Scotchgard™ Anti-Fog Coating, Clr AF-AS Lens, S2001SGAF-BGR-F EU	20	Each

Eye Protection

3M™ Solus™ 2000 Series Readers Safety Glasses

3M™ Solus™ Safety Reader Glasses 2000 Series are our stylish safety glasses which feature temple arms with an adjustable ratchet for a customised fit and different reader options.

- Stylish, low profile half frame 3M™ Solus™ Safety Readers Range with adjustable ratchet temples to adjust the lens for facial features and eyeglass position
- Available in a range of diopters: +1.5, +2.0 or +2.5
- Semi-soft nose and soft temple ends to improve comfort and fit



Product ID	Part Number	Product Name	MOQ	OU
7100218306	S2015AFBLU	3M™ Solus™ 2000 Safety Glasses, Blue/Grey Temples, Anti-Fog/Anti-Scratch, Reader +1.5 Clear Lens, S2015AF-BLU, 20/Case	20	Each
7100218163	S2020AFBLU	3M™ Solus™ 2000 Safety Glasses, Blue/Grey Temples, Anti-Fog/Anti-Scratch, Reader +2.0 Clear Lens, S2020AF-BLU, 20/Case	20	Each
7100218151	S2025AFBLU	3M™ Solus™ 2000 Safety Glasses, Blue/Grey Temples, Anti-Fog/Anti-Scratch, Reader +2.5 Clear Lens, S2025AF-BLU, 20/Case	20	Each

3M™ Solus™ CCS Safety Glasses

3M™ Solus™ CCS Safety Glasses are our rimless safety glasses that feature lime green temples with a Corded Control System (CCS) for attaching corded earplugs. The polycarbonate lens features a Scotchgard™ Anti-Fog and Anti-Scratch Coating on both sides for increased durability and improved vision. Available in a range of lens options.

- Modern 3M™ Solus™ Safety Glasses Range with Cord Control System (CCS) keeping the eyewear and corded earplugs attached and ready to use
- Designed for workers who put on and take off eyewear frequently throughout the day
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties (available on selected models)



Product ID	Part Number	Product Name	MOQ	OU
7000043086	7151100	3M™ CCS Safety Glasses, Anti-Scratch / Anti-Fog, Clear Lens, 71511-00000, 20/Case	1	Each
7100216261	SCCS01SGAFGRNF	3M™ Solus™ CCS Safety Glasses, Lime Green Temples, Foam Gasket, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, SCCS01SGAF-GRN-F-EU	20	Each
7100216507	SCCS01SGAFGRN	3M™ Solus™ CCS Safety Glasses, Lime Green Temples, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Clear Lens, SCCS01SGAF-GRN-EU	20	Each
7100216621	SCCS02SGAFGRN	3M™ Solus™ CCS Safety Glasses, Lime Green Temples, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Grey Lens, SCCS02SGAF-GRN-EU	20	Each
7100216595	SCCS07SGAFGRN	3M™ Solus™ CCS Safety Glasses, Lime Green Temples, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), I/O Grey Lens, SCCS07SGAF-GRN-EU	20	Each

Eye Protection

3M™ Virtua™ Safety Glasses

3M™ Virtua™ Safety Glasses are our rimless safety glasses with a wraparound design for full coverage and contoured flexible temples to ensure comfort. The integrated side-shields provide added protection from flying objects and the lens features an anti-scratch coating for increased durability. They are available in four lens options.



- Economical basic unisex safety glasses for single use protection
- Wraparound design improves the security of fit and prevents slipping
- Design provides maximum clarity, excellent coverage and a wide field of vision

Product ID	Part Number	Product Name	MOQ	OU
7100244069	715001AF	3M™ Virtua™ Safety Glasses, Anti-Scratch / Anti-Fog, Clear lens, 715001AF-EU, 20/Case	20	Each
7100243988	715003AF	3M™ Virtua™ Safety Glasses, Anti-Scratch / Anti-Fog, Amber lens, 715003AF-EU, 20/Case	20	Each
7100244065	715001AF-BULK	3M™ Virtua™ Safety Glasses, Anti-Scratch / Anti-Fog, Clear lens, 715001AF-EU, 5-pk 20Pks/Case	100	Each
7100244050	715002AF	3M™ Virtua™ Safety Glasses, Anti-Scratch / Anti-Fog, Grey lens, 715002AF-EU, 20/Case	20	Each

3M™ Virtua™ AP Safety Glasses

3M™ Virtua™ AP Safety Glasses are our wraparound, unisex styled safety glasses with strong, polycarbonate lenses, and an integral side shield and anti-scratch coating.



- Economical robust sturdy safety glasses
- Integrated brow guard for additional top coverage
- Easy to clean

Product ID	Part Number	Product Name	MOQ	OU
7100006209	7151200	3M™ Virtua™ AP Safety Glasses, Anti-Scratch, Clear Lens, 71512-00000, 20/Case	20	Each
7100010682	7151201	3M™ Virtua™ AP Safety Glasses, Anti-Scratch, Grey Lens, 71512-00001, 20/Case	20	Each

3M™ LED Light Vision™ Safety Glasses

3M™ LED Light Vision™ Safety Glasses are our durable safety glasses with integrated LED lights for lighting a dark zone while keeping your hands free for working.



- Safety glasses with LED Lights for safe and hands free working
- Illuminate dark areas while protecting your eyes
- Long battery life (over 50 hours)

Product ID	Part Number	Product Name	MOQ	OU
7000032466	11356000	3M™ LED Light Vision™ Safety Glasses, Anti-Scratch / Anti-Fog, Clear Lens, 11356-00000, 20/Case	20	Each

Eye Protection

Focus

3M™ SecureFit™ Overspectacles 3700 Series

3M™ SecureFit™ Overspectacles 3700 Series are our safety overspectacles designed for people with prescription glasses. They feature adjustable ratchet temples with Pressure Diffusion Temple (PDT) technology to ensure a close fit and a soft touch nose piece to help provide comfort. The polycarbonate lens is available with 3M™ Scotchgard™ Anti-Fog and anti-scratch coatings for increased durability and improved vision. Available in a range of frame and lens colours.



- Over The Glass (OTG) 3M™ SecureFit™ range designed to offer all-day wearability for workers wearing prescription glasses
- 3M's innovative SecureFit™ Pressure Diffusion Temple technology design features slotted ribs that provide comfortable pressure equalization. The temples flex and self-adjust to the size of wearer's head.
- Adjustable ratchet temples to adjust the lens for facial features and eyeglass position

Product ID	Part Number	Product Name	MOQ	OU
7100217946	SF3717ASPBLK	3M™ SecureFit™ 3700 Overspectacles, Black Temples, Anti-Scratch, IR 1.7 Grey Lens, SF3717AS-BLK, 20/Case	20	Each
7100218079	SF3750ASP-BLK	3M™ SecureFit™ 3700 Overspectacles, Black Temples, Anti-Scratch, IR 5.0 Grey Lens, SF3750AS-BLK, 20/Case	20	Each
7100209340	SF3701ASP-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Anti-Scratch+ (K), Clear Lens, SF3701ASP-BLU-EU, 20/Case	20	Each
7100209425	SF3701XSGAF-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Brow Guard, Scotchgard™ Anti-Fog (K&N), Clear Lens, SF3701XSGAF-BLU-EU, 20/Case	20	Each
7100209416	SF3702XSGAF-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Brow Guard, Scotchgard™ Anti-Fog (K&N), Grey Lens, SF3702XSGAF-BLU-EU, 20/Case	20	Each
7100209427	SF3707SGAF-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Scotchgard™ Anti-Fog (K&N), Indoor/Outdoor Light Grey Lens, SF3707SGAF-BLU-EU	20	Each
7100209252	SF3701SGAF-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Scotchgard™ Anti-Fog (K&N), Clear Lens, SF3701SGAF-BLU-EU, 20/Case	20	Each
7100209384	SF3702SGAF-BLU-EU	3M™ SecureFit™ 3700 Overspectacles, Blue Temples, Scotchgard™ Anti-Fog (K&N), Grey Lens, SF3702SGAF-BLU-EU, 20/Case	20	Each
7100209426	SF3703SGAF-GRN-EU	3M™ SecureFit™ 3700 Overspectacles, Lime Green Temples, Scotchgard™ Anti-Fog (K&N), Amber Lens, SF3703SGAF-GRN-EU, 20/Case	20	Each
7100209413	SF3701SGAF-GRN-EU	3M™ SecureFit™ 3700 Overspectacles, Lime Green Temples, Scotchgard™ Anti-Fog (K&N), Clear Lens, SF3701SGAF-GRN-EU, 20/Case	20	Each
7100209430	SF3701SGAF-ORG-EU	3M™ SecureFit™ 3700 Overspectacles, Orange Temples, Scotchgard™ Anti-Fog (K&N), Clear Lens, SF3701SGAF-ORG-EU, 20/Case	20	Each
7100209428	SF3707XSGAF-BLU-EU	3M™ SecureFit™ 3700 Series, Blue Temple Brow, Scotchgard™ Anti-Fog Coating, I/O Grey SGAF Lens, SF3707XSGAF-BLU EU	20	Each

3M™ Safety Overspectacles 2800 Series

3M™ Safety Overspectacles 2800 Series are our over-eyewear safety spectacles featuring inclinable lenses and four low-profile temple lengths. Our strong polycarbonate lens comes with an anti-scratch coating.



- Over The Glass (OTG) range designed to fit over most prescription glasses
- Excellent coverage and field of vision, combined with a high level of protection against impacts
- Adjustable ratchet temples to adjust the lens for facial features and eyeglass position

Product ID	Part Number	Product Name	MOQ	OU
7000032493	2800	3M™ Safety Overspectacles 2800 Series, Anti-Scratch, Clear Lens, 20/Case	20	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Eye Protection

3M™ Visitor Safety Overspectacles

3M™ Visitor Overspectacles are our safety spectacles that fit comfortably over prescription glasses or can be worn on their own. They feature clear, lightweight polycarbonate lenses, moulded side shields, and brow guards.



- Economical basic Over The Glass (OTG) range
- Fits over some small prescription glasses
- Popular to use as a visitor spectacle for short use

Product ID	Part Number	Product Name	MOQ	OU
7000062913	71448	3M™ Visitor Safety Overspectacles, Clear Lens, 71448-00001, 20/Case	20	Each

Safety Goggles

Focus

3M™ GoggleGear™ Safety Goggles 6000 Series

3M™ GoggleGear™ Safety Goggles 6000 Series features a large profile with indirect ventilation for air circulation with Scotchgard™ Anti-Fog and Anti-Scratch Coating.



- Large profile 3M™ GoggleGear™ Safety Goggles range, with enough space to fit over most prescription glasses and indirect airflow to help against fogging
- Premium spherical curved lens design for optimal horizontal and vertical field of vision
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties

Product ID	Part Number	Product Name	MOQ	OU
7100243987	GG6050AS-CLENS	3M™ GoggleGear™ 6000 Anti-Scratch Replacement Flip-Up Grey IR5 Cover lens, GG6050AS-CLENS-EU, 20/Case	20	Each
7100216582	GG6001SGAFBLK	3M™ GoggleGear™ 6000 Safety Goggles, Black Shroud, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, GG6001SGAF-BLK-EU	10	Each
7100216514	GG6002SGAFBLK	3M™ GoggleGear™ 6000 Safety Goggles, Black Shroud, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Grey Lens, GG6002SGAF-BLK-EU	10	Each
7100216191	GG6001NSGAFBLU	3M™ GoggleGear™ 6000 Safety Goggles, Blue Shroud, Neoprene Strap, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, GG6001NSGAF-BLU-EU	10	Each
7100216617	GG6001SGAFGRN	3M™ GoggleGear™ 6000 Safety Goggles, Lime Green Shroud, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, GG6001SGAF-GRN-EU	10	Each
7100216192	GG6001SGAFRED	3M™ GoggleGear™ 6000 Safety Goggles, Red Shroud, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, GG6001SGAF-RED-EU	10	Each
7100244200	GG6001SGAF-IR5	3M™ GoggleGear™ 6000 Safety Goggles, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N) Clear Lens, with Flip-Up Grey IR5 Cover Lens, GG6001SGAF-IR5	10	Each

Eye Protection

Focus

3M™ GoggleGear™ Safety Goggles 500 Series

3M™ Goggle Gear™ Safety Goggles 500 Series provides superior anti-fog protection in a modern slim-line and lightweight design.



- Small profile 3M™ GoggleGear™ Safety Goggles range with a lightweight design for all-day comfort and indirect airflow to help against fogging
- Premium spherical curved lens design for optimal horizontal and vertical field of vision
- 3M™ Scotchgard™ Anti-Fog Coating provides superior anti-fog and anti-scratch properties

Product ID	Part Number	Product Name	MOQ	OU
7100185183	GG501NSGAF-BLU	3M™ Goggle Gear™ 500 Safety Goggles, Neoprene Headband, Scotchgard™ Anti-Fog/Anti-Scratch Coating (K&N), Clear Lens, GG501NSGAF-EU	10	Each
7100074368	GG501S	3M™ Goggle Gear™ 500 Safety Goggles, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), GG501SGAF-EU, 10/Case	10	Each
7100185290	GG502SGAF	3M™ Goggle Gear™ 500 Safety Goggles, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Grey Lens, GG502SGAF-EU, 10/Case	10	Each

Focus

3M™ GoggleGear™ Safety Goggles 2890 Series

3M™ GoggleGear™ Safety Goggles 2890 Series are high-wrap safety goggles available with a superior anti-scratch and anti-fog coatings for increased durability and vision. Our goggles feature a modern, slim design and a wide, elastic strap for easy adjustability.



- Large profile 3M™ GoggleGear™ Safety Goggles range, with enough space to fit over most prescription glasses
- Polycarbonate lens options available for impact resistance and acetate lens options available for improved chemical resistance
- Indirect ventilation versions available to protect against liquid droplets and large dust particles and sealed ventilation versions available to protect against small dust particles and gas protection

Product ID	Part Number	Product Name	MOQ	OU
7000032480	2890	3M™ Safety Goggles 2890 Series, Indirect Vented, Anti-Scratch / Anti-Fog, Clear Polycarbonate Lens, 2890, 10/Case	10	Each
7100146292	2891-SGAF	3M™ Safety Goggles 2890 Series, Indirect Vented, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Clear Lens, 2891-SGAF, 10/Case	10	Each
7000032483	2890SAS	3M™ Safety Goggles 2890 Series, Sealed, Anti-Fog, Clear Acetate Lens, 2890SA, 10/Case	10	Each
7000061924	2890S	3M™ Safety Goggles 2890 Series, Sealed, Anti-Scratch / Anti-Fog, Clear Polycarbonate Lens, 2890S, 10/Case	10	Each
7100010431	2895S	3M™ Safety Goggles 2890 Series, Sealed, Anti-Scratch / Anti-Fog, Welding Shade 5.0, 2895S, 10/Case	10	Each
7100146291	2891S-SGAF	3M™ Safety Goggles 2890 Series, Sealed, Scotchgard™ Anti-Fog / Anti-Scratch Coating (K&N), Clear Lens, 2891S-SGAF, 10/Case	10	Each

Eye Protection

3M™ Fahrenheit™ Safety Goggles

3M™ Fahrenheit™ Safety Goggles are our safety goggles with a soft crystal frame and a wide support area around the face. They are designed with a specific channel on the side of the frame to accommodate the temple arms of prescription glasses.



- Economical large profile safety goggle range, with enough space to fit over most prescription glasses
- Polycarbonate lens options available for impact resistance and acetate lens options available for improved chemical resistance
- Indirect ventilation versions available to protect against liquid droplets and large dust particles and sealed ventilation versions available to protect against small dust particles and gas protection

Product ID	Part Number	Product Name	MOQ	OU
7000062781	7136011	3M™ Fahrenheit™ Safety Goggles, Indirect Vented, Anti-Scratch / Anti-Fog, Clear Polycarbonate Lens, 71360-00011, 10/Case	10	Each
7100010410	7136005	3M™ Fahrenheit™ Safety Goggles, Sealed, Neoprene Headband, Anti-Fog, Clear Acetate Lens, 71360-00015, 10/Case	10	Each

3M™ Safety Goggles 4800 Series

3M™ Safety Goggles 4800 Series are our safety goggles which feature a clear, strong polycarbonate lens for impact resistance and indirect ventilation for added comfort. They are available with an anti-fog lens coating.



- Basic economical safety goggle range with a flat lens design
- Indirect ventilation to protect against liquid droplets
- Polycarbonate lens for impact resistance

Product ID	Part Number	Product Name	MOQ	OU
7000062914	7134701	3M™ Safety Goggles 4800 Series, Indirect Vented, Clear Polycarbonate Lens, 71347-00011, 200/Case	1	Each

Eye Protection

Protective Eyewear Accessories

3M™ Safety Glasses Carrying Case

Product ID	Part Number	Product Name	MOQ	OU
7000032498	266780	3M™ Safety Glasses Microfibre Pouch, 26-6780-00M, 10/Case	10	Each

3M™ Lens Cleaning Tissue Dispensers

Product ID	Part Number	Product Name	MOQ	OU
7100014390	262000	3M™ Disposable Lens Cleaning Tissue Dispenser, 26-2000-00, 500/Disp	1	Pack

3M™ Lens Cleaning Solutions

Product ID	Part Number	Product Name	MOQ	OU
7000062428	LENSCS	3M™ Lens Cleaning Solution, 120ml, 71329-00000A, 12/Case	12	Each

3M™ Disposable Lens Cleaning Tissue Station

Product ID	Part Number	Product Name	MOQ	OU
7000062429	83735	3M™ Disposable Lens Cleaning Station, 83735-00000A, 6/Case	6	Each

3M™ Foam and TPE Gaskets

Product ID	Part Number	Product Name	MOQ	OU
7100102568	SF400FI	3M™ SecureFit™ 400 Foam Insert, SF400FI-EU, 100/Case	100	Each
7100243943	SF500-FOAM	3M™ SecureFit™ 500 Foam Insert, SF500-FOAM-EU, 5-pk 20Pks/Case	100	Each
7100112725	SF600FI	3M™ SecureFit™ 600 Foam Insert, SF600FI-EU, 100/Case	100	Each
7100081293	S1000G	3M™ Solus™ 1000 Foam Insert, 1000G-EU, 100/Case	100	Each
7100243935	S1000-TPE	3M™ Solus™ 1000 TPE Gasket, S1000-TPE-EU, 20/Case	20	Each
7100244145	S2000-FOAM	3M™ Solus™ 2000 Foam Gasket, S2000-FOAM -EU, 5-pk 20Pks/Case	100	Each

■ Eye Protection

3M™ Prescription Lens Inserts

Product ID	Part Number	Product Name	MOQ	OU
7010528331	RXSF400	3M™ SecureFit™ Prescription Insert for SecureFit™ 200, 400 Series, RX-SF400, 10/Case	10	Each
7100243141	S1000-RX	3M™ Solus™ 1000 Prescription Insert with TPE Gasket, S1000-RX-EU, 20/Case	20	Each

3M™ Safety Glasses Strap

Product ID	Part Number	Product Name	MOQ	OU
7000095022	272S	3M™ Safety Glasses Neck Cord with Safety Break, 272, 50/Case	100	Each
7000061868	90943	3M™ Safety Glasses Neck Cord, 90943, 50 ea/Bag	50	Pack
7000032501	90931-00000	3M™ Safety Glasses Strap, Nylon Elastic, Black, Adjustable, 90931-00000	50	Each
7100081292	S1000S	3M™ Solus™ 1000 Safety Glasses Headband, Adjustable Nylon, 1000S-EU, 5/Case	5	Each





Welding Safety

Selector table

● Best¹⁾ ● Better¹⁾ ● Good¹⁾ ✗ Not Recommended¹⁾

Specification	G5-01TW	G5-01VC	G5-02	9100XXi	9100XX	9100X	9100V	9002NC	100V	100B	
MMAW (electrode)	●	●	●	●	●	●	●	●	●	●	
MIG/MAG	●	●	●	●	●	●	●	●	●	●	
TIG (>20A)	●	●	●	●	●	●	●	●	●	✗	
TIG (1A-20A)	●	●	●	●	●	●	●	●	✗	✗	
Plasma (welding and cutting)	●	●	● ³⁾	●	●	●	●	●	✗	✗	
Risk for hidden arc	●	●	●	●	●	●	●	●	✗	✗	
Tack welding	●	●	●	●	●	●	●	●	●	✗	
Grinding	● ⁴⁾	● ⁴⁾	✗	●	●	●	●	●	●	●	
3M™ Speedglas™ Natural Colour Technology	Yes				No			Yes	No		
Switching time, dark-light	50-1 300 ms		50-1000 ms	40-800 ms	40-1 300 ms			60-400 ms	40-250 ms	150-250 ms	
Switching time, light -dark	0,1 ms (+23° C)										
Dark state	Shade 8-13	Shade 8-14	Shade 8-12	Shade 5, 8, 9-13			Shade 8-12		Shade 10-12		
Light state	Shade 3		Shade 2,5	Shade 3							
UV/IR Protection (permanent)	Shade 13	Shade 14	Shade 12	Shade 13			Shade 12				
Viewing area, approx. (mm)	109×73		150×76	107×73		107×54	93×45	107×55	93×44		
External grinding mode control	No			Yes ²⁾	No						
Auto ON	Yes				No			No			
Solar cell	No					Yes		No			
Battery lifetime (hours)	1500			1800	2 000	2 500	2 800	2 000	1500		
Number of sensors (arc detection)	4			3				2			
Classification	1/1/1/1	1/1/1/2	-	1/1/1/2					1/2/2/2		
Approval (welding filter)	EN 379		CE ⁵⁾	EN 379							

1) The ratings (best - better - good - not recommended) above refer to the products listed in this chart and should be seen as general recommendations based on differences in product comfort features and configuration options when using these selected Speedglas welding helmet series.

2) When used with the front cover 9100XXi and the 3M™ Speedglas™ Welding Helmets 9100, 9100-QR or 9100-Air.

3) G5-02 are very suitable for low amp plasma welding

4) G5-01TW and VC are used in flip-up helmet

5) Based on requirement in EN 379 and ISO 16321

Selector table


Standard welding helmets



Specification Welding helmets (non-air)	G5-02	9100	9100-QR	9002NC	100	100-QR
Eye and Face Protection (Approval) Welding Helmets Protection Plates Visor Plates	EN 175:F EN 166:FT	EN 175:B EN 166:BT	EN 175:B EN 166:BT	EN 175:B EN 166:BT	EN 175:B EN 166:BT	EN 175:B EN 166:BT
Head protection (Approval)	-	-	EN 397 ²⁾	-	-	EN 397 ²⁾
Respiratory protection¹⁾	All helmets are compatible with 3M disposable or reusable respirators. See next page for helmets available with powered and supplied air respiratory protection.					
Hearing protection – compatible options	Earmuffs Earplugs	Earmuffs Earplugs	Earmuffs Earplugs	Earmuffs Earplugs	Earmuffs Earplugs	Earplugs
① Exhaust vents	YES	YES	YES	YES	-	-
② Side windows	Curved ADF	Optional	YES	-	-	-
④ Flip-up with clear visor	-	-	-	-	-	-
Wide view	YES	-	-	-	-	-
Graphics option	-	-	-	-	YES	-
Auto-darkening filter options	G5-02 (Curved ADF)	9100V 9100X 9100XX 9100XXi	9100V 9100X 9100XX 9100XXi	9002NC	100V 100B	100V 100B

1) This overview shows only our helmets without air delivery connection. Helmets for powered or supplied air respirator systems see the next page.

2) With 3M™ Safety Helmet H-701.




① Exhaust vents – exhaled air is channeled out via side vents.




② Side windows – shade 5 filters that widen your field of vision.



③ High-comfort Speedglas headband with smooth ratchet for precise tightening.



④ Big, curved 17×10 cm clear protective visor, increasing your vision.



⑤ Adjust the airflow to your face or your visor, and the airflow coming from the top or side outlets – all without lifting your helmet.



⑥ Curved ADF follows the curvature of your head for wider total field of view in a slim helmet.

3M™ Speedglas™ Welding Helmets

Welding helmets for powered or supplied air respiratory protection



Specification Welding helmet systems (air)	G5-01	9100-Air	9100MP	9100MP-Lite
Eye and Face Protection (Approval) Welding Helmets Protection Plates Visor Plates	EN 175:B EN 166:BT EN 166:BT	EN 175:B EN 166:BT –	EN 175:B EN 166:BT EN 166:BT	EN 175:B EN 166:BT EN 166:BT
Head protection (Approval)	–	–	EN 397 Safety Helmet	EN 812 Bump Cap
Respiratory protection (Approval) ³⁾ Adflo Powered Air Purifying Respirator Versaflto Supplied Air Regulator V-500E	EN 12941 (TH3) NPF 500 EN 14594 (3B) NPF 200	EN 12941 (TH2) NPF 50 EN 14594 (3B) NPF 200	EN 12941 (TH3) NPF 500 EN 14594 (3B) NPF 200	EN 12941 (TH3) NPF 500 EN 14594 (3B) NPF 200
Hearing protection – compatible options	Earplugs	Earmuffs Earplugs	Earmuffs Earplugs	Earmuffs Earplugs
② Side windows	–	YES	YES	YES
③ High-comfort headband	YES	YES	–	–
④ Flip-up with clear visor	YES	–	YES	YES
⑤ Adjustable airflow	YES	–	– ⁴⁾	– ⁴⁾
Auto-darkening filter options	G5-01TW, G5-01VC	9100V, 9100X, 9100XX, 9100XXi	9100V, 9100X, 9100XX, 9100XXi	9100V, 9100X, 9100XX, 9100XXi

3) The nominal protection factor based on laboratory-measured performance data according to European Standards.
The protection factor is assigned by local authorities in each European country and can therefore be different for each country.

4) Limited adjustability of airflow.

Grinding headtops for powered or supplied air respiratory protection



Specification Visors and Helmets (air)	M-207	M-307	M-407
Eye and Face Protection (Approval) Visor Plates	EN 166 1:BT:3	EN 166 1:BT:3	EN 166 1:BT:3
Head protection (Approval)	EN812	EN 397	EN 397
Respiratory protection (Approval) ³⁾ Adflo Powered Air Purifying Respirator Versaflto Supplied Air Regulator	EN 12941 (TH2) NPF 50 EN 14594 (2B) NPF 50	EN 12941 (TH2) NPF 50 EN 14594 (3B) NPF 200	EN 12941 (TH2) NPF 50 EN 14594 (3B) NPF 200
Hearing protection – compatible options	Earmuffs Earplugs	Earmuffs Earplugs	Earmuffs Earplugs
Flame-retardant shroud	–	–	YES
Type of protective visor	Clear-coated polycarbonate	Clear-coated polycarbonate	Clear-coated polycarbonate

3) The nominal protection factor based on laboratory-measured performance data according to European Standards.
The protection factor is assigned by local authorities in each European country and can therefore be different for each country.

Welding Safety

Welding Helmets

Focus

3M™ Speedglas™ Welding Helmet G5-02

3M™ Speedglas™ Welding Helmet G5-02 with curved glass Auto-Darkening Lens. Thanks to the improved optics, the 3M™ Speedglas™ Curved Welding Lens G5-02 allows you to more readily recognize colors, using the 3M™ Speedglas™ Natural Color Technology.



- Our largest Auto-Darkening Lens field of view ever (150×76 mm), utilizing the 3M™ Speedglas™ Curved Glass Technology
- Bluetooth connectivity with app management
- Great clarity before, during and after welding, with our 3M™ Speedglas™ Natural Color Technology

Product ID	Part Number	Product Name	MOQ	OU
7100205306	621120	3M™ Speedglas™ Welding Helmet G5-02 with Curved Welding Filter, Headband, Cleaning Wipe & Bag, 621120	1	Each

Focus

3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01

3M™ Speedglas™ Heavy Duty Welding Helmet, G5-01 is specifically designed for the heavy duty welder. The helmets flip up functionality allows you to seamlessly switch between welding and grinding tasks while maintaining powered air respiratory protection.



- Available 3M™ Speedglas™ Welding Lens G5-01TW offers variable dark shades 5, 8-13 and tack welding comfort mode and G5-01VC offers variable dark shades 5, 8-14 plus Variable Color Technology
- The big (104 × 170 mm), clear protective visor is curved, with excellent views up, down and peripherally
- For more control over your comfort, the innovative G5-01 helmet airflow optimization system lets you direct the airflow to either your face, visor or somewhere in-between

Product ID	Part Number	Product Name	MOQ	OU
7100257945	611190	3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01, Replacement Shell, 611190	1	Each
7100257944	611120	3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01, with Welding Filter G5-01TW, 611120	1	Each
7100257812	611130	3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01, with Welding Filter G5-01VC, 611130	1	Each
7100256562	611100	3M™ Speedglas™ Heavy-Duty Welding Helmet G5-01, without Welding Filter, 611100	1	Each

Welding Safety

3M™ Speedglas™ Welding Helmets 9100 FX Series

The 3M™ Speedglas™ 9100 FX Welding Helmet features a flip-up Auto-Darkening Lens design. It incorporates a secondary clear faceshield that's ideal for grinding and set-up work, while the available Auto-Darkening Lens helps protect against the intense light of MIG, TIG, and stick applications. A highly adjustable head suspension system allows the helmet to comfortably fit many different head sizes and shapes, while side windows in the welding helmet give each welder a wider viewing field to see more of their work area.



- Flip-up function allows workers to switch between clear visor and available Auto-Darkening Lens
- 3M™ Speedglas™ Auto-Darkening Lenses provide good contrast and high optical quality
- Shade 5 side windows allows peripheral vision

Product ID	Part Number	Product Name	MOQ	OU
7000044521	541800	3M™ Speedglas™ Welding Helmets 9100 FX Series, without Welding Filter, 541800	1	Each

3M™ Speedglas™ Welding Helmets 9100 Air Series

3M™ Speedglas™ Welding Helmet Upgrade Kit 9100 Air, comes with the welding helmet 9100 Air, welding filter, self-adjusting QRS breathing tube and carry bag. The kit allows users to upgrade their existing 3M™ Adflo™ Powered Air Respirator or 3M™ Versaflo™ Supplied Air Regulator System.



- Upgrade kit with 3M™ Speedglas™ Welding Helmet 9100-Air, breathing tube and carry bag
- Side windows (shade 5) can help widen the field of vision
- 3M™ Speedglas™ Natural Colour Technology gives you high contrast and more natural-looking colours

Product ID	Part Number	Product Name	MOQ	OU
7100055548	569026	3M™ Speedglas™ Welding Helmets 9100 Air, upgrade kit 9100XXi, 569026	1	Each
7000044532	562800	3M™ Speedglas™ Welding Helmets 9100 Air, without Welding Filter, 562800	1	Each

3M™ Speedglas™ Welding Helmets 9100 Series

3M™ Speedglas™ 9100 Series Welding Helmets protect workers from radiation, heat and sparks, while providing a precise view of your work.



- Available Auto Darkening Lenses with seven variable dark shades (5, 8 and 9-13) for most types of arc welding
- Available in multiple models with various viewing area sizes
- Available with or without side windows

Product ID	Part Number	Product Name	MOQ	OU
7000000217	501805	3M™ Speedglas™ Welding Helmets 9100 Series, with Side Windows and Welding Filter 9100V, 501805	1	Each
7000000218	501815	3M™ Speedglas™ Welding Helmets 9100 Series, with Side Windows and Welding Filter 9100X, 501815	1	Each
7000000219	501825	3M™ Speedglas™ Welding Helmets 9100 Series, with Side Windows and Welding Filter 9100XX, 501825	1	Each
7100166722	501826	3M™ Speedglas™ Welding Helmets 9100 Series, with Side Windows, with Welding Filter 9100XXi, 501826	1	Each
7100011652	501800	3M™ Speedglas™ Welding Helmets 9100 Series, with Side Windows, without Welding Filter, 501800	1	Each
7000044482	501100	3M™ Speedglas™ Welding Helmets 9100 Series, without Welding Filter, 501100	1	Each

Welding Safety

3M™ Speedglas™ Welding Helmets 9100 QR Series

Protect your eyes and face from radiation, heat and sparks with integrated head protection with 3M™ Speedglas™ Welding Helmet 9100 QR Series.



- Eye, face and head protection for welding applications
- 3M™ Speedglas™ Welding Filter 9100XXi offers variable dark shades of 5, 8, and 9-13 for most types of arc welding. The special 9100XXi silver front panel houses external controls, enabling fast and easy access to the grinding and memory modes
- 3M™ Speedglas™ Natural Colour Technology gives you high contrast and more natural-looking colours

Product ID	Part Number	Product Name	MOQ	OU
7100166725	583615	3M™ Speedglas™ Welding Helmets 9100 QR Series, with Welding Filter 9100X, with 3M™ Safety Helmet H-701, 583615	1	Each
7100166718	583625	3M™ Speedglas™ Welding Helmets 9100 QR Series, with Welding Filter 9100XX, with 3M™ Safety Helmet H-701, 583625	1	Each
7100166721	582600	3M™ Speedglas™ Welding Helmets 9100 QR Series, without Welding Filter, 582600	1	Each

3M™ Speedglas™ Welding Helmets 9100 MP Series

3M™ Speedglas™ Welding Helmet 9100 MP Series combines with 3M™ Adflo™ Powered Air Respirator or 3M™ Versaflo™ Supplied Air Regulator System, for an easy to use head, eye, face and respiratory protection system.



- Comfortable, easy to use head, eye, face and respiratory protection
- Flip-up welding visor combined with a clear protective visor (170 mm x 100 mm)
- Side windows (shade 5) can help widen the field of vision

Product ID	Part Number	Product Name	MOQ	OU
7000044560	572800	3M™ Speedglas™ Welding Helmets 9100 MP, without Welding Filter, 572800	1	Each
7100112335	592800	3M™ Speedglas™ Welding Helmets 9100 MP-Lite, without Welding Filter, 592800	1	Each

3M™ Speedglas™ Welding Helmets 9000 Series

The 3M™ Speedglas™ 9000 Welding Helmet offers superior protection for both apprentices and professional welders. Its narrow width polyamide nylon construction is heat and chemical resistant, extremely durable and ideal for working in tight spots.



- Exclusive exhalation venting
- Comfortable and lightweight
- 3M™ Speedglas™ 9002NC Auto-Darkening Lens provides a large viewing area, natural color and customizable settings for multiple welding applications

Product ID	Part Number	Product Name	MOQ	OU
7100116824	401385	3M™ Speedglas™ Welding Helmets 9002NC, with Welding Filter, 401385	1	Each

Welding Safety

3M™ Speedglas™ 100 Series Welding Helmets

3M™ Speedglas™ 100 Series Welding Helmet helps protect welders from flying sparks and airborne debris, and the Auto-Darkening Lens helps keep the eyes safe from the intense light of MIG, TIG, and stick welding while offering an accurate view of the workspace, before during and after the weld. With an optional hard-hat adapter, this helmet is a great choice for welders starting off their careers, tradesmen, and DIYers.



- Welding helmet with optional safety helmet adapter
- Great choice for welders starting off their careers, tradesmen, and DIYers
- Auto-Darkening Lens with five adjustable dark shades 8–12 (not applicable to 3M Speedglas 100 Passive Welding Helmet)

Product ID	Part Number	Product Name	MOQ	OU
7100166705	751120	3M™ Speedglas™ Welding Helmets 100 Series, Black, with Welding Filter 100v, 751120	1	Each
7100166706	752520	3M™ Speedglas™ Welding Helmets 100 Series, Ice Hot, with Welding Filter 100v, 751520	1	Each
7100166689	752420	3M™ Speedglas™ Welding Helmets 100 Series, Razor Dragon, with Welding Filter 100v, 752420	1	Each
7100166702	751620	3M™ Speedglas™ Welding Helmets 100 Series, Trojan Warrior, with Welding Filter 100v, 751620	1	Each
7100166688	752220	3M™ Speedglas™ Welding Helmets 100 Series, Xterminator, with Welding Filter 100v, 752220	1	Each
7100166692	783120	3M™ Speedglas™ Welding Helmets 100 Series, with Safety Helmet and Welding Filter 100V, 783120	1	Each
7100259107	751114	3M™ Speedglas™ Welding Helmets 100 Series, with Welding Filter 100B, 751114	1	Each

Welding Safety

Welding Helmet & Respirator Sets

3M™ Adflo™ Powered Air Respirator System

For effective protection against a range of particulates and gases encountered in the welding process, use 3M™ Adflo™ Powered Air Respirator. The Adflo™ respirator connects directly with any Speedglas™ Series respiratory welding helmet and can protect users against both particles and gases depending on the filter used.

- Can protect you against particles and gases, all in one system, depending on filter used
- Nominal protection Factor up to 500 (TH3) in combination with Speedglas welding helmets
- Connects directly with any Speedglas Series respiratory welding helmet



Product ID	Part Number	Product Name	MOQ	OU
7100166698	837731	3M™ Complete Adflo™ System, Heavy-duty Battery, 837731	1	Each
7100166697	837730	3M™ Complete Adflo™ System, Standard Battery, 837730	1	Each
7100166696	837710	3M™ Complete Adflo™ System, without Belt, without Charger, 837710	1	Each

3M™ Adflo™ Powered Air Respirator Turbo Unit

3M™ Adflo™ Turbo Assembly is our replacement powered air turbo unit to be used with your original belt, filter and filter cover, battery, and charger.

- Replacement 3M™ Adflo™ turbo assembly
- Depending upon the filters used, can provide protection against particulates, gases and vapours commonly found in welding processes
- Connects with 3M™ Speedglas™ Respiratory Welding Helmets and selected 3M™ Versaflo™ Helmets



Product ID	Part Number	Product Name	MOQ	OU
7000044338	832000	3M™ Adflo™ Powered Air Respirator Turbo Assembly, 832000	1	Each

Welding Safety

Focus

3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Series Welding Helmet

3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Series Welding Helmet provides all of the benefits of our G5-01 series welding helmet with our convenient Adflo™ Powered Air Purifying Respirator system.



- Robust, compact design
- Ergonomic, adjustable head suspension
- Flip front welding shield allows for a clear, wide-view protective visor for grinding and setup

Product ID	Part Number	Product Name	MOQ	OU
7100256131	617820	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, with Welding Filter G5-01TW, 617820	1	Each
7100258327	617829	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, with Welding Filter G5-01TW, with consumable kit and bag, 617829	1	Each
7100257943	617830	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, with Welding Filter G5-01VC, 617830	1	Each
7100258328	617839	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, with Welding Filter G5-01VC, with consumable kit and bag, 617839	1	Each
7100258110	617800	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, without Welding Filter, 617800	1	Each
7100258326	617809	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ G5-01 Welding Helmet, without Welding Filter, with consumable kit and bag, 617809	1	Each

3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100-Air Welding Helmet

The 3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100-Air Welding Helmet is designed to help protect the eyes and face from radiation, sparks, and spatter.



- All the benefits of the 3M™ Speedglas™ Welding Helmet 9100 Air in combination with 3M™ Adflo™ Powered Air Purifying Respirator
- Ergonomically designed head suspension
- Fits with 3M™ PELTOR™ Welding Earmuff H505B

Product ID	Part Number	Product Name	MOQ	OU
7000044615	567700	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100-Air Welding Helmet, Without Welding Filter, 567700	1	Each
7100166723	567726	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100-Air Welding Helmet, with Welding Filter 9100XXi, 567726	1	Each

Welding Safety

3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100 MP Welding Helmet

The 3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100 MP Welding Helmet is designed to help protect the eyes and face from radiation, sparks, and spatter. This system also includes respiratory protection, head protection, optional hearing protection, and a flip-up welding shield.



- 3M™ Speedglas™ 9100 MP Welding Helmet with 3M™ Adflo™ Powered Air Purifying Respirator System
- Wide, clear visor plate
- Sold with options of 3M™ Speedglas™ 9100 Welding Filters

Product ID	Part Number	Product Name	MOQ	OU
7100054792	577726	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100 MP Welding Helmet, with Welding Filter 9100XXi, 577726	1	Each
7000044619	577700	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100 MP Welding Helmet, without Welding Filter, including Bag, 577700	1	Each
7100112333	597700	3M™ Adflo™ Powered Air Purifying Respirator System with 3M™ Speedglas™ 9100 MP-Lite Welding Helmet, without Welding Filter, 597700	1	Each

3M™ Versaflo™ V-500E Regulator Supplied Air System with 3M™ Speedglas™ 9100 MP Welding Helmet

3M™ Speedglas™ Welding Helmet 9100 MP, with 3M™ Versaflo™ Supplied Air Regulator V-500E offers head, eye, face and respiratory protection with a flip-up welding filter combined with a large (170 mm x 100 mm), clear protective visor and safety helmet. For use with Speedglas welding filter series 9100 (sold separately).



- Combined head, face, eye and supplied air respiratory protection for welding applications
- Fits with 3M™ Speedglas™ Welding Filter Series 9100 (passive or auto-darkening)
- Designed from inception to take one of our optional 3M™ Peltor™ Earmuffs

Product ID	Part Number	Product Name	MOQ	OU
7000044564	578800	3M™ Versaflo™ V-500E Regulator Supplied Air System with 3M™ Speedglas™ 9100 MP Welding Helmet, without Welding Filter, 578800	1	Each

Welding Safety

Welding Filters

Focus

3M™ Speedglas™ Curved Welding Filters G5 Series

Replacement Welding filter for the 3M™ Speedglas™ Welding Helmet G5-02 with curved glass auto-darkening filter (ADF), variable dark shades 8-12.



- Our largest ADF field of view ever (150×76 mm), utilizing the 3M™ Speedglas™ Curved Glass Technology
- Great clarity before, during and after welding, with our 3M™ Speedglas™ Natural Colour Technology
- By selecting just the right settings for each task, you help reduce eye strain and can improve the quality of every weld

Product ID	Part Number	Product Name	MOQ	OU
7100204034	620020	3M™ Speedglas™ Curved Welding Filter G5-02, 620020	1	Each

Focus

3M™ Speedglas™ Welding Filter G5 Series

Introducing the world's first curved auto-darkening filter (ADF) designed for the 3M™ Speedglas™ Welding Helmet G5-02. Utilizing the new 3M™ Speedglas™ Curved Glass Technology, its shape follows your head's curvature and the range of your peripheral vision.



- The world's first curved Auto Darkening Welding Filter
- Speedglas Natural Colour technology makes the filter view seem lighter, more detailed and colourful
- Bluetooth enabled: with the 3M Connected Equipment app, users get access to additional functionalities, statistics and documentation

Product ID	Part Number	Product Name	MOQ	OU
7100185852	610020	3M™ Speedglas™ Welding Filter G5 Series, G5-01TW, 610020	1	Each
7100185618	610030	3M™ Speedglas™ Welding Filter G5 Series, G5-01VC, 610030	1	Each

3M™ Speedglas™ Welding Filter Upgrade Kits 9100XXi Series

3M™ Speedglas™ Welding Filter 9100XXi Upgrade Kit with 3M™ Speedglas™ Natural Colour Technology and special silver front panel enabling outside control functions (grinding/memory) when used with 9100/9100Air/9100-QR welding helmets.



- Special silver front panel to access outside control functions (grinding/memory) when used with 9100/9100Air/9100-QR welding helmets
- Variable dark shades 5, 8 and 9-13
- Light shade 3

Product ID	Part Number	Product Name	MOQ	OU
7100032898	500126	3M™ Speedglas™ Welding Filter Upgrade Kits 9100XXi, 500126	1	Each

MOQ = Minimum Order Quantity, OU = Order Unit

Welding Safety

3M™ Speedglas™ Auto-Darkening Welding Filters 9100 Series

3M™ Speedglas™ 9100 Series Auto-Darkening Welding Filters are designed for the professional welder using 3M™ Speedglas™ Welding Helmet 9100 Series. Incorporating dark shade ranges 5, 8-13, grinding, and cutting modes, these filters are ideal for use with most arc welding processes.



- Auto-darkening welding filter designed for use with 3M™ Speedglas™ Welding Helmet 9100 Series, suitable for most types of arc welding
- Delivers minimal distortion across the entire filter viewing area
- The sensitivity of arc detection can be adjusted for unsurpassed switching reliability. Switching time (light-dark) of 0.1ms.

Product ID	Part Number	Product Name	MOQ	OU
7100080221	500005	3M™ Speedglas™ Auto-Darkening Welding Filters 9100 Series, 9100V, 500005	1	Carton
7000000221	500015	3M™ Speedglas™ Auto-Darkening Welding Filters 9100 Series, 9100X, 500015	1	Each
7000028044	500025	3M™ Speedglas™ Auto-Darkening Welding Filters 9100 Series, 9100XX, 500025	1	Each
7100032397	500026	3M™ Speedglas™ Auto-Darkening Welding Filters 9100 Series, 9100XXi, 500026	1	Each

3M™ Speedglas™ Auto-Darkening Welding Filters 9002NC

The 3M™ Speedglas™ Welding Lens 9002 is used with the 9000 welding helmet. This lens offers rugged, dependable protection with advanced auto darkening optics that adjust to your working conditions providing a view that appears lighter, brighter and more realistic for better control of the weld puddle. Shade 3 light state with adjustable dark shades 8-12. Simplified UI, easy to operate, with a larger 2.1"x4.2" viewing area.



- User interface easy to operate and maintain
- Runs on CR2032 Lithium 3V batteries
- Shade 3 light state with adjustable dark shades 8-12

Product ID	Part Number	Product Name	MOQ	OU
7100114634	400085	3M™ Speedglas™ Auto-Darkening Welding Filters 9002NC, 400085	1	Pack

3M™ Speedglas™ Auto-darkening Welding Filters SL Series

3M™ Speedglas™ Auto-Darkening Welding Filters SL Series are replacement auto-darkening welding filters designed for use with 3M™ Speedglas™ Welding Helmet SL.



- Auto-darkening welding filter designed for use with 3M™ Speedglas™ Welding Helmet SL Series, suitable for most arc welding processes, such as MMA, MIG/MAG, TIG, and plasma welding
- Five adjustable dark shades 8-12. Light shade 3
- Four levels of arc sensitivity (switching light to dark state)

Product ID	Part Number	Product Name	MOQ	OU
7000044451	700020	3M™ Speedglas™ Auto-darkening Welding Filters SL Series, 700020	1	Each

Welding Safety

3M™ Speedglas™ Auto-Darkening Welding Filters 100 Series

3M™ Speedglas™ Auto-Darkening Welding Filters 100-Series are replacement auto-darkening welding filters designed for use with 3M™ Speedglas™ Welding Helmet 100 Series.



- Replacement auto-darkening welding filters designed for use with 3M™ Speedglas™ Welding Helmet 100 Series
- 100V - Variable dark shades 8-12. 100B variable dark shades 10-12
- Light shade of 3

Product ID	Part Number	Product Name	MOQ	OU
7100259002	750014	3M™ Speedglas™ Auto-Darkening Welding Filters 100 Series, 100B, Shades 3, 10-12, 750014	10	Each
7100167242	750020	3M™ Speedglas™ Auto-Darkening Welding Filters 100 Series, 100V, 750020	1	Each

3M™ Passive Welding Filters

3M™ Speedglas™ Passive Welding Filters are replacement filters designed for 3M™ Welding lens



- Replacement passive filter
- Designed for 3M™ Speedglas™ Welding Helmets
- Passive lens shade 11

Product ID	Part Number	Product Name	MOQ	OU
7100257837	610011	3M™ Passive Welding Filters, G5-01, 610011	1	Each

3M™ Adflo™ Particulate & Gas Filters

3M™ Adflo™ Particulate and Gas Filters are replacement, high-efficiency filters for use with 3M™ Adflo™ Powered Air Purifying Respirators.



- Provides protection against a range of particulate and gas hazards (dependent upon filters selected)
- For use with 3M™ Adflo™ Powered Air Purifying Respirators (PAPR)
- Particle filter, gas filters, and odour filter/pad available

Product ID	Part Number	Product Name	MOQ	OU
7000028043	837242	3M™ Adflo™ Gas Filter, A1B1E1, 837242	1	Each
7000028075	837542	3M™ Adflo™ Gas Filter, A2, 837542	1	Each
7000028074	837110	3M™ Adflo™ Odour Filter, 837110	1	Each
7100288125	837012	3M™ Adflo™ Particle Filter P SL, pkg of 2, 837012	1	Pack
7100277745	837020	3M™ Adflo™ Particle Filter P SL, pkg of 20, 837020	20	Pack
7100277744	837080	3M™ Adflo™ Particle Filter P SL, pkg of 80, 837080	80	Pack

Welding Safety

Welding Parts & Accessories

3M™ Adflo™ Batteries

Product ID	Part Number	Product Name	MOQ	OU
7100279645	837631	3M™ Adflo™ Li-ion Battery, Heavy-Duty, 837631	1	Each
7100279646	837630	3M™ Adflo™ Li-ion Battery, Standard, 837630	1	Each

3M™ AdFlo™ Powered Air Respirator Filter and Battery Kit

Product ID	Part Number	Product Name	MOQ	OU
7000144540	837301	3M™ AdFlo™ Powered Air Respirator Filter and Battery Kit, A1B1E1 Filter and Heavy Duty Li-on Battery, 837301	1	Kit

3M™ AdFlo™ Powered Air Respirator Prefilters

Product ID	Part Number	Product Name	MOQ	OU
7100080248	836010	3M™ AdFlo™ Powered Air Respirator Prefilters, 836010	10	Carton

3M™ Adflo™ Spark Arrestors

Product ID	Part Number	Product Name	MOQ	OU
7000028010	836000	3M™ Adflo™ Spark Arrestor, 836000	10	Each

3M™ Adflo™ Battery Upgrade Kits

Product ID	Part Number	Product Name	MOQ	OU
7000144541	837635	3M™ Welding Upgrade Kits for Adflo™, Li-ion Battery Kit, Standard Upgrade Kit, 837635	1	Kit

3M™ Welding Breathing Tubes

Product ID	Part Number	Product Name	MOQ	OU
7000044527	834017	3M™ Welding Breathing Tubes, for Adflo™, Heavy Duty Rubber, QRS, 834017	1	Each
7000028067	834016	3M™ Welding Breathing Tubes, for Adflo™, Self-adjusting, QRS, 834016	1	Each

Welding Safety

3M™ Welding Breathing Tube Covers

Product ID	Part Number	Product Name	MOQ	OU
7000028062	834018	3M™ Welding Breathing Tube Cover, 834018	20	Each

3M™ Breathing Tube Adapters

Product ID	Part Number	Product Name	MOQ	OU
7000144525	533505	3M™ Breathing Tube Adapter for Non-QRS Breathing Tubes, 533505	1	Each

3M™ Welding Batteries

Product ID	Part Number	Product Name	MOQ	OU
7100222333	602000	3M™ Welding Filter Battery, CR2450, 602000	1	Bag
7100167881	422000	3M™ Welding Filter Battery, CR20320, 422000	5	Bag

3M™ Welding Battery Chargers

Product ID	Part Number	Product Name	MOQ	OU
7100217397	833111	3M™ Welding Battery Charger, for Adflo™ Li-ion Battery, 8333111	1	Each

3M™ Speedglas™ G5-01 Accessory Kits

Product ID	Part Number	Product Name	MOQ	OU
7100256371	792000	3M™ Speedglas™ Accessory Kit, Consumable Starter Kit, G5-01. 792000	1	Each

3M™ Speedglas™ Inner Cover Plates

Product ID	Part Number	Product Name	MOQ	OU
7100202350	624000	3M™ Speedglas™ Inner Cover Plate G5-02, 624000	10	Bag
7100080227	428020	3M™ Speedglas™ Inner Cover Plate, 9000V +1 Shade, 428020	1	Bag
7100080228	428040	3M™ Speedglas™ Inner Cover Plate, 9000V +2 Shades, 428040	1	Bag
7100090450	428030	3M™ Speedglas™ Inner Cover Plate, 9000X, 0.7 Shade, 428030	1	Bag
7000000225	528005	3M™ Speedglas™ Inner Cover Plate, 9100V, 528005	20	Bag
7000000226	528015	3M™ Speedglas™ Inner Cover Plate, 9100X, 528015	20	Bag
7000000227	528025	3M™ Speedglas™ Inner Cover Plate, 9100XX, 528025	20	Bag
7000000182	428000	3M™ Speedglas™ Inner Cover Plate, SL/100/10V, 428000	1	Bag

Welding Safety

3M™ Speedglas™ Welding Helmet Inner Grinding Visor Plates

Product ID	Part Number	Product Name	MOQ	OU
7100190170	613000	3M™ Speedglas™ Welding Helmet Inner Grinding Visor Plate, Anti-Fog and Hardcoated, 613000	1	Bag

3M™ Speedglas™ Welding Helmet Inner Shields

Product ID	Part Number	Product Name	MOQ	OU
7100257946	611195	3M™ Speedglas™ Welding Helmet Inner Shield, G5-01, 611195	1	Each

3M™ Speedglas™ Outer Protection Plates

Product ID	Part Number	Product Name	MOQ	OU
7100092252	776000	3M™ Speedglas™ Outer Protection Plate, 100, Standard, 776000	10	Bag
7100144401	126000	3M™ Speedglas™ Outer Protection Plate, 10V, 126000	6	Pack
7000000206	427071	3M™ Speedglas™ Outer Protection Plate, 9000, Heat Resistant, 427071	1	Bag
7000000183	427000	3M™ Speedglas™ Outer Protection Plate, 9000, Scratch Resistant, 427000	5	Bag
7100016860	426000	3M™ Speedglas™ Outer Protection Plate, 9000, Standard, 426000	10	Bag
7100016690	527070	3M™ Speedglas™ Outer Protection Plate, 9100, Heat Resistant, 527070	1	Bag
7000000223	527000	3M™ Speedglas™ Outer Protection Plate, 9100, Scratch Resistant, 527000	10	Bag
7100108831	527001	3M™ Speedglas™ Outer Protection Plate, 9100, Scratch Resistant, 527001	10	Bag
7100016691	526000	3M™ Speedglas™ Outer Protection Plate, 9100, Standard, 526000	10	Bag
7100205305	626000	3M™ Speedglas™ Outer Protection Plate, G5-02, 626000	1	Bag
7100080220	726000	3M™ Speedglas™ Outer Protection Plate, SL, Standard, 726000	1	Carton

Welding Safety

3M™ Speedglas™ Protective Covers Hoods & Shrouds

Product ID	Part Number	Product Name	MOQ	OU
710080224	164005	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Ear and Neck Protection, Leather, 164005	1	Bag
7000000230	169010	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Extended Neck and Ear Protection, 9100 Series, 169010	1	Each
7100189979	169035	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Extended Protection Kit, G5-01, 169035	1	Each
7100167240	169007	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Cover, 9100 FX, Extra-Large, 169007	1	Each
7100167239	169006	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Cover, 9100FX, Small, 169006	1	Each
7000144522	169005	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Cover, Extended Coverage, Crown, 9100/9100 Air, 169005	1	Each
7100185832	169020	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Protection, G5-01, Fabric, Small, 169020	10	Each
7100185833	169022	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Protection, G5-01, Leather 169022	10	Each
7100185847	169023	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Protection, G5-01, Leather, Large, 169023	1	Each
7100256090	169021	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Head Protection, Leather, Fluorescent yellow, 169021	1	Each
7100003083	169100	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Hood, 169100	10	Each
7100185845	169041	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Neck Protection, Fabric, G5-01, 169041	1	Each
7100185839	169042	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Neck Protection, Fabric, Large, G5-01, 169042	10	Each
7100186963	169043	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Neck Protection, Leather, G5-01, 169043	1	Each
7100181383	169040	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Rigid Neck Protection, G5-01, 169040	1	Each
7100167334	169014	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Safety Helmet Cover, 9100/ 9100MP-Lite, 169014	1	Each
7100106682	169015	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Shroud, 9100MP / 9100MP-Lite, 169015	10	Each
7100185817	169030	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Shroud, G5-01, 169030	1	Each
7000044371	169001	3M™ Speedglas™ Protective Covers, Hoods, & Shrouds, Throat Cover, 9100 Series, 169001	1	Each

3M™ Speedglas™ Welding Caps

Product ID	Part Number	Product Name	MOQ	OU
7100100079	954410	3M™ Speedglas™ Welding Cap, 954410	50	Pack
7100112650	896056	3M™ Speedglas™ Welding Cap, Bump Cap, 9100 MP-Lite, 896056	1	Each

Welding Safety

3M™ Sweatbands

Product ID	Part Number	Product Name	MOQ	OU
7100080223	168010	3M™ Sweatband, Fleecy Cotton, 168010	20	Bag
7100173404	198017	3M™ Sweatband, G5-01, Fleecy Cotton, 198017	1	Bag
7100190171	198018	3M™ Sweatband, G5-01, Leather, 198018	1	Bag
7100169234	198016	3M™ Sweatband, G5-01, Towelling, 198016	1	Bag
7100080253	167520	3M™ Sweatband, Towelling, 167520	10	Bag

3M™ Speedglas™ Welding Helmet Head Rests

Product ID	Part Number	Product Name	MOQ	OU
7100256659	536211	3M™ Speedglas™ Welding Helmet Head Rest, Large, 536211	1	Each

3M™ Speedglas™ Welding Helmet Task Light Kits

Product ID	Part Number	Product Name	MOQ	OU
7100185841	169200	3M™ Speedglas™ Welding Helmet Task Light Kit, G5-01, 169200	1	Each

3M™ Speedglas™ Welding Helmet Task Light Power Cables

Product ID	Part Number	Product Name	MOQ	OU
7100185830	169210	3M™ Speedglas™ Welding Helmet Task Light Power Cable, Long, 169210	1	Each
7100185829	169211	3M™ Speedglas™ Welding Helmet Task Light Power Cable, Short, 169211	1	Each

3M™ Speedglas™ Welding Helmet Task Light Protection Plates

Product ID	Part Number	Product Name	MOQ	OU
7100191825	169205	3M™ Speedglas™ Welding Helmet Task Light Protection Plate, G5-01, 169205	20	Bag

3M™ Welding Bags, Backpacks & Pouches

Product ID	Part Number	Product Name	MOQ	OU
7100282441	BPK-HD	3M™ Speedglas™ Heavy-Duty Back Pack, BPK-HD, 3 ea/Case	3	Each
7100167362	790105	3M™ Speedglas™ Welding Helmet Storage Bag, G5-01, 790105	1	Each
7100203048	790104	3M™ Speedglas™ Welding Helmet Storage Bag, G5-02, 790104	1	Bag

Welding Safety

3M™ Speedglas™ Magnifying Lens Holders

Product ID	Part Number	Product Name	MOQ	OU
7100181452	171035	3M™ Speedglas™ Magnifying Lens Holder, G5-01, 171035	1	Each

3M™ Speedglas™ Magnifying Lenses

Product ID	Part Number	Product Name	MOQ	OU
7100202396	172022	3M™ Speedglas™ G5-02 2.5X Magnifying Lens, 172022	1	Bag
7100090451	171020	3M™ Speedglas™ Magnifying Lens, 1.0X, 171020	1	Bag
7100167333	171021	3M™ Speedglas™ Magnifying Lens, 1.5X, 171021	1	Each
7100202361	172020	3M™ Speedglas™ Magnifying Lens, 1.5X, G5-02, 172020	1	Bag
7000144517	171022	3M™ Speedglas™ Magnifying Lens, 2.0X, 171022	1	Each
7100202360	172021	3M™ Speedglas™ Magnifying Lens, 2.0X, G5-02, 171021	1	Bag
7000028023	171023	3M™ Speedglas™ Magnifying Lens, 2.5X, 171023	1	Each
7000028033	171024	3M™ Speedglas™ Magnifying Lens, 3.0X, 171024	1	Each

3M™ Welding Clear Visors/Plates

Product ID	Part Number	Product Name	MOQ	OU
7100080231	523001	3M™ Welding Clear Visors Plate, 9100, Anti-fog, 523001	1	Bag
7000000236	523000	3M™ Welding Clear Visors Plate, 9100, Standard, 523000	25	Bag

3M™ Speedglas™ Welding Helmet Replacement Shells

Product ID	Part Number	Product Name	MOQ	OU
7000044531	560890	3M™ Speedglas™ Welding Helmet Replacement Shell, 9100 Air, Without Filter, 560890	1	Each
7000044502	541890	3M™ Speedglas™ Welding Helmet Replacement Shell, 9100 FX, Without Filter, 541890	1	Each
7100205307	621195	3M™ Speedglas™ Welding Helmet Replacement Shell, G5-02, 621195	1	Each
7000044572	570495	3M™ Speedglas™ Welding Helmet Replacement Shell, Outer Shield, 9100 MP, 570495	1	Each
7100185831	610195	3M™ Speedglas™ Welding Helmet Replacement Shell, Outer Shield, G5-01, Flip-Up, 610195	1	Each

3M™ Speedglas™ Face Seals

Product ID	Part Number	Product Name	MOQ	OU
7100011654	534100	3M™ Speedglas™ Face Seal, 9100 Air, 534100	1	Each
7100167238	534000	3M™ Speedglas™ Face Seal, 9100 FX-Air, 534000	1	Each
7100167292	534200	3M™ Speedglas™ Face Seal, 9100MP, 534200	1	Each
7100161510	614000	3M™ Speedglas™ Face Seal, G5-01, 614000	1	Each

Welding Safety

3M™ Speedglas™ Welding Helmet Front Covers

Product ID	Part Number	Product Name	MOQ	OU
7000028045	532000	3M™ Speedglas™ Welding Helmet Front Cover, 9100, Heat Reflective, Silver, 532000	1	Each
7010043778	532100	3M™ Speedglas™ Welding Helmet Front Cover, 9100XXi, Heat Reflective, Silver, 532100	1	Each
7100185834	610501	3M™ Speedglas™ Welding Helmet Front Cover, Flip Up, G5-01, 610501	10	Each
7100203042	622000	3M™ Speedglas™ Welding Helmet Front Cover, G5-02, 622000	1	Each
7100173966	610500	3M™ Speedglas™ Welding Helmet Front Cover, Inner Visor, G5-01, 610500	1	Bag
7100167200	540500	3M™ Speedglas™ Welding Helmet Front Cover, Kit, 9100FX/9100MP, 540500	1	Kit

3M™ Welding Headbands & Headband Components

Product ID	Part Number	Product Name	MOQ	OU
7000028072	705015	3M™ Speedglas™ Welding Helmet Headband, 100/9000/SL, 705015	1	Each
7100203041	705020	3M™ Speedglas™ Welding Helmet Headband, Assembly Parts and Sweatband, G5-02, 705020	1	Each
7000044488	536200	3M™ Speedglas™ Welding Helmet Headband, Back Part, Ratchet, 9100, 536200	1	Each
7100256092	616003	3M™ Speedglas™ Welding Helmet Headband, Back Part, Ratchet, G5-01, 616003	10	Each
7000044487	536100	3M™ Speedglas™ Welding Helmet Headband, Front Part, 9100, 536100	1	Each
7100256086	613200	3M™ Speedglas™ Welding Helmet Headband, G5-01, 613200	1	Each
7100001460	533000	3M™ Speedglas™ Welding Helmet Headbands, 9100, 533000	1	Each

3M™ Speedglas™ Quick Release Helmet Rail Components QR Series

Product ID	Part Number	Product Name	MOQ	OU
7100031606	197139	3M™ Speedglas™ Quick Release Helmet Rail Components, QR Series, 197139	1	Each





Apparel & Workwear

Apparel & Workwear

Coveralls

3M™ Protective Coverall 4500

3M™ Protective Coverall 4500 is made from a soft breathable polypropylene offering the wearer excellent heat dissipation and cool comfort. This coverall gives basic protection against dirt, dust and non-hazardous liquids and is CE Cat I Simple certified.



- Category 1 coverall designed for light duty protection against non-hazardous liquids and dusts
- Breathable 45gsm polypropylene material offers CE Simple certification for non-hazardous particles and liquids
- Excellent breathability and comfort for extended wear

Product ID	Part Number	Product Name	MOQ	OU
7000089594	4500W2XL	3M™ Coverall 4500, 2XL	20	Each
7000089595	4500W3XL	3M™ Coverall 4500, 3XL	20	Each
7000089596	4500W4XL	3M™ Coverall 4500, 4XL	20	Each
7000089592	4500WL	3M™ Coverall 4500, L	20	Each
7000089591	4500WM	3M™ Coverall 4500, M	20	Each
7000089590	4500WS	3M™ Coverall 4500, S	20	Each
7000089593	4500WXL	3M™ Coverall 4500, XL	20	Each

3M™ Protective Coverall 4515

3M™ Protective Coverall 4515 is a strong 50gsm SMS coverall with superb breathability and comfort meaning it can be worn comfortably for long periods of time and help productivity. CE certified it protects against toxic dusts Type 5, liquid splashes Type 6 and nuclear particles to EN 1073-2. An economic solution, it is available in a variety of colours to assist in identification and zoning.



- Type 5/6 Coverall designed to offer cost effective protection against hazardous dusts such as asbestos fibre
- Made from highly breathable SMS non-woven for effective release of body heat and moisture and reduced heat stress
- Soft and strong 50gsm SMS for strong performance

Product ID	Part Number	Product Name	MOQ	OU
7000089622	4515B2XL	3M™ Protective Coverall 4515, Blue, 2XL	20	Each
7000089623	4515B3XL	3M™ Protective Coverall 4515, Blue, 3XL	20	Each
7000089620	4515BL	3M™ Protective Coverall 4515, Blue, L	20	Each
7000089619	4515BM	3M™ Protective Coverall 4515, Blue, M	20	Each
7000089618	4515BS	3M™ Protective Coverall 4515, Blue, S	20	Each
7000089621	4515BXL	3M™ Protective Coverall 4515, Blue, XL	20	Each
7000089636	4515O2XL	3M™ Protective Coverall 4515, Orange, 2XL	20	Each
7000089634	4515OL	3M™ Protective Coverall 4515, Orange, L	20	Each
7000089633	4515OM	3M™ Protective Coverall 4515, Orange, M	20	Each
7000089632	4515OS	3M™ Protective Coverall 4515, Orange, S	20	Each
7000089635	4515OXL	3M™ Protective Coverall 4515, Orange, XL	20	Each

Apparel & Workwear

3M™ Protective Coverall 4520

3M™ Protective Coverall 4520 has been engineered to offer multiple layers of SMMMS for effective hold out and strength at a lightweight 43gsm. Superbly breathable and soft with a cloth like feel it can be worn for extended periods comfortably and protects against static discharge, hazardous particulates and liquid splash Type 5/6.



- Type 5/6 Coverall made from extremely lightweight and breathable material, designed to offer protection against hazardous dusts and limited liquid splashes and sprays
- Made from super breathable SMMMS non-woven for effective release of body heat and moisture and reduced heat stress
- Soft and strong multi-layered 43gsm SMS for strong performance

Product ID	Part Number	Product Name	MOQ	OU
7000034764	4520W2XL	3M™ Protective Coverall 4520, 2XL	20	Each
7000089643	4520W3XL	3M™ Protective Coverall 4520, 3XL	20	Each
7000089644	4520W4XL	3M™ Protective Coverall 4520, 4XL	20	Each
7000034762	4520WL	3M™ Protective Coverall 4520, L	20	Each
7000034761	4520MW	3M™ Protective Coverall 4520, M	20	Each
7000089642	4520WS	3M™ Protective Coverall 4520, S	20	Each
7000034763	4520WXL	3M™ Protective Coverall 4520, XL	20	Each
7100052199	4520C2XL	3M™ Protective Coverall 4520CS, 2XL	20	Each
7100048969	4520CL	3M™ Protective Coverall 4520CS, L	20	Each
7100048967	4520CM	3M™ Protective Coverall 4520CS, M	20	Each
7100048964	4520CXL	3M™ Protective Coverall 4520CS, XL	20	Each

3M™ Protective Coverall 4530

3M™ Protective Coverall 4530 has a specialist material treatment which offers fabric flame spread resistance to allow the garment to be worn over an Index 2/3 FR garment, enhancing the chemical splash and hazardous dust protection and extending the life cycle through reduced laundering. Certified to Cat III hazardous dust and splash type 5/6 protection and Antistatic EN 1149.



- Excellent barrier against dry particles and certain limited liquid chemical splash (CE Type 5/6)
- Soft and strong multi-layered 54gsm SMS for strong performance
- Made from super breathable SMMS non-woven for effective release of body heat and moisture and reduced heat stress

Product ID	Part Number	Product Name	MOQ	OU
7000109014	4530B2XL	3M™ Protective Coverall 4530, 2XL	20	Each
7000109015	4530B3XL	3M™ Protective Coverall 4530, 3XL	20	Each
7000109016	45304XL	3M™ Protective Coverall 4530, 4XL	20	Each
7000109012	4530BL	3M™ Protective Coverall 4530, L	20	Each
7000109011	4530BM	3M™ Protective Coverall 4530, M	20	Each
7100214328	4530BS	3M™ Protective Coverall 4530, S	20	Each
7000109013	4530BXL	3M™ Protective Coverall 4530, XL	20	Each

Apparel & Workwear

3M™ Protective Coverall 4532+

3M™ Protective Coverall 4532+ has a unique specialist material treatment which offers enhanced liquid hold out with added oil and alcohol repellency. Certified to Type 5 for hazardous particles and Type 6 for limited chemical splash it offers the soft super breathable comfort of an SSMMS with the improved liquid performance normally associated with a laminate.



- Unique liquid repellency with oil and alcohol resistance material treatment
- Soft and strong multi-layered 52gsm SSMMS for strong performance
- Made from super breathable SSMMS non-woven for effective release of body heat and moisture and reduced heat stress

Product ID	Part Number	Product Name	MOQ	OU
7100016008	4532B2XL	3M™ Protective Coverall 4532+, Blue, 2XL	20	Each
7100015994	4532BL	3M™ Protective Coverall 4532+, Blue, L	20	Each
7100015993	4532BM	3M™ Protective Coverall 4532+, Blue, M	20	Each
7100015922	4532BXL	3M™ Protective Coverall 4532+, Blue, XL	20	Each
7100015991	4532W2XL	3M™ Protective Coverall 4532+, Cool White, 2XL	20	Each
7100015978	4532W3XL	3M™ Protective Coverall 4532+, Cool White, 3XL	20	Each
7100016012	4532WL	3M™ Protective Coverall 4532+, Cool White, L	20	Each
7100015949	4532WM	3M™ Protective Coverall 4532+, Cool White, M	20	Each
7100015923	4532WXL	3M™ Protective Coverall 4532+, Cool White, XL	20	Each

3M™ Protective Coverall 4535

3M™ Protective Coverall 4535 provides a superb balance of comfort and protection. The front is made from a soft non-woven robust 60gsm material, with a microporous laminate for enhanced splash protection, combined with a SMMMS back panel for increased breathability. The 3M Protective Coverall 4535 acts as a barrier to limited liquid splashes and hazardous particles.



- Type 5/6 Coverall made from extremely soft, lightweight, yet durable fabric which provides a good barrier to hazardous particles and limited liquid splash
- Special breathable panel hood design combined with large breathable back panels reduce the risk of heat stress in hot environments
- 2-way zip and storm flap with elasticated apertures reduces the risk of skin exposure

Product ID	Part Number	Product Name	MOQ	OU
7100216850	4535W3XL	3M™ Protective Coverall 4535, 3XL	20	Each
7100216888	45354XL	3M™ Protective Coverall 4535, 4XL	20	Each
7100216889	4535W2XL	3M™ Protective Coverall, 4535-2XL	20	Each
7100217010	4535WL	3M™ Protective Coverall, 4535-L	20	Each
7100217011	4535WM	3M™ Protective Coverall, 4535-M	20	Each
7100217012	4535S	3M™ Protective Coverall, 4535-S	20	Each
7100216848	4535WXL	3M™ Protective Coverall, 4535-XL	20	Each

Apparel & Workwear

Focus

3M™ Protective Coverall 4540+

3M™ Protective Coverall 4540+ is made from a laminated premium bicomponent non-woven and features a breathable SMMMS triangular back panel for improved comfort. This soft and lightweight coverall provides an excellent barrier to hazardous particles and limited liquid splashes.



- Excellent barrier against dry particles and certain liquid chemical splash (CE Type 5/6)
- Soft and light, ultra low-linting laminated microporous material that drapes and hangs well over the body facilitating ease of movement
- 3 panel hood, 2-way zip and storm flap with sealable tape with elasticated back and ankles to reduce the risk of skin exposure

Product ID	Part Number	Product Name	MOQ	OU
7100036529	4540W2XL	3M™ Protective Coverall 4540+, 2XL	20	Each
7100040416	4540WL	3M™ Protective Coverall 4540+, L	20	Each
7100040087	4540WM	3M™ Protective Coverall 4540+, M	20	Each
7100040086	4540WXL	3M™ Protective Coverall 4540+, XL	20	Each

Focus

3M™ Protective Coverall 4545

3M™ Protective Coverall 4545 is made with a sophisticated bicomponent non-woven which offers high tensile strength and is covered with an ultra-low linting microporous laminate to provide an excellent barrier to hazardous splash, infective agents and particles.



- Designed to be comfortable but highly protective to CE Category III, Type 5/6 hazardous dusts and limited liquid splashes
- Soft and light, ultra low-linting laminated microporous material that drapes and hangs well over the body facilitating ease of movement
- 3 panel hood, 2-way zip and storm flap with sealable tape with elasticated back and ankles to reduce the risk of skin exposure

Product ID	Part Number	Product Name	MOQ	OU
7100198132	4545W2XL	3M™ Protective Coverall 4545, 2XL	20	Each
7100196882	4545W3XL	3M™ Protective Coverall 4545, 3XL	20	Each
7100198130	4545W4XL	3M™ Protective Coverall 4545, 4XL	20	Each
7100198241	4545WL	3M™ Protective Coverall 4545, L	20	Each
7100198129	4545WM	3M™ Protective Coverall 4545, M	20	Each
7100198128	4545WS	3M™ Protective Coverall 4545, S	20	Each
7100198131	4545WXL	3M™ Protective Coverall 4545, XL	20	Each

Apparel & Workwear

3M™ Protective Coverall 4570

3M™ Protective Coverall 4570 is made of a strong 92gsm non-microporous PE laminate and features a double front closing system and large zip pull for easy wear. This coverall provides an excellent barrier to liquid splashes and jet sprays to Type 3 and hazardous particles to Til class 2 EN 1073-2.

- High performance chemical protective suit, certified to PPE Directive Category III, Type 3/4/5/6 levels of protection, making it suitable to protect against a range of chemicals jet sprays
- Made of a 92gsm laminated nonwoven with chemically protective co-extruded taped seams
- Integrated double stormflap system with large ring pulls for easy taking on and off with gloves



Product ID	Part Number	Product Name	MOQ	OU
7000089691	4570G2XL	3M™ Protective Coverall 4570, 2XL	12	Each
7000089692	4570G3XL	3M™ Protective Coverall 4570, 3XL	12	Each
7000089693	4570G4XL	3M™ Protective Coverall 4570, 4XL	12	Each
7000089689	4570GL	3M™ Protective Coverall 4570, L	12	Each
7000089688	4570GM	3M™ Protective Coverall 4570, M	12	Each
7000089690	4570GXL	3M™ Protective Coverall 4570, XL	12	Each

3M™ Paintshop Coverall 50198

3M™ Paintshop Coverall 50198 is CE Certified Category III to Type 5/6 standards. It is certified to EN 119 to reduce the build up of static charge. Made from a super low-linting robust laminate on the front, it offers a breathable SMMS triangle in the back to offer the optimum balance between protection and comfort.

- Excellent barrier against dry particles and certain liquid chemical splash (CE Type 5/6)
- Anti-static coating EN 1149-5 reduces static discharge and the risk of sparks
- EN 1073-2 nuclear particulate hold out



Product ID	Part Number	Product Name	MOQ	OU
7000085107	50198XXL	3M™ Paintshop Coverall 50198, 2XL	25	Each
7000085110	50198L	3M™ Paintshop Coverall 50198, L	25	Each
7000085109	50198M	3M™ Paintshop Coverall 50198, M	25	Each
7000085108	50198XL	3M™ Paintshop Coverall 50198, XL	25	Each

3M™ Reusable Paintshop Coverall 50425

The 3M™ Reusable Coverall 50425 provides user and garment protection in a wide variety of environments and situations. Extremely comfortable, it is made from a lightweight, breathable polyester.

- Reusable coverall for general workshop tasks
- Washable
- Low-linting



Product ID	Part Number	Product Name	MOQ	OU
7000034321	50425XXL	3M™ Reusable Coverall 50425, 2XL	10	Each
7000034319	50425L	3M™ Reusable Coverall 50425, L	10	Each
7000034318	50425M	3M™ Reusable Coverall 50425, M	10	Each
7000034320	50425XL	3M™ Reusable Coverall 50425, XL	10	Each

Apparel & Workwear

Lab Coats

3M™ Disposable Lab Coat 4440

3M™ Lab Coat 4440 offers a general barrier to non-hazardous substances and liquid splashes, ideal for light duty applications. The lab coat is made of the same laminated material as the Type 5/6 3M™ Protective Coverall 4535.



- Category 1 Lab coat made from lightweight and breathable material, ideal for light duty applications
- Anti-static treated
- Front zip fastener

Product ID	Part Number	Product Name	MOQ	OU
7000089712	4440Z2XL	3M™ Lab Coat 4440, 2XL	50	Each
7000089713	4440Z3XL	3M™ Lab Coat 4440, 3XL	50	Each
7000089714	4440Z4XL	3M™ Lab Coat 4440, 4XL	50	Each
7000089710	4440ZL	3M™ Lab Coat 4440, L	50	Each
7000089709	4440ZM	3M™ Lab Coat 4440, M	50	Each
7000089708	4440ZS	3M™ Lab Coat 4440, S	50	Each
7000089711	4440ZXL	3M™ Lab Coat 4440, XL	50	Each

3M™ Visitors Coat 4400

3M™ Visitors Coat 4400 is made of soft, breathable polypropylene and is ideal for hygiene applications.



- Visitors coat made from lightweight and breathable material, ideal for hygiene applications
- Anti-static treated
- Front zip fastener

Product ID	Part Number	Product Name	MOQ	OU
7000089697	4400W2XL	3M™ Visitor Coat 4400, 2XL	50	Each
7000034777	4400WL	3M™ Visitor Coat 4400, L	50	Each
7000089695	4400WM	3M™ Visitor Coat 4400, M	50	Each
7000089696	4400WXL	3M™ Visitor Coat 4400, XL	50	Each

Apparel & Workwear

Protective Apparel Accessories

3M™ Disposable Protective Overboot Covers 450 Series

Product ID	Part Number	Product Name	MOQ	OU
7000088638	450BOOT	3M™ Disposable Protective Overboot Cover 450 Series, Universal Size	100	Pair

3M™ Disposable Protective Overboot Covers 440 Series

Product ID	Part Number	Product Name	MOQ	OU
7000089719	440	3M™ Disposable Protective Overboot Cover 440 Series, Universal Size	200	Each

3M™ Disposable Protective Overshoe Covers 402 Series

Product ID	Part Number	Product Name	MOQ	OU
7000089721	402	3M™ Disposable Protective Overshoe Cover 402 Series, Slip Resistant, Universal Size	300	Each

3M™ Disposable Protective Oversleeves 444 Series

Product ID	Part Number	Product Name	MOQ	OU
7000089717	444SL	3M™ Disposable Protective Oversleeve 444 Series, Universal Size	300	Each

3M™ Disposable Protective Overhood 446 Series

Product ID	Part Number	Product Name	MOQ	OU
7000089715	446HOOD	3M™ Disposable Protective Overhood 446 Series, White, Standard Size	300	Each

Product Index

Product ID	Page
7000000142	44
7000000144	44
7000000145	44
7000000147	45
7000000149	45
7000000151	45
7000000156	50
7000000158	49
7000000159	49
7000000182	160
7000000183	161
7000000206	161
7000000217	150
7000000218	150
7000000219	150
7000000221	157
7000000223	161
7000000225	160
7000000226	160
7000000227	160
7000000230	162
7000000236	164
7000001897	22
7000001898	22
7000001945	23
7000002042	22
7000002387	81
7000002409	80
7000006980	11
7000009698	114
7000009701	114
7000021315	20
7000027992	45
7000028010	159
7000028023	164
7000028033	164
7000028043	158
7000028044	157
7000028045	165
7000028062	160
7000028067	159
7000028072	165
7000028074	158
7000028075	158
7000029587	22
7000029735	20
7000032083	20
7000032466	137
7000032480	140
7000032483	140
7000032493	138
7000032498	142
7000032501	143
7000034318	172
7000034319	172
7000034320	172
7000034321	172
7000034734	11

Product ID	Page
7000034738	12
7000034739	12
7000034740	12
7000034746	20
7000034747	20
7000034749	20
7000034750	20
7000034751	20
7000034761	169
7000034762	169
7000034763	169
7000034764	169
7000034777	173
7000037673	20
7000037674	20
7000037675	20
7000038198	68
7000038199	69
7000038200	69
7000038202	68
7000038203	68
7000038205	75
7000038208	76
7000038210	76
7000038211	76
7000038212	76
7000038214	77
7000038216	116
7000039616	75
7000039617	75
7000039618	75
7000039619	76
7000039620	76
7000039621	76
7000039622	76
7000039623	76
7000039624	76
7000039648	95
7000039650	95
7000039713	114
7000039714	114
7000039715	114
7000039716	114
7000039717	114
7000039718	114
7000039719	114
7000039720	114
7000039721	114
7000039722	114
7000040037	95
7000042672	42
7000042673	52
7000042674	52
7000042675	47
7000042676	51
7000042677	51
7000042678	51
7000042683	50

Product ID	Page
7000042684	51
7000042685	51
7000042907	49
7000042917	50
7000043086	136
7000044238	47
7000044241	52
7000044242	51
7000044300	44
7000044301	44
7000044302	44
7000044317	48
7000044338	153
7000044371	162
7000044405	47
7000044451	157
7000044482	150
7000044487	165
7000044488	165
7000044502	164
7000044521	150
7000044527	159
7000044531	164
7000044532	150
7000044560	151
7000044564	155
7000044572	164
7000044615	154
7000044619	155
7000052348	20
7000052710	68
7000052711	68
7000052712	67
7000052713	67
7000052714	67
7000052715	69
7000052844	68
7000052845	68
7000052849	71
7000052850	70
7000052879	79
7000052882	80
7000052883	81
7000059880	49
7000059883	20
7000061553	14
7000061555	14
7000061868	143
7000061924	140
7000062428	142
7000062429	142
7000062781	141
7000062913	139
7000062914	141
7000085107	172
7000085108	172
7000085109	172
7000085110	172

Product ID	Page
7000087291	28
7000088331	52
7000088638	174
7000088730	10
7000088787	12
7000088835	11
7000088836	11
7000089105	20
7000089106	20
7000089404	72
7000089405	72
7000089406	71
7000089416	120
7000089590	168
7000089591	168
7000089592	168
7000089593	168
7000089594	168
7000089595	168
7000089596	168
7000089618	168
7000089619	168
7000089620	168
7000089621	168
7000089622	168
7000089623	168
7000089632	168
7000089633	168
7000089634	168
7000089635	168
7000089636	168
7000089642	169
7000089643	169
7000089644	169
7000089688	172
7000089689	172
7000089690	172
7000089691	172
7000089692	172
7000089693	172
7000089695	173
7000089696	173
7000089697	173
7000089708	173
7000089709	173
7000089710	173
7000089711	173
7000089712	173
7000089713	173
7000089714	173
7000089715	174
7000089717	174
7000089719	174
7000089721	174
7000095022	143
7000103721	69
7000103727	69
7000103729	72

Product Index

Product ID	Page
7000103730	72
7000103732	67
7000103735	69
7000103737	75
7000103745	69
7000103747	68
7000103748	68
7000103757	70
7000103777	68
7000103787	77
7000103788	119
7000103790	116
7000103792	119
7000103918	51
7000103964	49
7000103967	50
7000103970	48
7000103971	47
7000103973	47
7000103975	47
7000103979	51
7000103980	51
7000103987	73
7000103988	73
7000103989	73
7000103990	73
7000103991	74
7000103992	74
7000103993	74
7000103994	74
7000103995	75
7000103996	75
7000104037	43
7000104045	78
7000104046	78
7000104047	78
7000104048	78
7000104049	78
7000104061	53
7000104176	14
7000104177	14
7000104178	14
7000104208	115
7000104209	115
7000104210	115
7000104211	115
7000104212	115
7000104213	115
7000107763	76
7000107973	76
7000108016	78
7000108029	122
7000108030	122
7000108175	121
7000108288	114
7000108289	114
7000108296	114
7000108298	114

Product ID	Page
7000108315	114
7000108316	114
7000108376	93
7000108492	87
7000108538	93
7000108540	90
7000108541	90
7000108542	90
7000108590	28
7000109011	169
7000109012	169
7000109013	169
7000109014	169
7000109015	169
7000109016	169
7000127268	94
7000144498	42
7000144499	49
7000144501	47
7000144502	47
7000144503	47
7000144517	164
7000144522	162
7000144525	160
7000144540	159
7000144541	159
7000144936	122
7000146845	15
7000146847	15
7000146849	15
7010043778	165
7010044372	95
7010528331	143
7100001460	165
7100001829	50
7100001960	114
7100002023	114
7100003010	11
7100003083	162
7100004634	23
7100004635	22
7100004636	23
7100005643	47
7100005806	51
7100006000	20
7100006209	137
7100006955	49
7100006958	47
7100007089	47
7100010410	141
7100010431	140
7100010682	137
7100011287	45
7100011652	150
7100011654	164
7100014390	142
7100015050	20
7100015051	18

Product ID	Page
7100015052	18
7100015922	170
7100015923	170
7100015949	170
7100015974	18
7100015978	170
7100015991	170
7100015993	170
7100015994	170
7100016008	170
7100016012	170
7100016690	161
7100016691	161
7100016704	120
7100016860	161
7100018809	36
7100018861	36
7100018994	15
7100018995	15
7100020282	47
7100020699	15
7100020971	39
7100020995	39
7100020996	39
7100020997	39
7100020998	39
7100020999	39
7100021247	48
7100021248	48
7100021251	48
7100021252	48
7100021255	49
7100021336	48
7100024108	53
7100029146	116
7100029680	119
7100031606	165
7100032397	157
7100032898	156
7100034169	81
7100035841	51
7100035843	48
7100035845	48
7100035846	50
7100036529	171
7100040086	171
7100040087	171
7100040416	171
7100048964	169
7100048967	169
7100048969	169
7100050720	27
7100052193	20
7100052199	169
7100053532	37
7100054792	155
7100055314	47
7100055548	150

Product ID	Page
7100057145	11
7100062125	79
7100062126	81
7100062127	81
7100062128	81
7100063118	78
7100063882	50
7100063883	50
7100063886	52
7100063895	52
7100063944	50
7100064141	53
7100064142	51
7100064281	95
7100064410	79
7100064963	72
7100066103	27
7100066104	27
7100066371	86
7100066387	86
7100066388	86
7100067410	95
7100069524	49
7100069736	80
7100074090	87
7100074368	140
7100075338	95
7100075380	95
7100075611	95
7100077171	115
7100077179	115
7100077208	115
7100077212	115
7100077280	115
7100078880	130
7100078881	134
7100078882	134
7100078883	134
7100078986	130
7100078987	130
7100078988	130
7100078989	130
7100079870	45
7100079871	45
7100079872	45
7100079873	46
7100079874	46
7100080184	134
7100080185	134
7100080186	134
7100080187	134
7100080220	161
7100080221	157
7100080223	163
7100080224	162
7100080227	160
7100080228	160
7100080231	164

Product Index

Product ID	Page
7100080248	159
7100080252	48
7100080253	163
7100080258	134
7100081292	143
7100081293	142
7100081542	11
7100081543	11
7100082483	122
7100088423	90
7100088424	90
7100088455	90
7100088456	90
7100089368	92
7100089440	92
7100089592	71
7100090450	160
7100090451	164
7100091323	11
7100092252	161
7100092586	122
7100092588	122
7100092589	122
7100095525	73
7100095526	73
7100095550	75
7100095551	74
7100095553	74
7100096305	116
7100098846	35
7100098897	91
7100098898	91
7100098908	35
7100099097	94
7100099577	48
7100099844	93
7100099845	93
7100099853	49
7100099854	49
7100099881	93
7100099883	93
7100099908	49
7100099909	51
7100100079	162
7100100262	72
7100100263	69
7100100637	69
7100100638	69
7100101091	11
7100101874	78
7100102568	142
7100103087	86
7100104310	20
7100104312	20
7100104317	20
7100104327	20
7100106682	162
7100106703	93

Product ID	Page
7100106867	93
7100108831	161
7100111802	68
7100112010	129
7100112102	95
7100112180	129
7100112333	155
7100112335	151
7100112650	162
7100112712	133
7100112713	133
7100112715	133
7100112716	133
7100112717	133
7100112718	133
7100112721	133
7100112724	133
7100112725	142
7100113020	80
7100113098	13
7100113104	27
7100113964	94
7100114612	131
7100114613	131
7100114634	157
7100114948	131
7100116824	151
7100122439	78
7100123139	73
7100123157	73
7100123159	75
7100123160	74
7100123162	74
7100134313	10
7100134314	10
7100134761	133
7100135289	48
7100135812	13
7100137832	52
7100137850	53
7100137903	53
7100137904	53
7100137905	53
7100138120	10
7100138357	10
7100144401	161
7100146291	140
7100146292	140
7100148026	130
7100148052	130
7100148072	130
7100148073	130
7100148074	130
7100148075	130
7100148081	130
7100148082	130
7100148985	121
7100150921	51

Product ID	Page
7100150925	47
7100153224	19
7100153226	19
7100153231	19
7100153235	19
7100153236	19
7100153423	91
7100153479	91
7100153481	91
7100161510	164
7100166688	152
7100166689	152
7100166692	152
7100166696	153
7100166697	153
7100166698	153
7100166702	152
7100166705	152
7100166706	152
7100166718	151
7100166721	151
7100166722	150
7100166723	154
7100166725	151
7100167200	165
7100167238	164
7100167239	162
7100167240	162
7100167242	158
7100167292	164
7100167333	164
7100167334	162
7100167362	163
7100167881	160
7100169180	38
7100169234	163
7100171979	14
7100171980	14
7100172003	14
7100172004	14
7100172005	14
7100172006	14
7100173404	163
7100173966	165
7100175093	112
7100175094	112
7100175095	112
7100175096	112
7100175097	112
7100175098	112
7100175099	112
7100175100	112
7100175101	112
7100175511	112
7100175512	112
7100175533	112
7100175534	112
7100175535	112

Product ID	Page
7100175536	112
7100175537	112
7100175538	113
7100175539	113
7100175545	113
7100175546	113
7100175547	113
7100175553	113
7100175587	121
7100175589	121
7100175590	121
7100175591	113
7100175592	113
7100175593	113
7100175594	113
7100175595	113
7100175596	113
7100175597	113
7100175598	113
7100175599	113
7100175600	113
7100175601	113
7100175602	113
7100175603	113
7100175604	113
7100175605	113
7100175606	113
7100176840	119
7100176968	119
7100176972	119
7100180680	122
7100180681	121
7100180682	121
7100180703	121
7100181383	162
7100181452	164
7100181558	23
7100184498	27
7100185109	131
7100185183	140
7100185268	131
7100185269	131
7100185278	131
7100185279	129
7100185289	131
7100185290	140
7100185291	131
7100185292	131
7100185618	156
7100185762	96
7100185795	96
7100185797	96
7100185799	96
7100185800	96
7100185817	162
7100185829	163
7100185830	163
7100185831	164

Product Index

Product ID	Page
7100185832	162
7100185833	162
7100185834	165
7100185839	162
7100185841	163
7100185845	162
7100185847	162
7100185852	156
7100186963	162
7100188168	27
7100189372	49
7100189597	49
7100189979	162
7100190170	161
7100190171	163
7100191443	96
7100191444	96
7100191825	163
7100193170	96
7100193227	96
7100193228	96
7100193229	96
7100194360	86
7100195906	89
7100195960	89
7100195961	89
7100195976	89
7100196045	89
7100196882	171
7100197270	19
7100197283	19
7100197284	19
7100197285	19
7100197286	19
7100197481	19
7100197556	96
7100197565	96
7100197566	96
7100197568	96
7100197572	96
7100197718	96
7100197719	96
7100198128	171
7100198129	171
7100198130	171
7100198131	171
7100198132	171
7100198241	171
7100201938	91
7100202350	160
7100202360	164
7100202361	164
7100202396	164
7100203041	165
7100203042	165
7100203048	163
7100203150	93
7100203297	92

Product ID	Page
7100203298	92
7100203299	92
7100203302	92
7100203635	92
7100203636	92
7100203637	92
7100203638	93
7100203639	92
7100204034	156
7100204388	91
7100204418	91
7100205297	89
7100205299	89
7100205302	89
7100205304	89
7100205305	161
7100205306	149
7100205307	164
7100205729	93
7100206559	118
7100206560	118
7100206561	118
7100206562	118
7100206581	118
7100206582	118
7100206586	118
7100206593	118
7100206891	19
7100206892	19
7100207096	118
7100207323	96
7100208068	118
7100208382	135
7100208751	135
7100208793	135
7100208815	135
7100208817	135
7100208818	135
7100208819	135
7100208820	135
7100208825	135
7100208826	135
7100209252	138
7100209340	138
7100209384	138
7100209413	138
7100209416	138
7100209425	138
7100209426	138
7100209427	138
7100209428	138
7100209430	138
7100209600	135
7100212096	119
7100214328	169
7100216191	139
7100216192	139
7100216261	136

Product ID	Page
7100216507	136
7100216514	139
7100216582	139
7100216595	136
7100216617	139
7100216621	136
7100216848	170
7100216850	170
7100216888	170
7100216889	170
7100217010	170
7100217011	170
7100217012	170
7100217397	160
7100217750	117
7100217836	117
7100217837	117
7100217838	117
7100217844	117
7100217847	117
7100217850	117
7100217852	117
7100217854	117
7100217856	117
7100217857	117
7100217858	117
7100217859	117
7100217860	117
7100217861	117
7100217862	117
7100217863	117
7100217864	117
7100217865	117
7100217866	117
7100217867	117
7100217868	117
7100217873	117
7100217874	117
7100217875	117
7100217876	117
7100217877	117
7100217946	138
7100218079	138
7100218150	135
7100218151	136
7100218153	135
7100218163	136
7100218306	136
7100218783	49
7100219827	96
7100220423	135
7100220865	96
7100222333	160
7100222674	47
7100222675	47
7100224037	96
7100224039	96
7100224833	122

Product ID	Page
7100229259	90
7100229277	90
7100229734	122
7100232846	117
7100232855	121
7100233732	39
7100233763	39
7100233764	36
7100233765	36
7100233766	39
7100233767	36
7100236681	28
7100236811	47
7100236812	50
7100236816	28
7100236821	28
7100236838	47
7100236843	47
7100236853	49
7100236854	49
7100236885	17
7100236941	17
7100236942	17
7100236989	18
7100237033	18
7100237055	52
7100237883	48
7100237884	49
7100240278	94
7100240431	95
7100240432	94
7100240624	94
7100240628	20
7100241118	122
7100243141	143
7100243142	132
7100243934	132
7100243935	142
7100243943	142
7100243963	132
7100243964	132
7100243969	129
7100243970	134
7100243971	132
7100243977	132
7100243978	132
7100243979	132
7100243980	132
7100243987	139
7100243988	137
7100243989	132
7100243995	132
7100244022	132
7100244045	132
7100244046	129
7100244047	129
7100244048	129
7100244049	134

Product Index

Product ID	Page
7100244050	137
7100244060	129
7100244061	129
7100244062	132
7100244063	134
7100244064	129
7100244065	137
7100244066	134
7100244069	137
7100244145	142
7100244200	139
7100244201	132
7100245437	95
7100246136	123
7100246983	94
7100246985	94
7100246986	94
7100247026	94
7100247316	122
7100249088	56
7100249097	56
7100249356	56
7100251921	57
7100253622	94
7100254233	28
7100256071	43
7100256086	165
7100256090	162
7100256092	165
7100256131	154
7100256282	88
7100256283	88
7100256371	160
7100256562	149
7100256658	88
7100256659	163
7100256707	122
7100257811	88
7100257812	149
7100257837	158
7100257936	43
7100257937	43
7100257943	154
7100257944	149
7100257945	149
7100257946	161
7100258110	154
7100258326	154
7100258327	154
7100258328	154
7100258667	43
7100258668	43
7100258808	38
7100258809	38
7100258810	38
7100258909	10
7100258911	10
7100258912	10

Product ID	Page
7100258913	10
7100259002	158
7100259107	152
7100259576	37
7100260628	21
7100260645	21
7100260718	50
7100260719	50
7100262626	17
7100262627	17
7100262628	17
7100264002	94
7100264003	94
7100264326	95
7100264725	21
7100264730	47
7100264834	21
7100264835	21
7100264836	21
7100264837	21
7100264838	21
7100264839	21
7100264840	21
7100264841	21
7100265015	21
7100265016	41
7100265024	16
7100265025	49
7100265026	41
7100265028	42
7100265033	41
7100265034	42
7100265035	42
7100265036	42
7100265044	16
7100265048	42
7100265049	42
7100265050	52
7100265060	42
7100265070	16
7100265071	16
7100265072	16
7100265073	16
7100265074	18
7100265075	18
7100265192	47
7100265213	49
7100265218	47
7100265222	16
7100265223	16
7100265226	46
7100265228	16
7100265229	16
7100265235	16
7100265236	18
7100265237	21
7100265238	42
7100265239	21

Product ID	Page
7100265523	21
7100265524	16
7100265593	23
7100266028	21
7100266031	21
7100266045	52
7100266123	36
7100277744	158
7100277745	158
7100278098	28
7100279645	159
7100279646	159
7100282441	163
7100288125	158
7100288286	70
7100288287	70
7100290789	40
7100293324	40
7100293325	40
7100293327	40
7100293328	40
7100293329	40
7100293330	40
7100293333	50
7100295035	40
7100299964	40
7100300071	48

3M TERMS OF SALE

1. Application

1.1 These conditions apply to all contracts between 3M and the Buyer referred to in the order and override all conditions stipulated by the Buyer (even if submitted in a later document); any other agreements between the parties relating to the subject matter of this order are terminated (except an agreement into which these conditions are incorporated).

1.2 No variation of these conditions is permitted unless agreed in writing by an authorised officer of 3M. Lead times for delivery shall be as set out in 3M's quotation or proposal or if none is specified 3M's standard lead times shall apply.

2. Description

2.1 The description of the goods or services to be supplied by 3M shall be as set out in 3M's quotation, as modified by any written specification supplied by 3M, or otherwise agreed in writing by an authorised officer of 3M.

2.2 3M may amend any specification if required by any applicable statute or regulation, or by notification to the Buyer following which the applicable specification shall be that as so amended.

2.3 All samples, drawings, images, descriptive matter and advertising materials produced by 3M and any descriptions or illustrations contained in 3M's literature, digital media or emails are produced solely to describe the goods or services approximately and do not form part of the agreement into which these conditions are incorporated.

3. Price

3.1 Save where expressly stated otherwise by 3M the price to be paid for the goods or the services will be 3M's price at the date when the goods are dispatched or the services are provided.

3.2 The price of goods includes the cost of 3M's standard packaging and standard delivery within the UK and Ireland by 3M's normal transportation; the price does not include VAT. Where the price is based on pallets and/or packaging being returned to 3M, then failure to do so by the Buyer will result in a surcharge at 3M's standard rate.

4. Payment

4.1 Unless otherwise specified on 3M's invoice, payment for the goods or services must be received in cleared funds no later than thirty days of the date of invoice.

4.2 3M reserves the right to charge interest on overdue sums at the rate of 4% per annum above the Base Rate for the time being of Lloyds Bank plc calculated on a daily basis from the due date of payment in Clause 4.1 until the date upon which payment is made.

4.3 3M may at any time require the Buyer to make payment in advance of delivery or require security for payment.

4.4 If the Buyer fails to make payment by the due date or when required, 3M may (without prejudice to any other remedy which it may have) cancel this contract and/or any other contract between the Buyer and 3M and/or suspend delivery under this or any other contract until payment is made.

4.5 The Buyer will have no statutory or other right of set off.

5. Delivery

5.1 Delivery dates are approximate only and 3M shall not be responsible for any loss or damage arising from any delay in delivering all or part of any goods ordered or delay in the provision of any services.

5.2 Without prejudice to Clause 5.1, 3M will not be liable for any delay in delivery or non-delivery of goods or services or any other breach of these conditions caused by any circumstances beyond 3M's reasonable control including without limitation, any Act of God, explosion, fire, flood, war, hostilities, accident, delay in delivery or non-delivery by 3M's suppliers, breakdowns or accidents to machinery, labour strike or dispute, order or decree of any court or action of any governmental authority, or any other causes or any circumstances beyond 3M's control; on the occurrence of any of the above events 3M reserves the right to cancel or suspend the whole or part of any delivery or service provision.

5.3 In the case of any order for goods of a type or description not normally held in stock by 3M, and therefore specially made ordered or imported by 3M to meet such order, the Buyer will accept goods 10% more or 10% less than ordered, the total price of the order being correspondingly adjusted.

5.4 Where 3M references the international rules for the interpretation of trade terms prepared by the International Chamber of Commerce (Incoterms) in the relevant contract or proposal, such terms shall apply to delivery save that where they conflict with these conditions, these conditions shall prevail. For deliveries outside of the UK mainland the term of sale shall be FCA 3M UK warehouse unless otherwise mutually agreed in writing by 3M and Buyer.

5.5 Goods supplied may be subject to export controls. The Buyer should refer to 3M's packing list accompanying the goods for any export control status.

6. Risk

Risk in all goods supplied to the Buyer will pass to the Buyer on delivery. Unloading shall be at the Buyer's risk.

7. Inspection

7.1 If the goods or any of them are damaged or lost while in the custody of a carrier, 3M will (at its option) either replace such goods or refund to the Buyer the price paid for them, but 3M's liability in connection with any such goods will not exceed the cost of replacement or the price paid by the Buyer.

7.2 3M will not be under any liability under 7.1 above unless the following conditions are strictly complied with:

7.2:1 In the event of non-delivery of a whole consignment of goods the Buyer must inform 3M in writing within ten days of the date of the invoice.

7.2:2 In the case of damage to goods or loss of part of a consignment, the consignment must be inspected in the presence of the carrier. If any goods are damaged or lost the consignment note must be endorsed accordingly and the Buyer must notify 3M within forty-eight hours of delivery, such notification to be confirmed in writing within the following five days. 3M shall have no further liability for such damage or loss.

8. Liabilities and Warranties

8.1 Nothing in this clause will be deemed to exclude or restrict 3M's liability for (i) death or personal injury resulting from its negligence; (ii) fraud or fraudulent misrepresentation; (iii) breach of any obligation as to title implied by section 12 of the Sale of Goods Act 1979; and/or (iv) any act, omission or matter, liability for which may not be legally excluded or limited.

8.2 If any goods supplied or any services supplied or provided by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same (or the defective part) or refund to the Buyer the price of the goods or services (or a pro-rated amount of the price if not all the goods are defective).

8.3 The Buyer will determine the suitability of the goods for its intended use and will not rely upon any representations made by or on behalf of 3M.

8.4 3M's liability under these conditions shall never exceed the cost of replacement or the price paid by the Buyer for the goods or services.

8.5 3M will not be liable for any consequential or indirect loss or damage (whether for loss of profit, loss of business, depletion of goodwill or otherwise) costs, expenses or other claims for consequential compensation whatsoever suffered by the Buyer whether this loss or damage arises from a breach of duty, in contract or in tort or in any other way (including loss or damage arising from 3M's negligence).

8.6 The Buyer shall at all times comply with standards of business conduct that are consistent with 3M's Code of Conduct located at www.3m.com/businessconduct and all applicable laws, statutes, regulations and codes relating to anti-bribery including but not limited to the US Foreign Corrupt Practices Act and the UK Bribery Act 2010 ("Bribery Laws") and shall maintain in place its own policies and adequate procedures, to ensure full compliance with the Bribery Laws. The Buyer shall promptly report to 3M any request or demand for any undue financial or other advantage of any kind received by or offered to the Buyer in connection with 3M's goods or services.

8.7 Except as set out in these conditions, all other warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

9. Assignment

9.1 3M may assign, or deal in any other manner with, any contract between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts to any third party or agent.

9.2 The Buyer shall not be entitled to assign, or deal in any other manner with, any contracts between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts, without the prior written consent of 3M.

10. Termination

If there is appointed a Receiver, Administrator or Administrative Receiver of the Buyer's property or assets or any part of them, or a court order is made or a resolution is passed for the winding-up of the Buyer (except for the purpose of amalgamation or reconstruction) or if the Buyer commits any act of bankruptcy, or any bankruptcy petition is presented against the Buyer (or any analogous proceedings under the law of any country outside the United Kingdom are commenced), 3M may by notice in writing to the Buyer cancel all orders and contracts between 3M and the Buyer or any part of them remaining unfulfilled.

11. General

11.1 If any provision, or part of a provision, of these conditions is found by any court or administrative body of competent jurisdiction to be invalid, illegal or unenforceable (a "void provision") such invalidity, illegality or unenforceability shall not affect the other provisions of the conditions, which shall remain in full force and effect. If a void provision would be valid, legal and enforceable if some part of it were deleted, that void provision shall apply with such modification as may be necessary to make it valid, legal and enforceable and if it cannot be made valid, legal and enforceable it shall be deemed to be deleted.

11.2 No provision of the conditions shall be enforceable under the Contracts (Rights of Third Parties) Act 1999 by any person who is not a party to the contract between 3M and Buyer.

11.3 A failure to exercise, or delay in exercising a right, power or remedy provided to 3M by these conditions or by law does not constitute a waiver of that, or any other, right, power or remedy and shall not (and nor shall any single or partial exercise of any such right, power or remedy) preclude the further exercise of that, or any other, right, power or remedy.

12. Jurisdiction

12.1 All contracts between 3M and the Buyer where the goods are shipped to or services are provided in the Republic of Ireland shall be governed by and construed in accordance with the Laws of the Republic of Ireland, and the Buyer agrees to submit to the jurisdiction of the Courts of law in the Republic of Ireland in respect of them.

12.2 Except as provided above, all contracts between 3M and the Buyer shall be governed by and construed in accordance with the Laws of England, and the Buyer agrees to submit to the jurisdiction of the Courts of law in England in respect of them.





3M Ireland Limited
The Iveagh Building
The Park 18, Carrickmines,
D18 X015, Ireland
+353-1-2803555
www.3m.ie