

**3M** Science.  
Applied to Life.™



**Safety backed  
by science.**

**3M™ SecureFit™  
Protective Eyewear**

# Performance. Style. Comfort.

## 3M™ SecureFit™ Protective Eyewear

Protecting your vision on the job is important. But it doesn't have to mean sacrificing style or comfort. Get eyewear that performs — and looks good doing it. Featuring a comfortable fit and a sleek profile designed to work with other personal protective equipment, 3M™ SecureFit™ Protective Eyewear helps keep you safe and comfortable on the job.






## The science of comfort.

We collected data on head and face shapes around the world to develop a patented design that self-adjusts to individual head sizes and shapes. This design provides the same level of comfort to individuals across a diverse workforce.

Regardless of head size, from small heads to large heads, our 3M™ SecureFit™ Pressure Diffusion Temple Technology is designed to provide a secure and comfortable fit for an extended period of wear time.



## Designed to perform.



### Curved temples for enhanced security

Our design applies pressure on the less sensitive back of the head instead of the temples, achieving a comfortable fit even during rapid head movement.



### 3M™ Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalization, allowing the temples to flex and self-adjust to the size of the wearer's head.



## The benefits are clear.

Fogged lenses can be frustrating and dangerous. But 3M™ SecureFit™ Protective Eyewear models featuring 3M™ Scotchgard™ Protector Anti-Fog/Anti-Scratch Coating can help workers see clearly for longer, thanks to an active ingredient that bonds the coating to the lens.



**Uncoated**



Microscopic water droplets bead up, forming condensation and fog, which obscure vision.

**3M™ Scotchgard™ Protector  
Anti-Fog/Anti-Scratch Coating**



Reduced contact angle flattens water beads into a thin, transparent film that allows light to pass through.



### 3M™ Scotchgard™ Protector Anti-Fog/Anti-Scratch Coating

- Resists fogging longer than traditional anti-fog coatings through up to 25 washings with water.\*
- Helps provide scratch resistance in tough work environments.
- Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas.



# 3M™ SecureFit™

Family of Protective Eyewear

There's a lot of variety to choose from in the 3M™ SecureFit™ family, all with the comfort, safety and style your workforce demands.

Find the series with the right mix of features and value for you.

100 Series




200 Series



400 Series



500 Series




# 100 Series

Sleek, comfortable eye protection  
at an economical price.



# 100 Series

3M™ SecureFit™ 100 Series Protective Eyewear features a sleek, sporty lens shape and self-adjusting temples, providing a stylish yet comfortable fit for an extended period of time.



Workers can feel confident wearing 3M eye protection that meets the Impact-Rated Protector requirement of the AS/NZS 1337.1:2010 Standard.



# 100 Series



Product ID: **SF101AF-BLK**  
 Lens: **Clear**  
 Frame: **Black**  
 Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF101AS-BLK**  
 Lens: **Clear**  
 Frame: **Black**  
 Coating: **Anti-Scratch**



Product ID: **SF102AF-BLK**  
 Lens: **Grey**  
 Frame: **Black**  
 Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF103AF-BLK**  
 Lens: **Amber**  
 Frame: **Black**  
 Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF107AF-BLK**  
 Lens: **Indoor/Outdoor Grey**  
 Frame: **Black**  
 Coating: **Anti-Fog/Anti-Scratch**

## Available SKUs

3M™ ANTI-FOG COATING						
Product I.D.	3M I.D.	Description	Frame Colour	Lens Colour	Coating Performance	Each/Case
SF101AF-BLK	AT019494601	3M™ SecureFit™ Eyewear SF101AF-BLK, Clear Anti-Fog-Anti-Scratch	Black	Clear	AS/AF	20 EACH / CASE
SF101AS-BLK	AT019494619	3M™ SecureFit™ Eyewear SF101AS-BLK, Clear Anti-Scratch	Black	Clear	AS	20 EACH / CASE
SF102AF-BLK	AT019494627	3M™ SecureFit™ Eyewear SF102AF-BLK Grey Anti-Fog-Anti-Scratch	Black	Grey	AS/AF	20 EACH / CASE
SF103AF-BLK	AT019494635	3M™ SecureFit™ Eyewear SF103AF-BLK, Amber Anti-Fog-Anti-Scratch	Black	Amber	AS/AF	20 EACH / CASE
SF107AF-BLK	AT019494643	3M™ SecureFit™ Eyewear SF107AF-BLK, Indoor Outdoor Grey Anti-Fog-Anti-Scratch	Black	I/O Grey	AS/AF	20 EACH / CASE


# 200 Series

Lightweight comfort at  
an affordable price.



# 200 Series

The right fit changes everything. 3M™ SecureFit™ 200 Series Protective Eyewear features temples that automatically self-adjust to help provide a secure, comfortable fit every time.



# 200 Series



Product ID: **SF201AF-AS**  
Lens: **Clear**  
Frame: **Clear**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF202AF-AS**  
Lens: **Grey**  
Frame: **Grey**  
Coating: **Anti-Fog/Anti-Scratch**

## Available SKUs

3M™ ANTI-FOG COATING						
Product I.D.	3M I.D.	Description	Frame Colour	Lens Colour	Coating Performance	Each/Case
SF201AF-AS	70071676269	SecureFit 200 Clear Anti-Fog Lens	Clear	Clear	AF/AS	20 EACH / CASE
SF202AF-AS	70071695509	SecureFit 200 Grey Anti-Fog Lens	Grey	Grey	AF/AS	20 EACH / CASE




# 400 Series

Enhanced comfort and sleek design available in a variety of contemporary colours.



# 400 Series

Take the next step in comfort with 3M™ SecureFit™ 400 Series Protective Eyewear, featuring 3M™ Pressure Diffusion Temple Technology, a soft one-piece nose bridge, dual-injected temples and a range of options, including lens colours, premium coatings, readers and more.



# 400Series



Product ID: **SF401AF-AS**  
Lens: **Clear**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF402AF-AS**  
Lens: **Grey**  
Frame: **Green/Black**  
Coating: **Anti-Fog/Anti-Scratch**




Product ID: **SF410AS-AS**  
Lens: **Indoor/Outdoor Mirror**  
Frame: **Green/Black**  
Coating: **Anti-Scratch**

## Available SKUs

3M™ ANTI-FOG COATING						
Product I.D.	3M I.D.	Description	Frame Colour	Lens Colour	Coating Performance	Each/Case
SF401AF-AS	70071676368	Secure Fit 400 Clear Anti Fog Lens	Green/Black	Clear	AF/AS	20 EACH / CASE
SF402AF-AS	70071695426	Secure Fit 400 Grey Anti Fog Lens	Green/Black	Grey	AF/AS	20 EACH / CASE
SF410AS-AS	70071695434	Secure fit 400 Indoor/Outdoor Mirror Lens	Green/Black	Indoor, outdoor mirror	AS	20 EACH / CASE

# 500 Series

Contemporary safety glasses featuring a sporty, streamlined lens shape.





## PPE Compatibility

Sporty design with contemporary lens shape and a sleek profile of safety glasses that can combine well with other personal protective equipment.

SecureFit's flat and flexible temple design combines well with 3M™ Protective Earmuffs



The adjustable ratcheting temples of the SecureFit™ 500 Series are designed to help improve the positioning of the eyewear when worn with half-facepiece respirators

# 500 Series

3M™ SecureFit™ 500 Series features a contemporary lens design coupled with adjustable ratchet temples and 3M™ Pressure Diffusion Temple (PDT) technology to help provide a more personalised fit. This sporty eyewear also offers self-adjusting coloured temples, a variety of lens tints and models with Scotchgard™ Protector Anti-Fog Coating.



## Adjustable Ratchet Temples

Multiple position ratchet allows user to adjust lens for facial features and eyeglass position.

Adjustable ratcheting temples are designed to help improve the positioning of eyewear when worn with half-facepiece respirators.

## Slim Standout Style

Contemporary lens shape.

## Molded Nose Bridge

No removeable parts

## Pressure Diffusion Temple Technology

3M's innovative temple design features slotted ribs that provide comfortable pressure equalization.

Temples flex and self-adjust to the size and shape of wearer's head.



## Curved Temples for Enhanced Security

Eyewear design applies pressure on the less sensitive back of the head instead of temples

Helps achieve a comfortable fit, even during rapid head movement



## Polycarbonate Lenses

U6 rated polycarbonate lenses absorb 99.9% of UVA, UVB, and UVC rays between 200 nm and 380 nm.

Workers can feel confident wearing 3M eye protection have been tested and certified to AS/NZS 1337.1:2010 and have a medium impact rating.

## Choose Your Coating

Anti-Fog / Anti-Scratch

3M™ Scotchgard™ Anti-Fog Protector Coating

## Optional removable foam-line gasket




Resists fogging longer than traditional anti-fog coatings through up to 25 washings with water\*

Helps provide scratch resistance in tough work environments

Designed for working in challenging situations, such as hot and humid conditions, indoor/outdoor work, physically demanding tasks and climate-controlled areas

# 500 Series



Product ID: **SF501AF-BLK**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF501SGAF-BLK**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF502SGAF-BLK**  
Lens: **Gray**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF503SGAF-BLK**  
Lens: **Amber**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF507SGAF-BLK**  
Lens: **Indoor/Outdoor Gray**  
Frame: **Black**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF501SGAF-BLK-FM**  
Lens: **Clear**  
Frame: **Black**  
Coating: **Anti-Fog/Anti-Scratch**



Product ID: **SF505SGAF-DGR**  
Lens: **Brown**  
Frame: **Olive Green**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**



Product ID: **SF528SGAF-DGR**  
Lens: **Light Brown**  
Frame: **Olive Green**  
Coating: **Scotchgard™ Anti-Fog/Anti-Scratch**

## Available SKUs

3M™ ANTI-FOG COATING						
Product I.D.	3M I.D.	Description	Frame Colour	Lens Colour	Coating Performance	Each/Case
SF501AF-BLK	AT019494437	3M™ SecureFit™ Eyewear SF501AF-BLK, Clear Anti-Fog/Anti-Scratch	Black	Clear	AF/AS	20 EACH / CASE
SF501SGAF-BLK	AT019494445	3M™ SecureFit™ Eyewear SF501SGAF-BLK, Clear, Scotchgard™ Anti-Fog/Anti-Scratch	Black	Clear	SGAF	20 EACH / CASE
SF501SGAF-BLK-FM	AT019494452	3M™ SecureFit™ Eyewear SF501SGAF-BLK-FM, Clear, Scotchgard™ Anti-Fog/Anti-Scratch, Foam Gasket	Black	Clear	SGAF	20 EACH / CASE
SF502SGAF-BLK	AT019494478	3M™ SecureFit™ Eyewear SF502SGAF-BLK, Grey, Scotchgard™ Anti-Fog/Anti-Scratch	Black	Grey	SGAF	20 EACH / CASE
SF503SGAF-BLK	AT019494494	3M™ SecureFit™ Eyewear SF503SGAF-BLK, Amber, Scotchgard™ Anti-Fog/Anti-Scratch	Black	Amber	SGAF	20 EACH / CASE
SF507SGAF-BLK	AT019494528	3M™ SecureFit™ Eyewear SF507SGAF-BLK, Indoor/Outdoor, Scotchgard™ Anti Fog/Anti-Scratch	Black	Indoor/Outdoor	SGAF	20 EACH / CASE
SF505SGAF-DGR	AT019494502	3M™ SecureFit™ Eyewear SF505SGAF-DGR Olive Green, Brown lens, Scotchgard™ Anti-Fog/Anti-Scratch	Olive Green	Brown	SG/AF	20 EACH / CASE
SF528SGAF-DGR	AT019494569	3M™ SecureFit™ Eyewear SF528SGAF-DGR Olive Green, Light Brown lens, Scotchgard™ Anti-Fog/Anti-Scratch	Olive Green	Light Brown	SG/AF	20 EACH / CASE

# Series Comparison Chart

Features/Options	100 Series	200 Series	400 Series	500 Series
3M™ Pressure Diffusion Temple Technology	X	X	X	X
Anti-Fog/Anti-Scratch Coating	X	X	X	X
3M™ Scotchgard™				X
Rugged Anti-Scratch Coating	X		X	
Soft Nose Bridge			X	
Molded Nose Bridge	X	X		X
Adjustable Ratchet Temples				X
Brow Guard				
Removable Foam Gasket			X	X
Sporty Lens Shape				X
Food Segment		X		
Impact Rated, Medium Impact	X	X	X	X
Certified product AS/NZS1337.1:2010.	X	X	X	X




## Fit testing

Eye injuries can occur even while wearing eye protection if the Protective Eyewear do not fit properly. When fitted properly, eyewear should cover the soft tissue around the eye. Small spectacles on larger heads can leave exposed areas.

Spectacles that are too large for a person can leave gaps. Selecting the proper eye protection for the task and ensuring proper-fitting eyewear can help to reduce worker eye injuries.

3M has developed a step-by-step method to ensure you can find your best-fitting protective eyewear, and can help you to validate properly fitting eyewear.





## A difference you can see and feel.

Eyewear that's lightweight and comfortable — believe it. Contact your 3M sales rep to request trial wear samples of 3M™ SecureFit™ Protective Eyewear and feel the difference the instant you put them on. See for yourself.

▶ **3M Safety Glasses | 3M Australia**

▶ **Scan here to avail your  
“Trial wear Sample”\***



▶ **3M Australia Pty Ltd  
Personal Safety Division  
Bldg A, 1 Rivett Road  
North Ryde NSW 2113**

**TechAssist Helpline: 1800 024 464**

**Customer Service: 1300 363 565**

**Email: [techassist@mmm.com](mailto:techassist@mmm.com)**

**Web: [www.3M.com/au/ppesafety](http://www.3M.com/au/ppesafety)**