

3M™ Thermally Conductive Interface Tapes Selection Guide.

Engineered to provide efficient heat transfer along with adhesion and potentially replacing fasteners, 3M™ Thermally Conductive Interface Tapes are used to bond heat-generating components to heat sinks and cooling devices. Thermal management can help improve device reliability and extend the overall life of electronic devices. Each 3M tape combines high-performance adhesives and thermal conductivity for reliable thermal management. These tapes perform well in applications requiring high adhesion. Acrylic resin can typically operate up to 90°C. These tapes help provide robust thermal management for applications in a variety of market segments, such as automotive, LED lighting, communication infrastructure, and aerospace and defense.

For applications requiring heat distribution in select areas, 3M™ Thermally Conductive Heat Spreading Tape 9876 can be used to help provide heat distribution on the horizontal plane.

3M™ Thermally Conductive Interface Tapes

Product	Colour	Base material type	Product thickness (mm)	Filler type	Liner type	Peel strength @72 hr dwell (kg/in) <small>* ASTM D-3330 at 70°C 3M test method at RT</small>	Thermal conductivity (W/m-K) <small>***3M test method ** ASTM D5470 *ASTM C 1113 ASTM C177</small>	Thermal impedance °C-in ² /W (°C-cm ² /W) <small>3M test method</small>	Dielectric strength (kV/mm) <small>*3M test method ASTM D-149</small>	Volume resistivity (ohm-cm) <small>ASTM D-2577</small>	UL 94 flammability rating
8711-100	White	Filled acrylic polymer	0.1	Ceramic	Polyester dual liner	* >2.0	*0.6	-	26	Not applicable	V-0
8708-025	Yellowish white		0.25		Paper single liner	*Liner side > 3.0 *Non liner side > 1.0					15
8926-02			0.2		Clear polyester single liner	*Liner side: 2.0 *Non liner side: 2.0	**1.5	1.31 (8.49)	*15		
8926-025			0.25					1.35 (8.74)			
8926-05			0.5					1.50 (9.70)			
8805	White		0.125		Silicone-treated polyester dual liner	1.5	0.6	26 (8815)	0.5 (3.2)	5.2 × 10 ¹¹	-
8810			0.25			2.1			0.9 (5.8)	3.9 × 10 ¹¹	
8815			0.375			2.5			1.2 (7.7)	3.8 × 10 ¹¹	
8820			0.5			3			1.5 (9.7)		
9876-10	Pink		Acrylic polymer on Cu layer		0.1	Not applicable	Release coated white paper liner	>2.5	*** > 250 / 0.8 (X-Y / Z axis)	0.3 (1.93)	*29

Tested in accordance with 3M test method or test method otherwise specified. Contact your 3M technical representative for details.

℞ The following technical information and data should be considered representative or typical only and should not be used for specification purposes

℞ Per UL File Number: QMFZ2.E239181

℞ UL flame rating is only valid for the material coated on one side of aluminium plate with minimum 1.0mm thickness and the other side of recognised component (QMTS2) FR-4 laminate at minimum of 0.8mm thickness

For devices that deliver consistent reliability and performance, you need thermal management materials that stand up to a lifetime of heat. At 3M, we can help you find the right solution for your thermal management needs.

Contact us to learn more, or to help us find a custom solution for your application.

Visit:

www.3M.co.uk/TCITapes

www.3M.com.es/TCITapes

www.3MItalia.it/TCITapes

www.3M.fr/TCITapes

www.3M.de/TCITapes

www.3M.com.pl/TCITapes

Have questions? Need technical assistance? We're here to help!
Contact your 3M technical service representative for more information.

Warranty, limited remedy, and disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M United Kingdom PLC
Electronics Materials solution division
3M Centre, Cain Road,
Bracknell
Berkshire RG12 8HT
Tel: 0870 60 800 60

3M Ireland
The Iveagh Building
Carrickmines Park
Carrickmines
Dublin 18

© 3M 2022. 3M is a trademark of 3M Company. All rights reserved.
OMG252748.