

3M™ Mining Lamp Bracket Kit M-940 Technical Specifications

Description

The 3M™ Mining Lamp Bracket Kit M-940 is designed for use on certain 3M™ Versaflo™ M-200 Series, M-300 Series and M-400 Series headgear, when used with an approved air source. 3M has designed the Mining Lamp Bracket M-940 to be compatible with certain cordless and corded adjustable angle mining lamps that utilize a metal retaining clip on the lamp body. The 3M™ Mining Lamp Bracket is designed to allow the lamp retaining clip to slide into the slot on the M-940 bracket. The angle of the 3M™ Mining Lamp Bracket is adjustable allowing for a desired light angle.

Mining Lamps for use with the M-940

3M has evaluated the following mining lamps and found the mounting retaining clip to be compatible with the 3M™ Mining Lamp Bracket:

MANUFACTURER	MODEL (S)
Polaris	NL8005, NL0329
Koehler Bright Star	LI 6000-G Cordless LED Cap Lamp
Optimac	HaloLite H1, HaloLite H2, MiniHalo
TJL	KL6L7M Cap Lamp
Wisdom	4A Cordless Cap Lamp, KL5M
MST Global	TRAK Orb Cordless Lamp, ICCL Model
MineARC	SiriUS Cordless Lamp
Roobuck	RN2T Cordless Lamp

3M has not evaluated all mining lamps available in the market. If intending to use a mining lamp not listed above, please evaluate the security of the mining lamp in the bracket prior to use for acceptability. 3M expects lamps with similar mounting clips to those listed above to be acceptable for use with the M-940 mining lamp bracket, however security of the lamps should always be evaluated prior to use in your environment.

The 3M Mining Lamp Bracket Kit M-940 is not designed to be used with mining lamps that require special hardware/fasteners or adhesives to mount the lamp to the headgear. The slot on the mining lamp bracket is approximately 23mm wide. If you have any questions or concerns regarding a mining lamp with the 3M Mining Lamp Bracket Kit, please reach out to your local 3M sales representative for more information.

Specifications

For information on installing the 3M™ Mining Lamp Bracket Kit, please refer to [video](#) on how to install the bracket.

Before use of the 3M™ Mining Lamp Bracket Kit M-940, the wearer must read and understand the *User Instructions* for the 3M™ Versaflo™ M-Series Headgear and the 3M™ Mining Lamp Bracket Kit M-940.

3M Personal Safety Division

For information regarding the 3M Mining Lamp Bracket Kit M-940, please visit the 3M website (www.3m.com/workersafety) or contact your local 3M representative.



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M PSD products are
occupational use only.

3M Canada

P.O. Box 5757
London, Ontario
N6A 4T1

In United States of America

Technical Service: 1-800-243-4630

Customer Service: 1-800-328-1667
3M.com/workersafety

In Canada

Technical Service: 1-800-267-4414

Customer Service: 1-800-364-3577
3M.ca/Safety

3M is a trademark of 3M. Used under
license in Canada. © 2022, 3M.
All rights reserved. Please recycle.