






# Selection Guide - Surfaces

		PICTURE HANGING	GENERAL PURPOSE METALLIC & DECORATIVE	CLEAR	BATHROOM OUTDOOR	CLEAR OUTDOOR
APPLICATIONS		Pictures & frames New paints Indoor surfaces High moisture	Indoor surfaces New paints	Indoor surfaces New paints High visibility spaces	Indoor & outdoor surfaces High moisture UV exposure	Outdoor surfaces Windows exposed to UV High moisture
OBJECT HOLDING POWER MAX		7,2 kg	2,2 kg	1,8 kg	2,2 kg	0,9 kg
TEMPERATURE		+10 °C à +40 °C	+10 °C à +40 °C	+10 °C à +40 °C	-29 °c à +51 °C	-29 °C à +51 °C
						
Painted walls solid + hollow	Flat plaster wall	✓	✓	✓	✓	✓
	Textured plaster wall 0.5mm roughness	✓	✓		✓	
	Woodchip wallpaper fine/med up to 2.2kg	✓	✓			
	Brick and concrete, coated	✓	✓		✓	
	Wood (varnished)	✓	✓	✓	✓	
Multiple surfaces walls	Coated or veneered wood	✓	✓	✓	✓	
	Glazed tiles	✓	✓	✓	✓	✓
	Glass, metal, plastics, melamine	✓	✓	✓	✓	✓
	Stone	✓	✓		✓	
	Window, sunlight exposed				✓	✓
	Finished surfaces: vinyl siding, fence, deck				✓	

Not recommended for vinyl or unpainted paper or wallpaper, stucco, rough wall textures, bare wood, bare concrete, bare brick, MDF.