




## Ideal for a range of industrial applications:



Wide range of woodworking applications, with a good output and smooth operation.



Product assembly with a slim profile to help operators apply adhesive more accurately.



Carton closing and packaging applications, with a robust and reliable design that stands up to repeated use.

### Ordering Information

Product	Temp	SKU	Voltage	Plug Type	Glue Size	Heater	Temp Control	Operating Temp	Power Cable	Packaging
3M™ Hot Melt Applicator TC/TC-Q, GEN II	Low	7100278634	110-230V	US	5/8" (15.875)	PTC	Self-regulating heater	265°F (130°C)	10 ft	Cardboard box (10 per carton)
	Regular	7100278633						380°F (190°C)		
3M™ Hot Melt Applicator TC/TC-Q, GEN II	Low	7100255832	110-230V	Euro	5/8" (15.875)			265°F (130°C)		
	Regular	7100255953						380°F (190°C)		
3M™ Hot Melt Applicator TC/TC-Q, GEN II	Low	7100255955	110-230V	UK	5/8" (15.875)			265°F (130°C)		
	Regular	7100255954						380°F (190°C)		



**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for proper evaluation (including, but not limited to, fitness for purpose and suitability of application), selection, and use of 3M products. Safety products should always be selected and used in accordance with all applicable regulations and standards (e.g., OSHA, ANSI, and others), after conducting a proper hazard assessment. Failure to properly evaluate, select, and use a 3M product may result in injury, sickness, death, and/or harm to property. Dispose of used atomizing heads, residual paint/coatings, used containers/materials, and PPS in accordance with local regulations.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M is a trademark of 3M Company. All other trademarks are property of their respective owners.  
© 3M 2022. All rights reserved.