

3M Science.
Applied to Life.™


3M Industrial Maintenance and Repair Solutions for Surfaces

**For every job,
a solution.**

Request a consultation



► <https://go.3m.com/mro-surf>



Make the most of your floors and walls.

A complete set of solutions that help you solve problems.

They aren't just floors and walls. They are the foundation of your facility. Keeping them well maintained, organized, clean and easy to navigate helps keep your operations productive and your facility safe. That's why you trust high-quality, reliable 3M Industrial Maintenance and Repair Solutions that help you get the job done quickly — and done right — the first time.

With your know-how and all that 3M offers, you have what it takes to confidently take on these challenges. Together, we can help you keep things running smoothly, efficiently and safely — one job, one solution at a time.



**Surface Repair,
Maintenance and
Protection**

Keep your floors and walls functioning and looking their best with repair, maintenance, protection, organization and safety supplies.

**Floor Safety and Protection
Solutions**

**Wall Repair, Maintenance and
Hanging Solutions**

Worker Health and Safety






For every job, a solution.

**Quick, simple and effortless products that make your job easier.
Check tasks off your list and move onto the next thing.**

This is a partial product listing. For a complete listing, please ask your 3M representative.

Floor Protection Solutions



Protect floors and easy clean-up

Thin, lightweight adhesive-backed material helps prevent grease, grime, solvents and other liquids from seeping through and damaging the surfaces beneath; also traps dirt.

- Adhesive backing keeps material secure and makes for fast, easy application
- Apply to flat or irregular surfaces
- Applications: floors, tabletops, mats, carpets, part stands, hoses, machine rollers and more



**3M™ Self-Stick
Liquid Protection
Fabric**



Reduce tracked-in dust, dirt and contaminants

Multiple layer sticky mat captures dirt on contact before tracking it from one area to another.

- Prolongs life and appearance of floors and carpet and reduces facility maintenance and clean-up
- Thin floor mat profile minimizes tripping hazards
- Firmly attaches to most smooth, clean surfaces
- Framed, portable option is also available (5840)



**3M™ Clean-Walk
Mat 5830 Series**



Keep dirt and moisture at the door

Get cleaner-looking floors that are easier to maintain and less likely to be damaged by tracked-in dirt.

- Trap and hide dirt and moisture so the surface stays neat and clean
- Foam backing reduces creeping and provides added foot comfort
- Available in medium, heavy and extreme traffic volume applications



**3M™ Nomad™
Matting System**

Floor Maintenance Solutions



Cleaning and polishing

Two-sided floor pad cleans and shines in the same step.

- Removes black marks 3 times faster than traditional cleaning pads
- Save costs and labor by reducing or eliminating the need to burnish
- Effective on most coated and uncoated hard floors with only water or neutral cleaner



Scotch-Brite™
Clean &
Shine Pad



Top scrubbing and heavy-duty cleaning


Deeply cleans and scrubs wood, vinyl tile, sheet vinyl, marble, terrazzo and concrete floors.

- Removes floor finish top coats with only neutral cleaner or water
- Reduces the need for chemical strippers
- Heavy-duty scrubbing and deep cleaning for bare concrete floors



Scotch-Brite™
Surface
Preparation Pads

Floor Safety Solutions



Safety and lane marking

For heavy traffic and tough conditions. Provides excellent abrasion resistance and withstands lifting from forklift traffic and dragging pallets.

- Colours remain vivid even when exposed to heavy abrasion
- Easy, clean removal, even after extended use
- For straight lines




3M™ Ultra Durable Floor Marking Tape 971



Safety and lane marking

For everyday floor traffic. An exceptional choice for all but the heaviest lane and safety marking applications.

- Strength, instant adhesion and long-term clean removal
- Conforms to rough or irregular surfaces
- For straight or curved lines



3M™ Vinyl Tape 471 and 3M™ Safety Stripe Tapes 5702



Safety and lane marking

Sturdy metal dispenser applies tape quickly and easily at a walking pace.

- Ideal for long tape lines or repeated applications such as zone striping



3M™ Lane Marking Applicator M-1

Floor Safety Solutions (cont.)



Help prevent slip and trip injuries

Mineral-coated, slip-resistant material features a highly durable surface to withstand equipment traffic.

- Easy to apply, low-profile design
- Applications: flat surfaces, steps, entrances, ramps, ladders, lawn equipment, machinery and vehicles
- NFSI High Traction Certification
- 600 series: general purpose
- 500 series: conforms to corners, curves and irregular surfaces
- 700 series: prevents clogging in dirty and oily applications



**3M™ Safety-Walk™
Slip-Resistant
Tapes and Treads**



Contain drips and spills

High-capacity sorbents have a scrim on one or both sides to increase strength and help eliminate linting.

- Use on most non-aggressive liquids
- Highly absorbent, low profile, and non-granular so it will not damage plant equipment
- Perfect for cleaning up spills or placing around machines or in drip pans
- Available in multiple sizes and formats



**3M™ Maintenance
Sorbent Products**



Improve worker comfort and reduce fatigue

Provide a comfortable and safe surface for walking or standing

- Unbacked open hole construction mat for wet/greasy areas.
- Raised surface edges provide safe footing and slip resistance
- Easy to clean, pick up and hose off.
- Grease resistant terracotta red for oil/greasy work palces



**3M™ Safety-Walk™
Safety Cushion Mat
1200 Black/Red**

Wall Repair and Maintenance Solutions



Repair holes in walls and ceilings

For holes and cracks up to 5" in diameter.

- Makes repairs 5X faster than traditional vinyl spackling
- For drywall, plaster, concrete and wood
- Fiber-reinforced strength
- No shrinking, cracking or sagging



3M™ High Strength Large Hole Repair



Repair holes in walls and ceilings

For nicks and holes up to 3" in diameter.

- Makes repairs 3X faster than traditional vinyl spackling
- Resists flashing of paint
- Firmly hold nails and screws after repair



3M™ High Strength Small Hole Repair



Bonding and quick fixes

Extremely versatile, fast-drying spray adhesive that bonds strongly to a wide range of materials.

- Industrial strength, permanent bond for demanding applications
- Bonds laminate, wood, concrete, metal, plastic and more
- High-temperature and moisture resistant



3M™ Hi-Strength 90 Spray Adhesive



Painting prep (concrete or brick)

Industrial strength with instant adhesion delivers the holding power you rely on.

- Conforms and seals around corners and uneven surfaces, helping to create precise paint lines
- Removes cleanly from most substrates for up to 3 days indoors and 24 hours outdoors
- Hand tearable
- Alternate applications: bundling, holding, attaching, sealing and wrapping



3M™ General Purpose Masking Tape 203

Wall Repair and Maintenance Solutions (cont.)



Painting prep (drywall, smooth walls)

The tape that DIY painters and pros have loved for more than 30 years.

- Designed for use on smooth or lightly textured walls, trim, baseboards, tile and glass
- 14-day clean removal leaves behind no damage or sticky residue
- UV and sunlight resistant
- Available in multiple sizes and lengths



**ScotchBlue™
Original Painter's
Tape**



Marking for visibility and safety

The right tape for safety marking and colour coding walls and pipes.

- Available in a wide variety of colours
- Conforms to uneven surfaces
- Rubber adhesive provides instant adhesion
- Striped hazard marking tape (766/767) is also available



**3M™ General
Purpose Vinyl
Tape 764**



Cleaning walls and vertical surfaces


Dual-action medium duty cleaning sponge designed for everyday cleaning.

- A medium duty scouring pad (No. 96) on one side for scrubbing and cleaning
- A cellulose sponge to wipe spills and messes on the other



**Scotch-Brite™
Medium Duty
Scrub Sponge 74**


Hanging and Organizing Solutions



Permanent attachment and hanging

Fast and easy-to-use permanent bonding method provides high strength and long-term durability.

- Virtually invisible fastening keeps surfaces smooth
- Can replace mechanical fasteners (rivets, welds, screws) or liquid adhesives
- Bonds to a wide variety of substrates including powder-coated paints and irregular surfaces
- 0.045 in (1.1 mm); available in black or white



3M™ VHB™ Tape
5952



Organize without damage

No more holes, marks or sticky residue on your walls, doors, cabinets or closets.

- Adhesive holds strongly on a variety of surfaces, including paint, wood, tile and more
- Easy to use and removes cleanly
- Available in multiple options:
 - Designer Hooks, Utility Hooks or Wire Hooks (hold up to 5 lbs)
 - Picture Hanging Strips (hold up to 16 lbs)
 - Broom Gripper (hold up to 4 lbs)
 - Cord Bundlers (hold up to 2 lbs)



Command™
Products



Hold securely through repeated attachment and removal

A convenient alternative to traditional fastening methods. It is designed to deliver a durable, reclosable fastening solution.

- Interlocking mushroom-shaped heads (250 stem density per square inch) can be opened and closed multiple times
- Mates with Type 170, Type 250 or Type 400 stem densities to provide different strength combinations
- Bonds to a variety of substrates including metals and plastics such as acrylics, polycarbonate and ABS.
- Audible snap verifies closure



3M™ Dual Lock™
Reclosable
Fastener SJ3550

Worker Health and Safety



Respiratory Protection

3-panel design accommodates facial movement

- Low resistance filter technology helps you breathe easily
- Available with 3M™ Cool Flow™ Valve which helps reduce heat build-up
- Sculpted upper panel helps conforms to the nose and contours of the face
- Embossed top panel helps reduce eyewear fogging
- Chin tab designed for ease of positioning and adjustment
- Easy to store away with flat-fold design and individual wrapping
- Colour-coded headbands for easy identification



3M™ DR, Aura
(9322A+)



Reduce exposure to particles associated with welding and other applications: Dusts, mists, fumes, and other nonbiological and biological particles.

3-panel design allows accommodates facial movement

- 3M™ Welding/Particulate Kit 6528QL respirator starter kit.
- The kit comes complete with the 3M™ Half Face Reusable 6500QL Respirator for comfort and durability.
- It features 3M™ Cool Flow™ Exhalation Valve that reduces breathing resistance and minimizes heat build-up.
- The Quick Latch drop down mechanism provides ease in donning and doffing the facepiece.



6528QL
particulate kit



Hearing Protection

Extremely lightweight, low-profile earmuffs for use in high-noise exposure situations. Historically higher attenuating earmuffs meant larger and bulky cups, but no longer. The 3M™ PELTOR™ Earmuffs X4 can attenuate by as much as 31dB whilst maintaining a sleek, low profile aesthetically pleasing design. Using the same innovative technology, the 3M™ PELTOR™ X5 remains relatively lightweight with excellent balance and wearer comfort despite the larger cups, providing ratings as high as SLC80 35dB

- Easy to adjust headband
- Comes in electrically insulated (dielectric) and wire formats
- Twin headband design helps reduce heat build-up and provides a good fit and balance
- Earcups tilt for optimum comfort and efficiency
- Unique attenuation as a result of optimum combination of specially-formulated foam featured in the earcups, cushions and the innovative spacer and cup design
- Newly designed spacer improves attenuation without excess bulk or weight
- Integrated design for more robustness
- Colour-coded for ease of selection
- Easy to clean
- Extremely slim design providing excellent compatibility with other 3M personal protection products



X-series earmuf

Worker Health and Safety (cont.)



Hearing Protection

Enable easy insertion into the ear and efficient noise attenuation.

- Corded and uncorded, washable and suitable for multiple uses, suggested use for up to 10 washes
- No roll down required
- NRR available for both one-hand and two-hand insertion



3M™ E-A-R™
Flexible Fit
Earplug Corded

3M™ E-A-R™
Flexible Fit
Earplug Uncorded



Eye Protection

- 3M™ Scotchgard™ Anti-Fog coating, which lasts longer* than traditional anti-fog coatings and helps increase eyewear performance in wet and steamy environments
- A low profile design
- Adjustable cloth strap
- Indirect ventilation



3M™
GoggleGear™
Safety Goggles,
GG501SGAF



Skin Protection

- Type 5 & 6 protection
- Elasticated waist, ankles & wrists for convenience and freedom of movement
- Two-way zipper with sealable storm flap helps provide additional protection against contaminants
- Extra-roomy design in arms and legs deliver enhanced mobility



3M™ Protective
Coverall, 4515



For painting* and spraying environments to help reduce exposure to organic vapours and particulates.

*Not to be used when spraying isocyanate based paints."

- 3M™ Spraying Respirator Kit 6551QL respirator starter kit. The kit comes complete with the 3M™ Half Face Reusable 6500QL Respirator for comfort and durability. It features 3M™ Cool Flow™ Exhalation Valve which reduces breathing resistance and heat build-up. The Quick Latch drop down mechanism provides ease in donning and doffing the facepiece.



6551 QL
spraying kit

Always read and follow user instructions



Everything you need to get it all done.

When you have an enormous array of trusted maintenance, repair, cleaning and safety products like 3M, there's no task too big, no process too complex. Together, we take on what each day brings, break it down and get things done. All your ingenuity. All our technology. All working together.

3M Industrial Maintenance and Repair Solutions for:



**Machines and
Equipment**



Surfaces



**Cleaning and
Disinfecting**



**HVAC and
Plumbing**



Metal



Electrical

Rely on 3M. Ask your 3M representative.



3M Australia Pty Ltd
Electrical Markets Division
Bldg A, 1 Rivett Road
North Ryde NSW 2113
3M.com.au

3M New Zealand Ltd
Electrical Markets Division
94 Apollo Drive, Rosedale
Auckland 0632
3M.co.nz

Please recycle. Printed in USA © 3M 2022.

All rights reserved. 3M, Command, Dual Lock, Nomad, Safety-Walk, Scotch-Brite, Scotch-Weld, ScotchBlue, the BLUE color of the tape and VHB are trademarks of 3M.

Request a consultation



► <https://go.3m.com/mro-surf>