

3M Science.
Applied to Life.™

Paint shop solutions for every painter.

3M™ PPS™ Series 2.0 Spray Cup System

A revolution in painting productivity and quality began with the 3M™ PPS™ Paint Preparation System, the world's first disposable paint cup system. Guided by a commitment to continuous improvement, 3M™ PPS™ Series 2.0 helps make painting more efficient, cleaner, and easier in busy paint shops.

With lined and vented cup options available for premium or value line lid and liner kits, painters and shop owners can choose the system that best fits their workflow - while relying on consistent material flow and the high-quality results they expect from 3M.



3M™ PPS™ Series 2.0 Spray Cup System

Disposable Lined Cup System

From top to bottom, 3M™ PPS™ Series 2.0 is designed to help make your life easier. To make your painting process cleaner and faster. And to make you a better, more productive painter—more confident in the quality of your work and better able to exceed the expectations of your customers and your shop. Don't let anything come between you and a faster, cleaner, higher quality paint job.

Wide Spout Adapter with Four-Point Connection.

Maximizes stability while spraying. Makes cleaning easier.

Quarter-Turn Lid Locking System.

Comes with every lid. Stays cleaner. Locks faster. Fewer parts to keep track of.

Domed Lid with Full-Diameter Filter.

More paint below the filter improves flow and consistency, while reducing spitting from start to finish.

New Cup in Every Lid & Liner Kit.

Start with a clean cup more often, reducing paint build-up. On-cup ratios and fill markings eliminate traditional mixing cups.

Access Window.

Allows you to hold the liner for cleaner, easier lid removal when refilling. Also easier to check paint levels.

Larger Cup Sealing Plug.

Allows you to seal and protect coatings upside down with greater stability when not in use. Use fewer lids by keeping filters wet.



200 Micron Liner Cup System Kits

Product	Part No.	Items/ Kit	Items/ Case
Large (28oz, 850mL)	26024	50	1
Standard (22oz, 650mL)	26000	50	1
Midi (13.5oz, 400mL)	26112	50	1
Mini (6.8oz, 200mL)	26114	50	1
Micro (3oz, 90mL)	26028	50	1
Standard UV (22oz, 650mL)	26710	50	1

Note: Each kit contains 50 lids and liners, 32 sealing plugs, 1 reusable hard cup.

125 Micron Liner Cup System Kits

Product	Part No.	Items/ Kit	Items/ Case
Large (28oz, 850mL)	26325	50	1
Standard (22oz, 650mL)	26301	50	1
Midi (13.5oz, 400mL)	26312	50	1
Mini (6.8oz, 200mL)	26314	50	1
Micro (3oz, 90mL)	26328	50	1
Standard UV (22oz, 650mL)	20730	50	1

Note: Each kit contains 50 lids and liners, 32 sealing plugs, 1 reusable hard cup.

Lids Only (with Quarter-Turn Lid Locking System)

Product	Part No.	Items/ Pack	Items/ Case
Large / Standard - 200 micron filter	26200	25	1
Large / Standard - 125 micron filter	26199	25	1
Midi / Mini / Micro - 200 micron filter	26204	25	1
Midi / Mini / Micro - 125 micron filter	26205	25	1

Hard Cups— with Mixed Ratios on Cups

Product	Part No.	Items/ Carton	Items/ Case
Large Cups (28oz, 850mL)	26023	2	4
Standard Cups (22oz, 650mL)	26001	2	4
Midi Cups (13.5oz, 400mL)	26122	2	4
Mini Cups (6.8oz, 200mL & 3oz, 90mL)	26115	2	4

Accessories

Product	Part No.	Items/ Pack	Items/ Case
Universal Shaker Core	26458	1	12
Sealing Plug	26432	96	6

PPS Dispensers

Product	Part No.	Items/ Kit	Items/ Case
Lid Dispenser	16299	1	1
Liner Dispenser	16219	1	1

3M™ PPS™ Series 2.0 Vented Spray Cup System

When high standards are the expectation, you need equipment that delivers consistent results. The 3M™ PPS™ Series 2.0 Vented Spray Cup System - brings the advantages you expect from a premium vented cup with the proven technology of the first disposable spray cup system in the world.



Ready to Use Instantly

When speed and efficiency are vital, grab-and-go tools can make all the difference. With built-in filters and ready-to-use vents, minimal assembly is required before stepping into the booth.



Consistent Material Flow

Quality paint jobs matter, especially when your reputation is on the line. From start to finish, these vented spray cups provide a consistent material flow, even down to the final ounces (mL).



Confident Cup Design

Make the most of your time in the booth by using our largest cup (32 oz / 950mL) – one of four different sizes available. A sturdy but flexible cup design allows you to put your mind at ease when temporarily storing leftover paint. With no reusable parts, it's like spraying with a new cup every time.

Built-in filter within lid



Ready-to-use vent on bottom of the cup

200 Micron Vented Cup System Kits

Product	Part No.	Items/Kit	Kit/Case
Large (32oz, 950mL) Lids and Liners	26264	50	1
Standard (23.7oz, 700mL) Lids and Liners	26263	50	1
Midi (13.5oz, 400mL) Lids and Liners	26262	50	1
Mini (8.5oz, 250mL) Lids and Liners	26261	50	1
Standard UV (23.7oz, 700mL) Lids and Liners	26260	50	1

125 Micron Vented Cup System Kits

Product	Part No.	Items/Kit	Kit/Case
Large (32oz, 950mL) Lids and Liners	26164	50	1
Standard (23.7oz, 700mL) Lids and Liners	26163	50	1
Midi (13.5oz, 400mL) Lids and Liners	26162	50	1
Mini (8.5oz, 250mL) Lids and Liners	26161	50	1
Standard UV (23.7oz, 700mL) Lids and Liners	26160	50	1

Vented Lids Only

Product	Part No.	Items/Pack	Pack/Case
Large / Standard Lids - 200 micron filter	26265	50	1
Large / Standard Lids - 125 micron filter	26165	50	1
Midi / Mini Lids - 200 micron filter	26266	50	1
Midi / Mini Lids - 125 micron filter	26166	50	1

Vented Cups (with Mixed Ratios on Cups)

Product	Part No.	Items/Pack	Pack/Case
Large Cups (32oz, 950mL)	26364	50	1
Standard Cups (23.7oz, 700mL)	26363	50	1
Midi Cups (13.5oz, 400mL)	26362	50	1
Mini Cups (8.5oz, 250mL)	26361	50	1

Accessories

Product	Part No.	Items/Pack	Items/Case
PPS Dispensing Rack	26370	1	1
Vented Shaker Core	26457	1	12



Work Smarter with the Right Cup for Every Job

With premium, vented and basic lid and liner kit options in the 3M™ PPS™ Series 2.0 system, you can select the cup and system that meets your workflow needs while helping reduce paint consumption and overall operating costs.




Micro	Mini	Midi	Standard	Large
Lined: 3oz, 90mL	Lined: 6.8oz, 200mL Vented: 8.5oz, 250mL	Lined: 13.5oz, 400mL Vented: 13.5oz, 400mL	Lined: 22oz, 650mL Vented: 23.7oz, 700mL	Lined: 28oz, 850mL Vented: 32.1oz, 950mL
Ideal for: Spot Repairs	Ideal for: 1-Panel Repairs	Ideal for: 2-Panel Repairs, such as bumpers	Ideal for: 3-Panel Repairs	Ideal for: 4-Panel Repairs, including large, clear coat batches

3M™ PPS™ Basic Series Lid and Liner Kit (use with 3M™ PPS™ Series 2.0 Hard Cups, sold separately)



Part Number	Size	Volume	Filter	Content
PBS125	Standard	22oz / 650mL	125 micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar
PBS200	Standard	22oz / 650mL	200 micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar
PBL125	Large	28oz / 850mL	125 micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar
PBL200	Large	28oz / 850mL	200 micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar

3M™ PPS™ Basic Series Collar



Part Number	Size	Content
PBC005	Std / Large	5 re-useable collars/pack, 4 packs/case

Note: 3M™ PPS™ Series 2.0 Spray Cup System Hard Cups are necessary to support the liners of the 3M™ PPS™ Basic Series Lid and Liner Kit. 3M™ PPS™ Basic Series Kits are compatible with all existing 3M™ PPS™ Series 2.0 Spray Cup System adapters or 3M™ Performance Spray Gun, offering a stable and reliable four-point connection.

For best results, we recommend using 3M™ PPS™ Series 2.0 with 3M™ Performance Spray Gun Series. Alternatively choose one of the 3M™ PPS™ Series 2.0 Adapters to connect your spray gun to the spray system.

3M™ Performance Spray Gun Series



Part Number	Content
26852	3M™ Performance Spray Gun 2 with 3M™ Performance Air Flow Control Valve
26978	3M™ Performance Fine Finish Spray Gun System with PPS™ 2.0 (Kit incl. Spray Gun, Fine Finish Nozzles and 3M™ PPS™ Series 2.0 Kits)
26778	3M™ Performance HVLP Spray Gun System with PPS™ 2.0 (Kit incl. Spray Gun, HVLP Nozzles and 3M™ PPS™ Series 2.0 Kits)

For other spray guns, find a complete list of adapters at 3MCollision.com/PPSAdapters



ALWAYS WORK SAFE

Personal Protective Equipment (PPE) helps reduce exposure to certain workplace hazards. It is ultimately the responsibility of the employer to select the most appropriate PPE based on a full risk assessment. Always read the product performance, warnings and limitations before selection and use.



Automotive Aftermarket Division
3M Center
Building 223-4S-04
St. Paul, MN 55144-1000
1-877-666-2277

For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3MCollision.com/info

For industrial/occupational use only. Not for consumer sale or use.

3M and PPS are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2026. All rights reserved. 60-4405-0171-0

For more information, visit us at
3MCollision.com/PPS



/3MCollision



/3MCollision



/3MCollision