



Science.
Applied to Life.™

3M™ Industrial Tapes for Marking

Fast, flexible and
durable for no compromises.



The flexibility you need. The durability you depend on.


Mark your floors with the power of 3M tapes.

Floors, walls, or loading docks – whatever you need, we've got a tape for the job. From heavy traffic and pallet drag to colours and patterns for pipe marking, our tapes give you power to optimise your workflow any time you need to – while making sure everyone stays safe.

3M™ Durable Floor Marking Tape 971: Tough traffic areas

3M™ Vinyl Tape 471: Everyday medium traffic areas

3M™ Vinyl Tape 764i: Walls and pipes



**Avoid wasting your time
and money with paint.**

- ▶ Easy removal for changing layouts fast
- ▶ Easy application saves time and labour costs
- ▶ No masking, fumes, or curing time
- ▶ Makes both straight and curved lines simple to mark
- ▶ No spills or clean-up
- ▶ No liquid chemicals



Heavy floor traffic

Engineered for heavy traffic and tough conditions.

3M™ Durable Floor Marking Tape 971


3M™ Durable Floor Marking Tape 971 is specially engineered to stand up to tough conditions where you need floor marking staying power. Where other floor marking tapes fail, 971's thick backing provides excellent abrasion resistance and withstands lifting from forklift traffic and dragging pallets. When it comes time to change the layout of your factory or warehouse, the unique adhesive promotes easy, clean removal from your floor.

Product number	Colour	Adhesive type	Backing material	Backing thickness	Total thickness	Temperature range
971	Yellow, White, Blue, Green, Orange, Red	Rubber	Vinyl	0.36mm	0.42mm	4°C to 49°C


Note: The technical information and data on these pages should be considered representative or typical only and should not be used for specification purposes.

Easy to apply

Compatible with the 3M™ Lane Marking Applicator M-1 for even easier application.



- ▶ Excellent abrasion resistance
- ▶ Withstands lifting from forklift traffic
- ▶ Bright colours for high visibility
- ▶ Resists moisture and many chemicals
- ▶ Easy to clean
- ▶ Sticks on contact and stays where you put it
- ▶ Promotes clean removal without solvents and scraping
- ▶ Available in a variety of widths and colours



Everyday floor traffic

Reliable, vibrant, highly versatile marking tape.




3M™ Vinyl Tape 471 and 3M™ Safety Stripe Tapes 5702

Strength, conformability, instant adhesion and long-term clean removal make 3M™ Vinyl Tape and 3M™ Safety Stripe Tape an exceptional choice for all but the heaviest lane and safety marking applications. Designed with special stretch properties, these tapes conform to rough or irregular surfaces and can be used to make critical curved lines while resisting edge lifting which can lead to trip hazards and tape tear. Plus they retain their bright colours over time, even when exposed to abrasion, wear and many solvents.

Product number	Colour	Adhesive type	Backing material	Backing thickness	Total thickness	Temperature range
471	Black, Blue, Green, Orange, Red, White, Yellow	Rubber	Vinyl	0.10mm	0.14mm	4°C to 77°C
5702	Black/Yellow Stripe	Rubber	Vinyl	0.11mm	0.14mm	

Note: The technical information and data on these pages should be considered representative or typical only and should not be used for specification purposes.



- ▶ Excellent durability, abrasion and solvent resistance
- ▶ Quick stick and excellent holding strength
- ▶ Available in a wide variety of vivid colours
- ▶ Ideal for use on curved and irregular surfaces
- ▶ One-piece, clean removal from many surfaces
- ▶ Safety stripe tapes for hazardous areas



Pipes, walls and short term floor

Economical safety marking.

3M™ General Purpose Vinyl Tape 764i and 3M™ Hazard Marking Tapes 766i/767i

3M™ General Purpose Vinyl and Hazard Marking Tapes are the cost-effective choice for a variety of safety marking and colour coding applications where you don't see tough conditions or the need for long term clean removal. Conformability, instant adhesion and easy unwind make these tapes ideal for marking equipment, walls and pipes.

Product number	Colour	Adhesive type	Backing material	Backing thickness	Total thickness	Temperature range
764i	Black, Blue, Gray, Green, Orange, Red, Transparent, White, Yellow	Rubber	Vinyl	0.10mm	0.13mm	16°C to 27°C
766i	Black/Yellow Stripe					
767i	Red/White Stripe					

Note: The technical information and data on these pages should be considered representative or typical only and should not be used for specification purposes.

- ▶ Available in a wide variety of colours
- ▶ Conforms to uneven surfaces
- ▶ Rubber adhesive provides instant adhesion
- ▶ Ideal for marking in light traffic areas, walls and pipes





5S colour coding


When implementing 5S, think 3M.

3M™ Vinyl Tape 5S Colour Coding

The 5S visual management system helps make it easier to ensure your workplace is more organised, efficient and productive. 3M's convenient pack of colour coding vinyl tapes can help implement the 5S system by providing floor marking and safety identification. The included 3M™ Vinyl Tapes and 3M™ Safety Stripe Tapes come in a variety of bright colours that are locked into the vinyl for long term high visibility. Perfect for lane marking, hazard and safety marking of floors, loading docks, shipping areas and warehouses.

Learn more about the 5S visual management system at 3M.co.uk/floormarkingtapes

Pattern	Colour	Examples of where to use
	Yellow	Aisles, walk-ways and traffic lanes, work cells
	Orange	Material or product inspection or temporary storage locations
	Red	Safety/first aid, defect/scrap area, red tag area
	Green	Materials and manufacturing, finished goods
	Blue	Materials and manufacturing, raw materials
	Black	Materials and manufacturing, work in progress
	Black/ Yellow	Areas of potential health risks, extra caution needs to be taken
	Black/ White	Areas to stay out of for operational purposes



Help for marking traffic lanes and hazard areas.

3M applicators help to apply safety and vinyl tape with greater ease and accuracy. These tape applicators can increase tape-to-surface contact for reduced air bubbles and improved adhesion.

Product	Description
3M™ Lane Marking Applicator M-1	Constructed of sturdy metal, this wheeled dispenser is durable and extremely easy to use. The M-1 tape dispenser helps reduce physically taxing up-and-down movements by allowing application while standing and walking. Works with 3M™ Vinyl Tape 471 and 764i and 3M™ Durable Floor Marking 971 family of tapes.
3M™ Hand Applicator PA1-B Blue	Use a squeegee to smooth out bubbles and wrinkles when hand applying tape. Made of flexible, durable plastic. 



Scan or click on the QR code to find out more, or visit [3M.co.uk/floormarkingtapes](https://www.3m.co.uk/floormarkingtapes)



Industrial Adhesives and Tapes Division

3M United Kingdom PLC
3M Centre, Cain Road
Bracknell, Berkshire
RG12 8HT
www.3m.co.uk/industrial

3M Ireland Ltd
The Iveagh Building
The Park, Carrickmines
D18 X015
Ireland

Important note

Product Selection and Use: Many factors beyond 3M's control and uniquely within users' knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customers' application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.