

3M Science.
Applied to Life.™



Advancing worker health and safety during complex operations.

Pharmaceutical Manufacturing Global PPE Solutions Guide



Personal protection developed with science.

As global health and safety experts, we understand the challenges facing the pharmaceutical industry seeking to help protect workers in its complex manufacturing processes across the globe. We collaborate with our customers, engage with regulatory and standards groups across the globe, and use research-backed science to provide safety solutions that can help protect your workers against different hazard types. The 3M science of safety approach is your trusted partner for worker PPE.

Respiratory Protection

Each pharmaceutical manufacturing environment presents a unique set of needs and challenges when it comes to occupational inhalation hazards associated with handling of various pharmaceutical ingredients and disinfectants. To support your needs, we have a broad array of respiratory protection solutions and technical resources to assist you in selecting the appropriate personal protection equipment for your workers.

Powered Air Purifying Respirators (PAPR)

3M powered air purifying respirator systems offer comfortable, integrated protection against occupational hazards. Choose a system configuration that meets your specific needs.

3M Versaflo™ Hoods S-Series



Integrated Head Suspension
Economy Hood with Inner Shroud

Product #	Region Availability
● S-403 ¹	US CA APAC* MEA*



Integrated Head Suspension
High Durability Hood with Face Seal

Product #	Region Availability
● S-533 ^{1,2}	US CA APAC* EUR* MEA* LA*



Premium Reusable Suspension
Hood Assembly with Inner Shroud

Product #	Region Availability
● S-657 ^{1,2}	US CA APAC* EUR* MEA* LA*



Premium Reusable Suspension
Hood Assembly with Sealed Seams
and Inner Neck Collar

Product #	Region Availability
● S-855 ^{1,2}	US CA EUR*



Premium Reusable Suspension:
Hood Assembly with Sealed
Seams and Inner Shroud

Product #	Region Availability
● S-857 ¹	US CA

¹OSHA assigned protection factors defined in 29 CFR 1910.134. 3M supports an APF of 1000 for the S-Series.
²CEN assigned protection factors defined in EN 2291 class TH2. 3M supports an APF of 40 for the S-Series. Contact 3M Technical Service for supporting test procedures and data. In Canada, follow CSA Z94.4 or the requirements of the authority having jurisdiction in your region.

Breathing Tubes:



3M™ Versaflo™ Length
Adjusting Breathing Tube

Product #	Region Availability
● BT-30	US CA APAC* EUR* MEA* LA*



3m™ Versaflo™ Heavy Duty
Rubber Breathing Tube

Product #	Region Availability
● BT-40	US CA APAC* EUR* MEA* LA*

Powered Air Purifying Respirators

Turbos/Blowers

3M™ Versaflo™ TR-300 PAPR



TR-300 Turbo / Blower

Product #	Region Availability
● TR-302N+	US CA APAC* MEA* LA*
● TR-302E+	EUR* MEA* APAC* LA*

Filter Cover TR-371+ and Airflow Indicator TR-971 included with TR-302 Turbo/Blower Models.

3M™ Versaflo™ TR-600 PAPR



TR-600 Turbo / Blower

Product #	Region Availability
● TR-602N	US CA APAC* MEA* LA*
● TR-602E	EUR* MEA* APAC* LA*

Filter cover and Airflow Indicator TR-971 purchased separately for TR-602 Turbo/Blower Models.

3M™ Versaflo™ TR-800 PAPR



TR-800 Intrinsically Safe Turbo / Blower

Product #	Region Availability
● TR-802N	US CA APAC* MEA* LA*
● TR-802E	EUR* MEA* APAC* LA*

Filter cover and Airflow Indicator TR-971 purchased separately for TR-802 Turbo/Blower Models.

Batteries



High Capacity Battery for TR-300 Turbo / Blower

Product #	Region Availability
● TR-332	US CA APAC* EUR* MEA* LA*

Battery Charger TR-341 or TR-344 models purchased separately



Standard Battery for TR-600 Turbo / Blower

Product #	Region Availability
● TR-630	US CA APAC* EUR* MEA* LA*

Battery Charger TR-641 or TR-644 models purchased separately



Battery, Intrinsically Safe for TR-800 Turbo / Blower

Product #	Region Availability
● TR-830	US CA APAC* EUR* MEA* LA*

Includes TR-838 Battery Removal Tool
Battery Charger TR-641 or TR-644 models purchased separately

Cartridges/Filters

TR-300 Particulate Filters



High Efficiency Particulate Filter

Product #	Region Availability
● TR-3712N	US CA APAC* MEA* LA*



High Efficiency Particulate Filter

Product #	Region Availability
● TR-3712E	EUR* APAC* MEA* LA*

High Efficiency Particulate/
Nuisance Level Organic Vapour Filter

Product #	Region Availability
● TR-3802E	EUR* APAC* MEA* LA*

TR-600 and TR-800 Organic Vapor/Vapour, Acid Gas, Particulate Cartridges/Filters



Organic Vapor/
HEPA Cartridge

Product #	Region Availability
● TR-6510N	US CA APAC* MEA* LA*

Compatible with Filter Cover TR-6500FC



Organic Vapor
Acid Gas/
HEPA Cartridge

Product #	Region Availability
● TR-6530N	US CA APAC* MEA* LA*

Compatible with Filter Cover TR-6500FC



Multi-Gas/
HEPA Cartridge

Product #	Region Availability
● TR-6590N	US CA APAC* MEA* LA*

Compatible with Filter Cover TR-6500FC



High Efficiency Particulate Filter

Product #	Region Availability
● TR-6710N	US CA APAC* MEA* LA*

Compatible with Filter Cover TR-6700FC



High Efficiency Particulate &
Nuisance OV Filter

Product #	Region Availability
● TR-6820N	US CA APAC* MEA* LA*

Compatible with Filter Cover TR-6800FC



A2P
Gas & Vapour Filter

Product #	Region Availability
● TR-6130E	EUR* APAC* MEA* LA*

Compatible with Filter Cover TR-6100FC



ABE1P
Gas & Vapour Filter

Product #	Region Availability
● TR-6310E	EUR* APAC* MEA* LA*

Compatible with Filter Cover TR-6300FC



ABE2K1HgP
Gas & Vapour Filter

Product #	Region Availability
● TR-6580E	EUR* APAC* MEA* LA*

Compatible with Filter Cover TR-6500FC



Particulate Filter

Product #	Region Availability
● TR-6710E	EUR* APAC* MEA* LA*

Compatible with Filter Cover TR-6700FC



A2P Gas & Vapour Filter

Product #	Region Availability
● TR-6820E	EUR* APAC* MEA* LA*

Compatible with Filter Cover TR-6800FC

Filter Covers



Product #	Region Availability
● TR-371+	US CA APAC* EUR* MEA* LA*

Included with TR-302 Turbo/Blower Models.



Product #	Region Availability
● TR-6100FC	US CA APAC* MEA* LA*



Product #	Region Availability
● TR-6300FC	US CA APAC* MEA* LA*



Product #	Region Availability
● TR-6500FC	US CA APAC* MEA* LA*



Product #	Region Availability
● TR-6700FC	US CA APAC* MEA* LA*



Product #	Region Availability
● TR-6800FC	US CA APAC* MEA* LA*

Region Availability: US | CA | EUR* | APAC* | MEA* | LA*

Belts



Easy Clean Belt for TR-300 PAPR

Product #	Region Availability
● TR-327	US CA APAC* EUR* MEA* LA*



Easy Clean Belt for TR-600 and TR-800 PAPR

Product #	Region Availability
● TR-627	US CA APAC* EUR* MEA* LA*

Reusable Respirators

3M™ Half and Full Facepiece Reusable Respirators are paired with filters and cartridges to help protect workers against a variety of respiratory hazards in the workplace. Choose a facepiece and compatible filters and/or cartridges that address your site's needs.

Facepieces



3M™ Secure Click™ HF-800 Half Facepiece / Mask ●

Product #	Region Availability
HF-801 (S) HF-802 (M) HF-803 (L)	EUR* MEA*



3M™ 7500 Series Half Facepiece / Mask ●●

Product #	Region Availability
7501 (S) 7502 (M) 7503 (L)	US CA APAC* EUR* MEA*



3M™ 6500 Series Half Facepiece / Mask ●●

Product #	Region Availability
6501 (S) 6502 (M) 6503 (L)	US CA APAC* EUR* MEA*



3M™ 6000 Series Full Facepiece / Mask ●●

Product #	Region Availability
6700 (S) 6800 (M) 6900 (L)	US CA APAC* EUR* MEA*

3M™ Secure Click™ Cartridges / Filters



3M™ Secure Click™ P3 R Particulate Filter

Product #	Region Availability
● D3135	EUR* MEA*



3M™ Secure Click™ A2 OV Gas and Vapour Filter

Product #	Region Availability
● D8055	EUR* MEA*



3M™ Secure Click™ ABEK1 OV Gas and Vapour Filter

Product #	Region Availability
● D8059	EUR* MEA*



3M™ Secure Click™ ABEK3 R Gas, Vapour and Particulate Filter

Product #	Region Availability
● D8094	EUR* MEA*

3M Particulate Filter 2000 Series



3M™ Particulate Filter P100

Product #	Region Availability
● 2091	US CA APAC* MEA* LA*



3M™ P3 R Particulate Filter

Product #	Region Availability
● 2135	EUR* MEA* APAC* LA*

3M Gas & Vapour Cartridge 6000 Series



3M™ Organic Vapor Cartridge

Product #	Region Availability
● 6001	US CA APAC* MEA* LA*



3M™ A2 OV Gas and Vapour Filter

Product #	Region Availability
● 6055	EUR* MEA* APAC* LA*



3M™ Multi-Gas / Vapor Cartridge

Product #	Region Availability
● 6006	US CA APAC* MEA* LA*



3M™ ABEK1 OV Gas and Vapour Filter

Product #	Region Availability
● 6059	EUR* MEA* APAC* LA*

3M Gas & Vapour / Particulate 6000 Series



3M™ Organic Vapor / P100 Combo Cartridge

Product #	Region Availability
● 60921	US CA APAC* MEA* LA*



3M™ Multi-Gas / Vapor P100 Combo Cartridge

Product #	Region Availability
● 60926	US CA APAC* MEA* LA*



3M™ ABEK2P3R OV Gas and Vapour Combo Filter

Product #	Region Availability
● 60991	EUR* MEA* APAC* LA*

*Approved for use with 3M 6000 Series Full Facepiece

3M Filtering Facepiece Respirators

3M Filtering Facepiece Respirators (also known as disposable respirators) provide a number of model types with varying features that are designed to help protect from particulate hazards.



Particulate Respirator R95, Nuisance Level Organic Vapor Relief

Product #	Region Availability
8247	US CA APAC LA



Particulate Respirator, R95, Nuisance Level Acid Gas Relief

Product #	Region Availability
8246	US CA LA



Speciality Particulate Respirator, FFP1, Unvalved, Nuisance Level Acid Gas Relief

Product #	Region Availability
9915	EUR MEA



Speciality Particulate Respirator, FFP1, Unvalved, Nuisance Level Organic Vapor Relief

Product #	Region Availability
9913	EUR MEA



Particulate Respirator N95, Unvalved

Product #	Region Availability
8210	US CA APAC MEA LA



Aura™ Particulate Respirator, FFP2, Unvalved

Product #	Region Availability
9320+	EUR MEA LA



Particulate Respirator KN95, Unvalved

Product #	Region Availability
9502+	APAC



Aura™ Particulate Respirator FFP3, Shrouded Valve

Product #	Region Availability
1883+	EUR MEA



VFlex™ Particulate Respirator, N95, Unvalved

Product #	Region Availability
9105	US CA MEA LA



VFlex™ Particulate Respirator, FFP2, Unvalved

Product #	Region Availability
9152	EUR MEA LA

Visit 3M.com for other 3M Filtering Facepiece Respirators

Other Respirator Systems

Industrial work in IDLH environments or emergency response situations requiring SCBA protection is intense, physically demanding work. That's why 3M™ Scott™ SCBA and facepieces are designed with durability, dependability and user-focus in mind.

Please contact a local 3M Safety Specialist to help build & order product to your specifications.

3M™ Scott™ ProPak (EN)

Region Availability

US | CA | LA

3M™ Scott™ Air-Pak 75i SCBA (NIOSH)

Region Availability

EUR | MEA | APAC



3M™ Scott™ Air-Pak 75i SCBA (NIOSH)



3M™ Scott™ AV-3000 SureSeal Facepiece



3M™ Scott™ ProPak (EN)



3M™ Scott™ Promask Positive Pressure Facepiece

Eye Protection

With safety in sight, we offer high-quality eye protection solutions for occupational hazards and sensitive work environments with stringent contamination control requirements.



3M™ Safety Goggles

Modern designs offered in several configurations combined with the 3M™ Scotchgard™ Protector Anti-Fog Coating on select models* for added protection against fogging and scratching.

Goggle Gear 2890 Series Safety Goggles, Scotchgard™ Anti-Fog Lens*

Product #	Region Availability
GG2890	US CA APAC EUR MEA LA



Goggle Gear 500 Series Safety Goggles, Red Seal, Scotchgard™ Anti-Fog Lens*

Product #	Region Availability
GG500	US CA APAC MEA LA



Goggle Gear 500 Series Safety Goggles, Blue Seal, Scotchgard™ Anti-Fog Lens*, Autoclave Applications

Product #	Region Availability
GG500	EUR



Safety Goggles, Anti-Fog Lens

Product #	Region Availability
1623	APAC



Fahrenheit™ Series Safety Goggles, Anti-Fog Lens

Product #	Region Availability
71360	APAC EUR MEA

3M™ Safety Eyewear

Innovative design featuring the 3M™ Pressure Diffusion Temple Technology for improved comfort and secure fit and 3M™ Scotchgard™ Protector Anti-Fog Coating for added protection against fogging and scratching.



SecureFit™ 500 Series

Product #	Region Availability
SF500	US CA EUR



SecureFit™ 400 Series

Product #	Region Availability
SF400	US CA APAC EUR MEA LA



SecureFit™ 300 Series

Product #	Region Availability
SF300	US CA APAC EUR MEA LA



SecureFit™ 200 Series

Product #	Region Availability
SF200	US CA APAC EUR MEA LA



SecureFit™ 3700 OTG Series

Product #	Region Availability
SF3700	US CA EUR

Visit 3M.com for a full list of 3M Eye and Face Protection Options

Hearing Protection

We're dedicated to the success of your entire hearing conservation program. Implementing a solution that really makes a difference begins with understanding the hazards, the regulations, and the factors that impact hearing protection. With world-class, proven safety products, 3M Hearing Solutions is the partner you'll want with you every step of the way.

3M™ PELTOR™ Earmuffs

3M™ Peltor™ X Series earmuffs feature a wide range of attenuation levels that help meet hearing protection needs for most industrial applications. The X Series is 3M™ E-A-Rfit™ compatible. Offered in headband or helmet mounted configurations.



Headband

X1 Series Earmuffs

Product #	Region Availability
X1	US CA APAC EUR MEA LA



Helmet Mounted

X3 Series Earmuffs

Product #	Region Availability
X3	US CA APAC EUR MEA LA

Hygiene kits are available for select earmuff models. Kits include replaceable ear cushions and foam liners. See 3M.com for available kits.

3M™ E-A-R™ Earplugs

We provide a wide range of earplugs so you can choose the best solution for worker's individual needs. Following are few earplug models.



3M™ E-A-R™ Reusable Earplugs

Product Name	Region Availability
Ultrafit™ Earplugs, Corded	US CA APAC LA
Tri-Flange™ Earplugs, Corded	EUR MEA

Pic: 3M™ Ultrafit™ Earplugs



Pic: 3M™ Push-Ins Earplugs

3M™ E-A-R™ Push-Ins Earplugs

Product Name	Region Availability
Push-Ins Earplugs, Corded	US CA APAC EUR MEA LA
Express Push-Ins Earplugs, Corded	



Pic: 3M™ UltraFit™ Metal Detectable Earplugs

3M™ E-A-R™ Metal Detectable Earplugs

Product Name	Region Availability
Tracers™ Metal Detectable Earplugs, Corded	EUR MEA
UltraFit™ Metal Detectable Earplugs, Corded	US CA APAC MEA



3M™ E-A-R™ Disposable Earplugs

Product Name	Region Availability
Yellow Neons™ Earplugs, Corded	US CA APAC EUR MEA LA
Classic™ Earplugs, Corded	

Pic: 3M™ Yellow Neon™ Earplugs



Pic: 3M™ EEP-100 Electronic Earplugs

3M™ E-A-R™ Electronic Earplugs

Product #	Region Availability
EEP-100	US CA APAC EUR MEA
LEP-200	US CA EUR

Visit 3M.com for other 3M Hearing and Communications Solutions.



3M™ E-A-Rfit™ Dual-Ear Validation System

Real-world measurement. Real results.

The 3M™ E-A-Rfit™ Dual-Ear Validation System assesses the amount of attenuation provided to a user of hearing protection.

- Compliant with ANSI/ASA S12.71-2018
- Science-based, quantitative testing
- Fast, clear, and accurate results
- Tests both ears in 7 frequencies (125Hz to 8kHz) in less than 5 seconds
- Seamless software integration
- Compact design
- Earplug, earmuff, and banded HPD testing capability
- Tailored product selection that meets your needs

Hearing Conservation Management System

The 3M™ Hearing Conservation Program Manager* is here to help you keep track of critical hearing conservation program tasks and responsibilities – so you can spend less time searching and more time knowing. Part of the larger cloud-based 3M™ Connected Safety ecosystem, the 3M™ Hearing Conservation Program Manager delivers solutions to help take the complexity out of worker safety and help keep you in compliance.

- Organize and manage a Hearing Conservation Program
- Access resources on regulatory requirements and hearing conservation best practices
- Import new and existing E-A-Rfit™ test results
- Create a list of hearing protector options that meet your requirements
- Identify workers who must complete training, audiometric testing, and hearing protector fit testing
- Take control of your hearing conservation program

*Currently available in United States only



Confined Space Solutions

Confined spaces present some of the most challenging environments for any health and safety professional. From potentially toxic atmospheres and high chemical exposure to physically hazardous conditions, confined spaces often present challenges.

3M™ DBI-SALA® Davit Arm Systems System Components

Designed for confined space entry/retrieval applications, these hoist systems are constructed of lightweight, high-strength materials, feature adjustments for overhead clearance restrictions, and pivot for ease-of-rescue.

Davit Mast



(Includes Universal Lower Mast High Capacity 8000109 and one Winch Mount Bracket.)

Long Reach Davit Arm High Capacity
(70.2-113.2 cm / 27-44 in)

Product #	Region Availability
8000108	EUR MEA



(Includes on Winch Mount Bracket.)

Adjustable Offset Upper Davit Mast
(59.7-107.9 cm / 23.5-42.5 in)

Product #	Region Availability
8518006	US CA APAC LA

Mast Extension



Mast Extension High Capacity
(84 cm / 33.1 in)

Product #	Region Availability
8000113	EUR MEA



Lower Mast Extension
(83.8 cm / 33 in)

Product #	Region Availability
8518002	US CA APAC LA

Visit 3M.com for other Davit Arm options.

Visit 3M.com for other Mast Extension options.

Fixed Bases



Floor Mount Base High Capacity, Galvanized Steel


Product #	Region Availability
8000095	EUR MEA



Center Mount Sleeve Zinc-Plated Base

Product #	Region Availability
8512831	US CA APAC LA

Portable Bases



3-Piece Long Reach Base

Product #	Region Availability
8000105	EUR MEA
8000108	US CA APAC LA



Counterweight Cart Base
(weight plates ordered separately)

Product #	Region Availability
8000106	EUR MEA
8520775	US CA APAC LA

Visit 3M.com for other Base options.

Mechanical Devices



3-Way Sealed-Blok™ Self-Retracting Line, Cable 9 m / 30 ft

Product #	Region Availability
3400856	EUR MEA
3400850	US CA APAC LA



Digital Winch, Removable Handle, Galvanized Steel 18 m / 60 ft
(Includes one Mounting Bracket.)

Product #	Region Availability
8518560	US CA APAC EUR MEA LA

Mounting Brackets



High Capacity Davit Connecting Device Mounting Bracket with Winch/SRL Adapter

Product #	Region Availability
8000117	EUR MEA



Quick-Release Mounting Bracket for Upper & Lower Masts

Product #	Region Availability
8516824	US CA APAC LA



Winch/SRL Adapter With Flat Back

Product #	Region Availability
8510207	US CA APAC LA



Visit 3M.com for other Mechanical Devices and Mounting Brackets.

3M™ Body Harnesses

As an industry leader, 3M™ DBI-SALA® Fall Protection develops and delivers world-class, high-performing fall protection solutions for workers around the world.




DBI-SALA® ExoFit Nex™ Vest-Style Retrieval Harness

Product #	Region Availability
1113061 (S)	US CA APAC LA
1113064 (M)	
1113067 (L)	
1113070 (XL)	



DBI-SALA® ExoFit Nex™ Rescue Harness

Product #	Region Availability
1113970 (S)	EUR MEA APAC
1113971 (M)	
1113972 (L)	
1113973 (XL)	



DBI-SALA® Delta™ Comfort Rescue Harness

Product #	Region Availability
1112950 (S)	EUR MEA
1112949 (M/L)	
1112951 (XL)	

Visit 3M.com for other 3M Confined Space Solutions and Training.

Head Protection

3M™ delivers protection, comfort, and performance with complete solutions for head and face protection to accommodate the needs of your application or environment.



SecureFit™ 5000 Series Safety Helmet

Product #	Region Availability
X5000	US EUR



G3000 Series Helmets

Product #	Region Availability
G3000	EUR MEA LA



700 Series Hard Hat, 4-Point Ratchet Suspension

Product #	Region Availability
H-700	US CA APAC MEA LA

Visit 3M.com for other 3M Head Protection Options

Protective Apparel

Whether you're looking for protective suits, protective apparel, protective clothing or disposable coveralls, you can help protect your workers against hazards with 3M Protective Apparel.

3M™ Protective Coveralls

Protective Coveralls, Anti-Static, Low Linting



Microporous PE laminate material, elasticized cuffs, collared and hood models

Product #	Region Availability
4510	EUR MEA US APAC



Microporous PE laminate material, knitted cuffs, 3-panel hood

Product #	Region Availability
4545	EUR MEA US APAC



Non-microporous PE laminate material, knitted cuffs, 3-panel hood, taped seams

Product #	Region Availability
4565	EUR MEA US APAC



Multi-layer non-microporous PE laminate material, elasticized cuffs with thumb loops, 3-panel hood

Product #	Region Availability
4570	EUR MEA US APAC



Overboot Cover, Slip Resistant, Universal Size with Ties

Product #	Region Availability
450	EUR MEA US APAC



Visit 3M.com for other 3M Protective Coveralls

Global Reach & Technical Support

At 3M, we connect with customers around the world every minute of every day. We work across borders in cross-cultural teams with a focused, global mindset and local perspectives, proudly conducting business activities in over 200 countries.

- | | | | |
|--|---|---|---|
| <ul style="list-style-type: none"> • ◆ ■ Canada <ul style="list-style-type: none"> • Jamaica • Dominican Republic • Puerto Rico • ◆ ■ México <ul style="list-style-type: none"> • Guatemala • El Salvador • ◆ Costa Rica <ul style="list-style-type: none"> • Trinidad & Tobago • ◆ ■ Colombia <ul style="list-style-type: none"> • Panama • ◆ ■ Venezuela <ul style="list-style-type: none"> • Ecuador • ◆ ■ Brazil <ul style="list-style-type: none"> • Perú • Chile • ◆ ■ Argentina <ul style="list-style-type: none"> • Uruguay | <ul style="list-style-type: none"> • ◆ ■ UK • ◆ ■ Netherlands • ◆ ■ Germany <ul style="list-style-type: none"> • Denmark • Czech Republic • Norway • ◆ ■ Sweden <ul style="list-style-type: none"> • Estonia • Finland • Latvia • Lithuania • ◆ ■ Poland <ul style="list-style-type: none"> • Switzerland • Austria • Hungary • Ukraine • Romania • ◆ ■ Russia | <ul style="list-style-type: none"> • ◆ ■ China <ul style="list-style-type: none"> • Korea • Japan <ul style="list-style-type: none"> • Hongkong • ◆ ■ Taiwan • ◆ ■ Philippines • ◆ ■ Vietnam • ◆ ■ Thailand • ◆ ■ Malaysia • ◆ ■ Singapore • ◆ ■ Australia <ul style="list-style-type: none"> • New Zealand • ◆ ■ Indonesia • ◆ ■ India <ul style="list-style-type: none"> • Sri Lanka • Pakistan • Kazakhstan | <ul style="list-style-type: none"> • UAE • Israel • Kenya • Egypt • ■ South Africa • ◆ ■ Turkey • Greece • ◆ ■ Italy • ◆ ■ Belgium • Morocco • ◆ ■ France • Portugal • ◆ ■ Spain |
|--|---|---|---|



Personal Safety Division
 Building 235-2W-70
 St. Paul, MN 55144-1000
 United States
 Phone 800.328.1667
 Web 3M.com/PPESafety

West Europe
 3M Centre Cain Road,
 Bracknell, Berkshire RG12 8HT
 United Kingdom
 Phone +44 (0)1244 858000
 Web 3M.eu/PPESafety

China
 38th Floor, Mandu Center,
 No. 8 Xingyi Road,
 Hongqiao Development Zone,
 Shanghai 200336
 Phone 86-21-62753535
 Web 3M.com.cn

India
 3M Research and Development Centre
 No. 48-51, Electronic City,
 Bangalore 560 100, Karnataka, India
 Phone 1 800 425 3030
 Web 3M.com/IN_PPESafety

Visit 3M.com for additional country contact information.

Region Availability Legend:

- US = United States
- CA = Canada
- EUR = Europe (Western & Central)
- MEA = Middle East, Africa
- APAC = Asia Pacific
- LA = Latin America (Central and South)

Product availability may differ between countries within a region.
 Contact 3M local country or region office on product availability.

WARNING

Respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions. Follow all local regulations. Misuse may result in sickness or death. For correct use, consult supervisor and User Instructions, or call 3M.

3M PSD products are for occupational use only.



3M India Ltd
 3M Research and Development Centre
 No. 48-51, Electronic City,
 Bangalore 560 100 | Karnataka | India
 Customer Care - 1800 425 3030
 Email: 3mpersonalsafety.in@mmm.com
 Web: www.3mindia.in/3M/en_IN/p/c/ppe/respiratory-protection/