

3M-Matic™ Case Sealer 8000af/ 8000af3 with 3M™ AccuGlide™ 3 Taping Head

3M-Matic™ Case Sealer 8000af/8000af3 with 3M™ AccuGlide™ 3 Taping Head is an automatic flap folding machine that seals both the top and bottom of a box without an operator. The 3M-Matic™ Case Sealer 8000af/8000af3 folds the top flaps prior to sealing with either 48mm or 72mm wide tape.

- Energy Savings Feature automatically shuts sealer off if no box is present
- Integrated box gate (indexer) with adjustable pressure and height to separate boxes from flooded infeed conveyor
- One centrally-located emergency stop on each side for quick and easy access
- Safety-interlocked hinged access doors with steel screen for viewing case flow
- Consistent durable taping that is manually adjusted for a wide range of box sizes
- Welded 16-gauge steel construction for durability
- Upper flap folding eliminates need for an operator
- Two-height drive belt positions



Operating Rate

Seals up to 40 cases per minute

Box Capacities

Length: 6.0" to 30.0"


Width: 4.75" to 21.5" (8000af)
5.75" to 21.5" (8000af3)

Height: 3.75" to 28.5"

Weight: 5 to 85 lbs.

Consistent. Reliable. Tough.

3M-Matic™ Case Sealer 8000af/8000af3 with 3M™ AccuGlide™ 3 Taping Head



Specifications

Machine	Tape Size (mm)	Machine Weight* lbs. (kg)	Machine Dimensions in. (mm)									Power Requirements		Operating Rate (cs/min)	Belt-Drive Speed ft/min (m/s)
			W	L1	L2	H (min)	H (max)	B (min)	B (max)	C**	F	Electrical	Air		
8000af	36-48	820	45.8	75.6	138	62	86	24	35	5.25	32.5	115V 60Hz 3.8A	2.5 SCFM	Up to 40	100 (0.5)
8000af3	48-75	(370)	(1163)	(1920)	(3505.2)	(1575)	(2184)	(610)	(889)	(133)	(826)	440 watts 8 ft. cord	@ 85 PSIG		

*Uncrated ** Optional casters

Use with clean, dry boxes in dry, relatively clean environments at 40-120°F (4.4-48.9°C)

Box Capacities

Machine	Minimum (inches)			Maximum (inches)			Weight Range (lbs)
	L	W	H	L	W	H	
8000af	6.0	4.75	3.75	30.0	21.5	28.5	5-85
8000af3	6.0	5.75	3.75	30.0	21.5	28.5	



Contact your 3M representative for special modifications that may be available for sizes not listed.

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

Visit [3M.com/packaging](https://www.3m.com/packaging) for more information



Closure and Masking Systems Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000

Phone 800-362-3550
Fax 877-369-2923
Web [3M.com/Packaging](https://www.3m.com/Packaging)

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. **Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M, 3M-Matic and AccuGlide are trademarks of 3M Company. Please recycle. Printed in USA.
© 3M 2022. All rights reserved. 70-0710-0495-9 Rev 8/22