



900DZ

Premium Series

Xtract™

Clean Sanding Solutions

CUBITRON™ II
Industrial Abrasives

Sand less.
Make more.

3M Xtract™ Cubitron™ II Cloth Disc 900DZ

3M™ Cubitron™ II Cloth Disc 900DZ


Up to
99% dust
extraction*

Fast Cut
Increased throughput
with faster sanding
and more parts per
disc

Lasts
Longer*
Lower costs with long
disc life and fewer
disc changes

* Applies to 3M Xtract™ multihole discs.

* Compared to conventional abrasives.



3M Xtract™ Cubitron™ II Cloth Disc 900DZ

3M™ Cubitron™ II Cloth Disc 900DZ

900DZ
Premium Series

Durable, fast-cutting, long lasting with improved dust extraction.


Fast and effective cutting action on a variety of materials, 3M Xtract™ Cubitron™ II Cloth Disc 900DZ and 3M™ Cubitron™ II Cloth Disc 900DZ are built for tough sanding jobs. This abrasive is designed to reduce time-costly operation. It features 3M Precision-Shaped Grain that cuts fast and lasts longer than conventional abrasives. The open coat construction prevents the mineral from loading, resulting in a longer life abrasive disc that continues to cut, even when working on surfaces that would normally hinder sanding ability. It can be used on wood, metals and composites in applications requiring heavy stock removal. Finer grades are suitable for blending and finishing aluminum, hardwoods, softwoods and composites.

- Tough and durable cloth backing combines wear-resistance with flexibility
- Versatile disc performs well on aluminum, fiberglass, gelcoat, hard and soft woods
- 3M™ Hookit™ attachment system provides easy disc changes and optimises disc life




For best results, pair with a 3M Xtract™ Back-up Pad (multi-hole) and a Random Orbital Sander with vacuum*

*Both sold separately



3M Xtract™ proprietary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity and provide a cleaner work environment.



J-weight cloth backing combines wear-resistance with flexibility.

Ordering Information

3M Xtract™ Cubitron™ II Cloth Disc 900DZ

3M™ Cubitron™ II Cloth Disc 900DZ

75 mm				125 mm				150 mm			
ID	Grade	Per inner	Discs per case	ID	Grade	Per inner	Discs per case	ID	Grade	Per inner	Discs per case
no hole				no hole				no hole			
7100284768	40+	50	250	7100284663	40+	50	250	7100284772	40+	50	250
7100284269	60+	50	250	7100284212	60+	50	250	7100284214	60+	50	250
7100284510	80+	50	250	7100284210	80+	50	250	7100284610	80+	50	250
7100284511	120+	50	250	7100284525	120+	50	250	7100284566	120+	50	250
7100284519	150+	50	250	7100284535	150+	50	250	7100284574	150+	50	250
7100282480	180+	50	250	7100281808	180+	50	250	7100282301	180+	50	250
7100282509	220+	50	250	7100281801	220+	50	250	7100281805	220+	50	250
7100284509	320+	50	250	7100284512	320+	50	250	7100284609	320+	50	250
multihole				multihole				multihole			
7100284886	40+	50	250	7100284662	40+	50	250	7100284769	40+	50	250
7100284341	60+	50	250	7100284216	60+	50	250	7100284218	60+	50	250
7100284521	80+	50	250	7100284531	80+	50	250	7100284530	80+	50	250
7100284266	120+	50	250	7100284520	120+	50	250	7100284508	120+	50	250
7100284506	150+	50	250	7100284353	150+	50	250	7100284342	150+	50	250
7100282513	180+	50	250	7100282219	180+	50	250	7100281804	180+	50	250
7100282510	220+	50	250	7100281811	220+	50	250	7100281806	220+	50	250
7100284356	320+	50	250	7100284268	320+	50	250	7100284271	320+	50	250

Additional options for sizes, hole configurations, and backing types, such as Stikit, are available. For further information, please contact your local 3M Distributor.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and

standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.


© 3M 2024 All rights reserved. 3M, Cubitron, and 3M Xtract, and the unique hole pattern are trademarks of 3M Company.

Dust and Swarf Neutralised

An anti-static treatment neutralises the static charge generated by sanding, especially on wood. Electrically charged swarf tends to cling to the surface of the disc, the workpiece and the machinery when sanding.

Dust degrades performance and productivity. When used with an effective dust collection system, the anti-static properties help manage dust.

3M CUBITRON™ II Industrial Abrasives



3M™ Cubitron™ II Abrasives are designed with revolutionary 3M Precision-Shaped Grain technology. As the grain wears, it continuously fractures to form sharp points and edges that slice through material, wear evenly and provide super-long life and consistency.



3M United Kingdom PLC
3M Centre
Cain Road, Bracknell, RG12 8HT
Tel: +44 8705 360036
abrasives.uk@mmm.com
www.3M.co.uk/abrasives

3M Ireland Limited
The Iveagh Building
The Park
Carrickmines
Dublin 18, Ireland
Tel: +353 1800 303 437