



3M™ Bright Screen Privacy Filter

Description

3M™ Bright Screen Privacy Filters use nanolouver technology that powers a premium visual experience, perfectly balancing privacy, best-in-class brightness and exceptional clarity.

Applications

3M Bright Screen Privacy Filters deliver world-class effective “blackout” privacy from side views outside the 60-degree viewing angle. Whether in the office or at home, it effortlessly helps keep what’s on your screen private.

A reversible solution, 3M™ Privacy Filters provide a gloss option or a matte option that add an extra layer of protection from everyday scratches and dust.

Effectiveness

Offers world-class privacy without significantly darkening your screen, while still enjoying the same 60-degree privacy cutoff angle. Up to 25% brighter than the standard black privacy filters.*

Product Features

- Up to 85% more transmission of light*
- Reversible between a glossy side and a glare reducing matte
- Adds an extra layer of protection from everyday scratches and dust
- Nanolouver technology that powers a premium visual experience, perfectly balancing privacy and best-in-class brightness
- Ultra-thin and responsive to touch, one of our thinnest privacy filters

Typical Properties

Technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

Property	Typical Value
Viewing Angle	60 degrees
Transmission	Up to 85% more transmission of light*
Thickness	0.290 mm

Environmental Testing	Condition
Heat Resistance	65°C for 240 hours
Cold Resistance	-30°C for 240 hours
Humidity Resistance	40°C, 95% RH for 240 hours
Thermal Shock	-20°C for 1 hr to 60°C for 1 hr, 5 cycles

Metric After Environmental	Typical Value
Appearance	No significant change between previous and post environmental testing

Shelf Life and Storage (prior to application)

Material should be stored in its original packaging, laying in a horizontal orientation, away from direct sunlight. Heavy objects should not be placed on top of it to avoid damaging the product. Ambient temperature and humidity should be controlled to 10-30°C at 35-65% relative humidity.



Cleanability

Durable privacy filter that can withstand hundreds of cleanings.*

Availability

For availability, please contact our customer service group at 1-800-553-9215, DMSDcustomerservice@mmm.com, or visit our website at 3Mscreens.com.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

*As determined by 3M internal laboratory testing.



3M Display Materials & Systems Division

3M Center, Building 235-1E-54
St. Paul, MN 55144-1000 U.S.A.

Phone 800-553-9215
Web www.3Mscreens.com

3M is a trademark of 3M Company.
© 3M 2024. All rights reserved.
75-0501-4124-3-B