

3M Science.
Applied to Life.™

Discover 3M's next-generation reusable full face mask.

Introducing the
3M™ Secure Click™
Reusable Full Face
Mask FF-800 Series.



Introducing the 3M™ Secure Click™ Reusable Full Face Mask FF-800 Series

Designed with smart and intuitive features, the 3M™ Secure Click™ Reusable Full Face Mask FF-800 Series helps protect workers from particulates and a wide variety of gases and vapors when used with approved 3M™ Secure Click™ filters and cartridges.



3M™ Secure Click™ Reusable Full Face Mask FF-800 Series

Product: FF-801/FF-802/FF-803

Size: Small/medium/large



Hear it:

3M™ Secure Click™ connection helps provide confidence that filters are installed properly. Simply align the connections and push into place.



Check it:

Help increase worker confidence that the respirator is being worn properly with the easy, one-touch, user seal check.



Feel it:

Experience the breathability and comfort provided by the world's first quad-flow gas and vapour filter/combination filter systems.



Say it:

Utilise the speaking diaphragm to help provide easy communication.



Full face masks	
Product	Description
FF-801	3M™ Secure Click™ Reusable Full Face Mask, Small, FF-801
FF-802	3M™ Secure Click™ Reusable Full Face Mask, Medium, FF-802
FF-803	3M™ Secure Click™ Reusable Full Face Mask, Large, FF-803

Particulate filters	
Product	Description
D3125	3M™ Secure Click™ Particulate Filter, P2 R, D3125
D3135	3M™ Secure Click™ Particulate Filter, P3 R, D3135
D3128	3M™ Secure Click™ Particulate Filter with Nuisance Level Organic Vapour and Acid Gas Relief, and Ozone up to 10 x WEL, P2 R, D3128
D3138	3M™ Secure Click™ Particulate Filter with Nuisance Level Organic Vapour and Acid Gas Relief, and Ozone up to 10 x WEL, P3 R, D3138

Gas and vapour filters	
Product	Description
D8059	3M™ Secure Click™ Gas and Vapour Filter, A1B1E1K1, with Dual Flow, D8059
D8057	3M™ Secure Click™ Gas and Vapour Filter, A1B1E1, with Dual Flow, D8057
D8055	3M™ Secure Click™ Gas and Vapour Filter, A2, with Dual Flow, D8055
D8051	3M™ Secure Click™ Gas and Vapour Filter, A1, with Dual Flow, D8051

Particulate filters – compatible with gas and vapour filters	
Product	Description
D701	3M™ Secure Click™ Reusable Respirator Filter Retainer, D701
D7915	3M™ Secure Click™ Particulate Filter, P1 R, D7915
D7925	3M™ Secure Click™ Particulate Filter, P2 R, D7925
D7935	3M™ Secure Click™ Particulate Filter, P3 R, D7935

Combination filters	
Product	Description
D8097	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1+Hg P3 R, with Dual Flow, D8097
D8095	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A2 P3 R, with Dual Flow, D8095
D8094	3M™ Secure Click™ Gas, Vapour and Particulate Filter, A1B1E1K1 P3 R, with Dual Flow, D8094

Fit test adapters	
Product	Description
FF-800-06	3M™ Secure Click™ Quantitative Fit Test Adapter, FF-800-06

Spare parts and accessories	
Product	Description
FF-400-01	3M™ Secure Click™ FF-800 Series Buckle FF-400-01, 30 ea/case
FF-400-02	3M™ Secure Click™ FF-800 Series Button FF-400-02, 30 ea/case
FF-400-06	3M™ Secure Click™ FF-800 Series Comfort Cradle Head Harness Attachment FF-400-06, 5 ea/case
FF-400-07	3M™ Secure Click™ FF-800 Series Exhalation Valve Assembly FF-400-07, 5 ea/case
FF-400-11	3M™ Secure Click™ FF-800 Series Nose Cup Assembly FF-400-11, 5 ea/case
FF-400-13	3M™ Secure Click™ FF-800 Series Speaking Diaphragm Assembly FF-400-13, 5 ea/case
FF-800-01	3M™ Secure Click™ Lens Replacement FF-800-01, 5 ea/case
FF-800-02	3M™ Secure Click™ Lens Frame Assembly FF-800-02, 5 ea/case
FF-800-03	3M™ Secure Click™ Inhalation Valve Assembly FF-800-03, 10 ea/case
FF-800-04	3M™ Secure Click™ Exhalation Valve Cover Assembly FF-800-04, 5 ea/case
FF-800-05	3M™ Head Harness FF-800-05, 5 ea/case
7582	3M™ Inhalation Valve, 7582, 10 ea/bag
6583	3M™ Exhalation Valve, 6583, 10 ea/case
FF-400-15	3M™ Secure Click™ FF-800 Series Lens Cover FF-400-15, 100 ea/bag
FF-400-17	3M™ Secure Click™ FF-800 Series Semi-Permanent Lens Protector FF-400-17, 20 ea/case
FF-400-18	3M™ Secure Click™ FF-800 Series Stacked Lens Cover FF-400-18, 20 ea/case
6886	3M™ Tinted Lens Covers 6886, 25 ea/Bag
FF-800-06	3M™ Secure Click™ Quantitative Fit Test Adapter Kit FF-800-06, 1 ea/case
102	3M™ Universal Spectacle Kit, 102
FF-400-25	3M™ Secure Click™ FF-800 Series Reusable Nylon Respirator Storage Bag FF-400-25 10 ea/case



Personal Safety Division
3M Centre, Cain Road
Bracknell, Berkshire
RG12 8HT
United Kingdom

3M Ireland Limited
The Iveagh Building
Carrickmines Park
Carrickmines
Dublin 18

Tel: 0870 60 800 60 (UK)
Tel: 1800 320 500 (Ireland)
www.3M.co.uk/respiratory