

Filter Conversion Guide for 3M™ Secure Click™ Reusable Half Mask HF-800 Series and Full Face Mask FF-800 Series.

Designed with smart and intuitive features, the 3M™ Secure Click™ Reusable Half Mask HF-800 and Full Face Mask FF-800 helps protect workers from particulates and a wide variety of gases and vapours when used with approved 3M™ Secure Click™ filters shown below.

If you are currently using a 3M respirator with a bayonet connection, this guide will offer conversion suggestions to help you transition to 3M™ Secure Click™.



<p>Bayonet connection</p> <p>3M™ Secure Click™</p> <p>CE approved for:</p>	<p>Gas and vapour filters</p> <p>6051 A1 6055 A2 6057 ABE1 6059 ABEK1</p>	<p>Combination filters</p> <p>6092 ABEK3 R 6091 A2P3 R</p>
	<p>D8051 A1 D8055 A2 D8057 ABE1 D8059 ABEK1</p> <p>Certain organic vapours with BP > 65 °C</p>	<p>D8094 ABEK3 R D8097 ABEK3Hg R D8095 A2P3 R</p> <p>Certain organic vapours (BP > 65 °C), inorganic vapour, acid gas, ammonia and particulate</p>
<p>Bayonet connection</p> <p>3M™ Secure Click™</p> <p>CE approved for:</p>	<p>Particulate filters</p> <p>2125 P2 R 2135 P3 R</p>	<p>Particulate filters with nuisance level organic vapour and acid gas protection and ozone up to 10 x OEL</p> <p>2128 P2 R Nuisance Organic Vapour and Acid Gas 2138 P3 R Nuisance Organic Vapour and Acid Gas</p>
	<p>D3125 P2 R D3135 P3 R</p> <p>Particulates</p>	<p>D3128 P2 R/Nuisance Organic Vapour and Acid Gas D3138 P3 R/Nuisance Organic Vapour and Acid Gas</p> <p>Particulates</p>
<p>Bayonet connection</p> <p>3M™ Secure Click™</p> <p>CE approved for:</p>	<p>Hard case particulate filters</p> <p>6035 P3 R 6038 P3 R</p>	<p>Replaceable filter retainer</p> <p>Filter Retainer 501 5911 P1 R 5925 P2 R 5935 P3 R</p>
	<p>D9035 P3 R D9038 P3 R</p> <p>Particulates</p>	<p>Filter Retainer D701 D7915 P1 R D7925 P2 R D7935 P3 R</p> <p>Particulates</p>