

Solutions for welding and grinding hazards



Welding fumes



Exposure to radiation

- Welding exposes workers to toxic fumes.
- Overexposure can cause chronic health issues.
- Exposure to excessive ultraviolet (UV) radiation can lead to arc-eye in welders.
- Long-term over-exposure to arc radiation is linked to retinal burns, cataracts and skin cancer.



3M™ Particulate Welding Respirator 8515, N95
[Learn more](#)



3M™ Particulate Respirator 8210, N95
[Learn more](#)



3M™ Aura™ Particulate Respirator 9322A+, FFP2
[Learn more](#)



3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator 6502QL
[Learn more](#)



3M™ Secure Click™ Particulate Filter, P3 R, D3135
[Learn more](#)



3M™ Secure Click™ Half Facepiece Reusable Respirator with Speaking Diaphragm HF-802SD
[Learn more](#)



3M™ Particulate Filters 2135, P3R
[Learn more](#)



Noise Exposure

- Noise-Induced Hearing Loss is one of the most common industrial illnesses in the world.
- Often unnoticeable in the early stages and unfortunately permanently irreversible.



3M™ E-A-R™ Flexible Fit Earplug HA 328-1001, Corded
[Learn more](#)



3M™ E-A-R™ Flexible Fit Earplug HA 328-1000, Uncorded
[Learn more](#)



3M™ PELTOR™ Optime™ III Earmuffs
[Learn more](#)



3M™ PELTOR™ X4 Earmuffs
[Learn more](#)



3M™ PELTOR™ Earmuffs X4P5E, Hard-Hat Attached
[Learn more](#)

Solutions for painting and coating hazards



Vapour particulate Hazard

- Operations during painting and powder coating create respirable and inhalable dusts, mists, gases and vapours.



3M™ Secure Click™ Half Facepiece Reusable Respirator with Speaking Diaphragm HF-802SD
[Learn more](#)



3M™ Secure Click™ AIB1E1K1 Filter, D8059
[Learn more](#)



3M™ Secure Click™ Filter Retainer D701
[Learn more](#)



3M™ Secure Click™ Particulate Filter P2 R, D7925
[Learn more](#)



3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator 6502QL
[Learn more](#)



3M™ Gas and Vapour Filters 6059, ABEK1
[Learn more](#)



3M™ Filter Retainer 501
[Learn more](#)



3M™ Particulate Filters 5935, P3R
[Learn more](#)



3M™ Versaflo™ Heavy Industry PAPR Kit TR-600-HIK
[Learn more](#)



Eye Injuries

- Exposure to flying particles, liquid splash, mists, over-spray and gases/vapours and ultra-violet light from curing lamps



3M™ SecureFit™ Protective Eyewear SF301AF, Clear Anti-Fog Lens
[Learn more](#)



3M™ Safety Goggles 1621AF, Polycarbonate Lens for Splash
[Learn more](#)



3M™ SecureFit™ Safety Glasses SF401SGAF-BLU, Blue/Gray, Clear Scotchgard™ Anti-fog Lens
[Learn more](#)



3M™ Safety Goggles 1623AF, Wrap-around Design Anti-Fog Coat Hard-coated Polycarbonate Lens
[Learn more](#)

Solutions for confined space hazards



Atmospheric hazards

- Workers are exposed to combustible dust, hazardous chemicals and oxygen deficiency.



3M™ Scott™ Flite COV Airline Breathing Apparatus
[Learn more](#)



3M™ Scott™ Vision 3 Positive Pressure Facemask
[Learn more](#)



3M™ Scott™ ELSA Emergency Life Support Apparatus
[Learn more](#)



3M™ Scott™ ProPak-fx Self-Contained Breathing Apparatus
[Learn more](#)



3M™ Modular Airline Trolley System
[Learn more](#)



Physical Hazards

- Workers are exposed to hazardous working conditions that present potential for falls.



3M™ DBI-SALA® 5-Piece Hoist System
[Learn more](#)



3M™ DBI-SALA® Confined Space Pole Hoist System 8530252
[Learn more](#)



3M™ DBI-SALA® Confined Space Aluminium Tripod 8000000
[Learn more](#)



3M™ Protecta® Nano-Lok™ Personal Self Retracting Lifeline, Twin-leg, Web, 3101719
[Learn more](#)



3M™ Protecta® P200 Vest Climbing Safety Harness 1161610
[Learn more](#)

Solutions for working at height hazards



Falls from height

- Working at height comes with challenges of falls from ladders, scaffolds and MEWPs



3M™ DBI-SALA® Lad-Saf™ Cable Vertical Safety System
[Learn more](#)



3M™ DBI-SALA® Lad-Saf™ Detachable Cable Sleeve, 3/8 in. (9.5 mm) 6160054
[Learn more](#)



3M™ DBI-SALA® Roofsaf Anchor and Cable System
[Learn more](#)



3M™ DBI-SALA® Nano-Lok™ Personal Self Retracting Lifeline, Twin-leg, Web, 3101719
[Learn more](#)



3M™ DBI-SALA® Sliding Beam Anchor 2104710, Small
[Learn more](#)



3M™ DBI-SALA® FlexiGuard™ A-Frame System
[Learn more](#)



3M™ DBI-SALA® Fixed Ladder SRL Anchor 6100565, 6', Stainless Steel
[Learn more](#)



3M™ Protecta® Self Retracting Lifeline 3590628, Stainless Steel Cable, 15m
[Learn more](#)



3M™ Protecta® P200 Vest Climbing Safety Harness 1161610
[Learn more](#)



3M™ Protecta® First™ Twin Leg Shock Absorbing Rope Lanyard
[Learn more](#)



3M™ DBI-SALA® Vacuum Anchor Lifeline System
[Learn more](#)