

3M™ Trizact™ Pad Conditioner T Series B25T-2910

Product Description

3M™ Trizact™ Pad Conditioner T Series B25T-2910 uses precisely engineered three dimensional microreplicated ceramic structures coated with CVD diamond. The microreplicated structures provide consistent performance disk-to-disk and the metal-free cutting surface is ideal for advanced node process sensitive to metallic contamination. 3M™ Trizact™ Diamond Pad Conditioner T Series has CMP control, consistency, cost of ownership and customization in mind, and benefits from collaboration with 3M’s global technical capability and manufacturing capacity.


3M™ Trizact™ Pad Conditioner T Series disks are available in multiple sizes and configurations to fit most new and legacy CMP tools.

Key Features

- CVD diamond coated ceramic microreplicated surface to deliver precision and control
- Consistent disk-to-disk performance which reduces variability of CMP processes
- Metal-free cutting surface, ideal for advanced node processes sensitive to metallic contamination
- New, rougher CVD diamond coating technology for more stable removal rate and longer lifetime

Product Construction/Material Description

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.




Scanning Electron Microscope (SEM) image of the 3M™ Trizact™ Pad Conditioner T Series B25T-2910 microreplicated surface

3M™ Trizact™ Pad Conditioner T Series Design Parameters B25T-2910

Diamond film thickness	3~10 microns
Co-planarity : Tip count	387~639
Co-planarity : Max angle	≤0.215 deg
Mean Depression Angle (MDA):	0.461~0.581 rad

3M™ Trizact™ Pad Conditioner T Series B25T-2910


3M™ Trizact™ Pad Conditioner T Series B25T-2910-5S2 Backside



3M™ Trizact™ Pad Conditioner T Series B25T-2910-5S2 Construction

Carrier Material	304 SS
Carrier Size (Diameter, Nominal Size)	4.25 in
Abrasive Material	CVD coated ceramic
Abrasive Working Surface	B25T-2910 pattern

3M™ Trizact™ Pad Conditioner T Series B25T-2910-5S1 Backside



3M™ Trizact™ Pad Conditioner T Series B25T-2910-5S1 Construction

Carrier Material	410 SS
Carrier Size (Diameter, Nominal Size)	4 in
Abrasive Material	CVD coated ceramic
Abrasive Working Surface	B25T-2910 pattern

Storage and Shelf Life

The shelf life of 3M™ Trizact™ Pad Conditioner T Series B25T-2910 is 2 years from the date of manufacture when stored in the original packaging materials and stored at 21°C (70°F) and 50% relative humidity.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains the 3M test methods, specifications limits and test results for the product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

3M™ Trizact™ Pad Conditioner T Series B25T-2910

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specifications on the Certificate of Analysis, which is established when the product is manufactured and deemed commercially available and is provided at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.** If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.



Electronics Materials Solutions Division
3M Center, Building 224-3N-11
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
©3M 2023. All rights reserved.
60-5005-0422-4