

Expandable Slot Liner

Intended Use: These products are intended for use within electric motors to electrically insulate coil conductor from adjacent conductor or ground in automotive, off-highway, industrial and marine applications. Since there are many factors that can affect a product's use, the customer remains responsible for determining whether the 3M product is suitable and appropriate for the customer's specific application and system, including customer conducting an appropriate risk assessment and evaluating the 3M product in customer's application and system.

Restricted Use: 3M advises against the use of this 3M product in any application other than the stated intended use(s), since other applications have not been evaluated by 3M and may result in an unsafe or unintended condition.



Automotive and Aerospace Solutions Division

3M Center, Building 224-6NE-45

St. Paul, MN 55144-1000

Phone: 1-800-328-1684

Web: www.3M.com/evbattery

3M is a trademark of 3M Company

Please recycle. Printed in USA © 3M 2022

All rights reserved.