

Flex your creativity.

What if you had attachment methods that helped you realize your design vision without compromise? Every design requires a choice from a menu of options, and there are many applications where 3M™ Acrylic Foam Tapes make sense for your exterior trim needs.

How can 3M tapes enable design freedom?

-  **Material flexibility.** Compatible with a wide range of substrates and materials, including LSE surfaces.
-  **Proven products.** A long history of real-world and lab-tested performance.
-  **Strong support.** From technical consulting and training to prototyping and production consultation.
-  **Small parts.** Seamless attachment where other options might add bulk or damage small parts.
-  **Trusted data.** Customized testing before you implement tapes.
-  **Plastic on plastic.** Where drilling holes isn't optimal and ultrasonic welding might warp parts.
-  **Thin materials.** Where ultrasonic welding could cause read-through effects.
-  **Running changes.** For late-breaking changes, tapes can save the day.
-  **Supplementing clips.** Use in conjunction with clips to add a seal and extra support.



- 1 Emblems and lettering.**
Die cutting allows for precise bonding of badges, insignia and more.
- 2 Sensors.**
Attach sensors and sensor frames to a wide range of exterior surfaces.
- 3 Trim levels.**
Differentiate trim levels without making drastic design or assembly changes.