

Scotch®

Electrical Tape

The Electrical Tape

For excellent electrical insulation and moisture protection.

Scotch® Rubber Mastic Tape 2228

Professional Grade



Used for electrical insulating and moisture sealing applications, Scotch® Rubber Mastic Tape 2228 is a conformable self-fusing rubber electrical insulating and sealing tape with an EPR backing coated with mastic adhesive. This 2228 tape is suitable for low, medium and high voltage use.

Product Highlights:


- Thick construction allows quick application build-up and padding over irregular connections
- Compatible with solid dielectric cable insulations
- Self-fusing tape
- Flexible over wide temperature range up to 90°C
- Provides protection against UV rays with its ethylene propylene rubber backing
- Excellent adhesion and sealing characteristics with copper, aluminum and power cable jacket materials
- RoHS 2011/65/EU Compliant



Insulate cable drops



Splice cables in overhead cable trays



Moisture seal in wet environments



Splicing and sealing in outdoor areas

3M

3M United Kingdom PLC
3M Centre
Cain Road, Bracknell
Berkshire RG12 8HT
www.3m.co.uk

Suomen 3M Oy
Keilaniementie 1
02150 ESPOO
PL 600, 02151 ESPOO
puh. 09 525 21 Finland
www.3msuomi.fi

3M Ireland Limited
The Iveagh Building
Carrickmines Park,
Carrickmines, Dublin 18
www.3mireland.ie

3M Norge AS
Tærudgata 16
2004 Lillestrøm
Norway
www.3mnorge.no

3M a/s
Hannemanns Allé 53
DK-2300 København S
Denmark
www.3mdanmark.dk

3M Svenska AB
Herrjärvatorg 4
170 67 Solna
Sweden
www.3msverige.se

Important Notice: Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

©3M 2023. All rights reserved. 3M, Scotchflex, Super 33+, Dynatel and Scotch are trademarks of 3M Company.