

3M™ Liqui-Cel™ SP-4×28 Series Membrane Contactor

Typical Properties

Membrane Characteristics		
Cartridge Configuration	Extra-Flow with Centre Baffle	
Liquid Flow Guidelines	1.1-6.8 m³/hr (5-30 gpm) Liquid must flow on the shellside	
Membrane/Potting Material	Polyolefin / Polyethylene	
Priming Volume (approximate)	Polypropylene	316L SS
Shellside	2.9 L (0.8 gal)	2.9 L (0.8 gal)
Lumenside	0.9 L (0.2 gal)	0.7 L (0.2 gal)

Pressure Guidelines*	
Maximum Shellside <u>LIQUID</u> Working Temperature/Pressure	Polypropylene
	5-25°C, 4.1 barg (41-77°F, 60 psig) 40°C, 1.0 barg (104°F, 15 psig)
	316L SS
	5-25°C, 4.1 barg (41-77°F, 60 psig) 50°C, 1.0 barg (122°F, 15 psig)
If no vacuum is used, 1 barg (15 psig) can be added to pressures above.	
Maximum Applied Gas Pressure	4.1 barg at 25°C (60 psig at 77°F)
* See Operating Guide for complete temp/pressure limits for housings and membrane. Note: Liquid pressure should always exceed gas pressure.	


Housing Characteristics		
Material	Polypropylene	316L SS
Flange Connections		
Shellside (Wetted surface)	<ul style="list-style-type: none"> • 1 inch Sanitary • ¾ inch NPT Female • Rc ¾ per JIS B0203 	• 1 inch Sanitary
Lumenside (Gas/Vacuum)	<ul style="list-style-type: none"> • 1 inch 90° Sanitary • ¾ inch 90° NPT Female • Rc ¾ per JIS B0203 	• 1 inch Sanitary

Seal Material Options	Applications
FKM	General Purpose
FFKM (K - UPW)**	Ultra Pure Water
**Only available in PP housing with NPT connections.	

Weight (approximate)	Polypropylene	316L SS
Dry	4 kg (9 lbs)	7 kg (16 lbs)
Water-filled	7 kg (16 lbs)	10 kg (22 lbs)



Regulatory
Complies with the limits as set by (EU) 2015/863 amending Annex II to the Restriction on Hazardous Substances (RoHS) Directive (2011/65/EU). 3M™ Liqui-Cel™ SP-4×28 Series Membrane Contactors with FKM seals are constructed of FDA Title 21 CFR § 177-190 compliant materials for wetted parts only at ambient temperatures. 3M™ Liqui-Cel™ SP-4×28 Series Membrane Contactors with FFKM (K-UPW) seals are not constructed of FDA Title 21 CFR § 177-190 compliant materials.

Not for consumer sale or use.



All dimensions are nominal values for the polypropylene housing with NPT connections. See full housing drawing on 3M.ca/Liqui-Cel for additional details.

3M™ Liqui-Cel™ SP-4x28 Series Membrane Contactor



Curves represent nominal values, generated using water at 25°C (77°F).

Test condition: O₂ Removal with 50 torr abs vacuum.

Characteristics may change under different operating conditions.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M, 3M Science. Applied to Life. and Liqui-Cel are trademarks of 3M. Used under license in Canada. © 2023, 3M. All rights reserved. 2212-25352c E



3M Separation and Purification Sciences Division
3M Company
300 Tartan Drive
London, Ontario N5V 4M9
Canada
1-800-443-1661

LC-1082
Rev. 02/2021

[3M.ca/Liqui-Cel](https://www.3m.ca/Liqui-Cel)