



Testable with the
3M™ E-A-Rfit™
Validation System



AS/NZS 1270
Lic. SMK1147

3M™ E-A-Rsoft™ Yellow Neons™ Disposable Foam Earplugs

Technical Data Sheet

Product description

The E-A-Rsoft™ Yellow Neon™ disposable foam earplugs are designed for insertion into the ear canal to help reduce exposure to hazardous levels of noise. These products are available in both corded and uncorded versions.

The uncorded version is also available in refill bottle for the 3M™ E-A-R™ One Touch™ Pro Earplug Dispenser.



Features

- Complies with Australian/New Zealand Standard AS/NZS 1270:2002
- Slow expanding polyurethane foam helps make it easier to insert the earplug into the ear once it is properly rolled down into a crease free cylinder
- Extremely soft foam helps provide increasing comfort and wearability
- Multiple size earplug offering (regular and large) help fit a broad range of ear canal sizes
- Tapered shape conforms quickly to most ear canals
- Compatible with E-A-Rfit™ Dual Ear Validation System
- Vibrant bright colour
- Supplied in polybag or dispenser refills
- Available in both corded and uncorded versions
- SLC₈₀ 23dB (Class 4)

Applications

The E-A-Rsoft™ Yellow Neons™ disposable are ideal for a wide range of industrial workplace and leisure environments. Examples of typical applications include:

- Automotive
- Chemical & pharmaceutical manufacture
- Construction
- Heavy engineering
- Metal processing
- Textile manufacture
- Woodworking

Standards

These hearing protectors have been produced to comply with the requirements of the Australian /New Zealand Standard AS/NZS 1270:2002.

Laboratory Attenuation Values

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean (dB)	21.9	22.2	24.5	25.7	31.3	42.7	42.5
SD (dB)	8.1	7.4	7.7	6.2	4.8	5.5	7.9
Mean - SD (dB)	13.8	14.8	16.8	19.5	26.5	37.2	34.6

SLC₈₀ 23dB (Class 4)

Hearing protector Class 4 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269, this protector may be used in noise 100dB(A) to less than 105dB(A), assuming an 85dB(A) criterion. A lower criterion may require a higher protector class.

Key

- Mean** Mean attenuation value derived from testing in accordance with AS/NZS 1270:2002.
- SD** Standard Deviation derived from testing in accordance with AS/NZS 1270:2002.
- Mean-SD** Mean attenuation value minus Standard Deviation SLC₈₀ = Single number rating commonly used in Australia and New Zealand to compare acoustic performance of hearing protectors. The subscript '80' indicates that in well managed hearing protector programs, the protection provided is expected to equal or exceed the SLC₈₀ in 80% of protector-wearer noise spectrum combinations.
- Class** A simplified process for selecting hearing protectors based on the wearers 8-hour equivalent continuous A-weighted sound pressure level.

3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user. Refer to applicable regulations and guidance on how to adjust attenuation label value(s). In the absence of applicable regulations, it is recommended that the attenuation label value(s) be reduced to better estimate typical protection.

The effectiveness of a hearing protector reduces dramatically when the hearing protector does not fit properly, is incorrectly inserted or is not worn 100% of the time during ALL hazardous noise events. Removal of the hearing protector, even for brief moments, substantially reduces protection and greatly increases the risk of hearing damage.

Materials


The following materials are used in the manufacture of this product.

Component	Material
Earplugs	Polyurethane foam
Cord	PVC

Fitting Instructions

Always fit your ear plugs before entering a noise hazard area. Wash and rinse your hands before fitting ear plugs. Before fitting inspect the product to ensure that it is not torn or damaged. Replace as needed. Ensure hair and jewellery do not interfere with fitting. See Figures 1-5.

1. Roll earplug slowly with thumb and fingers. Gradually increase pressure to compress earplug to a small crease-free cylinder.
2. Insert compressed earplug well into ear canal while pulling ear outward and upward with opposite hand.
3. Hold in place until the ear plug expands. Touch earplug. You should feel only the end of the earplug. If you feel most of the earplug outside the ear canal remove earplug and repeat fitting.
4. Image of correctly fitted earplug. Insertion depth for correct fit will vary depending on the unique size and shape of each ear canal.
5. Image of incorrectly fitted earplug. The outer end of the earplug should not protrude beyond the tragus.



Fit Check

When ear plugs are correctly inserted your own voice should sound hollow and sounds around you should not sound as loud as before. Listen to steady loud sound with earplugs in both ears. Cover ears with tightly cupped hands. Noise should sound about the same whether or not ears are covered. Re-check the fit often during wear time. If earplugs become loose the actual protection obtained may be significantly reduced. To re-fit follow steps 1-5 above.

If you cannot obtain a good fit, try a different size or type of hearing protector. If you are unable to fit these earplugs correctly and comfortably in both ears, contact your safety officer or 3M for further advice.

Hearing Protector Fit Testing the 3M™ E-A-Rfit™ Dual-Ear Validation System

The success of your hearing conservation program requires more than offering earplugs or earmuffs. Each worker needs to wear the most effective hearing protector for the environment and the correct fit for their unique anatomy. With 3M™ E-A-Rfit™ Dual-Ear Validation System, you can quickly identify how much protection each worker receives from their 3M hearing protectors.

The Technology Behind 3M™ E-A-Rfit™

The 3M™ E-A-Rfit™ Dual-Ear Validation System is based on Field Microphone-In-Real Ear (F-MIRE) technology that measures the effectiveness of hearing protectors from inside a worker's ears, providing accurate, quantitative results. The tester wears a pair of modified 3M™ probed hearing protectors connected to a dual-element microphone. A loudspeaker is placed in front of the tester. When it emits a broadband noise, the dual-element microphone measures the signal in the ear canal and outside the ear plug. In less than five seconds, the difference between the two measurements is calculated and a Personal Attenuation Rating (PAR) is displayed.

It Starts with PAR

The 3M™ E-A-Rfit™ Validation System puts the worker in the context of their noise environment and helps you understand their level of attenuation.

The results you get from the 3M™ E-A-Rfit™ is displayed as a PAR. The PAR is a numerical value that shows the reduction in sound level within the ear when a hearing protector is worn. The resulting PAR, combined with the worker's exposure to noise, is used to determine if a worker is receiving appropriate protection from the noise hazard.

Knowing the PAR lets you identify workers who are inadequately protected, so you can provide real-time intervention and training.

Key Benefits of the 3M™ E-A-Rfit™ Dual-Ear Validation System include:

- Tests both ears simultaneously in less than 5 seconds
- Science-based, quantitative testing
- Fast, clear, and accurate results
- Tests 7 frequencies 125Hz to 8000Hz
- 3M™ Earplug, earmuff and headset (comms) testing capability

Contact your 3M Personal Safety Specialist to find out more about our 3M™ E-A-Rfit™ Dual-Ear Validation System or for assistance in solving your complex or day-to-day hearing conservation challenges.

Storage

- Store in area free of contamination
- Storage Temperature must be kept between -20°C and 40°C.
- Storage humidity <85% RH
- Product must be stored in original packaging.
- Regardless of storage history, always inspect hearing protectors before use and discard immediately if worn or damaged.

Shelf-Life

- 3M™ hearing protector product lifetimes assume the above storage conditions are met.
- Product lifetime = 5 years from date of manufacture as printed on the product packaging.

NOTE: Some locations may have regulations that include specific product lifetime requirements for hearing protectors, which should take precedence over these 3M™ recommendations if they are more restrictive.

Ordering Information

SAP ID	3M Order Code	Availability		Model #	Description
		AU	NZ		
XA006483649	7100330558	●	●	311-1250	3M™ E-A-Rsoft™ Yellow Neons™ Earplug 311-1250, Corded, Poly Bag, Regular Size, 2000 Pair/Case (replaced 7000002306, 70071515129 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs 311-1250, Corded, Poly Bag, Regular Size, 2000 Pair/Case * for NZ only)
7100330559	XA006483656	●	●	312-1250	3M™ E-A-Rsoft™ Yellow Neons™ Regular Uncorded Earplugs 312-1250, SLC ₈₀ 23dB (Class 4), Poly Bag, 200 Pairs/Box, 10 Boxes/Case (replaced 7000002303, 70071515020 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs 312-1250, Uncorded, Poly Bag, 2000 Pair/Case)
7100006342	7007151512	●	●	311-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Corded Earplugs 311-1251, SLC ₈₀ 23dB (Class 4), Poly Bag, 200 Pair/Box, 10 Boxes/Case
7000127175	70071515053	●	●	312-1251	3M™ E-A-Rsoft™ Yellow Neons™ Large Uncorded Earplugs, Poly Bag, 312-1251, 200 Pairs/Box, 10 Boxes/Case, SLC ₈₀ 23dB (Class 4)
7100336038	XA006483961	●	●	391-1004	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill, Uncorded Earplugs 391-1004, SLC ₈₀ 23dB (Class 4), 500 Pair/Bottle, 4 Bottles/Case (replaced 7000002305 70071515087 3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1004, Uncorded, Regular Size, 2000 Pair/Case)
7100001858	70071521309	●	●	391-1005	3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill Earplugs 391-1008, SLC ₈₀ 23dB (Class 4), Large Uncorded, 1600 Pair/Case
3M™ E-A-Rfit™ Dual-Ear Validation System - Probe					
7100069736	70071562741	●	●	393-2000-50	3M™ E-A-Rfit™ E-A-Rsoft™ Yellow Neons™ Probed Test Plug 393-2000-50
7000148551	70071650249	●	●	393-2014-50	3M™ E-A-Rfit™ E-A-R™ Yellow Neon™ Large Test Plug 393-2014-50, 50 Pairs/Case

WARNING!

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury. For proper use, see supervisor or User Instructions.

Always ensure the hearing protection device (HPD) is:

- Suitable for the application;
- Fitted correctly;
- Worn during all periods of exposure;
- Replaced when necessary.

Important Notice: To the extent permitted by law, 3M shall not be liable for any loss or damage including any loss of business, loss of profits, or for any indirect, special, incidental or consequential loss or damage arising from reliance upon any information herein provided by 3M. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.



3M Australia Pty Ltd
Personal Safety Division
 Bldg A, 1 Rivett Road
 North Ryde NSW 2113

Customer Service 1300 363 565
 Web www.3M.com.au/ppesafety

3M New Zealand Ltd
Personal Safety Division
 94 Apollo Drive, Rosedale
 Auckland 0632

Customer Service 0800 252 627
 Web www.3M.com/nz/ppesafety

3M, E-A-Rsoft, E-A-Rfit, One Touch and Yellow Neon are trademarks of 3M. All other trademarks are property of their respective owner.
 © 3M 2025. All rights reserved.