




3M™ Boron Nitride Cooling Fillers

For tailoring thermally conductive and electrically insulating polymers.

The next level of thermal management.



Designing polymers for demanding thermal management applications

Manufacturers of consumer and automotive electronics, high-capacity batteries, LED lighting, 5G applications and other electrical and electronic devices are increasingly utilizing high-performance polymers to help reduce component size and weight while simplifying assembly. Most polymers, however, have inherent limitations in their ability to conduct heat, which can greatly affect a device's long-term reliability and performance.


3M™ Boron Nitride Cooling Fillers offer a unique opportunity for designers, compounders and molders to help improve both thermal conductivity and electrical insulation in a wide range of plastics, elastomers, adhesives and more. Thanks to their enhanced thermal management capabilities, these materials are helping manufacturers enable a new generation of electrical and electronic components that may also offer improved performance, reliability and waste reduction.

Meeting the need for “smart” materials

3M Boron Nitride Cooling Fillers are a family of advanced ceramic materials used to help manufacturers improve thermal conductivity in polymers while maintaining or improving electrical insulation. They are also ideal for developing lightweight parts with complex geometries.

Using 3M Boron Nitride Cooling Fillers, thermal conductivity can be tailored to meet the thermal requirements in your system – harmonized with performance criteria such as target electric insulation, flame retardancy, mechanical properties and low dissipation factor.

For example, many modern electrical and electronics applications require materials that can effectively spread heat within a small space and transfer it to the surrounding air. Plastics are the material of choice in these kinds of applications – but plastics are generally not thermally conductive. Adding 3M Boron Nitride Cooling Fillers to the compound is an effective way to help resolve this issue.



Potential Applications

- Thermal interface materials (TIMs) for automotive, 5G and consumer electronics
- Thermally conductive adhesives and greases for bonding
- Automotive electrification, including housings for high-capacity batteries and electric motors in electric and hybrid vehicles
- Over molding of sensors and electronics by potting resins
- Injection molded thermoplastics and thermosets for motors, batteries and radome boxes
- Compounds with low dissipation factor for copper clad laminates (CCL)

Inside the Technology


Boron nitride: the “white graphite”

Hexagonal boron nitride (hBN) is a synthetic material with a high aspect ratio (ranging from 2:1 to 30:1) and a structure similar to graphite. Unlike graphite, 3M boron nitride has a pure white color and is not electrically conductive.

The particle geometry and composition of 3M Boron Nitride Cooling Fillers have been specially engineered for better heat transfer and dissipation – both of which are affected by the orientation of the material grades (platelets, and agglomerates) as shown in the illustrations below.


In-plane (x-y) heat dissipation

3M Boron Nitride Cooling Fillers are engineered to line up easily and form “bridges” to conduct heat in the direction of their orientation – either horizontal or vertical.



Through-plane (z) heat transfer

This general orientation is accomplished by employing various formulating and processing techniques.



Features and Benefits



Thermal conductivity (400 w/m•K in-plane)

- Intrinsically 8–20x more thermally conductive than alumina fillers
- 2–8x more thermally conductive when mixed in polymers



Electrical insulation

- $>10^{15}$ Ohm•cm electrical resistivity with a high breakdown strength
- Ideal for materials such as thin insulation foils



Low loss factor (0.00035 @1GHz)

- As signal transmissions and frequencies increase, so does the risk of signal loss
- Permittivity (Dk) of 4 @1 GHz



Low density (2.25 g/cm³)

- Allows for boosting of compound properties with final part density of 1.2–1.6 g/cm³
- Excellent for housings or LED lamp sockets



Very good processing properties

- One of the least abrasive fillers used in plastic compounds, it can help minimize equipment wear
- Available in multiple grades for excellent viscosity control



Optical properties

- Easy to color
- Excellent optical surface quality
- $>95\%$ reflectivity

With 3M Boron Nitride Cooling Fillers, you can create polymers with excellent thermal conductivity and electrical insulation.


Thermal Conductivity

Thermal conductivity in plastics is limited by the amount of fillers and the natural conductivity of the base polymer matrix. For example, with spherical alumina, thermal conductivity can be increased up to 3.5 or 4 W/m•K.* Compounds filled with 3M Boron Nitride Cooling Fillers, however, can reach conductivity levels up to 15 W/m•K while maintaining good processing properties.

* Laser flash measurement according to ASTM E 1461/DIN EN 821 on 2 mm samples.

Not for specification purposes.

Comparing In-Plane Thermal Conductivity of Thermally Conductive Plastics



Electrical Insulation

When using electrically conductive additives, such as graphite, additional insulation layers are typically required. These layers not only add to the size and cost of the component, but also form an added barrier to efficient heat transfer. By using electrically insulating thermal fillers, these layers can be virtually eliminated. With some of the highest electrical resistivity compared to other ceramic fillers, 3M Boron Nitride Cooling Fillers will help maintain or even improve the electrical insulation values of the filled compound while achieving high thermal conductivity.





Material	Dielectric Properties $\Omega \cdot \text{Cm}$	Dielectric Properties KV/mm
Boron Nitride	$>10^{15}$	>67
Al_2O_3	$>10^{12} - 10^{15}$	17-40
AlN	$>10^{12} - 10^{13}$	16-20

Low Loss Factor

As devices and applications for telecommunications continue to demand more data with increased signal transmission, this has a significant impact on existing devices and exacerbates design challenges. Adding 3M boron nitride as a filler to plastics and composites provides manufacturers with a solution with multiple functionalities in one material, allowing optimization of the component. 3M Boron Nitride Cooling Fillers help to provide thermal management, electrical insulation and low dielectric loss (Df). With a low intrinsic Df of 0.00051, 3M Boron Nitride Cooling Fillers help in reducing signal transmission power loss. Constant loss factor through wide frequency and temperature range helping enable high frequency data transmission.

Typical Electrical Properties (Not for specification purposes)

Material	Dielectric Properties Dk	Dielectric Properties Df
BN	~4.3	0.00051
Al ₂ O ₃	~9.5	0.0024
AlN	~8.4	0.0035
Minerals	~6-8	>0.005



Low Density

For equivalent thermal conductivity levels, a much lower weight percentage of boron nitride is necessary, compared to mineral- or oxide-based fillers. Consequently, a 3M boron nitride-filled compound at the same level has lower density. For example, an Al₂O₃-PA66 compound (2.3 kg/L) is 1.6X heavier than a 3M BN-PA66 compound (1.4 kg/L). The lower density of 3M Boron Nitride Cooling Fillers can help you improve processing and reduce your final part weight.



Density of Thermally Conductive Filler (Not for specification purposes)

Filler	Density (g/cm ³)
Al ₂ O ₃	3.99
AlN	3.26
Minerals (e.g. Al ₂ SiO ₅)	3.60
3M Boron Nitride Cooling Fillers	2.25

3M™ Boron Nitride Cooling Fillers

For tailoring thermally conductive and electrically insulating polymers.

Processing and optical properties

	3M Boron Nitride Cooling Filler	Aluminum Oxide (Al ₂ O ₃)	Aluminum Nitride (AlN)
Raw Materials	- Lower filler loading level, lower material consumption - Low density, lighter weight	- Requires higher filler loading to generate desired thermal conductivity (TC) - Higher density, heavier weight	- Requires higher filler loading to generate desired thermal conductivity - Medium density, medium weight
Processing	- Faster cycle times and line speeds due to high TC - No increase in wear on process tooling	Hard abrasive particulate cause wear on process tooling	Hard, abrasive particles cause wear on process tooling
Viscosity at 2 W/mK	- Low compound viscosity - Agglomerates give lower viscosities than Platelets	- Higher required loading results in medium compound viscosity - Spherical Al₂O₃ gives lower viscosity than bulk-shaped Al₂O₃	Higher required loading results in medium compound viscosity
Reflectivity	High reflectivity for LED applications	Low reflectivity for LED applications	Low reflectivity for LED applications

Powder Characteristics

(Not for specification purposes)

3M Boron Nitride Cooling Filler Grade	Filler Type	Particle Size Distribution d(0.1) µm	Particle Size Distribution d(0.5) µm	Particle Size Distribution d(0.9) µm	Particle Size Distribution d(0.97) µm	Bulk Density, Scott (g/cm ³)	Bulk Density, DIN (g/cm ³)	Surface Area (m ² /g)
001	Platelets	n.a.	0.5**	0.8**	n.a.	<0.14	n.a.	<30
003E	Platelets	0.5-2.5	1.3-8.8	n.a.***	n.a.	n.a.	<0.3	<15
003	Platelets	1-2	2-5	8.5-22.5	n.a.	<0.15	n.a.	<18
003SF	Platelets	0.5-2	2-6	6-14	n.a.	n.a.	<0.15	<20
006	Platelets	1.5-3	4.5-8	10-20	n.a.	<0.2	n.a.	<8.5
0075	Platelets	2-3.5	6-8.5	12-25	n.a.	<0.22	n.a.	<5.5
009	Platelets	2-3.5	6-12	14-32	n.a.	<0.22	n.a.	<5.5
012	Platelets	2-4.5	8-14	20-40	n.a.	<0.25	n.a.	<4.5
50M*	Agglomerates	5-10	15-30	35-70	n.a.	n.a.	0.1-0.4	<3.5
75*	Agglomerates	5-16	25-55	75-115	n.a.	n.a.	0.25-0.4	<3.5
100*	Agglomerates	10-35	50-80	95-145	n.a.	n.a.	0.25-0.4	<3.0
125*	Agglomerates	15-40	75-120	170-220	n.a.	n.a.	0.25-0.5	<3.0
150*	Agglomerates	20-80	120-200	240-360	n.a.	n.a.	0.3-0.55	<3.0
250S*	Agglomerates	8-20	40-100	120-210	n.a.	n.a.	0.3-0.6	<4.5

Bulk density determined according to ASTM B329/ISO 3923-2 (Scott density) and according to ISO 23145-2 (DIN density)

Particle size distribution measured by laser light scattering (Mastersizer 2000, dispersion in ethanol)

* Particle size distribution measured by laser light scattering (Mastersizer 2000, dry, 0.1 bar)

** Data determined by means of SEM pictures


*** Can include soft agglomerates with 50-100 µm

For calculation purpose: Density of bulk hBN 2.25 g/cm³

3M™ Boron Nitride Cooling Filler Grade Profiles

Platelets 003E, 003, 006, 0075, 009 and 012

Optimal all-purpose grades for pads and injection molded parts.




1 µm

SEM micrograph: Grade CFP 0075

Platelets 001 and 003SF

Preferred for thin films <25 µm and fibers, fine channels and windings. Grade CFP 003SF has a controlled top size.




1 µm

SEM micrograph: Grade CFP 003SF

3M™ Boron Nitride Cooling Filler Grade Profiles (continued)

Agglomerates 50M


Mix (M) of agglomerates, platelets and boron nitride clusters. Excellent for potting resins and encapsulation of electronic devices.



100 μ m SEM micrograph: Grade CFA 50M

Agglomerates 75


Soft agglomerates for high filler loadings and isotropic thermal conductivities. Used for potting resins and conformable TIM foils or pads with thin bond line 100-150 μ m.



100 μ m SEM micrograph: Grade CFA 75

Agglomerates 100


Soft agglomerates for high filler loadings and isotropic thermal conductivities. Used for potting resins and conformable TIM foils or pads with thin bond line 150-200 μ m.



100 μ m SEM micrograph: Grade CFA 100

Agglomerates 125


Soft agglomerates for high filler loadings and isotropic thermal conductivities. Used for potting resins and conformable TIM foils or pads with thin bond line 150-250 μ m.



100 μ m SEM micrograph Grade CFA 125

Agglomerates 150

Soft agglomerates for high filler loadings and isotropic thermal conductivities. Used in potting resins and conformable TIM pads with bond line above 200 μ m.



100 μ m SEM micrograph: Grade CFA 150

Agglomerates 250S

Boron nitride platelets spray-dried with inorganic binder to spherical (S) granulates for high flowability and dosing velocities during feeding. Ideal for TIM pads.



100 μ m SEM micrograph: Grade CFA 250S

3M™ Boron Nitride Cooling Fillers

For tailoring thermally conductive and electrically insulating polymers.

Expert application support.

3M is known throughout the world as a pioneer in advanced ceramics, and has provided the industry with innovative boron nitride for over 50 years. But when it comes to making finished parts, the quality of your raw material is just one piece of the puzzle.

Factors such as melt temperature, compounding technique, injection rate and more can have a significant effect on the thermal and electrical insulative properties of parts made with 3M Boron Nitride Cooling Fillers. That's why our experienced team of materials engineers, product specialists and field application engineers will work closely with you to develop formulations and processes that can help you achieve optimal thermal conductivity and desired performance levels.

Our mission is to help you be successful in the implementation of new product ideas or in the optimization of existing designs using 3M Boron Nitride Cooling Fillers. By taking advantage of our expertise and insights, you can realize the full potential of these materials.

[3M.com/thermalmanagement](https://www.3M.com/thermalmanagement)



Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user's use of 3M product does not violate any third party intellectual property rights. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OF NON-INFRINGEMENT OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. For industrial use only. Not intended, labeled or packaged for consumer sale or use.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damages arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

Technical Information: Technical information, recommendations, and other statements contained in this document or provided by 3M personnel are based on tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.



3M Advanced Materials Division

3M Center
St. Paul, MN 55144 USA

Phone 1-800-367-8905

Web www.3M.com/thermalmanagement

3M Technical Ceramics

Zweigniederlassung der 3M Deutschland GmbH
Max-Schaidhauf-Str. 25, 87437 Kempten, Germany

Phone +49 (0)831 5618-0

Web www.3M.de/bncf

3M is a trademark of 3M Company.
Used under license by 3M subsidiaries
and affiliates.

© 3M 2026. All rights reserved.
Issued: 04/2026