

3M™ Glass Cloth Automotive Electrical Tape 9



Features

- UL Component Recognized: UL510A Standard, Category OANZ2, File No. E17385
- CSA Certified: Standard C22.2 No. 66, File No. 093411, Class 9052-30
- Flame-retardant, UL temperature rated up to 200°C (392°F)
- Thermosetting silicone adhesive, glass cloth backing resists shrinking and burning
- RoHS Compliant

Potential Applications

- Applications requiring thermal and electrical insulation of components
- Other applications are currently out of scope but contact your 3M representative to discuss potential new applications

[Read our full Intended Use and Restricted Use Statements \(PDF\)](#)