

3M™ Polyester Film Electrical Tape 1350 Family



Features

- UL Component Recognized: UL510A Standard, Category OANZ2, File No. E17385
 - Flame-retardant
 - UL temperature rated up to 130°C (266°F)
- Available in roll format of different thicknesses and dielectric performances
- Non-corrosive, acrylic pressure-sensitive adhesive
- RoHS Compliant

Potential Applications

Automotive electric vehicles are being explored. Please contact your 3M Application Engineer to discuss.

These electrical insulation products are industrial products and were not designed for automotive applications. Additionally, not all electrical insulation products have been tested or validated for automotive applications. [Read our full Automotive Disclaimer](#)