



Cubitron™ 3
Performance Abrasives



Produce more. With less.

3M™ Cubitron™ 3 Fibre Discs

Breakthroughs in technology that are redefining the limits of cut rate and total stock removal, with a focus on prioritizing productivity, safety, sustainability, and optimizing automation.



3M™ Cubitron™ 3 Fibre Discs 1182C, 36+ and 1187C, 36+

A new era of abrasive performance is here.

Introducing 3M re-engineered Precision-Shaped Grain, boosting the speed and life of 3M™ Cubitron™ Performance Abrasives to new heights. This advancement prioritizes operator safety, maximizes sustainability, and amplifies time and labor efficiency.

3M™ Cubitron™ 3 Fibre Disc 1182C, 36+

Up to

60%

→ **Faster sustained cut rate**
→ **More total material removed**

vs. 3M™ Cubitron™ II Fibre Disc 982C, 36+

Enhanced mineral orientation

Re-shaping the way work gets done.



Cubitron™ 3
Performance Abrasives

Our latest 3M Precision-Shaped Grain




Re-engineered precision-shaped ceramic triangular grain using a proprietary breakthrough in grain shape. This helps increase productivity and lower overall grinding costs.

3M Precision-Shaped Grain

3M pioneered the first precision-shaped grain using 3M microreplication technology to form consistent sharp peaks that easily “slice” through metal—cutting cooler, faster, and lasting longer than conventional abrasive grain.

Conventional ceramic abrasive

Conventional ceramic abrasive grain tends to “plow” through metal, causing heat to build up in the workpiece and abrasive, resulting in a slower cut and shorter abrasive life compared to our latest precision-shaped grain.



Ideal for heavy grinding applications.

By using long-lasting, fast-cutting 3M™ Cubitron™ 3 Performance Abrasives, you can minimize abrasive changeover to save money over time. Stiff fiber backing and a strong resin bond provide durability and tear-resistance for heavy grinding applications from beveling, weld grinding, surface grinding to deburring, and flame cut smoothing. In each application the product grinds more freely and at lower temperatures, helping to reduce job times, operator fatigue and minimize rework.



Industries: ▶ **Metal fabrication** ▶ **Machinery manufacturing** ▶ **Shipyards**



3M™ Cubitron™ 3 Fibre Disc 1182C, 36+

Faster cut rate


Long lasting and faster cutting fibre discs help increase productivity and your bottom line

Total material removed

Fewer changeouts needed and less downtime

Less operator fatigue

Designed to cut with less pressure



More parts per disc




Faster throughput



Cool cutting


Carbon steel grinding

Up to
26%
Faster initial
cut rate*




Carbon Steel: the 'initial cut rate' claim is determined from averaging the cut/cycle from cycles 1–2 (first two minutes of grinding). Each cycle on the test method is 1 minute of grinding time. Error bars represent the results with a 95% confidence level.

Up to
36%
Faster sustained
cut rate*



Carbon Steel: the 'sustained cut rate' claim is determined from averaging the cut/cycle from cycles 7–20 (which is 14 minutes of grinding). Error bars represent the results with a 95% confidence level.

Up to
34%
More total material
removed*



Carbon Steel: the 'total material removed' claim is determined by averaging the amount of metal ground over the entire test method (30 cycles or 30 minutes of grinding). Error bars represent the results with a 95% confidence level.

*Compared to Competitive Shaped Grain Product A. Results are based on an automated, 30-minute, high pressure test on 1018 steel using 180mm 36+ grit fibre discs and 3M™ Disc Pad Face Plate Ribbed 80514 on a servo motor. Evaluated by 3M on 2023 August.

3M™ Cubitron™ 3 Fibre Disc 1187C, 36+

Faster cut rate

Long lasting and faster cutting fibre discs help increase productivity and your bottom line

Total material removed

Fewer changeouts needed and less downtime

Less operator fatigue

Designed to cut with less pressure

Grinding aid

Reduces the risk of discoloration from thermal damage in heat sensitive metals



More parts per disc




Faster throughput



Cool cutting


Stainless steel grinding

Up to
43%
Faster initial
cut rate*




Stainless Steel: the 'initial cut rate' claim is determined from averaging the cut/cycle from cycles 1–2 (first two minutes of grinding). Each cycle on the test method is 1 minute of grinding time. Error bars represent the results with a 95% confidence level.

Up to
61%
Faster sustained
cut rate*



Stainless Steel: the 'sustained cut rate' claim is determined from averaging the cut/cycle from cycles 3–6 (which is 4 minutes of grinding). Error bars represent the results with a 95% confidence level.

Up to
52%
More total material
removed*



Stainless Steel: the 'total material removed' claim is determined by averaging the amount of metal ground over the entire test method (10 cycles or 10 minutes of grinding). Error bars represent the results with a 95% confidence level.

*Compared to Competitive Shaped Grain Product A. Results are based on an automated, 10-minute, high pressure test on 304 steel using 180mm 36+ grit fibre discs and 3M™ Disc Pad Face Plate Ribbed 80514 on a servo motor. Evaluated by 3M on 2023 August.

Tools that take it to the next level.

The upgraded 3M™ Pneumatic Angle Grinder is designed for effective performance and operator comfort. Powered by a high-output 1.5HP pneumatic motor, this tool helps you get the job done quicker and more efficiently — whether you're grinding large welds, beveling or doing heavy deburring.

- ▶ 1.5 HP (1,100 W power)
- ▶ Wheel autobalancer
- ▶ Adjustable guard
- ▶ Vibration-reducing side handle with added padding; interchangeable for right or left hand usage
- ▶ Available accessories provide maximum functionality and flexibility
- ▶ Rear exhaust directs exhaust and swarf away from the workpiece



Get the full system advantage.

**3M™ Pneumatic Angle Grinder,
88566**



**3M™ Fibre Disc Back-up Pads,
Ribbed, Extra Hard**



TECH TIP:

Combine with 3M™ Fibre Disc Back-up Pads and 3M™ Pneumatic Angle Grinder to optimize performance of 3M™ Cubitron™ 3 Fibre Discs 1182C and 1187C including abrasive life, cut rate and consistency.

Get more value from your automation investment.

Automation
Ready

There are many reasons to invest in automating your abrasive processes: improvement gains in productivity; increase in consistency, quality and safety; an answer to your labor shortage. And to ensure maximized ROI from your investment, the best path comes from automating correctly from the start. That's where 3M products and engineering expertise come in.

The limitations of manual operation.

Manual operators are constrained by the amount of force they can apply and the angles they can hold a tool. Automation removes many of these constraints, working consistently and repeatedly at targeted angles and an optimized level of force and speed. A robot however, is still constrained by the abrasives it's running.

The vital importance of the right abrasives and process parameters in automation.

To realize the full ROI on your automation investment, you want to optimize your abrasive products and parameters for these four key elements:

- ▶ **Uptime:** Determined by abrasive life and full utilization of abrasive, change-over frequency is a key factor here.
- ▶ **Throughput:** Determined by abrasive performance, faster processing leads to more part throughput.
- ▶ **Consistency:** Determined by performance through the life of the abrasive product, resulting in increased finished good quality and less change over.
- ▶ **Efficiency:** 3M Robotic Application Engineers can help design a process that utilizes the full width of the abrasive. Reducing abrasive waste and cost.

At 3M, we have a deep understanding of the factors that affect an automated abrasive process. Our 100+ years of abrasive experience and 35+ years of abrasive automation experience is accessible through our Technical Experts, our 17 Global Proof of Concept automation labs, and deployed into how we engineer our products.


Contact our sales rep for consultation.

Products engineered with automation in mind.

3M™ Cubitron™ 3 Performance Abrasives elevate product life, cut rate, and wear consistency. This enhances processes that are already automated or increases the appeal of automating current manual ones.

Start your journey with 3M.

We know abrasive automation. We start with your part requirements in mind and offer consultation on the entire cell system; including recommendations on hardware and software, connections to partners in our 3M System Integrator Network, and running proof of concept projects in our labs; to meet the needs of your process.



Product Ordering Information

TECH TIP:

Keep discs in the closed, resealable foil bag to help maintain disc shape and quality when not in use.

3M™ Cubitron™ 3 Fibre Disc 1182C, Grade 36+

Product	Product ID	Diameter (mm)	Max RPM	Box/Case
	60440613077 (Slotted)	4 in x 5/8 in	13,300	25/100
	60440612970	5 in x 7/8 in	12,000	25/100
	60440612996	7 in x 7/8 in	8,600	25/100

3M™ Cubitron™ 3 Fibre Disc 1187C, Grade 36+

Product	Product ID	Diameter (mm)	Max RPM	Box/Case
	60440613234 (Slotted)	4 in x 5/8 in	13,300	25/100
	60440613135	5 in x 7/8 in	12,000	25/100
	60440613143	7 in x 7/8 in	8,600	25/100

3M™ Fibre Disc Back-up Pad

Product	Product ID	Diameter (mm)	Max RPM	Box/Case
	WX300923892	4 in	13,300	10
	WX300925012	5 in	12,000	10
	WX300923744	7 in	8,600	10

3M™ Pneumatic Angle Grinder, 88566

Product	Product ID	Diameter (mm)	Max RPM	Box/Case
	60440406472	115-125 (4.5-5.0)	12,000	1/1

Sustainability matters to 3M Abrasives.

When you buy from the SEAM value chain, you are helping to build a sustainable future for our industry, for people and for the planet.

3M is a founding member of the SEAM abrasives manufacturers program and aligns to the world's highest standards of quality, safety and performance in a sustainable environment. We commit to transparency, accountability, innovation and progress.

When buying from the SEAM value chain, customers are helping to build themselves a sustainable future.



Find out more at
www.seam.earth



Get the discs that get more done at go.3m.com/FibreDiscsIN



3M India Limited
48-51 Electronic City,
Hosur Road, Bengaluru,
Karnataka- 560100

Phone 1-800-425-3030
Web go.3M.com/INabrasives

Watch Video



bit.ly/fibrediscvideoIN

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com. **Warranty and Limited Remedy:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

3M and Cubitron are trademarks of 3M Company. All other trademarks are property of their respective owners. © 3M 2023. All rights reserved.

3M Abrasive Products are for industrial use only.