

3M Science.
Applied to Life.™



3M United Kingdom PLC | 3M Ireland Limited

Product catalogue 2023

Industrial Adhesives and Tapes

Valid from 01.06.2023

The information in this catalogue is current at the date of publication. Products availability may be amended by 3M from time to time. 3M is not liable in case of any errors or omissions.

■ Table of Contents

Hook & Loop

Hook & Loop Fasteners	4
Dual Lock	7



Hook & Loop

Hook & Loop

Hook & Loop Fasteners

3M™ Fastener Hook SJ3526N

3M™ Fastener SJ3526N is our high performance PSA nylon hook with a rubber adhesive and white polypropylene film liner. It provides a firm adhesive bond to a wide variety of surfaces including many low surface energy plastics and powder coats. It's designed for indoor use and has an engaged thickness of 4.4 mm.



- High performance rubber based adhesive designed for indoor applications requiring medium temperature resistance
- Provides a firm adhesive bond to a wide variety of surfaces
- Woven nylon is durable for thousands of closures

Product ID	Part Number	Product Name	MOQ	Order Unit
7000002127	SJ352615	3M™ Fastener Hook SJ3526N, Black, 16 mm x 45.7 m, 4.4 mm	4	Roll
7000002130	SJ352625	3M™ Fastener Hook SJ3526N, Black, 25 mm x 45.7 m, 4.4 mm	3	Roll
7000029691	SJ3526N	3M™ Fastener Hook SJ3526N, Black, 51 mm x 45.7 m, 4.4 mm	2	Roll
7000002132	SJ3526	3M™ Fastener Hook SJ3526N, White, 25 mm x 45.7 m, 4.4 mm	3	Roll

3M™ Loop Fastener SJ3527N

3M™ Fastener SJ3527N is our high performance PSA nylon loop with rubber adhesive and white polypropylene film liner. It provides a firm adhesive bond to a wide variety of surfaces including many low surface energy plastics and powder coats. It's designed for indoor use, and has an engaged thickness of 4.4 mm.



- Backed with a high performance rubber based adhesive, designed for indoor applications requiring medium temperature resistance
- Provides a firm adhesive bond to a wide variety of surfaces
- Durable for thousands of closures

Product ID	Part Number	Product Name	MOQ	Order Unit
7000002128	SJ352716	3M™ Fastener Loop SJ3527N, Black, 16 mm x 45.7 m, 4.4 mm	4	Roll
7000002133	568736	3M™ Fastener Loop SJ3527N, Black, 25 mm x 45.7 m, 4.4 mm	3	Roll
7000002131	3527W25	3M™ Fastener Loop SJ3527N, White, 25 mm x 45.7 m, 4.4 mm	3	Roll

3M™ Loop Fastener SJ3571

3M™ Loop Fastener SJ3571 is our premium performance PSA nylon loop with acrylic tape and clear polyethylene film liner. It has 3.8 mm engaged thickness.



- High performance acrylic adhesive designed for high temperature resistance
- Durable for thousands of closures
- Quick fastening that helps reduce production time and costs

Product ID	Part Number	Product Name	MOQ	Order Unit
7000001961	SJ3571	3M™ Fastener Loop SJ3571, Black, 25 mm x 45.7 m, 3.8 mm	3	Roll
7000051909	391472	3M™ Fastener Loop SJ3571, Black, 51 mm x 45.7 m, 3.8 mm	2	Roll
7000001972	SJ3571WT	3M™ Fastener Loop SJ3571, White, 25 mm x 45.7 m, 3.8 mm	3	Roll

Hook & Loop

3M™ Fastener Hook SJ3572

3M™ Hook Fastener SJ3572 is our premium performance PSA nylon loop with acrylic tape and clear polyethylene film liner. It has a 3.8 mm engaged thickness.

- High performance acrylic adhesive designed for high temperature resistance
- Durable for thousands of closures
- Quick fastening that helps reduce production time and costs



Product ID	Part Number	Product Name	MOQ	Order Unit
7000001962	SJ3572BK	3M™ Fastener Hook SJ3572, Black, 25 mm x 45.7 m, 3.8 mm	3	Roll
7000051903	715483	3M™ Fastener Hook SJ3572, Black, 51 mm x 45.7 m, 3.8 mm	2	Roll
7000001973	SJ3572WT	3M™ Fastener Hook SJ3572, White, 25 mm x 45.7 m, 3.8 mm	3	Roll

3M™ Hook and Loop Fastener SJ352B

3M™ Hook and Loop fastener SJ3520 is our white, high performance PSA nylon hook and loop with a rubber adhesive and white polypropylene film liner. It provides a firm adhesive bond to a wide variety of surfaces including many low surface energy plastics and powder coats. It's designed for indoor use and has an engaged thickness of 4.4 mm.

- High performance rubber based adhesive designed for indoor applications requiring medium temperature resistance
- Provides a firm adhesive bond to a wide variety of surfaces
- Woven nylon is durable for thousands of closures



Product ID	Part Number	Product Name	MOQ	Order Unit
7100123266	SJ352BBK25ST	3M™ Fastener Hook & Loop SJ352B, Black, 25 mm x 1.25 m, 4.4 mm, Blister IPC	4	Roll
7100123727	SJ352BWT25ST	3M™ Fastener Hook & Loop SJ352B, White, 25 mm x 1.25 m, 4.4 mm, Blister IPC	4	Roll

3M™ Reclosable Fastener SJ352D

Use 3M™ Reclosable Fastener SJ352D for a range of applications in a wide variety of industries. Our fastener's quick fastening feature can help reduce production time and costs. This box offers 5 m of both hook and loop systems, SJ3526N and SJ3527N.

- Backed with a high performance rubber based adhesive designed for indoor applications requiring medium temperature resistance
- Provide a firm adhesive bond to a wide variety of surfaces
- Durable for thousands of closures



Product ID	Part Number	Product Name	MOQ	Order Unit
7000070522	SJ352D	3M™ Fastener SJ352D, Black, 25 mm x 5 m, 4.4 mm, Twin Pack	4	Each

Hook & Loop

3M™ Fastener Loop Flame Resistant SJ3418FR

3M™ Flame Resistant Loop Fastener SJ3418FR is one part of our two-part fastener solution designed to provide great durability for thousands of closures. It's a nylon, woven loop reclosable fastener with 3.8 mm engaged thickness, and is plain backed for sew on applications. It mates with SJ3419FR.



- Plain backed loop fastener for sew on applications. Replaces zippers, buttons, snaps and laces
- Provides durability for thousands of closures through woven nylon design
- Resist flames and extreme heat with these rigorously tested fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7000051776	246889	3M™ Fastener Loop Flame Resistant SJ3418FR, Black, 25 mm x 45.7 m, 3.6 mm	12	Roll

3M™ Fastener Hook Flame Resistant SJ3419FR

3M™ Flame Resistant Hook Fastener SJ3419FR is one part of our two-part fastener solution designed to provide great durability for thousands of closures. It's a nylon, woven hook reclosable fastener with 3.8 mm engaged thickness, and is plain backed for sew on applications. It mates with SJ3418FR.



- Plain backed hook fastener for sew on applications. Replaces zippers, buttons, snaps and laces
- Provides durability for thousands of closures through woven nylon design
- Resist flames and extreme heat with these rigorously tested fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7000051782	246891	3M™ Fastener Hook Flame Resistant SJ3419FR, Black, 25 mm x 45.7 m	12	Roll

3M™ Fastener Loop Flame Resistant SJ3518FR

Fasten thousands of closures with 3M™ Flame Resistant Fastener SJ3518FR. Our loop fastener is durable, flame resistant (meeting F.A.R. 25.853 paragraph (a)(1)(i) 60 second vertical burn test) and backed with a rubber based adhesive for bonding to a wide variety of materials.



- Backed with a flame resistant rubber based adhesive for bonding to a wider variety of materials
- Provides durability for thousands of closures
- Rigorously tested to resist flames and extreme heat

Product ID	Part Number	Product Name	MOQ	Order Unit
7000052222	559039	3M™ Fastener Loop Flame Resistant SJ3518FR, Black, 25 mm x 45.7 m, 3.6 mm	3	Roll

Hook & Loop

3M™ Fastener Hook Flame Resistant SJ3519FR

3M™ Flame Resistant Hook Fastener SJ3519FR is one part of our two-part fastener solution designed to provide great durability for thousands of closures. This nylon, woven loop reclosable fastener features a rubber based adhesive and is flame resistant meeting F.A.R. 25.853 paragraph (a)(1)(i) 60 second vertical burn test. It mates with SJ3518FR.



- Backed with a flame resistant rubber based adhesive for bonding to a wider variety of materials
- Provides durability for thousands of closures
- Rigorously tested to resist flames and extreme heat

Product ID	Part Number	Product Name	MOQ	Order Unit
7000052226	559307	3M™ Fastener Hook Flame Resistant SJ3519FR, Black, 25 mm x 45.7 m, 3.6 mm	3	Roll
7000052227	559177	3M™ Fastener Hook Flame Resistant SJ3519FR, Black, 51 mm x 45.7 m, 3.6 mm	2	Roll

Dual Lock

3M™ Dual Lock™ Reclosable Fastener SJ3440

3M™ Dual Lock™ Reclosable Fastener SJ3440 is black, with 40 mushroom shaped stems / cm² and an engaged thickness of 4 mm. Our reclosable fastener is plain backed with no adhesive.



- Mushroom shaped stems, plain backed with no adhesive
- Type 250 mates to Type 170, 250 or 400
- Five times the tensile strength of typical hook-and-loop fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7000001979	SJ3440	3M™ Dual Lock™ Reclosable Fastener SJ3440, Black, 25 mm x 45.7 m, 4.1 mm	2	Roll

3M™ Dual Lock™ Reclosable Fastener SJ3541

3M™ Dual Lock™ Reclosable Fastener SJ3541 has a rubber based adhesive on the back of a black, polypropylene reclosable fastener, making it suitable for bonding many plastics, powder coated paints and other low surface energy materials. Our reclosable fastener has 62 mushroom shaped stems / cm² with a 5.8 mm engaged thickness.



- Black fastener with mushroom shaped stems, backed with a rubber based pressure sensitive adhesive
- Type 400 mates to Type 170 or 250. Closes with an audible snap
- Designed to bond to many plastics, powder coated paints and other low surface energy materials

Product ID	Part Number	Product Name	MOQ	Order Unit
7100108754	SJ354125MM	3M™ Dual Lock™ Reclosable Fastener SJ3541, Black, 25 mm x 45.7 m, 5.7 mm	2	Roll

Hook & Loop

3M™ Dual Lock™ Reclosable Fastener SJ3542

3M™ Dual Lock™ Reclosable Fastener SJ3542 has a rubber based adhesive on the back of a black, polypropylene reclosable fastener which makes it suitable for bonding many plastics, powder coated paints and other low surface energy materials. Our reclosable fastener has 26 mushroom shaped stems / cm² with a 5.8 mm engaged thickness.



- Black fastener with mushroom shaped stems, backed with a rubber based pressure sensitive adhesive
- Type 170 mates to Type 250, 400 or 170. Closes with an audible snap
- Designed to bond to many plastics, powder coated paints and other low surface energy materials

Product ID	Part Number	Product Name	MOQ	Order Unit
7100108756	SJ3542BK25	3M™ Dual Lock™ Reclosable Fastener SJ3542, Black, 25 mm x 45.7 m, 5.7 mm	2	Roll

3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ3540

3M™ Dual Lock™ Reclosable Fastener SJ3540 has a rubber based adhesive on the back of a black, polypropylene reclosable fastener. It's suitable for bonding many plastics, powder coated paints and other low surface energy materials. Our reclosable fastener has 40 mushroom shaped stems / cm² with a 5.8 mm engaged thickness.



- Black fastener with mushroom shaped stems, backed with a rubber based pressure sensitive adhesive
- Type 250 mates to Type 170, 250 or 400. Closes with an audible snap
- Designed to bond to many plastics, powder coated paints and other low surface energy materials

Product ID	Part Number	Product Name	MOQ	Order Unit
7000070523	SJ354D	3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ354D, Black, 25 mm x 5 m, 5.7 mm, PN34516	4	Each
7000145978	SJ354X	3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ354X, Black, 25 mm x 5 m, 5.7 mm, Twin Pack Squares, PN34517	4	Each
7100123339	SJ354B25ST	3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ3540, Black, 25 mm x 2.5 m, IPC	4	Roll
7100108749	SJ3450BLK25MM	3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ3540, Black, 25 mm x 45.7 m, 5.7 mm	2	Roll

Focus

3M™ Dual Lock™ Reclosable Fasteners SJ3550CF

3M™ Dual Lock™ Reclosable Fastener SJ3550CF is the convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution which bonds to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS. This fastener gives the adhesive a black appearance.



- Black, interlocking mushroom-shaped heads (250 stem density per square inch) provide strong, reliable and durable fastening that can be opened and closed multiple times
- Mates with Type 170, Type 250 or Type 400 stem densities to provide different strength combinations
- Clear, acrylic, tape bonds well to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS

Product ID	Part Number	Product Name	MOQ	Order Unit
7100279569	3550CF12	3M™ Dual Lock™ Reclosable Fastener SJ3550CF, Black, 12.5 mm x 45.7 m, Type 250	12	Roll
7100279337	3550CF19	3M™ Dual Lock™ Reclosable Fastener SJ3550CF, Black, 19 mm x 45.7 m, Type 250	2	Roll

Hook & Loop

Focus

3M™ Dual Lock™ Reclosable Fasteners SJ3550CF

3M™ Dual Lock™ Reclosable Fastener SJ3550CF is the convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution which bonds to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS. This fastener gives the adhesive a black appearance.

- Black, interlocking mushroom-shaped heads (250 stem density per square inch) provide strong, reliable and durable fastening that can be opened and closed multiple times
- Mates with Type 170, Type 250 or Type 400 stem densities to provide different strength combinations
- Clear, acrylic, tape bonds well to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS



Product ID	Part Number	Product Name	MOQ	Order Unit
7100279420	3550CF25	3M™ Dual Lock™ Reclosable Fastener SJ3550CF, Black, 25 mm x 45.7 m, Type 250	2	Roll
7100279570	3550CF50	3M™ Dual Lock™ Reclosable Fastener SJ3550CF, Black, 50 mm x 45.7 m, Type 250	1	Roll

Focus

3M™ Dual Lock™ Reclosable Fastener SJ3551CF

3M™ Dual Lock™ Reclosable Fastener SJ3551CF is the convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution which bonds to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS. This fastener gives the adhesive a black appearance.

- Black, interlocking mushroom-shaped heads (400 stem density per square inch) provide strong, reliable and durable fastening that can be opened and closed multiple times
- Mates with Type 170 and Type 250 stem densities to provide different strength combinations
- Clear, acrylic, tape bonds well to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS



Product ID	Part Number	Product Name	MOQ	Order Unit
7100279571	3551CF19	3M™ Dual Lock™ Reclosable Fastener SJ3551CF, Black, 19 mm x 45.7 m, Type 400	2	Roll
7100279572	3551CF25	3M™ Dual Lock™ Reclosable Fastener SJ3551CF, Black, 25 mm x 45.7 m, Type 400	2	Roll
7100279603	3551CF50	3M™ Dual Lock™ Reclosable Fastener SJ3551CF, Black, 50 mm x 45.7 m, Type 400	3	Roll

Hook & Loop

Focus

3M™ Dual Lock™ Reclosable Fastener SJ3552CF

3M™ Dual Lock™ Reclosable Fastener SJ3552CF is a convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution (which can be opened and closed multiple times) which bonds to a variety of substrates including metals and plastics such as acrylics, polycarbonate and ABS.



- Black, interlocking mushroom-shaped heads (170 stem density per square inch) provide strong, reliable and durable fastening that can be opened and closed multiple times
- Mates with Type 250 and Type 400 stem densities to provide different strength combinations
- Clear, acrylic, firm foam tape bonds well to a variety of substrates including metals and plastics such as acrylics, polycarbonate and ABS

Product ID	Part Number	Product Name	MOQ	Order Unit
7100279613	3552CF19	3M™ Dual Lock™ Reclosable Fastener SJ3552CF, Black, 19 mm x 45.7 m, Type 170	8	Roll
7100279614	3552CF25	3M™ Dual Lock™ Reclosable Fastener SJ3552CF, Black, 25 mm x 45.7 m, Type 170	2	Roll

3M™ Dual Lock™ Reclosable Fastener SJ3560

3M™ Dual Lock™ Reclosable Fastener SJ3560 has a clear acrylic adhesive on the back of a clear polypropylene reclosable fastener with 40 stems / cm² and 5.8 mm engaged thickness. Our reclosable fastener has a closure life of 1000 times before losing 50% of its original tensile strength.



- Designed to give a translucent appearance (glass, acryl glass (PMMA), polycarbonate)
- Snap-in-place installation replaces screws, nails, snaps and rivets
- Five times the tensile strength of typical hook-and-loop fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7000070525	SJ356D	3M™ Dual Lock™ Reclosable Fastener SJ356D, Transparent, 25 mm x 5 m, 5.7 mm, Twin Pack	4	Each
7100123340	SJ356B25ST	3M™ Dual Lock™ Reclosable Fastener SJ3560, 25 mm x 2.5 m, IPC, Twin Pack	4	Roll
7000051894	SJ356050	3M™ Dual Lock™ Reclosable Fastener SJ3560, Transparent 51 mm x 45.7 m, 5.7 mm	1	Roll
7000051892	SJ356012	3M™ Dual Lock™ Reclosable Fastener SJ3560, Transparent, 12.7 mm x 45.7 m, 5.7 mm, Twin Pack	4	Roll
7000051893	667643	3M™ Dual Lock™ Reclosable Fastener SJ3560, Transparent, 19 mm x 45.7 m, 5.7 mm	2	Roll
7100017793	DLSJ3560	3M™ Dual Lock™ Reclosable Fastener SJ3560, Transparent, 25 mm x 1.25 m, 5.7 mm	20	Roll

Hook & Loop

3M™ Dual Lock™ Reclosable Fastener SJ3561

3M™ Dual Lock™ Reclosable Fastener SJ3561 is the convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution (which can be opened and closed multiple times) which bonds to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS.



- Clear, interlocking mushroom-shaped heads (400 stem density per square inch) provide strong, reliable and durable fastening that can be opened and closed multiple times
- Mates with Type 170 and Type 250 stem densities to provide different strength combinations
- Clear, acrylic, tape bonds well to a variety of substrates including metals, glass and plastics such as acrylics, polycarbonate and ABS

Product ID	Part Number	Product Name	MOQ	Order Unit
7000126328	xxx	3M™ Dual Lock™ Reclosable Fastener SJ3561, Transparent, 25 mm x 45.7 m, Type 400	6	Roll

3M™ Dual Lock™ Reclosable Fastener TB3560

3M™ Dual Lock™ Reclosable Fastener SJ3560 has a clear acrylic adhesive on the back of a clear polypropylene reclosable fastener with 40 stems / cm² and 5.8 mm engaged thickness. Our reclosable fastener has a closure life of 1000 times before losing 50% of its original tensile strength.



- Clear fastener with mushroom shaped stems backed with a clear, acrylic pressure sensitive adhesive
- Type 250 mates to Type 170, 250 or 400
- Five times the tensile strength of typical hook-and-loop fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7100020027	3560TB25	3M™ Dual Lock™ Reclosable Fastener TB3560, Clear, 25 mm x 3 m, 5.7 mm	1	Bag

3M™ Dual Lock™ Reclosable Fastener SJ3870

3M™ Dual Lock™ Reclosable Fastener SJ3870 has a modified acrylic adhesive on the back of a black polypropylene reclosable fastener. Our product can be used both indoors and outside in a variety of applications; and has a slim 6.1 mm engaged thickness and long service life.



- Snap-in-place installation replaces screws, nails, snaps and rivets
- Five times the tensile strength of typical hook-and-loop fasteners
- Durable — up to 1,000 openings and closings before losing 50 % of original tensile strength

Product ID	Part Number	Product Name	MOQ	Order Unit
7100123347	SJ387B25ST	3M™ Dual Lock™ Reclosable Fastener SJ387B, Black, 25 mm x 2.5 m, 6.1 mm, Blister	4	Roll
7100214419	xxx	3M™ Dual Lock™ Reclosable Fastener SJ3870, Black, 15.9 mm x 41 m, 6.1 mm	2	Roll
7100108755	387025	3M™ Dual Lock™ Reclosable Fastener SJ3870, Black, 25 mm x 41 m, 6.1 mm, 40 pieces/cm ²	2	Roll
7100108752	SJ387050	3M™ Dual Lock™ Reclosable Fastener SJ3870, Black, 50 mm x 41 m, 6.1 mm, Type 250 BULK	3	Roll

Hook & Loop

3M™ Dual Lock™ Reclosable Fastener SJ3871

The 3M™ Dual Lock™ Reclosable Fastener SJ3871 has a modified acrylic adhesive on the back of a black polypropylene reclosable fastener. This product can be used both indoors and outside in a variety of applications; and has a slim 0.24" engaged thickness and long service life.



- Durable and secure, 3M™ Dual Lock™ Reclosable Fastener SJ3871 has exceptional strength through its interlocking mushroom shaped heads (250 stem density per square inch), providing up to 5X the tensile strength of typical hook and loop products. We designed this fastener with a black, modified acrylic, very conformable foam tape protected by a removable, film liner. This solid, pressure sensitive foam tape features a strong, durable bond that is chemical and UV resistant. With 3M™ Dual Lock™ Reclosable Fastener SJ3871, there is no need for any drilling, screwing or sewing tools which makes for quick installation.
- Black fastener with mushroom shaped stems, backed with a modified acrylic pressure sensitive adhesive
- Type 250 mates to Type 170, 250 or 400

Product ID	Part Number	Product Name	MOQ	Order Unit
7100108761	xxx	3M™ Dual Lock™ Reclosable Fastener SJ3871, Black, 25 mm x 41 m, 6.1 mm, 62 pieces/cm ²	2	Roll

3M™ Dual Lock™ Reclosable Fastener Low Profile SJ4570

3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570 is a modified acrylic adhesive on the back of a clear polypropylene reclosable fastener. Its modified acrylic adhesive enables you to bond medium to low surface energy materials such as metals, glass, many plastics and powder coated paints. With its 1.7 mm engaged thickness, our fastener is half the thickness of standard Dual Lock™ reclosable fasteners.



- Half the thickness of standard Dual Lock™ Reclosable Fasteners for low profile attachments
- Opens and closes up to 100 times before losing 50 % of original tensile strength
- Translucent fastener and adhesive is ideal for joining transparent materials

Product ID	Part Number	Product Name	MOQ	Order Unit
7000002105	SJ4570	3M	2	Roll
7000070534	SJ457D	3M™ Dual Lock™ Reclosable Fastener Low Profile SJ457D, Transparent, 25 mm x 10 m, 1.7 mm, Twin Pack	4	Each
7000052144	4570T15	3M™ Dual Lock™ Reclosable Fastener Low Profile SJ4570, Transparent, 16 mm x 45.7 m, 1.7 mm	1	Roll

3M™ Dual Lock™ Low Profile Reclosable Fastener TB4570

3M™ Dual Lock™ Low Profile Reclosable Fastener TB4570 is our modified acrylic adhesive on the back of a clear polypropylene reclosable fastener. Its modified acrylic adhesive enables you to bond medium to low surface energy materials such as metals, glass, many plastics and powder coated paints. With its 1.7 mm engaged thickness it's half the thickness of standard Dual Lock™ reclosable fasteners.



- Clear, low profile fastener with mushroom shaped stems backed with a clear, low surface energy acrylic pressure sensitive adhesive
- Great for small jobs, prototyping and design evaluation
- Opens and closes 100 times

Product ID	Part Number	Product Name	MOQ	Order Unit
7000124799	4570TB25	3M™ Dual Lock™ Low Profile Reclosable Fastener TB4570, Transparent, 25 mm x 3 m, 1.7 mm	1	Bag

Hook & Loop

3M™ Dual Lock™ Reclosable Fastener SJ4580

3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4580 is our clear acrylic adhesive on the back of a clear polypropylene reclosable fastener. It has a low profile 2.8 mm engaged thickness.



- Clear, low profile with mushroom shaped stems backed with clear, low surface energy acrylic pressure sensitive adhesive
- Low profile, polyolefin fastener is half the thickness of standard Dual Lock™ reclosable fasteners and is self-mating
- Opens and closes 100 times

Product ID	Part Number	Product Name	MOQ	Order Unit
7000052204	SJ4580VHB1X50	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4580, Clear, 1 in x 50 yd	2	Roll
7000052205	SJ4580100	3M™ Dual Lock™ Reclosable Fastener SJ4580, Transparent 102 mm x 45.7 m, 2.8 mm	1	Roll

3M™ Dual Lock™ Reclosable Fastener SJ3463

3M™ Dual Lock™ Reclosable Fastener SJ3463 is a black, rigid back, 20.6 mm circle with a 4.1 mm hole in the centre. Our reclosable fastener has 62 stems / cm² and is plain backed with no adhesive.



- Mushroom shaped stems, plain backed with no adhesive
- Type 400 mates to Type 170 or 250
- Five times the tensile strength of typical hook-and-loop fasteners

Product ID	Part Number	Product Name	MOQ	Order Unit
7000052009	SJ3463	3M™ Dual Lock™ Reclosable Fastener SJ3463, Black, Diameter 20.6 mm, Circle	1000	Each

3M TERMS OF SALE

1. Application

1.1 These conditions apply to all contracts between 3M and the Buyer referred to in the order and override all conditions stipulated by the Buyer (even if submitted in a later document); any other agreements between the parties relating to the subject matter of this order are terminated (except an agreement into which these conditions are incorporated).

1.2 No variation of these conditions is permitted unless agreed in writing by an authorised officer of 3M. Lead times for delivery shall be as set out in 3M's quotation or proposal or if none is specified 3M's standard lead times shall apply.

2. Description

2.1 The description of the goods or services to be supplied by 3M shall be as set out in 3M's quotation, as modified by any written specification supplied by 3M, or otherwise agreed in writing by an authorised officer of 3M.

2.2 3M may amend any specification if required by any applicable statute or regulation, or by notification to the Buyer following which the applicable specification shall be that as so amended.

2.3 All samples, drawings, images, descriptive matter and advertising materials produced by 3M and any descriptions or illustrations contained in 3M's literature, digital media or emails are produced solely to describe the goods or services approximately and do not form part of the agreement into which these conditions are incorporated.

3. Price

3.1 Save where expressly stated otherwise by 3M the price to be paid for the goods or the services will be 3M's price at the date when the goods are dispatched or the services are provided.

3.2 The price of goods includes the cost of 3M's standard packaging and standard delivery within the UK and Ireland by 3M's normal transportation; the price does not include VAT. Where the price is based on pallets and/or packaging being returned to 3M, then failure to do so by the Buyer will result in a surcharge at 3M's standard rate.

4. Payment

4.1 Unless otherwise specified on 3M's invoice, payment for the goods or services must be received in cleared funds no later than thirty days of the date of invoice.

4.2 3M reserves the right to charge interest on overdue sums at the rate of 4% per annum above the Base Rate for the time being of Lloyds Bank plc calculated on a daily basis from the due date of payment in Clause 4.1 until the date upon which payment is made.

4.3 3M may at any time require the Buyer to make payment in advance of delivery or require security for payment.

4.4 If the Buyer fails to make payment by the due date or when required, 3M may (without prejudice to any other remedy which it may have) cancel this contract and/or any other contract between the Buyer and 3M and/or suspend delivery under this or any other contract until payment is made.

4.5 The Buyer will have no statutory or other right of set off.

5. Delivery

5.1 Delivery dates are approximate only and 3M shall not be responsible for any loss or damage arising from any delay in delivering all or part of any goods ordered or delay in the provision of any services.

5.2 Without prejudice to Clause 5.1, 3M will not be liable for any delay in delivery or non-delivery of goods or services or any other breach of these conditions caused by any circumstances beyond 3M's reasonable control including without limitation, any Act of God, explosion, fire, flood, war, hostilities, accident, delay in delivery or non-delivery by 3M's suppliers, breakdowns or accidents to machinery, labour strike or dispute, order or decree of any court or action of any governmental authority, or any other causes or any circumstances beyond 3M's control; on the occurrence of any of the above events 3M reserves the right to cancel or suspend the whole or part of any delivery or service provision.

5.3 In the case of any order for goods of a type or description not normally held in stock by 3M, and therefore specially made ordered or imported by 3M to meet such order, the Buyer will accept goods 10% more or 10% less than ordered, the total price of the order being correspondingly adjusted.

5.4 Where 3M references the international rules for the interpretation of trade terms prepared by the International Chamber of Commerce (Incoterms) in the relevant contract or proposal, such terms shall apply to delivery save that where they conflict with these conditions, these conditions shall prevail. For deliveries outside of the UK mainland the term of sale shall be FCA 3M UK warehouse unless otherwise mutually agreed in writing by 3M and Buyer.

5.5 Goods supplied may be subject to export controls. The Buyer should refer to 3M's packing list accompanying the goods for any export control status.

6. Risk

Risk in all goods supplied to the Buyer will pass to the Buyer on delivery. Unloading shall be at the Buyer's risk.

7. Inspection

7.1 If the goods or any of them are damaged or lost while in the custody of a carrier, 3M will (at its option) either replace such goods or refund to the Buyer the price paid for them, but 3M's liability in connection with any such goods will not exceed the cost of replacement or the price paid by the Buyer.

7.2 3M will not be under any liability under 7.1 above unless the following conditions are strictly complied with:

7.2:1 In the event of non-delivery of a whole consignment of goods the Buyer must inform 3M in writing within ten days of the date of the invoice.

7.2:2 In the case of damage to goods or loss of part of a consignment, the consignment must be inspected in the presence of the carrier. If any goods are damaged or lost the consignment note must be endorsed accordingly and the Buyer must notify 3M within forty-eight hours of delivery, such notification to be confirmed in writing within the following five days. 3M shall have no further liability for such damage or loss.

8. Liabilities and Warranties

8.1 Nothing in this clause will be deemed to exclude or restrict 3M's liability for (i) death or personal injury resulting from its negligence; (ii) fraud or fraudulent misrepresentation; (iii) breach of any obligation as to title implied by section 12 of the Sale of Goods Act 1979; and/or (iv) any act, omission or matter, liability for which may not be legally excluded or limited.

8.2 If any goods supplied or any services supplied or provided by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same (or the defective part) or refund to the Buyer the price of the goods or services (or a pro-rated amount of the price if not all the goods are defective).

8.3 The Buyer will determine the suitability of the goods for its intended use and will not rely upon any representations made by or on behalf of 3M.

8.4 3M's liability under these conditions shall never exceed the cost of replacement or the price paid by the Buyer for the goods or services.

8.5 3M will not be liable for any consequential or indirect loss or damage (whether for loss of profit, loss of business, depletion of goodwill or otherwise) costs, expenses or other claims for consequential compensation whatsoever suffered by the Buyer whether this loss or damage arises from a breach of duty, in contract or in tort or in any other way (including loss or damage arising from 3M's negligence).

8.6 The Buyer shall at all times comply with standards of business conduct that are consistent with 3M's Code of Conduct located at www.3m.com/businessconduct and all applicable laws, statutes, regulations and codes relating to anti-bribery including but not limited to the US Foreign Corrupt Practices Act and the UK Bribery Act 2010 ("Bribery Laws") and shall maintain in place its own policies and adequate procedures, to ensure full compliance with the Bribery Laws. The Buyer shall promptly report to 3M any request or demand for any undue financial or other advantage of any kind received by or offered to the Buyer in connection with 3M's goods or services.

8.7 Except as set out in these conditions, all other warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

9. Assignment

9.1 3M may assign, or deal in any other manner with, any contract between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts to any third party or agent.

9.2 The Buyer shall not be entitled to assign, or deal in any other manner with, any contracts between 3M and Buyer or any part of them, including sub-contracting any of its obligations under such contracts, without the prior written consent of 3M.

10. Termination

If there is appointed a Receiver, Administrator or Administrative Receiver of the Buyer's property or assets or any part of them, or a court order is made or a resolution is passed for the winding-up of the Buyer (except for the purpose of amalgamation or reconstruction) or if the Buyer commits any act of bankruptcy, or any bankruptcy petition is presented against the Buyer (or any analogous proceedings under the law of any country outside the United Kingdom are commenced), 3M may by notice in writing to the Buyer cancel all orders and contracts between 3M and the Buyer or any part of them remaining unfulfilled.

11. General

11.1 If any provision, or part of a provision, of these conditions is found by any court or administrative body of competent jurisdiction to be invalid, illegal or unenforceable (a "void provision") such invalidity, illegality or unenforceability shall not affect the other provisions of the conditions, which shall remain in full force and effect. If a void provision would be valid, legal and enforceable if some part of it were deleted, that void provision shall apply with such modification as may be necessary to make it valid, legal and enforceable and if it cannot be made valid, legal and enforceable it shall be deemed to be deleted.

11.2 No provision of the conditions shall be enforceable under the Contracts (Rights of Third Parties) Act 1999 by any person who is not a party to the contract between 3M and Buyer.

11.3 A failure to exercise, or delay in exercising a right, power or remedy provided to 3M by these conditions or by law does not constitute a waiver of that, or any other, right, power or remedy and shall not (and nor shall any single or partial exercise of any such right, power or remedy) preclude the further exercise of that, or any other, right, power or remedy.

12. Jurisdiction

12.1 All contracts between 3M and the Buyer where the goods are shipped to or services are provided in the Republic of Ireland shall be governed by and construed in accordance with the Laws of the Republic of Ireland, and the Buyer agrees to submit to the jurisdiction of the Courts of law in the Republic of Ireland in respect of them.


12.2 Except as provided above, all contracts between 3M and the Buyer shall be governed by and construed in accordance with the Laws of England, and the Buyer agrees to submit to the jurisdiction of the Courts of law in England in respect of them.

Effective 1 January 2017



3M United Kingdom PLC
3M Centre Cain Road,
Bracknell,
Berkshire, RG12 8HT
Tel: 0870 6080050
www.3M.co.uk

3M Ireland Limited
The Iveagh Building
The Park 18, Carrickmines,
D18 X015, Ireland
Tel: +353-1-2803555
www.3m.ie



**Please scan the QR
code for additional
product information.**