



3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifelines

Stainless Steel, 85 ft., 130 ft., 175 ft. Lengths

Our heaviest-duty OSHA compliant SRL



Effective November 3, 2023, 3M™ DBI-SALA® Sealed-Blok™ Stainless Steel Cable Self-Retracting Lifelines in 85 ft., 130 ft. and 175 ft. lengths in overhead, retrieval and retrieval with bracket models will meet 29 CFR OSHA 1926.502 & OSHA 1910.140 regulations. These 3M™ DBI-SALA® Sealed-Blok™ OSHA products now have new part numbers and labels to reflect the updates.

Legacy Part Part Number	New Part Number	SAP ID	Description
3400874	3400167	7100323507	3M™ DBI-SALA® Sealed-Blok™ 3-Way Retrieval Self-Retracting Lifeline 3400167, Stainless Steel Cable, Snap Hook, 85 ft., OSHA
3400882	3400168	7100324055	3M™ DBI-SALA® Sealed-Blok™ 3-Way Retrieval Self-Retracting Lifeline with Bracket 3400168, Stainless Steel Cable, Snap Hook, 85 ft., OSHA
3400862	3400169	7012828686	3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifeline 3400168, Stainless Steel Cable, Snap Hook, 85 ft., OSHA
3400979	3400170	7100323508	3M™ DBI-SALA® Sealed-Blok™ 3-Way Retrieval Self-Retracting Lifeline 3400170, Stainless Steel Cable, Snap Hook, 130 ft., OSHA
3400987	3400171	7100324056	3M™ DBI-SALA® Sealed-Blok™ 3-Way Retrieval Self-Retracting Lifeline with Bracket 3400171, Stainless Steel Cable, Snap Hook, 130 ft., OSHA
3400967	3400172	7012828687	3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifeline 3400172, Stainless Steel Cable, Snap Hook, 130 ft., OSHA
3400652	3400173	7012828688	3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifeline 3400173, Stainless Steel Cable, Snap Hook, 175 ft., OSHA

Products manufactured to previous revisions of the ANSI Z359.14 standard may continue to be used as long as the product continues to meet the inspection requirements as defined by the manufacturer, conducted at the recommended intervals by a Competent Person.

3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifelines

Stainless Steel, 85 ft. Length

Below is a performance comparison for 3M™ DBI-SALA® Sealed Blok™ Self-Retracting Lifelines in comparison to the Industry Standard requirements:

	3M™ DBI-SALA® Sealed-Blok™ SRL 85' Previous Performance Claims	3M™ DBI-SALA® Sealed-Blok™ SRL 85' New Performance Claims
	OSHA 1926.502 & OSHA 1910.140	OSHA 1926.502 & OSHA 1910.140
SRD Class	Class B	N/A
Weight Capacity	130 lb. to 420 lb.	130 lb. to 420 lb.
Maximum Arrest Force	1,350 lb.	1,350 lb.
Average Arrest Force	900	900
Arrest Distance	42 in.	42 in.
Deceleration Distance	42 in.	42 in.

	Industry Standard Requirements			
	ANSI/ASSP Z359.14-2014		OSHA 1926.502 & OSHA 1910.140	ANSI/ASSP Z359.14-2021
SRD Class	Class A	Class B		Class 1 & 2
Weight Capacity	130 to 310 lb.	130 to 310 lb.	N/A	130 to 310 lb.
Maximum Arrest Force	1,800 lb.	1,800 lb.	1,800 lb.	1,800 lb.
Average Arrest Force	1,350 lb.	900 lb.	N/A	1,350 lb.
Arrest Distance	24 in.	54 in.	N/A	42 in.
Deceleration Distance	N/A	N/A	42 in.	N/A

For information on ANSI/ASSP Z359.14-2021 product certifications and what the standard update means for you, contact your 3M Fall Protection Representative or visit [3M.com/ANSIupdate](https://www.3m.com/ANSIupdate).



Continue to the next page for additional product information.

3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifelines

Stainless Steel, 130 ft., 175 ft. Lengths

Below is a performance comparison for 3M™ DBI-SALA® Sealed Blok™ Self-Retracting Lifelines in comparison to the Industry Standard requirements:

	3M™ DBI-SALA® Sealed-Blok™ SRL 130'/175' Previous Performance Claims	3M™ DBI-SALA® Sealed-Blok™ SRL 130'/175' New Performance Claims
	OSHA 1926.502 & OSHA 1910.140	OSHA 1926.502 & OSHA 1910.140
SRD Class	Class B	N/A
Weight Capacity	130 lb. to 420 lb.	130 lb. to 420 lb.
Maximum Arrest Force	1,350 lb.	1,800 lb.
Average Arrest Force	900	1,125 lb.
Arrest Distance	42 in.	55 in.
Deceleration Distance	42 in.	42 in.

	Industry Standard Requirements			
	ANSI/ASSP Z359.14-2014		OSHA 1926.502 & OSHA 1910.140	ANSI/ASSP Z359.14-2021
SRD Class	Class A	Class B		Class 1 & 2
Weight Capacity	130 to 310 lb.	130 to 310 lb.	N/A	130 to 310 lb.
Maximum Arrest Force	1,800 lb.	1,800 lb.	1,800 lb.	1,800 lb.
Average Arrest Force	1,350 lb.	900 lb.	N/A	1,350 lb.
Arrest Distance	24 in.	54 in.	N/A	42 in.
Deceleration Distance	N/A	N/A	42 in.	N/A

For information on ANSI/ASSP Z359.14-2021 product certifications and what the standard update means for you, contact your 3M Fall Protection Representative or visit [3M.com/ANSIupdate](https://www.3m.com/ANSIupdate).



3M Fall Protection
3833 SALA Way
Red Wing, MN 55066 USA

Phone 800.328.6146
Email 3mfallprotection@mmm.com
Web [3M.com/FallProtection](https://www.3m.com/FallProtection)

3M, DBI-SALA and Sealed Blok are trademarks of 3M Company.
© 2023, 3M. All rights reserved.