

# Niagara™ Products

## Floor Maintenance Pads

### STRIPPING



#### High Performance Stripping Pad 7400N

(Conventional Speed: 175–600 RPM)

- Heavy-duty stripping of finish, dirt and build-up



#### Black Stripping Pad 7200N

(Conventional Speed: 175–600 RPM)

- For long-lasting stripping of finish, dirt and buildup



### SCRUBBING/CLEANING/BUFFING



#### Deep Scrubbing Pad

(Conventional Speed: 175–600 RPM)

- Heavy-duty scrubbing prior to recoating
- Removes top layers of finish using water or neutral cleaner



#### Green Scrubbing Pad 5400N

(Conventional Speed: 175–600 RPM)

- Extra heavy-duty pad removes dirt, spills and scuffs, leaving a clean surface ready for recoating



#### Blue Cleaning Pad 5300N

(Conventional Speed: 175–600 RPM)

- For heavy-duty scrubbing prior to recoating
- Removes dirt, spills and scuffs, leaving a clean surface ready for recoating



#### Red Buffing Pad 5100N

(Conventional Speed: 175–600 RPM)

- Cleans when damp, buffs when dry
- Cleans and removes scuff marks while polishing floors to a high gloss



### POLISHING



#### White Polishing Pad 4100N

(Conventional Speed: 175–600 RPM)

- For buffing very soft finishes or for polishing soft waxes on wood floors

### BURNISHING



#### Super Tan Hog's Hair Pad 3700N

(Ultra-High Speed: 1500–3000 RPM)

- Higher content hog's hair and synthetic fiber pad
- Designed for scratch removal on hard finishes
- Designed for low frequency burnishing programs



#### Natural Tan Hog's Hair Pad 3500N

(Ultra-High Speed: 1500–3000 RPM)

- A natural hair pad for scratch removal on hard finishes
- Designed for low frequency burnishing programs



#### Tan Burnishing Pad 3400N

(Ultra-High Speed: 1500–3000 RPM)

- Specially formulated pad for dry burnishing
- Designed for mark removal on harder finishes or in high-traffic areas
- Produces brilliant “wet-look” gloss
- For low to moderate burnishing programs



#### Natural White Burnishing Pad 3300N

(Ultra-High Speed: 1500–3000 RPM)

- Natural hair and synthetic fiber pad
- Provides excellent results on a wide variety of floor finishes and traffic conditions



#### Aqua Burnishing Pad 3100N

(Ultra-High Speed: 1500–3000 RPM)

- Ideal for high frequency burnishing programs (daily)
- Specifically designed for soft finishes
- Produces less powdering and higher gloss levels

The polyester fiber used to make a range of maintenance floor pads\* will contain a minimum of 50% post consumer recycled content. The recycled polyester fiber used is third party certified for post consumer recycled content.

\*Niagara™ Brand Floor Pad families include 3300N, 3400N, 3500N, 3700N, 5100N, 5400N and 7200N.

## Utility Pads



#### White Utility Pad 8440N

- For delicate surfaces such as windows and ceramic tile

000-48011-35093-6

Pack: 5/box, 4 boxes/case



#### Brown Utility Pad 8541N

- For heavy-duty cleaning such as removing finish and wax from baseboards

000-48011-35094-3

Pack: 5/box, 4 boxes/case



#### Blue Utility Pad 8242N

- For medium-duty cleaning tasks such as cleaning stairs

000-48011-35095-0

Pack: 5/box, 4 boxes/case



Niagara Pads 7400N, 7200N, Deep Scrubbing, 5300N, and 5100N are certified by Green Seal® for Environmental Innovation based on a design for significantly improved initial and/or mid-life performance compared to competitive products, extending the useful life of the floor pad and reducing solid waste generation.

# Niagara™ Products

## Scouring Pads



### Light-Duty Scouring Pad 98N

- For light-duty cleaning
- Won't scratch or dull most surfaces
- Ideal for glass, stainless steel, chrome, copper, porcelain and ceramic

500-48011-19373-6  
Size: 6" x 9" Pack: 20/1



### Medium-Duty Scouring Pad 96N

- For most common cleaning jobs
- Cleans pots, pans and kitchen equipment
- Ideal for building interiors, including floors, stairways and baseboards

500-48011-19369-9  
Size: 6" x 9" Pack: 20/1

500-48011-18194-8  
Size: 6" x 9" Pack: 6/10



### General Purpose Scrubbing Pad 9650N

- Thick, hand-size scouring pad eliminates the need to cut or fold the pad
- Ideal for kitchen equipment, walls, ceilings, floors, desks and stairways

000-48011-59186-5  
Size: 3" x 4.5" Pack: 40/2




### Heavy-Duty Scouring Pad 86N

- For tough maintenance jobs
- Replaces scrapers, steel wool and metal sponges in the kitchen
- Ideal for food processing equipment, heavily baked-on food or removing scuff marks on floors

500-48011-19370-5  
Size: 6" x 9" Pack: 15/1

500-48011-20206-3  
Size: 6" x 9" Pack: 6/10



### Heavy-Duty Pot 'n Pan Pad 88N

- For extra heavy-duty cleaning
- Ideal for cleaning heavily encrusted pots and pans, kitchen equipment and grimy maintenance equipment

500-48011-19371-2  
Size: 3.5" x 5" Pack: 20/1

500-48011-20204-9  
Size: 3.5" x 5" Pack: 6/10

## Scrubbing Sponges



### Medium-Duty Scrubbing Sponge 74N

- One side for general purpose scouring; sponge side for absorbing liquids or carrying cleaning solutions to a surface
- Use on tables, fixtures, countertops and floors

500-48011-19428-3  
Size: 5.9" x 3.3" x 0.7" Pack: 20/1

500-48011-20208-7  
Size: 5.9" x 3.3" x 0.7" Pack: 6/10



### Light-Duty Scrubbing Sponge 63N

- One side for light-duty scouring; sponge side for absorbing liquids or carrying cleaning solutions to a surface
- Won't scratch or dull most surfaces
- Cleans up stainless steel, glass and ceramic, fine china, porcelain and non-stick cooking surfaces

500-48011-19429-0  
Size: 5.9" x 3.3" x 0.7" Pack: 20/1

## Griddle Cleaning Products



### Griddle Pad 46N

- Use between screen and holder to clean griddle surfaces or alone without screen to polish

500-48011-19372-9  
Size: 4" x 5.25" Pack: 20/1



### Griddle Screen 200N

- Loosens carbonized grease and food debris from the griddle

500-48011-18200-6  
Size: 4" x 5.5" Pack: 10/20