



Customer service you can count on.

Your work never slows down—and neither do we. Our Customer Service team is committed to ensuring you have the 3M Fall Protection you need when and where you need it.


Velocity Shipping



Velocity Ship items available to ship same day

on orders placed before 12pm CST.

Flat Fee Product Repair



Many of our products can be repaired at our Red Wing, Minnesota facility

in just 3 days

or they can be repaired at one of our

over 200 Approved Repair Centers.

Training that goes beyond the textbook.





3M's full range of fall protection, confined space and rescue training courses are offered throughout the year at our state-of-the-art training centers. 3M also offers on-site safety training across our portfolio that is tailored to meet the unique environment of your facility.

At our site or yours, you can trust 3M Fall Protection to provide world-class fall safety training. Topic areas include:

- ► Fall Protection Training Courses
- ► Confined Space Training Courses
- ► Rescuer Training Courses
- Advanced Level Training Courses
- ► Fall Protection for Tools Training Courses

3M.com/SafetyTraining




The gear you need.

The savings you want.

Trade In, Trade Up Program

We're so confident you'll love our fall protection products that we'll let you trade in your current gear and give you a rebate on new purchases. Harnesses, SRLs, lanyards and more — we're including over 1,200 products to choose from.

If you already use 3M Fall Protection products, you can trade up to get rebates when you upgrade on gear with more features and benefits. It's a great time to assess your equipment and make the switch to 3M™ DBI-SALA® Fall Protection.



Calculate your rebate at go.3M.com/FPtradein.

Connecting like never before.

3M Connected Safety is a cloud-based, Internet of Things (IoT) platform that combines data science and our PPE technology to help organizations advance the digital transformation of worker safety.

That means workers can be confident they're using products properly, and safety managers can have peace of mind that those products have been properly maintained, inspected and operated day in and day out.

Safety & Inspection Manager (SIM)

Gain valuable access to real-time product information and servicing data with a tap of your phone. Your customized dashboard gives you exactly the information you need and helps you track your PPE inventory like never before.


Now offering a Basic Fall Protection package to help meet your PPE inspection needs.

3M.com/ConnectedSafety



The ABCs of fall protection.


With over 20,000 products designed for the specific needs of every industry with at-height hazards, we can find the just-right combination of anchorages, body support and connector solutions to meet the requirements of virtually any application.



Anchorages

are a secure point of attachment.
Anchorage connectors vary by
industry, job, type of installation and
structure. They must be able to support
the intended loads and provide a
sufficient factor of safety for fall arrest.

| Anchorage connectors 5 |
|--------------------------|
| Horizontal systems |
| Vertical systems 23 |
| Engineered systems31 |
| Flexiguard™ solutions 35 |



Body support

harnesses distribute fall forces over the upper thighs, pelvis, chest and shoulders. They provide a connection point on the worker for the personal fall arrest system.


| Full-body harnesses 45 |
|-------------------------------------|
| Lineman belts and harnesses 62 |
| Belts, workseats and accessories 63 |



Connectors

such as self-retracting lifelines or shock-absorbing lanyards connect a worker's harness to the anchorage.


| Leading edge connectors 6 | 35 |
|---------------------------|----|
| Self-retracting lifelines | 71 |
| Shock-absorbing lanyards | 37 |
| Fall-restricting devices |)4 |



Descent and rescue

devices are used to raise or lower a fallen injured worker to safety or retrieve him from a confined space.


| Confined space rescue | • | • | • | • | • | • | • | • | • | 95 |
|-----------------------|---|---|---|---|---|---|---|---|---|-----|
| Rescue and descent | | | | | | | | | | 112 |



Education

is essential. We offer a variety of training and consultative services to fit your needs.

| Training | courses | | | | | | | | 11 | 18 | 3 |
|----------|---------|--|--|--|--|--|--|--|----|----|---|
| | | | | | | | | | | | |



Fall protection for tools

helps make work environments safer and more productive by reducing dropped object incidents.

| Fal | l pro | tection | for too | ls | • • • • | 120 |
|-----|-------|---------|---------|----|---------|-----|
|-----|-------|---------|---------|----|---------|-----|

Anchors designed to help you stay focused on the job.

Set your sights on a higher level of confidence and security with 3M™ DBI-SALA® Anchorage Connectors. Tested to meet OSHA and ANSI standards, our comprehensive portfolio of anchorage connectors gives you the gear you need to get the job done right.

- Anchorages for general/all-purpose, steel, concrete, roof, mining or specialty.
- Fixed or mobile.
- Permanent or portable.

All anchorages must provide a secure point of attachment for a complete personal fall arrest system and must be capable of supporting a load of 5,000 lbs. (22 kN), or of meeting OSHA's criteria of a 2-to-1 safety factor.

Anchorage Connectors: New Products



2104709

Strut Anchor

See page 7 for more information.



See page 7 for more information.



Swiveling Roof Anchor
See page 10 for more information.



2190073

Standing Seam Roof Anchor See page 10 for more information.



2190074

Construction Roof Anchor See page 10 for more information.

3M™ DBI-SALA® General Anchorage Connectors

Anchors are easily choked-off to the anchorage structure, to provide a fast and safe 5,000 lb. (22 kN) tie-off point for your personal fall protection system.

1003000

Web Tie-Off Adapter

Pass-through design. 1-3/4 in. polyester strength member with 3 in. wide polyester wear pad x 3 ft. (0.9 m)

1003006 Web Tie-Off Adapter, passthrough type x 6 ft. (1.8 m)

1002103 Adjustable Web Tie-Off Adapter, passthrough type x 3 ft. (0.9 m)

1002106 Adjustable Web Tie-Off Adapter, pass-through type x 6 ft. (1.8 m)

1002010 Web Tie-Off Adapter, pass-through type x 10 ft. (3.0 m)

1002202

Tie-Off Adapter for Hot Work Use

Reinforced with Kevlar® fiber webbing; ideal for high heat environments, pass-through type with 1-3/4 in. polyester strength member x 6 ft. (1.8 m)

1002200 Tie-Off Adapter, with Kevlar® fiber, passthrough type x 3 ft. (0.9 m)

1002201 Tie-Off Adapter, with Kevlar $^{\circ}$ fiber, pass-through type x 4 ft. (1.2 m)

5900550

Cable Tie-Off Adapter

Pass-through design. 7×19 (9.5 mm) stainless steel cable with O-rings $\times 4$ ft. (1.2 m)

5900551 Cable Tie-Off Adapter, pass-through type x 6 ft. (1.8 m)

5900552 Cable Tie-Off Adapter, pass-through type x 10 ft. (3.0 m)

1201390

Web Scaffold Choker

Choker style attaches to 3 in. (76 mm) diameter anchorage. 1 in. (25 mm) polyester strength member x 17 in. (43 cm)

1201391 Web Scaffold Choker x 24 in. (61 cm)

1201422 Coated Web Scaffold Choker, PVC Coated D-ring x 2 ft. (0.6 m)

3M™ DBI-SALA® Saflok™ Steel Carabiners



2000112 20

11/16 in. (17.5 mm) gate opening steel carabiner with self closing/ locking gate. 3,600 lb. (16 kN) gate strength.

2000113

1-3/16 in.
(30 mm) gate opening steel carabiner with self closing/ locking gate and captive eye pins.
3,600 lb. (16 kN) gate strength.

2000114

2-3/16 in. (55.5 mm) gate opening steel carabiner with self closing/ locking gate and captive eye pins. 3,600 lb. (16 kN) gate strength.

2104816

Drop-Through Anchor

10 ft. (3 m) drop-through anchor with swiveling D-ring for concrete (\geq 4 in. (101.6 mm) thick) and steel, fits 1-1/2 in. to 1-3/4 in. dia. hole (38.1 to 44.5 mm).

2104819 Drop-Through Anchor x 2 ft. (0.6 m)

2104818 Drop-Through Anchor x 6 ft. (1.8 m)

2104817 Drop-Through Anchor x 8.5 ft. (2.6 m)



3M™ DBI-SALA® Steel Anchorage Connectors

Anchors for steel that are lightweight and compact, providing an easy to install and safe 5,000 lb. (22 kN) tie-off point for your personal fall protection system.



Sliding Beam Anchor

- 3-1/2 in. to 14 in. beam width.
- Size ranges to fit a variety of beams.
- Replaceable wear pads.
- 360-degree swiveling D-ring anchor point.
- Integrated dual ratcheting system.
- Steel and aluminum construction weighs 3.5 lbs. (1.6 kg).
- 5,000 lb. (22 kN) strength

2104715 Sliding Beam Anchor, fits 12 in.-30 in. beam width

Call Customer Service for pallet offerings

2104709

Strut Anchor

- Allows for one step, one hand installation.
- One-piece design is simple, lightweight and compact.
- Accommodates 1-5/8 in. (4.1 cm) wide strut.
- Includes visual indicator that anchorage is installed correctly and ready for use.
 (Reflective tape visible from ground level with artificial light source.)





Fixed Beam Anchor

It installs to the beam structure in any orientation, with final tightening using a built-in adjustment handle. Ideal as a single-person anchor point or as end-anchors for any 3M Pre-engineered Horizontal Lifeline System. Fits up to 1-1/2 in. thick beam flange, 2-1/2 in. to 12 in. wide.

2108407 Fixed Beam Anchor, fits up to 1-1/2 in. thick x 2-1/2 in. to 18 in. wide beam flange.

2108408 Fixed Beam Anchor, fits up to 1-1/2 in. thick x 2-1/2 in. to 24 in. wide beam flange.

2108410 Fixed Beam Anchor, fits up to 1/2 in. to 2-1/2 in. thick x 12 in. to 36 in. wide beam flange.

2103143

Trolley for I-Beam

The trolley is for use with selfretracting lifelines on horizontal beams and has been engineered to glide along the beam and provide horizontal mobility.

- Double-shielded wheel bearings.
- Trolley guards protect the wheels from damage and keep beam clear of debris.
- Fits 3 in. to 8 in. flange width and thickness up to 11/16 in.

2103147 Trolley for I-Beam, all stainless steel, fits 3 in. to 8 in. flange width and thickness up to 11/16 in.



8800023

Tandem Pulley

For 3/8 in. to 1/2 in. rope or cable.



2104550

Steel Plate Anchor

This plate anchor offers a compact attachment to 3/8 in. to 1 in. thick plate steel for connecting your lanyard, vertical lifeline system or self-retracting lifeline.

- Easy-to-use set-screw design ensures positive and safe connection.
- Complete with integral D-ring tie-off point.
- Durable, corrosion-resistant zinc-plated steel construction.



3M™ DBI-SALA® Steel Anchorage Connectors (cont.)

2101630

D-Ring Anchorage Plate

The D-Ring Anchorage Plate can be bolted or welded to a structure, offering a compact connection point for your fall protection system.

- Two 1/2 in. diameter attachment holes.
- · Cadmium-plated steel D-ring.
- 304 stainless steel anchorage plate.
- Plate size: 1/4 in. x 2 in. x 4-1/2 in.

2101634 D-Ring Anchorage Plate with cadmium-plated steel D-ring, raw steel anchorage plate.

2101636 D-Ring Anchorage Plate with 304 stainless steel D-ring and anchorage plate.

2101638 D-Ring Anchorage Plate with 316 stainless steel D-ring and anchorage plate.



3M™ DBI-SALA® Concrete Anchorage Connectors

Anchors for concrete that are compact, providing an easy to install 5,000 lb. (22 kN) tie-off point for your personal fall protection system.

2104560

Concrete D-Ring Anchor

Concrete anchor solution for use in temporary or permanent applications, providing a safe tie-off point.

- Reusable D-ring assembly.
- Indicator shows when anchor is properly tightened.
- Install into 11/16 in. (18 mm) or 3/4 in. (19 mm) holes.



2104561 Concrete D-Ring Anchor with 5 additional bolts.

2104562 Concrete D-Ring Anchor with 11 additional bolts.

2100066 10-pack of Replacement Bolts for Concrete D-Ring Anchor.

2101004

Concrete Detent Anchor

Concrete anchor utilizing preinstalled sockets, enabling the user to connect and disconnect from the anchorage by simply pressing a button.

- Use for floor, wall or ceiling type applications.
- Provides convenient tie-off points wherever needed.
- Push-button operation for fast and easy operation.
- Socket includes cover cap to hide recess, blending into the decor.

2101000 Concrete Detent Socket and cap only.

2101002 Concrete Detent Pin only.

2100152 Concrete Pour-in-Place Anchor.

2100169 Pour-in-Place Detent Anchor Assembly with detent pin and socket.




3M™ DBI-SALA® Concrete Anchorage Connectors (cont.)

8523178

Concrete Parapet Anchor

Portable anchorage connector developed for use in locations where a low parapet wall provides an anchor site for a shock-absorbing lanyard or self-retracting lifeline.

- Non-penetrating design.
- Adjustment range 1 in. to 14-1/2 in. wide.
- No tools required for installation.



1231305

Web Anchor

Anchor can be directly connected to many concrete wall forms to provide a tie-off point for your system. Web anchor strap with large opening, Hook at one end, D-ring at other x 1.5 ft. (45 cm).



2100050

Concrete Anchor Strap

Our disposable concrete anchor strap provides a temporary anchorage on concrete forms.

- Loop slips over rebar, then concrete is poured over. When no longer needed, simply cut strap and discard.
- Durable 1-3/4 in. polyester construction x 3-1/2 ft. (1 m). Full length wear pad for abrasion resistance.
- D-ring provides compatible tie-off point.

2100053 Concrete Anchor Strap with D-ring, 48 in. (1.2 m)

2100061 Concrete Anchor Strap, no D-ring, 3-1/2 ft. (1 m)

3M™ DBI-SALA® Roof Anchorage Connectors

Wood or steel. Residential or commercial. Flat or sloped. No matter what type of roof you're working on, your fall protection system needs specialized components to help keep you safe. Our anchorage devices help to provide reliable solutions and meet applicable OSHA and ANSI standards for anchorage connectors.



Rooftop Anchors

- Four similar rooftop anchors designed specifically for certain roof types.
- Tip-over design reduces need for structural reinforcement and allows for connection right to roof deck.
- Can be used as a single point anchor, or pair two together to create a temporary horizontal lifeline.

 Connection method*

| 2100138 | Rooftop Anchor for Standing Seam Roofs | Standing Seam Clamps | 10/27/2013 |
|---------|--|----------------------|------------|
| 2100139 | Rooftop Anchor for Standard Membrane Roofs | Toggle / Screw | 6 |
| 2100140 | Rooftop Anchor for PVC Membrane Roofs | Toggle / Screw | 1 |
| 2100142 | Rooftop Anchor for Bitumen Membrane Roofs | Toggle / Screw | |

*Call Customer Service for item numbers.



2100185Freestanding
Counterweight Anchor



Permanent Roof Anchor with Flashing and Cap



2103673Portable Reusable Roof Anchor



2103677Portable Reusable Roof Anchor



2104541Detachable Roof Anchor with Flashing



3-Man Reusable Swiveling Roof Anchor



2190071

Swiveling Roof Anchor

- Installs to sloped or flat wood and metal decking roofs.
- Fast and easy installation.
- Secondary d-ring anchor point.
- Portable and reusable.



2190073

Standing Seam Roof Anchor

- Installs to flat or sloped standing seam roofs.
- Built-in non-penetrating clamp design.
- Slide on the tube.
- Portable and reusable.



2190074

2103690

Construction Roof Anchor

- Installs to rebar ring during pre-cast concrete work.
- Built-in ratcheting securement system.
- Dual-use design.
- Portable and reusable.

3M™ DBI-SALA® Roof Anchorage Connectors (cont.)

Selection Guide:

| Part # | Wood attachment - OK | Metal attachment - OK, minimum thickness | OK to Use with HLL | Attachment method | Permanent installation | OSHA compliant |
|---------|----------------------|--|---|--|------------------------|-------------------|
| 2100133 | ■ (5/8 in. plywood) | ■ 24 Ga. | • | Lag screws (wood), anchors (concrete), rivets or Fablok or Tek screws (metal) | ■ (5/8 in. plywood) | • |
| 2100138 | | ■ Fits standing seam centers 15.75 in. x 11.8 in. w/clamp kits | • | 7241204 for bulb type seam, 7241206 for double folded standing seam, 7241208 for single folding seam | | • |
| 2100139 | | ■ Installs to standard membrane and built-up type roofs | 4 bolts: 7241182 6 in. toggle bolt, or 7241183 12 in. toggle bolt | | • | |
| 2100140 | | ■ Single-ply PVC membrane and built-up roofs | • | 4 bolts: 7241182 6 in. toggle bolt, or 7241183 12 in. toggle bolt | | |
| 2100142 | | ■ Single ply Bitumin and built-up roofs | • | 4 bolts: 7241182 6 in. toggle bolt, or 7241183 12 in. toggle bolt | | |
| 2100185 | | ■ Flat roofs up to 5 degrees of slope | | 4 bolts: 7241182 6 in. toggle bolt, or 7241183 12 in. toggle bolt | | |
| 2103670 | • | | U-Bolt clamps (included) to rafter or truss, 2 × 4 , 2 × 8 | | • | |
| 2103671 | • | | | U-Bolt clamps (included) to rafter or truss, 2 × 10, 2 × 12 | • | |
| 2103673 | • | | ■ Synthetic Sayfline™ or PRO-Line of slope | or (1/4 inch size) Lag screws | | |
| 2190073 | | ■ Flat or sloped roofs | | Clamps to seam | | |
| 2190074 | | | | Built-in ratchet system that installs to rebar ring | | |
| 2103676 | | ■ 22 Ga. deck | | Nails or Tek screws | | |
| 2103677 | | | | Lag screws | | |
| 2103690 | • | | | Deck screws | | |
| 2104540 | | | | Bolts w/clamp | - | |
| 2104541 | • | | | Bolts w/clamp | - | • |
| 2104542 | | | | Bolts w/clamp | • | • |
| 2105682 | | | | Lag screws or nails | | |

 ${\it Read user instruction manual for complete information on use and limitations.}$



2104168

Roofer's Fall Protection Kit

Complete fall protection system in a bag for convenient compliance and safety on the job.

Kit includes:

- Reusable Roof Anchor (2103673)
- Full-Body Harness (1103513)
- Rope Adjuster with Shock-Absorbing Lanyard (1246037)
- Lifeline x 50 ft. (1202794)
- Counterweight (5901583)
- Carrying Bag (9503806)

2104169 Roofer's Fall Protection Kit with Roof Anchor (2103676)



Specific jobsites call for unique anchorage devices. That's why we developed a complete line, all rigorously tested to meet OSHA and ANSI standards and help ensure strength. These devices support loads of 5,000 lbs. (22 kN) per worker, helping to anchor your personal fall arrest system to the main structure—whether it's concrete, wood, steel or something else.

3M™ Protecta®

General (All-Purpose) Anchorage

These lightweight, portable anchors are a great choice for a variety of applications. Many are "choker" style, designed to create an easy-to-use anchor on an overhead location beyond normal reach—all with a high strength 5,000 lb. (22 kN) rating.

Web Tie-Off Adapter 5900578

Pass-through design makes attaching to anchorage quick and easy. 1-3/4 in. x 6ft (1.8m) polyester.

5900576 1-3/4 in. x 2 ft. (0.61 m) Adapter

5900577 1-3/4 in. x 3 ft. (0.9 m) Adapter

5900578 1-3/4 in. x 6 ft. (1.8 m) Adapter

5900579 1-3/4 in. x 8 ft. (2.4 m) Adapter

5900580 2 in. x 12 ft. (3.7 m) Adapter 5900581 2 in. x 16 ft. (4.9 m) Adapter

5900582 2 in. x 20 ft. (6.1 m) Adapter

Cable Dual Ring Tie-Off Adapter 2190102

1/4 in. galvanized cable dual-ring tie-off adaptor, carabiner at one end, two D-rings at the other x 6 ft. (1.8 m).

2190100 3 ft. (0.9 m) Adapter

2190101 4 ft. (1.2 m) Adapter

85

Cable Tie-Off Adapter 2100193

Galvanized cable tie-off adapter, pass-through type x 6 ft. (1.8 m). 2100192 4 ft. (1.2 m) Adapter



Cable Anchorage Extension AJ408AG

Lightweight and extremely durable 1/4 in. (6.4 mm) coated galvanized cable stands up to harsh environments Snap hook at one end, O-ring at other x 6 ft. (1.8 m).

AJ408AG4 4 ft. (1.2 m) 1/4 in. Extension

Carabiner 2000112

Reduced weight. Easy operation. Steel carabiners make for a versatile option to help keep your system securely connected. The 5,000 lb. (22 kN) minimum breaking strength and 3,600 lb. (16 kN) self-closing/locking gate enhance safety. 11/16 in. (17.5 mm) opening.

2000117 With roll pin, 11/16 in. (1.75 cm) opening

2000114 With 2-3/16 in. (5.56 cm) opening



Anchorage Connectors

3M[™] Protecta[®] Sliding Beam Anchor

Work confidently with the 3M[™] Protecta[®] Sliding Beam Anchor. This durable solution provides a high-strength anchorage point that follows you while you work. Once you

secure it to the beam using the integrated adjustment buttons, simply connect your Self-Retracting Lifeline (SRL)* or lanyard to the rotating D-ring and you're ready to work.

*Use 3M™ DBI-SALA® Nano-Lok™ edge Twin-Leg Quick-Connect Self-Retracting Lifeline – Cable when tying off at feet.





- ▶ Bridge work
- **▶** Buildings
- **▶** Warehouses
- Arenas
- ▶ Parking ramps

Versatile size ranges to fit a variety of beams

- Replaceable wear pads
- Centered, D-ring anchor point
- ➤ 5,000 lb. (22 kN) strength and up to 420 lb. (189 kg) capacity



Ordering information

| Part # | Beam Width | Flange Thickness | Description |
|---------|---------------|---------------------|-------------------------------|
| 2104703 | 3.5-14 in. | 1.25 in. | Sliding Beam Anchor (ANSI) |

For foot level tie-off, use 3M™ DBI-SALA® Nano-Lok™ edge Twin-Leg Quick-Connect Self-Retracting Lifeline – Cable, 8 ft. (2.4 m)

Model shown 3500225



Fully adjustable

Integrated dual ratcheting adjustment system slides to fit snugly against the beam.

Guarded locking mechanism

Located on the bottom to reduce chance of accidental disengagement.

Versatile size range

Fits beam flanges 3-1/2 in. to 14 in. (9 cm-35.5 cm) wide and up to 1-1/4 in. (3.2 cm) thick.

Built to last

Rugged, corrosion resistant construction enhances longevity.

Replaceable wear pads

Eliminate metal-tometal contact and extend the usability

Compliant

Meets ANSI Z359.18 and OSHA 1910.140, 1926.502 Anchorage Connector standards.

3M™ Protecta®

Steel Anchorage

These lightweight, versatile anchors are often used during commercial construction and attached to steel columns and beams. Models can be permanently attached or temporarily clamped, offering a fixed or mobile anchorage connector. The result is an easy-to-install and secure 5,000 lb. (22 kN) tie-off point for your personal fall protection system.

Eyebolt Anchor – Unthreaded AN111A

Unthreaded ring only (no bolt), forged steel construction with zinc plating, 1-1/2 in. ID anchor area.



Eyebolt Anchor – Threaded AN112A

Forged steel construction with zinc plating, 1/2 in. x 1-3/8 in. mounting bolt, 2-3/4 in. ID horizontal anchor area and 1-3/8 in. ID vertical anchor area.



3M™ Protecta®

Concrete Anchorage

Secured to concrete decks and columns, these anchors are lightweight and compact, providing an easy to install and secure 5,000 lb. (22 kN) tie-off point for enhanced worker mobility on concrete construction sites.


Reusable Wedge Anchor 2190053

A portable, easy-to-use concrete anchor for vertical walls or overhead ceilings.



Concrete Anchor Strap 2190057

Pack of 25 disposable anchor straps with D-ring x 3-1/2 ft. (1 m) is designed to provide a temporary anchorage on concrete forms. Loop slips over rebar, then concrete is poured over. When no longer needed, simply cut strap and discard.



2190063 Without D-Ring x 3-1/2 ft. (1 m) - Pack of 25



Concrete D-Ring Anchor 2190055

Simple, versatile concrete anchor for temporary or permanent applications. Extremely rugged design for extended life and jobsite flexibility.

2190060 With 6 bolts



Mounts horizontally or vertically to concrete or steel. Includes forced D-ring for tie-off point and 4 concrete wedge anchor bolts.



Creates a mobile anchor in standard strut material. Stainless steel plates with steel carabiner. Accommodates 1-5/8 in. (4.1 cm) wide strut material.







Anchorage Connectors

3M™ Protecta®

Roof Anchors

Create a secure anchor point on a variety of roof designs without damaging the structure. Our complete array of anchorage devices for sloped wood and flat commercial steel roofs can help you customize the fall protection solution that's right for your application.

Portable Reusable Roof Anchor 2104000


For use on flat or sloped wood roofs. Installs with 32 ea. #8 screws or 32 ea. 16d nails. Simple hinge-style design is extremely easy to transport, install, dismantle and store.



Knock-Down Disposable Roof Anchor Kit 2103680

Simply nail into sheathing and roof member. When job is complete, knock down or shingle over. Kit contains 12 anchors and nails.





Fast and easy anchor points for at-height work.

3M[™] Protecta[®] Roof Anchors give you versatility to get the job done.

For harsh construction environments, you need roof anchorage points you can count on. 3M™ Protecta® Roof Anchors are durable to help you get the job done efficiently day after day, month after month. They're easy to install on flat or sloped roofs and can be used for wood or metal surfaces.



Standing Seam Roof Anchor 2190072

- ► Installs to Flat or Sloped Standing Seam Roofs System clamps to standing seams without special tools, providing an anchorage point for an SRL.
- Non-Penetrating Design Four seam clamps allows for quick attachment without damaging the roof.
- Adjustable Legs Simple bolt style adjustable legs allow you to size the system to a variety of seam spacing. Fits a variety of seam spacings up to 36 in.
- Portable and Reusable
 Anchor can be removed and simply reinstalled in a new location for added jobsite flexibility.

Swiveling Roof Anchor 2190070



- Installs to Sloped or Flat Wood and Metal Decking Roofs Anchor can be installed to a variety of roofing materials to provide an anchorage point for an SRL.
- Fast and Easy Installation
 Fastener kit included—includes 16 ea. ¼-14 × 2-1/2 in. self-tapping screws for steel installation and 8 ea. ¼ x 2-1/2 in. lag screws for wood.
- Portable and Reusable Anchor can be removed and simply reinstalled in a new location for added jobsite flexibility.
- 360-degree Swiveling Maximizes your mobility.

3M™ DBI-SALA® Remote Anchoring Systems





2104527

Remote Anchoring System

Provides anchorage connection to secure a fall protection device to an overhead location beyond normal reach.

- Pole adjusts from 6 ft. to 12 ft. (1.8 m to 3.6 m)
- Tie-off adapter tool for installation of anchorage device.
- Hook attachment tool for installation of 3,600 lb. gated snap hooks.
- Tie-off adapter x 3 ft. (0.9 m) and carrying bag.

2104528 System with 8 ft.-16 ft. (2.4 m-4.8 m) adjustable pole

2104529 Snap Hook Connector Tool for 3,600 lb. gated hooks.



Freestanding, non-penetrating anchor for concrete decking construction and provides overhead anchorages for up to two users.

- Large foam filled trailer tires won't go flat and provide easy movement.
- 7-1/2 ft. (2.3 m) mast and anchorage arm for added freedom of movement.
- Pre-drilled holes for accessory rescue winches.



2100080

Door/Window Jamb Anchor

Non-penetrating anchor is lightweight and portable, requiring no tools for attachment. Adjustable opening ranging from 21-1/2 in. to 51-1/2 in. (54.6 cm to 130.8 cm). Rated for 3,600 lbs. (16 kN)



This Self-Contained Vacuum Anchor (SCVA) System allows workers to anchor to compatible, smooth, non-porous surfaces—enabling them to work where they need to without compromising their fall protection safety. At just over 19 lbs., the system provides workers the freedom to move about with confidence. All models are OSHA, CE and AS/NZS compliant and feature a comprehensive backup system to enhance worker safety.



Anchorage Connectors

3M™ DBI-SALA® Ultra-Lok™ Self Retracting Lifeline, Rope Page 83



Product specifications:

| | Shop air powered | Shop air/gas powered | |
|--|---|-----------------------|--|
| Main support assembly | Anodized a | aluminum | |
| Vacuum seal pad material — aviation | EPD | M | |
| Vacuum seal pad material — general industry | Vacuum seal pad material — general industry Polybutadiene | | |
| Shop air requirements | 80 psi to 150 psi | | |
| Compressed gas bottle requirements | — 3,000 ps | | |
| Dimensions | 22 in. x 22 in. x 6 in. (55 | 5 cm x 55 cm x 15 cm) | |
| System weight | 17.4 lbs. (7.8 kg) | 19.9 lbs. (9.0 kg) | |
| Capacity | 310 lbs. (140 kg); One person | | |
| Surface temperature range -20°F to 140°F (-29°C to 60°C) | | | |

Selection Guide:

| Components | Aviation | General industry | |
|--|----------|------------------|--|
| SCVA assembly (shop air powered) | 2200107 | 2200094 | |
| SCVA assembly with on board bottle attachment (shop air or gas powered) | 2200108* | 2200095 | |
| Secondary pad assembly (optional) | 2200109 | 2200096 | |
| Secondary pad hose (optional) — 50 ft. (15 m) | 2200130 | | |
| Aviation HLL kit (includes secondary pad, 40 ft. HLL, and secondary pad 50 ft. hose) | 2200123 | _ | |
| Compressed gas cylinder (bottle sold separately) | 2200 | 085 | |



3M[™] DBI-SALA[®] Horizontal Systems

Choosing a horizontal lifeline system

It's critical to choose a system that has been precision engineered and rigorously tested to meet OSHA requirements. Some other important considerations include:

Anchorage structure

The I-beam, rebar stud, concrete column or roof you attach your system to can dictate the type of system required.

Portable or permanent

Temporary jobs require portable systems that can be moved efficiently from one location to another. For hazardous areas that need to be accessed often, a permanent solution may be a better choice.

Lifeline type

Synthetic lines are lightweight and compact, while galvanized or stainless steel offer enhanced corrosion and abrasion resistance.

Number of users

Consider the number of workers required and choose a system that can accommodate them safely.

Clearance requirements

The distance between the work area and the next level or obstruction below is called "fall clearance." Anchorage height, type of lifeline and length are some of the factors that will affect the required clearance needed.



3M[™] DBI-SALA® Temporary Cable Horizontal Lifeline System for Stanchions

These systems incorporate a modular, multi-base design that accommodates a wide range of steel and concrete beams.

- Interchangeable stanchions—great for steel and concrete applications.
- Portable.
- Single and multi-span options available.
- Pass-through bracket provides 100% tie-off capability.
- Integrated 3M[™] DBI-SALA[®] metal energy absorber limits forces on structure.

Steel I-Beam Applications

- Single clamp and wing nut design.
- Adjustments made from top of beam.
- Fits flanges 6 in.-12 in. wide, 2-1/4 in. thick.
- Optional bases for 18 in., 24 in. and 36 in. widths.

Concrete rebar & shear stud applications

- Attach with torque wrench.
- Chain tie-back connection.
- Fits 1/2 in-1 in. diameter (#4-#8 rebar) and 4 in.-12 in. center to center.

3M[™] DBI-SALA[®] Temporary Cable Horizontal Lifeline System for Stanchions

Complete single span system includes two stanchions (7400047) and cable assembly with tensioner and metal energy absorber. 60 ft. (18.3 m)

Selection guide:

| | Stanchion | Tie-Back Base |
|------------------|-----------|---------------|
| I-Beam | 7400047 | - |
| Rebar/Shear Stud | 7400215 | 7400214 |

Systems shown with intermediate stanchions—sold separately.


3M™ DBI-SALA® Temporary Cable Loop Rebar Horizontal Lifeline System for Stanchions

These complete single-span systems include two stanchions and cable assembly with tensioner and metal energy absorber.

Selection guide:

| 20 ft. | 40 ft. | 60 ft. | Stanchion | |
|---------|---------|---------|-----------|--|
| 7400320 | 7400340 | 7400360 | 7400045 | |

Systems shown with intermediate stanchions—sold separately.





Stanchion with Loop Rebar
Base and Pass-Through Bracket




Shown with tie-back base with chain.

3M™ DBI-SALA® Temporary Cable Horizontal Lifeline System for Stanchions I-Beam Components

7400087

Perpendicular I-Beam System Components Stanchion with Perpendicular I-Beam Base No tie back, fits 8 in.–14 in. flange.



7400086

Perpendicular I-Beam Base Only Fits 8 in.–14 in. flange.



7400089

Perpendicular Pass-Through Kit

3M™ DBI-SALA® Temporary Cable Horizontal Lifeline System for Stanchions Parallel I-Beam Components

| Carrollian with I Danie Danie | 6 - 12 in. Flange | 12 - 18 in. Flange | 18 - 24 in. Flange | 24 - 36 in. Flange |
|--|--|---|---|---|
| Stanchion with I-Beam Base | 7400047 | 7400055 | 7400056 | 7400057 |
| L Baam Baaa Onbi | 6 - 12 in. Flange | 12 - 18 in. Flange | 18 - 24 in. Flange | 24 - 36 in. Flange |
| I-Beam Base Only | 7400052 | 7400065 | 7400066 | 6700067 |
| Stanchion with I-Beam Base, Range of 2-2/3 in. to | Range of 2-2/3 in. to 3-3/8 in. thick, 6 - 12 in. wide | Range of 2-2/3 in. to 3-3/8 in. thick, 12 - 18 in. wide | Range of 2-2/3 in. to 3-3/8 in. thick, 18 - 24 in. wide | Range of 2-2/3 in. to 3-3/8 in. thick, 24 - 36 in. wide |
| 3-3/8 in. Thick Flange | 7400015 | 7400032 | 7400033 | 7400034 |

3M™ DBI-SALA® Temporary Cable Horizontal Lifeline System for Stanchions Cable Assembly

Available 10–330 ft. lengths in 10 ft. increments. Cables available up to 720 ft.—please call customer service for part number on any cable over 330 ft. in length.





Lifeline options for all systems—cable assembly with turnbuckle and metal energy absorber are available in 10 ft. increments. Cable assemblies over 60 ft. include two metal energy absorbers.

3M™ DBI-SALA® Temporary Cable Horizontal Lifeline System for Stanchions Rebar System Components

7400215

Stanchion with Rebar/Shear Stud Base Pass-through and end anchor brackets.

7400053

End-Anchor Retro-Fit Kit

With rebar/shear stud base, tie-back assembly, end-anchor and pass-through bracket.

7400054

Intermediate Retro-Fit Kit With rebar/shear stud base and pass-through bracket.

7400214

Tie-Back Base and Chain Assembly



3M™ DBI-SALA® EZ-Line™ Retractable Horizontal Lifeline (HLL) System





Retractable Horizontal Lifeline (HLL) System

This is an easy-to-use lifeline system that you can install, remove and store quickly.

- Can reduce installation time vs. standard horizontal lifeline systems.
- Can be setup to accommodate 6 total users (2 per sub-span).
- Includes built in pre-tension and impact indicators.

7600002 Replacement EZ-Line Handle Assembly

See product instruction manual for complete clearance information.


7241031 Metal energy absorber kit used when multi-spans are required

3M™ DBI-SALA® Temporary Cable Horizontal Lifeline System

These systems are portable and can be used for situations where welding, sparks or harsh environments are present, or where minimum clearance exists.

- Includes cable lifeline assembly with wedge grip termination, tensioner and 3M™ DBI-SALA® metal energy absorber.
- Durable all-metal system can be left in place for long periods.
- Use with any 5,000 lb. anchorage device.

Two worker capacity.



Selection guide

length

| 20 ft. | 30 ft. | 40 ft. | 50 ft. | 60 ft. | 70 ft. | 80 ft. | 90 ft. | 100 ft. |
|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 7602020 | 7602030 | 7602040 | 7602050 | 7602060 | 7602070 | 7602080 | 7602090 | 7602100 |

3M™ DBI-SALA® Temporary Kernmantle Rope Horizontal Lifeline System

Portable systems that can be used for maintenance, bridge work, construction and general industry applications.

- Kernmantle rope lifeline with tensioner and shock absorber.
- Capacity of two workers.



Selection guide:

| 20 ft. | 30 ft. | 40 ft. | 50 ft. | 60 ft. | 70 ft. | 80 ft. | 90 ft. | 100 ft. | |
|---------|---------|---------|---------|---------|---------|---------|---------|---------|--|
| 7600502 | 7600503 | 7600504 | 7600505 | 7600506 | 7600507 | 7600508 | 7600509 | 7600510 | |

length

See product instruction manual for complete clearance information.

3M™ DBI-SALA® Temporary Cable Pour-in-Place Horizontal Lifeline System for Stanchions

7400203

This portable system installs to column tops, providing an overhead tie-off point during the decking process. Complete system includes two stanchions, and 20 ft. cable assembly with tensioner and 3M™ DBI-SALA® metal energy absorber.

- Single and multi-span options with unlimited length.
- Pass-through design provides protection for up to two workers.



3M[™] DBI-SALA[®] Temporary Cable Pour-in-Place Horizontal Lifeline System for Stanchions Accessories

7400200

Intermediate Bracket

Allows system to be configured into multi-span type; intermediate can be bypassed with connector snap hook.



Stanchion Assembly 7 ft. 6 in. tall.

7400201

Concrete Sleeve

For pour-in-place post horizontal lifeline systems.



7400211

Clamp-On Vertical Base

Clamps to existing vertical steel and concrete structures, zincplated steel construction.



7400222

Weld-On Vertical Base

Welds to vertical steel structures, steel C-channel construction.



7400218

Bolt-On Vertical Base

Bolts to vertical steel and concrete structures, zinc-plated steel construction.



8530267

Bolt-On Floor Base

Bolts to steel and concrete horizontal surfaces, zinc-plated steel construction.

8530827 304 Stainless Steel.



3M™ DBI-SALA® Horizontal Lifeline Components

3M™ DBI-SALA® Metal Energy Absorber Kits

Allows use of standard 5,000 lb. rated anchors.

Accessory products:

- 1. Cable clips 9501563
- 2. O-rings 9503880
- 3. Thimbles 9506596
- 4. Turnbuckle 7002050
- 5. Wedge Grip Horizontal Lifeline Termination Device 7608008
- 6. Metal energy absorber 7401013



Selection guide:

| 7401013 | 7401031 | 7401032 | 7401033 | 7600580 |
|-------------------------------|--|--|--|---|
| metal energy absorber only | metal energy absorber with 2 shackles, bolts, nuts | metal energy absorber with 2 shackles, bolts, nuts, turnbuckle | metal energy absorber with 3 shackles, bolts, nuts, turnbuckle, thimbles, cable clips | metal energy absorber with 3 shackles, bolts, nuts, turnbuckle, thimbles, cable clips with wedge grip, 2 O-rings |

4.

These horizontal lifeline systems aren't just easy to use—they're easy to install with the support of our network of certified installers. Call customer service for more information.

- Pre-engineered or customized.
- Provides continuous fall protection.
- Shouldn't conflict with other building safety systems.

See page 31 for more information on 3M™ DBI-SALA® Engineered Systems.




Comparison guide:

| | EZ-Line [™] | Sayfline Synthetic | Sayfline Cable | Multi-Span | SecuraSpan | | |
|-------------------------------|---|--------------------|----------------|------------|---------------------------------|--|--|
| Maximum Length | 60 ft. | 100 ft. | 100 ft. | 180 ft. | 600+ ft. | | |
| Maximum Span Length | 60 ft. | 100 ft. | 100 ft. | 30 ft. | 60 ft. w/stanchions, 100 ft. | | |
| Minimum Anchorage Strength | 5,000 lbs. | 5,000 lbs. | 5,000 lbs. | 5,000 lbs. | 5,000 lbs. | | |
| Multi-spans Allowed | Yes | No | No | Yes | Yes | | |
| Maximum Number of Spans | Many | 1 | Many | 12 | Many | | |
| Maximum Users on System | 6 | 2 | 6 | 2 | 6 | | |
| Maximum Users on Span | 2 | 2 | 2 | 2 | 2 | | |
| 420 lb. Capacity | Yes, derate system to single person per span. | | | | | | |

3M[™] DBI-SALA[®] Temporary Multispan Cable Horizontal Lifeline System

Temporary Multispan Cable Horizontal Lifeline Systems are designed for "off-the-shelf" user installation. Custom lengths are available, call customer service for more information.

- Provides 100% continuous fall protection for two workers when they are properly attached to the appropriate lifeline.
- One-piece sleeve bypasses intermediates.
- System includes lifeline, intermediate bracket (one per 30 ft. span), termination hardware, tensioner and two metal energy absorbers.





Selection guide:

| | 20 ft. | 40 ft. | 60 ft. | 80 ft. | 100 ft. | 120 ft. | 140 ft. | 160 ft. | 180 ft. |
|--------------------|---------|--|---------|---------|---------|---------|---------|---------|---------|
| Galvanized | 7603020 | 7603040 | 7603060 | 7603080 | 7603100 | 7603120 | 7603140 | 7603160 | 7603180 |
| Stainless Steel | | Contact Customer Service for part numbers. | | | | | | | |

Sayflink sleeve sold separately.

Temporary Multispan Cable Accessories


7608001

Intermediate Bracket For multi-span systems.



7608002





3M™ DBI-SALA® Vertical Systems are designed to complement your ability to work while meeting all applicable OSHA and ANSI standards.

Vertical fall protection systems allow workers to move up and down the entire height of the lifeline rather than having to disconnect and find new tie-off points along the way. Some important considerations when selecting a system include:

Portable or permanent

Temporary jobs require portable systems with synthetic lifelines that can be moved from one location to another. For structures that are accessed often, a permanent solution is a better choice.

Mobile or fixed

Mobile rope grab or ladder sleeve designs automatically follow the user for easy operation. Fixed devices allow the user to fix the unit in place for positioning or restraint applications.

The rules have changed: walking-working surfaces

OSHA's final rule to update general industry walkingworking surfaces and fall protection standards (29 CFR 1910.140) means that outdoor advertising fixed ladders over 24 feet will require ladder safety or personal fall arrest systems. It also means that fixed ladder cages and wells must be phased out and replaced by ladder safety or fall arrest systems by 2036.

3M[™] DBI-SALA[®] Lad-Saf[™] Flexible Cable Vertical Safety Systems

Adding or upgrading your vertical safety systems just got easier. The new generation of Lad-Saf Systems are reengineered to simplify and speed up the installation process. With up to 72% fewer loose components* than some of our previous models, these lightweight systems are streamlined for easy installation and maintenance on a variety of structures—such as fixed ladders and telecommunication towers.

They have also been designed to meet the requirements of the new ANSI Z359.16 standard when used with our Lad-Saf X2 or X3 sleeve, helping you to stay in compliance with the current fall protection standards.

6116632

Rung, 2 User, Stainless Steel

6116631

Rung, 2 User, Galvanized Steel



Convenient

Integrated fall arrest-rated anchor point.

Fast

Installation is easy with fewer loose parts and more robust cable tensioning and termination as compared to our previous systems.

New Pre-Swaged Cable Termination

Durable, high-strength steel construction that allows for easy installation and maintenance-free longevity.

Flexible

Mounting brackets can be used on a variety of fixed ladder styles that may consist of different rung spacings and shapes.

Light

Total system weighs less than our previous 2- and 4-user systems.

Simple

Most configurations use fewer than 13 separate components—up to 72% less than some of our previous models.



Previous Generation

Cable

Compatible

Designed for use with your Lad-Saf X3 Detachable Cable Sleeve (6160054). Also compatible with Lad-Saf X2 Detachable Cable Sleeve (6160030).

*On specific models.

Introducing

3M[™] SecureFit[™] Safety Helmet X5000 Series

Achieve comfort without compromise while you climb.

3M.com/SecureFitSafetyHelmet





3M[™] DBI-SALA[®] Lad-Saf[™] Flexible Cable Vertical Safety Systems

6116633 6116634 6116618 6116636 Rung, 4 User, Monopole, 4 User, Telescoping Extension, Climb Extension, 4 User, Galvanized Steel 2 User, Galvanized Steel Galvanized Steel Ideal to provide access to rooftops through a roof hatch. Galvanized Steel 6116638 Monopole, 4 User, Stainless Steel

3M[™] DBI-SALA[®] Lad-Saf[™] Custom Configured Systems

Choose from each of the following categories:

Top & Bottom Bracket System (both brackets included)

| Application | User | Material | Part # |
|-----------------------|--------|------------------|---------|
| Rung | 2 User | Galvanized Steel | 6116631 |
| Rung | 2 User | Stainless Steel | 6116632 |
| Rung | 4 User | Galvanized Steel | 6116633 |
| Wood Pole | 2 User | Galvanized Steel | 6116635 |
| Monopole | 4 User | Galvanized Steel | 6116634 |
| Monopole | 4 User | Stainless Steel | 6116638 |
| Climb Extension | 2 User | Galvanized Steel | 6116636 |
| Telescoping Extension | 4 User | Galvanized Steel | 6116618 |

Pre-swaged cable at desired length

First 4 numbers in SKU represent the cable type, last 3 numbers represent cable length in feet.

| Part # | 6104XXX | 6105XXX | 6106XXX | 6107XXX |
|-------------------|---------------------|---------------------|---------------------|---------------------|
| Diameter | 3/8 in. (9.5 mm) |
| Strand | 1×7 | 1×7 | 7 × 19 | 7 × 19 |
| Steel | Galvanized | Stainless | Galvanized | Stainless |
| Preformed | Left, Regular Lay | Left, Regular Lay | Right, Regular Lay | Right, Regular Lay |
| Compliance | RR-W-410 | RR-W-410 | RR-W-410 | RR-W-410 |
| Breaking strength | 15,400 lbs. minimum | 18,000 lbs. minimum | 14,400 lbs. minimum | 12,000 lbs. minimum |

Lifeline cable offered in:

- 10-100 ft. in 5 ft. increments
- 100-200 ft. in 10 ft. increments
- Over 200 ft. in 20 ft. increments





Cable guides as needed (recommended every 20-40 feet)

| • | · | , | |
|-------------------------|----------------|------------------|---------|
| Application(s) | Туре | Material | Part # |
| Ladder | Straight Guide | Galvanized Steel | 6100400 |
| Ladder | Straight Guide | Stainless Steel | 6100457 |
| Ladder | L Guide | Stainless Steel | 6100513 |
| Ladder | Straight Guide | Galvanized Steel | 6100530 |
| Telescoping & Extension | Straight Guide | Stainless Steel | 6100401 |
| Monopole | L Guide | Galvanized Steel | 6100515 |
| Wood Pole | Straight Guide | Stainless Steel | 6100140 |

6100400



Additional cable guides available. Contact your 3M Fall Protection Sales Representative for more information.

3M™ DBI-SALA® Lad-Saf™ Complete Systems

Ordering a complete system is now even easier. We offer our most popular systems and lengths including all bracketry, cable, and guides—all in one single SKU.

2-User Ladder System and Cable

| Cable Length | 20 ft. | 30 ft. | 40 ft. | 50 ft. | 60 ft. | 70 ft. | 80 ft. | 90 ft. | 100 ft. |
|--|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| Guides Included | 0 | 1 | 1 | 1 | 2 | 2 | 2 | 3 | 3 |
| Galvanized Steel: • 6116631: Rung, 2-User • 6104XXX: 1 × 7 Swaged Cable, 3/8 in. • 6100400: Cable Guide for fixed ladder (1 per 30 ft.) | 6118020 | 6118030 | 6118040 | 6118050 | 6118060 | 6118070 | 6118080 | 6118090 | 6118100 |
| Stainless Steel: | 6119020 | 6119030 | 6119040 | 6119050 | 6119060 | 6119070 | 6119080 | 6119090 | 6119100 |



5901980

Ladder Gate

Designed to help protect you from the dangers (and liability) of unauthorized ladder access.

- Fits ladder widths up to 20 in. (50.8 cm). Mounting hardware included.
- Aluminum construction 8 ft. (2.4 m) height x 36 in. (91.4 cm) width.

Walking-Working Surfaces:

General Industry 29 CFR 1910 Ladder Requirements

Applies to fixed ladders that extend over 24 feet.

Employers must equip existing fixed ladders with a cage, well, ladder safety system or personal fall arrest system.


Effective November 19, 2018

Employers must begin equipping new fixed ladders with a ladder safety system or personal fall arrest system.

Effective November 19, 2018

All fixed ladders must be equipped with a ladder safety system or personal fall arrest system.

Deadline: November 18, 2036



3M™ DBI-SALA® Fixed Ladder SRL Anchor



An alternative option to bring your ladders into compliance is here: the 3M™ DBI-SALA® Fixed Ladder SRL Anchor. At under 30 lbs., this solution adds a convenient tie-off point to existing ladders, helping you meet OSHA's walking working surfaces standard.

Designed with versatile mounting capabilities, the ladder anchor can be positioned to the left or right, and in front or behind the ladder rungs to stay out of the way.

Transportable.

 Under 30 lbs. for ease of transport and installation.

Simple setup.

• Some installations may be made in as little as 5 minutes.

Compatible with your existing fall protection harness.

 Unlike a fixed cable system, this solution doesn't require a front D-ring, which can reduce overall implementation costs.

Versatile installation.

 The ladder anchor can be mounted to the front or behind the ladder with left, right or center alignments.

Designed for durability.

 Available in galvanized or stainless steel.

Compliant to standards.

 Meets 29 CFR OSHA 1910 Walking Working Surfaces Section 1910.27.

3M™ DBI-SALA® Fixed Ladder SRL Anchors

| Model # | Length* | Material |
|---------|---------|-----------------|
| 6100562 | 4 ft. | Galvanized |
| 6100563 | 4 ft. | Stainless Steel |
| 6100564 | 6 ft. | Galvanized |
| 6100565 | 6 ft. | Stainless Steel |

^{*}Average distance from top rung connection to the anchor point

All ladder anchor SKUs and associated products available in pallet SKUs. Please contact Customer Service.

Accessories

3M[™] DBI-SALA[®] Smart Lock Self-Retracting Lifeline

1,350 lb. Maximum Arresting Force (MAF)

3503803 20 ft. SRL, Galv. Cable

3503804 20 ft. SRL, SS Cable

3503800 30 ft. SRL, Galv. Cable

3503801 30 ft. SRL, SS Cable

6100566

Ladder Anchor Tagline



Complete Systems

6100568

- 3M[™] DBI-SALA® Fixed Ladder SRL Anchor, 4 ft. galvanized
- Smart Lock SRL, 30 ft.
- Tagline

6100569

- 3M[™] DBI-SALA[®] Fixed Ladder SRL Anchor, 4 ft. galvanized
- Smart Lock SRL, 50 ft.
- Tagline



3M™ DBI-SALA® SSB Systems

SSB (Speed Sensing Brake) Systems support workers' motions and provides fall protection while climbing tall ladders and towers. Great for on-shore and off-shore drilling platforms.


Added safety

Counterweight includes a runaway brake as a backup safety measure.

Many length options

Durable materials

Block pulley features aluminum housing and system is galvanized for corrosion resistance.



1 3511063

1

2

SSB Safety Block

Climb assist main block pulley assembly.

2 3512XXX

Lifeline Assembly

Galvanized 1/4 in. (6.3 cm) 7 × 19 cable assembly with rung and belt hook (last three digits in part number signify length).

3530XXX Stainless Steel Lifeline Assembly

3 3511783

Mounting bracket

Attaches safety block to strucsture. Fits round rungs up to 3/4 in. (1.9 cm) diameter or square rungs up to 9/16 in. (1.4 cm) per side.

3511785 Mounting bracket, fits round rungs over 3/4 in. (1.9 cm) up to 1-1/2 in. (3.8 cm) diameter or square rungs over 9/16 in. and up to 1-1/2 in.


(3.8 cm) per side.

3511645 Rung Belt Assembly

3511598

Counterweight Assembly

80 lb. (36.3 kg) counterweight with integrated runaway brake system.



3M[™] DBI-SALA[®] Rope Grabs

5000335

3M™ DBI-SALA® Lad-Saf™ Mobile Rope Grab

Detachable design can be attached or removed anywhere along lifeline. For use on 3M approved 5/8 in. (16 mm) polyester/polypropylene rope lifeline. Use with 3 ft. (0.9 m) shockabsorbing lanyard.

5002045 Lad-Saf Rope Grab with attached EZ-Stop™ Shock-Absorbing Lanyard x 3 ft. (0.9 m)

5001442 Lad-Saf Rope Grab for use on 3M approved 3/4 in. (19 mm) polyester/ polypropylene rope lifeline x 3 ft. (0.9 m). For use with 3 ft. shock-absorbing lanyard.



3M™ DBI-SALA® EZ-Stop™ Rope Adjuster

Installs at top or bottom of the lifeline. For use on 3M approved 5/8 in. (16 mm) rope lifeline. Equipped with RFID.

Rope Lifelines

Various styles and lengths are available to suit any need.



5000338

Lad-Saf Wire Rope Grab

Manual design for use in extremely abrasive or corrosive environments. For use on 3M approved 3/8 in. (9.5 mm) 7 × 19 galvanized or stainless steel cable. Use with 4 ft. (1.2 m) shock-absorbing lanyard.



5000400

Rope Grab Kit

Complete rope grab system in a bag for convenient fall protection compliance on the job. Kit includes:

- Mobile Rope Grab (5000335)
- Shock-Absorbing Lanyard (1246012)
- Lifeline x 50 ft. (1202794)
- Counterweight (5901583)
- Tie-Off Adapter (1003000)
- Carrying Bag (9511597)

5000401 Rope Grab Kit with 100 ft. (30 m) Lifeline (1202844) and Carrying Bag. (9503806)



5901583

Counterweight

5.7 lb. (2.6 kg) flexible counterweight keeps lifeline taught. Nylon construction. Built-in web loop for attachment to lifeline. Compact and portable design. Equipped with RFID.



Polyester/Polypropolene Blended Rope Lifeline

| Hook style | Lifeline diameter (inch/mm) | 25 ft. (8 m) lifeline | 50 ft. (15 m) lifeline | 75 ft. (22 m)lifeline | 100 ft. (30 m) lifeline | 150 ft. (46 m) lifeline |
|---------------------------|--------------------------------|--------------------------|---------------------------|-----------------------|----------------------------|----------------------------|
| Snap hook | 5/8 in. (15.9 mm) | 1202742 | 1202794 | 1202821 | 1202844 | 1202879 |
| at one end | 3/4 in. (19.05 mm) | 1202739 | 1202785 | 1202818 | 1202838 | 1202877 |
| Snap hook at both ends | 5/8 in. (15.9 mm) | 1202740 | 1202790 | 1202823 | 1202842 | 1202878 |

Custom sizes available.



Safety. Productivity. 3M™ Protecta® Vertical and Horizontal Lifeline Systems are built to deliver both. Workers across a wide variety of industries trust our systems to keep them safe and complement their work—all while meeting applicable standards and regulations.

3M[™] Protecta[®]

Synthetic Horizontal Lifeline (HLL) System

1200101

Lightweight, easy to install, disassemble and transport.

- Complete kit includes two tie-off adapters for simple anchorage to structure
- Built-in shock absorber reduces anchorage loadings to help preserve the structure
- Fall-arrest rated for two users, providing jobsite flexibility
- 60 ft. (18 m) web lifeline is compact, portable and versatile

1200105 Synthetic HLL System with carrying bag (no tie-off adapters) x 60 ft. (18 m)



Vertical and Horizontal Systems

3M™ Protecta®

Rope Grabs

Rope Grab (Auto/Manual) AC202D

- Mobile design automatically follows user for hands-free operation
- Manual option allows user to fix unit in place for positioning or restraint
- Detachable design allows for attachment or removal anywhere along lifeline
- For use on 5/8 in. (16 mm) nylon rope lifeline



- Mobile design automatically follows user for hands-free operation
- Detachable design allows for attachment or removal anywhere along lifeline
- For use on 5/8 in. (16 mm) polyester/ polypropylene rope lifeline
- Lightweight and compact design



Rope Grab/Lanyard (Manual) 1340005

- Manual design allows user to fix unit in place for positioning or restraint
- Attached 2 ft. (0.6 m) shock-absorbing lanyard
- For use on 5/8 in. (16 mm) polyester/ polypropylene rope lifeline



3M[™] Protecta®

Lifelines

How to choose the right lifeline

- 1. Nylon rope provides resistance to UV, wear and shock, making it a great choice for long-term use even in harsh environments.
- 2. Polypropylene/polyester blended rope is light, less absorbent, chemical resistant and economical.

Lifeline – Nylon AC215A

50 ft. (15 m) nylon rope lifeline with attached snap hook.

- AC210A1 25 ft. (7.6 m), 5/8 in. (16 mm) nylon, carabiner at one end, taped at other
- AC210A2 25 ft. (7.6 m), 5/8 in. (16 mm) nylon, snap hooks at both ends
- AC215A1 50 ft. (15 m), 5/8 in. (16 mm) nylon, carabiner at one end, taped at other
- AC215A2 50 ft. (15 m), 5/8 in. (16 mm) nylon, snap hooks at both ends
- AC225A1 75 ft. (22 m), 5/8 in. (16 mm) nylon, carabiner at one end, taped at other
- AC230A1 100 ft. (30 m), 5/8 in. (16 mm) nylon, carabiner at one end, taped at other

Lifeline – Polyester/Polypropylene 1299997

50 ft. (15 m) polyester/polypropylene blended rope lifeline with attached snap hook.

- 1299996 25 ft. (7.6 m), 5/8 in. (16 mm) blended polyester/polypropylene, snap hook at one end, taped at other
- 1299991 30 ft. (9 m), 5/8 in. (16 mm) blended polyester/ polypropylene, snap hook at one end, taped at other
- 1299992 75 ft. (22 m), 5/8 in. (16 mm) blended polyester/polypropylene, snap hook at one end, taped at other
- 129998 100 ft. (30 m), 5/8 in. (16 mm) blended polyester/polypropylene, snap hook at one end, taped at other



3M[™] DBI-SALA[®] Engineered Systems

Flexibility for demanding worksites.

Meet the fall protection needs of your unique worksite with a safety system designed specifically for your application. A 3M certified specialist will help you with options for the selection, installation, training and use of your engineered system. Contact customer service to find a certified specialist to assist you.



Overhead Applications

- Specifically designed to meet the needs of transport and industrial applications.
- Can be used for work at height on trains, trucks, aircraft, crane walkways and loading bays.
- Supports self-retracting lifelines and controlled rate descent devices up to 33.1 lbs. (150.1 kg).
- Allows up to 200 ft. (61 m) single span for one user and up to 100 ft. (30.5) single span for multiple users.*

*The number of system users and span lengths must be verified by the calculation software.

3504550

3M™ DBI-SALA® Ultra-Lok™ RSQ Self-Retracting Lifeline

Dual mode RSQ allows for a simple, effective rescue should a fall event occur.





Wall and Floor Applications

- Engineered lifeline systems can be used for modern building projects, refurbishments and industrial safety applications.
- Can be fitted to steel beams, concrete and brickwork.
- Suitable for use on older roof constructions in conjunction with fabricated anchor posts.**

**Not supplied by 3M Fall Protection.

3500214

3M[™] DBI-SALA[®] Nano-Lok[™] edge Quick-Connect Self-Retracting Lifeline

8 ft. (2.4 m) lifeline with 3/16 in. (5 mm) galvanized steel wire rope and aluminum captive carabiner, quick connector for harness mounting.



See customizable systems on the following page.

3M™ DBI-SALA® Engineered Systems

Each worksite presents its own set of unique challenges, so fall protection systems need to be adaptable to ensure worker safety. We offer a comprehensive range of fully compliant, practical solutions for most industries.

Roof Safe Cable and Anchor System

Designed with today's modern lightweight roofs in mind, these systems include minimally intrusive fixing procedures. They're designed for installation on a wide variety of roofing structures while protecting their integrity, and feature a variety of components that can be combined in a multitude of configurations.

- Posts can be used as part of an HLL System or as standalone single point rooftop anchors.
- Span up to 15 m (50 ft.) between anchors.
- Provides continuous hands-free access for up to four simultaneous users.



8 mm Permanent Horizontal Lifeline Systems

Cloud based software helps with installation procedures. These systems are easy to calculate, design, specify, install and use.

- Posts can be used as part of an HLL System or as standalone single point rooftop anchors.
- Span up to 15 m (50 ft.) between anchors.
- Provides continuous hands-free access for up to four simultaneous users.



Horizontal Rail Safety Systems

Made of a quality extruded aluminum, these rail systems combine a simple, continuous and functional anchorage system for user safety, along with a low profile design that may help with facility or building aesthetics. In addition to fall protection applications, it has also been used extensively as the primary anchor point for suspended rope access tasks.

- Span up to 15 m (50 ft.) between anchors.
- Posts can be used as part of an HLL System or as an individual anchor point
- Provides continuous hands-free access for up to four simultaneous users.





3M™ DBI-SALA® Engineered Systems

Start Anchor

Contact EngineeredSystems-FP@mmm.com to consult with a certified specialist today.

Roof Safe Cable and Anchor System A range of system components are available including free-flowing intermediate guides and corner attachments, providing complete hands-free movement across a Horizontal Lifeline System. Variable 90° Intermediate Corner Guide 8 mm Hex 45° Corner System Corner Swage Toggle Eye & Pin Anchor 8 mm Hex 8 mm Swage Unigrab & Intermediate Tensioner Carabiner Anchor Corner Anchor **End Anchor**





Scan the QR code and Download the 3M™ Fall Protection Configurator App





Unique solutions for unique applications.

No two jobs or job sites are the same. Whether you're working on airplanes or oil rigs, you need a secure anchor point to get the job done. 3M™ DBI-SALA® Flexiguard™ Solutions are designed to help provide safe working areas with overhead anchor points for one or more workers in a variety of challenging situations. These systems are versatile and often mobile. Rugged enough for indoor or outdoor applications, these systems are great for the transportation, construction, oil and gas, mining and utilities industries.

The 3M Fall Protection Configurator App is here—view select 3M™ DBI-SALA® Flexiguard™ Solutions in your work environment, right from your phone. Contact 3M for more information or to schedule a site assessment.

| System Type | Transportation | Mining | Defense | General Industry | |
|---|----------------|--------|---------|------------------|--|
| Modular Jib System | • | | | | |
| Counterweighted Rail | • | | | | |
| Counterweighted Jib | | _ | | • | |
| C-Frame | • | | _ | | |
| A-Frame | | _ | | | |
| Box Frame | • | | | | |
| Portable Access Ladder | • | | | | |
| Freestanding Access Ladder | • | | • | | |
| Trailer Mounted | | | | _ | |
| ■ Primary Application ■ Alternate Application | | | | | |

3M[™] DBI-SALA[®] Flexiguard[™] Modular Jib System — M200


Get the coverage you need with this modular fall protection system. Available in both the M100 and M200 Series, the 3M™ DBI-SALA® Flexiguard™ Modular Jib System features a simplified design that enhances worker safety in multiple applications. Increased rail-length configurations improve working coverage while a new design facilitates easier system transport.

M200

| Total System Weight | Max. Component Weight | Offset/Reach (A) | Height (B) | Mast Rotation Range | SRL Maximum Arresting Force |
|---------------------------|--------------------------|--|-------------------------|------------------------|--------------------------------|
| 12,668 lbs. (5,746 kg) | 5,000 lbs. (2,268 kg) | 15 ft. (4.6 m) Single User Models 12 ft. (3.7 m) Dual User Models | Up to 30 ft. (9.1 m) | 360° for all bases. | 1,350 lbs. (6 kN) |



1. Choose from 14 interchangeable mast options.




Semi-Fixed Height* Single User Masts

8530899 15 – 20 ft. (4.6 – 6 m) 8530900 20 – 25 ft. (6 – 7.6 m) 8530901 25 – 30 ft. (7.6 – 9.1 m)




Semi-Fixed Height* Dual User Masts

8530902 15 - 20 ft. (4.6 - 6 m) 8530903 20 - 25 ft. (6 - 7.6 m) 8530904 25 - 30 ft. (7.6 - 9.1 m)



Adjustable Height** Single User Masts

8530891 12.3 – 15 ft. (3.8 – 4.6 m) 8530892 14.8 – 20 ft. (4.5 – 6.1 m) 8530893 17.3 – 25 ft. (5.3 – 7.6 m) 8530894 19.8 – 30 ft. (6 – 9.1 m)



Adjustable Height** Dual User Masts

8530895 12.3 - 15 ft. (3.8 - 4.6 m) 8530896 14.8 - 20 ft. (4.5 - 6.1 m) 8530897 17.3 - 25 ft. (5.3 - 7.6 m) 8530898 19.8 - 30 ft. (6 - 9.1 m)

2. Choose from 4 interchangeable base options.



8530887

Portable Counterweight Base with concrete fill* 8530886 Without concrete

*Portable Counterweight Base optional leveling jacks sold separately



8530888

Permanent Floor Mounted Base



8530889

Permanent Flush Mounted Base

3. Choose your accessories on P.38

^{*}Semi-fixed masts have a small amount (5 ft. or 1.5 m) of adjustment to optimize the anchor height during installation.

^{**}Adjustable height masts are adjusted easily using the integrated hand crank winch, or by using a power drill with the optional overload clutch accessory equipped.

3M™ DBI-SALA® Flexiguard™ Modular Jib System — M100

M100

| Total System Weight | Max. Component Weight | Offset/Reach (A) | Height (B) | Mast Rotation Range | SRL Maximum Arresting Force |
|-------------------------|--------------------------|------------------|-------------------------|---|--------------------------------|
| 4,995 lbs (2,266 kg) | 3,095 lbs. (1,404 kg) | 7.5 ft. (2.3 m) | Up to 30 ft. (9.1 m) | 270° with counterweight base. 360° with others. | 1,350 lbs. (6 kN) |

1. Choose from 7 interchangeable mast options.



Adjustable Height* Single User Masts

8530874 10 - 15 ft. (3 - 4.6 m)

8530875 2.5 - 20 ft. (3.8 - 6.1 m)

8530876 15 - 25 ft. (4.6 - 7.6 m) 8530877 17.5 - 30 ft. (5.3 - 9.1 m)

*Adjustable height masts are adjusted easily using the integrated hand crank winch, or by using a power drill with the optional overload clutch accessory equipped.

Semi-Fixed Height** Single User Masts

8530882 15 - 20 ft. (4.6 - 6 m)

8530883 20 - 25 ft. (6 - 7.6 m)

8530884 25 - 30 ft. (7.6 - 9.1 m)

**Semi-fixed masts offer a small amount (5 ft. or 1.5 m) of adjustment to optimize the anchor height during installation.



2. Choose from 5 interchangeable base options.



Portable Counterweight Base with concrete fill*

8530869 Without concrete

*Portable Counterweight Base includes leveling jacks







3. Choose your accessories on P.38 ►

3M[™] DBI-SALA[®] Flexiguard[™] Modular Jib System Accessories

3. Choose your accessories.



Confined Space & Rescue Pulley Kit

Enables a rescue device to be mounted to the system. Includes mounting brackets and re-direct pulleys. Rescue devices sold separately.

8530885 M100

8530905 M200



Jack Stabilizing Kit

Designed to stabilize and level counterweight base systems on slightly uneven surfaces. (M200 only)

8530907 M200



Smooth Surface Caster Kit

Allows counterweight base systems to be maneuvered into tight spaces on smooth surfaces.

8530908 M100

8530908 M200



Forklift Pocket Mast Transport Kit

Allows mast to be separated from the base and transported vertically using a forklift.

8530911 M100

8530911 M200



Overload Clutch

Required to raise and lower adjustable masts with a power drill. (Drill not included)

8512936 M100

8512936 M200



Counterweight Box Lifting Ring Kit

Allows counterweight box to be moved with overhead lifting equipment. Includes four rings per kit. One kit needed per counterweight system.

8530914 M100

8530777 M200

3M[™] DBI-SALA[®] Flexiguard[™] Counterweighted Rail System

The Counterweighted Rail System is a portable solution with a counterbalanced design utilizing concrete blocks as ballast. The design allows for optimal positioning and maximum safe working coverage.

- Aluminum glide rail provides continuous fall protection up to 54 ft. long.
- Helps easily create an overhead anchor point for multiple workers.
- Portable system provides flexibility and versatility, letting you position close to the work surface without obstructing the equipment being accessed.
- Systems available with or without concrete counterweight on base.

Counterweighted Jib Rail Models

| sku | Weight (lbs.) w/ concrete | Concrete Counterweight | Overall Height | Users |
|---------|------------------------------|---------------------------|-------------------|-------|
| 8517760 | 11,380 | No | 23' 7" | 2 |
| 8517761 | 11,380 | Yes | 23' 7" | 2 |
| 8517762 | 11,540 | No | 23' 7" | 2 |
| 8517763 | 11,540 | Yes | 23' 7" | 2 |

Systems with concrete counterweight included ship with two 3,500 lb. concrete blocks.



3M™ DBI-SALA® Flexiguard™ Jib Arms & Rails

The Pivoting Jib Arm & Rail systems are permanently mounted and integrated systems, providing optimal and non-intrusive coverage. These designs clamp to pre-existing structures making them ideal for manufacturing environments and other similar applications.

- Non-base mounted system attaches to supporting, fixed structure (e.g. on I-Beam) on the job site.
- Mounting clamps, plates and hardware included with systems.
- System rotates 180 degrees and locks every 7.5 degrees.

1-User Rated Pivoting Jib Boom Models

| sku | Weight (lbs.) | Overall Height | Overall Width | Rail Length | Max Beam Thickness | Max Beam Width |
|---------|------------------|-------------------|------------------|-------------|-----------------------|-------------------|
| 8530433 | 560 | 5' 8" | 1' 7" | 20' 0" | 0' 10" | 1' ½" |



3M™ DBI-SALA® C-Frame System

The C-Frame System is a mobile solution designed to be positioned manually, or with the use of a tow bar (optional) and service vehicle. The freestanding design utilizes protruding outriggers that extend below the work surface for stability. Available in adjustable height and fixed height models for a wide variety of applications.

- Designed to be moved manually or with a tow bar and service vehicle.
- Designed to be positioned under equipment with minimal ground clearances.
- Adjustable systems allow rail height to be adjusted by manually cranking the winch—allowing for passage under obstructions and building doorways.

2-User Rated Fixed Height Models

| sku | Weight (lbs.) | Overall Height | Anchor Height | Trolley Rail Width |
|---------|------------------|----------------|---------------|--------------------|
| 8530842 | 1,450 | 22' 0" | 20' 0" | 15' 0" |
| 8530843 | 1,500 | 27' 0" | 25' 0" | 15' 0" |
| 8530844 | 1,600 | 22' 0" | 20' 0" | 20' 0" |
| 8530845 | 1,650 | 27' 0" | 25' 0" | 20' 0" |

2-User Rated Adjustable Height Models

| sku | Weight (lbs.) | Overall Height | Anchor Height | Trolley Rail Width |
|---------|------------------|-----------------|-----------------|--------------------|
| 8517701 | 1,650 | 13' 3" – 19' 7" | 12' 4" – 18' 8" | 10' 0" |
| 8517703 | 1,970 | 13' 3" – 19' 7" | 12' 2" – 18' 5" | 15' 0" |
| 8517705 | 2,100 | 13' 3" – 19' 7" | 12' 2" – 18' 5" | 20' 0" |
| 8517707 | 2,105 | 18' 2" – 29' 8" | 17' 2" – 28' 7" | 15' 0" |
| 8517709 | 2,236 | 18' 2" – 29' 8" | 17' 2" – 28' 7" | 20' 0" |
| 8517711 | 2,240 | 23' 4" - 99' 8" | 22' 2" – 38' 6" | 15' 0" |
| 8517713 | 2,370 | 23' 4" – 99' 8" | 22' 2" – 38' 6" | 20' 0" |




| Description | Part # | | - 11 |
|--------------------------------------|---------|---|-----------|
| Tow bar kit (does not include hitch) | 8530859 | - | Λ |
| Hitch ball, 2" adapter assembly | 8513572 | | |
| Pintle hitch, adapter assembly | 8516187 | | |
| | | | |

3M™ DBI-SALA® A-Frame System

The A-Frame System is a mobile solution designed to be positioned manually. The freestanding design straddles the work surface, taking up minimal floor space. Available in adjustable height and fixed height models, this two-user solution can be utilized for a wide variety of applications.

- System contains a single rail rated for two users.
- Glide rail includes two trolleys rated for one user each.
- Systems include heavy-duty leveling jacks.
- Lightweight aluminum construction.*
- Portable design that can be moved easily.
- Four integrated swiveling wheels.





2-User Rated Fixed Height Models

| | <u>-</u> | | |
|---------|---------------|----------------|--------------------|
| SKU | Weight (lbs.) | Overall Height | Trolley Rail Width |
| 8517790 | 1,230 | 17' 0" | 15' 0" |
| 8517791 | 1,380 | 17' 0" | 20' 0" |
| 8517792 | 1,540 | 17' 0" | 30'0" |
| 8517793 | 1,530 | 22' 0" | 15' 0" |
| 8517794 | 1,680 | 22' 0" | 20' 0" |
| 8517795 | 2,175 | 22' 0" | 30'0" |
| 8517796 | 2,160 | 32' 0" | 15' 0" |
| 8517797 | 2,240 | 32' 0" | 20' 0" |
| 8517798 | 2,420 | 32' 0" | 30'0" |

^{16&}quot; rubber molded wheels.

2-User Rated Adjustable Height Models

| SKU | Weight (lbs.) | Overall Height | Trolley Rail Width |
|---------|---------------|------------------|--------------------|
| 8517780 | 3,160 | 17' 11" – 24' 5" | 20' 0" |
| 8517781 | 3,225 | 17' 11" – 24' 5" | 30'0" |

^{16&}quot; foam filled wheels.



8529744

Converts wheels (qty. 4 required) to 16 in. foam filled pneumatic tires. (Fixed height A-frame systems only.)



9502782 Grounding reel kit.

^{*}Compared to comparable steel construction.

3M™ DBI-SALA® Flexiguard™ Box Frame



The Box Frame System is a mobile solution designed to be positioned manually. The freestanding design straddles the work surface, allowing the fall protection rails to run parallel with the work surface. This system will provide fall protection coverage over a large footprint or area. Available in adjustable height and fixed height models, this two-user solution can be utilized for a wide variety of applications.

Fixed Height Features:

- Provides an effective overhead anchor point.
- Available as a permanent frame or portable for easy relocation.

Adjustable Height Features:

- Adjustable using an overhead crane, forklift or powered system.
- Combines overhead anchorages with mobility in areas with overhead obstructions or door height restrictions.
- Integrated pin-height selection system.

2-User Rated Fixed Height Models

| sku | Weight (lbs.) | Wheel Type | Overall Height | Trolley Rail Width |
|---------|---------------|---------------|----------------|--------------------|
| 8530345 | 1,300 | 16" pneumatic | 15' 0" | Dual rail 15' 6" |
| 8530361 | 1,500 | 12" rubber | 22' 4" | Single rail 28' 0" |
| 8530427 | 4,370 | 16" pneumatic | 31' 11" | Dual rail 32' 0" |

2-User Rated Adjustable Height Model

| sku | Weight (lbs.) | Wheel Type | Overall Height | Trolley Rail Width |
|---------|---------------|------------|-----------------|--------------------|
| 8530288 | 1,370 | 12" rubber | 13' 4" - 19' 4" | Single rail 28' 0" |

3M™ DBI-SALA® Flexiguard™ Portable Access Ladder

The Portable Access Ladder System (PALS) is a mobile solution designed to be positioned manually or with the use of a tow bar (optional) and service vehicle. An adjustable height integrated ladder provides access and egress from elevated work surfaces with an integrated anchor point for added security. The optional rescue kit enables confined space rescue and retrieval capabilities on elevated work surfaces. A variety of other options and accessories make this ladder highly configurable for unique applications.

• Manual height adjustment via winch assembly.

• Multiple height adjustment ranges available.

• All systems include a fall arrest bar for accessing ladder.

• System includes heavy-duty leveling jacks.

2-User Rated Portable Access Ladder System

| SKU | Weight (lbs.) | Platform Height | Anchor Height | Base Length |
|---------|---------------|-----------------|------------------|-------------|
| 8530852 | 1.020 | 8' 2" – 13' 9" | 16' 5" – 22' 0" | 5' 2" |
| 0530052 | 1,030 | 7' 8" – 13' 3"* | 16' 7" – 22' 2"* | 5 2 |
| 0520052 | 30853 1,046 | 10' 1" – 15' 8" | 18' 3" – 23' 10" | 5' 2" |
| 0030853 | | 9' 7" – 15' 2"* | 18' 6" – 24' 1"* | 5 2 |

*When assembled with 8530854, 8530855, 8530856.



8530854 Guardrail Cage, 5.5 ft. diameter



8530856Guardrail add-on kit for uneven surfaces




8530855 Rescue kit



8515349

8530859





3M™ DBI-SALA® Flexiguard™ Freestanding Access Ladder

This system is a mobile solution designed to be positioned manually or with the use of a tow bar and service vehicle. An adjustable height integrated ladder provides safe access and egress from elevated work surfaces with integrated anchor points supporting up to two workers simultaneously. Adjustable platform heights up to 30 ft. 11 in. provide the ability to serve a multitude of applications.

- Manual height adjustment via winch assembly.
- All systems include a fall arrest bar for accessing ladder.
- System includes leveling jacks.
- Includes 6 ft. working platform with foam bottom and collapsible guardrail handles.

2-User Rated Free-Standing Access Ladder Models

| SKU | Weight (lbs.) | Platform Height | Anchor Height | Base Length | Overall Length |
|---------|------------------|--------------------|------------------|----------------|-------------------|
| 8517715 | 2,056 | 10' 8" – 15' 8" | 19' 7" – 24' 6" | 12' 4" | 12' 10" |
| 8517717 | 2,206 | 14' 5" – 23' 2" | 23' 4" – 32' 1" | 14' 4" | 17' 0" |
| 8517719 | 2,850 | 18' 4" – 30' 10" | 27' 2" – 39' 9" | 17' 4" | 20' 10" |



3M[™] DBI-SALA[®] Flexiguard[™] Trailer Mounted Anchor System

The Trailer Mounted Anchor System is a mobile solution designed to be towed with a service vehicle from application to application. This self-supported design does not require the service vehicle to be attached for use. With an adjustable anchor height of 20 ft. 6 in., and the capacity for two workers, this solution provides maximum versatility.

- Trailer mounted solutions maximize portability and versatility to and from job site.
- System quickly raises and lowers with integrated winch and handle.
- Integrated brake mechanism automatically locks the mast height in the desired position.

2-User Rated Trailer System

| sku | Weight (lbs.) | Tongue Weight | Overall Height | Anchor Height | Overall Length | Cantilever from Trailer | Trailer Length | Trailer Width |
|---------|---------------|------------------|-------------------|------------------|-------------------|----------------------------|-------------------|------------------|
| 8530690 | 5,500 | 550 | 13' 3" – 21' 0" | 12' 9" – 20' 6" | 17' 7" | 3' 0" | 14' 5" | 7' 0" |





3M™ DBI-SALA® ExoFit™ X300 Harness

For those who refuse to compromise.

Personal SRL adapter*

allows for connection

of personal SRLs with

confidence and ease.

One of our most advanced harnesses just got better. With comfort and fit, it's optimized to help increase the performance and productivity of professionals who take pride in a job done right.


Automatic standup back D-ring,* conveniently connect faster and easier.



Anti-Slide Dorsal D-Ring Pad

Weight Distribution System* takes weight off your shoulders.**

3M™ Scotchlite™ reflective panels to enhance visibility in low-light environments.



Auto-Resetting Lanyard Keepers*



Integrated Low-Profile Suspension Trauma Relief Straps*

3M[™] Connected Safety ID* Auto-locking quick connect buckles* to help maintain fit — greatly reducing buckle slide.

Lightweight Aluminum Tongue-Buckle

And Durable Belt



Comfort back pad with built-in durable shoulder caps.


Radio/ Cell Phone Holster**



Revolving torso adjusters* are fast and easy to adjust and lock webbing into place — maintaining a comfortable and safe harness fit.

Lightweight Aluminum D-Rings

Comfort hip pad with robust belt loops and rigid belt for tool pouch-carrying convenience.



^{*}Comes integrated on select models.

3M™ DBI-SALA® ExoFit™ X-Series Harnesses







| Feature | X100 | X200 | X300 |
|---|---------------------------------|--------------------------------|-------------------------------|
| Personal SRL Adapter* | | Steel** | Aluminum |
| Breathable Back Pads | Removable Shoulders (adaptable) | Mesh Shoulders (breathable) | Rubber Shoulders (durable) |
| Weight Distribution System* Models Available | ✓ | | ✓ |
| Automatic Stand-Up D-Ring* | | Steel** | Aluminum |
| Leg Padding | | | |
| Secure-Fitting Quick-Connect Buckles | | Dual-locking* | Auto-locking* |
| 3M™ Scotchlite™ Reflective Material | | | Padding Panels |
| Equipped with Radio/Phone Holster | | | √ " |
| Robust Comfort Hip Pad Belt Loops | | | ✓ |

New ExoFit™ Comfort Harnesses available in a variety of styles:

- Vest
- Vest Climbing
- Vest Positioning
- Vest Retrieval
- Vest Climbing/Positioning
- Vest Climbing/Positioning/Retrieval
- X100 / X200 / X300 all include Suspension Trauma Straps

- Construction
- Construction Climbing
- ► Construction Positioning
- Construction Climbing/ Positioning
- Construction Weight Distribution Positioning
- Construction Weight Distribution Climbing/ Positioning

- ► Tower Climbing/Positioning
- Wind Energy Vest Climbing/ Positioning
- Wind Energy Construction Climbing/Positioning
- Oil and Gas Vest Climbing/ Positioning
- Oil and Gas Construction Climbing/Positioning
- ► Construction Mining


^{*3}M Patented Technology

^{**}Indicates availability on select models.

Designed for ultimate comfort and performance.

Wherever your work takes you, staying comfortably fitted in your safety harness is critical. Designed for comfort and performance, our new line of 3M™ DBI-SALA® ExoFit™ X-Series Harnesses help change the way you work and redefine what you should expect from a safety harness.

3M™ DBI-SALA® ExoFit™ X-Series Harness Sizing Chart X100 | X200 | X300



3M™ DBI-SALA® ExoFit™ X100 Safety Harnesses

Gear up with confidence, quality, and performance.

General Industry



Construction



Construction Weight Distribution



Telecommunications



| Harness Style | Configuration (D-ring(s), Leg Buckles, Chest Buckle) | WDS ⁴ | Small | Medium | Large | X-Large |
|--|---|------------------|---------|---------|---------|---------|
| General Industry | | | | | | |
| Comfort Vest ¹ | Back, Tongue Buckle, Pass-Thru | | 1401000 | 1401001 | 1401002 | 1401003 |
| Comfort Vest ¹ | Back, Quick-Connect, Quick-Connect | | 1401020 | 1401021 | 1401022 | 1401023 |
| Comfort Vest Climbing ¹ | Back Front, Tongue Buckle, Pass-Thru | | 1401005 | 1401006 | 1401007 | 1401008 |
| Comfort Vest Climbing ¹ | Back Front, Quick-Connect, Quick-Connect | | 1401025 | 1401026 | 1401027 | 1401028 |
| Comfort Vest Positioning ¹ | Back Hip, Tongue Buckle, Pass-Thru | | 1401010 | 1401011 | 1401012 | 1401013 |
| Comfort Vest Positioning ¹ | Back Hip, Quick-Connect, Quick-Connect | | 1401030 | 1401031 | 1401032 | 1401033 |
| Comfort Vest Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Pass-Thru | | 1401015 | 1401016 | 1401017 | 1401018 |
| Comfort Vest Climbing/Positioning ¹ | Back Front Hip, Quick-Connect, Quick-Connect | | 1401035 | 1401036 | 1401037 | 1401038 |
| Construction | | | | | | |
| Comfort Construction Positioning ¹ | Back Hip, Tongue Buckle, Pass-Thru | | 1401070 | 1401071 | 1401072 | 1401073 |
| Comfort Construction Positioning ^{1,4} | Back Hip, Tongue Buckle, Pass-Thru | Х | 1401040 | 1401041 | 1401042 | 1401043 |
| Comfort Construction Positioning ¹ | Back Hip, Quick-Connect, Quick-Connect | | 1401090 | 1401091 | 1401092 | 1401093 |
| Comfort Construction Positioning ^{1,4} | Back Hip, Quick-Connect, Quick-Connect | Х | 1401050 | 1401051 | 1401052 | 1401053 |
| Comfort Construction Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Pass-Thru | | 1401075 | 1401076 | 1401077 | 1401078 |
| Comfort Construction Climbing/Positioning ^{1,4} | Back Front Hip, Tongue Buckle, Pass-Thru | Х | 1401045 | 1401046 | 1401047 | 1401048 |
| Comfort Construction Climbing/Positioning ¹ | Back Front Hip, Quick-Connect, Quick-Connect | | 1401095 | 1401096 | 1401097 | 1401098 |
| Comfort Construction Climbing/Positioning ^{1,4} | Back Front Hip, Quick-Connect, Quick-Connect | Х | 1401055 | 1401056 | 1401057 | 1401058 |
| Telecommunications | | | | • | | • |
| Comfort Tower Climbing ¹ | Back Front Hip, Tongue Buckle, Quick-Connect | | 1401140 | 1401141 | 1401142 | 1401143 |
| Retrieval | | | | | | |
| Comfort Retrieval ¹ | Back Shoulder, Tongue Buckle, Pass-Thru | | 1401156 | 1401157 | 1401158 | 1401159 |
| Comfort Retrieval ¹ | Back Front Hip Shoulder, Tongue Buckle, Pass-Thru | | 1401161 | 1401162 | 1401163 | 1401164 |

¹Available in 2X-Large.

² Available in 3X-Large.

³ Available in X-Small.

⁴ Includes Weight Distribution System (WDS).

3M[™] DBI-SALA[®] ExoFit[™] X200 Safety Harnesses

Gear up with confidence, quality, and performance.

General Industry



Construction



Wind Energy



Oil and Gas



Telecommunications



| Harness Style | Configuration (D-ring(s), Leg Buckles, Chest Buckle) | Small | Medium | Large | X-Large |
|--|--|---------|---------|---------|---------|
| General Industry | | | | | |
| Comfort Vest ¹ | Back, Tongue Buckle, Pass-Thru | | 1402001 | 1402002 | 1402003 |
| Comfort Vest ¹ | Back, Dual Lock Quick-Connect, Dual Locking Quick-Connect | 1402020 | 1402021 | 1402022 | 1402023 |
| Comfort Vest Climbing ¹ | Back Front, Tongue Buckle, Pass-Thru | 1402005 | 1402006 | 1402007 | 1402008 |
| Comfort Vest Climbing ¹ | Back Front, Dual Lock Quick-Connect, Dual Locking Quick-Connect | 1402035 | 1402036 | 1402037 | 1402038 |
| Comfort Vest Positioning ¹ | Back Hip, Tongue Buckle, Pass-Thru | 1402010 | 1402011 | 1402012 | 1402013 |
| Comfort Vest Positioning ¹ | Back Hip, Dual Lock Quick-Connect, Dual Locking Quick-Connect | 1402040 | 1402041 | 1402042 | 1402043 |
| Comfort Vest Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Pass-Thru | 1402015 | 1402016 | 1402017 | 1402018 |
| Comfort Vest Climbing/Positioning ¹ | Back Front Hip, Dual Lock Quick-Connect, Dual Locking Quick-Connect | 1402050 | 1402051 | 1402052 | 1402053 |
| Construction | | | 1 | T | ı |
| Comfort Construction Positioning ^{1,3} | Back Hip, Tongue Buckle, Dual Locking Quick-Connect | 1402082 | 1402083 | 1402084 | 1402085 |
| Comfort Construction Positioning ^{1,3} | Back Hip, Dual Lock Quick-Connect, Dual Locking Quick-Connect | 1402105 | 1402106 | 1402107 | 1402108 |
| Comfort Construction Climbing/Positioning ^{1,3} | Back Front Hip, Tongue Buckle, Quick-Connect | 1402088 | 1402089 | 1402090 | 1402091 |
| Comfort Construction Climbing/Positioning ^{1,2} | Back Front Hip, Dual Lock Quick-Connect, Quick-Connect | 1402110 | 1402111 | 1402112 | 1402113 |
| Wind Energy | | | | | |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402125 | 1402126 | 1402127 | 1402128 |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402130 | 1402131 | 1402132 | 1402133 |
| Oil and Gas | | | | | |
| Comfort Oil and Gas Climbing ¹ | Back Hip, Tongue Buckle, Quick-Connect | 1402115 | 1402116 | 1402117 | 1402118 |
| Telecommunications | | | | | |
| Comfort Telecom Climbing/Positioning ¹ | Back Front Hip, Dual Lock Quick-Connect, Quick-Connect | 1402135 | 1402136 | 1402137 | 1402138 |
| Comfort Telecom Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Quick-Connect | 1402140 | 1402141 | 1402142 | 1402143 |
| Cross-Over | | | | | |
| Comfort Cross-Over Climbing ¹ | Back Front, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402156 | 1402157 | 1402158 | 1402159 |
| Comfort Cross-Over Climbing/Positioning ¹ | Back Front Hip, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402160 | 1402161 | 1402162 | 1402163 |
| Retrieval | | | | | |
| Comfort Climbing/Positioning/Retrieval ¹ | Back Front Hip Shoulder, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402150 | 1402151 | 1402152 | 1402153 |
| Comfort Retrieval ¹ | Back Shoulder, Dual Locking Quick-Connect, Dual Locking Quick-Connect | 1402145 | 1402146 | 1402147 | 1402148 |
| | | | | | |

¹Available in 2X-Large.

² Available in 3X-Large.

³ Available in X-Small.

⁴ Includes Weight Distribution System (WDS).

3M[™] DBI-SALA[®] ExoFit[™] X300 Safety Harnesses

Gear up with confidence, quality, and performance.

General Industry



Construction



Construction Weight Distribution



Wind Energy



Telecommunications



| Harness Style | Configuration (D-ring(s), Leg Buckles, Chest Buckle) | WDS ⁴ | Small | Medium | Large | X-Large |
|--|---|------------------|---------|---------|---------|---------|
| General Industry | | | | | | |
| Comfort Vest ¹ | Back, Tongue Buckle, Auto-Locking Quick-Connect | | 1140127 | 1140128 | 1140129 | 1140130 |
| Comfort Vest ^{1,2,3} | Back, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113001 | 1113004 | 1113007 | 1113010 |
| Comfort Vest Climbing ¹ | rt Vest Climbing¹ Back Front, Tongue Buckle, Auto-Locking Quick-Connect | | 1403006 | 1403007 | 1403008 | 1403009 |
| Comfort Vest Climbing ^{1,3} | nfort Vest Climbing ^{1,3} Back Front, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113031 | 1113034 | 1113037 | 1113040 |
| Comfort Vest Positioning ^{1,3} | tioning ^{1,3} Back Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113046 | 1113049 | 1113052 | 1113055 |
| Comfort Vest Positioning ¹ | Back Hip, Tongue Buckle, Auto-Locking Quick-Connect | | 1403011 | 1403012 | 1403013 | 1403014 |
| Comfort Vest Climbing/Positioning ^{1,3} | Back Front Hip, Tongue Buckle, Auto-Locking Quick-Connect | | 1403017 | 1403018 | 1403019 | 1403020 |
| Comfort Vest Climbing/Positioning ^{1,2,3} | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113076 | 1113079 | 1113082 | 1113085 |
| Construction | | | | | | |
| Comfort Construction Positioning ^{1,3} | Back Hip, Tongue Buckle, Auto-Locking Quick-Connect | | 1140181 | 1140182 | 1140183 | 1140184 |
| Comfort Construction Positioning ^{1,3} | Back Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113121 | 1113124 | 1113127 | 1113130 |
| Comfort Construction Climbing/Positioning ^{1,3} | Back Front Hip, Tongue Buckle, Auto-Locking Quick-Connect | | 1140187 | 1140188 | 1140189 | 1140190 |
| Comfort Construction Climbing/Positioning ^{1,3} | nfort Construction Climbing/Positioning ^{1,3} Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113151 | 1113154 | 1113157 | 1113160 |
| Comfort Construction Positioning ^{1,4} | t Construction Positioning ^{1,4} Back Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1403098 | 1403099 | 1403100 | 1403101 |
| Comfort Construction Positioning ^{1,4} | Back Hip, Tongue Buckle, Auto-Locking Quick-Connect | Х | 1403088 | 1403089 | 1403090 | 1403091 |
| Comfort Construction Climbing/Positioning ^{1,4} | Back Front Hip, Tongue Buckle, Auto-Locking Quick-Connect | Х | 1403093 | 1403094 | 1403095 | 1403096 |
| Comfort Construction Climbing/Positioning ^{1,4} | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | x | 1403103 | 1403104 | 1403105 | 1403106 |
| Wind Energy | | | | | | |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Quick-Connect | | 1113175 | 1113176 | 1113177 | 1113178 |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113210 | 1113211 | 1113212 | 1113213 |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113215 | 1113216 | 1113217 | 1113218 |
| Comfort Wind Energy Climbing/Positioning ¹ | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113449 | 1113450 | 1113451 | 1113452 |
| Oil and Gas | | | | | | |
| Comfort Oil and Gas Climbing ¹ | Back Front, Tongue Buckle, Auto-Locking Quick-Connect | | 1113290 | 1113291 | 1113292 | 1113293 |
| Comfort Oil and Gas Climbing ¹ | Back Front, Tongue Buckle, Pass-Through | | 1113305 | 1113306 | 1113307 | 1113308 |
| Telecommunications | | | | | | |
| Comfort Telecom Climbing/Positioning ¹ | Back Front Hip, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113190 | 1113191 | 1113192 | 1113193 |
| Comfort Telecom Climbing/Positioning ¹ | Back Front Hip, Tongue Buckle, Auto-Locking Quick-Connect | | 1113375 | 1113376 | 1113377 | 1113378 |
| Retrieval | | | | | | |
| Comfort Retrieval ¹ | Back Shoulder, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113061 | 1113064 | 1113067 | 1113070 |
| Mining | | | | | | |
| Comfort Mining ¹ | Back Front Hip Shoulder, Auto-Locking Quick-Connect, Auto-Locking Quick-Connect | | 1113195 | 1113196 | 1113197 | 1113199 |

Belts, Workseats and Accessories



3M™ DBI-SALA® Suspension Trauma Safety Straps

Relief. It can make a big difference when you're suspended in your safety harness. It's why every worker should be equipped with suspension trauma safety straps. They deploy and hook together, allowing a suspended worker to stand up in their harness with one or both feet to relieve downward pressure. They're compact, lightweight and compatible with most harness brands in the field.



| Description | Universal |
|---|-----------|
| Suspension trauma safety straps, one pair, connects to most harnesses | 9501403 |
| Flame-resistant suspension trauma safety straps, one pair, connects to most harnesses | 9505712 |

3M™ DBI-SALA® Harness and Lanyard Bag



| Description | Universal |
|--|-----------|
| 3M [™] DBI-SALA [®] Bag 7-½" wide x 6-½" deep x 15-½" long (19 cm x 16.5 cm x 39.4 cm), holds a harness and lanyard or 50 ft (15.2 m) of $\frac{9}{8}$ " (0.6 cm) rope | 9511597 |

3M™ DBI-SALA® Fall Protection Accessories

| Description | Image | Universal |
|---|-------|-----------------------------------|
| Weight distribution back bars. | | 1150530 (XS-M) 1150531 (L-3XL) |
| Attachment breakaway lanyard keeper plastic ring with Velcro used to "park" lanyard when not in use. Qty. 2. | | 1150443 |
| D-ring Extension with D-ring at one end, snap hook at other x 18" (46 cm). | | 1231117 |
| 3M [™] DBI-SALA [®] Delta [™] Comfort Pad attaches to most harnesses to provide wrap-around comfort. | | 9501207 |
| 3M™ DBI-SALA® ExoFit X100 Leg Pad Kit hook-to-loop attachment | | 1150528 |
| 3M™ DBI-SALA® ExoFitX100 Shoulder Pad hook-to-loop attachment | | 9515281 |

3M[™] DBI-SALA[®] ExoFit[™] STRATA[™] Full-Body Harnesses

Lighten up with the first harness to feature an innovative load distribution system that literally takes the weight off your shoulders.

- Patented design redistributes weight off wearer's shoulders.
- Lightweight aluminum D-rings.
- Easy-linking SRL adapter & standup D-ring simplify connections.
- Mesh padding enhances breathability and comfort.
- Revolving adjusters maintain fit and lock excess webbing in place.
- 420 lb. capacity (Model shown #1112538).
- Quick-connecting buckles enhance adjust-ability.








Triple Action Buckle Tongue Buckle

Quick Connect Buckle



3M™ DBI-SALA® ExoFit™ STRATA™

Tower-Climbing Harnesses

Selection guide:

| Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge |
|---------------|---------------|--|---------|---------|---------|---------|
| Triple Action | Triple Action | 1B, 1C | 1112580 | 1112581 | 1112582 | 1112583 |
| Triple Action | Tongue Buckle | 1B, 1C, 2H | 1112585 | 1112586 | 1112587 | 1112588 |











3M™ DBI-SALA® ExoFit™ STRATA™

Construction-Style Harnesses



1112538

Selection guide:

| Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge |
|---------------|---------------|--|---------|---------|---------|---------|
| Quick Connect | Quick Connect | 1B, 2H | 1112500 | 1112501 | 1112502 | 1112503 |
| Triple Action | Triple Action | 1B, 2H | 1112535 | 1112536 | 1112537 | 1112538 |
| Triple Action | Triple Action | 1B, 1C, 2H | 1112540 | 1112541 | 1112542 | 1112543 |
| Triple Action | Triple Action | 1B, 1C, 2H, 2S | 1112545 | 1112546 | 1112547 | 1112548 |
| Quick Connect | Quick Connect | 1B, 2H | 1112550 | 1112551 | 1112552 | 1112553 |
| Quick Connect | Quick Connect | 1B, 1C | 1112555 | 1112556 | 1112557 | 1112558 |
| Quick Connect | Quick Connect | 1B, 1C, 2H, 2S | 1112560 | 1112561 | 1112562 | 1112563 |
| Triple Action | Tongue Buckle | 1B, 2H | 1112565 | 1112566 | 1112567 | 1112568 |
| Triple Action | Tongue Buckle | 1B, 1C | 1112570 | 1112571 | 1112572 | 1112573 |
| Triple Action | Tongue Buckle | 1B, 1C, 2H, 2S | 1112575 | 1112576 | 1112577 | 1112578 |
| Triple Action | Triple Action | 1B | 1112665 | 1112666 | 1112667 | 1112668 |
| Triple Action | Tongue Buckle | 1B | 1112670 | 1112671 | 1112672 | 1112673 |
| Triple Action | Triple Action | 1B, 1C, 2H | 1112679 | _ | _ | _ |
| Triple Action | Triple Action | 1B, 1C, 2H | 1114082 | 1114083 | 1114084 | 1114085 |

3M™ DBI-SALA® ExoFit™ STRATA™

Vest-Style Harnesses

These harnesses include the same great features of the ExoFit™ STRATA™ without the integrated load distribution system.

Selection guide:



1112483

| Selection guide: | | | | | | | |
|------------------|---------------|--|---------|---------|---------|---------|--|
| Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge | |
| Triple Action | Triple Action | 1B | 1112475 | 1112476 | 1112477 | 1112478 | |
| Triple Action | Triple Action | 1B, 2H | 1112480 | 1112481 | 1112482 | 1112483 | |
| Triple Action | Triple Action | 1B, 1C | 1112485 | 1112486 | 1112487 | 1112488 | |
| Triple Action | Triple Action | 1B, 1C, 2H | 1112490 | 1112491 | 1112492 | 1112493 | |
| Quick Connect | Quick Connect | 1B | 1112495 | 1112496 | 1112497 | 1112498 | |
| Quick Connect | Quick Connect | 1B, 1C | 1112505 | 1112506 | 1112507 | 1112508 | |
| Quick Connect | Quick Connect | 1B, 1C, 2H | 1112510 | 1112511 | 1112512 | 1112513 | |
| Triple Action | Tongue Buckle | 1B | 1112515 | 1112516 | 1112517 | 1112518 | |
| Triple Action | Tongue Buckle | 1B, 2H | 1112520 | 1112521 | 1112522 | 1112523 | |
| Triple Action | Tongue Buckle | 1B, 1C | 1112525 | 1112526 | 1112527 | 1112528 | |
| Triple Action | Tongue Buckle | 1B, 1C, 2H | 1112530 | 1112531 | 1112532 | 1112533 | |
| Triple Action | Tongue Action | 1B, 1C, 2H, 2S | 1114086 | 114087 | 1114088 | 1114089 | |

Harnesses

3M™ DBI-SALA® ExoFit™ STRATA™

Construction-Style Harnesses



| Description | Small | Medium | Large | XLarge |
|--|---------|---------|---------|---------|
| Tri-Lock Revolver™ Buckles, back and side D-rings | 1112535 | 1112536 | 1112537 | 1112537 |
| Duo-Lok™ Quick-Connect Buckles, back and side D-rings | 1112550 | 1112551 | 1112552 | 1112553 |
| Tri-Lock Revolver™ Buckles, back, front and side D-rings | 1112540 | 1112541 | 1112542 | 1112553 |
| Tongue buckle leg straps, back and side D-rings | 1112565 | 1112566 | 1112567 | 1112568 |

3M™ DBI-SALA® ExoFit™ STRATA™

Tower-Climbing Harnesses



| Description | Small | Medium | Large | XLarge |
|---|---------|---------|---------|---------|
| Tri-Lock Revolver Buckles, aluminum front, back and side D-rings, removable seat sling with positioning D-rings | 1112580 | 1112581 | 1112582 | 1112583 |
| Tongue buckle leg straps, aluminum front, back and side D-rings, removable seat sling with positioning D-rings | 1112585 | 1112586 | 1112587 | 1112588 |

3M™ DBI-SALA® ExoFit™ STRATA™

Vest-Style Harnesses without LIFTech™ Technology



| Description | Small | Medium | Large | XLarge | 2X |
|--|---------|---------|---------|---------|---------|
| Aluminum back D-rings, Tri-Lock Revolver™ Quick-Connect Buckles, comfort padding | 1112475 | 1112476 | 1112477 | 1112478 | 1112479 |
| Positioning Harness. Aluminum back and side D-rings, Tri-Lock Revolver™ Quick-Connect Buckles, comfort padding | 1112480 | 1112481 | 1112482 | 1112483 | 1112484 |
| Climbing Harness. Aluminum back, front and side D-rings, tongue buckle leg straps, Tri-Lock Revolver™ chest strap, comfort padding | 1112530 | 1112531 | 1112532 | 1112533 | 1112534 |
| Aluminum back, front, and side D-rings, Tri-Lock Revolver™ Quick-Connect Buckles, comfort padding | 1112490 | 1112491 | 1112492 | 1112493 | 1112494 |
| Aluminum back and side D-rings, tongue buckle leg straps, Tri-Lock Revolver™ chest strap, comfort padding | 1112520 | 1112521 | 1112522 | 1112523 | 1112524 |
| Aluminum back and side D-rings, Duo-Lok™ Quick-Connect Buckles, comfort padding | 1112500 | 1112501 | 1112502 | 1112503 | 1112504 |

3M™ DBI-SALA® ExoFit™ NEX/ExoFit™ NEX Plus

Crossover-Style Harnesses



A front-mounted D-ring makes the crossover-style ideal as a rescue harness and for ladder climbing applications.

| Description | Small | Medium | Large | XLarge |
|--|---------|---------|---------|---------|
| Aluminum front and back D-rings, locking quick-connect buckles | 1113091 | 1113094 | 1113097 | 1113100 |
| Aluminum front, back and side D-rings, locking quick-connect buckles | 1140199 | 1140200 | 1140201 | 1140202 |

3M™ DBI-SALA® ExoFit™ NEX/ExoFit™ NEX Plus

Rope Access and Rescue Harnesses



Complex jobs are easier when your equipment is suited to the task. These multi-use harnesses incorporate components and hardware to optimize rope rescue and industrial rope access work. This makes them ideal for the professional performing rescue and emergency services, industrial rope access and rigging, wind energy and tower maintenance — as well as for arborist activities.

| Description | Small | Medium | Large | XLarge |
|---|---------|---------|---------|---------|
| REPEL Technology Webbing, Tech-Lite™ Aluminum Front, Back and Side D-rings, Duo-Lok™ Quick-Connect Buckles and hybrid comfort padding | 1113345 | 1113346 | 1113347 | 1113348 |
| REPEL Technology Webbing, Tech-Lite™ Aluminum Front, Back and Side D-rings, Duo-Lok™ Quick-Connect Buckles and hybrid comfort padding | 1113370 | 1113371 | 1113372 | 1113373 |

3M™ DBI-SALA® ExoFit™

Crossover-Style Harnesses



A front-mounted D-ring makes the crossover-style ideal for ladder climbing and rescue applications.

| Description | Small | Medium | Large | XLarge |
|---|---------|---------|---------|---------|
| Front and back D-rings, loops for belt, quick-connect buckles | 1402156 | 1402157 | 1402158 | 1402159 |
| Front, back and side D-rings, loops for belt, quick-connect buckles | 1402161 | 1402162 | 1402163 | 1402164 |

Harnesses

3M™ DBI-SALA® ExoFit™ NEX Arc Flash

Vest-Style Full-Body Harnesses



| Description | Small | Medium | Large | XLarge |
|--|---------|---------|---------|---------|
| Nomex®/Kevlar® fiber web, PVC coated aluminum back D-ring, locking quick-connect buckles, comfort padding | 1103085 | 1103086 | 1103087 | 1103088 |
| Nomex®/Kevlar® fiber web, PVC coated aluminum back and side D-rings, locking quick-connect buckles, comfort padding | 1103070 | 1103071 | 1103072 | 1103073 |
| Nomex®/Kevlar® fiber web, dorsal web loop and front rescue loops, locking quick-connect buckles, comfort padding | 1113325 | 1113326 | 1113327 | 1113328 |
| Nomex®/Kevlar® fiber web, PVC coated aluminum front, back and side D-rings, locking quick-connect buckles, comfort padding | 1113330 | 1113331 | 1113332 | 1113333 |

3M™ DBI-SALA® ExoFit™ NEX Arc Flash

Construction-Style Harnesses

With integrated hip pad and body belt, these harnesses have excellent tool-carrying capabilities, allow work positioning and provide added back support.

| Description | Small | Medium | Large | XLarge |
|---|---------|---------|---------|---------|
| Nomex®/Kevlar® fiber web, PVC coated aluminum back and side D-rings, locking quick-connect buckles, sewn-in hip pad and belt, comfort padding | 1113315 | 1113316 | 1113317 | 1113318 |

3M™ DBI-SALA® Delta™

Construction-Style Harnesses



Made for general construction work, these harnesses have tool-carrying capability, a sewn-in hip pad and removable body belt.

| Description | Small | Medium | Large | XLarge | Universal |
|---|---------|---------|---------|---------|-----------|
| Back and side D-rings, quick-connect buckle legs and chest strap, belt with sewn-in back pad | 1110575 | 1110576 | 1110577 | 1110578 | _ |
| Vest-style, back and side D-rings, belt with sewn-in back and shoulder pads, tongue buckle leg straps | 1102201 | 1101654 | 1101655 | 1101656 | _ |
| Front, back and side D-rings, belt and hip pad, tongue buckle leg | 1107805 | 1107802 | 1107801 | 1107809 | _ |

3M™ DBI-SALA® Delta™

Vest-Style Harnesses

Vest-style harnesses are widely used, with multiple configurations and connection point options. They're used across a wide variety of industries.



1102000

Selection guide:

| Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Universal Size |
|---------------|---------------|---------------------------------------|----------------|
| Pass-Through | Pass-Through | 1B, 2S | 1101781 |
| Pass-Through | Tongue Buckle | 1B, 2S | 1101254 |
| Quick Connect | Quick Connect | 1B, 2S | 1110602 |
| Pass-Through | Tongue Buckle | 1B | 1102000 |
| Quick Connect | Quick Connect | 1B | 1110600 |
| Pass-Through | Pass-Through | 1B | 1103321 |
| Pass-Through | Tongue Buckle | 1B, 2H | 1102008 |
| Quick Connect | Quick Connect | 1B, 2H | 1110625 |
| Pass-Through | Pass-Through | 1B, 2H | 1103875 |
| Quick Connect | Quick Connect | 1B, 1C | 1102090 |
| Pass-Through | Tongue Buckle | 1B, 1C | 1107807 |
| Pass-Through | Pass-Through | 1B, 1C | 1112126 |
| Quick-Connect | Tongue Buckle | 1B | 1112052 |
| Quick Connect | Pass-Through | 1B, Conductive-resistant hardware | 1104725 |

3M[™] DBI-SALA[®] Delta[™]

Arc Flash Harnesses

Tested to perform in accordance with the stringent ASTM F887 Standard Specification for Personal Climbing Equipment. Features 7,000 lb. nylon web and leather insulators.



1110782

Selection guide:

| Chest Buckle | Leg Buckles | Web Loop (Back, Front) | Small | Medium | Large | | XLarge |
|---------------|---------------|---------------------------|-----------------------------|---------|---------|----------------|---------|
| N/A | Pass-Through | 1B, 1F | 1110754 | 1110750 | 1110751 | | 1110752 |
| Quick Connect | Quick Connect | 1B, 2F | 1110788 | 1110780 | 1110781 | | 1110782 |
| Quick Connect | Tongue Buckle | 1B, 2F | 1110773 | 1110774 | N/A | | N/A |
| Harness Type | Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest) | | | Universal Size | |
| Standard | Pass-Through | Pass-Through | 1B | | | 1110830 | |
| Vest | Quick Connect | Quick Connect | Back Loop | | | 1110820 | |
| Crossover | Pass-Through | Pass-Through | 1B, 1C, 2H | | | 1110940 | |

1150058

3M™ DBI-SALA® Delta™ Arc Flash Kit

Includes 1110752 Delta Arc Flash Nylon Harness with web loop and Arc Flash Shock-Absorbing Lanyard, 6 ft. (1246305), with bag. (XLarge)

1150054 Kit with Large harness (1110752)



Harnesses

3M™ DBI-SALA® Delta™ Vest

Hi-Vis Reflective and Non-Reflective Workvest Harnesses



Safety is a top priority any time of day. That's why our sleeveless waist-length vests feature a built-in harness for high visibility while working at-height, day or night. They meet CSA Z259.10 for high visibility vests.

| Description | Universal |
|--|-----------|
| High visibility yellow workvest-style harness, reflective, back D-ring, tongue buckle legs | 1107420 |
| High visibility orange workvest-style harness, reflective, back D-ring, tongue buckle legs | 1107404 |
| Blue cotton workvest-style harness, non-reflective, back D-ring, tongue buckle legs | 1107416 |

3M™ DBI-SALA® Delta™

Harnesses for Hot Work Use



Featuring heat-resistant and flame-retardant Nomex®/Kevlar® fiber webbing.

| Description | Universal |
|--|-----------|
| Vest-style, with Nomex®/Kevlar® fiber web, back D-ring, pass-through buckle leg straps, loops for belt | 1105475 |
| Crossover-style, front, back and side D-rings, with Nomex®/Kevlar® fiber web, pass-through buckle leg straps, loops for belt | 1104775 |
| Vest-style, back D-ring, with Nomex®/Kevlar® fiber web, pass-through buckle leg straps, loops for belt | 1104625 |

Delta™ Resist Webbing Harness



Protect against grease, oil, dirt and grime with integrated Resist Technology (polyurethane coated webbing).

| Description | Universal |
|---|-----------|
| Vest-style, back D-ring, tongue buckle legs | 1110990 |

Delta™ Harnesses feature detachable shoulder padding (not shown).

Belts, Workseats and Accessories

3M™ DBI-SALA® Workseats

Bosun Chair



| Description | Universal |
|--|-----------|
| Bosun chair, 12" x 24" x 1" (30.5 cm x 61 cm x 2.5 cm) board, cushion and side snaps | 1001190 |
| Bosun chair only, 12" x 24" x 1" (30.5 cm x 61 cm x 2.5 cm) board | 1001140 |

3M™ DBI-SALA® Tongue Buckle Belts



| Description | Small | Medium | Large | XLarge |
|---|---------|---------|---------|---------|
| Tongue buckle belt with side D-rings, 3" (7.6 cm) pad | 1000022 | 1000023 | 1000024 | 1000025 |
| Delta™ Tongue Buckle Belt with no D-ring and no pad | 1000052 | 1000053 | 1000054 | 1000055 |
| Tongue buckle belt with back D-ring, 3" (7.6 cm) pad | 1000002 | 1000003 | 1000004 | 1000005 |
| Tongue buckle belt with floating D-ring, no pad | 1000162 | 1000163 | 1000164 | 1000165 |
| ExoFit™ Tongue Buckle Belt with no D-ring, no pad | 1000708 | 1000709 | 1000716 | 1000717 |



3M[™] DBI-SALA[®] ExoFit NEX[™] Arc Flash Full-Body Harnesses

All the comfort, function and durability you expect, paired with the flame resistance and conductive-resistant construction needed for high voltage electricity or hotwork, like welding. Meets arc flash standard specifications for personal climbing equipment as well as ANSI/ASSP Z359.11 and CSA Z259.10 requirements.

- Flame-resistant Nomex[®]/Kevlar[®] webbing rated to 7,000 lbs.
- Revolving adjusters maintain fit and lock excess webbing in place.
- Flame-resistant trauma straps.
- Conductive-resistant, PVC-coated aluminum D-rings.
- Leather insulators help prevent contact between hardware and body.
- Comfortable, lightweight arc flash-rated padding and soft edging.
- Quick-connecting buckles enhance productivity.
- Tested to perform to ASTM F887 for personal climbing equipment.
- 420 lb. capacity (Model shown 1113318).



3M™ DBI-SALA® ExoFit NEX™ Arc Flash

Vest-Style Full-Body Harnesses

These harnesses feature Nomex®/Kevlar® fiber webbing, PVC coated D-rings and comfort padding.



Selection guide:

| Harness Type | Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge |
|-----------------|---------------|---------------|---|---------|---------|---------|---------|
| Standard | Quick Connect | Quick Connect | 1B | 1103085 | 1103086 | 1103087 | 1103088 |
| Standard | Pass-Through | Pass-Through | 1B | 1113335 | 1113336 | 1113337 | 1113338 |
| Positioning | Quick Connect | Quick Connect | 1B, 2H | 1103070 | 1103071 | 1103072 | 1103073 |
| Rescue | Quick Connect | Quick Connect | 1B Loop, 2C Loops | 1113325 | 1113326 | 1113327 | 1113328 |
| Climbing | Quick Connect | Quick Connect | 1B, 1C, 2H | 1113330 | 1113331 | 1113332 | 1113333 |
| Construction | Quick Connect | Quick Connect | 1B, 1C, 2H | 1113490 | 1113492 | 1113491 | 1113493 |

1113493

With an integrated hip pad and body belt, these harnesses have excellent tool-carrying capabilities and allow work positioning.

Construction-Style Harnesses



Selection guide:

3M™ DBI-SALA® ExoFit NEX™ Arc Flash

| Harness Type | Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge |
|-----------------------|---------------|---------------|---|---------|---------|---------|---------|
| Construction | Quick Connect | Quick Connect | 1B, 2H | 1113315 | 1113316 | 1113317 | 1113318 |
| Tower Climbing AFK | Quick Connect | Quick Connect | 1B Loop, 1C, 2H, Seat Sling | 1113357 | 1113358 | 1113368 | 1113369 |

1113369

3M™ DBI-SALA® ExoFit NEX™ Arc Flash

Full-Body Harnesses



Selection guide:

| Harness Type | Chest Buckle | Leg Buckles | D-rings (Back, Hips, Chest, Shoulder) | Small | Medium | Large | XLarge |
|-------------------------|---------------|---------------|---|---------|---------|---------|---------|
| Rope Access/ Rescue | Quick Connect | Quick Connect | 1B, 2H | 1113761 | 1113762 | 1113763 | 1113764 |
| Rope Access/ Rescue | Quick Connect | Quick Connect | 1B, 2H | 1113757 | 1113758 | 1113759 | 1113760 |
| Lineman with 2D Belt | Quick Connect | Quick Connect | 1B, 2H | 1113676 | 1113682 | 1113688 | 1113692 |







1113760 1113786 1113764

For Lineman Belts and Harnesses, see page 62.

Lineman Belts and Harnesses


3M™ DBI-SALA® 4D Lineman Belts

Innovative design keeps the center of gravity at the top of the belt for improved safety and optimal comfort.

- 1 Leather construction
- 2 Connections to S-shaped, full floating D-rings
- 3 3M[™] DBI-SALA® Cynch-Lok[™] Fall-Restricting Device compatible (see 92)
- 4 Distributes weight throughout the contoured, reinforced seat
- 5 Adjustable tongue buckle belt of nylon construction



| ExoFit NEX [™] Arc Flash Harness with 2D Belt | | | | | | | |
|--|---------------|---------------|---------------|---------------|--|--|--|
| Small | 1113675 – D20 | 1113676 – D21 | 1113677 – D22 | 1113678 – D23 | | | |
| Medium | 1113681 – D22 | 1113682 – D23 | 1113683 – D24 | 1113684 – D25 | | | |
| Large | 1113688 – D25 | 1113689 – D26 | 1113690 – D27 | _ | | | |
| XLarge | 1113691 – D25 | 1113692 – D26 | 1113693 – D27 | - | | | |





Where to measure to determine the correct "D" size for a Lineman's Belt:

X = Distance from waist or top of hip bone to where Lineman's Belt is worn.

Y = Measurement is from front of hip bone around the back to the front of the other hip bone. This measurement is the "D" size.



| 2D Belt | | | | | | |
|---------|---------|--|--|--|--|--|
| D Size | SKU | | | | | |
| D18 | 1001379 | | | | | |
| D19 | 1001380 | | | | | |
| D20 | 1001381 | | | | | |
| D21 | 1001382 | | | | | |
| D22 | 1001383 | | | | | |
| D24 | 1001385 | | | | | |
| D25 | 1001386 | | | | | |
| D26 | 1001387 | | | | | |
| D27 | 1001388 | | | | | |
| D28 | 1001389 | | | | | |
| D29 | 1001390 | | | | | |
| D30 | 1001391 | | | | | |

| 4D Belt | | | | | | |
|---------|---------|--|--|--|--|--|
| D Size | SKU | | | | | |
| D18 | 1001392 | | | | | |
| D19 | 1001393 | | | | | |
| D20 | 1001394 | | | | | |
| D21 | 1001395 | | | | | |
| D22 | 1001396 | | | | | |
| D23 | 1001397 | | | | | |
| D24 | 1001398 | | | | | |
| D25 | 1001399 | | | | | |
| D26 | 1001400 | | | | | |
| D27 | 1001401 | | | | | |
| D28 | 1001402 | | | | | |
| D29 | 1001403 | | | | | |
| D30 | 1001404 | | | | | |

| D Size | Belt Sizing (in.) | | | | |
|--------|-------------------|-------------|---------|--|--|
| (in.) | Minimum | Center Hole | Maximum | | |
| D18 | 32 | 36 | 40 | | |
| D19 | 33 | 37 | 41 | | |
| D20 | 34 | 38 | 42 | | |
| D21 | 36 | 40 | 44 | | |
| D22 | 37 | 41 | 45 | | |
| D23 | 38 | 42 | 46 | | |
| D24 | 40 | 44 | 48 | | |
| D25 | 41 | 45 | 49 | | |
| D26 | 42 | 46 | 50 | | |
| D27 | 44 | 48 | 52 | | |
| D28 | 45 | 49 | 53 | | |
| D29 | 46 | 50 | 54 | | |
| D30 | 47 | 51 | 55 | | |





3M[™] Protecta[®] Full-Body Harnesses



Comfort Construction-Style (1161205)

Upgraded features:

- ► Modern New Look
- ► Fixed Back D-ring
- ► Comfort Back Pad with U-shaped Neck
- ► Softer and More Robust Hip Pad
- ► Durable and Sturdy Belt
- Auto-resetting Lanyard Keepers
- ► Impact Indicators
- ► Protected Labels



Selection Guide

| Chest Buckle | Leg Buckles | D-Rings (Back, Hips, Chest, Shoulder) | Small | Medium/ Large | XLarge | 2XLarge |
|---------------|---------------|--|---------|------------------|---------|---------|
| Quick Connect | Quick Connect | 1B, 2H | 1161200 | 1161201 | 1161202 | 1161203 |
| Pass-Thru | Tongue | 1B, 2H | 1161204 | 1161205* | 1161207 | 1161208 |
| Quick Connect | Tongue | 1B, 2H | 1161216 | 1161217 | 1161218 | 1161219 |
| Pass-Thru | Tongue | 1B, 2H | 1161209 | 1161210 | 1161211 | N/A |
| Quick Connect | Quick connect | 1B, 1C, 2H | 1161220 | 1161221 | 1161222 | N/A |
| Pass-Thru | Tongue | 1B, 1C, 2H | 1161226 | 1161227 | 1161228 | N/A |
| Quick Connect | Tongue | 1B, 1C, 2H | 1161223 | 1161224 | 1161225 | N/A |

^{*1161206} is the 1161205 Medium/Large Harness with an Extra Large Belt



Standard Construction-Style (1161309)

Upgraded features:

- ► Modern New Look
- ► Fixed Back D-ring
- ► Shoulder Pads
- ► Softer and More Robust Hip Pad
- ► Durable and Sturdy Belt
- Auto-resetting Lanyard Keepers
- ► Impact Indicators
- ► Protected Labels

Selection Guide

| Chest Buckle | Leg Buckles | D-Rings (Back, Hips, Chest, Shoulder) | Small | Medium/ Large | XLarge | 2XLarge |
|---------------|-------------|--|---------|------------------|---------|---------|
| Pass-Thru | Pass-Thru | 1B, 2H | 1161304 | 1161305 | 1661306 | 1161307 |
| Pass-thru | Tongue | 1B, 2H | 1161308 | 1161309 | 1161310 | 1161311 |
| Quick Connect | Tongue | 1B, 2H | 1161315 | 1161316 | 1161317 | N/A |
| Pass-Thru | Tongue | 1B | 1161300 | 1161301 | 1161302 | 1161303 |



Hot Work Use (1191369)

Features:

- Heat Resistant and flame retardant Kevlar Fiber Webbing
- ► Impact Indicator
- ► Protective Label Pack

Selection Guide

| Chest Buckle | Leg Buckles | D-Rings (Back, Hips, Chest, Shoulder) | Small | Medium/ Large | XLarge |
|--------------|-------------|--|---------|------------------|---------|
| Pass-Thru | Pass-Thru | 1B | 1191369 | 1191379 | 1191380 |
| Pass-thru | Pass-Thru | 1B, 2H | 1191370 | 1191381 | 1191382 |
| Pass-Thru | Tongue | 1B | 1191371 | 1191383 | 1191384 |
| Pass-Thru | Tongue | 1B, 2H | 1191372 | 1191385 | 1191386 |

3M[™] Protecta[®] Full-Body Harnesses



Comfort Vest-Style (1161418)

Upgraded features:

- ► Modern New Look
- ► Fixed Back D-ring
- ► Comfort Back Pad with U-shaped Neck
- Auto-resetting Lanyard Keepers
- ► Impact Indicators
- ► Protected Labels



1161418 Shown

Selection Guide

| Chest Buckle | Leg Buckles | D-Rings (Back, Hips, Chest, Shoulder) | Small | Medium/ Large | XLarge | 2XLarge |
|---------------|---------------|--|---------|------------------|---------|---------|
| Pass-Thru | Pass-Thru | 1B | 1161423 | 1161424 | 1161425 | N/A |
| Quick Connect | Quick Connect | 1B | 1161426 | 1161427 | 1161428 | N/A |
| Pass-Thru | Tongue | 1B | 1161417 | 1161418 | 1161419 | N/A |
| Quick Connect | Tongue | 1B, 2H | 1161420 | 1161421 | 1161422 | N/A |
| Quick Connect | Quick Connect | 1B, 2H | 1161400 | 1161401 | 1161402 | 1161403 |
| Pass-Thru | Tongue | 1B, 2H | 1161413 | 1161414 | 1161415 | 1161416 |
| Pass-Thru | Pass-Thru | 1B, 1C, 2H | 1161436 | 1161437 | 1161438 | N/A |
| Quick Connect | Quick Connect | 1B, 1C, 2H | 1161442 | 1161443 | 1161444 | N/A |
| Quick Connect | Tongue | 1B, 1C, 2H | 1161439 | 1161440 | 1161441 | N/A |
| Pass-Thru | Pass-Thru | 1B, 1C | 1161433 | 1161434 | 1161435 | N/A |
| Quick Connect | Quick Connect | 1B, 1C | 1161404 | 1161405 | 1161406 | N/A |
| Pass-Thru | Tongue | 1B, 1C | 1161429 | 1161430 | 1161431 | 1161432 |





Selection Guide 116

1161542 Shown

Standard Vest-Style (1161542)

Upgraded features:

- ► Modern New Look
- Impact Indicators
- ► Fixed Back D-ring
- ► Protected Labels
- ► Auto-resetting Lanyard Keepers

| Chest Buckle | Leg Buckles | D-Rings (Back, Hips, Chest, Shoulder) | XSmall | Small | Medium/ Large | XLarge | 2XLarge | 3XLarge |
|---------------|---------------|--|---------|---------|------------------|---------|---------|---------|
| Pass-Thru | Pass-Thru | 1B, 1C, 2H | N/A | 1161510 | 1161511 | 1161512 | N/A | N/A |
| Pass-Thru | Tongue | 1B, 1C, 2H | N/A | 1161506 | 1161507 | 1161508 | 1161509 | N/A |
| Pass-Thru | Pass-Thru | 1B, 2H, 2S | N/A | 1161563 | 1161564 | 1161565 | N/A | N/A |
| Pass-Thru | Tongue | 1B, 2H, 2S | N/A | 1161538 | 1161539 | 1161540 | N/A | N/A |
| Pass-Thru | Pass-Thru | 1B, 1C, Rescue | N/A | 1161517 | 1161518 | 1161519 | N/A | N/A |
| Pass-Thru | Pass-Thru | 1B, 2S | N/A | 1161576 | 1161577 | 1161578 | 1161579 | N/A |
| Quick Connect | Quick Connect | 1B, 2S | N/A | 1161528 | 1161529 | 1161530 | N/A | N/A |
| Pass-Thru | Tongue | 1B, 2S | N/A | 1161549 | 1161550 | 1161551 | 1161552 | N/A |
| Pass-Thru | Pass-Thru | 1B, 1C, 2H, 2S | N/A | 1161513 | 1161514 | 1161515 | 1161516 | N/A |
| Pass-Thru | Pass-Thru | 1B, 1C | N/A | 1161553 | 1161554 | 1161555 | N/A | N/A |
| Quick Connect | Quick Connect | 1B, 1C | N/A | 1161556 | 1161557 | 1161558 | N/A | N/A |
| Pass-Thru | Tongue | 1B, 1C | N/A | 1161520 | 1161521 | 1161522 | 1161523 | N/A |
| Pass-Thru | Pass-Thru | 1B, 2H | N/A | 1161559 | 1161560 | 1161561 | 1161562 | N/A |
| Quick Connect | Quick Connect | 1B, 2H | N/A | 1161566 | 1161567 | 1161568 | 1161569 | N/A |
| Pass-Thru | Tongue | 1B, 2H | N/A | 1161531 | 1161532 | 1161533 | 1161534 | N/A |
| Pass-Thru | Pass-Thru | 1B | N/A | 1161570 | 1161571 | 1161572 | 1161573 | N/A |
| Quick Connect | Quick Connect | 1B | N/A | 1161524 | 1161525 | 1161526 | 1161527 | N/A |
| Pass-Thru | Tongue | 1B | N/A | 1161541 | 1161542 | 1161543 | 1161544 | 1161545 |
| Quick Connect | Tongue | 1B | 1161500 | 1161501 | 1161502 | 1161503 | 1161504 | 1161505 |

3M™ Protecta®Harness
Accessories



Equipment Bag AK048A

Compact harness/lanyard bag, 13 in. x 12 in. (33 cm x 30 cm).



Equipment Bag AK066A

Large bag for harness and lanyard or 50 ft. (15 m) lifeline, 9-1/2 in. \times 10 in. \times 15-1/2 in. (24 cm \times 25 cm \times 40 cm).



Body Belt

Tongue buckle belt with hip pad and side D-rings.

1091013 Small

1091014 Medium/Large **1091015** XLarge



D-Ring Extender 1385000

Dorsal D-ring extender with D-ring at one end, snap hook at other x 18 in. (45 cm).

The new generation of

3M[™] Protecta[®] Full-Body Harnesses



| | | Comfort Construction- Style Harness | Standard Construction- Style Harness | Comfort Vest-Style Harness | Standard Vest-Style Harness |
|--|---------------|--|---|--------------------------------|--------------------------------|
| Modern New Look | | ✓ | ✓ | ✓ | ✓ |
| Easy-Link SRL Adapter | | ✓ | | ✓ | |
| Fixed Back D-Ring | | ✓ | ✓ | ✓ | ✓ |
| Comfort Back/Shoulder Pa | dding | Back Pad with U-Shaped Neck | Shoulder Pads | Back Pad with U-Shaped Neck | |
| Softer Hip Pad | | ✓ | ✓ | | |
| Sturdier Belt | | ✓ | ✓ | | |
| ANSI Z359.11 Compliant Au Lanyard Keepers | ito-Resetting | ~ | ~ | ✓ | ~ |
| Impact Indicators | | ✓ | ✓ | ✓ | ✓ |
| Protected Labels | | ✓ | ✓ | ✓ | ✓ |
| Part Numbers Previous SKU ► New SKU | SM | 1191432 & 1191286 > 1161204 | 1191208 1161308 | 1191429 1161417 | 1191236 - 1161541 |
| rievious and New and | MED/LG | 1191433 & 1191287 > 1161205 | 1191209 1161309 | 1191430 1161418 | 1191237 1161542 |
| | XL | 1191434 & 1191288 > 1161207 | 1191210 > 1161310 | 1191431 1161419 | 1191238 - 1161543 |

Reduced worker fatigue and increased productivity is within reach. The improved fit, lightweight hardware and padding and updated colors make 3M™ Protecta® Full-Body Harnesses an excellent choice for comfort, style and safety on the job. Plus, each harness features built-in lanyard keepers and a worker capacity of up to 420 lbs. (190 kg). These harnesses meet OSHA and ANSI standards, including the stringent ANSI Z359.11.

Harness Sizing Chart





New 3M customers can **Trade-in:**




Trade in competitive fall protection products

Purchase comparable qualifying*
3M Fall Protection products

Receive a cash rebate

Existing 3M customers can Trade-up:



Trade in current 3M Fall Protection products

Purchase new, upgraded qualifying**
3M Fall Protection products

Receive a cash rebate

Offer subject to change without notice. Requires digital copy of your receipt of purchase from a 3M authorized distributor and digital images proving your old equipment was taken out of service (e.g. Harnesses with D-rings cut off, SRLs & Lanyards with hooks cut off). End users and/or distributors responsible for collecting and disposing of trade-in/trade-up products. Must follow requirements online to receive rebate. Distributors and wholesalers excluded. End user rebate only. Visit go.3M.com/FPtradein for full terms and conditions.

 $^{{}^{\}star}\,\text{Comparable qualifying products means anchor for anchor, harness for harness, etc.}\,\text{Except as noted in the Terms \& Conditions.}$

^{**} Upgraded qualifying products means current 3M customer must purchase a higher value comparable product to qualify for a rebate. (Example: Delta[™] Harness traded in for an ExoFit NEX" Harness. ExoFit NEX" Harness for ExoFit" STRATA" Harness. 3M" Protecta® SRL for 3M" DBI-SALA® SRL.)

Understanding leading and sharp edges



The smaller the edge radius, the sharper the edge.

Sharp edges are found in many leading edge applications where the edge is able to cut or damage a traditional lifeline upon contact. Typical I-beams have edge radii that range from .005 in. to .032 in. Do you know how sharp your edges are?



Leading Edge

To visualize a leading edge, imagine a worker installing steel decking on a new building. Now imagine the worker's fall protection system is anchored at foot-level behind him. As the worker moves out and away from the anchor point while installing the decking, the worker is exposed to a potential fall over the edge of the building or the edge of an elevated platform.




Sharp Edge

A sharp edge is one that, for practical purposes, is not rounded and has the potential to cut most types of lifelines. The ANSI Z359.14 standard for sharp edges, for example, involves testing the fall arrest device's lifeline over a piece of steel bar with a radius of no more than 0.005 in. (5 one thousands of an inch). If the lifeline is cut or severely damaged, the device fails the test and does not comply with ANSI.

Understanding leading and sharp edges

Unique risks of leading and sharp edges:


Increased fall distance



When workers are attached at foot-level, as they often are in leading edge applications, they will fall farther than they would if they were anchored at shoulder height or above. The required clearance when anchored at foot-level varies by product so make sure to reference the products' user instructions.

2. Lock-up speed

Required time to reach velocity to engage lifeline takes longer because of longer fall distance.



Self-retracting lifelines react to a fall when the lifeline accelerates out of the housing at a certain velocity. When self-retracting lifelines are anchored at foot-level, the lifeline does not achieve the required acceleration during a fall until after the user's D-ring passes over the leading edge and below the level of the anchor. This means the user has already fallen approximately 5 feet before the self-retracting lifeline device will engage to arrest the fall.

Increased fall arrest forces

Potentially higher impact to the body when the fall is arrested.


fall clearance.



Falling further means the impact on the body through the fall protection system will potentially be greater when the fall is arrested. This is why leading edge and sharp edge rated products contain additional energyabsorbing devices.

4. Increased potential for swing hazards

This could create a sawing action on a lifeline strung taught over a sharp edge.



Depending on a worker's position during a fall, they may swing like a pendulum after the fall is arrested. While swinging is a hazard under any circumstances, the danger is compounded if the worker's lifeline is strung taught over a sharp edge and saws back and forth across that edge.

Leading Edge Self-Retracting Lifelines

3M[™] DBI-SALA[®] Smart Lock Leading Edge SRL and Modular Connector

3M testing shows that back D-ring extenders used with standard leading edge SRLs in leading or sharp edge applications could create the potential for a system component to be severed, but not anymore. The Smart Lock Leading Edge SRL is engineered to address this risk and allows for use of a 14 in. modular extension in leading or sharp edge applications.

- Integrated onto existing 3M™ DBI-SALA® Smart Lock Leading Edge SRL (30 ft.)
- Engineered to address risk of use for D-ring extensions in Leading Edge applications.
- Allows for use of 14 in. extension.
- Addresses durability constraints with replaceable shock-pack extender.
- Meets ANSI Z359.14.

| Application | Part # | Length | Lifeline Material |
|--|----------|--------|-------------------|
| Leading Edge SRL with D-ring extension | 3503848* | 30' | Galvanized Steel |
| Modular D-ring extension | 1246500 | 14" | _ |

^{*}D-ring extensions can only be used with these models.






Leading Edge Self-Retracting Lifelines

3M™ DBI-SALA® Ultra-Lok™ Leading **Edge Self-Retracting Lifelines**

This line of retractables includes lengths from 15 ft. to 55 ft. is approved for leading edge work and foot-level tie-off.

- Top swivel limits lifeline twisting.
- Thermoplastic housing.
- Ergonomic cable handle provides added comfort and ease-of-use when making connections.
- · Self-locking swivel hook limits lifeline twisting.
- Impact indicator provides visual indication of fall arrest.
- 3,600 lb. gate reduces chances of accidental disengagement ("roll-out").
- Stainless steel components and anti-ratcheting brake system.

| Application | Part # | Length | Lifeline Material |
|------------------------------|---------|--------|-------------------|
| | 3504422 | 15' | Galvanized Steel |
| Horizontal (Leading Edge) | 3504500 | 30' | Galvanized Steel |
| | 3504600 | 55' | Galvanized Steel |



3M™ DBI-SALA® Smart Lock Leading **Edge Self-Retracting Lifelines**

The 3M™ DBI-SALA® Smart Lock Self-Retracting Lifeline is designed to help increase your productivity and convenience. Significant internal testing was completed to make this product work while reducing the unintentional lockups.

Compared to our existing devices, the new Smart Lock SRL locked up 29% less when tested against 422 work motion profiles.

- Swiveling anchorage and carabiner.
- · Built-in handle.
- Magnetic retraction control
- Patent pending dual label system.
- Highly-visible orange energy-absorber cover.

| Application | Part # | Length | Lifeline Material |
|----------------|---------|--------|-------------------|
| Horizontal | 3503802 | 20' | Galvanized Steel |
| (Leading Edge) | 3503822 | 30' | Galvanized Steel |



Leading Edge Self-Retracting Lifelines

3M[™] DBI-SALA[®] Nano-Lok[™] Edge Self-Retracting Lifeline

- Connector provides 360 degrees of rotation and leaves the D-ring open for rescue or other equipment.
- Impact-resistant housing provides durability.
- Global sharp edge icon makes identification of sharp edge product quick and easy.
- 8 ft. (2.4 m) of 3/16 in. (5 mm) galvanized cable lifeline.
- Backpack design stays tight to the harness and helps evenly distribute the unit's weights.
- Backpack-style energy absorber and connector work together to help limit forces on both the worker and the impacted edge.





Selection guide:



















| ì | Lifeline he | ماد | | | | | | | | CDI |
|---|-------------|--------------------------------|-----------------------------|---------------------------|------------------------|-----------------------|------------------------------|----------------------------------|--------------------------|---------|
| | Lifeline ho | | | | | | | | | SRL |
| | Tie-back* | Aluminum Rebar Lock Hook | Steel Rebar Lock Hook | Aluminum Rebar Hook | Steel Rebar Hook | Steel Snap Hook | Steel Swivel Snap Hook | Aluminum Captive Carabiner | Aluminum Snap Hook | Part # |
| | • | | | | | | | | | 3500228 |
| | | • | | | | | | | | 3500231 |
| | | | | | | | | | | 3500227 |
| | | | | | | | | | | 3500249 |
| | | | | | | | | | | 3500246 |
| | | | | | | | | | | 3500225 |
| ľ | | | | | | | • | | | 3500226 |
| | | | | | | | | | | 3500229 |
| | | | | | | | | | | 3500230 |
| | | | | | | | | | | 3500213 |
| | | | | | | | | | | 3500216 |
| | | | | | | | | | | 3500212 |
| | | | | | | | | | | 3500247 |
| | | | | | | | | | | 3500248 |
| | | | | | | | | | | 3500210 |
| | | | | | | | | | | 3500211 |
| | | | | | | | | | | 3500214 |
| | | | | | | | | | | 3500215 |

^{*}All versions are 8 ft. in length except tie-back models. Tie-back versions are 9 ft.

3M DBI-SALA® Anchors for Leading Edge Applications

Anchors Commonly Used in Leading Edge Applications. Compatible with all versions of Ultra-Lok Leading Edge SRL's (15 ft., 30 ft., 55 ft.) and all Smart Lock Leading Edge SRL's (20 ft. & 30 ft.)



Standing Seam Roof Anchor

- Installs to flat or sloped roofs, providing an SRL anchorage point.
- Four built-in non-penetrating clamps allow for attachment without damaging the roof.
- Slide on the tube legs fit a variety of seam spacings up to 36 in.



2190074

Construction Roof Anchor

- Installs to rebar ring during pre-cast concrete work utilizing built-in ratcheting securement system—no special tools required.
- Dual-use design allows for use as end anchors for a 2-person temporary 3M[™] DBI-SALA[®] Horizontal Lifeline System.
- For use with 3M[™] DBI-SALA[®] Smart Lock SRL (Sold Separately).




2190071

Swiveling Roof Anchor

- Installs to a variety of sloped or flat wood and metal decking roofs to provide an anchorage point for an SRL or a tie-off point.
- Install with included fastener kit: 16 ea. 1/4-14 × 2-1/2 in. self-tapping screws for steel installation and 8 ea. 1/4 × 2-1/2 in. lag screws for wood.
- Secondary D-ring anchor allows for tie-off with lanyard or install a Horizontal Lifeline between two anchors.

3M[™] DBI-SALA[®] Nano-Lok[™] Self-Retracting Lifelines





3100483Dual-Pin style SRL Connector (optional)

Light on weight. Heavy on features.

Introducing the new 3M™ DBI-SALA® Nano-Lok™ Personal Self-Retracting Lifeline. Our latest version doesn't just match the performance of the outgoing model—it surpasses it and then some. It's sleeker with a more compact design. It's tougher with a longer lasting cover. It's easier and faster to connect.* All while complying with OSHA's 1910.140 General Industry 4 ft. fall protection rule and ANSI Z359.14 Class A & B standards.

- 900 lb. average arresting force
- 1,350 lb. maximum arresting force
- Installs 60% faster*
- Inspect easily and quickly
- Nitrile rubber cover lasts 4X longer than outgoing mode
- 4 ft. overhead fall clearance per OSHA 1910 General Industry
- ANSI Class A/B units arrest falls within 24" and limit average arresting forces to 900 lbs.
- Knee-level or higher tie-off
- 310 lb. capacity

^{*}Compared to previous generation.

3M[™] DBI-SALA[®] Nano-Lok[™] Personal Self-Retracting Lifelines

Connector Options

| E | Ţ | Ar | nchorage Type Lifeline Hook Options | | | | | | | | | | | |
|----------------|------------|--|-------------------------------------|-------------------------------|-----------------------|-----------------------|--------------------------|---|---------------------------|-----------------------------|---|--|----------------------|-----------|
| | | D | O | 0 | luded | 8 | 8 | 8 | P | | | | 8 | |
| 8 | | NEW Nano-Lok" Single Pin Connector 3100480 | Steel Carabiner 2000112 | Aluminum Carabiner 2000025 | No Connector Included | Steel Snap Hook | Aluminum Snap Hook | Aluminum Captive Eye Carabiner | Aluminum Rebar Hook | Flat Steel Rebar Hook | Aluminum Rebar Hook with Locking Nose | Steel Rebar Hook with Locking Nose | Comfort Grip Hook | |
| Gate Openii | ng | W Na e Pin 3100 | eel Ca 200 | inum 200(| 8 | 3/4 in. (19 mm) | 3/4 in. (19 mm) | 3/4 in. (19 mm) | 2-1/4 in. (57 mm) | 2-1/2 in. (62.5 mm) | 2-1/2 in. (62.5 mm) | 2-1/2 in. (62.5 mm) | 2-1/4 in. (57 mm) | |
| Gate Streng | | Singl | St | Alun | | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | Pa Num |
| | | • | | | | • | | | | | | | | 3101 |
| | | • | | | | | | | | | | | | 3101 |
| | | • | | | | | | • | | | | | | 3101 |
| | | • | | | | | | | | | | | | 3101 |
| | | | | | | | | | | | | | | 3101 |
| | | • | | | | | | | | | | | | 3101 |
| | | • | | | | | | | | | | | | 31013 |
| | | • | | | | | | | | | | | - | 31016 |
| | Leg | | - | | | - | | | | | | | | 3101 |
| | Single Leg | | | | | | | | | | | | | 3101 |
| | | | | | | | | | | | | | | 31012 |
| | | | | | | | | | | | | | | 31012 |
| ANSI Class A/B | | | - | | | | | | | • | | | | 3101 |
| Class | | | | | _ | _ | | | | | | | | 31014 |
| n Z | | | | | | - | _ | | | | | | | 31012 |
| ∢ | | | | | - | | | | | | | | | 31012 |
| | | | | | | | | | | | | | | 31012 |
| | | | | | | | | | | | | | | 31012 |
| | | | | | - | | | | | - | | | | 31012 |
| | | • | | | _ | • | | | | | | | _ | 31012 |
| | | - | | | | | | | | | | | | 31012 |
| | | | | | | | | | | | | | | 31012 |
| | eg | _ | | | | | | | | | | | | 31012 |
| | Twin Leg | - | | | | | | | | • | | | | 31012 |
| | H | • | | | | | | | | | • | | | 31014 |
| | | • | | | | | | | | | | | | 3101 |
| | | • | | | | | | | | | | | | 31016 |

For ANSI Class B only models, see next page.

3M[™] DBI-SALA[®] Nano-Lok[™] Personal Self-Retracting Lifelines, ANSI Class B

What's a Class B SRL?

Like Class A SRLs, these are OSHA 1926.500 subpart M compliant, but they differ in how quickly they stop a fall (within 54 in. or less), and the subsequent average arrest force on the worker (900 lbs.).

- ANSI Class B device utilizes smart activating brake system to provide 89% fewer unintentional lock-ups*
- Lightweight speed connect system reduces connect and disconnect time by up to 60%*
- Durable nitrile rubber energy absorber cover designed to last 4 times longer*
- 6 ft. fall clearance required on Class B SRLs

Connector Options

| ~ | 3 | Ar | nchorag | ge Type | | | | | Lifeline | Hook Optio | ns | | | |
|----------------|------------|--|----------------------------|-------------------------------|-----------------------|-----------------------|--------------------------|---|---------------------------|-----------------------------|---|--|----------------------|----------------|
| Ė | | Ď | 0 | 0 | Inded | 8 | 8 | 8 | P | | | | 8 | |
| d | | NEW Nano-Lok" ngle Pin Connector 3100480 | Steel Carabiner 2000112 | Aluminum Carabiner 2000025 | No Connector Included | Steel Snap Hook | Aluminum Snap Hook | Aluminum Captive Eye Carabiner | Aluminum Rebar Hook | Flat Steel Rebar Hook | Aluminum Rebar Hook with Locking Nose | Steel Rebar Hook with Locking Nose | Comfort Grip Hook | |
| Gate Openi | ng | NEW Na Single Pin (3100 | teel Ca 2000 | minum 2000 | N _o N | 3/4 in. (19 mm) | 3/4 in. (19 mm) | 3/4 in. (19 mm) | 2-1/4 in. (57 mm) | 2-1/2 in. (62.5 mm) | 2-1/2 in. (62.5 mm) | 2-1/2 in. (62.5 mm) | 2-1/4 in. (57 mm) | |
| Gate Streng | th | Sing | S | Alur | | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | 3,600 lb. (16 kN) | Part Number |
| | | | | | | | | | | | | | | 3101703 |
| | э Ге | • | | | | | | | | | | | | 3101701 |
| ss B | Single Leg | • | | | | | | | | | | | | 3101702 |
| ANSI Class B | | | | | | | | | | | | | | 3101704 |
| ANS | eg | • | | | | | | | | | | | | 3101705 |
| | Twin Leg | | | | | | | | | | | | | 3101706 |
| | Ę | | | | | | | | | | | | | 3101707 |

3101703

Nano-Lok[™] Self-Retracting Lifeline, Class B

With single pin quick connector and Steel Snap Hook x 6 ft. (1.8 m)



3101704

Nano-Lok™ Self-Retracting Lifeline, Class B

With single pin quick connector and Steel Rebar Hook x 6 ft. (1.8 m)



3101706 Nano-Lok™

Twin-Leg
Self-Retracting
Lifeline, Class B

With single pin quick connector and Steel Rebar Hooks x 6 ft. (1.8 m)



3101707

Nano-Lok™ Twin-Leg Self-Retracting Lifeline, Class B

With quick connector and Aluminum Comfort Grip Snap Hooks x 6 ft. (1.8 m)



^{*} Compared to previous generation.

3M™ DBI-SALA® Nano-Lok™ Extended Length Self-Retracting Lifelines

3101582

Nano-Lok™ Extended Length Quick-Connect Self-Retracting Lifeline With Anchor Hook x 11 ft. (3.35 m)



3101588

Nano-Lok™ Extended Length Order Picker Self-Retracting Lifeline With Snap Hook x 11 ft. (3.35 m)



3101590

Nano-Lok™ Extended Length Quick-Connect Self-Retracting Lifeline With Aluminum Rebar Hook x 9 ft. (2.74 m)



3101621

Nano-Lok[™] Extended Length Twin-Leg Quick-Connect Self-Retracting Lifeline

With Snap Hook x 11 ft. (3.35 m)

3101624

Nano-Lok™ Extended Length Twin-Leg Quick-Connect Self-Retracting Lifeline

With Aluminum Locking Rebar Hooks x 9 ft. (2.74 m)



Nano-Lok™ Extended Length Twin-Leg Quick-Connect Self-Retracting Lifeline

With Aluminum Rebar Hooks x 9 ft. (2.74 m)



*Additional Models Available, Contact 3M Fall Protection

3M[™] DBI-SALA[®] Nano-Lok[™] Connected Order Picker Self-Retracting Lifeline

This innovative Fall Protection system senses a worker's presence on an order picking vehicle, verifies their tie-off status, and communicates visual and audible alerts in real time to promote situational awareness and self behavior.

- Connected Sensor Box
 Overhead unit detects worker's presence on vehicle
- Connected Aluminum Carabiner
 Sensing carabiner detects if it's
 connected to worker's harness
 D-Ring and if the carabiner gate
 is closed and locked.



3100273 Nano-Lok[™] Connected Order



3M[™] DBI-SALA[®] Nano-Lok[™] Wrap-Back Self-Retracting Lifelines

Functioning as both a fall protection device and tie-off adapter, it allows safety managers to consolidate multiple equipment capabilities in one versatile solution. The Nano-Lok™ Wrap Back SRL is approved for overhead or foot level tie-off applications.* It connects to beams, rebar walls and other structures that can properly support fall arrest forces—helping protect workers in a wide variety of at-height environments.

- Designed for foot-level anchorage around non-sharp edges
- Wrap back design with specialized Dyneema® web lifeline
- Twin-leg 100% tie-off design
- Built-in pin-style connector for direct attachment to harness
- 8 ft. (2.4 m) of 3/4" (19 mm) wide blue Dyneema® fiber polyester web
- · Self-locking snap hook on end of lifeline
- · Thermoplastic housing
- Swiveling anchorage loop
- Quick activating speed sensing brake systems
- Integrated backpack style energy absorber
- 3M[™] Connected Safety ID (CSID) equipped
- 310 lbs. capacity



3101659

Nano-Lok[™] Wrap Back

8 ft. (2.4 m) twin-leg tie-back type lifeline with 3/4 in. (19 mm) wide Dyneema® fiber web and steel rebar hook. Quick connector for harness mounting. 3101658 Single Leg



3101653

Nano-Lok[™] Wrap Back

8 ft. (2.4 m) twin-leg tie-back type lifelines with 3/4 in. (19 mm) wide Dyneema® fiber web and tie-back snap hook. Quick connector for harness mounting.

3101654 Single Leg

3M[™] DBI-SALA[®] Nano-Lok[™] Arc Flash Self-Retracting Lifelines



Designed specifically for utility applications.

- 8 ft. (2.4 m) working length.
- With Nomex®/Kevlar® fiber web lifeline and reinforced edges for improved wear resistance and durability over standard webbing.
- Features an arc flash industry logo to easily identify the product application.
- Arc flash compliant, tested to 40 cal/cm². Meets ASTM F887.

3101655

Nano-Lok[™] for Aerial Work Platforms

4.5 ft. (1.4 m)
lifeline with
3/4 in. (19 mm)
Nomex®/Kevlar® fiber
web and aluminum
carabiner. Quick
connector for
harness mounting.



3101656

Nano-Lok[™] for Aerial Work Platforms

3.5 ft. (1.1 m) lifeline with 3/4 in. (19 mm) Nomex®/Kevlar® fiber web and aluminum carabiner, swiveling anchor loop with 13 in. (35 mm) web extension and aluminum snap hook.



C

3M[™] DBI-SALA[®] Nano-Lok[™] Arc Flash Self-Retracting Lifelines





3101526

Nano-Lok[™] Arc Flash Self-Retracting Lifeline

3/4 in. (19 mm) Nomex®/Kevlar® fiber webbing and steel snap hook, quick connector for harness mounting x 8 ft. (2.4m).



3101575

Nano-Lok™ Arc Flash Self-Retracting Lifeline

3/4 in. (19 mm) Nomex®/Kevlar® fiber webbing and aluminum carabiner, swiveling anchor loop with 13 in. (33mm) web extension with aluminum snap hoox x 8 ft. (2.4m). Best seller for bucket truck applications.



3101536

Nano-Lok™ Arc Flash Twin-Leg Self-Retracting Lifeline

3/4 in. (19 mm) Nomex®/Kevlar® web and steel rebar hooks, quick connector for harness mounting x 8 ft. (2.4m).



3101574

Nano-Lok™ Arc Flash Self-Retracting Lifeline

3/4 in. (19 mm) Nomex®/Kevlar® fiber webbing and web loop, swiveling anchor loop with 13 in. (33mm) web extension with aluminum snap hoox x 8 ft. (2.4m).

3M™ DBI-SALA® Nano-Lok™ Arc Flash Self Retracting Lifeline Selection Guide:

| | | Α | nchor | age ty | /pe | | | | | ifeline ho | ok | | | | |
|------------------|-----------------------|-------------------------|-----------------------|-----------------|----------------------------------|--------------------|------------------------------|--------------------------|--|--------------------------------------|------------------------|---|------------------------|--------------|----------------|
| | | 9 | | 0 | | 000 | 0 | | Q | 8 | 9 | 0 | 8 | | |
| CMO A | Single-Leg Connect | Single-Leg Interface | Twin-Leg Interface | Steel Carabiner | Web Leg w/ Aluminum Snap Hook | Steel Snap Hook | Steel Swiveling Snap Hook | Flat Steel Rebar Hook | Steel Rebar Hook with Locking Nose | Aluminum Captive Eye Carabiner | Aluminum Rebar Hook | Aluminum Rebar Hook with Locking Nose | Dielectric Web Loop | 11' Tie-Back | Part Number |
| | | • | | | | • | | | | | | | | | 3101526 |
| | | | | | | | | | | | | | | | 3101527 |
| | | • | | | | | | • | | | | | | | 3101528 |
| Leg | | | | | | | | | • | | | | | | 3101529 |
| gle | | | | | | | | | | • | | | | | 3101530 |
| 8 ft. Single Leg | | | | | | | | | | | | | | | 3101531 |
| 8 | | | | | | | | | | | | | | | 3101532 |
| | | | | - | | | | | | | | | | | 3101533 |
| | | | | | | | | | | | | | | - | 3101562 |
| | | | | | | | | | | | | | | - | 3101563 |
| | | | | | | - | | | | | | | | | 3101534 |
| | | | - | | | | | | | | | | | | 3101535 |
| Leg | | | - | | | | | | | | | | | | 3101536 |
| 6 ft. Twin Leg | | | | | | | | | | _ | | | | | 3101537 |
| f. T | | | | | | | | | | | _ | | | | 3101538 |
| 9 | | | | | | | | | | | | _ | | | 3101539 |
| | | | | | | | | | | | | | | | 3101540 |
| | | | • | | | | | | | | | | | - | 3101565 |
| Z Ck | | | | | | | | | | _ | | | | | 3101574 |
| Bucket Truck | | | | | | | | | | - | | | | | 3101575 |
| Buck | _ | | | | | | | | | | | | | | 3101656 |
| | | | | | | | | | | | | | | | 3101655 |

3M[™] DBI-SALA[®] Nano-Lok[™] for Hot Work Use Self-Retracting Lifelines



This SRL was tested to 8 calories, ensuring durability in applications like welding, grinding and torching. It is reinforced with Kevlar® fiber to withstand sparks, weld splatter and other high-heat exposure.

- 6 ft. (1.8 m) working length.
- Universal hot work icon to quickly and easily identify hot work product.
- 3M™ Connected Safety ID (CSID) equipped.



Selection guide:

| | | Anc | horage | type | | | | Lifelin | ie hook | | | | |
|------------|------------|-----------|-----------------------|--------------------|--------------------|---------------------------------|-----------------------------|---|--------------------------------------|------------------------|--|-------------|----------------|
| | | | | 0 | 8 | 0 | Q. | | 8 | Q. | | | |
| 8 | Single-Leg | Interface | Twin-Leg Interface | Steel Carabiner | Steel Snap Hook | Steel Swiveling Snap Hook | Flat Steel Rebar Hook | Steel Rebar Hook with Loking Nose | Aluminum Captive Eye Carabiner | Aluminum Rebar Hook | Aluminum Rebar Hook with Locking Nose | 9' Tie-Back | Part Number |
| | Ŀ | | | | - | | | | | | | | 3101491 |
| | ' | | | | | | | | | | | | 3101492 |
| | | | | | | | | | | | | | 3101493 |
| - 0 | | | | | | | | | | | | | 3101494 |
| | | | | | | | | | | | | | 3101495 |
| ö | | | | | | | | | | | | | 3101496 |
| ò | | | | | | | | | | | - | | 3101497 |
| | | | | | | | | | | | | | 3101498 |
| | Ŀ | | | | | | | | | | | | 3101322 |
| | | | | | | | | | | | | - | 3101324 |
| | | | | | • | | | | | | | | 3101499 |
| | | | | | | | | | | | | | 3101500 |
| 8 | <u>ה</u> | | | | | | | | | | | | 3101501 |
| - | | | | | | | | | | | | | 3101502 |
| T of the L | | | | | | | | | = | | | | 3101503 |
| 0 | | | • | | | | | | | | | | 3101504 |
| | | | | | | | | | | | • | | 3101505 |
| | | | | | | | | | | | | | 3101326 |



3M[™] DBI-SALA[®] Sealed-Blok[™] Self-Retracting Lifeline

Grease, dirt and moisture are just part of your job. Keeping them from affecting the performance of your SRL is ours. These sealed SRLs are constructed from heavy-duty, corrosion-resistant materials, and incorporate a patented concept that separates all dynamic components—including the motor spring and brake—from foreign elements.

1 Carrying handle

Built-in design for transport—certified as secondary fall arrest rated anchorage point.

2 Galvanized & stainless steel cable

Abrasion resistant and corrosion-resistant lifeline options.

3 Self-locking swivel hook

- · Limits lifeline twisting
- Integrated impact indicator
- 3,600 lb. gate reduces accidental disengagements ("roll-out")

4 Fast Line

Provides the user with ability to replace the lifeline in the field.

5 Pivoting anchorage loop

Centers the load.

6 Aluminum housing

Provides exceptional strength durability and corrosion resistance.

7 Aluminum cast cover



3M[™] DBI-SALA[®] Sealed-Blok[™] Self-Retracting Lifelines



Sealed-Blok™ SRL



Automatic Rescue/
Descent Sealed-Blok™



Sealed-Blok™ SRL with Retrieval



Sealed-Blok™ SRL with Magnetic Retraction Control

Product selection guide

| | Lifeline material | Hook material | Includes mounting bracket | Retrieval capability | RSQ capacity | 310 lb. (141 kg) weight capacity | 420 lb. (189 kg) weight capacity | Magnetic Retraction. | 15 ft. (4.5 m) | 30 ft. (9.1 m) | 50 ft. (15.2 m) | 85 ft. (25.6 m) | 130 ft (39.6 m) | 175 ft. (53.3 m) |
|-----------|-----------------------|---------------|------------------------------|-------------------------|--------------|-------------------------------------|-------------------------------------|-------------------------|-------------------|-------------------|--------------------|--------------------|--------------------|---------------------|
| | | | | | | | | | 3400825 | 3400800 | | | | |
| | | | | | | | | | | | 3400900 | 3400860 | 3400965 | 3400650 |
| | able | | | | | | | | | 3400850 | | | | |
| | Galvanized cable | Steel | | | | | | | | | 3400920 | 3400870 | 3400975 | 3400660 |
| | /aniz | ŭ | | | | | | | | | 3400940 | 3400910 | | |
| | Gal | | | | | | | | | | 3400930 | 3400885 | 3400990 | |
| | | | | | | | | | | 3400853 | | | | |
| ISN | | | • | | | | • | | | | 3400923 | 3400871 | 3400976 | |
| OSHA/ANSI | | | | | | | | | | | 3400846 | | | |
| os | | | | | | | | | 3400827 | 3400802 | | | | |
| | <u>e</u> | | | | | | | | | | 3400902 | 3400862 | 3400967 | 3400652 |
| | | | | | | | | | | | 3400932 | 3400886 | 3400991 | |
| | | | | | | | | | | 3400852 | | | | |
| | Stainless steel cable | | | | | | | | | | | 3400874 | 3400979 | 3400661 |
| | | | | | | | | | | | 3400942 | 3400912 | | |
| | | | | | | | | | | 3400858 | | | | |
| | | | • | | | | | | | | 3400942 | 3400882 | 3400987 | |

Other models available; please contact us.

3M™ DBI-SALA® Fast Line Cable Replacement Assemblies



3900105

Galvanized Cable with Plated Hook

Fast Line Galvanized Replacement Cable Assembly x 50 ft. (15 m)

3900105 50 ft. (15 m)

3900108 85 ft. (25.5)

3900112 130 ft. (39 m)

3900107

Stainless Steel Cable with Stainless Steel Hook

Fast Line Stainless Steel Replacement Cable Assembly x 50 ft. (15 m)

3900107 50 ft. (15 m)

3900111 85 ft. (25.5 m)

3900114 130 ft. (39 m)

3M[™] DBI-SALA[®] Ultra-Lok[™] Self-Retracting Lifelines

Stainless steel components, an anti-ratcheting brake system and a semi-sealed design.

- 1 Top swivel
 Limits lifeline twisting.
- 2 Thermoplastic housing
- 3 Ergonomic cable handle
- 4 Multiple lifeline options

 Galvanized or stainless steel cable, nylon or Nomex®/Kevlar® web, or Vectran™ rope for ultimate jobsite flexibility.
- 5 Self-locking swivel hook Limits lifeline twisting.
- 6 Impact indicator
 Provides visual indication of fall arrest.
- 7 3,600 lb. gate

 Reduces chances of accidental disengagement ("roll-out").



3M[™] DBI-SALA[®] Ultra-Lok[™] Self-Retracting Lifelines

Like our Sealed-Blok[™], the Ultra-Lok[™] Lifeline also extends and retracts, so you can move about freely at normal speeds within a recommended working area. Should a fall occur, a speed-sensing brake system will activate, stopping the fall and reducing the imposed forces to 900 lbs. (4 kN) AAF.



3504500

Ultra-Lok™ Leading Edge SRL

This design incorporates larger diameter 30 ft. (9.1 m) of 7/32 in. cable and an in-line shock absorber for the demands of leading edge applications.

3504505

Ultra-Lok™ RSQ SRL

50 ft. RSQ Automatic Rescue/Descent SRL with 3/16 in. (5 mm) galvanized steel wire rope with swivel snap hook.



3504480

Ultra-Lok™ Self-Retracting Lifeline 1/4" (6 mm) Vectran Synthetic

Rope with Swivel Snap Hook.

3501102

Ultra-Lok™ Retrieval SRL


50 ft. (15.2 m) of 3/16 in. (5 mm) galvanized steel wire rope with emergency retrieval winch, mounting bracket, swiveling snap hook and anchorage carabiner.

3M™ DBI-SALA™ Ultra-Lok™ Self-Retracting Lifelines

| | | | | | | | - 3 | | | | | | | |
|-------------------|-----------------|---------------------------|-------------------------------|-------------|--------------|-----|-------------------------------|-------------------|-------------------|-------------------|-------------------|--------------------|--------------------|------------------|
| Lifeline material | Hook style | Hook throat size (in.) | Rated gate capacity (lbs.) | Swivel hook | Leading edge | RSQ | SRL weight capacity (lbs.) | 15 ft. (4.6 m) | 20 ft. (6.1 m) | 30 ft. (9.1 m) | 35 ft. (9.1 m) | 50 ft. (10.6 m) | 55 ft. (16.7 m) | 85 ft. (26 m) |
| | Steel carabiner | 5/8 | 3,600 | | | | 310 | | 3504445 | 3504446 | | 3504463 | | |
| Galvanized | Steel hook | 5/8 | 3,600 | | | | 310 | 3504422 | | 3504500 | | | 3504600 | |
| cable | | 3/4 | 2.000 | • | | • | 310 | | | | | 3504550 | | |
| | | 3/4 | 3,600 | • | | | 310 | | 3504433 | | | 3504450 | | 3504485 |
| Stainless | Stainless steel | 2/4 | 2.000 | - | | • | 310 | | | | | 3504552 | | |
| | | 3/4 | 3,600 | • | | | 310 | | 3504437 | 3504432 | | 3504452 | | 3504487 |
| Vectran rope | Steel hook | 3/4 | 3,600 | | | | 310 | | | | 3504453 | 3504480 | | |
| Retrieval SRLs | Galvanized | 3/4 | 2.000 | | | | 310 | | | | | 3501102 | | |
| | Stainless Steel | 3/4 | 3,600 | | | | 310 | | | | | 3501103 | | |

Other Models available, contact 3M Fall Protection

3M™ DBI-SALA™ Smart Lock **Self-Retracting Lifelines**





Built-in handle

Designed for easy transport and support during overhead installation.

Magnetic retraction control

The lifeline rewinds at an evenly controlled pace, helping reduce the possibility for harm to people or equipment (compared to solutions with gearbased retraction).



Patent pending dual label system

An extra label stored in the bumper on the lifeline allows users to easily access critical asset information and keeps it protected from damage to help reduce cost of ownership.




Highly-visible orange energy-absorber cover

Identifies product as meeting Leading Edge standards and allows you to more easily confirm that workers are tied off (Horizontal models).



420 lb. weight capacity



Horizontal

(Leading Edge)



Fewer sudden stops

Enhanced testing programs were performed during the design and qualification of this product to reduce unintentional lockups. Compared to our existing devices the new Smart Lock SRL locked up 29% less when tested against 422 work motion profiles.









Complies with OSHA 1910.140 General Industry

Helps protect general industry workers up to 310 lbs. from falls when working with as little as 4 ft. of fall clearance.

3M[™] DBI-SALA[®] Smart Lock Self-Retracting Lifelines



3503800

Smart Lock SRL – Vertical 30 ft. Galvanized Steel lifeline.

3503822

Smart Lock SRL – Horizontal Leading Edge 30 ft. Galvanized Steel lifeline.



3503805

Smart Lock SRL – Vertical Arc Flash 20 ft. Rope.

3503848

Smart Lock SRL – Horizontal Modular Works with D-ring extensions.

Learn more about the 3M™ DBI-SALA® Smart Lock Leading Edge SRL and Modular Connector. See page 67.

3M™ DBI-SALA® Smart Lock Self-Retracting Lifelines

| Application | Part # | Length | Lifeline Material | | | | |
|---------------------------|--|----------------|-------------------|--|--|--|--|
| | 3503803 | 20 ft. | Galvanized Steel | | | | |
| | 3503804 | 3503804 20 ft. | | | | | |
| | 3503800 | 30 ft. | Galvanized Steel | | | | |
| Vertical (Overhead) | 3503801 | 30 ft. | Stainless Steel | | | | |
| vertical (Overnead) | 3503820 | 35 ft. | Rope | | | | |
| | 3503821 | 35 ft. | Stainless Steel | | | | |
| | 3503824 | 50 ft. | Galvanized Steel | | | | |
| | 3503823 | 50 ft. | Stainless Steel | | | | |
| Havinantal (Landing Edga) | 3503802 | 20 ft. | Galvanized Steel | | | | |
| Horizontal (Leading Edge) | 3503822 | 30 ft. | Galvanized Steel | | | | |
| Arc Flash (Overhead) | Arc Flash (Overhead) 3503805 20 ft. Rope | | | | | | |

3M™ DBI-SALA® Smart Lock Leading Edge SRL and Modular Connector

| Application | Part # | Length | Description |
|---------------------------|---------|--------|---|
| Horizontal (Leading Edge) | 3503848 | 30 ft. | 3M™ DBI-SALA® Smart Lock Leading Edge SRL with D-Ring Ext. |
| with D-ring Extension | 1246500 | 14 in. | 3M [™] DBI-SALA [®] EZ Stop [™] LE Shock Pack for Modular Connector SRL |

3M[™] DBI-SALA[®] Nano-Lok[™] Extended Length Self-Retracting Lifelines

We're advancing the versatility of 3M™ DBI-SALA® Nano-Lok™ SRLs. Available in 9 ft., 11 ft., 15 ft. and now 20 ft. lengths, the family of Nano-Lok™ SRLs combines fall protection with ease-of-use and comfort for even more applications.

- Swiveling anchorage loop limits lifeline twisting.
- Thermoplastic housing designed to withstand demanding worksites.
- As low as 6 ft. of required fall clearance.
- Dyneema® Fiber and Polyester Web Lifeline reduces overall weight and the retractable design provides freedom of movement.
- External energy absorber maintains safe fall arrest forces for users (and tools) up to 420 lbs. (190 kg)
- Impact indicator provides a visual alert that the SRL has been involved in a fall.



3M™ DBI-SALA® Nano-Lok™ XL Self-Retracting Lifelines

| Lifeline Material | Length | Connector | Anchor Mount | Part # |
|--------------------------|--------|---|---------------------------------|---------|
| Kevlar® | 11 ft. | Swiveling Steel Snap Hook | Steel Carabiner | 3101684 |
| Dyneema® | 20 ft. | Steel Snap Hook | Steel Carabiner | 3103865 |
| Dyneema® | 20 ft. | Swiveling Steel Snap Hook | Steel Carabiner | 3103866 |
| Dyneema® | 20 ft. | Aluminum Carabiner | Aluminum Carabiner | 3103872 |
| Dyneema® | 20 ft. | Swiveling Stainless Steel Snap Hook | Stainless Steel Carabiner | 3103873 |
| Galvanized Cable | 15 ft. | Swiveling Steel Snap Hook | Steel Carabiner | 3501694 |
| Stainless Steel Cable | 15 ft. | Swiveling Stainless Steel Snap Hook | Steel Carabiner | 3501695 |



Protecta[®] Rebel[™] **Leading Edge Self-Retracting** Lifelines

Lightweight, Durable and Affordable

The leading edge cable unit leverages our impressive Rebel technologies to continue to set the standard for performance and value.

| Part # | 3590540 | 3590543 | 3590546 | 3590548 |
|---------------|------------------|------------------|------------------|------------------|
| Cable Length | 20 ft. | 33 ft. | 50 ft. | 66 ft. |
| LxWxH | 42" x 10" x 4.5" | 42" x 11" x 4.5" | 46" x 13" x 5.5" | 46" x 13" x 5.5" |
| Weight | 17 lbs | 19 lbs | 25 lbs | 26 lbs |
| *Cover Part # | 3590010 | 3590011 | 3590012 | 3590012 |





Fully integrated into lifeline. Specifically designed for foot level tie-off.

Standards

OSHA 1926.502, OSHA 1910.66, ANSI Z359.14.

310 lb. (141 kg) capacity and 1,350 lbs. (6kn) maximum arresting force.

All solutions adhere to ANSI Z359.14 leading and sharp edge requirements.

3M™ Protecta® Personal Self-Retracting Lifelines

1 Swiveling top anchor

Helps prevent lifeline twisting and reduces wear on web lifeline.

2 Triple action carabiner

Simplifies connection to anchor point or harness.

3 Impact resistant

Thermoplastic housing is lightweight, compact and durable.

4 Heat-shrunk

Clear PVC coating over EVA foam label on shock pack improves durability.

5 High strength webbing

Designed to accomodate users up to 310 lbs.

6 Fully compliant

Self-locking snap hook meets ANSI Standards with a 3,600 lb. rated gate.

> Model shown 3100477



Product selection guide

Singleleg



Twin-leg

R

3100403

6 ft. (1.8 m) of 1 in. (2.5 cm) polyester web with steel snap hook, swiveling anchorage and carabiner.

3100404

6 ft. (1.8 m) of 1 in. (2.5 cm) polyester web with steel swiveling snap hook, swiveling anchorage and carabiner.

3100405

6 ft. (1.8 m) of 1 in. (2.5 cm) polyester web with steel rebar hook, swiveling anchorage and carabiner.

3100477

6ft (1.8m) of 1 in. (2.5 cm) polyester web with aluminum rebar hook, swiveling anchorage and carabiner.

3100412

6 ft. (1.8 m) twin-leg with 1 in. (2.5 cm) polyester web and steel snap hooks, quick connector for harness mounting.

3100413

6 ft. (1.8 m) twin-leg with 1 in. (2.5 cm) polyester web and steel swiveling snap hooks, quick connector for harness mounting.


3100414

6 ft. (1.8 m) twin-leg with 1 in. (2.5 cm) polyester web and steel rebar hooks, quick connector for harness mounting.

3100476

6ft (1.8m) twin-leg with 1 in. (2.5 cm) polyester web with aluminum rebar hooks, quick connector for harness mounting.

Example fall clearance requirements of our 6 ft. SRL vs. lanyard of similar length



How to choose the right SRL

1. Anchor location

Not all SRLs are the same. SRLs designed for anchoring at foot-level are different than those meant for overhead anchorage.

2. Lifeline material

Galvanized and stainless steel increase durability and dependability, while web is lighter for personal use.

3. Length

Select a length that will allow maximum mobility while still arresting your fall at a safe distance.

4. Hook options

A variety of hook options help you to be flexible on the job when tying off to fall arrest rated anchor points.

Product selection guide

| Lifeline Material | Thermoplastic Housing | Aluminum Housing | Stackable | Impact Indicator | Swiveling Anchorage | Self-Locking Snap Hook | Rebar Hook | Swiveling Hook | Leading Edge (foot level, sharp edge use) | Twin-Leg | 310 lb. (140 kg) Weight Capacity | 420 lb. (190 kg) Weight Capacity | 6 ft. (1.8 m) | 11 ft. (3.3 m) | 15 ft. (4.5 m) | 20 ft. (6 m) | 33 ft. (10 m) | 50 ft. (15 m) | 66 ft. (20 m) | 85 ft. (26 m) | 100 ft. (30 m) |
|-------------------|-----------------------|------------------|-----------|------------------|---------------------|------------------------|------------|----------------|---|----------|----------------------------------|----------------------------------|----------------------|--------------------|---------------------|-----------------------|-----------------------|---------------------|---------------------|---------------------|---------------------|
| | | | | | - | | | • | | • | • | | 3590015 | 3590016 | 3590019 | , , | | , , , | | , , | , |
| <u>e</u> | ١. | | | | - | | | | | | - | | | | 3590018 | | | | | | |
| d cak | | | • | • | - | • | | • | | | | • | | | | 3590517 | 3590500 | 3590550 | 3590590 | 3590630 | 3590670 |
| Galvanized cable | | • | • | | - | - | | • | | | | • | | | | 3590514 | 3590510 | 3590560 | 3590600 | 3590640 | 3590680 |
| Galv | | | - | • | - | - | | • | • | | - | | | | | 3590540 | 3590543 | 3590546 | 3590548 | | |
| | • | | | | - | - | • | | | | - | | | | 3590020 | | | | | | |
| able | • | | • | | - | - | | • | | | | • | | | | 3590504 | 3590501 | 3590551 | 3590591 | 3590631 | 3590671 |
| SS cable | | - | • | • | - | - | | • | | | | • | | | | 3590509 | 3590511 | 3590561 | 3590601 | 3590641 | 3590681 |
| | • | | | | - | • | | | | | • | | 3100403 | 3100425 | | 3100431 | | | | | |
| | • | | | | - | - | | • | | | - | | 3100404 | 3100426 | | 3100432 | | | | | |
| Web | • | | | | - | - | - | | | | - | | 3100405 | 3100427 | | 3100433 | | | | | |
| 3 | Ŀ | | | | - | • | | | | - | - | | 3100412 | | | | | | | | |
| | Ŀ | | | | • | • | | • | | - | - | | 3100413 | | | | | | | | |
| | Ŀ | | | | • | • | • | | | • | • | | 3100414 | | | | | | | | |
| | Weight | | | | | | ight | Varies | Varies | Varies | Varies | 13.5 lb. (6.1 kg) | 17.3 lb. (7.8 kg) | 22 lb. (10 kg) | 28.6 lb. (13 kg) | 29.5 lb. (13.4 kg) | | | | | |
| | | | | | | | | Ap | prox | imat | te de | pth | 2 in. (5 cm) | 3 in. (8 cm) | 3 in. (8 cm) | 4.6 in. (12 cm) | 4.6 in. (12 cm) | 4.6 in. (12 cm) | 5.5 in. (14 cm) | 5.5 in. (14 cm) | 5.5 in. (14 cm) |
| | | | | | | | | Aı | pprox | kima | te wi | idth | 3.5 in. (8.9 cm) | 6 in. (15 cm) | 6 in. (15 cm) | 9.8 in. (14 cm) | 9.8 in. (24.9 cm) | 11 in. (28 cm) | 12.8 in. (33 cm) | 12.8 in. (33 cm) | 12.8 in. (33 cm) |
| | | | | | | | | App | roxii | nate | heig | ght* | 19 in. (48 cm) | 19 in. (48 cm) | 29 in. (74 cm) | 22.5 in. (57.1 cm) | 22.5 in. (57.1 cm) | 23.8 in. (61 cm) | 25.7 in. (65 cm) | 25.7 in. (65 cm) | 25.7 in. (65 cm) |

*Anchor point to anchor point

Standards: Meets OSHA 1926.502, OSHA 1910.140, ANSI Z359.14, ANSI 2359.12, ANSI A10.32, CSA Z259.2.2 Type II

3M[™] Protecta®

Self-Retracting Lifelines

33 ft. (10 m) SRL 3590500

3/16 in. (5 mm) galvanized steel wire rope with swiveling snap hook, thermoplastic housing and anchorage carabiner.



11 ft. (3.3 m) SRL 3100427

1 in. (2.5 cm) polyester web with steel rebar hook, swiveling anchorage and carabiner.



20 ft. (6.1 m) SRL 3100432

1 in. (2.5 cm) polyester web with steel swiveling snap hook, swiveling anchorage and carabiner.



15 ft. (4.5 m) SRL 3590019

3/16 in. (5 mm) galvanized steel wire rope with steel swiveling snap hook, swiveling anchorage and carabiner.



11 ft. (3.3 m) SRL 3100425

1 in. (2.5 cm) polyester web with steel snap hook, swiveling anchorage and carabiner.



11 ft. (3.3 m) SRL 3100426

1 in. (2.5 cm) polyester web with steel swiveling snap hook, swiveling anchorage and carabiner.



3M™ Protecta®

Self-Retracting Lifeline Covers

Self-Retracting Lifeline Cover (20-33 ft.) 3590010

Vinyl cover with hook and loop closure, for use with 20-33 ft. standard cable and 20 ft. leading-edge models.

Self-Retracting Lifeline Cover (50 ft.) 3590011

Vinyl cover with hook and loop closure, for use with 50 ft. standard cable and 33 ft. leading-edge models.

Self-Retracting Lifeline Cover (66-100 ft.) 3590012

Vinyl cover with hook and loop closure, for use with 66-100 ft. standard cable and 50-66 ft. leading edge models.



OSHA Final Rule on Walking-Working Surfaces


This new rule applies to all general industry workplaces, covering surfaces like floors, stairs, ladders, scaffolds and elevated walkways. The goal is to reduce slips, trips and falls across several industries. This rule increases consistency between the general industry and construction standards. Compliance dates vary to give businesses time to understand the changes and upgrade their equipment. See our Technical Bulletin or contact customer service for more information.


OSHA 29 CFR 1910.140

If workers use personal fall protection or work in other high hazard situations, they must be trained and retrained in a manner they understand.




KEY CHANGE:





Fixed ladder cages and wells will be phased out and replaced with ladder safety systems or personal fall arrest systems.

KEY CHANGE:



Outdoor advertising qualified climbers will need fall protection, and fixed ladders over 24 ft. will require a ladder safety system.

KEY CHANGE:



Fall protection D-rings, carabiners and snap hooks must be proof tested for tensile loads of 3,600 lbs, and gate strengths must also be designed to withstand at 3,600 lbs.

Learn more about this and other safety standard updates at 3M.com/FallProtection.

3M[™] DBI-SALA[®] Shock-Absorbing Lanyards

Meeting industry standards.

When you place your trust in a 3M[™] DBI-SALA® Lanyard, you can depend on the fact that every one meets rigorous industry safety standards, including OSHA 29 CFR 1926.502, 1910.140 and ANSI/ASSP Z359.13.

Choosing a lanyard

Look for these features when selecting a lanyard.

A. Webbing

Choose your webbing based on the type of conditions you work in. Options include Nomex®/Kevlar® with fiber, polyurethane-coated and cable.

B. Impact indicators

Impact indicators let you know if a shock absorber has been involved in a fall, so you can remove it from service.

C. Connector/hook

3M™ DBI-SALA® Snap Hooks allow one-handed use and won't pinch thumbs or fingers.

D. Lenath

The standard lanyard length is 6 ft (1.8 m), but other lengths are available.

E. Shock absorber

Most shock absorbers keep forces below 900 lbs. (4 kN) AFF and are available in pack or tubular styles.



Types of 3M™ DBI-SALA® Snap Hooks

All of our lanyards feature 3,600 lb. (16 kN) rated gates.























| | | | _ | | | | _ | _ | | _ | |
|----------|--------------------|-----------------------|---------------------------|-----------------------------|---|--------------------------------------|---|--|-------------------|-----------------------|----------------------|
| | Steel Snap Hook | Aluminum Snap Hook | Aluminum Rebar Hook | Flat Steel Rebar Hook | Saflok [™] Max Steel Rebar Hook | Saflok [™] Tower Hook | Aluminum Rebar Hook with Locking Nose | Steel Rebar Hook with Locking Nose | Wrap Back Hook | Tie-Back Carabiner | Comfort Grip Hook |
| Gate | 3/4 in. | 3/4 in. | 2-1/4 in. | 2-1/2 in. | 3 in. | 4-5/16 in. | 2-1/2 in. | 2-1/2 in. | 3/4 in. | 3/4 in. | 2-1/4 in. |
| Opening | (19 mm) | (19 mm) | (57 mm) | (62.5 mm) | (76.2 mm) | (116.84 mm) | (62.5 mm) | (62.5 mm) | (19 mm) | (19 mm) | (57 mm) |
| Gate | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. | 3,600 lb. |
| Strength | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) | (16 kN) |

3M[™] DBI-SALA[®] Shock-Absorbing Lanyards

Types of Lanyards



Pack-Style Shock-Absorbing Lanyards

These lanyards dissipate energy, limiting the forces on the body in a fall arrest event.



Tubular-Style Shock-Absorbing Lanyards

These lanyards are available in both fixed length and "stretch" style designs.



Twin-Leg Lanyards

Twin-Leg lanyards provide 100% tie-off, allowing users to stay protected when changing locations.



Positioning Lanyards

Designed without shock absorbers for positioning or restraint applications only.



Tie-Back Lanyards

Tie-Back lanyards act as both a connecting means and an anchorage connector when a qualified anchorage connector is not available.



Lanyards for Arc Flash and Hot Work Use

These lanyards are designed with Kevlar® fiber for use in high temperatures or applications requiring arc flash protection.



Lanyards for Foot-Level Tie-Off

Used at the feet, these lanyards allow a 12 ft. (3.7 m) free fall and maintain forces below 1,800 lbs. (8 kN) MAF.



Fall-Restricting Device

Clinches around a wood pole during "cut outs" to help prevent users from falling and allowing them to regain footing.

3M™ DBI-SALA® ShockWave™ 2

Shock-Absorbing Lanyards

Avoid trips and snags with lanyards that expand and contract (6 ft.-4-1/2 ft.) in reaction to movement. They have a built-in impact indicator and limit the average fall arresting forces to 900 lbs. (4 kN)





| Part # | Single-Leg/ Hook 1 (Harness) Twin-Leg Material/Style | | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|---------|--|---------------|-----------------------------------|-----------------------------------|
| 1244306 | Single | Steel/Snap | Steel/Snap | - |
| 1244311 | Single | Aluminum/Snap | Aluminum/Rebar Locking Nose | - |
| 1244321 | Single | Steel/Snap | Steel/Rebar Locking Nose | - |
| 1244360 | Single | Steel/Snap | Steel/Saflok™ Max Rebar | - |
| 1244406 | Twin | Steel/Snap | Steel/Snap | Steel/Snap |
| 1244409 | Twin | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |
| 1244412 | Twin | Steel/Snap | Steel/Rebar Locking Nose | Steel/Rebar Locking Nose |

All lanyards are 6 ft. long unless otherwise noted.

3M[™] DBI-SALA® **Shock-Absorbing Lanyards**

3M™ DBI-SALA® ShockWave™ 2

Shock-Absorbing Lanyards

Rescue Lanyards

These lanyards incorporate an integrated D-ring to help facilitate the rescue of a fallen worker.



Arc Flash Lanyards

Constructed from materials, these lanyards have Nomex®/Kevlar® fiber and are great for high heat environments or for electrical work when arc flash is a concern. Meets arc requirements of ASTM F887.



1244610

Tie-Back Lanyards

When a qualified anchorage connector is not available, a tie-back lanyard acts as both a connecting means and an anchorage connector.



1244650

Selection guide:

| Part # | Туре | Single-Leg/ Twin-Leg | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|---------|-------------|-------------------------|------------------------------------|--|--|
| 1244456 | Rescue | Twin | Steel/Snap, D-ring | Steel/Rebar Locking Nose | Steel/Rebar Locking Nose |
| 1244750 | Rescue | Twin | Steel/Snap | Steel/Rebar Locking Nose, D-ring | Steel/Rebar Locking Nose, D-ring |
| 1244455 | Rescue | Twin | Steel/Snap, D-ring | Steel/Snap | Steel/Snap |
| 1244459 | Rescue | Twin | Steel/Snap, D-ring | Steel/Saflok™ Max Rebar | Steel/Saflok™ Max Rebar |
| 1244751 | Rescue | Twin | Aluminum/Snap | Aluminum/Rebar Locking Nose, D-ring | Aluminum/Rebar Locking Nose, D-ring |
| 1244610 | Arc Flash 🛕 | Single | Steel/Snap | Steel/Snap | - |
| 1244611 | Arc Flash 🛕 | Single | Web Choker | Steel/Snap | - |
| 1244630 | Arc Flash 🛕 | Twin | Steel/Snap | Steel/Snap | Steel/Snap |
| 1244631 | Arc Flash 🛕 | Twin | Web Choker | Steel/Snap | Steel/Snap |
| 1244632 | Arc Flash 🛕 | Twin | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |
| 1244639 | Arc Flash 🛕 | Twin | Aluminum/Snap | Steel/Saflok™ Max Rebar | Steel/Saflok™ Max Rebar |
| 1244650 | Tie-Back | Single | Steel/Snap | Steel/Tie-back Carabiner | - |
| 1244675 | Tie-Back | Twin | Steel/Snap | Steel/Tie-back Carabiner | Steel/Tie-back Carabiner |

3M™ DBI-SALA® **Shock-Absorbing Lanyards**

3M™ DBI-SALA® Force™ 2

Foot-Level Tie Off Shock-Absorbing Lanyards

Selection guide:

Great for when there is no overhead anchorage and your only option is to tie off at your feet. These lanyards can be used for up to a 12 ft. (3.7 m) free fall and limit the forces below 1,800 lbs. (8 kN) MAF.

| Part # | Single-Leg/ Twin-Leg | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|---------|-------------------------|--------------|------------------------------------|-----------------------------------|-----------------------------------|
| 1246143 | Twin | Web, Elastic | Steel/Snap | Steel/Saflok™ Max Rebar | Steel/Saflok™ Max Rebar |
| 1246145 | Twin | Web, Elastic | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |
| 1246147 | Twin | Web, Elastic | Steel/Snap | Steel/Snap | Steel/Snap |
| 1246159 | Twin | Web | Steel/Snap | Steel/Rebar Locking Nose | Steel/Rebar Locking Nose |
| 1246161 | Twin | Web | Steel/Snap | Steel/Snap | Steel/Snap |
| 1246167 | Single | Web | Steel/Snap | Steel/Snap | - |
| 1246273 | Twin | Rope | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |

3M[™] DBI-SALA[®] Wrap Back

Tie-Back Lanyards

These lanyards can help eliminate the need for a separate anchorage connector. They offer a unique 5,000 lb. (22 kN) hook and heavy-duty



1246229

| Selection guide | |
|-----------------|--|
|-----------------|--|

| Part # | Single-Leg/ Twin-Leg | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------|-------------------------|-----------------|------------------------------------|-----------------------------------|-----------------------------------|
| 1246075* | Twin | Web | Steel/Snap | Steel/Wrap Back | Steel/Wrap Back |
| 1246080 | Twin | Web | Steel/Snap | Steel/Wrap Back | Steel/Wrap Back |
| 1246173* | Single | Web | Steel/Snap | Steel/Wrap Back | - |
| 1246229 | Single | Web | Steel/Snap | Steel/Wrap Back | - |

^{*}Force[™]2, foot-level tie off.

3M™ DBI-SALA® Force™ 2 Wind Energy

Foot-Level Tie Off Lanyards

Selection guide:



| Part # | Single-Leg/ Twin-Leg | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|---------|-------------------------|-----------------|------------------------------------|-----------------------------------|-----------------------------------|
| 1246030 | Twin | Web, Elastic | Steel/Snap | Steel/Rebar Locking Nose | Steel/Rebar Locking Nose |
| 1246032 | Twin | Web, Elastic | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |
| 1246152 | Twin | Web, Elastic | Steel/Snap | Steel/Saflok™ Max Rebar | Steel/Saflok™ Max Rebar |
| 1246153 | Twin | Web, Elastic | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |

3M™ DBI-SALA® EZ-Stop™ 👍



Leading Edge Shock-Absorbing Lanyards

Selection guide:

Engineered for sharp edges, these lanyards incorporate edge certified cable construction and offer Force™2 foot-level tie-off ability (for maximum 12 ft. free fall).



1246066

| Part # | Туре | Single-Leg/ Twin-Leg | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|---------|--------------|-------------------------|---------------------|------------------------------------|-----------------------------------|-----------------------------------|
| 1246066 | Leading Edge | Single | Cable, Vinyl Coated | Steel/Snap | Steel/Snap | - |
| 1246068 | Leading Edge | Twin | Cable, Vinyl Coated | Aluminum/Snap | Aluminum/Snap | Aluminum/Snap |
| 1246178 | Leading Edge | Twin | Cable, Vinyl Coated | Aluminum/Snap | Aluminum/Rebar Locking Nose | Aluminum/Rebar Locking Nose |
| 1246261 | Leading Edge | Single | Cable, Vinyl Coated | Steel/Snap | Steel/Rebar Locking Nose | - |

3M™ DBI-SALA®

Positioning Web & Rope Lanyards

3M™ DBI-SALA®

Positioning Web & Rope Lanyards

Lanyards without shock absorbers, such as rope or web lanyards are designed for positioning or restraint applications.







Selection guide:

| | | | <u> </u> | | | |
|---------|---------------|--|------------------------------------|---------------------------------------|--|--|
| Part # | Length | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | | |
| 1232354 | 6 ft. (1.8 m) | Rope, Nylon | Steel/Snap | Steel/Snap | | |
| 1232209 | 6 ft. (1.8 m) | Rope, Nylon, Adjustable | Steel/Snap | Steel/Snap | | |
| 1231102 | 2 ft. (0.6 m) | Web | Steel/Snap | Steel/Snap | | |
| 1231103 | 3 ft. (0.9 m) | Web | Steel/Snap | Steel/Snap | | |
| 1231104 | 4 ft. (1.2 m) | Web | Steel/Snap | Steel/Snap | | |
| 1231106 | 6 ft. (1.8 m) | Web | Steel/Snap | Steel/Snap | | |
| 1231016 | 6 ft. (1.8 m) | Web, Adjustable | Steel/Snap | Steel/Snap | | |
| 1234070 | 8 ft. (2.4 m) | Rope, Technora® Kernmantle, Adjustable | Steel/Snap | Steel/Rope Adjuster with Carabiner | | |
| 1234071 | 8 ft. (2.4 m) | Rope, Technora® Kernmantle, Adjustable | Aluminum/Snap | Aluminum/Rope Adjuster with Carabiner | | |
| 1234083 | 8 ft. (2.4 m) | Rope, Technora® Kernmantle, Adjustable | Aluminum/Carabiner | Aluminum/Rope Adjuster with Carabiner | | |
| 1234080 | 8 ft. (2.4 m) | Rope, Technora® Kernmantle, Adjustable | Aluminum/Carabiner | Aluminum/Rope Adjuster with Carabiner | | |

3M™ DBI-SALA®

Chain & Web Rebar Positioning Lanyards

5920059

5920059 Chain Rebar Assembly

With snap hooks and swiveling Saflok™ Max Hook at center x 24 in. (60 cm)

5920050

Chain Rebar Lanyard

Chain rebar assembly with snap hooks and swiveling flat steel rebar hook at center x 1.7 ft. (52 cm)

5920051

Chain Rebar Lanyard

Chain rebar assembly with snap hooks and swiveling aluminum rebar hook at center x 22 in. (56 cm) Made of twist link chain or polyester web for strength and durability. A variety of hook options provide a compatible connection to many types of structures.

1231380

Web Rebar Assembly

With snap hooks and aluminum rebar hook at center x 18 in. (45 cm)

1231389

Web Rebar Lanyard

Web rebar assembly with snap hooks and Saflok Max Hook at center x 22 in. (45 cm)

1231520

Web Rebar Lanyard

Web rebar assembly with snap hooks and swiveling aluminum hook at center x 22 in. (56 cm)



3M™ DBI-SALA® **Fall-Restricting Devices**

3M™ DBI-SALA® Cynch-Lok™

Fall-Restricting Devices

Adjust and cinch around poles during "cut-outs" and hitch-hike poles (move or jump the strap upwards past obstacles) with a hand position consideration. Meets CSA Z259.14 for Type A and AB (dry, wet and icy poles) and ASTM F887.

Selection guide:

| Part # | Description | Pole Size Minimum (Dia./Circ.) | Pole Size Maximum (Dia./Circ.) | Weight |
|---------|--|-----------------------------------|-----------------------------------|-------------------|
| 1200110 | Replacement Strap for Distribution Poles | 5-1/2 in./17-1/2 in. | 18-1/2 in./58 in. | 1.9 lbs. (.86 kg) |
| 1204057 | Rope for Distribution Poles | 5-1/2 in./17-1/2 in. | 18-1/2 in./58 in. | 4.8 lbs. (2.1 kg) |
| 1204075 | Web for Distribution Poles | 5-1/2 in./17-1/2 in. | 18-1/2 in./58 in. | 4.9 lbs. (2.2 kg) |
| 1200111 | Replacement Strap for Transmission Poles | 5-1/2 in./17-1/2 in. | 30-1/2 in./96 in. | 2.4 lbs. (1.1 kg) |
| 1204058 | Rope for Transmission Poles | 5-1/2 in./17-1/2 in. | 30-1/2 in./96 in. | 5.3 lbs. (2.4 kg) |
| 1204076 | Web for Transmission Poles | 5-1/2 in./17-1/2 in. | 30-1/2 in./96 in. | 5.4 lbs. (2.4 kg) |





1200115

Cynch-Lok Replacement Rope Interior Strap

Weight: 2.9 lbs. (1.3 kg)

1200136

Cynch-Lok Replacement Web Interior Strap Weight: 3 lbs. (1.3 kg)

1204077

Cynch-Lok Left Carabiner Conversion Kit—Web

1204074

Cynch-Lok Left Carabiner Conversion Kit—Rope



Compliance and confidence, all at an economical price. 3M™ Protecta® Shock-Absorbing Lanyards are trusted by workers in a wide variety of industries. They feature 3,600 lb. gated hooks, durable lanyard material construction and plated alloy steel hardware for strength and corrosion resistance. All of our shock-absorbing lanyards meet or exceed rigorous OSHA and ANSI industry standards.

3M[™] Protecta[®] Shock-Absorbing Lanyards

1 Reduced impact forces

Built-in energy absorber helps limit fall arresting forces to meet or exceed rigorous OSHA and ANSI industry standards.

2 High strength and capacity

5,000 lb. (22 kN) breaking strength for durability and 310 lb. (140 kg) capacity for worker flexibility.

3 3,600 lb. gated hooks

Every lanyard features 3,600 lb. (16kN) gated hooks.

4 Tough webbing

Polyester construction is strong enough to endure rough use and the elements.

5 Impact indicator

Simplifies inspection for prior fall events.

6 Durable hardware

Alloy steel construction with zinc plating for strength, durability and corrosion resistance.

Various styles and lengths

A variety of styles and lengths are available. Contact customer service for more.

2 5 Model Shown 1340101

Hook options



Standard hook with 3/4 in. (19 mm) gate opening

3,600 lb. (16 kN) gate strength.



Flat steel rebar hook with 2-1/4 in. (57 mm) gate opening

3,600 lb. (16 kN) gate strength.



Tie-back carabiner with 3/4 in. (19 mm) gate opening

5,000 lb. (22 kN) gate strength.

Shock-Absorbing Lanyards

3M™ Protecta®

Shock-Absorbing Lanyards

For general use or bucket truck applications, these lanyards feature durable 1 in. (25 mm) polyester webbing, 1/2 in. (13 mm) nylon rope or 1/4 in. (6 mm) vinyl covered cable with 3,600 lb. (16 kN) gated hooks.



| Part Number | Length | Legs | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------------|--------|--------|-----------------|---------------------------------------|--------------------------------------|--------------------------------------|
| 1341001 | 6' | Single | Web | Steel/ Snap | Steel/ Snap | - |
| 1341004 | 4' | Single | Web | Steel/ Snap | Steel/ Snap | - |
| 1341002 | 3' | Single | Web | Steel/ Snap | Steel/ Snap | - |
| 1342250 | 6' | Twin | Web, Adjustable | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1342275 | 6' | Twin | Web, Adjustable | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |
| 1342001 | 6' | Twin | Web | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1340451 | 6' | Twin | Cable | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1340125 | 6' | Single | Web | Steel/ Snap | Steel/ Rebar | - |
| 1340401 | 6' | Single | Cable | Steel/ Snap | Steel/ Snap | - |
| 1341050 | 6' | Single | Web, Adjustable | Steel/ Snap | Steel/ Snap | - |
| 1340180 | 6' | Twin | Web | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |
| 1340181 | 5' | Twin | Web | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |
| 1340751 | 6' | Twin | Rope | Steel/ Snap | Steel/ Snap | Steel/ Snap |

3M™ Protecta®

Lanyards for Hot Work Use

For welding or metal cutting applications, these lanyards feature heat-resistant Kevlar® fiber webbing, a shock pack and 3,600 lb. (16 kN) gated hooks.

| Part Number | Length | Legs | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------------|--------|--------|-----------------|---------------------------------------|--------------------------------------|--------------------------------------|
| 1340128 | 6' | Single | Kevlar® | Steel/ Snap | Steel/ Rebar | - |
| 1340129 | 6' | Single | Kevlar® | Steel/ Snap | Steel/ Snap | - |
| 1340185 | 6' | Twin | Kevlar® | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |
| 1340187 | 6' | Twin | Kevlar® | Steel/ Snap | Steel/ Snap | Steel/ Snap |



3M™ Protecta®

Tie-Back Shock-Absorbing Lanyards

For applications with no anchor point, these lanyards feature specialized webbing and hardware that withstands the rigors of tie-back use and include 3,600 lb. (16 kN) gated hooks.

1340200 Shown

| Part Number | Length | Legs | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------------|--------|--------|-----------------|---------------------------------------|--------------------------------------|--------------------------------------|
| 1340200 | 6' | Single | Web | Steel/ Snap | Steel/ Snap | - |
| 1340040 | 6' | Single | Web | Steel/ Snap | Tie-back carabiner | - |
| 1342200 | 6' | Twin | Web | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1340060 | 6' | Twin | Web | Steel/ Snap | Tie-back carabiner | Tie-back carabiner |

3M™ Protecta®

Tubular Web Lanyards

For bucket trucks, lifts, and other applications where a lighter lanyard may be advantageous, these lanyards feature polyester tubular web instead of a traditional shock pack and 3,600 lb. (16 kN) gated hooks.

| 1340220 Shown | |
|---------------|--|

| Part Number | Length | Legs | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------------|--------|--------|-----------------|---------------------------------------|--------------------------------------|--------------------------------------|
| 1340220 | 6' | Single | Web, Tubular | Steel/ Snap | Steel/ Snap | - |
| 1340230 | 6' | Single | Web, Tubular | Steel/ Snap | Steel/ Rebar | - |
| 1340240 | 6' | Twin | Web, Tubular | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1340250 | 6' | Twin | Web, Tubular | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |

3M[™] Protecta®

Elastic Shock-Absorbing Lanyards

These lanyards combine the packstyle energy absorber with stretch capabilities, expanding to 6 ft. (1.8 m) and contracting to 4-1/2 ft. (1.4 m). That means optimal mobility while otherwise staying out of the way. The 3,600 lb. (16 kN) gated hooks and an energy absorber design limit fall arresting forces.

| Part Number | Length | Legs | Leg Material | Hook 1 (Harness) Material/Style | Hook 2 (Anchor) Material/Style | Hook 3 (Anchor) Material/Style |
|----------------|--------|--------|-----------------|---------------------------------------|--------------------------------------|--------------------------------------|
| 1341101 | 6' | Single | Web, Elastic | Steel/ Snap | Steel/ Snap | - |
| 1342101 | 6' | Single | Web, Elastic | Steel/ Snap | Steel/ Snap | Steel/ Snap |
| 1342125 | 6' | Twin | Web, Elastic | Steel/ Snap | Steel/ Rebar | Steel/ Rebar |



Shock-Absorbing Lanyards

Part

Number

1340101

1340141

1340121

1340161

Length

6'

6'

6'

6'

Legs

Single

Twin

Single

Twin

3M™ Protecta®

Stretch Shock-Absorbing Lanyards

For vertical climbing applications, these lanyards feature a polyester tubular web that expands to 6 ft. (1.8 m) and contracts to 4-1/2 ft. (1.4 m) in reaction to the worker's movements. Their 3,600 lb. (16 kN) gated hooks and an energy-absorber design limit fall arresting forces.

The state of the s

1340101 Shown

3M[™] Protecta®

Positioning Lanyards

For maintaining a working position in applications such as rebar walls, these lanyards feature 3,600 lb. (16 kN) gated hooks. These devices do not incorporate shock absorbers and can only be used without a fall arrest system if the fall possibility is 2 ft. (0.6 m) or less.



Hook 1

(Harness)

Steel/ Snap

Steel/Snap

Steel/ Snap

Steel/Snap

Material/Style

Leg Material

Web, Elastic

Web, Elastic

Web. Elastic

Web, Elastic

Hook 2

(Anchor)

Steel/ Snap

Steel/Snap

Steel/ Rebar

Steel/Rebar

Material/Style

Hook 3

(Anchor)

Steel/Snap

Steel/Rebar

Material/Style



3M[™] Protecta[®]

Lanyard Accessories

Shock Absorber 1340260

Add in-line to a non-shock absorbing lanyard for fall arrest applications, including leading edges (non-sharp edges only). With D-ring at one end, snap hook at other x 18-1/2 in. (47 cm)

D-Ring Extension 1385000

Dorsal D-ring extender with D-ring at one end, snap hook at other x 18 in. (45 cm)





systems are used to rescue workers in confined spaces.

What to look for in a confined space rescue system:

Ease-of-use

Systems should be easy to set up, use and dismantle.

Mechanical systems

Lifeline types and length are just a few of the options you need to consider.

Durability

Components must be made from quality materials that can endure rough handling and harsh environments.

Versatility

Systems should be adjustable and adaptable to extreme environments. Modular systems allow you to add to your system over time.

Strength

Systems must be rated for your application. Look for maximum strength with minimal weight.

Portability

Systems should be lightweight and easy to transport, set up and store.

3M™ DBI-SALA® Hoist Systems



Engineered with aluminum, 3M™ DBI-SALA® Hoist Systems are adjustable and extendable to meet the specific needs of your job site.


8530352

4-in-1 Davit Guard System

Provides a basic hoist and a passive restraint guardrail system protecting companion workers and bystanders. It offers ample room for worker entry and maneuvering while keeping the confined space opening secure. A standard tie-off point provides a convenient 5,000 lb. (22 kN) anchor point for fall arrest devices where required.



3M[™] DBI-SALA[®] Davit Arm System Components




3M™ DBI-SALA® Hoist Systems

8518000

5-Piece Hoist System

Davit arm and base system includes 11.5 in.—27.5 in. (29.2 cm—69.8 cm) Adjustable Offset Upper Mast (8518001), 33 in. (83.8 cm) Lightweight Lower Mast (8518002), and 3-Piece Lightweight Base (8518005). Includes winch mounting bracket. Order winch and Self-Retracting Lifeline separately. Weight: 100 lbs. (45.5 kg)



















| | Short Reach 5-Piece Davit System | Digital Winch | Salalift [™] II Winch | Ultra-Lok [™] Retrieval SRL | Sealed- Blok [™] Retrieval SRL | Davit Carrying Bags | Digital Winch Bags | Extra Winch Bracket |
|---------|---|------------------|-----------------------------------|--|--|---------------------------|-----------------------|------------------------|
| 8301100 | 8518000 | | | 3501102 | | 8518513 | | |
| 8301102 | 8518000 | 8518558 | | | | 8518513 | 8517567 | |
| 8301103 | 8518000 | | 8102001 | 3501102 | | 8518513 | | 8549915 |
| 8301105 | 8518000 | 8518558 | | | 3400923 | 8518513 | 8517567 | 8549915 |
| 8301107 | | | | 3501102 | | | | |
| 8301109 | | 8518558 | | | | | 8517567 | |
| 8301110 | | | 8102001 | 3501102 | | | | 8549915 |
| 8301112 | | 8518558 | | | 3400923 | | 8517567 | 8549915 |
| 8518000 | 8518000 | | | | | | | |




8518270

5-Piece Equipment Cart

Transport the 5-Piece System with ease over smooth or rough terrain. Ideal for tight storage situations.

8518513 Set of two carrying bags for 5-Piece Hoist System (8518000)

3M[™] DBI-SALA[®] One-Piece Adjustable Offset Davit Masts



| Adjustable offset davit mast | 66 in.– 76 in. (167.6 cm– 193 cm) | 78 in.– 88 in. (198.1 cm– 223.5 cm) | 90 in.– 100 in. (228.6 cm– 254 cm) | 69.5 in 87.5 in. (176.5 cm- 222.2 cm) | 81.5 in 91.5 in. (207 cm- 232.4 cm) | 93.5 in 111.5 in. (237.5 cm- 282.2 cm) |
|--------------------------------------|--|--|---|--|--|---|
| 11.5 in27.5 in. (29.2 cm-69.8 cm) | 8518382 | 8518383 | 8518384 | - | - | - |
| 223.5 in42.5 in. (59.7 cm-108 cm) | - | _ | - | 8518385 | 8518386 | 8518387 |

Offset Davit Masts & Lower Mast Extensions


Customize the height of these davit masts with up to two Lower Mast Extensions. Custom lengths are available—call us for details.



8518001

11.5 in.–27.5 in. Adjustable Offset Davit Mast


(Includes winch mount bracket.) Combine with up to two lower mast extensions to increase anchorage height. Combined extension length cannot exceed 90 in. (228 cm).



8518006

23.5 in.-42.5 in. Adjustable Offset Davit Mast

(Includes winch mount bracket.) Combine with up to two lower mast extensions to increase anchorage height. Combined extension length cannot exceed 78 in. (198 cm).



8518509 21 in. (53.3 cm) Lower Mast Extension.

8518002 33 in. (83.8 cm) Lower Mast Extension.

8518003 45 in. (114.3 cm) Lower Mast Extension.

8518004 57 in. (144.8 cm) Lower Mast Extension.

8513330

Carrying Bag

Carrying bag with protective plastic liner for one piece davit arm (8518382–8518387) and 10 ft. aluminum tripod (8513159).


8513564 Bag with protective plastic liner for Adjustable Offset Davit Mast, with Lower Mast Extension.



3M™ DBI-SALA® Fixed Bases

Fixed bases allow for easier setup and teardown, making them ideal for work areas where a base can be permanently installed to an existing structure. All bases come with PVC sleeve liners.





8512831

Center Mount Sleeve Zinc-Plated

Zinc-plated mild steel construction construction. Mounts to concrete or steel structure.

Weight: 13 lbs. (5.9 kg)

8516563 304 Stainless steel construction. Mounts to concrete or steel structure.




8518348


Wall Mount Sleeve 304 Stainless Steel


304 stainless steel construction. Compact design mounts to vertical concrete or steel structures.

Weight: 12 lbs. (5.5 kg)

8516191 Wall Mount Sleeve, zinc-plated mild steel construction.







8510109

Core Mount Sleeve

Zinc-plated mild steel construction. Designed for slip-in installation into 4 in. (10.1 cm) core hole in concrete or in an existing steel structure. Weight: 8 lbs. (3.6 kg)

8510110 Core Mount Sleeve, stainless steel construction.

8510316

Floor Mount Sleeve

Mild steel construction. Recessed fastener pockets allow for bolt-in installation into existing concrete or steel structure. Flush mount design eliminates trip hazards when not in use. Weight: 21 lbs. (9.5 kg)


8512827 Flush Floor Mount Sleeve, stainless steel construction.

8510057

Offset Floor Mount Sleeve

Zinc-plated mild steel construction. Mounts to horizontal concrete or steel structure. Offset design allows for maximum reach of the mast being used. Weight: 25 lbs. (11.3 kg)







8515162

Deck Mount Sleeve

Zinc-plated mild steel construction. Designed to slip into a 4 in. (10.1 cm) hole in existing flooring. Flush mount design eliminates trip hazards when not in use. Comes with plastic stopper and mounting hardware—mounts to thicknesses from 1/4 in.-2 in. (6.4 mm-50.8 mm). Weight: 17 lbs. (7.7 kg)

8515834 Deck Mount Sleeve, stainless steel construction.

8510311

Flush Floor Mount Sleeve

Mild steel construction. Comes with pins for fresh concrete anchors for new construction or renovation. Flush mount design eliminates trip hazards when not in use. Weight: 21 lbs. (9.5 kg)

8512828 Flush Floor Mount Sleeve, stainless steel construction.

8510827


Heavy-Duty Sleeve Cap

Stainless steel construction. Used with permanent mounted sleeves when installed in high traffic or other severe service locations. Weight: 1.2 lbs. (0.54 kg)

8510826 Heavy-Duty Sleeve Cap, zinc-plated mild steel construction.

3M™ DBI-SALA® Portable Bases

Portable Bases work with a variety of Davit Arm and Mast Extensions. They're ideal when you need to move and access various confined space areas. Bases are lightweight, easy to transport, set up and use.



8513565

Carrying Bag

Bag with protective plastic liner for 3-Piece Davit Base (8518005).


Zinc-plated mild steel construction. Eight independent clamping screws allow temporary installations over edges of shoring cans, walls and other structures. Comes with PVC inner liner. Custom fit openings available.

8510429 Barrel Mount Sleeve with 3.5 in. (76.2 mm) opening, stainless steel.


8510568

Forklift Basket

Designed to convert your forklift into a versatile confined space and fall arrest work platform. Add a davit mast and winch/ Self-Retracting Lifeline to the basket and you're ready to go.



Lightweight aluminum construction and tool-free assembly simplifies setup, transport and storage. Durable powder coated finish with anti-slip finish on walking surfaces. Includes spring-loaded gate. Weight: 215 lbs. (98 kg)



Designed for shoring, wall and parapet applications. Standard unit accommodates wall thicknesses up to a maximum of 24 in. (60.9 cm), with shorter or longer adjustment tubes available on request. Anodized, welded aluminum with zinc-plated steel hardware with inner sleeve.

8510715 Adjustable Barrel Mount Sleeve for 0 in.-12 in. opening.

8516088 Adjustable Barrel Mount Sleeve for 42 in. maximum opening.

3M™ DBI-SALA® Portable Bases

8510501


3M™ DBI-SALA® Manhole Collars

17.5 in. (44.5 cm) Manhole Collar, fits 18 in.—20 in. (45.7 cm—50.8 cm) diameter. Provides a Portable Davit Base by simply fitting within manhole opening. Powder coated aluminum construction with PVC sleeve liner.

- 8510520 19.5 in. (49.5 cm) Manhole Collar fits 20 in.-22 in. (50.8 cm-55.8 cm) diameter.
- 8510457 21.5 in. (54.6 cm) Manhole Collar fits 22 in.-24 in. (55.8 cm-60.9 cm) diameter.
- 8510163 23.5 in. (59.7 cm) Manhole Collar fits 24 in.-26 in. (60.9 cm-66 cm) diameter.
- 8510633 25.5 in. (64.7 cm) Manhole Collar fits 26 in.–28 in. (66 cm–71.1 cm) diameter.
- 8510632 27.5 in. (69.8 cm) Manhole Collar fits 28 in.–30 in. (71.1 cm–76.2 cm) diameter.
- 8510546 29.5 in. (74.9 cm) Manhole Collar fits 30 in.-32 in. (76.2 cm-81.2 cm) diameter.
- 8530312 31.5 in. (80 cm) Manhole Collar fits 32 in.-34 in. (81.3 cm-86.4 cm) diameter.
- 8512994 33.5 in. (83.1 cm) Manhole Collar fits 34 in.-36 in. (86.3 cm-91.4 cm) diameter.



For small davit arms only



8510140

Vehicle Hitch Mount Sleeve

Designed to install into a 2 in. (51 mm) hitch receiver on an attendant vehicle to provide a portable anchor point for confined space entry, rescue and fall arrest systems. Assembly for a maximum 27.5 in. (69.8 cm) Offset Davit Mast.

8514461 Assembly for a maximum 42.5 in. (108 cm) Offset Davit Mast.

Vehicle Hitch Sleeve Extensions

A maximum of one extension can be used with a hitch mount and a bumper attachment.

- 8514503 2 ft. (0.61 m) Vehicle hitch mount sleeve extension. Weight: 17 lbs. (7.7 kg)
- 8512829 4 ft. (1.21 m) Vehicle hitch mount sleeve extension. Weight: 27.8 lbs. (12.6 kg)
- 8511384 6 ft. (1.83 m) Vehicle hitch mount sleeve extension. Weight: 39 lbs. (17.6 kg)



8511401

Universal Joint Assembly

Installs between the Hitch Mount Sleeve (8510140) or extension and the vehicle to compensate for uneven ground conditions. Weight: 10 lbs. (4.5 kg)



3M™ DBI-SALA® Counterweight Systems


Counterweight Systems are composed of a central base unit to accommodate a variety of anchoring options, positioning and adjustment legs, and extension assemblies.

8512894

Counterweight System

Counterweight system base with pole leg assembly. Weight: 199 lbs. (90.2 kg)

Counterweight requirements determined by application. Contact customer service to order.



8520775

Mobile Counterweighted Cart Base

Ideal for areas that require access near a leading edge or into large tanks. System comes complete with counterweight cart, 36 in. (91.4 cm) inner extension tube, center section, and two outrigger screw assemblies. System counterweighted by 50 lb. (22.7 kg) weight plates. (Weight plates, davit mast and winch not included—order separately.)

8530088


Portable Catwalk Clamping Base

Designed to secure to 36 in. (91.4 cm) wide walkways. Ideal for areas that require access off a mezzanine or walkway. System comes complete with catwalk hook, 16 in. (40.6 cm) inner extension tube, center section and two outrigger screw assemblies. Other models available to accommodate different widths of walkways. (Davit mast and winch not included—order separately. More options available.)

8530256

Portable Anchor Point Base

Ideal for areas that require access over a leading edge. System comes complete with U-bolt anchor point to attach to secondary fixed anchor, 36 in. (91.4 cm) inner extension tube, center section, and two outrigger screw assemblies. System requires a 5,000 lb. (22 kN) anchorage point to be tied down to. (Davit mast and winch not included—order separately.)



6

3

Constructed of lightweight tubular aluminum with a rugged steel head assembly. Quick-release pins positively locate components at all adjustment points for tool-free setup and adjustment.

- **Mechanical Devices** Supports up to three winches or SRLs for complete flexibility.
- **Quick-Connect Bracket** Fast and easy attachment of mechanical devices.
- **Safety Chain** Added support in demanding applications.
- **Top Mounted Pulley System** Mount up to three pulleys to route mechanical device lifelines.
- **Secondary Anchor Point** 5,000 lb. (22 kN) anchor point for secondary fall arrest system.
- **Aluminum Construction** Lightweight and durable for ease-of-use.



8000000

3M[™] DBI-SALA® 7 ft. Aluminum Tripod


- Lightweight, durable aluminum construction.
- Telescoping adjustable locking legs.
- Built-in pulley system.
- 5,000 lb. (22 kN) built-in head mounted anchor point.
- Capacity: 350 lbs. (159 kg) 8000010 9 ft. Tripod

Winch and SRL not included—order separately.



8512292

Winch/SRL Mounting Bracket for Tripod (8513159)



8512293

Top Pulley Assembly for UCT Series Tripods

Routes mechanical device's lifeline over and into confined space area.



8513158

3M™ DBI-SALA® UCT-300 7 ft. Tripod

- Lightweight, durable aluminum construction.
- Telescoping adjustable locking legs.
- Built-in pulley system—can accommodate up to three pulleys.
- 5,000 lb. (22 kN) built-in head mounted anchor point.
- Capacity: 450 lbs. (204 kg) 8513159 10 ft. (3 m) Tripod

Winch and SRL not included—order separately.



Carrying Bag


For 10 ft. (3 m) Tripod with protective plastic liner (8513159).

8513329 For 7 ft. (2.1 m) tripod with protective plastic liner (8513158)

9503094 For 7 ft. (2.1 m) tripod (8000000)

9503095 For 9 ft. (2.7 m) tripod (8000010)







3M[™] DBI-SALA® Tripods

Complete Tripod Solutions


















| | 1 | | 9 | 111 | • | 8 | • | | - Alle |
|---------|--------------------|--------------------|------------------|-----------------------------------|--------------------------------------|--|---------------------------|--------------------------------------|------------------------|
| | 7' Alum. Tripod | 9' Alum. Tripod | Lifeline Type | Salalift [™] II Winch | Sealed- Blok™ Retrieval SRL | Ultra-Lok [™] Retrieval SRL | Tripod Carrying Bag | Winch/ SRL Mounting Bracket | Leg Mount Pulley |
| 8300030 | 8000000 | | Galvanized | 60 ft. (18.3 m) | | | | | |
| 8300032 | 8000000 | | Galvanized | 90 ft. (27.4 m) | | | | | |
| 8300034 | 8000000 | | Galvanized | 120 ft. (36.6 m) | | | | | |
| 8301030 | 8000000 | | Galvanized | | 50 ft. (15.2 m) | | | | |
| 8301041 | 8000000 | | Galvanized | 60 ft. (18.3 m) | 50 ft. (15.2 m) | | | 8005048 | 8003238 |
| 8301062 | 8000000 | | Galvanized | | | 50 ft. (15.2 m) | 9503094 | | |
| 8301066 | 8000000 | | Galvanized | 60 ft. (18.3 m) | | 50 ft. (15.2 m) | 9503094 | 8005048 | 8003238 |
| 8300040 | | 8000010 | Galvanized | 60 ft. (18.3 m) | | | | | |
| 8301035 | | 8000010 | Galvanized | | 50 ft. (15.2 m) | | | | |
| 8301049 | | 8000010 | Galvanized | | 85 ft. (25.9 m) | | | | |
| 8301043 | | 8000010 | Galvanized | 60 ft. (18.3 m) | 50 ft. (15.2 m) | | | 8005048 | 8003238 |
| 8301064 | | 8000010 | Galvanized | | | 50 ft. (15.2 m) | 9503094 | | |
| 8301068 | | 8000010 | Galvanized | 60 ft. (18.3 m) | | 50 ft. (15.2 m) | 9503094 | 8005048 | 8003238 |
| 8300031 | 8000000 | | Stainless Steel | 60 ft. (18.3 m) | | | | | |
| 8300033 | 8000000 | | Stainless Steel | 90 ft. (27.4 m) | | | | | |
| 8300035 | 8000000 | | Stainless Steel | 120 ft. (36.6 m) | | | | | |
| 8301031 | 8000000 | | Stainless Steel | | 50 ft. (15.2 m) | | | | |
| 8301042 | 8000000 | | Stainless Steel | 60 ft. (18.3 m) | 50 ft. (15.2 m) | | | 8005048 | 8003238 |
| 8301063 | 8000000 | | Stainless Steel | | | 50 ft. (15.2 m) | 9503094 | | |
| 8301067 | 8000000 | | Stainless Steel | 60 ft. (18.3 m) | | 50 ft. (15.2 m) | 9503094 | 8005048 | 8003238 |
| 8300041 | | 8000010 | Stainless Steel | 60 ft. (18.3 m) | | | | | |
| 8301036 | | 8000010 | Stainless Steel | | 50 ft. (15.2 m) | | | | |
| 8301037 | | 8000010 | Stainless Steel | | 85 ft. (25.9 m) | | | | |
| 8301044 | | 8000010 | Stainless Steel | 60 ft. (18.3 m) | 50 ft. (15.2 m) | | | 8005048 | 8003238 |
| 8301069 | | 8000010 | Stainless Steel | 60 ft. (18.3 m) | | 50 ft. (15.2 m) | 9503094 | 8005048 | 8003238 |

3M™ DBI-SALA® Pole Hoist System

The pole hoist attaches with a carabiner on the universal bracket to a suitable anchor point. It has a unique swivel head that rotates 360 degrees, providing flexibility in both vertical and horizontal confined space entries.







8520777

Clamp-On Anchor for Pole Hoists

Designed to secure to a vertical or horizontal flange up to 6 in. (15.2 cm) thick and provide an anchorage point to connect a pole hoist device to.



2104550

Steel Anchor Plate with D-Ring

This plate anchor offers a compact, reliable attachment to 3/8 in.-1 in. thick plate steel for connecting your lanyard, vertical lifeline system or self-retracting lifeline.



6320008

Web Sling

 $6,\!000$ lb. rated, 1 ft. (30.5 cm) long; 3/4 ft (19.1 mm) wide Kevlar® web anchor sling.



3M™ DBI-SALA® Portable Fall Arrest Posts


Our portable fall arrest post allows for up to three workers on top of transformers or other types of vertical platforms with potential fall hazards.

8516693

Rescue Davit Arm for Portable Fall Arrest Post

The optional rescue davit arm assembles to our portable fall arrest post, providing rescue and material handling capabilities.

8516691 post not included—order separately.



8516691

Portable Fall Arrest Post

- Three independent swiveling tie-off points.
- 360 degrees of protection for three workers.
- Telescopic design;
 32.75 in.-46 in.-57.25 in.
 (83.2 cm-116.8 cm-145.4 cm)
- Aluminum construction.

8516996

Uni-Anchor Fall Arrest Post

The 14 ft. (4.3 m) uni-anchor fall arrest post mounts using uni-anchor plates and extends up to 14 ft. (4.3 m) to provide a 1-man-rated fall arrest anchor point. Weight: 71 lbs. (32.2 kg)




Anchor Bases for Portable Fall Arrest Post

8517412


Bare Steel Uni-Anchor with Tie-Off Anchors

For closed environments without chemical or moisture exposure.



8510816

Weld-On Mounting Plate
Unplated mild steel construction.



8517413

Incline Adapter with Tie-Off Anchor


Permanently weld to inclined surfaces.



8519819

Base Concrete Anchor

Bolt-on anchor plate for concrete or steel surfaces.



Accessories

8516692

14 in. Anchor Post Extension

Provides option to tie-off one worker at an increased height of 68.5 in. (174 cm). Weight: 5 lbs. (2.2 kg)



8517565

Carrying Bag

Heavy-duty carrying bag for Portable Fall Arrest Post (8516691) or Rescue Davit for Fall Arrest Post (8516693).



Retrieving incapacitated workers and bringing them to safety makes the mechanical device one of the most critical parts of your rescue system. In some situations, you may need a secondary

3M™ DBI-SALA® Mechanical Systems


1 Digital Winches

or backup system.

- Man rated 450 lb. (201 kg) capacity.
- Digital usage indicator tracks drum revolutions to determine service intervals.
- Triple redundant braking system.
- Sealed bearings at all contact points.

2 Retrieval Sealed-Blok™ Self-Retracting Lifeline

- Ideal for secondary or backup.
- Man rated 420 lb. (190 kg) capacity.
- Fall arrest system limits forces to 900 lbs. (4 kN)
- Built-in emergency retrieval winch.
- Input handle with primary brake.





3M™ DBI-SALA® Salalift™ II Winches

- Man rated 350 lb. (159 kg) capacity.
- Overload clutch.
- Gear ratio of 6:1.
- Free-wheel mode.
- Shielded ball bearings.



3M™ DBI-SALA® Winches

Digital Winch

| Drive Type | Lifeline Type | Mounting Bracket | 60 ft. (18 m) | 90 ft. (27 m) | 140 ft. (42 m) | 190 ft. (58 m) | 240 ft. (73 m) | 290 ft. (88 m) |
|---------------------|------------------|--------------------------------|------------------------|------------------------|----------------------|----------------------|----------------------|------------------------|
| | Galvanized steel | • | 8518567 | 8518568 | 8518588 | 8518589 | 8518610 | 8518611 |
| Power drive* | Stainless steel | • | 8518565 | 8518566 | 8518586 | 8518587 | 8518608 | 8518609 |
| ш | Technora® rope | • | 8518571 | | | | | |
| p p e | Galvanized steel | | 8518560 | 8518561 | 8518581 | 8518582 | 8518603 | 8518604 |
| Removable handle | Stainless steel | • | 8518558 | 8518559 | 8518579 | 8518580 | 8518601 | 8518602 |
| Rei | Technora® rope | • | 8518564 | | | | | |
| Digital Winch | | Cable model weight | 30.5 lbs. (13.8 kg) | 32.5 lbs. (14.7 kg) | 40 lbs. (18.4 kg) | 43 lbs. (19.5 kg) | 50 lbs. (22.6 kg) | 53.5 lbs. (19.5 kg) |
| | | Technora® rope model weight | 27 lbs. (12.2 kg) | | | | | |

Power drive units require Overload Protection Clutch (8512936) — Not Included. Overload Protection Clutch used in conjunction with a drill for retrieving an entrant.

Salalift™ II Winch

| Drive Type | Lifeline Type | Mounting Bracket | Winch Bag | 50 ft. (15.2 m) | 60 ft. (18 m) | 90 ft. (27 m) | 120 ft. (36.5 m) |
|--------------------------------|---|---------------------|----------------|--------------------|------------------------|------------------------|------------------------|
| ble | Galvanized steel | • | | | 8102001 | 8102009 | 8102005 |
| Removable handle | Stainless steel | | | | 8102003 | 8102011 | 8102007 |
| Rer | Technora® rope | | | 8102050 | | | |
| Salalift [™] Winch | Salalift [™] II Cable model weight Winch | | del weight | | 30.5 lbs. (13.8 kg) | 32.5 lbs. (14.7 kg) | 38.5 lbs. (17.5 kg) |
| 1 | | Technora® rop | e model weight | 27 lbs. (12.2 kg) | | | |



8549915Extra Winch Bracket



8512936Overload Protection Clutch
450 lbs. maximum working load.



8510207Winch/SRL Adapter with Flat Back
Attaches 3M™ DBI-SALA® Winch/SRL
to structures.



8516824Quick-Release Mounting Bracket For upper and lower masts.



1001210 Retrieval Wristlets

For upper and lower masts. Ideal for narrow extractions. D-ring at end x 2 ft. (0.6 m).

1001220 Attached with an O-ring at one end x 18 in. (0.46 m).



1231460

Y-Lanyard

Rescue/retrieval design ideal for use with harness incorporating D-rings. D-ring at center x 2 ft. (0.6 m).

1231470 Without spreader bar



8517567Padded Carrying Bag
For digital winch.

3M™ DBI-SALA® Retrieval Self-Retracting Lifelines

3M™ DBI-SALA® Sealed-Blok™ Self-Retracting Lifelines with Retrieval incorporate a concept that separates all dynamic components, including the motor spring and break, from foreign elements such as grease, moisture and dirt. The sealed design meets IP69K rating.

- Available with RSQ Dual-Mode Design—allows users to select either standard fall arrest mode or automatic descent mode.
- Available lengths ranging from 30 ft. (9.1 m) to 175 ft. (53.3 m).
- IP69K Sealed Rating.



Retrieval Sealed-Blok™ SRL



Retrieval Sealed-Blok™ SRL - RSQ

3M™ DBI-SALA® Ultra-Lok™ Self-Retracting Lifelines with Retrieval are engineered devices you can count on for safety, efficiency and comfort.

• Available in 50 ft. length.



Retrieval Ultra-Lok™ SRL

3M™ DBI-SALA® Sealed-Blok™ vs 3M™ DBI-SALA® Ultra-Lok™

| | Maximum | Maximum | | DOG 4 "111 | | |
|--------------|---------------------|------------------|----------------|------------|-----------------|---------------|
| | Capacity | Lifeline Length | Technora® rope | Galvanized | Stainless steel | RSQ Available |
| Sealed-Blok™ | 420 lbs. (190.5 kg) | 175 ft. (53.3 m) | | • | • | |
| Ultra-Lok™ | 310 lbs. (140.6 kg) | 50 ft. (15.2 m) | | • | • | |

3M™ DBI-SALA® Retrieval Self-Retracting Lifelines

| Cable Type | Sealed- Blok [™] | Sealed- Blok [™] Without Bracket | Sealed- Blok™/ RSQ Without Bracket | Ultra-Lok [™] | 30 ft. (9.1 m) | 50 ft. (15.2 m) | 55 ft. (16.8 m) | 85 ft. (25.9 m) | 130 ft. (39.6 m) | 175 ft. (52.5m) |
|------------------|------------------------------|--|---|------------------------|-------------------|--------------------|--------------------|--------------------|---------------------|--------------------|
| | - | | | | 3400853 | 3400923 | | 3400871 | 3400976 | |
| Galvanized steel | | | | | 3400850 | 3400920 | | 3400870 | 3400975 | 3400660 |
| Galvanized steel | | | | | | 3400940 | | 3400910 | | |
| | | | | | | 3501102 | | | | |
| | | | | | 3400858 | 3400926 | | 3400882 | 3400987 | |
| Stainless steel | | | | | 3400852 | | | 3400874 | 3400979 | 3400661 |
| Stainless steel | | | | | | 3400942 | | 3400912 | | |
| | | | | | | 3501103 | | | | |
| Technora® rope | | | | | 3400840 | | 3400843 | | | |



3401025

Mounting Bracket for Sealed-Blok™ Retrieval SRL Fits most sizes of Sealed-Blok™ Retrieval SRL.

3M™ DBI-SALA® Dual-Mode Descent





Work and rescue with the same equipment with the built-in rescue operation of our dual-mode descent technology.



Fall arrest mode

A speed-sensing brake stops the fall, reduces forces imposed on the user to safe levels, and allows for assisted rescue via hand, by pole, or a traditional assisted rescue operation.



Automatic descent mode

A speed-sensing brake stops the fall, and a centrifugal brake instantly activates to lower the user at a controlled speed to the next level or ground.











Sealed-Blok™ RSQ Self-Retracting Lifelines

Stainless steel wire rope with swivel snap hook, RSQ dual-mode, anchorage carabiner, 4 ft. (1.2 m) cable tie-off adapter.

3400932 50 ft. (15.23 m)

3400886 85 ft. (25.5 m)

3400991 130 ft. (39 m)

Also available with galvanized cable and snap hook, please contact 3M Fall Protection.



Ultra-Lok™ RSQ Self-Retracting Lifelines

50 ft. (15.2 m) of 3/16 in. (5 mm) wire rope with swivel snap hook and RSQ dual-mode.

3504550 Galvanized Steel Wire Rope

3504552 Stainless Steel Wire Rope

3M™ DBI-SALA® Rollgliss™ R550 Rescue and Descent

- 1 Drill Adapter
 Provides a mechanical option to raise a victim.
- 2 Cast Aluminum Housing
- Bi-Directional Hub

 Brings one hook up as the other goes down, for immediate use after each descent.
- 4 Anchorage
- 5 Integrated Rope Ears
 Greater descent speed
 control in assisted rescues.
- 6 Dual Brakes
 Added security, safety and peace of mind.
- 7 Durable Rope 3/8 in. (9.5 mm) Static Kernmantle Rope.
- 8 Lifeline Hook
 Patented Self-Locking
 Snap Hook.





Drill adapter



Multiple Length Options

Lengths between 50 ft. (15 m) and 500 ft. (152 m)

Two-Person Capacity

Can be used from heights up to 1,640 ft. (500 m) for one user at 310 lbs. (141 kg) or 575 ft. (175 m) for two users totaling 620 lbs. (282 kg)

Optional Ladder Bracket

Sold separately—3320014.



7

3M™ DBI-SALA® Rollgliss™

R550 Rescue Units

Includes carabiner (two), 4 ft. (1.22 m) anchor sling and rope bag.

Selection guide:

| 3 | |
|---------|-----------------|
| Part # | Length |
| 3327050 | 50 ft. (16 m) |
| 3327100 | 100 ft. (31 m) |
| 3327150 | 150 ft. (46 m) |
| 3327200 | 200 ft. (61 m) |
| 3327275 | 275 ft. (84 m) |
| 3327300 | 300 ft. (92 m) |
| 3327325 | 325 ft. (100 m) |
| 3327350 | 350 ft. (107 m) |
| 3327400 | 400 ft. (122 m) |
| 3327450 | 450 ft. (137 m) |
| 3327500 | 500 ft. (153 m) |



3M™ DBI-SALA® Rollgliss™

R550 Escape Units

Includes carabiner (two), 4 ft. (1.22 m) anchor sling.

Selection guide:

| Part # | Length | | |
|---------|-----------------|--|--|
| 3325100 | 100 ft. (31 m) | | |
| 3325200 | 200 ft. (61 m) | | |
| 3325300 | 300 ft. (92 m) | | |
| 3325400 | 400 ft. (122 m) | | |
| 3325500 | 500 ft. (152 m) | | |

3M™ DBI-SALA® Rollgliss™

R550 Rescue Units with Case

Includes edge protector, 4 ft. (1.22 m) anchor sling (two), 2.5 ft. (0.76 m) anchor sling, pulley, rope grab, carabiner (three), rope bag and humidity case.

Selection guide:

| Part # | Length | | |
|---------|-----------------|--|--|
| 3326100 | 100 ft. (31 m) | | |
| 3326300 | 300 ft. (92 m) | | |
| 3326350 | 350 ft. (107 m) | | |





9506162

Rope Bag



3620005

Anchoring Sling 4 ft. (1.22 m)

3620004

Anchoring Sling 2.5 ft. (0.76 m)



Edge Protector with Carabiner



9504733

Pulley



8900298

Rescue Pole



8900293

Rescue Pole Hook for Hot Stick



3320014

Ladder Bracket



9508289

Humidity Case

Fully sealed case provides 10 year minimum storage life. External humidity indicator allows user to inspect the seal without opening case.



2000112

Carabiner 11/16 in. (1.75 cm) gate.



2000041

Carabiner 2-1/8 in. (5.38 cm) gate.



3M[™] DBI-SALA[®] Rollgliss[™] R350 Rescue and Descent Positioning Device

8902004

Rollgliss™ R350 Rescue System

50 ft. travel/200 ft. of 3/8 in. rope (15.2 m/61 m), 3:1 ratio with pulleys, rope control device, anchor strap, carabiner and carrying bag.

8902006

Rollgliss™ R350 Rescue System

100 ft. travel/400 ft. of 3/8 in. rope (30.5 m/ 122 m), 3:1 ratio with pulleys, rope control device, anchor strap, carabiner and carrying bag.

Other lengths available in 10 ft. (3 m) increments. Accessories including 2:1, 4:1 and 5:1 pulleys are available.



Rollgliss™ Rescue Positioning Device

Service buildings, bridges and dams with this versatile rescue positioning device. It features a speed-sensing lock that allows you to manually lock off the device once you reach a work level. It serves both as a rescue system and has features for raising, lowering and positioning during normal work activities.

- Pre-rigged for quick and easy installation and use.
- No special tools, power source or extensive skills needed.
- Built-in brake.
- Lock-out mechanism allows user to stop/start anywhere.

3602050

Rollgliss™ Rescue Positioning Device

50 ft. travel/260 ft. of 3/8 in. rope (15.25 m/79.3 m), 4:1 ratio with pulleys, rope anchor straps, two carabiners and carrying bag.

3602100 100 ft. travel/510 ft. (30.5 m/155.5 m)

3M™ DBI-SALA® Rollgliss™ Descender

Make a quick and safe escape. Either vertical or sloped descent models are available to provide complete versatility and flexibility for any job site or work environment.



| 3301061 Work Over Rig Adapter Kit | Descent type | Lifeline material | Low or high speed | 115 ft. (35 m) | 200 ft. (61 m) |
|---|--------------|----------------------|----------------------|----------------|----------------|
| Sloped | ical | Galv | Low | 3303000 | - |
| | | | Low | - | 3303017 |
| | Vert | ss | Low | 3303002 | - |
| | | | Low | - | 3303018 |
| | Sloped | Galv | Low | 3303001 | 3303021 |
| | | | High | - | 3303015 |
| | | | Low | 3303003 | 3303019 |
| | SS | High | - | 3303016 | |

Sloped low speed models also include linkage, guide cable sleeve and suspension bars. Sloped high speed models include linkage, braking trolley and suspension bars.

3M[™] DBI-SALA[®] Rollgliss[™] Systems

8900292

Rollgliss™ R250 Rescue Kit

Enables the rescuer to remove a person from danger without putting themselves at risk by descending to them.

- 33 ft. (10 m) travel length.
- Transported in backpack-style bags.

8900293 Rollgliss™ Rescue Kit with 66 ft. (20 m) travel length.

8900294 Rollgliss™ Rescue Kit with 99 ft. (30 m) travel length.

3601490

Rollgliss™ Sealed Tension Limiter

Attaches to man-riding system in-line between the person and the raising/lowering line to warn operator and limit forces on an entangled worker.

Always use a separate back-up fall protection device with this system.



8516294

Rollgliss™ Rescue Ladder

Provides a way to assist rescue after a fall has occurred. It can be anchored to a structure and dropped to the victim, so they can climb up or down to safety.

- Available in 8 ft. (2.4 m) sections.
- Extra sections can be added.
- Includes three carabiners for attachment.
- For use with Rollgliss™ Rescue Ladder Anchor (8516316).



8516316

Rollgliss™ Rescue Ladder Anchor

For mounting rescue ladder to a davit arm or single anchorage point.

• For use with Rollgliss™ Rescue Ladder (8516294).





Protect your people. Protect your business.

All around the world, we bring expertise to education development, delivery and management. Our training focuses on education, knowledge and principles. No matter your location or industry, application, gear or requirement, you and your workers will benefit from our content and delivery methodologies.

Our vision:

Training that protects people, improves lives and enhances productivity.

Our mission is ensuring every single worker we train receives the critical knowledge and skill development they need for their industry in a way that's relatable and understandable to them.

Our instructors use our structured curriculum—with their individual style—and your situations and environment to create the best overall experience possible.

What's the 3M difference?



Protecting People.
Improving Lives. Enhancing Productivity.

Six customer value drivers. Each leveraging the 3M Science of Safety.













There's a broad spectrum of safety training offerings, so it's critical to dig deeper to ensure that you get the quality up-to-date training that you require. Here's what you can expect with 3M Safety Training:

Dedicated Instructors

It's not enough to just know the rules or know the gear. Our instructors have strong technical, industry and teaching backgrounds so they know how to make training knowledge real and relevant to each person they train.

Instructor-Led Courses

Fall protection. Confined spaces. Rescue. Just about anywhere the job takes you, we've got relevant courses that educate on the standards, practical applications and hands-on exercises to make it all "stick" with students.

Certified Instructor Program

For some organizations, it's more sensible to "train a new trainer," so you can invest in a dedicated, trained employee and have the ability to continuously train employees throughout the year on an as-needed basis.

Regulatory Standards Compliance

We don't just follow the rules—some of our team actively advise and contribute to the development of them. Our technical understanding and adherence to all relevant safety standards in every region allows us to help guide and clarify them for you and your team.

World-Class Training Centers, On-Site Delivery, or Virtual Instructor-Led Training

With dedicated training facilities across the U.S. and Canada, to virtual studios that deliver select programs with virtual instructor-led training, as well as on-site instructor-led training capabilities, 3M Safety Training is right where you need it to be.

Broad Employee Appeal

As students of science, we never stop learning—and you shouldn't either. Whether you're upper management, a foreman, supervisor, safety specialist or front line worker, we have training solutions that can teach you valuable insights you won't soon find anywhere else.

Ready for training with true value?

Visit 3M.com/SafetyTraining to learn more.



Protecting workers takes more than just keeping them from falling.

From construction sites to oil rigs, 3M™ DBI-SALA® Fall Protection for Tools helps work environments stay safe by reducing falling object incidents that can result in personal injury, equipment damage, and tool loss.

ANSI/ISEA 121-2018

Certified and tested.

Our drop prevention solutions are designed with the craft in mind, and are third-party tested in the harshest possible conditions—extreme heat, cold, moisture, corrosion and abrasion. We conduct dynamic and static strength tests, both in the field and in our ISO 9001-certified manufacturing facilities to ensure you get high quality and reliable fall protection for tools.

3M™ DBI-SALA® Attachment Points

D-Rings

- D-rings can be attached to tools under 5 lb (2.3 kg) or 2 lb (0.9 kg) using our Quick-Wrap Tape (see page 47).
- Dual D-rings allow for 100% tool tie-off during tool transfers.



Selection guide:


| Part # | Description | Load rating | Quantity | Non-conductive |
|---------|--|---------------|----------|----------------|
| 1500003 | D-ring 0.5" x 2.25" (1.3 cm x 5.7 cm) | 2 lb (0.9 kg) | 10 Pack | No |
| 1500004 | D-ring 0.5" x 2.25" (1.3 cm x 5.7 cm) | 2 lb (0.9 kg) | 100 Pack | No |
| 1500005 | D-ring 0.5" x 2.25" (1.3 cm x 5.7 cm) non-conductive | 2 lb (0.9 kg) | 10 Pack | Yes |
| 1500006 | D-ring 0.5" x 2.25" (1.3 cm x 5.7 cm) non-conductive | 2 lb (0.9 kg) | 100 Pack | No |
| 1500007 | D-ring 1" x 3.5" (2.5 cm x 8.9 cm) | 5 lb (2.3 kg) | 10 Pack | No |
| 1500008 | D-ring 1" x 3.5" (2.5 cm x 8.9 cm) | 5 lb (2.3 kg) | 50 Pack | No |
| 1500001 | Dual D-ring small | 2 lb (0.9 kg) | 10 Pack | No |

Quick-Wrap Tape

- 1" (2.5 cm) wide tape conforms to the shape of whatever it is applied to.
- Used with our D-Rings and Tool Cinch Attachments to create tethering points on tools.
- Made from a self-fusing silicone rubber that leaves no adhesive or residue behind.
- Inner fiberglass webbing increases the strength of the tape and makes the tape resistant to sharp objects.


Selection guide:

| Part # | Description | Quantity | Length |
|---------|-----------------------------|----------|-----------------|
| 1500174 | Quick wrap, yellow | 1 | 108" (274.3 cm) |
| 1500175 | Quick wrap, yellow | 10 | 108" (274.3 cm) |
| 1500168 | Quick wrap, blue | 1 | 108" (274.3 cm) |
| 1500169 | Quick wrap, blue | 10 | 108" (274.3 cm) |
| 1500171 | Quick wrap, blue, 2x length | 1 | 216" (548.6 cm) |
| 1500172 | Quick wrap, blue, 2x length | 10 | 216" (548.6 cm) |




Tool Cinch Attachments


- Tool Cinch Attachments feature a cinch design that allows users to secure equipment up to 35 lb (15.9 kg) or 80 lb (36.3 kg).
- Stabilization wings can be used to keep Tool Cinch Attachments in place using our Quick-Wrap Tape.



Selection guide:

| Part # | Description | Load rating | Stabilization wings |
|----------|---|-----------------|---------------------|
| 1500015* | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | 2 |
| 1500016 | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | 2 |
| 1500013* | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | 1 |
| 1500014 | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | 1 |
| 1500011* | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | None |
| 1500012 | V-Ring attachment point, stabilization wing | 35 lb (15.9 kg) | None |
| 1500017 | V-Ring attachment point, stabilization wing | 80 lb (36.3 kg) | 2 |
| 1500018 | V-Ring attachment point, stabilization wing | 80 lb (36.3 kg) | 2 |







1500009

D-Ring Cord


- Cinches to tools weighing up to 5 lb (2.3 kg).
- Pass the loop end of a D-Ring Cord through a pre-drilled hole or closed handle to create an attachment point.
- Comes in a pack of 10.





Bungee Tethers

Our bungee tethers are third-party load rated and thoughtfully designed to prevent dropped objects.



| Part # | Description | Load rating | Length (relaxed) | Length (stretched) |
|---------|-------------------------------------|-----------------|------------------|--------------------|
| 1500047 | Hook2Loop Bungee Tether | 15 lb (4.5 kg) | 32" (81.3 cm) | 47" (119.4 cm) |
| 1500048 | Hook2Loop Bungee Tether (10 pack) | 15 lb (4.5 kg) | 32" (81.3 cm) | 47" (119.4 cm) |
| 1500049 | Medium-Duty Hook2Loop Bungee Tether | 35 lb (15.9 kg) | 31" (78.7 cm) | 52" (132.1 cm) |

Coil Tethers

Easy to clean and out of the way—exactly what a tether should be. The lightweight vinyl construction and compact design of our Coil Tethers makes them an ideal alternative to classic bungee tethers.



Hook2Hook Coil Tether with Swivel

- Compact design stays close to the body
- 5 lb (2.3 kg) load rating



1500065

Hook2QuickRing Coil Tether with Tail

- Use with hammers and other long-handled tools
- Available as a combo with our Hammer Holster
- 2 lb. (0.9 kg) load rating



Hard Hat Tether

- Simple installation and removal
- Patented clip holds stronger when force is applied to it
- 4 lb. (1.8 kg) load rating

3M™ DBI-SALA® Tool Lanyards



1500050

Medium-Duty Hook2Loop Lanyard

- Features an aluminum double-action twist-lock carabiner to help prevent accidental openings
- Works well with medium-duty tool cinch
- 35 lb (15.9 kg) load rating
- 72" (182.9 cm) length



1500052

Heavy-Duty Hook2Rail Lanyard

- Features an aluminum double-action twistlock carabiner to help prevent accidental openings
- Large double-action twist-lock rail carabiner
- Works well with heavy-duty tool cinch
- 80 lb (36.3 kg) load rating
- 72" (182.9 cm) length

3M™ DBI-SALA® Single and Dual Tool Holsters



- Single and Dual Tool Holsters are equipped with D-rings that are load rated for 5 lb (2.3 kg).
- Several variants of these holsters come with Retractors (indicated below).
 Retractors are load rated for 1-1/2 lb (0.7 kg).
- Single and dual tool holsters feature High-Visibility Reflectors and the Magnetic Tool Staging System.
- A bottom drain vent allows the holster to perform even in wet conditions.

Selection guide:

| Part # | Description | Retractors included | Attachment |
|----------|------------------------------------|---------------------|------------|
| 1500104* | Single Tool Holster with Retractor | 1x | Harness |
| 1500102* | Single Tool Holster with Retractor | 1x | Belt |
| 1500105* | Extra-Deep Single Tool Holster | None | Belt |
| 1500108 | Dual Tool Holster | None | Harness |
| 1500109* | Dual Tool Holster with Retractors | 2x | Harness |
| 1500106 | Dual Tool Holster | None | Belt |
| 1500107* | Dual Tool Holster with Retractors | 2x | Belt |

^{*}Patent pending

1500098

Tape Measure Holster with Retractor

- Designed to be used with a tape measure, or the optional tape measure sleeve, allowing tape measures to be safely tethered and holstered.
- Includes a Retractor.
- The tape measure sleeve conforms to the size of most tape measures.
- Features High-Visibility Reflectors.

1500099 Tape Measure Sleeve

1500100 Tape Measure Holster with Retractor and Sleeve Combo



3M™ DBI-SALA® Tool Holsters

1500165

Large Tape Measure Sleeve

- Compliment to existing 25' Tape Measure Sleeve.
- Provides a solution for most large tape measures used on a job site.



1500095

Pouch Holster with Retractor

- Quickly holster tape measures and other small tools.
- Includes a Retractor.

Patent pending



1500096

Scaffold Wrench Holster with Retractor

- Quickly holster scaffold wrenches while working at height.
- Features High-Visibility Reflectors.

1500097 Scaffold Wrench Holster with Retractor and Hook2Loop Bungee Tether





Back of holster features pouch for Safety Retractor 1500069. Rear feed system allows retractor to tie off a scaffold wrench while staying out of the way.

1500093

Hammer Holster

- The Hammer Holster allows for the safe holstering of most hammers under 5 lb (2.3 kg).
- D-ring on the side of the holster is load rated for 5 lb (2.3 kg).
- The 1500094 combo comes with a 1500065 Hook2Quick Ring Coil Tether that is specially designed for use with the Hammer Holster. The Hook2Quick Ring Coil Tether is load rated for 2 lb (0.9 kg).
- During transport, the Hammer Holster can be locked shut with a hook and loop strap. While being used, the strap can be locked up allowing for easy hammer access and holstering.

1500094 Hammer Holster & Hook2Quick Ring Coil Tether



locked, preventing hammer

unlocked, making it suitable for active use.



1500090

Battery Holster/Sleeve

- Unique sleeve design conforms to the size of most drill batteries.
- Sleeve is cinched to the drill, allowing the drill to be tethered off while being used at height.
- 10 lb. (4.5 kg) load rating.







- · Holster adjusts to fit most hand-held radios, cell phones, and many other devices.
- Can be worn from belt or harness.
- A Micro D-Ring can be placed on the back of a device, and can then be tethered to a D-ring on the front of the Adjustable Radio Holster using a 1500065 Clip2Loop Coil Tether.

1500089 Adjustable Radio Holster, Clip2Loop Coil Tether and Micro D-Ring

3M™ DBI-SALA® Tool Pouches



- 1500132 **Utility Pouch**
- Features two outside pockets for storing spud wrenches and two inner pockets for storing additional tools.
- Tools can be tethered to D-rings on the inside and outside of the pouch.
- Adjustable side-release closure system helps prevent objects from falling out when the pouch isn't being used.

1500130 Utility Pouch with Zipper Closure



Small Parts Pouches

- Self-closure system traps objects inside, making it nearly impossible for objects to fall out once placed in the bag.
- Easy to retrieve objects since no opening or closing is necessary.
- Compatible with most tool belts; belt loops located on back of pouch.

| Part # | Description |
|---------|--|
| 1500123 | Small Parts Pouch, extra deep canvas black |
| 1500121 | Small Parts Pouch, canvas orange |
| 1500120 | Small Parts Pouch, canvas camo |
| 1500122 | Small Parts Pouch, vinyl yellow |
| 1500119 | Small Parts Pouch, canvas black |

3M™ DBI-SALA® Safe Buckets

With an integrated closure system that helps prevent dropped objects, these Safe Buckets are designed to be the perfect companion for workers at height carrying heavy loads.

1500134

Standard Safe Bucket

- Built-in connection points.
- Canvas version is load rated for 100 lb (45.4 kg), and vinyl load rated for 250 lb (113.4 kg).
- Integrated carabiner and hoisting strap.
- Durable material helps prevent punctures.





1500134

1500140

Selection guide:

| Part # | Load rating | Closure system | Body material | Height/diameter | Capacity |
|---------|-------------------|----------------|---------------|-------------------------------|---|
| 1500134 | 100 lb (45.4 kg) | Hook and loop | Canvas | 15"/12.5" (38 cm/31.75 cm) | 1840 in. ³ (4673.6 cm ³) |
| 1500133 | 100 lb (45.4 kg) | Drawstring | Canvas | 15"/12.5" (38 cm/31.75 cm) | 1840 in. ³ (4673.6 cm ³) |
| 1500140 | 250 lb (113.4 kg) | Hook and loop | Vinyl | 15"/12.5" (38 cm/31.75 cm) | 1840 in. ³ (4673.6 cm ³) |
| 1500139 | 250 lb (113.4 kg) | Drawstring | Vinyl | 15"/12.5" (38 cm/31.75 cm) | 1840 in. ³ (4673.6 cm ³) |



Closure systems

Every Safe Bucket features either a unique drawstring or a locking hook and loop closure system that acts as an extra layer of spill-protection during transport and lifting. Colourful indicator tabs provide quick visual cues to indicate whether the bucket is in lockdown mode or easy-access mode.



1500141

Hard-Body Safe Bucket Insert

- Converts a standard soft-body Safe Bucket into a hard-body Safe Bucket.
- Our reusable hard-body Safe Bucket insert keeps your Safe Bucket standing upright, making it easier to stage tools and stay productive.
- Integrated inner pockets allow tools to be holstered and organized quickly.

Additional Information

AWARNING

Compliant fall protection and emergency rescue systems help prevent serious injuries associated with fall events. Users must read and understand the User Instructions provided with the product, and must be properly trained by their employers in the safe use of these systems before using them, per OSHA 1910.140 and 1926.503 or applicable local standards. Misuse or failure to follow warnings and instructions may result in serious personal injury or death. For proper use, see supervisor, User Instructions, or call 800-328-6146 (Opt. 1).

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

3M, DBI-SALA, Cynch-Lok, Delta, Delta Vest, ExoFit, ExoFit NEX, Flexiguard, Force, Lad-Saf, Nano-Lok, Rollgliss, Salalift, Sayfl ink, ShockWave, STRATA, and Ultra-Lok are registered trademarks of 3M. Kevlar, Nomex and Technora are trademarks of their respective owners.



3M Fall Protection 3833 SALA Way Red Wing, MN 55066 USA

Phone 800.328.6146
Email 3mfallprotection@mmm.com
Web 3M.com/FallProtection

Please recycle. Printed in USA. © 3M 2022. All rights reserved.

