



Technical Data Sheet

3M™ ScotchPad™ Repositionable Tape Pad
802



[Product Details](#)

Product Description

3M™ ScotchPad™ Repositionable Tape Pad 802 are pre-cut pads composed of lined sheets of low adhesion tape and can be easily applied to a surface, removed, and reapplied to another surface. The conformable acetate backing and Post-it® adhesive in these sheets give excellent long aging characteristics. The matte surface can be written on.

Product Features

- Paper liner at one end of sheet.
- Cleanly removable from most surfaces.
- Will not yellow or stayd
- Will not dry out, harden, or become brittle.
- Matte surface can be written on with pen, pencil, and other writing implements.
- Almost invisible appearance when applied.
- Labor saving and portable.
- Will hold a note or label which can be moved or peeled away from the tape without damage.
- Corrections, directions, changes can be noted on surface.
- When copies are made the tape will not shadow.
- Can be read through easily.
- Will stay supple and protect the surface below it from moisture and aging.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Clear
Adhesive Type		Post-it® low adhesion adhesive
Backing		Acetate
Total Tape Thickness	ASTM D3652	0.051 mm (2 mil)

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Value
180° Peel Adhesion	ASTM D3330	23 °C (73 °F)	0.18 N/cm (1.5 oz/in) ¹
Elongation at Break	ASTM D3759		15 %
Tensile Strength	ASTM D3759		26.5 N/cm (15 lb/in)

¹ 304 mm/min (12 in/min)

Handling/Application Information

Application Techniques

3M™ ScotchPad™ Repositionable Tape Pad 802 sheets will remove cleanly from most office papers, manila folders, painted wall board, wallpaper, finished woods, metals and plastics, but test the product before using. Avoid applications on lacquered finishes, blackboards, CIBA chrome photographic paper, lexan plastic and leather, because adhesive will shred on these surfaces. Removal is possible with a dry tissue, soft eraser, window cleaner or rubbing alcohol.

Storage and Shelf Life

Store under normal conditions of 4° to 27°C (40° to 80°F) and 40 to 50% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Available Sizes

Attribute Name	Value
Product Size	2 in x 4
	4 in x 6 in
Standard Size	4 in x 6 in (25 sheets per pad)

Available Sizes - Detailed

Tape pads are available in various sizes. Consult your local 3M sales representative.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/packaging.