



Technical Data Sheet

3M™ ScotchPad™ Premium Hang Tabs 1075



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ ScotchPad™ Hang Tabs are designed to stick to a product surface and to then hang that product from a peg for display purposes. 3M™ ScotchPad™ Hang Tab 1075 is composed of a 3M™ Scotchpar™ polyester that is the most abrasion resistant backing with the most consistent pressure sensitive hot melt adhesive system available and is laminated to a thick polyester top in which a hole is punched for the peg. This precut tab is prestacked 10 high in convenient pads for easy manual application and portability. It is handy for hanging shrink-wrapped packages as well as for in-store repair of damaged packaging. Because the whole tab is not rigid, the tab can be applied before case packing a product and will stay folded down until it is unpacked and hung up.

Product Features

- Adheres instantly to shrink-wrapped packages, cartons, and product surfaces.
- Strong abrasion, edge tear and split resistant backing.
- ScotchPad hang tabs 1074/1075/1076 have bendable tabs.
- Hold products out where they are easy to see.
- Strong film edge resists tearing and ripping of these hang tabs.
- Stiff polyester header gives clean product display.
- Clear tape does not obscure graphics.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Substrate	Value
Adhesive Type			Pressure sensitive hot melt rubber-resin adhesive
Backing			Biaxially oriented 3M™ Scotchpar™ polyester film
Total Hang Tab (Top)	ASTM D3652		0.343 mm (13.5 mil)
Holes			Delta - works with double pegs
Holding Power	ASTM D3654	Fiberboard	14,000+ min
Header Laminate			Copolyester PETG

Test Method: ASTM D3652

Attribute Name	Value
Total Tape Thickness	0.089 mm (3.5 mil)
Thickness Laminate	0.254 mm (10 mil)
Backing Thickness	0.051 mm (2 mil)

Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	6 N/cm (78 oz/in) ¹

¹ 300 mm/min (12 in/min)

Test Method: ASTM D3759

Attribute Name	Test Condition	Value
Elongation at Break		130 %
Tensile Strength	Machine Direction	117 N/cm (67 lb/in)
Tensile Strength	Cross Direction	121 N/cm (69 lb/in)
Tensile Strength		117 N/cm ¹

¹ Machine Direction

Handling/Application Information

Application Techniques

Application of 3M™ ScotchPad™ Hang Tabs is most easily accomplished at room temperature because at colder temperatures, approaching 32°F (0°C), the adhesive becomes firmer. Once applied, the ScotchPad hang tabs will perform well throughout the normal temperature ranges typically encountered by packaged products in shipping and storage environments to a surface that allows a straight vertical position with no peel. Unless testing is done to confirm a ScotchPad hang tab will hold a heavier product, 3/4 lb. or less is the recommended weight unit. Some well-balanced three pound products have been displayed using two ScotchPad hang tabs placed on one object in opposing placement. Pre-testing is advised. Three ScotchPad 1074/1075/1076 hang tabs can be used to hold thick flat samples in a 3-ring binder. Because the whole tab is not rigid, they can also be preapplied to products and folded down before shipping thus eliminating excessive shipping bulk. Some manufacturers pack extra pads in with product so the retailer can repair broken or damaged package chipboard headers thus reducing profitstealing unsellables.


Storage and Shelf Life

Store under normal conditions of 4° to 27°C (40° to 80°F) and 40 to 50% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Product Size	2in x 2in

Available Sizes - Detailed



Delta hole
ScotchPad
hang tab 1075
2 in. x 2 in.
10 per pad

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division
3M Center, St. Paul, MN 55144-1000
www.3M.com

©3M 2025 (4/25)