



Technical Data Sheet

3M™ Double Coated Splicing Tape 9738R



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Splicing Tapes 9738 and 9738R are similar products, but produced with a nonwoven tissue carrier. These products offer good temperature resistance and adhere well to kraft and coated papers. These high performance splicing tapes are appropriate for use on paper, plastics and other continuous web processes. Especially appropriate in the manufacture of corrugated paper.

Product Features

- Versatile splicing tape product meets a wide variety of application requirements.
- Excellent peel, tack and shear.
- Adheres well to Kraft and coated papers.
- Moisture resistant.
- Good temperature resistance.
- Excellent performance at high and low temperatures.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Red
Adhesive Carrier		Non-Woven Tissue
Total Tape Thickness	ASTM D3652	0.1092 mm (4.3 mil)
Carrier Thickness		0.033 mm (1.3 mil)
Liner		55# Densified Kraft Paper
Liner Thickness		0.081 mm (3.2 mil)
Primary Liner Color		White

Typical Performance Characteristics

Temperature: 22 °C (72 °F)

Attribute Name	Test Condition	Substrate	Backing	Value
180° Peel Adhesion		Steel	2 mil Aluminum Foil	5.5 N/cm (50 oz/in) ¹
Static Shear	1000g			>500 h ²

¹ 12 in/min (300 mm/min)

² 1 in x 1 in sample area, test terminated after 10,000 minutes

Attribute Name	Value
Minimum Continuous Temperature	-23 °C (-10 °F)
Short Term Temperature Resistance	149 °C (300 °F) ¹
Long Term Temperature Resistance	127 °C (260 °F) ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Handling/Application Information

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact. Firm application pressure helps ensure better adhesive contact and improve bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry, and uniform. Some typical surface cleaning solvents are isopropyl alcohol or heptane.*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

Application Equipment

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

Storage and Shelf Life

Store in original cartons at 70°F (21°C) and 50% relative humidity.

If stored under proper conditions, product retains its performance and properties for 12 months from date of manufacture.

Available Sizes - Detailed

Please contact your 3M sales representative or contact 3M customer service at 1-800-362-3550 for details on available sizes.

Recognition/Certification

MSDS: 3M has not prepared MSDS's for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, these products should not present a health and safety hazard. However, use or processing of these products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

TSCA: These product are not defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

3M is a trademark of 3M Company.
©3M 2008 (3/08)