



# Technical Data Sheet

3M™ ScotchPad™ Pouch Tape Pads  
830/830CP



[Product Details](#)



[Regulatory Info/SDS](#)

## Product Description

3M™ ScotchPad™ Pouch Tape Pads are pre-cut pressure-sensitive tapes with a sticky border and a printed, non-tacky center section that comes either as a standard or custom printed pouch which is clear and becomes a “see-through” window. Each piece of tape is coupled with a strip of liner material for easy handling and application without the need of a dispenser. The product provides a quick, simple, and secure method of attaching and protecting packing lists and other documents on a wide range of shipping containers. With the liner left in place, the product may be used as an open-ended pouch, allowing work tickets, inventory lists, and other shipping documents to be inserted or removed as necessary.

830 Pouch Tapes are pre-printed with the phrase “Documents Enclosed”. 830CP Pouch Tapes are custom printed with your custom logo or message.

## Product Features

- Liner tab.
- Pre-cut individual sheets.
- Strong and abrasion-resistant.
- Easy removal of single sheets.
- Aggressive adhesive provides excellent adhesion to various surfaces.
- Easy removal of liner.
- Portable, lightweight.
- Space-saving.
- Standard and custom messages available.
- Consistent dimensions.
- Exact replication of sheet size and border print.
- Helps prevent labels, invoices, and such from being scuffed off.
- Easy to read label.
- Holds securely to most cartons and containers; keeps packing list or label on package for safe delivery.
- Fast application; saves time.
- Easy to carry in pad form.
- Calls attention to and prevents disposal of documents.
- Excellent bar code protection.
- Customer’s name, address, and logo or telephone and advertisement may be printed on the custom pouch tape pads.

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Attribute Name	Test Method	Value
Color		Transparent film with orange/white message border.
Adhesive Type		Pressure-sensitive rubber resin
Backing		3M™ Scotchpro™ polypropylene film
Total Tape Thickness	ASTM D3652	0.066 mm (2.5 mil)

Attribute Name	Value
----------------	-------

Attribute Name	Value
Available Formats	25 Sheets Per Pad 40 Pads per Carton 5 Cartons per Case 200 Pads per Case 5000 Applications per Case

## Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Test Condition	Substrate	Value
180° Peel Adhesion	ASTM D3330	22 °C (72 °F)			5.5 N/cm (50 oz/in) <sup>1</sup>
Elongation at Break	ASTM D3759				160 %
Tensile Strength			Crosswise		52.5 N/cm (30 lb/in)
Tensile Strength			Lengthwise		105 N/cm (60 lb/in)
Holding Power	ASTM D3654			Fiberboard	8,000+ min

<sup>1</sup> 12 in/min (300 mm/min)

## Storage and Shelf Life

It is recommended that 3M™ ScotchPad™ Pouch Tape Pads be stored below 85°F (29°C). To obtain best performance, use this product within 18 months from date of manufacture.

## Available Sizes

Attribute Name	Value
Tack Free Area	4 x 4 7/8 in
Tape Sheet Dimensions	5 x 6 in
Window (Readable Area)	3 1/8 x 4 1/2 in

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M  
Closure and Masking Systems Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com

©3M 2003 (5/03)