



Technical Data Sheet

Scotch® Pouch Tape Sheet
830/830CP/830CN



[Additional Info](#)

Product Description

Scotch® Pouch Tape Sheets 830, 830CP and 830CN are pre-cut, pressure-sensitive adhesive tapes designed for efficient document attachment and protection on shipping containers. Each sheet features a sticky border surrounding a non-adhesive, printed center section, forming a transparent “see-through” pouch window. 25 individual sheets are stacked to create a pad. The tapes are available in standard or custom-printed versions.

Each individual sheet includes a liner strip that enables easy handling and application without the need of a dispenser. This design allows for a fast, secure, and convenient method of adhering packing lists, invoices, or other shipping documents to cartons and containers.

When the liner remains in place, the tape can function as an open-ended pouch, allowing users to insert, remove, or update work tickets, inventory sheets, or shipping documents as needed.

- 830 Pouch Tape: Standard version pre-printed with “Documents Enclosed”
- 830CP Pouch Tape: Custom version printed with your company logo or personalized message
- 830CN Pouch Tape: Standard version pre-printed with "Documents Enclosed / Documentos Adjuntos". Only available in Canada

Product Features

- Protects documents and labels from scuffing or damage
- Pre-cut sheets for convenience and consistency
- Aggressive adhesive bonds to most surfaces
- Available with standard or custom printing options
- Clear window ensures easy label visibility and barcode scanning

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Transparent film with orange/white message border.
Adhesive Type		Pressure-sensitive rubber resin
Backing		Biaxially Oriented Polypropylene
Total Tape Thickness	ASTM D3652	0.066 mm (2.6 mil)

Attribute Name	Value
Available Formats	25 Sheets Per Pad
	40 Pads per Carton
	5 Cartons per Case
	200 Pads per Case
	5000 Applications per Case

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Test Condition	Value
180° Peel Adhesion	ASTM D3330	23 °C (73 °F)		55 N/100mm (50 oz/in) ¹
Elongation at Break	ASTM D3759			130 %
Tensile Strength	ASTM D3759		Machine Direction	620 N/100mm (35.4 lb/in)

¹ 300 mm/min (12 in/min)

Handling/Application Information

Directions for Use

- Apply to a clean, dry surface for optimal adhesion
- Press firmly along the borders to ensure full contact
- For reusable pouch function, leave liner partially or fully in place

Application Examples

- Attaching packing lists, invoices, and bills of lading to cartons or containers
- Protecting production, inventory, or shipping documents
- Displaying barcodes, identification labels, or quality records

Storage and Shelf Life

Store under normal conditions of 4° to 27°C (40° to 80°F) and 40 to 50% relative humidity in the original packaging, out of direct sunlight.

For best performance, use this product within 18 months from date of manufacture

Available Sizes

25 sheets per pad

Attribute Name	Value
Tack Free Area	10 x 13 cm (4 x 5 in)
Tape Sheet Dimensions	13 x 15 cm (5 x 6 in)
Window (Readable Area)	8 x 11.4 cm (3 1/8 x 4 1/2 in)

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or

packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division
3M Center, St. Paul, MN 55144-1000
www.3M.com

©3M 2025 (12/25)