



## Technical Data Sheet

### 3M™ Double Coated Tape 9741R



[Product Details](#)



[Regulatory Info/SDS](#)

#### Product Description

3M™ Double Coated Tape 9741R is a 6.5 mil double coated tape utilizing a 0.5 mil hand-tearable polyester film heavily coated on both sides with 3 mils of an ultra high peel acrylic adhesive system. The heavy adhesive deposition allows for superior bonding and conformability to irregular as well as flat surfaces. The special acrylic adhesive, bonds well to most substrates including low surface energy plastics. This product provides excellent U.V. and heat resistance. Super aggressive splicing tape for demanding applications.

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Typical Physical Properties

| Attribute Name       | Test Method | Value              |
|----------------------|-------------|--------------------|
| Color                |             | Red                |
| Adhesive Type        |             | Acrylic            |
| Adhesive Carrier     |             | Polyester          |
| Total Tape Thickness | ASTM D3652  | 0.165 mm (6.5 mil) |
| Adhesive Thickness   |             | 0.076 mm (3 mil)   |
| Carrier Thickness    |             | 0.013 mm (0.5 mil) |
| Liner                |             | 55# Glassine       |
| Liner Thickness      |             | 0.07 mm (3 mil)    |

#### Typical Performance Characteristics

Substrate: Steel

Temperature: 23 °C (73 °F)

Backing: 2 mil Aluminum Foil

| Attribute Name     | Value                            |
|--------------------|----------------------------------|
| 180° Peel Adhesion | 13 N/cm (120 oz/in) <sup>1</sup> |

<sup>1</sup> 304 mm/min (12 in/min)

| Attribute Name                    | Value                       |
|-----------------------------------|-----------------------------|
| Minimum Continuous Temperature    | -40 °C (-40 °F)             |
| Short Term Temperature Resistance | 93 °C (200 °F) <sup>1</sup> |
| Long Term Temperature Resistance  | 49 °C (120 °F) <sup>2</sup> |

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## **Handling/Application Information**

### **Application Examples**

For bonding irregular surfaces, bonding to plastics and metal profile extrusions, bonding of decorative trim

### **Application Techniques**

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.\*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

\*Note: Carefully read and follow the manufacturer's precautions and directions for use when using solvents.

### **Application Equipment**

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes - Detailed**

Please contact your 3M sales representative or customer service at 1-800-362-3550 for sizes and availability.

## **Recognition/Certification**

**MSDS:** 3M has not prepared an MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, this product should not present a health and safety hazard. However, use or processing of this product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

**TSCA:** This product is not defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division  
3M Center, St. Paul, MN 55144-1000  
[www.3M.com](http://www.3M.com)

3M is a trademark of 3M Company.  
©3M 2024 (9/24)