



## Technical Data Sheet

### 3M™ Repulpable Double-Coated Splicing Tape 900B



[Regulatory Info/SDS](#)

#### **Product Description**

3M™ Repulpable Double-Coated Splicing Tape 900B has a light-weight tissue coated on both sides with a blue, repulpable adhesive and furnished on a repulpable easy-release paper liner.

#### **Product Features**

- Can be used for splicing of many LWC (light weight coated) papers, particularly for coated gravure papers. It has also performed well in many other finished splice applications, even with “alkaline coatings” and with stearate sizing.
- Packing in sealed plastic bags helps assure constant moisture content of unused tape.
- Water solubility and alkali dispersability are excellent and eliminate danger of contaminating the paper mill broke with non-repulpable material. (Poor quality paper and plugged Fourdrinier screens can be caused by non-repulpable, rubber-base splicing media.)
- All components of the adhesive and backing meet the requirements of indirect food additive regulations as described under 21 CFR 176.170 (Components of paper and paperboard in contact with aqueous and fatty food) and 21 CFR 176.180 (Components of paper and paperboard in contact with dry foods).

#### **Technical Information Note**

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### **Typical Physical Properties**

Attribute Name	Test Method	Value
Color		Blue
Adhesive Type		Repulpable
Total Tape Thickness	ASTM D3652	0.06 mm (2.5 mil)
Repulpability	TAPPI UM-213, Procedure A	Tape - Completely Liner - Completely
Bond Strength		Delaminates most papers (including many LWC coating formulations, however adheres well to many other papers, too)
Temperature Resistance		Up to 204 °C (Up to 400 °F) <sup>1</sup>
Liner		Repulpable, semi-bleached kraft with easy-release treatment

<sup>1</sup> Web temperature: As tested in laboratory, results may vary depending on machine and web tensions, nature of paper surface, application pressure, etc. which are outside of 3M control.

#### **Typical Performance Characteristics**

Attribute Name	Value
Short Term Temperature Resistance	204 °C (400 °F) <sup>1</sup>

<sup>1</sup> Short Term (minutes, hour)

## **Handling/Application Information**

### **Application Examples**

- Overlap finished splices in a paper mill (especially on many papers with LWC and other new coating formulations).
- Transfer (pull through) splices in Supercalenders.

### **Application Techniques**

For optimum results, firm, even rub down pressure must be applied to the taped area to create the best possible adhesion between the tape and paper surface. A plastic squeegee or similar tool can help achieve the proper uniform pressure.

## **Industry Specifications**

21 CFR 176.170  
21 CFR 176.180

### **FDA Statement**

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

## **Available Sizes**

<b>Attribute Name</b>	<b>Value</b>
Standard Roll Length	33 m (36 yd)

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division  
3M Center, St. Paul, MN 55144-1000  
[www.3M.com](http://www.3M.com)

3M is a trademark of 3M Company.  
©3M 2024 (6/24)