



Technical Data Sheet

3M™ Carry Handle Tape 8346HP



[Product Details](#)

Product Description

3M™ Carry Handle Tape 8346HP is a high-performance tape featuring a durable polyester film backing and an aggressive rubber resin adhesive especially suited for high shear performance carrying handles that allows for items up to 20 lbs. to be carried easily.

Product Features

- Excellent adhesion to most shrink film over wraps that helps assure good attachment of handle
- No dwell time necessary, adheres immediately and fast to apply.
- Efficient application on automated handle application equipment and good handling properties.
- Fewer roll changes on application equipment which increases production rate for lower unit cost.
- Designed for use on automatic carry handle application equipment with packages weighing 20 lbs. (9.0 kg) or less.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Clear
Adhesive Type		*Synthetic rubber resin.
Backing		Polyester Film
Backing Thickness	AFERA 4006	0.05 mm (2 mil)
Total Thickness	ASTM D3652	0.085 mm (3.4 mil)

Attribute Name	Value
*Note	Requires no heat, moisture, or solvent activation prior to use.

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Substrate	Value
180° Peel Adhesion		22 °C (72 °F)	High Density Polyethylene (HDPE)	5.7 N/cm (52 oz/in)
Tensile Strength	AFERA 4004			17.4 N/cm (67 lb/in)
Elongation at Break	AFERA 4005			130 %

Handling/Application Information

Application Techniques

Recommended Surfaces

- Paperboard printed and unprinted.
- Corrugated cardboard.
- Polyethylene and polypropylene (strong shrink film/poly bags).
- Polyester film.
- Polyvinyl chloride (PVC) film.

Surfaces That Should Be Reviewed For Suitability

- Wax coated/siliconized surfaces.
- Wet surfaces (moisture condensation).
- Cold surfaces (<50°F [10°C]).
- Some lacquer coated board.
- Rough textured surfaces on which tape surface contact is significantly reduced.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Available Sizes

Attribute Name	Value
Core Size (ID)	152 mm (6 in)
Standard Roll Length	3000 (level wound) m (3280 (level wound) yd)
Standard Width	25.4 mm (1 in)

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division
3M Center, St. Paul, MN 55144-1000
www.3M.com

3M is a trademark of 3M
©3M 2014 (1/14)