



# Technical Data Sheet

## 3M™ Window and Door Flashing Tape 8067



[Product Details](#)

### Product Description

3M™ Window and Door Flashing Tape 8067 is a self-adhered, waterproof flashing membrane designed for sealing around openings and penetrations in exterior walls. This product has a unique acrylic pressure sensitive adhesive that aggressively sticks and stays stuck both at lower and higher application temperatures than traditional flashing tapes. It even adheres to damp surfaces. The proprietary backing seals around hand driven nails and staples to prevent moisture intrusion. This backing is also tough, resists punctures and tears, yet it is thin to fit conveniently into corners and under siding. The split paper release liner provides fast application with easy and accurate positioning of the tape.

### Product Features

- Very low vapor transmission rate.
- Meets AAMA 711-05 Voluntary Specification for Self Adhering Flashing Use for Installation of Exterior Wall Fenestration Products:  
Adhesion Type Rating Type A (no need for primer at tested conditions) Thermal Exposure Class 3 - Highest level (176°F/80°C at 7 days)
- Nail Sealability: Passes both ASTM D1970 and ASTM E331/547 (per AAMA 711-05, Annex 1) before and after thermal cycling.
- Meets the criteria to contribute to the Environmental Quality ("EQ") Credit 4.1: Low-Emitting Materials: Adhesives & Sealants under the United States Green Building Council's Rating System for New Construction & Major Renovations (LEED-NC), Version 2.2, Core and Shell (LEED-CS), Version 2.0, and Commercial Interiors (LEED-CI), Version 2.0.
- High tack adhesive sticks and stays stuck to most common building materials.
- Unique adhesive even adheres to damp surfaces.
- Adhesive provides an unusual combination of both cold temperature and hot temperature adhesion to most substrates, which can extend the construction season in many climates.
- No adhesive melting or staining in summer heat.
- Proprietary backing seals around nails and staples to prevent moisture intrusion.
- Unique backing is thin to conveniently fit into corners and under siding.
- Tough backing resists punctures and tears during application.
- Resists UV exposure for up to 12 months.
- Can be installed at temperatures as low as 0°F (-18°C) and as warm as 150°F (66°C).
- Compatible with many building sealants: No adverse reaction with synthetic rubber, butyl, polyurethane, silicone and silane terminated hybrid sealants.
- Split release liner provides fast application with easy and accurate positioning of the tape.
- 12 inch measurement markings for ease in cutting to the desired length.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

| Attribute Name           | Test Method | Environmental Condition                  | Value            |
|--------------------------|-------------|------------------------------------------|------------------|
| Color                    |             |                                          | Tan              |
| Adhesive Type            |             |                                          | Acrylic          |
| Backing                  |             |                                          | Proprietary Film |
| Water Vapor Transmission | ASTM E96    |                                          | 0.13             |
| Wall Assembly Fire Test  | NFPA 285    |                                          | 5 <sup>1</sup>   |
| Nail Sealability         | ASTM E331   | Initial                                  | Pass             |
| Nail Sealability         | ASTM D1970  | 127 mm(5 inches) water head after 3 days | Dry/Pass         |
| Nail Sealability         | ASTM E331   | After Thermal Cycling                    | Pass             |

<sup>1</sup> Pass as part of various assemblies with foam plastic insulation

| Attribute Name       | Test Method | Value              |
|----------------------|-------------|--------------------|
| Adhesive Thickness   |             | 0.127 mm (5 mil)   |
| Total Tape Thickness | ASTM D3652  | 0.25 mm (9.9 mil)  |
| Carrier Thickness    | ASTM D3652  | 0.13 mm (5 mil)    |
| Backing Thickness    | ASTM D3652  | 0.25 mm (5 mil)    |
| Liner                |             | Heavy Paper, split |

## **Typical Performance Characteristics**

### **90° Peel Adhesion**

Test Method: ASTM D3330

| Dwell Time | Temperature    | Substrate                            | Value                            |
|------------|----------------|--------------------------------------|----------------------------------|
| 72 h       | 23 °C (73 °F)  | OSB                                  | 6.6 N/cm (60 oz/in) <sup>1</sup> |
| 72 h       | 23 °C (73 °F)  | High Density Polyethylene (HDPE)     | 6.6 N/cm (60 oz/in) <sup>1</sup> |
| 72 h       | 23 °C (73 °F)  | Housewrap (Spun bonded polyethylene) | 5.5 N/cm (50 oz/in) <sup>1</sup> |
| 7 d        | 80 °C (176 °F) | Anodized Aluminum                    | 7.7 N/cm (70 oz/in) <sup>1</sup> |

<sup>1</sup> 300 mm/min (12 in/min)

| Attribute Name            | Test Method | Value                   |
|---------------------------|-------------|-------------------------|
| Application Temperature   | AAMA 711-05 | -18-66 °C (0 — 150 °F)  |
| Service Temperature Range | AAMA 711-05 | -40-116 °C (-40-240 °F) |
| Elongation at Break       | ASTM D882   | >700 %                  |
| Flame Spread Index        | ASTM E84    | 25                      |

## **Typical Environmental Performance**

### **90° Peel Adhesion**

Substrate: Anodized Aluminum

Test Method: ASTM D3330

| Dwell Time | Environmental Condition | Value                            |
|------------|-------------------------|----------------------------------|
| 7 d        | Water                   | 7.1 N/cm (65 oz/in) <sup>1</sup> |
|            | After Thermal Cycling   | 8.2 N/cm (75 oz/in) <sup>1</sup> |
|            | After UV Exposure       | 6.6 N/cm (60 oz/in) <sup>1</sup> |

<sup>1</sup> 300 mm/min (12 in/min)

## **Handling/Application Information**

### **Directions for Use**

3M™ All Weather Flashing Tape 8067 is intended to provide a weatherproof seal around openings and penetrations in exterior walls when installed in accordance with these guidelines. The following conditions apply to the use of 3M™ All Weather Flashing Tape 8067:

- Installation Temperature Range: To obtain the best adhesion, 3M™ All Weather Flashing Tape 8067 should be installed when outdoor temperatures range from 0°F (-18°C) up to 150°F (66°C) over clean surfaces that are free from dirt and debris and have not absorbed water. Surfaces should be free of any damaged, unsupported areas, sharp protrusions or voids.
- Adheres to most common building materials. For difficult to stick to surfaces, test flashing tape adhesion before application. Use 3M™ Hi-Strength 90 Spray Adhesive to prime the substrate as needed prior to applying the flashing tape.
- To apply, peel back a few inches of one side of the split paper release liner to position the tape. Remove the liner while applying firm pressure to the flashing tape surface as it comes into contact with the building surface. Repeat this procedure with the remaining side of the paper release liner and tape. Using a roller (rubber, wood or steel "J" roller) apply sufficient pressure along the entire tape surface to ensure a continuous seal and to eliminate trapping air beneath the tape.
- Environmental Conditions: may remain exposed to direct sunlight for up to 12 months.
- Warning: The paper release liner is slippery and should not be walked on at any time. Discard the paper release liner in a designated container.

### **Application Examples**

- Sealing joints around sills, jambs and heads of rectangular windows in wood frame construction.
- Sealing around other wall interruptions in non-roof areas, such as thresholds, dryer vents and hose bibs.
- When installed properly as a concealed flashing in vertical walls in frame construction, it prevents moisture intrusion and avoids the problems caused by water infiltration.

## **Industry Specifications**

- Meets AAMA 711-05 Voluntary Specification for Self Adhering Flashing Use for Installation of Exterior Wall Fenestration Products: Adhesion Type Rating Type A (no need for primer at tested conditions) Thermal Exposure Class 3 - Highest level (176°F/80°C at 7 days)
- Nail Sealability: Passes both ASTM D1970 and ASTM E331/547 (per AAMA 711-05, Annex 1) before and after thermal cycling.
- Meets the criteria to contribute to the Environmental Quality ("EQ") Credit 4.1: Low-Emitting Materials: Adhesives & Sealants under the United States Green Building Council's Rating System for New Construction & Major Renovations (LEED-NC), Version 2.2, Core and Shell (LEED-CS), Version 2.0, and Commercial Interiors (LEED-CI), Version 2.0.
- GreenGuard/GreenGuard Gold Certified for Low Chemical Emissions - UL 2818

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

| Attribute Name       | Value          |
|----------------------|----------------|
| Standard Roll Length | 22.8 m (25 yd) |

## **Available Sizes - Detailed**

### **Available in rolls of:**

2 inches x 75 feet (50 mm x 22,8 m)  
24 rolls/case  
3 inches x 75 feet (76 mm x 22,8 m)  
12 rolls/case  
4 inches x 75 feet (101 mm x 22,8 m) 12 rolls/case  
6 inches x 75 feet (152 mm x 22,8 m)  
8 rolls/case  
9 inches x 75 feet (228 mm x 22,8 m)  
4 rolls/case  
12 inches x 75 feet (305 mm x 22,8 m)  
4 rolls/case

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/isd](http://3M.com/isd)

3M is a trademark of 3M Company.  
©3M 2025 (4/25)