



Technical Data Sheet

3M™ Scotch-Weld™ Epoxy Adhesive DP125 Gray



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

Scotch-Weld epoxy adhesive DP125 Gray is a filled, pigmented version of the Scotch-Weld epoxy adhesive DP125 Translucent and has similar performance and flexibility properties.

Available in bulk containers as 3M™ Scotch-Weld™ Epoxy Adhesive 125 B/A Gray.

Product Features

- 25 minute worklife
- Flexible
- Gray
- High peel and shear strength
- 1:1 mix ratio
- Recognized as meeting UL 94 HB

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Test Method	Temperature	Value
Accelerator Net Weight			1.01 — 1.05 g/cm ³ (8.4 — 8.8 lb/gal)
Mix Ratio by Volume (B:A)			1:1
Base Resin			Epoxy
Base Color			Dark Gray
Accelerator Resin			Amine
Accelerator Color			Clear Amber
Base Net Weight			1.23 — 1.28 g/cm ³ (10.3 — 10.7 lb/gal)
Base Viscosity	3M C1d	27 °C (80 °F)	35000 - 75000 cP ¹
Accelerator Viscosity	3M C1d	27 °C (80 °F)	22000 - 33000 cP ¹
Mix Ratio by Weight (B:A)			1.2:1

¹ Procedure involves Brookfield RVF, #7 spindle, 20 rpm. Measurement taken after 1 minute rotation.

Typical Mixed Physical Properties

Attribute Name	Temperature	Value
Open Time		25 min ¹
Time to Handling Strength	23 °C (73 °F)	2.5 h

¹ Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend on adhesive temperature. Hotmelts: The approx. bonding range of a 3.2 mm (1/8 in) bead of molten adhesive on a non-metallic surface.

Typical Physical Properties

Attribute Name	Value
Cured Color	Gray

Typical Cured Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Shore D Hardness	ASTM D2240	70

Typical Performance Characteristics

Overlap Shear Strength

Temperature: 23 °C (73 °F)

Test Method: ASTM D1002, ISO 4587

Dwell Time	Substrate	Surface Prep	Value
7 d	ABS	IPA Wipe	653 (AF) lb/in ² ¹
7 d	Polyvinyl chloride (PVC)	IPA Wipe/Abrade/IPA Wipe	653 (AF) lb/in ² ¹
7 d	Polycarbonate (PC)	IPA Wipe	559 (MF) lb/in ² ¹
7 d	Acrylic (PMMA)	IPA Wipe	315 (AF) lb/in ² ¹
24 h	Aluminum	Etched	4,200 lb/in ² ¹
7 d	FRP (Epoxy)	Acetone/Abrade/Acetone	4402 (AF/SF) lb/in ² ¹
7 d	CRS	Acetone/Abrade/Acetone	2084 (MF) lb/in ² ¹
7 d	FRP (Polyester)	Acetone/Abrade/Acetone	1834 (MF/SF) lb/in ² ¹

¹ 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber

Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)

Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Overlap Shear Strength

Substrate: Aluminum

Surface Prep: Sandblasted

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Test Condition	Value
-40 °F	2,426 lb/in ² ¹
49 °C (120 °F)	428 lb/in ² ¹
82 °C (180 °F)	220 lb/in ² ¹
200 °C (392°F)	170 lb/in ² ¹

¹ Overlap shear (OLS) strengths were measured on 25 mm wide x 13 mm overlap (1 x 0.5 in) specimens on 25 x 102 x 1.5 mm (1 x 4 x 0.06 in) substrates.

Jaw separation 2.5 mm/min (0.1 in/min). 0.25 mm (10 mil) bondline.

Substrate: Aluminum

Attribute Name	Test Method	Temperature	Test Condition	Surface Prep	Value
Bell Peel	ASTM D3167	23 °C (73 °F)	23 °C	Etched	79 lb/in width ¹
Impact Shear Strength	ASTM D950		Pendulum Impact		19.6 J ²

¹ Floating roller peel; adhesives allowed to cure for 24 hours @RT; 25 mm (1 in) wide samples;

Samples pulled at 15 mm/min (6 in/min)

Cohesive (CF), Adhesive (AF) and Substrate (SF) Failure

² 21.7J Hammer

Test Method: ASTM D638, ISO 527

Attribute Name	Temperature	Test Condition	Value
Elongation	23 °C (73 °F)	10 mm/min	95 % ¹
Modulus			2,842 lb/in ²
Tensile Strength			2,155 lb/in ²

¹ Type IV dogbone

Typical Environmental Performance

Overlap Shear Strength

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Environmental Condition	Substrate	Surface Prep	Value
Gasoline: 500 hrs	Aluminum	MEK,Sandblast,MEK	21 lb/in ² ¹
Salt water (5% wt in water): 500 hrs	Aluminum	MEK,Sandblast,MEK	1,528 lb/in ² ¹
Water: 500 hrs	Aluminum	MEK,Sandblast,MEK	1,454 lb/in ² ¹
49 °C + 80 %RH	PVC	50/50 IPA	911 lb/in ² ¹
85 °C + 85 %RH: 500 hrs	Aluminum	MEK,Sandblast,MEK	2,328 lb/in ² ¹
200°C / 30 minutes	Cold Rolled Steel	Acetone/Abrade/Acetone	2,371 lb/in ² ¹
Diesel Fuel: 500 hrs	Aluminum	MEK,Sandblast,MEK	2,407 lb/in ² ¹
200°C / 30 minutes	Aluminum	MEK,Sandblast,MEK	2,886 lb/in ² ¹

¹ 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber

Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)

Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Electrical and Thermal Properties

Attribute Name	Test Method	Test Condition	Value
Glass Transition Temperature (Tg)			34 °C ¹
Thermal Conductivity	ASTM E1530	50 °C, 25 psi	0.24 W/m/K
Coefficient of Thermal Expansion		Above Tg	206 x 10 ⁻⁶ m/m/°C ²
Coefficient of Thermal Expansion		Below Tg	93.8 x 10 ⁻⁶ ²

¹ Glass Transition Temperature (Tg) determined using DSC Analyzer with a heating rate of 10 °C per minute. Second heat values given.

² CTE determined using TMA Analyzer using a heating rate of 3 °C per minute. Second heat values given.

Handling/Application Information

Directions for Use

1. For high strength structural bonds, paints, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user. For specific surface preparations on common substrates, see the section on surface preparation.

2. Use gloves to minimize skin contact. Do not use solvents for cleaning hands.

3. Mixing.

For Duo Pak Cartridges

3M™ Scotch-Weld™ Epoxy Adhesives DP125 Translucent and Gray are supplied in a dual syringe plastic duo-pak cartridge as part of the 3M™ EPX™ Applicator System. To use, simply insert the duo-pak cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Next, remove the duo-pak cartridge cap and expel a small amount of adhesive to be sure both sides of the duo-pak cartridge are flowing evenly and freely. If automatic mixing of Part A and Part B is desired, attach the EPX applicator mixing nozzle to the duo-pak cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after uniform color is obtained.

For Bulk Containers

Mix thoroughly by weight or volume in the proportions specified in the typical uncured properties section. Mix approximately 15 seconds after uniform color is obtained.

4. For maximum bond strength, apply adhesive evenly to both surfaces to be joined.

5. Application to the substrates should be made within 20 minutes. Larger quantities and/or higher temperatures will reduce this working time.

6. Join the adhesive coated surfaces and allow to cure at 60°F (16°C) or above until completely firm. Heat up to 200°F (93°C), will speed curing. These products will cure in 7 days @ 75°F (24°C).

7. Keep parts from moving during cure. Contact pressure necessary. Maximum shear strength is obtained with a 3-5 mil bond line.

8. Excess uncured adhesive can be cleaned up with ketone type solvents.*

*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow manufacturer's precautions and directions for use.

Adhesive Coverage (typical): A 0.005 in. thick bondline will yield a coverage of 320 sqft/gallon.

Surface Preparation

For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user.

The following cleaning methods are suggested for common surfaces:

Steel:

1. Wipe free of dust with oil-free solvent such as acetone, isopropyl or alcohol solvents.*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with solvent to remove loose particles.*
4. If a primer is used, it should be applied within 4 hours after surface preparation.

Aluminum:

1. Alkaline Degrease: Oakite 164 solution (9-11 oz./gallon water) at 190°F ± 10°F for 10-20 minutes. Rinse immediately in large quantities of cold running water.
2. Acid Etch: Place panels in the following solution for 10 minutes at 150°F ± 5°F .
Sodium Dichromate 4.1 - 4.9 oz./gallon
Sulfuric Acid, 66°Be 38.5 - 41.5 oz./gallon
2024-T3 aluminum (dissolved) 0.2 oz./gallon minimum
Tap water as needed to balance
3. Rinse: Rinse panels in clear running tap water.
4. Dry: Air dry 15 minutes; force dry 10 minutes at 150°F ± 10°F.
5. If primer is to be used, it should be applied within 4 hours after surface preparation.

Note: Read and follow supplier's environmental, health, and safety documentation for these chemicals prior to preparation of this solution.

Plastics/Rubber:

1. Wipe with isopropyl alcohol.*
2. Abrade using fine grit abrasives.
3. Wipe with isopropyl alcohol.*

Glass:

1. Solvent wipe surface using acetone or MEK.*
2. Apply a thin coating (0.0001 in. or less) of primer such as 3M™ Scotch-Weld™ Metal Primer EC3901 to the glass surfaces to be bonded and allow the primer to dry before bonding.

***Note:**When using solvents, extinguish all ignition sources, including pilot lights, and follow manufacturer's precautions and directions for use.

Application Equipment

For small or intermittent applications the 3M™ EPX™ Applicator System is a convenient method of application.

For larger applications these products may be applied by use of flow equipment.

Two part meter/mixing/proportioning/dispensing equipment is available for intermittent or production line use. These systems may be desirable because of their variable shot size and flow rate characteristics and are adaptable to many applications.

Industry Specifications

UL 94 HB

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) in the original, unopened packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

Automotive Disclaimer**Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M, Scotch-Weld and EPX are trademarks of 3M Company.
©3M 2025 (1/25)