



## Technical Data Sheet

### 3M™ Scotch-Weld™ Multi-Material & Composite Urethane Adhesives DP6330NS



[Product Details](#)



[Regulatory Info/SDS](#)

#### Product Description

3M™ Scotch-Weld™ Multi-Material & Composite Urethane Adhesive DP6330NS is a multi-purpose urethane adhesive for bonding a variety of composites, plastics, metals and wood. It is a high-strength bonder with some flexibility to accommodate thermal expansion and contraction differences with dissimilar material bonding

3M™ Scotch-Weld™ Multi-Material & Composite Urethane Adhesive DP6330NS can replace rivets and screws in attaching composites to other substrates, providing a more aesthetically-pleasing, fatigue-resistant bond line. It also bonds well to most metals without requiring priming.

**Note:** Unless otherwise indicated, all properties measured at 72°F (22°C).

#### Product Features

- Ability to bond most composites and dissimilar substrates
- Primerless to most surfaces
- Non-sag formulation resists running and slumping of adhesive
- 3M™ Scotch-Weld™ Multi-Material & Composite Urethane Adhesive DP6330NS meets the following OEM strength requirements:
  - o Freightliner; Standard No. 49-00093 Revision C
  - o PACCAR; Specification No. CMT0038
- Excellent water and humidity resistance, very good chemical resistance.
- Solvent-free adhesive system
- Convenient hand-held applicator
- Room temperature cure
- Cure can be accelerated with heat
- Available in bulk

**Note:** The data in this sheet were generated using the 3M™ EPX™ Applicator System equipped with an EPX static mixer, according to manufacturer's directions. Thorough hand-mixing will afford comparable results.

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Typical Uncured Physical Properties

Attribute Name	Value
Mix Ratio by Weight (B:A)	1:1.09
Mix Ratio by Volume (B:A)	1:1
Viscosity	Non-sag paste

Attribute Name	Temperature	Value
Base Color		Green
Accelerator Color		Off-White
Base Density		1.2 — 1.32 g/cm <sup>3</sup> (10 — 11 lb/gal)
Accelerator Density		1.26 — 1.38 g/cm <sup>3</sup> (10.5 — 11.5 lb/gal)
Base Viscosity	27 °C (80 °F)	15,000-35,000 cP <sup>1</sup>
Accelerator Viscosity	27 °C (80 °F)	9,000-25,000 cP <sup>1</sup>

<sup>1</sup> Viscosity measured using Brookfield RTV, spindle #7, 20 RPM

## Typical Mixed Physical Properties

Attribute Name	Temperature	Value
Worklife		15 min <sup>1</sup>
Open Time		30 min <sup>2</sup>
Time to Handling Strength	23 °C (73 °F)	2 h <sup>3</sup>

<sup>1</sup> Maximum time that adhesive can remain in a static mixing nozzle and still be expelled without undue force on the applicator. Cure times are approximate and depend on adhesive temperature.

<sup>2</sup> Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend on adhesive temperature. Hotmelts: The approx. bonding range of a 3.2 mm (1/8 in) bead of molten adhesive on a non-metallic surface.

<sup>3</sup> Minimum time required to achieve 0.3 MPa (50 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

## Typical Physical Properties

Attribute Name	Value
Full Strength	168 h

## Typical Cured Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Shore D Hardness	ASTM D2240	70

## Typical Performance Characteristics

### Overlap Shear Strength

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Substrate	Surface Prep	Value
Aluminum	MEK/Abrade/MEK	18 MPa (2612 lb/in <sup>2</sup> ) (CF) <sup>1</sup>
Cold Rolled Steel	MEK/Abrade/MEK	14.3 MPa (2068 lb/in <sup>2</sup> ) (AF) <sup>1</sup>
Stainless Steel	MEK/Abrade/MEK	20.3 MPa (2946 lb/in <sup>2</sup> ) (CF) <sup>1</sup>
Galvanized Steel	MEK/Abrade/MEK	11.7 MPa (1700 lb/in <sup>2</sup> ) (AF) <sup>1</sup>
Polycarbonate (PC)	MEK/Abrade/MEK	7.6 MPa (1100 lb/in <sup>2</sup> ) (SF) <sup>1</sup>
Fiber-Reinforced Plastic	IPA Wipe/Abrade/IPA Wipe	6.9 MPa (1000 lb/in <sup>2</sup> ) (SF) <sup>1</sup>
ABS	MEK/Abrade/MEK	4.5 MPa (650 lb/in <sup>2</sup> ) (AF) <sup>1</sup>
Glass Filled Epoxy LW	IPA Wipe/Abrade/IPA Wipe	20.7 MPa (3000 lb/in <sup>2</sup> ) (SF) <sup>1</sup>
Glass Filled Polyester	IPA Wipe/Abrade/IPA Wipe	8.3 MPa (1200 lb/in <sup>2</sup> ) (SF) <sup>1</sup>

<sup>1</sup> 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber.

Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)

Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Substrate: Etched Aluminum

Temperature: 23 °C (73 °F)

Dwell Time: 24 h

Attribute Name	Test Method	Value
Bell Peel	ASTM D3167	53 N/cm (30 lb/in) <sup>1</sup>

<sup>1</sup> 25 mm (1 in) wide samples; 0.4 mm (0.017 in) bond line thickness. The testing jaw separation rate was 15 cm/min (6 in/min). The bonds are made with 1.6 mm (0.064 in) bonded to 0.64 mm (0.025 in) thick adherends.

## Electrical and Thermal Properties

Attribute Name	Value
Glass Transition Temperature (Tg)	41 °C (106 °F) <sup>1</sup>

<sup>1</sup> Measured at six weeks via DMA

## Handling/Application Information

### Directions for Use

1. To obtain the highest strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength and environmental aging resistance desired by user. For suggested surface preparations on common substrates, see the section on surface preparation.

#### 2. Mixing

##### For Duo-Pak Cartridges

Store cartridges with cap end up to allow any air bubbles to rise towards the tip. To use, simply insert the cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Then remove the cap and expel a small amount of adhesive to ensure material flows freely from both sides of cartridge. For automatic mixing, attach an EPX mixing nozzle to the cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after obtaining a uniform color.

##### For Bulk Containers

Mix thoroughly by weight or volume in the proportion specified on the product label or in the typical uncured properties section. Mix approximately 15 seconds after obtaining a uniform color.

3. Apply adhesive and join surfaces within the open time listed for the specific product. Larger quantities and/or higher temperatures will reduce this working time.

4. Allow adhesive to cure at 60°F (16°C) or above until completely firm. Applying heat up to 200°F (93°C) will increase cure speed.

5. Keep parts from moving during cure. Apply contact pressure or fixture in place if necessary. Optimum bond line thickness ranges from 0.005 to 0.020 inch; shear strength will be maximized with thinner bond lines, while peel strength reaches a maximum with thicker bond lines.

6. Excess uncured adhesive can be cleaned up with ketone type solvents.\*

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

### Surface Preparation

3MTM Scotch-Weld™ Multi-Material & Composite Urethane Adhesive DP6330NS is designed to be used on composites, metal, wood, and most plastic surfaces. The following cleaning methods are suggested for common surfaces:

#### Steel:

1. Wipe free of dust and dirt with pure solvent such as acetone or isopropyl alcohol.\*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with clean solvent to remove loose particles.\*
4. For best results, apply a primer to bare steel before bonding, such as an epoxy-based primer or 3M™ Adhesion Promoter 111.

#### Aluminum:

1. Wipe free of dust and dirt with pure solvent such as acetone or isopropyl alcohol.\*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with clean solvent to remove loose particles.\*

#### Plastics/Rubbers/Paints/Coatings:

1. Wipe with isopropyl alcohol.\*
2. Abrade using fine grit abrasives.
3. Wipe with isopropyl alcohol.\*

#### Glass:

1. Solvent wipe surface using acetone or MEK.\*
2. Apply a thin coating of a silane adhesion promoter to the glass surfaces to be bonded and allow to dry completely before bonding.

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

## **Industry Specifications**

Freightliner; Standard No. 49-00093 Revision C  
PACCAR; Specification No. CMT0038  
[EN 45545 test report details \(ISO 5659-2, ISO 5660-1, ISO 5658-2\)](#)

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

## **Precautionary Information**

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

### **Automotive Disclaimer:**

**Intended Use:** 3M™ Scotch-Weld™ Multi-Material & Composite Urethane Adhesive DP6310NS and DP6330NS are intended for use in general industrial bonding applications to metals, high surface energy plastics, and composites, when used in accordance with the guidance provided by 3M in this Technical Data Sheet and other product instructions. Since there are many factors that can affect a product's use, the customer remains responsible for determining whether the 3M product is suitable and appropriate for the customer's specific application and system, including customer conducting an appropriate risk assessment and evaluating the 3M product in customer's application and system.

**Restricted Use:** 3M advises against the use of this 3M product in any application other than the stated intended use(s), since other applications have not been evaluated by 3M and may result in an unsafe or unintended condition.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M, Scotch-Weld and EPX are trademarks of 3M Company.  
©3M 2024 (9/24)