



# Technical Data Sheet

## 3M™ Scotch-Weld™ Non-Flammable Instant Adhesive Activator AC09



[Product Details](#)



[Regulatory Info/SDS](#)

### **Product Description**

3M™ Scotch-Weld™ Instant Adhesive Activators and Primers are liquid chemical products used in conjunction with 3M™ Scotch-Weld™ Instant Adhesives.

3M™ Scotch-Weld™ Instant Adhesive Activators AC09, AC11, AC113, and AC452 are activators that promote very fast curing that may be useful for the fast cure of thick bond lines and in bonding situations where the absorption of a lower viscosity cyanoacrylate into a porous substrate needs to be curtailed. These activators may also be used to “fillet-cure” Scotch-Weld cyanoacrylates and to cure adhesives outside the joint. They primarily differ in their solvent base.

**Note:** These products should be tested on substrates before use since their overspray or excess may attack certain substrates (especially some plastics) causing unsightly effects.

### **Product Features**

3M™ Scotch-Weld™ Instant Adhesive Activator AC09 is a fluorinated solvent based activator that is non-flammable.

### **Technical Information Note**

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### **Typical Uncured Physical Properties**

Attribute Name	Value
Color	Clear <sup>1</sup>
Viscosity	1 cP <sup>2</sup>

<sup>1</sup> Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

<sup>2</sup> Viscosity measured by Brookfield Viscometer RVT Spindle #1 @ 30 rpm

### **Typical Physical Properties**

Attribute Name	Value
Appearance	Liquid
Solvent Resistance	Fluorinated Ether
Specific Gravity	1.4 g/mL

### **Handling/Application Information**

#### **Directions for Use**

1. Apply activator by wipe, brush, or pump spray.
2. Allow activator's solvent to evaporate completely.
3. Apply cyanoacrylate adhesive within one minute of solvent drying.
4. Reapply activator if there is a delay greater than one minute between activator drying and cyanoacrylate dispensing.

#### **Surface Preparation**

Prepare bonding surfaces according to Surface Preparation recommendations for the cyanoacrylate that will be used.

### **Storage and Shelf Life**

Store product in cool, dry area out of direct sunlight. Product retains its performance and properties for 21 months from date of manufacture when stored at 60° to 80°F (16° to 27°C) in the original unopened container.

## **Precautionary Information**

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

## **Automotive Disclaimer**

**Select Automotive Applications:** This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a quality system registered to ISO 9001 standards.

3M  
Industrial Adhesives and Tapes Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550

3M and Scotch-Weld are trademarks of 3M Company.  
©3M 2022 (5/22)