



# **Technical Data Sheet**

3M<sup>™</sup> Scotch-Weld<sup>™</sup> Urethane Adhesive DP620NS Black

**English-US** Last Revision Date: April, 2025

Supersedes: September, 2024





Product Details

Regulatory Info/SDS

# **Product Description**

3M™ Scotch-Weld™ Urethane Adhesive DP620NS is a black, rapid setting, two-component polyurethane. It is packaged as 1:1 ratio liquids in a duo-pak cartridge. With the squeeze of the trigger, the components are automatically mixed and easily dispensed as a bubble-free non-sag paste.

## **Product Features**

- Medium open time
- 1:1 Mix Ratio
- · Bonds to a wide variety of substrates
- Easy Mixing, Non-Sag formulationLow Temperature Flexibility
- Low shrinkage

## **Technical Information Note**

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

# **Typical Uncured Physical Properties**

Attribute Name	Value
Color	Black <sup>1</sup>
Mix Ratio by Volume (B:A)	1:1
Mix Ratio by Weight (B:A)	1:1

Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

Attribute Name	Temperature	Value
Base Color		Clear Yellowish
Accelerator Color		Opaque Black
Base Density		1.08 - 1.12
Accelerator Density		1.14 - 1.19
Base Viscosity	23 °C (73 °F)	3000 — 6000 cP <sup>1</sup>
Accelerator Viscosity	23 °C (73 °F)	1000 — 5000 cP <sup>1</sup>

<sup>&</sup>lt;sup>1</sup> Brookfield CP #52 @ 50 rpm

# **Typical Mixed Physical Properties**

Attribute Name	Temperature	Value	
Open Time		20 min <sup>1</sup>	
Worklife, 10g mixed	23 °C (73 °F)	20 min	
Time to Handling Strength	23 °C (73 °F)	4 h <sup>2</sup>	

Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend on adhesive temperature. Hotmelts: The approx. bonding range of a 3.2 mm (1/8 in) bead of molten adhesive on a non-metallic

Minimum time required to achieve 0.3 MPa (50 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

# **Typical Physical Properties**

A	Attribute Name	Value
C	Cured Color	Black

# **Typical Cured Characteristics**

Attribute Name	Test Method	Temperature	Test Condition	Value
Modulus	ASTM D638, ISO 527	23 °C (73 °F)		903 MPa (131000
Modulus	A31M D030, 130 327	25 C (75 1)		lb/in²)
Strain at Break	ASTM D638, ISO 527	23 °C (73 °F)		110 %
Tomporatura Banga			Continuous	-51-121 °C (-60-250
Temperature Range			Continuous	°F)
Shore D Hardness	ASTM D2240	23 °C (73 °F)		50

# **Typical Performance Characteristics**

# **Overlap Shear Strength**

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Substrate	Surface Prep	Value
Aluminum	MEK/Abrade/MEK	19.9 MPa (2880 lb/in²) <sup>1</sup>
Cold Rolled Steel	MEK/Abrade/MEK	11.7 MPa (1700 lb/in²) <sup>1</sup>
ABS	IPA Wipe/Abrade/IPA Wipe	4.34 MPa (630 lb/in²) <sup>1</sup>
Polycarbonate (PC)	IPA Wipe/Abrade/IPA Wipe	2.96 MPa (430 lb/in²) <sup>1</sup>
Acrylic (PMMA)	IPA Wipe/Abrade/IPA Wipe	2.76 MPa (400 lb/in²) <sup>1</sup>
Fiber-Reinforced Plastic	IPA Wipe/Abrade/IPA Wipe	4.83 MPa (700 lb/in²) <sup>1</sup>
Polyvinyl chloride (PVC)	IPA Wipe/Abrade/IPA Wipe	3.3 MPa (480 lb/in²) <sup>1</sup>

<sup>25</sup> mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber. Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil) Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Substrate: Aluminum Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Bell Peel	ASTM D3167	53 N/cm (30 lb/in) <sup>1</sup>

<sup>25</sup> mm (1 in) wide bonds. 0.5 mm (0.02 in) thick, 1.7 mm (0.065 in) bondline Jaw separation rate 15 mm/min (6 in/min)
AF: adhesive failure CF: cohesive failure SF: substrate failure

Attribute Name	Value
Long Term Temperature Resistance	121 °C (250 °F) <sup>1</sup>
Minimum Long Term Temperature Resistance	-51 °C (-60 °F) ¹

Long Term (day, weeks)

# Handling/Application Information

#### **Directions for Use**

 $3M^{\text{TM}}$  Scotch-Weld Urethane Adhesive DP620NS is supplied in dual syringe plastic duo- pak cartridges as part of the  $3M^{\text{TM}}$  EPX Applicator System. The duo-pak cartridges are supplied in 48.5 ml configuration. To use the EPX cartridge system simply insert the duo-pak cartridge into the EPX applicator. Next, remove the duo-pak cartridge cap and expel a small amount of adhesive to be sure both sides of the duo-pak cartridge are flowing evenly and freely. If simultaneous mixing of Part A and Part B is desired, attach the EPX mixing nozzle to the duo-pak cartridge and begin dispensing the adhesive.

When mixing Part A and Part B manually the components must be mixed in the ratio indicated in the typical uncured properties section of this data sheet. Complete mixing of the two components is required to obtain optimum properties. Two-part mixing/proportioning/dispensing equipment is available for intermittent or production line use. These systems are ideal for line uses because of their variable shot size and flow rate characteristics and are adaptable to most

Apply adhesive to clean, dry surfaces, joint parts and secure until adhesive sets.

## **Surface Preparation**

The following surface preparations were used for substrates described in this Technical Data Sheet.

A. Aluminum Etch

Optimized FPL Etch - 3M (test method C-2803)

1. Alkaline degrease - Oakite 164 solution (9-11 oz./gallon water) at 190°F ± 10°F (88°C ± 5°C) for 10-20 minutes. Rinse immediately in large quantities of cold running water (3M test method C-2802).

2. Optimized FPL Etch Solution (1 liter):

Material Amount

Distilled Water 700 ml plus balance of liter (see below)

Sodium Dichromate 28 to 67.3 grams

Sulfuric Acid 287.9 to 310.0 grams
Aluminum Chips 1.5 grams/liter of mixed solution
To prepare 1 liter of this solution, dissolve sodium dichromate in 700 ml of distilled water. Add sulfuric acid and mix well.
Add additional distilled water to fill to 1 liter. Heat mixed solution to 66 to 71°C (150 to 160°F).

Dissolve 1.5 grams of 2024 bare aluminum chips per liter of mixed solution. Gentle agitation will help aluminum dissolve in about 24 hours.

To FPL etch panels, place them in the above solution at 150 to 160°F (66 to 71°C) for 12 to 15 minutes.

Note: Review and follow precautionary information provided by chemical suppliers prior to preparation of this etch

Rinse immediately in large quantities of clear running tap water.

Dry – air dry approximately 15 minutes followed by force dry at 140°F (60°C) maximum for 10 minutes (minimum).

3. Both surface structure and chemistry play a significant role in determining the strength and permanence of bonded structures. It is therefore advisable to bond or prime freshly primed clean surfaces as soon as possible after surface preparation in order to avoid contamination and/or mechanical damage. Please contact your 3M sales representative for primer recommendations.

B. Oakite Degrease

Oakite 164 solutions (9-11 oz./gallon of water) at 190°F ± 10°F (88°C ± 5°C) for 2 minutes. Rinse immediately in large quantities of cold running water.

C. MEK/Abrade/MEK

Wipe surface with a methyl ethyl ketone (MEK) soaked swab, abrade and wipe with a MEK soaked swab.\* Allow solvent to evaporate before applying adhesive.

D. Isopropyl Alcohol Wipe Only Surface Preparation
Wipe surface with an isopropyl alcohol soaked swab.\* Allow solvent to evaporate before applying adhesive.
E. Isopropyl Alcohol/Abrade/Isopropyl Alcohol Surface Preparation
Wipe surface with an isopropyl alcohol soaked swab, abrade using clean fine grit abrasives, and wipe with an isopropyl alcohol soaked swab.\* Then allow solvent to evaporate before applying adhesive.

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

## **Application Examples**

- Prototype building
- Bonding of dis-similar substrates
- As a combination structural adhesive and sealant in construction applications
- General bonding and sealing (structural sealing)

# **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

#### **Automotive Disclaimer**

**Select Automotive Applications:** 

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www 3M com visit www.3M.com.

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division 3M Center, St. Paul, MN 55144-1000 3M.com/iatd

3M, Scotch-Weld and EPX are trademarks of 3M Company. ©3M 2025 (4/25)